




	BI	REVISED PER ECO-12-007711	26APR2012	KH	MS





284008-3 AS SHOWN




- 1
- MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
POST: COPPER ALLOY, TIN PLATED.
- 2
- SUITABLE FOR 1,6-2,4mm PC BOARD THICKNESS.
- 3
- NOT CUMULATIVE TOLERANCE
- 4
- IMQ CERTIFICATE WITH SURVEILLANCE IN
CONFORMITY WITH IEC 998-1/998-2-1.

121.10	21	2-284008-1
116.02	20	2-284008-0
110.94	19	1-284008-9
105.86	18	1-284008-8
100.78	17	1-284008-7
95.70	16	1-284008-6
90.62	15	1-284008-5
85.54	14	1-284008-4
80.46	13	1-284008-3
75.38	12	1-284008-2
70.30	11	1-284008-1
65.22	10	1-284008-0
60.14	9	284008-9
55.06	8	284008-8
49.98	7	284008-7
44.90	6	284008-6
39.82	5	284008-5
34.74	4	284008-4
29.66	3	284008-3
24.58	2	284008-2
DIM. A		N° OF POS. PART NUMBER



RECOMMENDED PC BOARD LAYOUT



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:
0 PLC ±.3
1 PLC ±.25
2 PLC ±.25
3 PLC ±.
4 PLC ±.
ANGLES ±2

MATERIAL

FINISH

DWN
E. ZANOLINI
02JAN2002

CHK
E. ZANOLINI
02JAN2002

APVD
D. BIEVENOUR
02JAN2002

PRODUCT SPEC
108-20166

APPLICATION SPEC
114-20079

WEIGHT
-

CUSTOMER DRAWING

TE Connectivity

NAME
TERMINAL BLOCK HEADER ASSEMBLY
90 DEGREE WITH EJECTORS
5.08mm PITCH

SIZE
A3

CAGE CODE
00779

DRAWING NO
C-284008

RESTRICTED TO
-

SCALE
3:1

SHEET
1

OF
1

REV
BI