



Ø16.00
[.630 in]



PANEL CUTOUT
MAX. PANEL THICKNESS
14.0mm [.55]

SWITCH FUNCTION	
POS. 1	POS. 2
ON	(ON)
1-3	1-2

(ON) = MOMENTARY



NOTE:

- ALL DIMENSIONS IN MM [INCH]
- GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
- TERMINAL NUMBERS FOR REF ONLY
- CONTACT MATERIAL: SILVER
- RATING: 1A 24VDC
- ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
- INSULATION RESISTANCE: 1,000 MΩ MIN.
- DIELECTRIC STRENGTH: 2,000 VAC MIN. FOR 1 MINUTE
- CONTACT RESISTANCE: 50mΩ MAX. @ 1A 12VDC
- OPERATING TEMP.: -20°C to 55°C
- ▲ DENOTES CRITICAL PARAMETER.
- HARDWARE SUPPLIED: O-RING AND HEXNUT
- INGRESS RATING: IP65
- 2011/65/EU (ROHS) COMPLIANT
- LAMP VOLTAGE: 24V

Ø18.00
[.71 in]




Ø10.40
[.41 in]

Ø12.00
[.472 in]

▲ RING ILLUMINATION
COLOR: BLUE

▲ FLAT ACTUATOR
POLISHED STAINLESS
STEEL

▲ BODY
POLISHED STAINLESS
STEEL



M16x1.0



E-SWITCH®

B	22883	UPDATED RATING TO 1A 24VDC	6/9/17	MJR
A	21545	INITIAL RELEASE	8/8/14	EBP
REV	PCR NO	DESCRIPTION	DATE	BY

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY
TO E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED

TITLE PV3WF2B0SS-345

SCALE 3:2	DATE 8/8/2014	DR EBP	DWG 52-PV3WF2B0SS345	REV B
--------------	------------------	-----------	-------------------------	----------