


ROTARY SWITCH

MODEL

SR2511F-0112-(L)R0B-E9-N-W

SPECIFICATIONS

Rating	AC125V 0.3A
Contact Resistance	50 mΩ Max.
Insulation Resistance	DC500V-100 MΩ Min.
Withstand Voltage	AC500V-1 Minute
Rotation Torque	1.0±0.5 Kg-cm
Sizes (m.m)	As Following Drawings



- NOTE: 1. TOLERANCES UNLESS OTHERWISE SPECIFIED: $\pm 0.4\text{mm}$
 2. ACCESSORY PARTS: $\phi 9$ HEXAGON NUT ONE PIECE & WASHER ONE PIECES
 3. TIMING: NON-SHORTING

Date

2005.09.02

DWN

張
04.9.02
月琴

CHKD

王
04.9.2
茂松

APP'D

楊
2004-9-2
子雲