


FOR DIMENSIONS NOT SPECIFIED, SEE SPEC. HE 17-01



NOTE RoHS INFORMATION

- The "LF" products meet European Union Directives and other country regulations as described in GS-22-008.
- The housing will withstand exposure to 260°C peak temperature for 3.5 seconds in a wave solder application with a 1.6mm minimum thick circuit board. See application notes/procedures if they are available.
- Termination plating spec: 1.27µm Nickel mini, 2.5 to 7.5µm Sn (pure matte)
- Packaging spec: see GS-14-920

TIN LEAD P/N : 86293204113285002E1

LEAD FREE P/N : 86293204113285AALF

GENERAL CHARACTERISTICS

In accordance with specification HE 17-01

SPECIFIC CHARACTERISTICS

PLATING

Mating area: gold thickness 1µ minimum (density = 19.3) over nickel

KEYING

Delivered without any accessory

rev	ecn no	dr	date
D	-	ROU	1992/07/01
E	LS06-0208	LGO	2006/12/16
F	LS07-0157	HLE	2007/06/07
-	-	-	-
-	-	-	-
-	-	-	-

www.fciconnect.com			surface ISO 1302	tolerance std ISO 406 ISO 1101	projection A3	mm
			TOLERANCES UNLESS OTHERWISE SPECIFIED			
Dr	CHAMPION	1990/01/08	ANGULAR	0.X	±0.1	size
Eng	A BALE	1990/01/08	LINEAR	0.XX	±0.1	A3
Chr	A BALE	1990/01/08		0.XXX	±0.1	Scale
Appr	A BALE	1990/01/08	Product family	DIN HPC		3
			ECN		LS07-0157	
			Spec ref		-	
FCI			8629 female connector - 320 contacts			Rev.
			for SEL - ALCATEL :1 AB 00 473 0007			F
			C-8629-0026			sheet 1 of 1

REV F - 2006-04-17