


REV	DOCUMENT	CHANGED BY	CHECK
6	0038225	PRS 04APR08	BLR



NOTE -

 MOUNTING HOLES WILL ACCEPT PINS OR SCREWS OF .087 MAX DIA
ON .375 ±.002 CENTERS

2- TERMINALS ARE PLATED FOR SOLDERING

RELEASE NO.	SR - 12297
REPLACES	

CHARACTERISTICS		ELECTRICAL DATA				DESIGN UNITS: INCH				DRAWN	VK	23 OCT 07		Honeywell				
OPERATING FORCE – – – – 2-5 OZ		CONTACT ARRANGEMENT S P D T				TOLERANCES UNLESS NOTED:				CHECK	RJ	23 OCT 07						
RELEASE FORCE – – – – 1 OZ MIN		30 VOLTS DC RATING				NO PLACE X ± -				THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.				TITLE SWITCH - BASIC				
		SEA LEVEL 50.000 FT				ONE PLACE .X ± 0.030												
DIFFERENTIAL TRAVEL – – – .006 MAX		INDUCTIVE	3 AMP	2.5 AMP	TWO PLACE .XX ± 0.015													
OVERTRAVEL – – – – – .008 MIN		RESISTIVE	5 AMP	5 AMP	THREE PLACE .XXX ± 0.005													
		MAXIMUM INRUSH 24 AMP				FOUR PLACE .XXXX ± -				INTERPRET PER ANSI Y14.5M-1982 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY				SIZE	TYPE	DRAWING NAME		REV
APPROVALS	KEMA CE	5A. 250V ~ T85 1E4			THIRD ANGLE PROJECTION 				B					I	51SM1-T		6	
	UL CSA	5A. 250 VAC		BRAID L4														
										RASTER				SCALE	-	WEIGHT .006 LB MAX	SHEET	1 OF 1