

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

,19 .

© COPYRIGHT 19

BY AMP INCORPORATED. ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

G

14

P

LTR

DESCRIPTION

DATE

DWN

APVD


F

REDRAWN PER 0720-0470-95

23JAN95

LO

ME



1. STAMP AMP LOCATE APPROX AS SHOWN

2. WIRE INSUL DIA, 1.27-2.08 [.050-.082]

3. TONGUE MATL THK, 0.46±0.05 [.018±.002]

|      |              |         |
|------|--------------|---------|
| 1000 | LOOSE PIECE  | 31516   |
| QTY  | PACKAGE TYPE | PART NO |

AMP INCORPORATED  
CUSTOMER SERVICE SYSTEM

MAX RECOMMENDED OPERATING  
TEMPERATURE:

THIS DRAWING IS A CONTROLLED DOCUMENT FOR AMP INCORPORATED.  
IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING  
ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.

DWN L OLMEDA 23JAN95

CHK M ELLIS 23JAN95

APVD S BORTNER 23JAN95

PRODUCT SPEC

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING

AMP Incorporated  
Harrisburg, PA 17105-3608

NAME TERMINAL, RING,  
DIAMOND GRIP,  
WIRE SIZE, 26-22 AWG

SIZE A3 CAGE CODE 00779 DRAWING NO C-31516

SCALE 10:1 SHEET 1 OF 1 REV F

FOR ADDITIONAL  
PRODUCT INFORMATION OR  
COPIES OF DRAWINGS  
AND TECHNICAL DOCUMENTS

PRODUCT INFORMATION CENTER  
1-800-522-6752

FOR APPLICATION  
TOOLING INFORMATION

TOOLING ASSISTANCE CENTER  
1-800-722-1111

FOR ORDER ENTRY

1-800-526-5142


VOLTAGE RATING:

-

CIRCULAR MIL AREA:  
0.10mm<sup>2</sup>-0.41mm<sup>2</sup> [202-810]

STRANDED WIRE

DIMENSIONS:  
mm [in]



MATERIAL  
BODY, CU, SLV, CU PER  
ASTM B152

TOLERANCES UNLESS  
OTHERWISE SPECIFIED:

0 PLC ±-  
1 PLC ±-  
2 PLC ±0.20 [.008]  
3 PLC ±-  
4 PLC ±-  
ANGLES ±-

FINISH  
TIN PLATE  
PER MIL-T-10727