


Dimensions: mm (in.)

**Electrical Specifications:**

- Rating: 50mA/50 VDC
- Contact Resistance: 100mΩ max.
- Insulation Resistance: 100 VDC 1,000MΩ min.
- Dielectric Strength: 250 V AC(50Hz or 60Hz) for 1 minute

Note:

- RoHS Compliant

Mechanical Specifications:

- Operating Temperature: -40° C to +90° C
- Storage Temperature: -40° C to +90° C
- Operating Force: 101-TH71-EV= 130gf, 101-TH72-EV= 300gf
- Operating Force: 130 ± 50g
- Stroke: .50 ± .20 mm

Tactile Switches
101-TH71-EV, 101-TH72-EV

**Mountain
Switch**

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Mountain Switch:](#)

[101-TH71-EV](#) [101-TH72-EV](#)