





REV.	DATE	DESCRIPTION
NC	01/01/05	INITIAL RELEASE
A	03/18/05	UPDATE DRAWING FORMAT
B	08/28/06	REVISE BARREL DIMENSIONS TO 2.24mm ID / 3.20mm O.D.
		CONTACT PIN I.D. TO .60mm/ INSULATOR .50mm I.D. AND 2.2mm O.D.



RECOMMENDED
CABLE STRIPPING DIM'S



NOTE:
1. CRIMPED CONTACT PIN
HEX CRIMP SIZE 1.72 [0.068"]

					UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. DIMENSIONS IN [] ARE IN INCHES AND FOR CUSTOMER REFERENCE ONLY. UNLESS OTHERWISE SPECIFIED TOLERANCES FOR MILLIMETERS ARE: 0.5 – 8mm ± 0.20mm 8 – 30mm ± 0.40mm 30 – 120mm ± 0.50mm UNLESS OTHERWISE SPECIFIED TOLERANCES FOR INCHES ARE: .020 – .315 = ± 0.007" .315 – 1.180 = ± 0.015" 1.180 – 4.724 = ± 0.020" DO NOT SCALE DRAWING	APPROVALS	DATE	Amphenol Connex					
8						DRAWN	G.R.S.						08/28/06
7						CHECKED							
6						ISSUED			PART DESCRIPTION BNC DIRECT SOLDER PLUG (FOR .085”, .086” SEMI RIGID CABLE)				
5						SHEET	1 OF 1						
4						CAD FILE	C:/112/112552.DWG						
3	CONTACT PIN	BRASS	GOLD	1								PART NO. 112552	
2	INSULATOR	TEFLON	NATURAL	1			DWG. NO. 112552.DWG						
1	BODY	BRASS	GOLD	1								REV. B	
	DESCRIPTION	MATERIAL	FINISH	QTY			SIZE A						
												SCALE NA	