

1.0A Surface Mount Rectifier

Features

- Low profile surface mounted package
- Ideal for automated placement
- Glass passivated chip junction
- Low forward voltage drop
- Low leakage current
- High forward surge capability
- High temperature soldering: 250 °C / 10 seconds at terminals
- RoHS compliant



DO-214AC
(SMA)



Mechanical Data

Case:	JEDEC DO-214AC(SMA) molded plastic
Epoxy:	Plastic package has UL flammability classification 94V-0
Terminals:	Solder plated, solderable per MIL-STD-750, Method 2026
Polarity:	Color band denotes cathode end
Weight:	0.002 ounce, 0.064 gram

Maximum Ratings ($T_{Ambient}=25^{\circ}C$ unless noted)

Symbol	Description	S1A	S1B	S1D	S1G	S1J	S1K	S1M	Unit	Conditions
V_{RRM}	Maximum Repetitive Peak Reverse Voltage	50	100	200	400	600	800	1000	V	
V_{RMS}	Maximum RMS Voltage	35	70	140	280	420	560	700	V	
V_{DC}	Maximum DC Blocking Voltage	50	100	200	400	600	800	1000	V	
I_{F(AV)}	Maximum Average Forward Rectified Current	1.0							A	
I_{FSM}	Peak Forward Surge Current	40					30		A	8.3ms single half sine-wave superimposed on rated load (JEDEC Method) T _L =110°C
T_J, T_{STG}	Operating Junction and Storage Temperature Range	-55 to 150							° C	

1.0A Surface Mount Rectifier



S1A - S1M

Electrical Characteristics ($T_{Ambient}=25^{\circ}\text{C}$ unless noted)

Symbol	Description	S1A	S1B	S1D	S1G	S1J	S1K	S1M	Unit	Conditions
V _F	Maximum Instantaneous Forward Voltage	1.1							V	I _F =1.0 A
I _R	Maximum DC Reverse Current at Rated DC Blocking Voltage	1.0					5.0		μA	T _A =25 °C
		50						T _A =125 °C		
T _{rr}	Typical Reverse Recovery Time	1.8							μS	I _F =0.5A, I _R =1.0A, I _{rr} =0.25A
C _J	Typical Junction Capacitance	12							pF	V _R =4V, f=1MHz
R _{θ-JA}	Typical Thermal Resistance	75					85		° C/W	Note 1
R _{θ-JL}		27					30			

Note: (1) Thermal resistance from junction to ambient and from junction to lead mounted on P.C.B. with 0.2 x 0.2" (5.0 x 5.0mm) copper pad areas.
 (2) Single phase half wave, 60 Hz, resistive or inductive load.
 For capacitive load, derate current by 20%.

Typical Characteristics Curves



1.0A Surface Mount Rectifier

S1A - S1M

Fig.3- Typical Instantaneous Forward Characteristics




Fig.4- Typical Reverse Characteristics






Fig.5- Junction Capacitance



1.0A Surface Mount Rectifier


S1A - S1M

Dimensions in inch (mm)



**DO-214AC
(SMA)**

Mounting Pad Layout in inch (mm)



How to contact us:

US HEADQUARTERS

28040 WEST HARRISON PARKWAY, VALENCIA, CA 91355-4162

Tel: (800) TAITRON (800) 824-8766 (661) 257-6060

Fax: (800) TAITFAX (800) 824-8329 (661) 257-6415

Email: taitron@taitroncomponents.com

Http://www.taitroncomponents.com

TAITRON COMPONENTS MEXICO, S.A .DE C.V.

BOULEVARD CENTRAL 5000 INTERIOR 5 PARQUE INDUSTRIAL ATITALAQUIA, HIDALGO C.P.
42970 MEXICO

Tel: +52-55-5560-1519

Fax: +52-55-5560-2190

TAITRON COMPONENTS INCORPORATED E REPRESENTAÇÕES DO BRASIL LTDA

RUA DOMINGOS DE MORAIS, 2777, 2.ANDAR, SALA 24 SAÚDE - SÃO PAULO-SP 04035-001 BRAZIL

Tel: +55-11-5574-7949

Fax: +55-11-5572-0052

TAITRON COMPONENTS INCORPORATED, SHANGHAI REPRESENTATIVE OFFICE

METROBANK PLAZA, 1160 WEST YAN' AN ROAD, SUITE 1503, SHANGHAI, 200052, CHINA

Tel: +86-21-54249942

Fax: +86-21-5424-9931