




VRLA Rechargeable Battery

BC18-12 (BC18-12FR)



Measures

Technology

Values

Innovation

FEATURES

- Maintenance free(no water topping-up required)
- No free acid(Non-spillable battery)
- Can be used in any orientation(excluding used inverted)
- Absorbent Glass Mat technology for efficient gas recombination
- Its design life is up to 5 years in floating application

APPLICATION

- UPS
- Fishing Lights
- Emergency Lights
- Lawn Mowers
- Video Camcorders(VCR)

SPECIFICATIONS

Nominal Voltage	12V	
Nominal Capacity	20 Hour Rate (900mA, 10.5V)	18.0 Ah
	10 Hour Rate (1710mA, 10.5V)	17.1 Ah
	5 Hour Rate (3060mA, 10.5V)	15.3 Ah
	1 Hour Rate (10800mA, 9.30V)	10.8 Ah
Approx. Weight	5620g(12.39lbs.)	
Terminals	B1 (Fitting M5 bolt & nut) , T2 and I1 are optional	
Max. Discharge Current	270 A (5 sec.)	
Max. Charge Current	5.4 A	
Operating Temperature Range	Charge	0°C~40°C(32°F~104°F)
	Discharge	-20°C~50°C(-4°F~122°F)
	Storage	-20°C~40°C(-4°F~104°F)
Self Discharge	< 3% per month (25°C)	
Internal Resistance	≤ 16mΩ (Fully Charged)	




CONTAINER MATERIAL

- BC18-12:
ABS: UL 94-HB (Dark gray color)
- BC18-12FR:
ABS: UL 94-V0 (Light gray color)

 ISO 9001	 ISO 14001
 UL MH19884	 CE C4M20310-2474-E-16
● IEC61056 ● GB/T 19639	● JIS C 8702


OUTER DIMENSIONS mm(inch)

Length (L)	Width (W)	Container Height (H)	Total Height (TH)
181±1.5(7.13±0.06)	76±1.5(2.99±0.06)	166±1.5(6.54±0.06)	166±1.5(6.54±0.06)




TERMINAL TYPE


● Terminal B1



● Terminal T2




● Terminal I1




Terminal Hardware Initial Torque:

B1(2.5Nm±5%),I1(4.0Nm±5%)

BC18-12 (BC18-12FR) discharge characteristics (25°C/77°F)




Battery Charging Characteristics



Charging Procedure

Application	Charging method	Charging Voltage at 25°C (V/cell)	Temperature compensation coefficient of charging voltage (mV/°C/cell)	Max. charging current (CA)	Charging time 0.1CA, 25°C (h)		Temp (°C)
					100% discharge	50% discharge	
For standby power Source	Constant voltage & Constant current charging (with current restriction)	2.25~2.30	-3	0.3	24	20	0~40 (32~104°F)
For cycle service		2.40~2.50	-4	0.3	16	10	

Effect Of Temperature On Long Term Float Life



Constant power discharge characteristics at 25 °C/77 °F

Unit: W

F.V. (V/cell) \ Discharge Time	5 Min	10 Min	15 Min	30 Min	1 Hr	3 Hr	5 Hr	10 Hr	20 Hr
1.80V	651	479	384	229	131.0	52.5	36.2	20.21	10.64
1.75V	753	519	401	237	134.9	53.5	36.7	20.52	10.80
1.70V	800	538	414	242	137.3	54.0	37.0	20.63	10.85
1.65V	836	551	424	246	139.0	54.4	37.1	20.69	10.88
1.60V	864	561	432	249	140.4	54.7	37.2	20.69	10.88

Constant current discharge characteristics at 25 °C/77 °F

Unit: A

F.V. (V/cell) \ Discharge Time	5 Min	10 Min	15 Min	30 Min	1 Hr	3 Hr	5 Hr	10 Hr	20 Hr
1.80V	58.63	42.17	33.38	19.36	11.01	4.372	3.014	1.685	0.886
1.75V	69.11	45.69	34.92	20.10	11.34	4.460	3.060	1.710	0.900
1.70V	73.43	47.33	36.00	20.55	11.54	4.500	3.077	1.718	0.904
1.65V	76.72	48.46	36.83	20.84	11.68	4.532	3.088	1.724	0.907
1.60V	79.26	49.44	37.57	21.05	11.80	4.558	3.097	1.724	0.907

All data shall be changed without prior notice, BB reserves the right to explain and update the information contained hereinto.

Trial A/0 REV. Jun. 2011

USA:
B&B BATTERY(USA) INC.
6415 RANDOLPH ST.COMMERCE, CA,90040 U.S.A.
TEL:1-323-278-1900.1-800-278-8599
FAX:1-323-278-1268
E-Mail:sales@bb-battery.com

CHINA FACTORY:
B.B. BATTERY CO., LTD.
CHENG DONG TRIAL AREA,HUANG GANG,
RAOPING, GUANG DONG,CHINA,515700
TEL:86-768-7601001-2
FAX:86-768-7601469
E-Mail:maggy@bb-battery.com

EUROPE:
B&B BATTERY(EUROPE) B.V.
SUITE 8, HAAKSBERGWEG 33, 1101
BP AMSTERDAM,THE NETHERLANDS
TEL: 31-30-3200190
MOBILE: 886-933896989
E-Mail: gary@bb-battery.com

HONG KONG:
B&B BATTERY(Hong Kong) Co.
TEL:852-2311-4918
FAX:852-2739-1182
E-Mail:bbhk@hkstar.com

JAPAN:
B&B BATTERY(JAPAN) CO., LTD.
1375-11 NARAHARA-MACHI,HACHIOJI,
TOKYO 193-0803,JAPAN.
TEL:81-426-25-6375
FAX:81-426-25-6375
E-Mail:miyata@bb-battery.com

TAIWAN:
B.B. BATTERY(TAIWAN) CO., LTD.
TEL:886-6-502-5150
FAX:886-6-589-8087
E-Mail:kevin@bb-battery.com