





DETAIL1


NOTE:
1.MATERIAL:
HOUSING, HIGH TEMPERATURE POLYMER.
TERMINAL, COPPER ALLOY.
GROUNDING CLIP, COPPER ALLOY.
2.FINISH: TERMINAL:
NICKEL OVERALL THICKNESS 0.5 MICRON MINIMUM,
CONTACT AREA(SEE TABLE):
a. SELECTIVE GOLD 0.1 MICRON MINIMUM OVER
PALLADIUM/NICKEL 0.5 MICRON MINIMUM,
b. SELECTIVE GOLD 0.75 MICRON MINIMUM OVER
NICKEL 0.5 MICRON MINIMUM (FOR P/N:67799-0008),
SOLDER AREA:(SEE TABLE)
a.MATTE TIN /TIN-LEAD 5.0 MICRON MINIMUM
b.GOLD FLASH 0.05 MICRON MINIMUM,
GROUNDING CLIP:
GOLD FLASH OVERALL OVER NICKEL 1.25 MICRON MINIMUM.
3.TERMINAL COPLANARITY 0.08mm MAXIMUM.
4.PRODUCT SPECIFICATION: PS-67799-001.
5.PACKAGE: PK-67799-001.
6.GROUNDING CLIP CONDUCTS WITH TERMINAL NO.1, NO.26.



GROUNDING CLIP



PCB LAYOUT RECOMMEND



HOUSING STOPPER FOR 67799-001*

PLATING TYPE IN SOLDER TAIL	MATTE TIN PLATING		GOLD FLASH PLATING		CONTACT AREA: 30U" GOLD SOLDER TAIL: GOLD FLASH	
HOUSING STOPPER	WITHOUT	WITH	WITHOUT	WITH	WITHOUT	WITH
MATERIAL NO.	67799-0004	67799-0014	67799-0007	67799-0017	67799-0008	67799-0018

REVISED CARRIER TAPE EC NO: S2014-0266 DRWN: ZENG CHKD: JIAN02 APPR: KHL IM L1	DESCRIPTION 2013/09/12 2013/10/22 2013/10/28	QUALITY SYMBOLS F _A =0 F _G =0 F _P =0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	 THIRD ANGLE PROJECTION
				mm	INCH	DRAWN BY BRAD	DATE 2003/02/20	TITLE 50 CKT CF RECEPTACLE SMT TYPE B, OFFSET 0.20MM	
			4 PLACES	± ---	± ---	CHECKED BY WILSON	DATE 2003/02/20		
			3 PLACES	± ---	± ---	APPROVED BY AYIN	DATE 2012/10/26		
			2 PLACES	± 0.25	± ---	molex			
			1 PLACE	± 0.25	± ---				
			0 PLACE	±	±	MATERIAL NO.	DOCUMENT NO. SD-67799-004	SHEET NO. 1 OF 2	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS			SIZE A3	SEE TABLE THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					

10 9 8 7 6 5 4 3 2 1

F

E

D

C

B

A

F


E

D

C

B

A



NOTES:

1. MATERIAL: POIYSTYRENE, THICKNESS: 0.40±0.05mm.
2. COMPONENT LOAD PER 13" REEL: 1,000 PCS.

SEE SHEET 1 EC NO: S2014-0266 DRWN: ZENG CHKD: JIAN02 APPR: KHL IM	DESCRIPTION 2013/09/12 2013/10/22 2013/10/28	QUALITY SYMBOLS FA=0 FG=0 FB=0	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE MM ONLY		SCALE 1:1	DESIGN UNITS METRIC	THIRD ANGLE PROJECTION						
				mm	INCH	DRAWN BY BRAD	DATE 2003/02/20	TITLE 50 CKT CF RECEPTACLE SMT TYPE B,OFFSET 0.20MM							
			4 PLACES	± ---	± ---	CHECKED BY WILSON	DATE 2003/02/20								
			3 PLACES	± ---	± ---	APPROVED BY AYIN		DATE 2012/10/26	molex						
			2 PLACES	± 0.25	± ---	MATERIAL NO.		DOCUMENT NO.						SHEET NO.	
			1 PLACE	± 0.25	± ---	SEE SHEET 1		SD-67799-004						2 OF 2	
			0 PLACE	±	±	SIZE A3		THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION							
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS															