




- 1 HOUSING: LIQUID CRYSTAL POLYMER, COLOR BLACK.
CONTACTS: HIGH RELIABILITY COPPER ALLOY.
GROUND BUSES: BRASS,UNS C26000
- 2 CONTACTS & GROUND BUSES: NICKEL UNDERPLATE ALL OVER,
MATING SURFACE PLATED TO MEET LEVEL 1 PERFORMANCE
REQUIREMENTS OF TE PRODUCT SPECIFICATION 108-1422,
SOLDER TAILS PLATED TIN-LEAD.
- 3 DATE CODE MARKED IN AREA INDICATED ON SIDE OPPOSITE
POSITION #1.
- 4 ONE GROUND BUS WITH 5 TAILS PER EACH MODULE.
- 5 TOLERANCE NON-ACCUMULATIVE.
- 6 FOR STANDARD APPLICATIONS, ORIENTATION HOLE TO BE
Ø.094 ± .002 [2.39 ± 0.05].
FOR SLIP-FIT APPLICATIONS, ORIENTATION HOLE TO BE
Ø.079 ± .001 [2.00 ± 0.03].

4.724[120]	3.000[76.2]	6	3.450[87.63]	3.898[99.01]	4.000[101.6]	266	767120-7
4.094[104]	2.500[63.5]	5	2.950[74.93]	3.398[86.31]	3.500[88.9]	228	767120-6
3.465[88]	2.000[50.8]	4	2.450[62.23]	2.898[73.61]	3.000[76.2]	190	767120-5
3.465[88]	1.500[38.1]	3	1.950[49.53]	2.398[60.91]	2.500[63.5]	152	767120-4
2.835[72]	1.000[25.4]	2	1.450[36.83]	1.898[48.21]	2.000[50.8]	114	767120-3
2.205[56]	.500[12.7]	1	.950[24.13]	1.398[35.51]	1.500[38.1]	76	767120-2
1.732[44]	.000[0]	0	.450[11.43]	.898[22.81]	1.000[25.4]	38	767120-1
F	E	D	C	B	A	NO OF POS	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. GERACE 12-11-98	TE Connectivity					
DIMENSIONS: INCHES		CHK S. STRICKLER 12-11-98						
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD A. MONK 12-11-98	NAME					
0 PLC ± -		PRODUCT SPEC		PLUG ASSEMBLY, .495[12.57] VERTICAL, .025[0.64] CL, GULL WING LEADS, MICTOR				
1 PLC ± -		108-1422						
2 PLC ± -		APPLICATION SPEC						
3 PLC ± .005[0.13]		114-11004		SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
4 PLC ± -		WEIGHT		A1	00779	C=767120	-	
ANGLES		CUSTOMER DRAWING		SCALE		SHEET	OF	REV
1		2		8:1		1	1	C