




F = .000100" PURE TIN. MATTE OVERALL

PROCESSING TEMP: WAVE ONLY

PROCESSING TEMP: 260°C FOR 10 SECS MAX



## SECTION A-A

## STRAIGHT

1. INSULATOR MATERIAL: SEE PART NUMBER CODING
2. CONTACT MATERIAL: SEE PART NUMBER CODING
3. PLATING: SEE PART NUMBER CODING
4. UL FLAMMABILITY RATING: 94V-0
5. VOLTAGE RATING: 750 VAC MINIMUM AT SEA LEVEL.
6. CURRENT RATING: 3 AMPS
7. CONTACT RESISTANCE: 30 MILLIOHMS MAX.
8. INSULATION RESISTANCE: 5000 MEGOHMS MIN.

|  |  |                            |  |  |
|--|--|----------------------------|--|--|
|  |  | PROCESSING TIME FOR 1 MILE |  |  |
|--|--|----------------------------|--|--|

[illegible]

|  |  |  |  |  |  |
|--|--|--|--|--|--|
|  |  |  |  |  |  |
|--|--|--|--|--|--|



**SULLINS**  
CONNECTOR SOLUTIONS

|            |              |
|------------|--------------|
| SCALE: 4:1 | SHEET 1 OF 1 |
|------------|--------------|

