


MATERIAL AND FINISHES:

U.FL (73118-0360) MATED HEIGHT: 2.5MM (.098)
HOUSING: PHOSPHOR BRONZE
FINISH: GOLD

CONTACT: PHOSPHOR BRONZE
FINISH: GOLD

INSULATOR: PBT

CABLE: 1.32 CABLE OR EQUIVALENT



73116-0792	3.625±.125	92.07±3.17	BULK	YES	.335 / 8.50	.177 / 4.50	.079 / 2.00
73116-0791	7.966±.900	202.34±22.86	BULK	NO	.326 / 8.28	.193 / 4.90	.106 / 2.69
73116-0790	32.503±.900	825.58±22.86	BULK	NO	.256 / 6.49	.112 / 2.85	.059 / 1.50
73116-0029	12.503±.225	317.58±5.72	BULK	NO	.256 / 6.49	.112 / 2.85	.059 / 1.50
73116-0028	8.503±.180	215.98±4.57	BULK	NO	.256 / 6.49	.112 / 2.85	.059 / 1.50
73116-0027	12.000±.250	304.80±6.34	SINGLE	YES	.276 / 7.00	.157 / 4.00	.079 / 2.00
73116-0026	9.000±.250	228.60±6.34	SINGLE	YES	.276 / 7.00	.157 / 4.00	.079 / 2.00
73116-0025	6.000±.125	152.40±3.17	SINGLE	YES	.276 / 7.00	.157 / 4.00	.079 / 2.00
73116-0024	3.000±.125	76.20±3.17	SINGLE	YES	.276 / 7.00	.157 / 4.00	.079 / 2.00
73116-0023	12.000±.250	304.80±6.34	BULK	YES	.276 / 7.00	.157 / 4.00	.079 / 2.00
73116-0022	9.000±.250	228.60±6.34	BULK	YES	.276 / 7.00	.157 / 4.00	.079 / 2.00
73116-0021	6.000±.125	152.40±3.17	BULK	YES	.276 / 7.00	.157 / 4.00	.079 / 2.00
73116-0020	3.000±.125	76.20±3.17	BULK	YES	.276 / 7.00	.157 / 4.00	.079 / 2.00
PART NO.	IN	MM	PACKAGING	TINNED	IN / MM	IN / MM	IN / MM
DIM A				YES / NO	DIM B	DIM C	DIM D

CHG: ADDED -0792 EC NO: URF2013-0231 2012/10/08 DRWN:JLEE02 CHKD:SSS 2012/10/08 APPR:JWIENER 2012/10/30 REV DESCRIPTION				QUALITY SYMBOLS ▽=0 ▽=0	GENERAL TOLERANCES (UNLESS SPECIFIED) mm INCH 4 PLACES ± --- ± --- 3 PLACES ± --- ± --- 2 PLACES ± --- ± --- 1 PLACE ± --- ± --- ANGULAR ± 2 °	DIMENSION STYLE MM/IN DRAWN BY DATE JLEE02 2011/08/19 CHECKED BY DATE SSS 2011/08/19 APPROVED BY DATE JWIENER 2011/09/02	SCALE DESIGN UNITS METRIC	THIRD ANGLE PROJECTION	TITLE CA, U.FL TO PIGTAIL, 1.32MM CABLE, H25 EWR-4778, CA-UFL/PIGTAIL	MATERIAL NO. SEE TABLE	DOCUMENT NO. SD-73116-002	SHEET NO. 1 OF 1
					DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	SIZE C	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION					