




Customer Information Sheet


DRAWING No.: D2XXX-01 / D2XXX-21 SHEET 2 OF 2 IF IN DOUBT - ASK (C) NOT TO SCALE THIRD ANGLE PROJECTION ALL DIMENSIONS IN mm




STYLE '1'



STYLE '2'



STYLE '3'



STYLE '4'

NOTES:

- COMPONENTS SUPPLIED IN PLASTIC TUBES 537mm LONG.
- RECOMMENDED MOUNTING HOLE SIZE = $\varnothing 0.80\text{mm}$

HARWIN PART No.	No. OF WAYS	STYLE	DIM 'A'	DIM 'B'	DIM 'C'	DIM 'D'
D2806-XX	6	1	7.6	5.08	7.62	10.02
D2808-XX	8	1	10.1	7.62	7.62	10.02
D2814-XX	14	1	17.7	15.24	7.62	10.02
D2816-XX	16	1	20.3	17.78	7.62	10.02
D2818-XX	18	2	22.8	20.32	7.62	10.02
D2820-XX	20	2	25.3	22.86	7.62	10.02
D2922-XX	22	2	27.8	25.4	7.62	10.02
D2822-XX	22	2	27.8	25.4	10.16	12.6
D2824-XX	24	2	30.4	27.94	15.24	17.64
D2924-XX	24	2	30.4	27.94	7.62	10.02
D2724-XX	24	2	30.4	27.94	10.16	12.6
D2828-XX	28	2	35.5	33.02	15.24	17.64
D2832-XX	32	2	40.6	38.1	15.24	17.64
D2840-XX	40	3	50.8	48.26	15.24	17.64
D2928-XX	28	3	35.5	33.02	7.62	10.02
D2948-XX	48	3	60.9	58.42	15.24	17.64
D2864-XX	64	4	81.2	78.74	22.86	25.4

SPECIFICATIONS:

MATERIAL:
 MOULDING - 30% GLASS FILLED POLYESTER UL94V-0, BLACK
 SHELL - BRASS
 CLIP - BERYLLIUM COPPER
FINISH:
 01 - TIN SHELL, GOLD CLIP
 21 - TIN SHELL, GOLD FLASH
MECHANICAL:
 INITIAL INSERTION FORCE - 3N MAX ($\varnothing 0.43\text{mm}$ GAUGE)
 INITIAL WITHDRAWAL FORCE - 0.5N MIN ($\varnothing 0.43\text{mm}$ GAUGE)
 RETENTION FORCE MEASURED WITH A POLISHED STEEL GAUGE
 DIAMETER $\varnothing 0.40\text{mm}$ AFTER 3 INSERTIONS OF A PIN WITH
 A DIAMETER $\varnothing 0.53\text{mm}$: 0.14N MIN
 MECHANICAL LIFE - 100 CYCLES MIN
ELECTRICAL:
 MAXIMUM WORKING CURRENT (1 TERMINAL) - 1 AMP
 RATED VOLTAGE - 100V RMS / 150V DC
 CONTACT RESISTANCE - 10 MILLIOHMS MAXIMUM
 INSULATION RESISTANCE - 10000 MEGOHMS
 DIELECTRIC STRENGTH - 1000V RMS MIN
TEMPERATURE:
 OPERATING TEMPERATURE - -55°C TO 125°C
 FOR COMPLETE SPECIFICATION, SEE COMPONENT
 SPECIFICATION C004XX (LATEST ISSUE).

ORDER CODE:

SERIES CODE:
(SEE TABLE)

No. OF WAYS:

FINISH:

01 - TIN SHELL/GOLD CLIP

21 - TIN SHELL/GOLD FLASH CLIP

D2XXX-XX

JAE	14	21.03.02	6560
NAME	ISS.	DATE	C/NOTE
APPROVED:			
CHECKED:			
DRAWN:			A LIOTTA
CUSTOMER REF.			
ASSEMBLY DRG.			

HARWIN

HARWIN INC
U.S.A.
TEL: (812) 285 0055
FAX: (812) 285 0056

HARWIN PLC
U.K.
TEL: 023 9237 0451
FAX: 023 9231 4590

HARWIN PTE
SINGAPORE
TEL: 65 7794909
FAX: 65 7793868

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION

TOLERANCES
 X. - $\pm 1\text{mm}$
 XX - $\pm 0.25\text{mm}$
 XXX - $\pm 0.10\text{mm}$
 XXXX - $\pm 0.01\text{mm}$
 ANGLES - $\pm 5^\circ$
 UNLESS STATED

MATERIAL:
 SEE ABOVE
FINISH: SEE ABOVE
 S/AREA: mm²

TITLE:
DIL IC SOCKET
OPEN FRAME

DRAWING NUMBER:
D2XXX-01/D2XXX-21

SHT
2 OF 2