

Distributed by:




www.Jameco.com ♦ 1-800-831-4242

The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 1970746

3.00mm (.118") Pitch Micro-Fit 3.0™ Wire-to-Board Header

43650
Single Row, Vertical
With Solderable Retention Clip



Features and Benefits

- Offset terminal retention for optimum retention to PC board during wave soldering
- Fully polarized to mating receptacle
- Solderable retention clip provides optimum retention to PCB
- Surface Mount Compatible

Reference Information

Product Specification: PS-43650
Packaging: Tray
UL File No.: E29179
CSA File No.: LR19980A
TUV License No.: R72040445
Mates With: 43645
Designed In: Millimeters

Electrical

Voltage: 250V
Current: 5.0A max.
Contact Resistance: 10 milliohms max.
Dielectric Withstanding Voltage: 1500V AC
Insulation Resistance: 1000 Megohms min.


Physical

Housing: LCP, UL 94V-0
Contact: Brass
Plating: Tin or Gold

Circuits	Order No.			Lead-free
	Tin	15μ" Gold	30μ" Gold	
2	43650-0218	43650-0219	43650-0220	Yes
3	43650-0318	43650-0319	43650-0320	
4	43650-0418	43650-0419	43650-0420	
5	43650-0518	43650-0519	43650-0520	
6	43650-0618	43650-0619	43650-0620	
7	43650-0718	43650-0719	43650-0720	
8	43650-0818	43650-0819	43650-0820	
9	43650-0918	43650-0919	43650-0920	
10	43650-1018	43650-1019	43650-1020	
11	43650-1118	43650-1119	43650-1120	
12	43650-1218	43650-1219	43650-1220	

3.00mm (.118") Pitch Micro-Fit 3.0™ Wire-to-Board Header

43650
Single Row, Vertical, SMT
With Solderable Retention Clip



Features and Benefits

- Solderable retention clip provides optimum retention to PCB
- Fully polarized to mating receptacle
- Tape and reel packaging eliminates handling and provides for higher insertion speeds compared to tray packing or hand assembly

Reference Information

Product Specification: PS-43650
Packaging: Tape and reel
UL File No.: E29179
CSA File No.: LR19980A
TUV License No.: R72040445
Mates With: 43645
Designed In: Millimeters

Electrical

Voltage: 250V
Current: 5.0A max.
Contact Resistance: 10 milliohms max.
Dielectric Withstanding Voltage: 1500V AC
Insulation Resistance: 1000 Megohms min.

Physical

Housing: High temperature LCP, UL 94V-0
Contact: Brass
Plating: Tin or Gold


Circuits	Order No.			Lead-free
	Tin	15μ" Gold	30μ" Gold	
2	43650-0221	43650-0222	43650-0223	Yes
3	43650-0321	43650-0322	43650-0323	
4	43650-0421	43650-0422	43650-0423	
5	43650-0521	43650-0522	43650-0523	
6	43650-0621	43650-0622	43650-0623	
7	43650-0721	43650-0722	43650-0723	

Circuits	Order No.			Lead-free
	Tin	15μ" Gold	30μ" Gold	
8	43650-0821	43650-0822	43650-0823	Yes
9	43650-0921	43650-0922	43650-0923	
10	43650-1021	43650-1022	43650-1023	
11	43650-1121	43650-1122	43650-1123	
12	43650-1221	43650-1222	43650-1223	

3.00mm (.118") Pitch Micro-Fit 3.0™ Wire-to-Board Header

43650

**Single Row, Vertical, SMT
With Solderable Fitting Nail**



Features and Benefits

- Solder tabs provide retention to PCB
- Fully polarized to mating receptacle
- Tape and reel packaging eliminates handling and provides for higher insertion speeds compared to tray packing or hand assembly

Reference Information

Product Specification: PS-43650
Packaging: Tape and reel
UL File No.: E29179
CSA File No.: LR19980A
TUV License No.: R72040445
Mates With: 43645
Designed In: Millimeters

Electrical

Voltage: 250V
Current: 5.0A max.
Contact Resistance: 10 milliohms max.
Dielectric Withstanding Voltage: 1500V AC
Insulation Resistance: 1000 Megohms min.

Physical

Housing: High temperature LCP, UL 94V-0
Contact: Brass
Plating: Tin or Gold


Circuits	Order No.			Lead-free
	Tin	15µ" Gold	30µ" Gold	
2	43650-0224	43650-0225	43650-0226	Yes
3	43650-0324	43650-0325	43650-0326	
4	43650-0424	43650-0425	43650-0426	
5	43650-0524	43650-0525	43650-0526	
6	43650-0624	43650-0625	43650-0626	
7	43650-0724	43650-0725	43650-0726	

Circuits	Order No.			Lead-free
	Tin	15µ" Gold	30µ" Gold	
8	43650-0824	43650-0825	43650-0826	Yes
9	43650-0924	43650-0925	43650-0926	
10	43650-1024	43650-1025	43650-1026	
11	43650-1124	43650-1125	43650-1126	
12	43650-1224	43650-1225	43650-1226	

3.00mm (.118") Pitch Micro-Fit 3.0™ Wire-to-Board Header

43650

**Single Row
Right Angle**



Features and Benefits

- Snap-in peg locks header to PCB for optimum retention
- Fully polarized to mating receptacle
- Surface Mount Compatible

Reference Information

Product Specification: PS-43650
Packaging: Tray
UL File No.: E29179
CSA File No.: LR19980
TUV License No.: R72040445
Mates With: 43645
Designed In: Millimeters

Electrical

Voltage: 250V
Current: 5.0A max.
Contact Resistance: 10 milliohms max.
Dielectric Withstanding Voltage: 1500V AC
Insulation Resistance: 1000 Megohms min.


Physical

Housing: High temperature LCP, UL 94V-0
Contact: Brass
Plating: Tin or Gold

Circuits	Order No.			Lead-free
	Tin	15µ" Gold	30µ" Gold	
2	43650-0200	43650-0201	43650-0202	Yes
3	43650-0300	43650-0301	43650-0302	
4	43650-0400	43650-0401	43650-0402	
5	43650-0500	43650-0501	43650-0502	
6	43650-0600	43650-0601	43650-0602	
7	43650-0700	43650-0701	43650-0702	

Circuits	Order No.			Lead-free
	Tin	15µ" Gold	30µ" Gold	
8	43650-0800	43650-0801	43650-0802	Yes
9	43650-0900	43650-0901	43650-0902	
10	43650-1000	43650-1001	43650-1002	
11	43650-1100	43650-1101	43650-1102	
12	43650-1200	43650-1201	43650-1202	

3.00mm (.118") Pitch Micro-Fit 3.0™ Wire-to-Board Header

43650
**Single Row
Right Angle**


Features and Benefits

- "Offset Terminal Retention" for optimum retention to PCB during wave soldering
- Fully polarized to mating receptacle
- Peg feature provides polarization to PCB
- Surface Mount Compatible

Reference Information

Product Specification: PS-43650
Packaging: Tray
UL File No.: E29179
CSA File No.: LR19980
TUV License No.: R72040445
Mates With: 43645
Designed In: Millimeters

Electrical

Voltage: 250V
Current: 5.0A max.
Contact Resistance: 10 milliohms max.
Dielectric Withstanding Voltage: 1500V AC
Insulation Resistance: 1000 Megohms min.

Mechanical


Insertion Force to PCB: 7.5kgf max. (16.5 lb)

Physical

Housing: High temperature LCP, UL 94V-0
Contact: Brass
Plating: Tin or Gold

Circuits	Order No.						Lead-free
	Standard "OTR" Version			Straight Tail Version			
	Tin	15µ" Gold	30µ" Gold	Tin	15µ" Gold	30µ" Gold	
2	43650-0215	43650-0216	43650-0217	43650-0227	43650-0228	43650-0229	Yes
3	43650-0315	43650-0316	43650-0317	43650-0327	43650-0328	43650-0329	
4	43650-0415	43650-0416	43650-0417	43650-0427	43650-0428	43650-0429	
5	43650-0515	43650-0516	43650-0517	43650-0527	43650-0528	43650-0529	
6	43650-0615	43650-0616	43650-0617	43650-0627	43650-0628	43650-0629	
7	43650-0715	43650-0716	43650-0717	43650-0727	43650-0728	43650-0729	
8	43650-0815	43650-0816	43650-0817	43650-0827	43650-0828	43650-0829	
9	43650-0915	43650-0916	43650-0917	43650-0927	43650-0928	43650-0929	
10	43650-1015	43650-1016	43650-1017	43650-1027	43650-1028	43650-1029	
11	43650-1115	43650-1116	43650-1117	43650-1127	43650-1128	43650-1129	
12	43650-1215	43650-1216	43650-1217	43650-1227	43650-1228	43650-1229	

3.00mm (.103") Pitch Micro-Fit 3.0™ Wire-to-Board Header

43650
**Single Row, Right Angle
With Solderable Retention Clip**


Features and Benefits

- Solderable clip provides optimum retention to PCB
- Fully polarized to mating receptacle
- Surface Mount Compatible

Reference Information

Product Specification: PS-43650
Packaging: Tray
UL File No.: E29179
CSA File No.: LR04980A
TUV License No.: R72040445
Mates With: 43645
Designed In: Millimeters

Electrical

Voltage: 250V
Current: 5.0A max.
Contact Resistance: 10 milliohms max.
Dielectric Withstanding Voltage: 1500V AC
Insulation Resistance: 1000 Megohms min.

Mechanical

Insertion Force to PCB: 7.5kgf max. (16.5 lb)

Physical


Housing: High temperature LCP, UL 94V-0
Contact: Brass
Plating: Tin or Gold

Circuits	Order No.			Lead-free
	Tin	15µ" Gold	30µ" Gold	
2	43650-0203	43650-0204	43650-0205	Yes
3	43650-0303	43650-0304	43650-0305	
4	43650-0403	43650-0404	43650-0405	
5	43650-0503	43650-0504	43650-0505	
6	43650-0603	43650-0604	43650-0605	
7	43650-0703	43650-0704	43650-0705	
8	43650-0803	43650-0804	43650-0805	
9	43650-0903	43650-0904	43650-0905	
10	43650-1003	43650-1004	43650-1005	
11	43650-1103	43650-1104	43650-1105	
12	43650-1203	43650-1204	43650-1205	

3.00mm (.118") Pitch Micro-Fit 3.0™ Wire-to-Board Header

43650

**Single Row, Right Angle, SMT
With Solderable Retention Clip**



Features and Benefits

- Solderable retention clip provides optimum retention to PCB
- Fully polarized to mating receptacle
- Tape and reel packaging eliminates handling and provides higher insertion speed compared to tray packing or hand assembly

Reference Information

Product Specification: PS-43650
Packaging: Tape and reel
UL File No.: E29179
CSA File No.: LR19980A
TUV License No.: R72040445
Mates With: 43645
Designed In: Millimeters

Electrical

Voltage: 250V
Current: 5.0A max.
Contact Resistance: 10 milliohms max.
Dielectric Withstanding Voltage: 1500V AC
Insulation Resistance: 1000 Megohms min.

Mechanical

Insertion Force to PCB: 7.5kgf max. (16.5 lb)

Physical

Housing: High temperature LCP, UL 94V-0
Contact: Brass
Plating: Tin or Gold


Circuits	Order No.			Lead-free
	Tin	15µ" Gold	30µ" Gold	
2	43650-0209	43650-0210	43650-0211	Yes
3	43650-0309	43650-0310	43650-0311	
4	43650-0409	43650-0410	43650-0411	
5	43650-0509	43650-0510	43650-0511	
6	43650-0609	43650-0610	43650-0611	
7	43650-0709	43650-0710	43650-0711	

Circuits	Order No.			Lead-free
	Tin	15µ" Gold	30µ" Gold	
8	43650-0809	43650-0810	43650-0811	Yes
9	43650-0909	43650-0910	43650-0911	
10	43650-1009	43650-1010	43650-1011	
11	43650-1109	43650-1110	43650-1111	
12	43650-1209	43650-1210	43650-1211	

3.00mm (.118") Pitch Micro-Fit 3.0™ Wire-to-Board Header

43650

**Single Row, Right Angle, SMT
With Solderable Fitting Nail**



Features and Benefits

- Solder tabs provide retention to PCB
- Fully polarized to mating receptacle
- Tape and reel packaging eliminates handling and provides higher insertion speeds compared to tray packing or hand assembly

Reference Information

Product Specification: PS-43650
Packaging: Tape and reel for robotic placement
UL File No.: E29179
CSA File No.: LR19980A
TUV License No.: R72040445
Mates With: 43645
Designed In: Millimeters

Electrical

Voltage: 250V
Current: 5.0A max.
Contact Resistance: 10 milliohms max.
Dielectric Withstanding Voltage: 1500V AC
Insulation Resistance: 1000 Megohms min.

Physical

Housing: High temperature LCP, UL 94V-0
Contact: Brass
Plating: Tin or Gold

Circuits	Order No.			Lead-free
	Tin	15µ" Gold	30µ" Gold	
2	43650-0212	43650-0213	43650-0214	Yes
3	43650-0312	43650-0313	43650-0314	
4	43650-0412	43650-0413	43650-0414	
5	43650-0512	43650-0513	43650-0514	
6	43650-0612	43650-0613	43650-0614	
7	43650-0712	43650-0713	43650-0714	

Circuits	Order No.			Lead-free
	Tin	15µ" Gold	30µ" Gold	
8	43650-0812	43650-0813	43650-0814	Yes
9	43650-0912	43650-0913	43650-0914	
10	43650-1012	43650-1013	43650-1014	
11	43650-1112	43650-1113	43650-1114	
12	43650-1212	43650-1213	43650-1214	



PRODUCT SPECIFICATION

MICRO-FIT SINGLE ROW CONNECTOR SYSTEM

1.0 SCOPE

This Product Specification covers the 3.00 mm (.118 inch) centerline (pitch) square pin headers when mated with either printed circuit board (PCB) connector or connectors terminated with 20 to 30 AWG wire using crimp technology.

2.0 PRODUCT DESCRIPTION

2.1 PRODUCT NAME AND SERIES NUMBERS

Receptacle: 43645 Female Crimp Terminal: 43030

Plug: 43640 Male Crimp Terminal: 43031

Headers: 43650

Test Plug: 44242 (recommended for continuity testing only)

Other products conforming to this specification are noted on the individual drawings.

2.2 DIMENSIONS, MATERIALS, PLATINGS AND MARKINGS

Housings: Receptacle and Plug - Polyester; Headers - LCP

Crimp Terminals: Phosphor Bronze

Pins: Brass

2.3 SAFETY AGENCY APPROVALS

UL File Number: E29179

CSA: LR19980

TUV: 72040445

3.0 APPLICABLE DOCUMENTS AND SPECIFICATIONS

Test Summary: TS-43045-001

4.0 RATINGS

4.1 VOLTAGE

UL: 43650 and 43645 series: 600 Volts AC RMS or DC

43640 series: 250 Volts AC RMS or DC

TUV: 250 Volts

4.2 CURRENT AND APPLICABLE WIRES (Current is dependent on connector size, contact material, plating, ambient temperature, printed circuit board characteristics and related factors. Actual current rating is application dependent and should be evaluated for each application.)

AWG	Amps	Max. Outside Insulation Diameter
20	5	1.85 mm (.073 inch)
22	5	1.85 mm (.073 inch)
24	4	1.85 mm (.073 inch)
26	3	1.27 mm (.050 inch)
28	2	1.27 mm (.050 inch)
30	1	1.27 mm (.050 inch)

4.2.1 CURRENT FOR TEST PLUG 44242

2.5 Amps Maximum (Pogo pin current capacity)

(Test plugs are for testing purposes only and not intended for continuous use.)

4.3 TEMPERATURE

Operating: - 40°C to + 105°C (Including Terminal Temperature Rise)

Nonoperating: - 40°C to + 105°C

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
L2	EC No: UCP2009-0508 DATE: 2008/08/26	PRODUCT SPECIFICATION MICRO-FIT SINGLE ROW CONNECTORS	1 of 7
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-43650	GAVERILL	SSOUSEK	FSMITH



PRODUCT SPECIFICATION

5.0 PERFORMANCE

5.1 ELECTRICAL REQUIREMENTS

DESCRIPTION	TEST CONDITION	REQUIREMENT
Contact Resistance (Low Level)	Mate connectors: apply a maximum voltage of 20 mV and a current of 100 mA. (Does not include wire resistance)	10 milliohms MAXIMUM [initial]
Contact Resistance @ Rated Current	Mate connectors: apply a maximum voltage of 20 mV at rated current.	30 milliohms MAXIMUM [initial]
Contact Resistance of Wire Termination (Low Level)	Terminate the applicable wire to the terminal and measure wire using a voltage of 20 mV and a current of 100 mA.	5 milliohms MAXIMUM [initial]
Insulation Resistance	Unmate & unmount connectors: apply a voltage of 500 VDC between adjacent terminals and between terminals to ground.	1000 Megohms MINIMUM
Dielectric Withstanding Voltage	Unmate connectors: apply a voltage of {two times the rated voltage plus 1000 volts} VAC for 1 minute between adjacent terminals and between terminals to ground.	No breakdown; current leakage < 5 mA
Capacitance	Measure between adjacent terminals at 1 MHz.	2 picofarads MAXIMUM
Temperature Rise (via Current Cycling)	Mate connectors: measure the temperature rise at the rated current after: 1) 96 hours (steady state) 2) 240 hours (45 minutes ON and 15 minutes OFF per hour) 3) 96 hours (steady state)	Temperature rise: +30°C MAXIMUM

REVISION: L2	ECR/ECN INFORMATION: EC No: UCP2009-0508 DATE: 2008/08/26	TITLE: PRODUCT SPECIFICATION MICRO-FIT SINGLE ROW CONNECTORS	SHEET No. 2 of 7
DOCUMENT NUMBER: PS-43650	CREATED / REVISED BY: GAVERILL	CHECKED BY: SSOUSEK	APPROVED BY: FSMITH



PRODUCT SPECIFICATION

5.2 MECHANICAL REQUIREMENTS

DESCRIPTION	TEST CONDITION	REQUIREMENT
Connector Mate and Unmate Forces	Mate and unmate connector (male to female) at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute. (per circuit)	8.0 N (1.8 lbf) MAXIMUM insertion force & 3.7 N (0.8 lbf) MINIMUM withdrawal force
Terminal Retention Force (in Housing)	Axial pullout force on the terminal in the housing at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute.	24.5 N (5.5 lbf) MINIMUM retention force
Terminal Insertion Force (into Housing)	Apply an axial insertion force on the terminal at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute.	14.7 N (3.3 lbf) MAXIMUM insertion force
Durability	Mate connectors up to 30 cycles at a maximum rate of 10 cycles per minute prior to Environmental Tests.	20 milliohms MAXIMUM (change from initial)
Vibration (Random)	Mate connectors and vibrate per EIA 364-28, test condition VII, Letter D. Test Duration: 15 minutes each axis.	20 milliohms MAXIMUM (change from initial) & Discontinuity < 1 microsecond
Shock (Mechanical)	Mate connectors and shock at 50 g's with $\frac{1}{2}$ sine wave (11 milliseconds) shocks in the $\pm X, \pm Y, \pm Z$ axes (18 shocks total).	20 milliohms MAXIMUM (change from initial) & Discontinuity < 1 microsecond
Wire Pullout Force (Axial)	Apply an axial pullout force on the wire at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute.	MINIMUM pullout force 20 awg: 57.8 N (13.0 lbf) 22 awg: 35.6 N (8.0 lbf) 24 awg: 22.2 N (5.0 lbf) 26 awg: 13.3 N (3.0 lbf) 28 awg: 8.9 N (2.0 lbf) 30 awg: 6.6 N (1.5 lbf)
Normal Force	Apply a perpendicular force.	2.7 N (0.6 lbf) MINIMUM
Pin to Header Retention	Apply axial push force to pin at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute.	13.7 N (3.1 lbf) MINIMUM pushout force
Thumb Latch to Ramp Yield Strength	Full mate and then Unmate the connectors at a rate of 25 ± 6 mm ($1 \pm \frac{1}{4}$ inch) per minute.	68.4 N (15.4 lbf) MINIMUM Yield Strength

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
L2	EC No: UCP2009-0508 DATE: 2008/08/26	PRODUCT SPECIFICATION MICRO-FIT SINGLE ROW CONNECTORS	3 of 7
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-43650	GAVERILL	SSOUSEK	FSMITH



PRODUCT SPECIFICATION

5.3 ENVIRONMENTAL REQUIREMENTS

DESCRIPTION	TEST CONDITION	REQUIREMENT
Thermal Aging	Mate connectors; expose to: 240 hours at $105 \pm 2^{\circ}\text{C}$ OR 500 hours at $85 \pm 2^{\circ}\text{C}$	20 milliohms MAXIMUM (change from initial)
Humidity (Steady State)	Mate connectors: expose to a temperature of $40 \pm 2^{\circ}\text{C}$ with a relative humidity of 90-95% for 96 hours. Note: Remove surface moisture and air dry for 1 hour prior to measurements.	20 milliohms MAXIMUM (change from initial) & Dielectric Withstanding Voltage: No Breakdown at 500 VAC & Insulation Resistance: 1000 Megohms MINIMUM
Solderability	Per SMES-152	Solder coverage: 95% MINIMUM (per SMES-152)
Solder Resistance	A) Wave Solder Process Dip connector terminal tails in solder; Solder Duration: 10 seconds MAX Solder Temperature: 260°C MAX Per ES-40000-5013 B) Convection Reflow Solder Process 235°C MAX Per ES-40000-5013 Parts identified with a blue dot on the primary shipping carton label and all parts with a manufacturing date after 9/1/2007: 260°C MAX Per ES-40000-5013	Visual: No Damage to insulator material
Cold Resistance	Mate connectors: Duration: 96 hours; Temperature: $-40 \pm 3^{\circ}\text{C}$	20 milliohms MAXIMUM (change from initial)

6.0 PACKAGING

Parts shall be packaged to protect against damage during handling, transit and storage per the packaging specifications listed below:

Receptacle and Plug: Bulk Packaged

Headers: PK-70873-0321, PK-70873-0811, PK-70873-07**

REVISION:	ECR/ECN INFORMATION:	TITLE:	SHEET No.
L2	EC No: UCP2009-0508 DATE: 2008/08/26	PRODUCT SPECIFICATION MICRO-FIT SINGLE ROW CONNECTORS	4 of 7
DOCUMENT NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:
PS-43650	GAVERILL	SSOUSEK	FSMITH



PRODUCT SPECIFICATION


7.0 GAGES AND FIXTURES

It is recommended that test plugs (Series 44242) be used for continuity testing of receptacles. Standard mating parts should not be used for harness testing.

8.0 OTHER INFORMATION

8.1 CABLE TIE AND OR WIRE TWIST LOCATION

CKT Sizes	Dim T	Min.
2-4	.500	(12.70)
5-8	.750	(19.10)
9-12	1.000	(25.40)




REVISION: L2	ECR/ECN INFORMATION: EC No: UCP2009-0508 DATE: 2008/08/26	TITLE: PRODUCT SPECIFICATION MICRO-FIT SINGLE ROW CONNECTORS	SHEET No. 5 of 7
DOCUMENT NUMBER: PS-43650	CREATED / REVISED BY: GAVERILL	CHECKED BY: SSOUSEK	APPROVED BY: FSMITH
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A](V.1).DOC			




PRODUCT SPECIFICATION


8.2 STANDARD POLARIZATION FOR HEADERS AND PLUGS (HEADERS ARE SHOWN)




12-CKT.




11-CKT.




10-CKT.




9-CKT.




8-CKT.




2-CKT.




3-CKT.




4-CKT.



5-CKT.



6-CKT.




7-CKT.

REVISION: L2	ECR/ECN INFORMATION: EC No: UCP2009-0508 DATE: 2008/08/26	TITLE: PRODUCT SPECIFICATION MICRO-FIT SINGLE ROW CONNECTORS	SHEET No. 6 of 7
DOCUMENT NUMBER: PS-43650	CREATED / REVISED BY: GAVERILL	CHECKED BY: SSOUSEK	APPROVED BY: FSMITH




PRODUCT SPECIFICATION


8.2 STANDARD POLARIZATION FOR RECEPTACLES




12-CKT.




11-CKT.




10-CKT.




9-CKT.




8-CKT.




2-CKT.




3-CKT.




4-CKT.



5-CKT.




6-CKT.



7-CKT.

REVISION: L2	ECR/ECN INFORMATION: EC No: UCP2009-0508 DATE: 2008/08/26	TITLE: PRODUCT SPECIFICATION MICRO-FIT SINGLE ROW CONNECTORS	SHEET No. 7 of 7
DOCUMENT NUMBER: PS-43650	CREATED / REVISED BY: GAVERILL	CHECKED BY: SSOUSEK	APPROVED BY: FSMITH



CKTS	A	B	C
2	.380 9.65	.118 3.00	.559 14.20
3	.498 12.65	.236 6.00	.677 17.20
4	.616 15.65	.354 9.00	.795 20.20
5	.734 18.64	.472 12.00	.913 23.20
6	.852 21.64	.591 15.00	1.031 26.20
7	.970 24.64	.709 18.00	1.150 29.20
8	1.088 27.64	.827 21.00	1.268 32.20
9	1.206 30.63	.945 24.00	1.386 35.20
10	1.325 33.66	1.063 27.00	1.504 38.20
11	1.443 36.65	1.181 30.00	1.622 41.20
12	1.561 39.65	1.299 33.00	1.740 44.20

	FINISH A	FINISH B	FINISH C
CKTS	MATERIAL NO:	MATERIAL NO:	MATERIAL NO:
02	43650-0212	43650-0213	43650-0214
03	43650-0312	43650-0313	43650-0314
04	43650-0412	43650-0413	43650-0414
05	43650-0512	43650-0513	43650-0514
06	43650-0612	43650-0613	43650-0614
07	43650-0712	43650-0713	43650-0714
08	43650-0812	43650-0813	43650-0814
09	43650-0912	43650-0913	43650-0914
10	43650-1012	43650-1013	43650-1014
11	43650-1112	43650-1113	43650-1114
12	43650-1212	43650-1213	43650-1214

ADD NOTES 7 AND 8

EC NO: UCP2008-0037

2007/09/06

2007/09/11

2007/09/12

DRWN:KIPPER

CHKD:SSOUSEK

APPR:FSM TH

REV

QUALITY SYMBOLS

GENERAL TOLERANCES (UNLESS SPECIFIED)

DIMENSION STYLE

SCALE

DESIGN UNITS

THIRD ANGLE PROJECTION

DRAFT WHERE APPLICABLE

SEE CHART

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION

MOLEX INCORPORATED

SD-43650-005

1 OF 1