



	13	12	11	10	9	8	7	6	5	4	3	2	1
	MATERIAL NUMBER	ENGINEERING NUMBER	STUD SIZE	SLOT "S" ± 0.10 ± 0.25	PACKAGING								
J	191640006	SA-235-06	6	$\varnothing.146/3.71$	LOOSE PIECE								
	191640007	SA-235-08	8	$\varnothing.173/4.39$									
	191640008	SA-235-10	10	$\varnothing.198/5.03$									
I	191641155	SA-235-06T	6	$\varnothing.146/3.71$	TAPE MOUNTED								
	191641156	SA-235-08T	8	$\varnothing.173/4.39$									
	191641157	SA-235-10T	10	$\varnothing.198/5.03$									

Ⓒ



PARTS ON TAPE

Ⓒ

NOTES:

1. TERMINAL MATERIAL: COPPER ALLOY
2. FINISH: ELECTRO TIN PLATE.
3. INSULATION MATERIAL: HEAT SHRINKABLE TUBING WITH HOTMELT ADHESIVE INNER LINER. COLOR: RED.
4. MWID = MAXIMUM WIRE INSULATION DIAMETER.
5. PARTS ARE ROHS COMPLIANT.

SALES DRAWING

ADD TAPE NUMBERS		DESCRIPTION	QUALITY SYMBOLS	GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION STYLE		SCALE	DESIGN UNITS	 THIRD ANGLE PROJECTION
					mm	INCH	IN/MM	DATE	---	
EC NO: IPG2016-1045 DRWNG:GROJAS01 CHKD:JMACNEIL APPR:JMACNEIL	2016/01/26 2016/01/26 2016/03/29	REV	 =0  =0	4 PLACES	±---	±---	DRAWN BY	DATE	TITLE SPADE TERMINAL NIAC 22-18 AWG	
				3 PLACES	±---	±---	CHECKED BY	DATE		
				2 PLACES	±---	±---	JLOMASTRO	05/12/13		
				1 PLACE	±---	±---	APPROVED BY	DATE		
						ANGULAR ±---°		RDEROSS	05/12/13	 MOLEX MOLEX INCORPORATED
				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		MATERIAL NO. SEE CHART		DOCUMENT NO. SD-19164-025		SHEET NO. 1 OF 1
				SIZE C THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION						