








| N° POS. | POS. MANCANTI RIF. A DET. UNLOADED POS. REF. TO DETAIL | DIM. "A" | DIM. "B" | DIM. "C" | P.N. STAGNATO (TIN PLTD. VERSION) | DORATO 0.37µm AREA CONTATTO STAGNATO NELLA ZONA A SALDARE   | DORATO 0.76µm AREA CONTATTO STAGNATO NELLA ZONA A SALDARE   | DORATO 1.27µm AREA CONTATTO STAGNATO NELLA ZONA A SALDARE   |
|---------|--------------------------------------------------------|----------|----------|----------|-----------------------------------|-------------------------------------------------------------|-------------------------------------------------------------|-------------------------------------------------------------|
| 12      | -                                                      | 45.9     | 43.59    | 21.4     | 280620-1                          | 280620-2                                                    | 280620-4                                                    | 280620-3                                                    |
| 10      | -                                                      | 37.9     | 35.86    | 17.5     | 280619-1                          | 280619-2                                                    | 280619-4                                                    | 280619-3                                                    |
| 8       | -                                                      | 30.0     | 27.74    | 13.5     | 280618-1                          | 280618-2                                                    | 280618-4                                                    | 280618-3                                                    |
| 6       | DET. "W"                                               | 22.1     | 15.85    | 9.5      | 282468-1                          | -                                                           | -                                                           | -                                                           |
| 6       | -                                                      | 22.1     | 19.81    | 9.5      | 280617-1                          | 280617-2                                                    | 280617-4                                                    | 280617-3                                                    |
| 4       | -                                                      | 14.2     | 11.89    | 5.6      | 280616-1                          | 280616-2                                                    | 280616-4                                                    | 280616-3                                                    |
| 2       | -                                                      | 6.2      | 3.96     | 1.6      | 280615-1                          | 280615-2                                                    | 280615-4                                                    | 280615-3                                                    |
|         |                                                        |          |          |          |                                   | 0.37µm GOLD PLTD ON CONTACT AREA<br>TIN PLTD ON SOLDER TAIL | 0.76µm GOLD PLTD ON CONTACT AREA<br>TIN PLTD ON SOLDER TAIL | 1.27µm GOLD PLTD ON CONTACT AREA<br>TIN PLTD ON SOLDER TAIL |

DET. VIEWS FROM "D"



- 1 EVENTUALE POSIZIONE DEI CONTATTI MANCANTI, VEDERE DETTAGLI (POSITIONS OF UNLOADED CONTACTS, SEE DETAILS)
- 2 TOLLERANZA NON CUMULATIVA (NOT CUMULATIVE TOLERANCE)
- 3 ALLA BASE (AT BASE)
- 4 DIMENSIONE MISURATA ALLA BASE DEI POSTS (POSTS BASE DIMENSION)
- 5 NOT IN PRODUCTION
- 6 P/N OBSOLETO (OBSOLETE P/N)
- 7 PER VERSIONI CARICATE PARZIALMENTE LA DIMENSIONE "B" E' MISURATA TRA IL PRIMO E L'ULTIMO CONTATTO DISPONIBILE (FOR PARTIALLY LOADED VERSION, DIM "B" IS MEASURED BETWEEN FIRST AND LAST AVAILABLE CONTACT)

- 8 SUPERSEDED  
280615-3 SUPERSEDED BY 280615-2  
280616-3 SUPERSEDED BY 280616-2
- 9 OBSOLETE PARTS: OBSOLETE CIS STREAMLINING PER D.RENAUD/D.SINISI
- 10 OBSOLETE

CONTATTI: (CONTACTS) OTTONE (BRASS)

BLOCCHETTO: (HOUSING) POLICARBONATO CARICATO VETRO COLORE VERDE (POLYCARBONATE GLAS FIBER FILLED COLOUR GREEN)

MATERIALE (MATERIAL)

CUSTOMER DRAWING FOR REFERENCE ONLY

DISEGNO PER CLIENTE SOLO PER RIFERIMENTO

THIS DRAWING IS UNPUBLISHED RELEASE FOR PUBLICATION 19

© COPYRIGHT 19 BY TE INCORPORATED, HARRISBURG, PA. ALL INTERNATIONAL RIGHT RESERVED. TE PRODUCTS MAY BE COVERED BY U.S. AND FOREIGN PATENT AND/OR PATENT PENDING

TOLLERANZE, SE NON DIVERSAMENTE SPECIFICATO (TOLERANCES, UNLESS OTHERWISE SPECIFIED)

± 0.4

ANGOLI (ANGLES) ± 2°

DESCRIZIONE (DESCRIPTION) AMP-MODU MOD. I RIGHT ANGLE POST SUPPORT ASS Y

LOC. SIZE NUMERO (DWG NO) REV. FOGLIO (SHEET)

I A3 C-280615 T 1 01 1

| T    | STREAMLINING OF CONTACT BASE MATERIAL CHANGED TO BRASS | SMT            | 09APR 2013  |
|------|--------------------------------------------------------|----------------|-------------|
| S2   | ECR-10-022530                                          | KK             | 29MAY11     |
| S1   | REVISED PER ECO-09-021826                              | KK             | JAN10       |
| S    | OBSOLETE P/N's ET00-0244-97                            | F.B.           | 97          |
| R    | OBSOLETE P/N's 280615-3 AND 280616-3 (ET00-478-96)     | C.P.           | 14 Nov '96  |
| P    | REV. PER EC ET00-0030 -94                              | C.C.           | 16 FEB '94  |
| N    | P.N. 282468-1 WAS 1A92-51085                           | C.C.           | 10-92       |
| M    | ADDED 1A92-51085 CANCELLED 15 POS. PROPOSAL REDRAWN    | C.C.           | 3-92        |
| L    | ADDED 0.76µGOLD VERSION                                | A.B.           | 6-85        |
| J    | ADDED P.C.B. LAYOUT                                    | Z.R.           | 1-83        |
| H    | ADDED FINISH NOTE                                      | A.B.           | 10-82       |
| E    | ADDED DASH 3                                           | R.G.           | 9-78        |
| REV. | REVISIONI (REVISION RECORD)                            | DIS. DATA (DR) | APP. (APP.) |