

ROITHNER LASERTECHNIK

A-1040 WIEN, FLEISCHMANNGASSE 9
TEL: +43 -1- 586 52 43 FAX: +43 -1- 586 41 43
e-mail: rlt@mcb.at http://www.roithner.mcb.at

RLT6615G TECHNICAL DATA




High Power Visible Wavelength Laserdiode

Structure: **AlGaInP**, index guided
Lasing wavelength: **660 nm typ.**
Max. optical power: **15 mW**
Package: **9 mm**


NOTE!
LASERDIODE
MUST BE COOLED!



PIN CONNECTION:



- 1) Laser diode cathode
- 2) Laser diode anode and photodiode cathode
- 3) Photodiode anode



Absolute Maximum Ratings (Tc=25°C)

CHARACTERISTIC	SYMBOL	RATING	UNIT
Optical Output Power	P_o	15	mW
LD Reverse Voltage	$V_{R(LD)}$	2	V
PD Reverse Voltage	$V_{R(PD)}$	30	V
Operation Case Temperature	T_c	-10 .. +50	°C
Storage Temperature	T_{STG}	-40 .. +85	°C

Optical-Electrical Characteristics (Tc = 25°C)

CHARACTERISTIC	SYMBOL	TEST CONDITION	MIN	TYP	MAX	UNIT
Threshold Current	I_{th}		25	40	60	mA
Operation Current	I_{op}	$P_o = 15 \text{ mW}$		50	70	mA
Operating Voltage	V_{op}	$P_o = 15 \text{ mW}$		2.5	2.6	V
Lasing Wavelength	λ_p	$P_o = 15 \text{ mW}$		660	665	nm
Beam Divergence	$\theta_{//}$	$P_o = 15 \text{ mW}$	6	9	16	°
Beam Divergence	$\theta_{\perp}$	$P_o = 15 \text{ mW}$		30		°
Monitor Current	I_m	$P_o = 15 \text{ mW}$		100		μA
Astigmatism	A_s	$P_o = 15 \text{ mW}$		11		μm