

TDK MLCC Datasheet

1

TDK P/N

C0603 C0G 1E 6R2 C T XXXX

1) 2) 3) 4) 5) 6) 7)

Close Window | Print Page

No.	Segment	Detail	Comments
1	Case Size	0.6 X 0.3 mm	See below for dimensions.
2	Temperature Characteristics	0 to +0 C & -30 to +30 ppm/C	Class1 Conforms to EIA 198
3	Rated Voltage	25.0 V	DC
4	Capacitance	6 pF	1.0 +/- 0.2 Vrms 1 MHz +/- 10%
5	Capacitance Tolerance	0 to 0 %	Conforms to IEC 384 - 9
6	Packaging Style	Punched (Paper)Taping [180mm Reel]	EIA 481 Format
7	TDK internal Code	XXXX	(Internal TDK use only)
-	Q	524 min	0.5 - 5.0 Vrms 1 MHz +/- 10%
-	Insulation Resistance	11,521 MOhm min	Apply rated voltage for 60s

Physical Dimensions		Material System																									
Symbol	Dimensions	<table border="1"> <thead> <tr> <th rowspan="2">No</th> <th rowspan="2">Name</th> <th colspan="2">Material</th> </tr> <tr> <th>Class 1</th> <th>Class 2</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>Dielectric</td> <td>CaZr03</td> <td>BaTi03</td> </tr> <tr> <td>2</td> <td>Electrode</td> <td>Ni</td> <td>Ni</td> </tr> <tr> <td>3</td> <td rowspan="3">Termination</td> <td>Cu</td> <td>Cu</td> </tr> <tr> <td>4</td> <td>Ni</td> <td>Ni</td> </tr> <tr> <td>5</td> <td>Sn</td> <td>Sn</td> </tr> </tbody> </table>		No	Name	Material		Class 1	Class 2	1	Dielectric	CaZr03	BaTi03	2	Electrode	Ni	Ni	3	Termination	Cu	Cu	4	Ni	Ni	5	Sn	Sn
No	Name	Material																									
		Class 1	Class 2																								
1	Dielectric	CaZr03	BaTi03																								
2	Electrode	Ni	Ni																								
3	Termination	Cu	Cu																								
4		Ni	Ni																								
5		Sn	Sn																								
L	0.6																										
W	0.3																										
T	0.3																										
B	0.1 min																										
G	0.2 min																										

1 This datasheet is to be used for reference purposes only and is subject to change by TDK without notice. It reflects an overview of the product characteristics/performance for the particular part number. For product specification information, please refer to TDK's general product specification. Please note that this standard part is not designed or warranted to meet any specifications of any intermediate or end user different from or in addition to the specifications set forth in TDK's general product specification. Note also that this standard part has not been specially designed or manufactured for, nor is it intended or warranted for use in, or permitted to be resold for, specialized applications such as aviation, medical, and/or governmental/military applications (collectively, "Excluded Applications").