



基板取付穴推奨寸法 (t=0.8)
RECOMMENDED P.C.BOARD HOLE DIM.(t=0.8)

適合ターミナル 
APPLICABLE TERMINAL 

注記
NOTE

△ 適合ターミナル : 50061-8*00
50080-8*00
△ APPLICABLE TERMINAL : 50061-8*00
50080-8*00



17.5	19.3	51022-1500	15
16.25	18.05	▲ -1400	14
15	16.8	-1300	13
13.75	15.55	-1200	12
12.5	14.3	-1100	11
11.25	13.05	-1000	10
10	11.8	-0900	9
8.75	10.55	-0800	8
7.5	9.3	-0700	7
6.25	8.05	-0600	6
5	6.8	-0500	5
3.75	5.55	-0400	4
2.5	4.3	▼ -0300	3
1.25	3.05	51022-0200	2
B	A	ENG. NO.	検査 CKT.NO.

						材料 MATERIAL ポリエステル、UL94V-0 POLYESTER,UL94V-0	
						仕上げ FINISH	—H—
角度 ANGLE	±3°					適用電線範囲 WIRE RANGE	—H—
30 以上 OVER	±0.3					被覆外径 INS. RANGE	—H—
10 以上 30 未満 OVER UNDER	±0.25						
10 未満 UNDER	±0.2	C	再作図 REDRAWN	(JC70313)	h.i	DRAWN BY '96/05/29 H.IJIMA	CHK'D BY '96/05/29 M.FUKUSHIMA
般公差 GENERAL TOLERANCES	記号 LITER	変更内容 REVISION RECORD	DR.	日付 DATE	S.K	APP'D BY '96/05/29 M.FENOMOTO	尺度 SCALE 10: 1

 MOLEX-JAPAN CO.,LTD.
日本モレックス株式会社


REVISE ONLY ON CAD SYSTEM

TITLE 名称	
----------	--

1.25 BOARD IN CONN. HOUSING

DWG. NO.	SD-51022-**-00
----------	----------------

REV	
C	



材料 MATERIAL	ポリエステル、UL94V-0 POLYESTER,UL94V-0
仕上げ FINISH	—
適用電線範囲 WIRE RANGE	—
被覆外径 INS. RANGE	—

REVISED	2006/04/05
EC NO: J2006-2413	2006/04/06
DRWN:AOYAGI	2006/04/06
CHKD:MTANAKA	2006/04/12
APPR:NUKITA	2006/04/12
DESCRIPTION	
REV	D

GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 UNDER	± 0.2
10 OVER 30 UNDER	± 0.25
30 OVER	± 0.3
ANGULAR	± 3 °
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

DIMENSION STYLE MM ONLY	
DRAWN BY	DATE
H.IIJIMA	1996/05/29
CHECKED BY	DATE
M.FUKUSHIMA	1996/05/29
APPROVED BY	DATE
M.ENOMOTO	1996/05/29
MATERIAL NO.	
SEE CHART	
SIZE	A3

SCALE	10:1
DESIGN UNITS	METRIC
THIRD ANGLE PROJECTION	
1.25 BOARD IN CONN HSG	
MOLEX INCORPORATED	
DOCUMENT NO.	SD-51022-001
SHEET NO.	1 OF 1
THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX INCORPORATED AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION	