CATALOGUE 7

Identification systems

Identification systems

Introduction

Terminal markers

Wire and cable markers

Device markers

Printing systems

Appendix

Weidmüller Service

Index
Search according to Type or order number, Worldwide activities

Identification systems

Terminal markers

Dekafix card, printed
Page B.6

MultiCard Dekafix, WS, ZS
Page B.10

MultiFit
Page B.16

WAD MultiCard
Page B.34

Tag carriers
Page B.35

ELS
Page B.37

Wire and cable markers

SlimFix
Page C.4

SlimFix Clip
Page C.6

TM-I
Page C.8

Transparent sleeves
Page C.10

Wire and cable markers

ELS
Page C.13

TwinMark
Page C.14

WriteOn
Page C.17

CableLine®
Page C.18

Stainless steel markers / Cable ties
Page C.55

Device markers

DMC
Page D.3

ESG
Page D.4

SwitchMark / ClipCard CC
Page D.6

Labels / KSW
Page D.11

Identification systems

Printer systems

PrintJet PRO

Page E.3

MCP Plotter

Page E.4



Thermal transfer printer

Page E.8

Software

M-Print® PRO

Page E.12

Identification systems

Identification systems

Systemised marking	A.2
Materials	A.4
Weidmüller tests and test procedures	A.5

System-based marking for optimized processes

For more than 25 years, the Weidmüller name has stood for innovative and mutually compatible marking and printing systems with all the necessary software and service. As a technological and market leader, we feel it is our duty to move with the times. Our products set standards and play a significant part in helping you to master increasingly complex production processes efficiently and reliably.

The PrintJet PRO is part of this unique concept that unites hardware, software and service that have been developed and synchronised to perfection, offering everything from a single source. All of the elements knit together, offering you all sorts of new options in terms of marking terminals, wires, cables and devices. For big companies or small, the system has just the right modules for your needs and can be fine-tuned to meet specific requirements.

Marker

Weidmüller has set new standards in its field with its MultiCard program. With a choice of 160 versions and the ongoing expansion of its portfolio, which already includes labels, shrinkable tubing and CableLine® markers, it caters for all possible needs. If necessary, we are happy to develop a customised solution for your specific needs too.

- A large selection of markers for connectors, cables, wires and devices
- Also available for terminals and components from other manufacturers
- Print is highly resistant to industrial environment
- We deliver blank, standard, or custom-printed markers according to your needs

Printer

The PrintJet PRO is a groundbreaking printer, setting new standards in terms of performance and innovation. Our range of printing systems also includes the THM Plus for shrinkable tubing and the SMark Laser for printing larger batches quickly and in top quality.

- The right printing system for any marker type
- Laser, ink-jet and thermal-transfer systems
- Very little maintenance and easy to operate
- Diverse range of connection possibilities

Software

Import, edit and manage your data with our software package that consists of modules catering for the entire field of application, from the CAD workplace to implementing cabinet components in close cooperation with leading CAE manufacturers.

- Data transfer from the leading CAE systems
- Import wizard with use of import filter
- Convenient and quick design by means of a wide range of automatic filling functions
- Work easier with individual templates for reoccurring processes

Service

We are here to help you with your requirements at all times, assisting you with everything from installation to training sessions and a whole host of different solutions such as preprinted markers. We break down barriers and are there for you, wherever you are in the world.

- Professional consulting for all marking and printing system questions
- Customized solutions which take your application into account
- Representatives throughout the world with trained specialists on-site
- Online software training via web conference tool

Materials

Material	Description
Polyamide	Polyamide (PA) is one of the most common commercial plastics. The advantages of this material are its very good electrical and mechanical properties, its flexibility and resistance to breakage. Furthermore, owing to its chemical structure, PA achieves good fire resistance even without the use of flame-retardant agents. **Temperature range:** **–40 °C to +100 °C**
PVC	Plasticised PVC is manufactured from polyvinyl chloride and softeners together with additives like stabilisers and lubricants. It is generally transparent but can be dyed any colour. PVC is resistant to corrosive salt solutions and the majority of acids and alkalis. Owing to its chemical structure, raw PVC resists ageing and is not attacked by oxygen or ozone **Temperature range:** **–30 °C to +80 °C**
Polypropylene	Polypropylene (PP) belongs to the polyolefins group of materials. These partially crystallised synthetic materials are distinguished by their good chemical resistance and good electrical properties. PP can be attacked by strongly oxidising chemicals. **Temperature range:** **–40 °C to +80 °C**
Stainless steel	SS 2348 corresponds to Al Si 316 and steel grade 1.4404. This acid-resistant steel contains at least 17 % chromium, 11 % nickel and 2 % molybdenum. The material exhibits good weathering resistance in salt-laden and moist atmospheres and does not corrode in the presence of acids. **Temperature range:** **–80 °C to +500 °C**
Hard PVC	Hard PVC is manufactured from polyvinyl chloride without plasticisers. This is the reason for its high mechanical strength, rigidity and hardness characteristics. In addition, high resistance to chemicals is further distinguishing feature. The absence of plasticisers in hard PVC ensures that the material ‘self-extinguishes’ once it is removed from the flames. **Temperature range:** **–30 °C to +80 °C**
POM	Polyacetal is also known as polyoxymethylene, abbreviated to POM. Its distinguishing characteristics include a high-degree of tensile strength, hardness and stiffness across a wide temperature range. **Temperature range:** **–40 °C to +80 °C**

Weidmüller tests and test procedures

Tests	Test conditions/requirements
Materials test	Flammability in accordance with UL94 Shore A hardness test A – ISO 868 Surface resistance – DIN IEC 60093
Ageing	All marker materials are tested for their ageing resistance. Weidmüller test specification LPV 2216.
Function test of PTFE and PVC wire insulation	Suitability of markers for installation at temperatures between –10 °C to +40 °C. Correct attachment test of the respective marker size for the smallest to the largest wire diameter. Test for symmetry of the marker on the wire
Vibration resistance on carrier	Vibration test, industry, in accordance with: DIN EN 60068-2-6, sinusoidal (3 axes, 10 cycles per axis, acceleration 5g, frequency 10-500 Hz, sweep rate 1 octave/minute) Weidmüller test specification – LPV 2272
Wipe resistance	Resistance of the print against the affects of hand perspiration, machine oil, water and ethanol. A slight alteration is permissible; however, clear identification (legibility) must be guaranteed. In the case of printing subject to VDE 0611 pt 4 (rating plate details), the wipe resistance against water and mineral spirits is to be tested for a period of 15 minutes. Standards: DIN VDE 0611-4 / Pt. 3.1.3 DIN EN 60947-1/ Pt. 5.1 DIN EN 60742, CEI 16-7 Weidmüller test specification – LPV 2166
Scratch resistance	No scratches may be visible on the base or the carrier following the fingernail test. A slight alteration is permissible; however, clear identification must be guaranteed. Weidmüller test specification – LPV 2165
UV light resistance	The function must be guaranteed. The print or colour of the product must be clearly recognisable. Standard: DIN EN ISO 4892-2; Weidmüller test specification – LPV 2216
Chemical resistance of the print	Weidmüller test specification – LPV 2167

Owing to the sheer number of possible applications and environmental influences such as moisture, radiation, gases or heat/cold to which the products can be exposed, Weidmüller accepts no liability for the suitability of products in all customer applications. Suitability tests for specific applications must therefore be carried out by the customer. However, Weidmüller will be happy to provide help and advice upon request.

Due to the different identification system available on the market, we wish to point out that Weidmüller does not guarantee industrial identification products if the Weidmüller components (markers – transparent sleeves – ink/toner/colour ink ribbons – printing systems) are combined with third-party products, unless Weidmüller has explicitly agreed for the purpose of an individual application.

Terminal markers

Terminal markers

Introduction	B.2
Selection table – terminal markers	B.3
DEK card	B.6
DEK MultiCard	B.10
WS / ZS	B.12
MultiFit for use with other makes of terminals	B.16
Cross-reference table	B.20
Terminal marker WAD	B.34
Tag carrier	B.35

Terminal markers

Weidmüller's multitude of different terminal markers enable users to solve virtually every labelling task of all types of wire and cable connectors. Whether multi-character labelling, ready-to-use markers with standard printing or individual, custom markers, whether white or coloured or group designations at terminals, the comprehensive range of Weidmüller products solves every marking task simply, quickly and clearly.

The tables on the following pages show which markers fit the various terminal series. The terminal pitch governs the selection of a marker. For example, a WDU 2.5 terminal has a pitch of 5 mm, the WS 12/5 marker is 12 mm long and suitable for a 5 mm pitch.

Whole blocks of terminals can be marked as a strip using the Weidmüller system. When a terminal with a larger pitch has to be marked (e.g. WDU 16), a smaller marker (e.g. WS 12/5) can be clipped onto it. Most of the markers are compatible with each other.

The two traditional marker series, DEK and WS, are available as ready-to-use markers. And these markers are also available in the MultiCard format for printing by users themselves.

MultiCards can be printed on with the innovative PrintJet, Smark Laser, Plotter MCP Plus or MC-Mobilo printing systems, using M-Print PRO® software.

To see a small selection of the Weidmüller markers, order our bag of samples, order No. **1646670000**.

W series

Z series

I series



P series



Owing to the sheer number of possible applications and environmental influences such as moisture, radiation, gases or heat/cold to which the products can be exposed, Weidmüller accepts no liability for the suitability of products in all customer applications. Suitability tests for specific applications must therefore be carried out by the customer. However, Weidmüller will be happy to provide help and advice upon request.

Due to the different identification system available on the market, we wish to point out that Weidmüller does not guarantee industrial identification products if the Weidmüller components (markers – transparent sleeves – ink/toner/colour ink ribbons – printing systems) are combined with third-party products, unless Weidmüller has explicitly agreed for the purpose of an individual application.

Selection table

Designation	Terminal width	DEK	WS	ZS	SchT 7	SchT 9/4	SchT 14/6	WTS 3/4	WGB 5 / WAD 5	WGB 8 / WAD 8	WAD 12	WAD 27	ZGB 15 / ZGB 30	BZT 1	BZT 2	EM 8/30	Other
ADK 1	**6**	6	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
AKA 4	**6**	6	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
AKE 2.5/AKZ 2.5...	**5**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
AKE 2.5	**5.1**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
AKE 4	**7**	6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
AKZ 1.5...	**5**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
AKZ 1.5-2.5	**5.1**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
AKZ 4	**6.1**	6	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
AKZ 4.../AKB 4...	**6**	6	8/5	-	-	x	-	-	-	-	-	-	-	-	-	-	-
AL 1	**6.5**	6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
ASK 1	**8**	8	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
AST 1-4/35	**6.2**	6	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
AST 5/35	**6.5**	6	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
BZT ZVL 1.5	**5.08**	5	12/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DK 4…	**6**	6	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DKT 4…	**6**	6	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
DLA 2.5...	**6**	6	8/5	-	x	x	x	-	-	-	-	-	-	-	-	-	-
DLD 2.5...	**6**	6	8/5	-	x	x	x	-	-	-	-	-	-	-	-	-	-
DLI 2.5	**6**	6	8/5	-	x	x	x	-	-	-	-	-	-	-	-	-	-
EK 10	**10**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
EK 16	**12**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
EK 2.5…	**6**	6	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
EK 35…	**16**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
EK 4…	**6.5**	6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
EK 6/35	**8**	8	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
EW 15	**9.5**	5	12/5	-	x	x	-	x	-	-	-	-	-	-	-	-	-
EW 15/2	**8**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
EW 35	**8.5**	5	8/5	-	-	-	-	x	-	-	-	-	-	-	-	-	-
EWK	**8.5**	5	8/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
EWK 1	**8.5**	5	8/5	-	-	-	-	x	-	-	-	-	-	-	-	-	-
EWK 2	**8.5**	5	8/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
IAK 1.5N 3L	**5**	5	10/5[2)]	10/5	-	-	-	-	-	-	-	-	x	-	-	-	-
IDK 1.5N	**5**	5	10/5[2)]	10/5	-	x[3)]	-	-	-	-	-	-	-	-	-	-	-
IDK 1.5N/V	**5**	5	10/5[2)]	10/5	-	-	-	-	-	-	-	-	x	-	-	-	-
IDU 1.5 N ...	**5**	5	10/5[2)]	10/5	-	-	-	-	-	-	-	-	x	-	-	-	-
IEK 1.5N...	**5**	5	10/5[2)]	10/5	-	-	-	-	-	-	-	-	x	-	-	-	-
IIK 1.5N...	**5**	5	10/5[2)]	10/5	-	-	-	-	-	-	-	-	x	-	-	-	-
IPE 1.5N...	**5**	5	10/5[2)]	10/5	-	-	-	-	-	-	-	-	x	-	-	-	-
ITR 1.5N...	**5**	5	10/5[2)]	10/5	-	-	-	-	-	-	-	-	x	-	-	-	-
KDKS 1…	**8**	8	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
KMVF…	**6**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
KSKM…	**13**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
KST…	**24-34**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
MAK 2.5/VLI 1.5...	**6**	6	8/5	-	x	x	x	-	-	-	-	-	x	-	-	-	-
NT…	**6-12**	6	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PDK 2.5/4	**5**	5	12/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PDL 4...	**5**	5	12/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PDU 16	**12**	-	10/12	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PDU 2.5/4...	**5**	5	12/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PDU 6/10...	**8**	8	10/8	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PEI 16	**12**	-	10/12	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PNT 16	**12**	-	10/12	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PNT 2.5/4	**5**	5	12/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PNT 6/10	**8**	8	10/8	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PPE 16	**12**	-	10/12	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PPE 2.5/4	**5**	5	12/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PPE 6/10	**8**	8	10/8	-	-	-	-	-	-	-	-	-	-	-	-	-	-
PTR 2.5/4…	**5.1**	5/5	10/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
RSF 1-3…	**8**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
SAK 10…	**10**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
SAK 16…	**12**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
SAK 2.5	**6.1**	6	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAK 2.5/35	**5**	5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAK 35…	**18**	5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAK 4…	**6.5**	6.5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAK 6…	**8**	8	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAK 95/35	**28**	5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAKA 10	**12**	5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAKB 10	**10**	5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAKC 10/35	**12**	6.5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAKC 4/35	**6.5**	6.5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAKD 2.5N	**5**	5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAKG…	**32-54**	5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAKH 35	**18**	6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
SAKH 4-10	**6.5-14**	5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAKK 10..	**11.5**	5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAKK 4..	**8**	6.5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAKR…	**6.5**	6.5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAKS....	**13-28**	5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
SAKT…	**8**	6.5	-	-	x	-	-	-	-	-	-	-	-	-	-	-	-
VWGK 4…	**10**	5/5	12/6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
VWGK 6…	**10**	5/5	12/6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WDK 1.5/R 3.5...	**3.5**	3.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-

1) = WS 10/6 Middle; 2) = WS 10/5 Middle; 3) = SnapMark

Selection table – terminal markers

Designation	Terminal width	DEK	WS	ZS	SchT 7	SchT 9/4	SchT 14/6	WTS 3/4	WGB 5 / WAD 5	WGB 8 / WAD 8	WAD 12	WAD 27	ZGB 15 / ZGB 30	BZT 1	BZT 2	EM 8/30	Other
WDK 2.5 ...	**5**	5	8/5	-	-	x	-	-	-	-	-	-	x	-	-	-	-
WDK 2.5 800V	**6**	6	8/5	-	-	x	-	-	-	-	-	-	x	-	-	-	-
WDK 2.5/BLA R5.08	**5.08**	5	8/5	-	-	-	-	x	-	-	-	-	-	-	-	-	-
WDK 2.5/BLZ R5.08	**5.08**	5	8/5	-	-	-	-	x	-	-	-	-	-	-	-	-	-
WDK 2.5N...	**5**	5	8/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WDK 4N...	**5**	5	8/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WDL 2.5/...	**6**	6	8/5	-	-	-	-	x	-	-	-	-	x	-	-	-	-
WDT 1.5	**6.5**	6.5	8/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WDTR 2.5...	**6.2**	6	8/5	-	-	x	-	-	-	-	-	-	-	-	-	-	-
WDU (WPE) 120/150	**32**	5	10/5	-	-	-	-	x	-	-	-	x	-	-	-	-	-
WDU (WPE) 35 N	**16**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WDU (WPE) 70/95	**27**	5	12/5	-	-	-	-	x	-	-	-	x	-	-	-	-	-
WDU (WPE) 70N	**20.5**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WDU 1.5 LD/BLA	**5.08**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WDU 1.5/BLA	**5.08**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WDU 1.5/BLZ R7.62	**7.62**	5	-	-	-	-	-	-	-	-	-	-	x	-	-	-	-
WDU 1.5/BLZ/5.08	**5.08**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WDU 1.5/BLZ/LD/5.08	**5.08**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WDU 1.5/R 3.5...	**3.5**	3.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WDU 1.5/R/BLA	**5.08**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WDU 1.5/ZZ	**5**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WDU 10 SL	**10**	5	12/5	-	x	x	x	x	x	x	-	-	x	-	-	-	-
WDU 10...	**10**	5	12/5	-	x	x	x	x	x	x	-	-	x	-	-	-	-
WDU 16 (/ZA)	**12**	5	12/5	-	x	x	x	x	-	-	x	-	x	-	-	-	-
WDU 16 N	**12**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WDU 2.5 F	**5**	5	12/5	-	-	-	-	x	-	-	-	-	-	-	-	-	-
WDU 2.5 FF	**5**	5	12/5	-	x	-	-	x	-	-	-	-	-	-	-	-	-
WDU 2.5 N (WDU 1.5)	**5**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WDU 2.5 TC...	**5**	5	12/5	-	x	x	-	x	-	-	-	-	x	-	-	-	-
WDU 2.5...	**5**	5	12/5	-	x	x	x	x	x	-	-	-	x	-	-	-	-
WDU 2.5/1.5/ZZ	**5**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WDU 2.5/BLZ R7.62	**7.62**	5	-	-	-	-	-	-	-	-	-	-	x	-	-	-	-
WDU 240...	**36**	5	12/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WDU 35	**16**	5	12/5	-	x	x	x	x	-	-	x	-	x	-	-	-	-
WDU 4 ...	**6**	6	12/6	-	x	x	x	x	x	-	-	-	x	-	-	-	-
WDU 4N ...	**6**	6	12/6	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WDU 50N	**18.5**	5	12/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WDU 6 ...	**8**	8	12/8	-	x	x	x	x	x	x	-	-	x	-	-	-	-
WDU 95N	**27**	8	15/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WDUL 4	**6**	6	12/6	-	x	x	x	x	x	-	-	-	x	-	-	-	-
WEW 32/1	**12.2**	5	12/5	-	x	x	x	x	-	-	-	x	x	-	-	-	-
WEW 35/1	**12.2**	5	12/5	-	x	x	x	x	-	-	-	-	-	-	-	-	-
WEW 35/2	**8**	8	12/5	-	x	x	x	x	x	x	-	-	-	-	-	x	-
WF 10...	**35.6**	6	15/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WF 12...	**35.6**	6	15/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WF 5...	**13**	6	15/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WF 6...	**19.6**	6	15/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WF 8...	**24.6**	6	15/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WFF 120...	**42**	5	12/6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WFF 185...	**55**	5	12/6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WFF 300...	**55**	5	12/6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WFF 35...	**27**	5	12/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WFF 70...	**32**	5	12/6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WGK 10.../WGKV 10..	**10.1**	5/5	12/6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WGK 16...	**12.1**	5/5	12/6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WGK 25.../WGKV 25...	**15.1**	5/5	12/6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WGK 4.../WGKV 4...	**8.1**	5/8	10/8	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WGK 50...	**18.8**	6/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WGK 95...	**25**	5/8	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WMA 4...	**6**	6	12/6	-	x	x	x	x	x	-	-	-	x	-	-	-	-
WNT 10	**10**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WNT 16 N	**12**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WNT 2.5	**5**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WNT 35 N	**16**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WNT 4	**6**	6	12/6	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WNT 6	**8**	8	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WNT 70 N	**20.5**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WPDB...		-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	LM MT3000 15x9 GE
WPE 1.5/R3.5	**3.5**	3.5	12/3.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WPE 1.5/ZZ	**5**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WPE 10...	**10**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WPE 120	**32**	8	12/6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WPE 16	**12**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WPE 16 N	**12**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WPE 2.5 N (WPE 1.5)	**5**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WPE 2.5...	**5**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WPE 2.5/1.5/ZR	**5**	5	12/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WPE 35...	**16**	5	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WPE 4	**6**	6	12/6	-	x	x	x	x	-	-	-	-	x	-	-	-	-
WPE 4N	**6**	6	12/6	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WPE 50N	**18.5**	8	12/6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WPE 6	**8**	8	12/5	-	x	x	x	x	-	-	-	-	x	-	-	-	-

Designation	Terminal width	DEK	WS	ZS	SchT 7	SchT 9/4	SchT 14/6	WTS 3/4	WGB 5 / WAD 5	WGB 8 / WAD 8	WAD 12	WAD 27	ZGB 15 / ZGB 30	BZT 1	BZT 2	EM 8/30	Other
WPE 95N/120N	**27**	8	15/5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WPO 4	**6**	6	10/6	-	-	-	-	-	-	-	-	-	x	-	-	-	-
WSI 25…	**18**	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-	ESG 6/15
WSI 6…	**8**	8	12/5	-	-	-	-	x	-	-	-	-	x	-	-	-	-
WSI 6/2…	**12**	8	12/6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WTD 6/1	**8**	8	12/5	-	-	-	-	x	-	-	-	-	x	-	-	-	-
WTL 35	**16**	-	12/6														-
WTL 4 …	**6**	6	12/6	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WTL 6/1…	**8**	8	12/8	-	-	-	-	x	-	-	-	-	x	-	-	-	-
WTL 6/2	**8**	8	12/8	-	-	-	-	x	-	-	-	-	x	-	-	-	-
WTL 6/3…	**8**	8	12/8	-	-	-	-	x	-	-	-	-	x	-	-	-	-
WTQ 6/1	**8**	8	12/8	-	-	-	-	x	-	-	-	-	x	-	-	-	-
WTR 2.5 …	**5**	5	12/5	-	-	-	-	x	-	-	-	-	x	-	-	-	-
WTR 35 E	**32**	-	12/6	-	-	-	-	-	-	-	-	-	-	-	-	-	-
WTR 4…	**6**	6	12/6	-	-	-	-	-	-	-	-	-	-	-	-	-	-
ZAP/TW ZIA 1.5/…	**3.8**	3.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
ZDK 1.5…	**3.5**	3.5	12/3.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
ZDK 2.5…	**5**	5	12/5	15/5	-	-	-	x	-	-	-	-	x	-	-	-	-
ZDK 2.5-2…	**5**	5	10/5	10/5	-	-	-	-	-	-	-	-	-	-	-	-	-
ZDK 2.5N…	**5.1**	5/5	10/5	-	-	-	-	-	-	-	-	-	-	-	-	-	ZAD 9/4
ZDK 4/S/…	**6**	6	-	12/6	-	-	-	x	-	-	-	-	x	-	-	-	-
ZDK 6/S/…	**8**	8	-	-	-	-	-	x	-	-	-	-	x	-	-	-	-
ZDKPE 2.5	**5**	5	10/5	10/5	-	-	-	-	-	-	-	-	-	-	-	-	-
ZDL 2.5/…	**5**	5	-	10/5	-	-	-	-	-	-	-	-	x	-	-	-	-
ZDLD 2.5-2…	**5**	5	-	10/5	-	-	-	-	-	-	-	-	x	-	-	-	-
ZDT 2.5 …	**5**	5	10/5	10/5	-	-	-	-	-	-	-	-	-	-	-	-	-
ZDTPE 2.5…	**5**	5	10/5	10/5	-	-	-	-	-	-	-	-	-	-	-	-	-
ZDTR 2.5	**5**	5	12/5	15/5	-	-	-	x	-	-	-	-	x	-	-	-	-
ZDU (ZPE) 10	**10**	5	12/5	15/5	-	x	-	-	-	-	-	-	x	x	x	-	-
ZDU (ZPE) 10/S…	**10**	5	10/5	15/5	-	x	-	-	-	-	-	-	x	x	x	-	-
ZDU (ZPE) 16…	**12**	5	12/5	15/5	-	x	-	x	-	-	-	-	x	x	x	-	-
ZDU (ZPE) 16/S…	**12**	5	10/5	15/5	-	x	-	-	-	-	-	-	x	x	x	-	-
ZDU (ZPE) 2.5 …	**5**	5	12/5	15/5	-	-	-	x	-	-	-	-	x	x	x	-	-
ZDU (ZPE) 2.5-2/…	**5**	5	12/5	15/5	-	-	-	x	-	-	-	-	x	-	-	-	-
ZDU (ZPE) 2.5N…	**5.1**	5/5	10/5	-	-	-	-	-	-	-	-	-	-	-	-	-	ZAD 9/4
ZDU (ZPE) 35…	**16**	5	12/5	15/5	-	-	-	x	-	-	-	-	x	x	x	-	-
ZDU (ZPE) 4…	**6**	6	12/6	12/6	-	-	-	x	-	-	-	-	x	x	x	-	-
ZDU (ZPE) 4-2…	**6**	6	12/6	12/6	-	-	-	-	-	-	-	-	-	-	-	-	-
ZDU (ZPE) 6…	**8**	8	12/8	15/5	-	-	-	x	-	-	-	-	x	x	x	-	-
ZDU (ZPE) 6-2…	**8**	8	12/8	12/6	-	-	-	-	-	-	-	-	-	-	-	-	-
ZDU 1.5…	**3.5**	3.5	12/3.5	-	-	-	-	-	-	-	-	-	-	x	x	-	-
ZDUA (ZPEA) 2.5-2	**5**	5	8/5	15/5	-	-	-	x	-	-	-	-	x	-	-	-	-
ZDUA 2.5-2N	**5**	5	10/5	10/5	-	-	-	-	-	-	-	-	-	-	-	-	-
ZDUB (ZPEB) 2.5-2/…	**5**	5	8/5	15/5	-	-	-	-	-	-	-	-	x	-	-	-	-
ZEI 16	**16**	5	12/5	15/5	-	-	-	x	-	-	-	-	x	-	-	-	-
ZEI 6	**10**	8	12/6	12/6	-	-	-	x	-	-	-	-	x	x	x	-	-
ZEW 35/2	**8**	8	-	-	-	-	-	-	-	-	-	-	-	-	-	x	-
ZIA 1.5 …	**5.08**	5	8/5	15/5	-	-	-	x	-	-	-	-	x	-	-	-	-
ZMAK 2.5	**5**	5	10/5	15/5	-	-	-	-	-	-	-	-	x	-	-	-	-
ZNT 10/S	**10**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
ZNT 16/S	**12**	5	-	-	-	-	-	-	-	-	-	-	-	-	-	-	-
ZNT 2.5/S	**5**	5	10/5	10/5	-	-	-	-	-	-	-	-	-	-	-	-	-
ZNT 4/S	**6**	6	10/6	12/6	-	-	-	-	-	-	-	-	-	-	-	-	-
ZNT 6/S	**8**	8	10/6	12/6	-	-	-	-	-	-	-	-	-	-	-	-	-
ZP 2.5…	**5.1**	5/5	10/5	10/5	-	-	-	-	-	-	-	-	-	-	-	-	-
ZPE 16-2/1 AN	**12**	8	12/6	12/6	-	-	-	-	-	-	-	-	-	-	-	-	-
ZPV 1.5	**5.08**	5	12/5	15/5	-	x	x	x	-	-	-	-	x	-	-	-	-
ZRV 1.5…	**5**	5	8/5	10/5	-	x	x	x	-	-	-	-	x	-	-	-	-
ZSI 2.5…	**8**	8	12/5	15/5	-	-	-	x	-	-	-	-	x	-	-	-	-
ZSI 2.5/2…	**12**	5	12/5	15/5	-	-	-	x	-	-	-	-	x	-	-	-	-
ZSI 6-2/FC	**8**	6	12/6	12/6	-	-	-	-	-	-	-	-	-	-	-	-	-
ZT 2.5 …	**5**	5	10/5	10/5	-	-	-	-	-	-	-	-	-	-	-	-	-
ZTD 6	**8**	8	12/6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
ZTL 6	**8**	8	12/6.5	-	-	-	-	-	-	-	-	-	-	-	-	-	-
ZTPE 2.5 …	**5**	5	10/5	10/5	-	-	-	-	-	-	-	-	-	-	-	-	-
ZTR 2.5…	**5**	5	12/5	15/5	-	-	-	x	-	-	-	-	x	-	-	-	-
ZTR 2.5-2…	**5**	5	14/5	10/5	-	-	-	-	-	-	-	-	-	-	-	-	-

DEK card with printing

The Dekafix marker is the universal marker for terminals and plug-in connectors as well as electronic modules from the Weidmüller product range. Dekafix provides you with a wide range of standard printing options. The system is particularly suitable for short sequences of numbers and is also available with customer specific printing.

- In strips for fast installation
- Large selection of ready-to-use printed markers
- Excellent printing quality thanks to the MC Laser
- Available in 4 widths
- Custom printing also possible



Technical data

Material	Polyamide 66, halogen-free
UL 94 flammability rating	V2
Temperature range	–40 °C to 100 °C
Printing	black

Ordering data

Colour	Available in all colours of the international colour code; for MC on request ● brown ● red ● orange ● yellow ● green ● blue ● violet ● grey ○ white	
Qty	500 pcs	
Pitch	DEK 5 = 5 mm : DEK 6 = 6 mm : DEK 6.5 = 6.5 mm : DEK 8 = 8 mm	
Printing variations	FW = consecutive horizontal	e.g. DEK 5 FW 1-50
	FS = consecutive vertical	e.g. DEK 5 FS 51-100
	FWZ = consecutive horizontal line	e.g. DEK 5 FWZ 1-10
	FSZ = consecutive vertical line	e.g. DEK 5 FSZ 21-30
	GW = identical horizontal	e.g. DEK 5 GW A
	GS = identical vertical	e.g. DEK 5 GS B

No. of characters	horizontal	vertical
DEK 5	max. 3 characters	max. 3 characters
DEK 6	max. 3 characters	max. 3 characters
DEK 6.5	max. 4 characters	max. 3 characters
DEK 8	max. 5 characters	max. 3 characters

Specify colour and characters for special printing

Versions DEK

Type/Print	Order No.
DEK 5 BL NEUTRAL	0473391693
DEK 5 BR NEUTRAL	0473391692
DEK 5 FS 1-50	0473560001
DEK 5 FS 101-150	0473560101
DEK 5 FS 151-200	0473560151
DEK 5 FS 201-250	0473560201
DEK 5 FS 251-300	0473560251
DEK 5 FS 301-350	0473560301
DEK 5 FS 351-400	0473560351
DEK 5 FS 401-450	0473560401
DEK 5 FS 451-500	0473560451
DEK 5 FS 501-550	0473560501
DEK 5 FS 51-100	0473560051
DEK 5 FS 551-600	0473560551
DEK 5 FS 601-650	0473560601
DEK 5 FS 651-700	0473560651
DEK 5 FS 701-750	0473560701
DEK 5 FS 751-800	0473560751
DEK 5 FS 801-850	0473560801
DEK 5 FS 851-900	0473560851
DEK 5 FS 901-950	0473560901
DEK 5 FS 951-999	0473560951
DEK 5 FSZ 1-10	0460660001
DEK 5 FSZ 11-20	0460660011
DEK 5 FSZ 21-30	0460660021
DEK 5 FSZ 31-40	0460660031
DEK 5 FSZ 41-50	0460660041
DEK 5 FSZ 51-60	0460660051
DEK 5 FSZ 61-70	0460660061
DEK 5 FSZ 71-80	0460660071
DEK 5 FSZ 81-90	0460660081
DEK 5 FSZ 91-100	0460660091
DEK 5 FW 1,3,5,...99	1358460000
DEK 5 FW 1-50	0473460001
DEK 5 FW 10-500	0132660010
DEK 5 FW 101-150	0473460101
DEK 5 FW 151-200	0473460151
DEK 5 FW 2,4,...100	1358560000
DEK 5 FW 201-250	0473460201
DEK 5 FW 251-300	0473460251
DEK 5 FW 301-350	0473460301
DEK 5 FW 351-400	0473460351
DEK 5 FW 401-450	0473460401
DEK 5 FW 451-500	0473460451
DEK 5 FW 501-550	0473460501
DEK 5 FW 51-100	0473460051
DEK 5 FW 551-600	0473460551
DEK 5 FW 601-650	0473460601
DEK 5 FW 651-700	0473460651
DEK 5 FW 701-750	0473460701
DEK 5 FW 751-800	0473460751
DEK 5 FW 801-850	0473460801
DEK 5 FW 851-900	0473460851
DEK 5 FW 901-950	0473460901
DEK 5 FW 951-999	0473460951
DEK 5 FW U1-PE1	0133161114
DEK 5 FW U2-PE2	0133161115
DEK 5 FW U3-PE3	0133161116
DEK 5 FW U4-PE4	0133161117
DEK 5 FW U5-PE5	0133161118
DEK 5 FW U6-PE6	0133161119
DEK 5 FW U7-PE7	0133161120
DEK 5 FW U8-PE8	0133161121
DEK 5 FW U9-PE9	0133161122
DEK 5 FW X1-Z1	0133261150
DEK 5 FW X10-Z10	0133261159
DEK 5 FW X2-Z2	0133261151
DEK 5 FW X3-Z3	0133261152
DEK 5 FW X4-Z4	0133261153
DEK 5 FW X5-Z5	0133261154
DEK 5 FW X6-Z6	0133261155
DEK 5 FW X7-Z7	0133261156
DEK 5 FW X8-Z8	0133261157
DEK 5 FW X9-Z9	0133261158
DEK 5 FWZ 1-10	0523060001
DEK 5 FWZ 1-19	0235860000
DEK 5 FWZ 1-9	1572000000
DEK 5 FWZ 11-20	0523060011
DEK 5 FWZ 2-20	0236160000
DEK 5 FWZ 21-30	0523060021
DEK 5 FWZ 21-39	0235960000
DEK 5 FWZ 22-40	0236260000
DEK 5 FWZ 31-40	0523060031
DEK 5 FWZ 41-50	0523060041
DEK 5 FWZ 41-59	0236060000
DEK 5 FWZ 42-60	0236360000

Type/Print	Order No.
DEK 5 FWZ 51-60	0523060051
DEK 5 FWZ 61-70	0523060061
DEK 5 FWZ 71-80	0523060071
DEK 5 FWZ 81-90	0523060081
DEK 5 FWZ 91-100	0523060091
DEK 5 FWZ L1-EIK	0354361203
DEK 5 FWZ L1-PE	0354361187
DEK 5 FWZ U,V,W,N,PE	0558360000
DEK 5 GE NEUTRAL	0473391687
DEK 5 GN NEUTRAL	0473391688
DEK 5 GR NEUTRAL	0473391691
DEK 5 GS A	0132961021
DEK 5 GS B	0132961022
DEK 5 GS C	0132961023
DEK 5 GS D	0132961024
DEK 5 GS E	0132961025
DEK 5 GS F	0132961026
DEK 5 GS G	0132961027
DEK 5 GS H	0132961028
DEK 5 GS I	0132961029
DEK 5 GS J	0132961030
DEK 5 GS K	0132961031
DEK 5 GS L	0132961032
DEK 5 GS M	0132961033
DEK 5 GS N	0132961034
DEK 5 GS O	0132961035
DEK 5 GS P	0132961036
DEK 5 GS PE	0157261187
DEK 5 GS Q	0132961037
DEK 5 GS R	0132961038
DEK 5 GS S	0132961039
DEK 5 GS T	0132961040
DEK 5 GS U	0132961041
DEK 5 GS V	0132961042
DEK 5 GS W	0132961043
DEK 5 GS X	0132961044
DEK 5 GS Y	0132961045
DEK 5 GS Z	0132961046
DEK 5 GS ⏚	0157261202
DEK 5 GS ⏚	0157261203
DEK 5 GW	0576260000
DEK 5 GW 1	0522660001
DEK 5 GW 2	0522660002
DEK 5 GW 3	0522660003
DEK 5 GW 4	0522660004
DEK 5 GW 5	0522660005
DEK 5 GW 6	0522660006
DEK 5 GW 7	0522660007
DEK 5 GW 8	0522660008
DEK 5 GW 9	0522660009
DEK 5 GW 10	0522660010
DEK 5 GW 11	0522660011
DEK 5 GW 12	0522660012
DEK 5 GW 13	0522660013
DEK 5 GW 14	0522660014
DEK 5 GW 15	0522660015
DEK 5 GW 16	0522660016
DEK 5 GW 17	0522660017
DEK 5 GW 18	0522660018
DEK 5 GW 19	0522660019
DEK 5 GW 20	0522660020
DEK 5 GW 21	0522660021
DEK 5 GW 22	0522660022
DEK 5 GW 23	0522660023
DEK 5 GW 24	0522660024
DEK 5 GW 25	0522660025
DEK 5 GW 26	0522660026
DEK 5 GW 27	0522660027
DEK 5 GW 28	0522660028
DEK 5 GW 29	0522660029
DEK 5 GW 30	0522660030
DEK 5 GW 31	0522660031
DEK 5 GW 32	0522660032
DEK 5 GW 33	0522660033
DEK 5 GW 34	0522660034
DEK 5 GW 35	0522660035
DEK 5 GW 36	0522660036
DEK 5 GW 37	0522660037
DEK 5 GW 38	0522660038
DEK 5 GW 39	0522660039
DEK 5 GW 40	0522660040
DEK 5 GW 41	0522660041
DEK 5 GW 42	0522660042
DEK 5 GW 43	0522660043
DEK 5 GW 44	0522660044
DEK 5 GW 45	0522660045

Type/Print	Order No.
DEK 5 GW 46	0522660046
DEK 5 GW 47	0522660047
DEK 5 GW 48	0522660048
DEK 5 GW 49	0522660049
DEK 5 GW 50	0522660050
DEK 5 GW 51	0522660051
DEK 5 GW 52	0522660052
DEK 5 GW 53	0522660053
DEK 5 GW 54	0522660054
DEK 5 GW 55	0522660055
DEK 5 GW 56	0522660056
DEK 5 GW 57	0522660057
DEK 5 GW 58	0522660058
DEK 5 GW 59	0522660059
DEK 5 GW 60	0522660060
DEK 5 GW 61	0522660061
DEK 5 GW 62	0522660062
DEK 5 GW 63	0522660063
DEK 5 GW 64	0522660064
DEK 5 GW 65	0522660065
DEK 5 GW 66	0522660066
DEK 5 GW 67	0522660067
DEK 5 GW 68	0522660068
DEK 5 GW 69	0522660069
DEK 5 GW 70	0522660070
DEK 5 GW 71	0522660071
DEK 5 GW 72	0522660072
DEK 5 GW 73	0522660073
DEK 5 GW 74	0522660074
DEK 5 GW 75	0522660075
DEK 5 GW 76	0522660076
DEK 5 GW 77	0522660077
DEK 5 GW 78	0522660078
DEK 5 GW 79	0522660079
DEK 5 GW 80	0522660080
DEK 5 GW 81	0522660081
DEK 5 GW 82	0522660082
DEK 5 GW 83	0522660083
DEK 5 GW 84	0522660084
DEK 5 GW 85	0522660085
DEK 5 GW 86	0522660086
DEK 5 GW 87	0522660087
DEK 5 GW 88	0522660088
DEK 5 GW 89	0522660089
DEK 5 GW 90	0522660090
DEK 5 GW 91	0522660091
DEK 5 GW 92	0522660092
DEK 5 GW 93	0522660093
DEK 5 GW 94	0522660094
DEK 5 GW 95	0522660095
DEK 5 GW 96	0522660096
DEK 5 GW 97	0522660097
DEK 5 GW 98	0522660098
DEK 5 GW 99	0522660099
DEK 5 GW 100	0522660100
DEK 5 GW 101	0522660101
DEK 5 GW 102	0522660102
DEK 5 GW 103	0522660103
DEK 5 GW 104	0522660104
DEK 5 GW 105	0522660105
DEK 5 GW 106	0522660106
DEK 5 GW 107	0522660107
DEK 5 GW 108	0522660108
DEK 5 GW 109	0522660109
DEK 5 GW 110	0522660110
DEK 5 GW 111	0522660111
DEK 5 GW 112	0522660112
DEK 5 GW 113	0522660113
DEK 5 GW 114	0522660114
DEK 5 GW 115	0522660115
DEK 5 GW 116	0522660116
DEK 5 GW 117	0522660117
DEK 5 GW 118	0522660118
DEK 5 GW 119	0522660119
DEK 5 GW 120	0522660120
DEK 5 GW 121	0522660121
DEK 5 GW 122	0522660122
DEK 5 GW 123	0522660123
DEK 5 GW 124	0522660124
DEK 5 GW 125	0522660125
DEK 5 GW 126	0522660126
DEK 5 GW 127	0522660127
DEK 5 GW 128	0522660128
DEK 5 GW 129	0522660129
DEK 5 GW 130	0522660130
DEK 5 GW 131	0522660131

Type/Print	Order No.
DEK 5 GW 132	0522660132
DEK 5 GW 133	0522660133
DEK 5 GW 134	0522660134
DEK 5 GW 135	0522660135
DEK 5 GW 136	0522660136
DEK 5 GW 137	0522660137
DEK 5 GW 138	0522660138
DEK 5 GW 139	0522660139
DEK 5 GW 140	0522660140
DEK 5 GW 141	0522660141
DEK 5 GW 142	0522660142
DEK 5 GW 143	0522660143
DEK 5 GW 144	0522660144
DEK 5 GW 145	0522660145
DEK 5 GW 146	0522660146
DEK 5 GW 147	0522660147
DEK 5 GW 148	0522660148
DEK 5 GW 149	0522660149
DEK 5 GW 150	0522660150
DEK 5 GW 151	0522660151
DEK 5 GW 152	0522660152
DEK 5 GW 153	0522660153
DEK 5 GW 154	0522660154
DEK 5 GW 155	0522660155
DEK 5 GW 156	0522660156
DEK 5 GW 157	0522660157
DEK 5 GW 158	0522660158
DEK 5 GW 159	0522660159
DEK 5 GW 160	0522660160
DEK 5 GW 161	0522660161
DEK 5 GW 162	0522660162
DEK 5 GW 163	0522660163
DEK 5 GW 164	0522660164
DEK 5 GW 165	0522660165
DEK 5 GW 166	0522660166
DEK 5 GW 167	0522660167
DEK 5 GW 168	0522660168
DEK 5 GW 169	0522660169
DEK 5 GW 170	0522660170
DEK 5 GW 171	0522660171
DEK 5 GW 172	0522660172
DEK 5 GW 173	0522660173
DEK 5 GW 174	0522660174
DEK 5 GW 175	0522660175
DEK 5 GW 176	0522660176
DEK 5 GW 177	0522660177
DEK 5 GW 178	0522660178
DEK 5 GW 179	0522660179
DEK 5 GW 180	0522660180
DEK 5 GW 181	0522660181
DEK 5 GW 182	0522660182
DEK 5 GW 183	0522660183
DEK 5 GW 184	0522660184
DEK 5 GW 185	0522660185
DEK 5 GW 186	0522660186
DEK 5 GW 187	0522660187
DEK 5 GW 188	0522660188
DEK 5 GW 189	0522660189
DEK 5 GW 190	0522660190
DEK 5 GW 191	0522660191
DEK 5 GW 192	0522660192
DEK 5 GW 193	0522660193
DEK 5 GW 194	0522660194
DEK 5 GW 195	0522660195
DEK 5 GW 196	0522660196
DEK 5 GW 197	0522660197
DEK 5 GW 198	0522660198
DEK 5 GW 199	0522660199
DEK 5 GW 200	0522660200
DEK 5 GW A	0522761021
DEK 5 GW B	0522761022
DEK 5 GW BL/SW -	0576291741
DEK 5 GW C	0522761023
DEK 5 GW D	0522761024
DEK 5 GW E	0522761025
DEK 5 GW F	0522761026
DEK 5 GW G	0522761027
DEK 5 GW H	0522761028
DEK 5 GW I	0522761029
DEK 5 GW J	0522761030
DEK 5 GW K	0522761031
DEK 5 GW L	0522761032
DEK 5 GW L1	0522361075
DEK 5 GW L2	0522361076
DEK 5 GW L3	0522361077
DEK 5 GW M	0522761033

DEK standard printing

Varianten DEK

Type/Print	Order No.
DEK 5 GW MP	0537261235
DEK 5 GW N	0522761034
DEK 5 GW O	0522761035
DEK 5 GW P	0522761036
DEK 5 GW PE	0537261187
DEK 5 GW PEN	0537261188
DEK 5 GW Q	0522761037
DEK 5 GW R	0522761038
DEK 5 GW RT/SW +	0576291737
DEK 5 GW S	0522761039
DEK 5 GW T	0522761040
DEK 5 GW U	0522761041
DEK 5 GW V	0522761042
DEK 5 GW W	0522761043
DEK 5 GW W-STROM	0576261215
DEK 5 GW X	0522761044
DEK 5 GW Y	0522761045
DEK 5 GW Z	0522761046
DEK 5 GW +	0576261198
DEK 5 GW -	0576261199
DEK 5 GW ⏚	0576261202
DEK 5 GW ⏚	0576261203
DEK 5 NEUTRAL	0473360000
DEK 5 OR NEUTRAL	0473391690
DEK 5 RT NEUTRAL	0473391686
DEK 5 SW NEUTRAL	0473391694
DEK 5 VI NEUTRAL	0473391689
DEK 5/3,5 MC FS 1-10	1762320001
DEK 5/3,5 MC FS 101-110	1762320101
DEK 5/3,5 MC FS 11-20	1762320011
DEK 5/3,5 MC FS 111-120	1762320111
DEK 5/3,5 MC FS 121-130	1762320121
DEK 5/3,5 MC FS 131-140	1762320131
DEK 5/3,5 MC FS 141-150	1762320141
DEK 5/3,5 MC FS 21-30	1762320021
DEK 5/3,5 MC FS 31-40	1762320031
DEK 5/3,5 MC FS 41-50	1762320041
DEK 5/3,5 MC FS 51-60	1762320051
DEK 5/3,5 MC FS 61-70	1762320061
DEK 5/3,5 MC FS 71-80	1762320071
DEK 5/3,5 MC FS 81-90	1762320081
DEK 5/3,5 MC FS 91-100	1762320091
DEK 5/3,5 MC GW 0	1755281000
DEK 5/3,5 MC GW 1	1755280001
DEK 5/3,5 MC GW 2	1755280002
DEK 5/3,5 MC GW 3	1755280003
DEK 5/3,5 MC GW 4	1755280004
DEK 5/3,5 MC GW 5	1755280005
DEK 5/3,5 MC GW 6	1755280006
DEK 5/3,5 MC GW 7	1755280007
DEK 5/3,5 MC GW 8	1755280008
DEK 5/3,5 MC GW 9	1755280009
DEK 6 BL NEUTRAL	0468591693
DEK 6 BR NEUTRAL	0468591692
DEK 6 FS 1-50	0468760001
DEK 6 FS 101-150	0468760101
DEK 6 FS 151-200	0468760151
DEK 6 FS 201-250	0468760201
DEK 6 FS 251-300	0468760251
DEK 6 FS 301-350	0468760301
DEK 6 FS 351-400	0468760351
DEK 6 FS 401-450	0468760401
DEK 6 FS 451-500	0468760451
DEK 6 FS 501-550	0468760501
DEK 6 FS 51-100	0468760051
DEK 6 FS 551-600	0468760551
DEK 6 FS 601-650	0468760601
DEK 6 FS 651-700	0468760651
DEK 6 FS 701-750	0468760701
DEK 6 FS 751-800	0468760751
DEK 6 FS 801-850	0468760801
DEK 6 FS 851-900	0468760851
DEK 6 FS 901-950	0468760901
DEK 6 FS 951-999	0468760951
DEK 6 FSZ 1-10	0133360001
DEK 6 FSZ 11-20	0133360011
DEK 6 FSZ 21-30	0133360021
DEK 6 FSZ 31-40	0133360031
DEK 6 FSZ 41-50	0133360041
DEK 6 FSZ 51-60	0133360051
DEK 6 FSZ 61-70	0133360061
DEK 6 FSZ 71-80	0133360071
DEK 6 FSZ 81-90	0133360081
DEK 6 FSZ 91-100	0133360091

Type/Print	Order No.
DEK 6 FW 1,3,5...99	1358660000
DEK 6 FW 1-5 (10X)	0688660000
DEK 6 FW 1-50	0468660001
DEK 6 FW 101-150	0468660101
DEK 6 FW 151-200	0468660151
DEK 6 FW 2,4,...100	1358760000
DEK 6 FW 201-250	0468660201
DEK 6 FW 251-300	0468660251
DEK 6 FW 301-350	0468660301
DEK 6 FW 351-400	0468660351
DEK 6 FW 401-450	0468660401
DEK 6 FW 451-500	0468660451
DEK 6 FW 501-550	0468660501
DEK 6 FW 51-100	0468660051
DEK 6 FW 551-600	0468660551
DEK 6 FW 601-650	0468660601
DEK 6 FW 651-700	0468660651
DEK 6 FW 701-750	0468660701
DEK 6 FW 751-800	0468660751
DEK 6 FW 801-850	0468660801
DEK 6 FW 851-900	0468660851
DEK 6 FW 901-950	0468660901
DEK 6 FW 951-999	0468660951
DEK 6 FW L,N,PE	0632560000
DEK 6 FWZ 1-10	0518960001
DEK 6 FWZ 101-110	0518960101
DEK 6 FWZ 11-20	0518960011
DEK 6 FWZ 111-120	0518960111
DEK 6 FWZ 121-130	0518960121
DEK 6 FWZ 131-140	0518960131
DEK 6 FWZ 141-150	0518960141
DEK 6 FWZ 151-160	0518960151
DEK 6 FWZ 161-170	0518960161
DEK 6 FWZ 171-180	0518960171
DEK 6 FWZ 181-190	0518960181
DEK 6 FWZ 191-200	0518960191
DEK 6 FWZ 201-210	0518960201
DEK 6 FWZ 21-30	0518960021
DEK 6 FWZ 31-40	0518960031
DEK 6 FWZ 41-50	0518960041
DEK 6 FWZ 51-60	0518960051
DEK 6 FWZ 61-70	0518960061
DEK 6 FWZ 71-80	0518960071
DEK 6 FWZ 81-90	0518960081
DEK 6 FWZ 91-100	0518960091
DEK 6 FWZ L1-⏚	0631961203
DEK 6 FWZ L1-PE	0631961187
DEK 6 FWZ R,S,T,N, ⏚	0631860000
DEK 6 GE NEUTRAL	0468591687
DEK 6 GN NEUTRAL	0468591688
DEK 6 GR NEUTRAL	0468591691
DEK 6 GW 0	0526961000
DEK 6 GW 1	0526960001
DEK 6 GW 2	0526960002
DEK 6 GW 3	0526960003
DEK 6 GW 4	0526960004
DEK 6 GW 5	0526960005
DEK 6 GW 6	0526960006
DEK 6 GW 7	0526960007
DEK 6 GW 8	0526960008
DEK 6 GW 9	0526960009
DEK 6 GW 10	0526960010
DEK 6 GW 11	0526960011
DEK 6 GW 12	0526960012
DEK 6 GW 13	0526960013
DEK 6 GW 14	0526960014
DEK 6 GW 15	0526960015
DEK 6 GW 16	0526960016
DEK 6 GW 17	0526960017
DEK 6 GW 18	0526960018
DEK 6 GW 19	0526960019
DEK 6 GW 20	0526960020
DEK 6 GW 21	0526960021
DEK 6 GW 22	0526960022
DEK 6 GW 23	0526960023
DEK 6 GW 24	0526960024
DEK 6 GW 25	0526960025
DEK 6 GW 26	0526960026
DEK 6 GW 27	0526960027
DEK 6 GW 28	0526960028
DEK 6 GW 29	0526960029
DEK 6 GW 30	0526960030
DEK 6 GW 31	0526960031
DEK 6 GW 32	0526960032
DEK 6 GW 33	0526960033
DEK 6 GW 34	0526960034

Type/Print	Order No.
DEK 6 GW 35	0526960035
DEK 6 GW 36	0526960036
DEK 6 GW 37	0526960037
DEK 6 GW 38	0526960038
DEK 6 GW 39	0526960039
DEK 6 GW 40	0526960040
DEK 6 GW 41	0526960041
DEK 6 GW 42	0526960042
DEK 6 GW 43	0526960043
DEK 6 GW 44	0526960044
DEK 6 GW 45	0526960045
DEK 6 GW 46	0526960046
DEK 6 GW 47	0526960047
DEK 6 GW 48	0526960048
DEK 6 GW 49	0526960049
DEK 6 GW 50	0526960050
DEK 6 GW 51	0526960051
DEK 6 GW 52	0526960052
DEK 6 GW 53	0526960053
DEK 6 GW 54	0526960054
DEK 6 GW 55	0526960055
DEK 6 GW 56	0526960056
DEK 6 GW 57	0526960057
DEK 6 GW 58	0526960058
DEK 6 GW 59	0526960059
DEK 6 GW 60	0526960060
DEK 6 GW 61	0526960061
DEK 6 GW 62	0526960062
DEK 6 GW 63	0526960063
DEK 6 GW 64	0526960064
DEK 6 GW 65	0526960065
DEK 6 GW 66	0526960066
DEK 6 GW 67	0526960067
DEK 6 GW 68	0526960068
DEK 6 GW 69	0526960069
DEK 6 GW 70	0526960070
DEK 6 GW 71	0526960071
DEK 6 GW 72	0526960072
DEK 6 GW 73	0526960073
DEK 6 GW 74	0526960074
DEK 6 GW 75	0526960075
DEK 6 GW 76	0526960076
DEK 6 GW 77	0526960077
DEK 6 GW 78	0526960078
DEK 6 GW 79	0526960079
DEK 6 GW 80	0526960080
DEK 6 GW 81	0526960081
DEK 6 GW 82	0526960082
DEK 6 GW 83	0526960083
DEK 6 GW 84	0526960084
DEK 6 GW 85	0526960085
DEK 6 GW 86	0526960086
DEK 6 GW 87	0526960087
DEK 6 GW 88	0526960088
DEK 6 GW 89	0526960089
DEK 6 GW 90	0526960090
DEK 6 GW 91	0526960091
DEK 6 GW 92	0526960092
DEK 6 GW 93	0526960093
DEK 6 GW 94	0526960094
DEK 6 GW 95	0526960095
DEK 6 GW 96	0526960096
DEK 6 GW 97	0526960097
DEK 6 GW 98	0526960098
DEK 6 GW 99	0526960099
DEK 6 GW 100	0526960100
DEK 6 GW BL/SW -	1318091741
DEK 6 GW PE	1318061187
DEK 6 GW RT/SW +	1318091737
DEK 6 GW +	1318061198
DEK 6 GW -	1318061199
DEK 6 GW ⏚	1318061202
DEK 6 GW ⏚	1318061203
DEK 6 NEUTRAL	0468560000
DEK 6 OR NEUTRAL	0468591690
DEK 6 RT NEUTRAL	0468591686
DEK 6 SW NEUTRAL	0468591694
DEK 6 VI NEUTRAL	0468591689
DEK 6,5 BL NEUTRAL	0468091693
DEK 6,5 FS 1-50	0468260001
DEK 6,5 FS 101-150	0468260101
DEK 6,5 FS 51-100	0468260051
DEK 6,5 FSZ 1-10	0407360001
DEK 6,5 FSZ 11-20	0407360011
DEK 6,5 FSZ 21-30	0407360021

Type/Print	Order No.
DEK 6,5 FSZ 31-40	0407360031
DEK 6,5 FSZ 41-50	0407360041
DEK 6,5 FSZ 51-60	0407360051
DEK 6,5 FSZ 61-70	0407360061
DEK 6,5 FSZ 71-80	0407360071
DEK 6,5 FSZ 81-90	0407360081
DEK 6,5 FSZ 91-100	0407360091
DEK 6,5 FW 1-50	0468160001
DEK 6,5 FW 101-150	0468160101
DEK 6,5 FW 151-200	0468160151
DEK 6,5 FW 201-250	0468160201
DEK 6,5 FW 251-300	0468160251
DEK 6,5 FW 301-350	0468160301
DEK 6,5 FW 351-400	0468160351
DEK 6,5 FW 401-450	0468160401
DEK 6,5 FW 451-500	0468160451
DEK 6,5 FW 501-550	0468160501
DEK 6,5 FW 51-100	0468160051
DEK 6,5 FW L1- h	0632161203
DEK 6,5 FW L1-PE	0632161187
DEK 6,5 FWZ 1-10	0519060001
DEK 6,5 FWZ 11-20	0519060011
DEK 6,5 FWZ 21-30	0519060021
DEK 6,5 FWZ 31-40	0519060031
DEK 6,5 FWZ 41-50	0519060041
DEK 6,5 FWZ 51-60	0519060051
DEK 6,5 FWZ 61-70	0519060061
DEK 6,5 FWZ 71-80	0519060071
DEK 6,5 FWZ 81-90	0519060081
DEK 6,5 FWZ 91-100	0519060091
DEK 6,5 FWZ R,S,T,N,ERD	0632060000
DEK 6,5 GE NEUTRAL	0468091687
DEK 6,5 GN NEUTRAL	0468091688
DEK 6,5 NEUTRAL	0468060000
DEK 6,5 OR NEUTRAL	0468091690
DEK 6,5 RT NEUTRAL	0468091686
DEK 6,5 SW NEUTRAL	0468091694
DEK 6,5 VI NEUTRAL	0468091689
DEK 8 BEDR./FARBIG	1289690000
DEK 8 FS 1-50 TAMPOPR.	1653350001
DEK 8 FS 51-100 TAMPOP.	1653350051
DEK 8 FSZ 1-10	1289660001
DEK 8 FSZ 11-20	1289660011
DEK 8 FSZ 21-30	1289660021
DEK 8 FSZ 31-40	1289660031
DEK 8 FSZ 41-50	1289660041
DEK 8 FSZ 51-60	1289660051
DEK 8 FSZ 61-70	1289660061
DEK 8 FSZ 71-80	1289660071
DEK 8 FSZ 81-90	1289660081
DEK 8 FSZ 91-100	1289660091
DEK 8 FW 1-50 TAMPOPR.	1653340001
DEK 8 FW 51-100 TAMPOP.	1653340051
DEK 8 FWZ 1-10	1276960001
DEK 8 FWZ 101-110	1276960101
DEK 8 FWZ 11-20	1276960011
DEK 8 FWZ 111-120	1276960111
DEK 8 FWZ 121-130	1276960121
DEK 8 FWZ 131-140	1276960131
DEK 8 FWZ 141-150	1276960141
DEK 8 FWZ 21-30	1276960021
DEK 8 FWZ 31-40	1276960031
DEK 8 FWZ 41-50	1276960041
DEK 8 FWZ 51-60	1276960051
DEK 8 FWZ 61-70	1276960061
DEK 8 FWZ 71-80	1276960071
DEK 8 FWZ 81-90	1276960081
DEK 8 FWZ 91-100	1276960091
DEK 8 GE NEUTRAL	1277091687
DEK 8 GN NEUTRAL	1277091688
DEK 8 NEUTRAL	1277060000
DEK 8 OR NEUTRAL	1277091690
DEK 8 RT NEUTRAL	1277091686
DEK 8 SONDERDR. WEIß	1326660000
DEK 8 VI NEUTRAL	1277091689

DEK MultiCard

The Dekafix marker in MultiCard format is the universal marker for all kinds of connectors and also electronic modules from the Weidmüller product range. The blank DEK marker is ideal for flexible, fast printing in situ with our innovative labelling systems SMark-Laser, PrintJet, MCP Plus Plotter or MC-Mobilo. The system is particularly suitable for short sequences of numbers and is also available with special printing.

- In strips for fast installation
- Flexible, fast printing on site during installation
- Excellent printing quality thanks to the Weidmüller MultiCard printers
- Available in 6 widths
- Custom printing with the MC Laser also possible



Technical data

Material	Polyamide 66, halogen-free
UL 94 flammability rating	V2
Temperature range	–40 °C to 100 °C
Printing	black

Ordering data

Colour	Available in all colours of the international colour code; for MC on request ● brown ● red ● orange ● yellow ● green ● blue ● violet ○ grey ○ white
Special printing	Specify special printing and colours per diskette, Excel file or using the M-Print® PRO software.
Minimum order quantity	1 pack
Notes on mounting	Mount in strips when the marker pitch (width) corresponds to the pitch of the terminals. For example, DEK 5 mm pitch for terminals with 5 mm pitch such as the WDU 2.5. Mount individual markers when the terminal pitch is larger than the marker pitch (width). For example, DEK 6.5 mount individually on WDU 6 terminals.

Dekafix - the universal marker for SAK series, W-series, Z-series, P-series and I-series plus WEICOS connectors and electronics devices.

Clamping width: 3.5 mm

DEK - blank

Ordering data

Type	Material colour	Length	Qty.	Order No.
DEK 5/3,5 MC	white	5 mm	500	**1755270000**

DEK - Custom printing

Type	Material colour	Length	Qty.	Order No.
DEK 5/3,5 MC	white	5 mm	100	**1767730000**

Clamping width: 5.0 mm

DEK - blank

Type	Material colour	Length	Qty.	Order No.
DEK 5/5 Plus MC	white	5 mm	1000	**1854490000**
DEK 5/5 Plus MC GE	yellow	5 mm	1000	**1907520000**
DEK 5/5 MC	white	5 mm	1000	**1609801044**
DEK 5/5 MC GE	yellow	5 mm	1000	**1609801687**
DEK 5/5 MC BL	blue	5 mm	1000	**1609801693**
DEK 5/5 MC GR	grey	5 mm	1000	**1609801691**
DEK 5/5 MC GN	green	5 mm	1000	**1609801688**
DEK 5/5 MC RT	red	5 mm	1000	**1609801686**

DEK - Custom printing

Type	Material colour	Length	Qty.	Order No.
DEK 5/5 MC	white	5 mm	200	**1609810000**
DEK 5/5 Plus MC	white	5 mm	200	**1854500000**

Clamping width: 6.0 / 6.5 mm

DEK - blank

Type	Material colour	Length	Qty.	Order No.
DEK 5/6 MC	white	5 mm	1000	**1609820000**
DEK 5/6 MC PLUS	white	5 mm	1000	**1011320000**
DEK 5/6,5 MC	white	5 mm	900	**1609840000**
DEK 5/6,5 PLUS MC	white	5 mm	900	**1046340000**

DEK - Custom printing

Type	Material colour	Length	Qty.	Order No.
DEK 5/6 MC SDR	white	5 mm	200	**1609830000**
DEK 5/6 MC SDR PLUS	white	5 mm	200	**1038650000**
DEK 5/6,5 MC	white	5 mm	180	**1609850000**
DEK 5/6,5 PLUS MC	white	5 mm	180	**1046360000**

Clamping width: 7.5 / 8.0 mm

DEK - blank

Type	Material colour	Length	Qty.	Order No.
DEK 5/7,5 MC	white	5 mm	320	**1720620000**
DEK 5/8 MC	white	5 mm	800	**1856740000**
DEK 5/8 PLUS MC	white	5 mm	800	**1046350000**

DEK - Custom printing

Type	Material colour	Length	Qty.	Order No.
DEK 5/7,5 MC	white	5 mm	64	**1770490000**
DEK 5/8 MC	white	5 mm	160	**1856750000**
DEK 5/8 PLUS MC	white	5 mm	160	**1046370000**

WS

WS markers are designed specifically for W series terminals. But thanks to their system compatibility, WS markers can also be used with the I series, Z series and P series. The generous size of these markers permit long characters strings and multiple-line printing.

WS markers are ideal for labelling where long, individual character strings are required. And the proven MultiCard format makes labelling possible with the SMark-Laser, PrintJet, MCP Plus Plotter or MC-Mobilo as well.

- Mount in strips or individually
- Markers in the proven MultiCard format
- Excellent printing quality thanks to the Weidmüller MultiCard printers

Technical data

Material	Polyamide 66, halogen-free
UL 94 flammability rating	V2
Temperature range	–40 °C to 100 °C
Printing	black

Bestellhinweis

Colour	Available in all colours of the international colour code; for MC on request ● brown ● red ● orange ● yellow ● green ● blue ● violet ● grey O white
Special printing	Specify special printing and colours per diskette, Excel file or using the M-Print® PRO software.
Minimum order quantity	1 pack
Notes on mounting	Mount in strips when the marker pitch (width) corresponds to the pitch of the terminals. For example, WS 10/6 = 6 mm pitch for terminals with 6 mm pitch such as the WDU 4. Mount individual markers when the terminal pitch is larger than the marker pitch (width). For example, WS 12/6.5 mount individually on WDU 6 terminals. Weidmüller markers with 5 mm pitch (width) are suitable for all widths of terminals.

ZS

ZS markers – in the proven MultiCard format – were specially developed for Z series terminals. They provide users with a large labelling area. Their unique hinged form means that cross-connectors, for example, are still readily accessible without having to remove the marker. Markers can be clipped on in strips to guarantee fast installation, but individual markers are easily separated.

- Hinged labelling area
- Mount in strips or individually
- Markers in the proven MultiCard format
- Flexible, fast printing on site during installation

Technical data

Material	Polyamide 66, halogen-free
UL 94 flammability rating	V2
Temperature range	–40 °C to 100 °C
Printing	black

Ordering data

Colour	white
Notes on mounting	height x width (pitch), e.g. ZS 10/5: 10 mm high, 5 mm wide = 5 mm pitch
Special printing	Specify special printing per diskette, Excel file or using the M-Print® PRO software.
Suitable printing systems	SMark-Laser, PrintJet, MCP Plus Plotter, MC-Mobilo
Minimum order quantity	1 pack

WS / ZS

WS markers are perfect for the connectors of the W-series, I-series, P-series and Z-series. WS 10/5 and 10/6 Middle are fitted with a centre foot and can be used for the I-series. The ZS markers are specially conceived for the Z-series.

Clamping width: 3.5 mm

WS - blank

Ordering data

Type	Material colour	Length	Qty.	Order No.
WS 12/3,5 MC	white	12 mm	600	**1778270000**

WS - Custom printing

Type	Material colour	Length	Qty.	Order No.
WS 12/3,5 MC	white	12 mm	120	**1778280000**

Clamping width: 5.0 mm

WS - blank

Type	Material colour	Length	Qty.	Order No.
WS 8/5 MC	white	8 mm	720	**1640740000**
WS 8/5 MC GE	yellow	8 mm	720	**1773521687**
WS 8/5 MC RT	red	8 mm	720	**1773521686**
WS 8/5 MC BL	blue	8 mm	720	**1773521693**
WS 8/5 MC OR	orange	8 mm	720	**1773521690**
WS 8/5 PLUS MC	white	8 mm	600	**1951870000**
WS 10/5 MC	white	10 mm	720	**1635000000**
WS 10/5 MC GE	yellow	10 mm	720	**1773531687**
WS 10/5 MC Middle	white	10 mm	720	**1792000000**
WS 10/5 MC RT	red	10 mm	720	**1773531686**
WS 10/5 MC BL	blue	10 mm	720	**1773531693**
WS 10/5 PLUS MC	white	10 mm	600	**1046380000**
WS 12/5 MC	white	12 mm	720	**1609860000**
WS 12/5 MC GE	yellow	12 mm	720	**1773541687**
WS 12/5 MC RT	red	12 mm	720	**1773541686**
WS 12/5 MC BL	blue	12 mm	720	**1773541693**
WS 12/5 MC OR	orange	12 mm	720	**1773541690**
WS 12/5 MC PLUS	white	12 mm	600	**1927510000**
WS 14/5 MC	white	14 mm	480	**1768090000**
WS 15/5 MC	white	15 mm	480	**1609880000**
WS 15/5 MC GE	yellow	15 mm	480	**1773571687**

WS - Custom printing

Type	Material colour	Length	Qty.	Order No.
WS 8/5 MC	white	8 mm	144	**1640750000**
WS 8/5 MC PLUS	white	8 mm	120	**1038790000**
WS 10/5 MC	white	10 mm	144	**1635010000**
WS 10/5 MC Middle	white	10 mm	144	**1792010000**
WS 10/5 PLUS MC	white	10 mm	120	**1046320000**
WS 12/5 MC	white	12 mm	144	**1609870000**
WS 12/5 MC PLUS	white	12 mm	120	**1927520000**
WS 15/5 MC	white	15 mm	96	**1609890000**

Clamping width: 6.0 mm

WS - blank

Type	Material colour	Length	Qty.	Order No.
WS 8/6 PLUS MC	white	8 mm	600	**1951880000**
WS 10/6 MC	white	10 mm	600	**1828450000**
WS 10/6 MC Middle	white	10 mm	600	**1818400000**
WS 10/6 MC Middle GN	green	10 mm	600	**1917420000**
WS 10/6 MC Middle GE	yellow	10 mm	600	**1917430000**
WS 10/6 MC Middle RT	red	10 mm	600	**1917440000**
WS 10/6 MC Middle OR	orange	10 mm	600	**1917410000**
WS 10/6 PLUS MC	white	10 mm	600	**1046390000**
WS 12/6 MC	white	12 mm	600	**1609900000**
WS 12/6 MC GE	yellow	12 mm	600	**1773551687**
WS 12/6 MC RT	red	12 mm	600	**1773551686**
WS 12/6 MC BL	blue	12 mm	600	**1773551693**
WS 12/6 MC OR	orange	12 mm	600	**1773551690**
WS 12/6 MC BR	brown	12 mm	600	**1773551692**
WS 12/6 MC VI	magenta	12 mm	600	**1773551689**
WS 12/6 MC PLUS	white	12 mm	600	**1927530000**

WS markers are perfect for the connectors of the W-series, I-series, P-series and Z-series. WS 10/5 and 10/6 Middle are fitted with a centre foot and can be used for the I-series. The ZS markers are specially conceived for the Z-series.

Ordering data

WS - Custom printing

Type	Material colour	Length	Qty.	Order No.
WS 8/6 PLUS MC	white	8 mm	120	**1038820000**
WS 10/6 MC	white	10 mm	120	**1828460000**
WS 10/6 MC Middle	white	10 mm	120	**1818410000**
WS 10/6 PLUS MC	white	10 mm	120	**1046330000**
WS 12/6 MC	white	12 mm	120	**1609910000**
WS 12/6 MC PLUS	white	12 mm	120	**1927540000**

Clamping width: 6.5 mm

WS - blank

Type	Material colour	Length	Qty.	Order No.
WS 12/6,5 MC	white	12 mm	540	**1609920000**
WS 12/6,5 MC GE	yellow	12 mm	540	**1773561687**
WS 12/6,5 MC RT	red	12 mm	540	**1773561686**
WS 12/6,5 MC BL	blue	12 mm	540	**1773561693**
WS 12/6,5 MC GN	green	12 mm	540	**1773561688**

WS - Custom printing

Type	Material colour	Length	Qty.	Order No.
WS 12/6,5 MC	white	12 mm	108	**1609930000**

Clamping width: 8.0 mm

WS - blank

Type	Material colour	Length	Qty.	Order No.
WS 10/8 MC	white	10 mm	420	**1905950000**
WS 12/8 MC	white	12 mm	420	**1906000000**

WS - Custom printing

Type	Material colour	Length	Qty.	Order No.
WS 10/8 MC	white	10 mm	84	**1906030000**
WS 12/8 MC	white	12 mm	84	**1906010000**

Clamping width: 12.0 / 15.0 mm

WS - blank

Type	Material colour	Length	Qty.	Order No.
WS 10/12 MC	white	10 mm	300	**1905970000**
WS 10/15 MC	white	10 mm	240	**1854090000**

WS - Custom printing

Type	Material colour	Length	Qty.	Order No.
WS 10/12 MC	white	10 mm	60	**1906060000**
WS 10/15 MC	white	10 mm	48	**1854100000**

Clamping width: 5.0 mm

ZS - blank

Type	Material colour	Length	Qty.	Order No.
ZS 10/5 MC	white	10 mm	480	**1610000000**
ZS 15/5 MC	white	15 mm	480	**1646630000**

ZS - Custom printing

Type	Material colour	Length	Qty.	Order No.
ZS 10/5 MC	white	10 mm	96	**1610010000**
ZS 15/5 MC	white	15 mm	96	**1646640000**

Clamping width: 6.0 mm

ZS - blank

Type	Material colour	Length	Qty.	Order No.
ZS 12/6 MC	white	12 mm	400	**1610020000**

ZS - Custom printing

Type	Material colour	Length	Qty.	Order No.
ZS 12/6 MC	white	12 mm	80	**1610030000**

MultiFit

MultiFit is Weidmüller's marker system for use with other makes of terminals with pitches of 4, 5, 6, 7.5, 8 and 10 mm.

- Blank markers ready for users to print with SMark-Laser, PrintJet, Plotter or MC-Mobilo
- Individually printed markers supplied based on customer CAE data or specifications
- One marker suitable for various terminal manufacturers



Technical data

Material	Polyamide 66, halogen-free
UL 94 flammability rating	V2
Temperature range	–40 °C to 100 °C
Printing	black

Ordering data

Colour	Available in all colours of the international colour code; for MC on request ● brown ● red ● orange ● yellow ● green ● blue ● violet ● grey ○ white
Special printing	Specify special printing and colours per diskette, Excel file or using the M-Print® PRO software.
Minimum order quantity	1 pack

Application options

	MF 8/5	MF 10/5 MF 10/6	MF 12/5	MF 5/4 MF 5/5 MF 5/6	MF-W 5/5 Mini	MF-W 9/4 MF-W 9/5 MF-W 9/6	MF-W 9/5 F MF-W 9/4.2 F MF-W 9/5.2 F MF-W 9/6.2 F
Wago	●	●	●		● Similar to the WagoMini WSB Type 248-...264-...	● Similar to the Wago WSB Type 209-...249-...	● Similar to the Wago WMB Type 793-...794-... For Wago TopJob S
Phoenix	●	●	●	● MF 5/5 Similar to the Phoenix Contact ZBF 5 MF 5/6 Similar to the Phoenix Contact ZBF 6 MF 5/4 Similar to the Phoenix ZBF 4			
Wieland	●	●	●				
Legrand	●	●	●		●	●	●
Entrelec	●	●	●		●		
Télémécanique	●	●	●				

	MF 10/8	MF 10/10	MF 4/5.2	MF 5/7.5	MF 10/5 MF 12/5	MF-SI	MF-WO	MFF
Siemens						●		
Phoenix	● ZB 8	● ZB 10	● BN-ZB 5.2	● BN-ZB 7.5				
Wieland								
Legrand								
Entrelec	●	●						
Woertz							●	
Adels RKW				● BZ 14				
Cabur					● Cabur			
Festo								●

● = OK

(Please select the marker according to the width of the terminal)

Please note:

The recommended applications given above do not release the user from his obligation to check the applicability in each individual application. The marker/terminal combination should in each case be chosen in such a way that either the marker pitch matches the terminal pitch, or the marker pitch is smaller than the terminal pitch.

MulitFit for use with other makes of terminals

Clamping width: 4.0 mm

MultiFit - blank

Ordering data

Type	Material colour	Length	Qty.	Order No.
MF 5/4 MC	white	5 mm	500	**1877690000**
MFF 9/4 MC	white	9 mm	500	**1877720000**
MF-W 9/4 MC	white	9 mm	500	**1877730000**
MF-W 9/4.2F MC	white	9 mm	500	**1011430000**

MultiFit - Custom printing

Type	Material colour	Length	Qty.	Order No.
MF 5/4 MC	white	5 mm	100	**1877670000**
MFF 9/4 MC	white	9 mm	100	**1877700000**
MF-W 9/4 MC	white	9 mm	100	**1877710000**
MF-W 9/4.2F MC	white	9 mm	100	**1038750000**

Clamping width: 5.0 mm

MultiFit - blank

Type	Material colour	Length	Qty.	Order No.
MF 4/5,2 MC	white	4 mm	500	**1907530000**
MF 5/5 MC	white	5 mm	500	**1816250000**
MF-W 5/5 MC Mini	white	5 mm	500	**1816240000**
MF-W 5/5 MC Mini GN	green	5 mm	500	**1924290000**
MF-W 5/5 MC Mini BL	Blue	5 mm	500	**1924270000**
MF-W 5/5 MC Mini GE	yellow	5 mm	500	**1924280000**
MF-W 5/5 MC Mini RT	red	5 mm	500	**1924260000**
MF-WO 5/5 MC	white	5 mm	400	**1716800000**
MF 8/5 MC	white	8 mm	600	**1677140000**
MF-SI 8/5 MC	white	8 mm	400	**1889180000**
MF-W 9/5 MC	white	9 mm	500	**1816270000**
MF-W 9/5F MC	white	9 mm	500	**1816280000**
MF-W 9/5.2F MC	white	9 mm	500	**1011410000**
MF-WO 9/5 MC	white	9 mm	400	**1716840000**
MF 10/5 MC	white	10 mm	600	**1677160000**
MF-SI 10/5 MC	white	10 mm	400	**1889190000**
MF 10/5 MC Cabur	white	10 mm	600	**1854510000**
MF 12/5 MC	white	12 mm	600	**1677180000**
MF-WO 12/5 MC	white	12 mm	400	**1692270000**
MF 12/5 MC Cabur	white	12 mm	600	**1854520000**

MultiFit - Custom printing

Type	Material colour	Length	Qty.	Order No.
MF 4/5.2 MC	white	4 mm	100	**1038690000**
MF 5/5 MC	white	5 mm	500	**1816320000**
MF-W 5/5 Mini MC	white	5 mm	500	**1816310000**
MF-WO 5/5 MC	white	5 mm	80	**1716810000**
MF 8/5 MC	white	8 mm	120	**1677150000**
MF-SI 8/5 MC	white	8 mm	80	**1886270000**
MF-W 9/5 MC	white	9 mm	500	**1816340000**
MF-W 9/5F MC	white	9 mm	500	**1816350000**
MF-WO 9/5 MC	white	9 mm	80	**1716850000**
MF-W 9/5.2F MC	white	9 mm	100	**1038760000**
MF 10/5 MC	white	10 mm	120	**1677170000**
MF-SI 10/5 MC	white	10 mm	80	**1889170000**
MF 10/5 MC CABUR	white	10 mm	120	**1038660000**
MF 12/5 MC	white	12 mm	120	**1677190000**
MF-WO 12/5 MC	white	12 mm	80	**1692280000**
MF 12/5 MC CABUR	white	12 mm	120	**1038670000**

Clamping width: 6.0 mm

MultiFit - blank

Ordering data

Type	Material colour	Length	Qty.	Order No.
MF 5/6 MC	white	5 mm	500	**1816260000**
MF-SI 8/6 MC	white	8 mm	320	**1889240000**
MF-W 9/6 MC	white	9 mm	500	**1816290000**
MF-W 9/6.2F MC	white	9 mm	500	**1011420000**
MF-WO 9/6 MC	white	9 mm	400	**1716820000**
MF 10/6 MC	white	10 mm	600	**1677220000**
MFF 10/6 MC	white	10 mm	600	**1856780000**
MF-SI 10/6 MC	white	10 mm	320	**1889260000**
MF-WO 12/6 MC	white	12 mm	400	**1692290000**

MultiFit - Custom printing

Type	Material colour	Length	Qty.	Order No.
MF 5/6 MC	white	5 mm	500	**1816330000**
MF-SI 8/6 MC	white	8 mm	64	**1889230000**
MF-W 9/6 MC	white	9 mm	500	**1816360000**
MF-WO 9/6 MC	white	9 mm	80	**1716830000**
MF-W 9/6.2F MC	white	9 mm	100	**1038770000**
MF 10/6 MC	white	10 mm	120	**1677230000**
MFF 10/6 MC	white	10 mm	120	**1856790000**
MF-SI 10/6 MC	white	10 mm	64	**1889250000**
MF-WO 12/6 MC	white	12 mm	80	**1692300000**

Clamping width: 6.5 / 7.5 mm

MultiFit - blank

Type	Material colour	Length	Qty.	Order No.
MF 5/ 7,5 MC	white	5	320	**1877680000**
MF-SI 7/5-6,5 MC	white	7	320	**1889780000**
MF-SI 10/5-6,5 MC	white	10	320	**1889800000**

MultiFit - Custom printing

Type	Material colour	Length	Qty.	Order No.
MF 5/7,5 MC	white	5	64	**1877660000**
MF-SI 7/5-6,5 MC	white	7	64	**1889770000**
MF-SI 10/5-6,5 MC	white	10	64	**1889790000**

Clamping width: 8.0 / 10.0 mm

MultiFit - blank

Type	Material colour	Length	Qty.	Order No.
MF 5/10 MC	white	5	250	**1954050000**
MF 10/8 MC	white	10	350	**1868440000**
MF 10/10 MC	white	10	200	**1856760000**

MultiFit - Custom printing

Type	Material colour	Length	Qty.	Order No.
MF 5/10 MC	white	5	50	**1038730000**
MF 10/8 MC	white	10	70	**1868430000**
MF 10/10 MC	white	10	40	**1856770000**

Cross-reference table

Cross-reference table

Phoenix

	MF 5/4	MF 5/5	MF 8/5	MF 10/5	MF 12/5	MF 5/6	MF 10/6	MF 10/8	MF 10/10	MF 5/7,5	MF 4/5,2
AKG 16…							X				
AKG 35…							X				
AKG 4			X	X	X						
DFK 4…							X				
DFK 5…							X				
DIK 1,5…						X	X				
DIKD 1,5…						X	X				
DLK.. 2,5…						X	X				
DOK 1,5…						X	X				
DT 6/2,5-DREH…									X		
DTI 2,5 …		X	X	X							
DTI 4 …						X	X				
DTI 6 …								X			
DTME.. 6 …								X			
DTN 2,5 …		X	X	X							
DTN 4 …						X	X				
DTN 6 …								X			
EC-E…		X									
GE 10…									X		
GE 35…									X		
GTF 76/…									X		
HDFK 10								X			
HDFK 16									X		
HDFK 25									X		
HDFK 4							X				
HDFK 50/…									X		
HDFK 95									X		
HV M5/…									X		
HV M6/…									X		
HV M8/…									X		
HV M10/…									X		
HV M12/…											
IL…						X					
IB…						X					
MKB …											X
MBK 2,5/E…											X
MBK 3…											X
MBK 3/E-Z…		X	X	X	X						
MBK 5…											X
MBK 5/E-…											X
MBK 5/E-Z…						X	X				
MBK 6/E…								X			
MBKKB 2,5…		X	X	X	X						
MSB 2,5 …		X									
MSDB 2,5 …		X									
MSBV 2,5 …		X									
MSDBV 2,5 …		X									
MSLKG 2,5										X	
MSLKG 5										X	
MSLKG 6								X			
MT 1,5…	X										
MTK …		X	X	X	X						
MTKD-…									X		
MTTB 1,5…	X										
MZB 1,5…		X									
MZDB 1,5…		X									
MZFK 1,5…		X									
MZFKK 1,5 …		X									
MZFKKB 1,5		X									
OTTA 2,5								X			
OTTA 25									X		
OTTA 6…									X		
PCVK 4-7,62 …						X	X				
PIK 4-…						X	X				
PIK 6-…								X			
PIT 2,5 …		X									
PITTB 2,5 …		X									
PITTBS 2,5 …		X									
PIT 2,5-3 …		X									
PIT 2,5-PE/../..		X									
PP-H 2,5/…		X									
PVB…							X				
QP 1,5/..		X									
QTC 1,5 …		X	X	X							
QTC 2,5 …						X	X				
QTC 2,5-HE..I …						X					
QTCS 1,5 …		X	X	X							
QTCS 2,5 …						X	X				

	MF 5/4	MF 5/5	MF 8/5	MF 10/5	MF 12/5	MF 5/6	MF 10/6	MF 10/8	MF 10/10	MF 5/7,5	MF 4/5,2
QTCU 1,5 …		X	X	X							
QTCU 2,5 …						X	X				
QTTCB 1,5 …		X									
QTTCBS 1,5 …		X									
RT 3…									X		
RT 5…									X		
RT 8…									X		
RTO 3…									X		
RTO 5…									X		
RTO 8…									X		
RV 8-TP …							X				
RVS 10-TP…							X				
SC 2,5…		X									
SC 4…						X					
SGSK 6								X			
SP 2,5/…		X									
SP.. 2,5/…		X									
SP 4/…						X					
SLKK 5…						X	X				
SRDK 6								X			
SRTK 6								X			
SSL 2,5		X									
ST 1,5…	X										
ST 2,5….		X	X								
ST 2,5-3…		X									
ST 2,5-PCB…		X									
ST 2,5-PE/../..		X									
ST 2,5-4…		X									
ST 4….						X					
ST 4-PE/…						X					
ST 4-HE..I…						X					
ST 4-FSI/C …								X			
ST 4-PCB…						X					
ST 6 …						X					
ST 10 …						X					
ST 16 …						X					
ST 35 …						X					
STI 10…		X									
STI 16…						X					
STI 2,5…		X	X	X							
STI 2,5-PE/../..		X	X	X	X						
STI 2,5-L …		X	X	X	X						
STI 4…						X	X				
STIO 2,5/3-…		X									
STIO-IN 2,5/3…		X									
STIO 2,5/4-…						X					
STIO-IN 2,5/4…						X					
STME .. 6 …								X			
STN 10									X		
STN 16						X					
STN 2,5		X									
STN 35									X		
STN 4						X					
STS 2,5…		X	X	X	X						
STS 4…						X	X				
STS 6…								X			
STTB 1,5…	X										
STTB 2,5…		X									
STTB 4…						X					
STTBS 2,5 …		X	X	X							
STTBS 4-…						X	X				
STU 2,5-TWIN …		X	X								
STU 4-TWIN …						X					
STU 10/ …						X					
STU 35/ …						X					
STTBU 4 …						X					
TCP…		X									
TMC…							X				
TMCP-CONNECT-LR							X				
TMCP-SOCKET-M							X				
TRK 4 (pitch 7.5)										X	
TT-STTB-…							X				
UDK 3…		X	X	X	X						
UDK 4…						X	X				
UDK 4-MTK						X	X				
UDK 5-MTK						X	X				
UDMTK 5….						X	X				
UGSK 6								X			

Individual mounting is required if the terminal pitch is larger than the marker.

Phoenix

	MF 5/4	MF 5/5	MF 8/5	MF 10/5	MF 12/5	MF 5/6	MF 10/6	MF 10/8	MF 10/10	MF 5/7,5	MF 4/5,2
UGSK/S								X			
UHK 4-FS…						X	X				
UHV 150-…									X		
UHV 240-…									X		
UHV 25-…									X		
UHV 50-…									X		
UHV 95-…									X		
UIK 16…									X		
UIK 35…									X		
UISLKG 16…									X		
UISLKG 35…									X		
UK 1,5 N…	X										
UK 10 N									X		
UK 10,3-… HESI…									X		
UK 10-DRHESI…							X				
UK 16 N									X		
UK 2,5 N		X	X	X	X						
UK 3 N		X	X	X	X						
UK 35									X		
UK 35 N…									X		
UK 4…						X	X				
UK 5 N						X	X				
UK 5-HESI								X			
UK 5-MTK…						X	X				
UK 6 N								X			
UK 6,3-HESI									X		
UK 6-FSI/C…								X			
UKB 4 …							X				
UKH 150 …									X		
UKH 240 …									X		
UKH 50 …									X		
UKH 95 …									X		
UKK 3…		X	X	X	X						
UKK 4-FS…						X	X				
UKK 5…						X	X				
UKKB 3…		X	X	X	X						
UKKB 5…						X	X				
UKKB 10									X		
UKKB 10/2,5		X	X	X	X				X		
UKN 10 N…									X		
UKN 16 N…									X		
UKN 2,5…						X	X				
UKN 35…									X		
UKN 5…						X	X				
UKN 6 N…								X			
UK-SI								X			
URDK 6								X			
URKN									X		
URKN/S								X			
URTK 6								X			
URTK/S								X			
URTK/S-BEN …								X			
URTK/SP								X			
URTK/SS						X	X				
URTKD/SP								X			
UP 4/…						X					
UPBV 2,5/…		X									
UPBV 4/…						X					
UPCV3K …						X	X				
USED 16									X		
USED 27									X		
USEN 14									X		
USEN 18									X		
USIG…									X		
USK 4-FS…						X	X				
USKLG 1,5 N	X										
USKLG 10 N…									X		
USKLG 16 N…									X		
USKLG 2,5 N…		X	X	X	X						
USKLG 3…		X	X	X	X						
USKLG 35									X		
USLKG 35 N									X		
USKLG 5…						X	X				
USKLG 50									X		
USKLG 6 N…								X			
USKLG 95									X		
UT 10 …									X		
UT 16 …									X		

	MF 5/4	MF 5/5	MF 8/5	MF 10/5	MF 12/5	MF 5/6	MF 10/6	MF 10/8	MF 10/10	MF 5/7,5	MF 4/5,2
UT 35 …									X		
UT 2,5 …			X	X	X						
UT 4 …							X				
UT 4-HEDI …						X	X				
UT 4-HESI …						X	X				
UT 4-PE/…						X	X				
UTME .. 6 …								X			
UTTB 2,5-…		X	X	X	X						
UTTB 4-…						X	X				
UT 6 …								X			
UT 6-TMC M…									X		
UTI 16 …									X		
UTI 35 …									X		
UTN 2,5		X	X	X	X						
UTN 4						X	X				
UTN 6								X			
UTN 10									X		
UTN 16									X		
UTN 35									X		
UVKB 4-FS…						X	X				
VBSN 4							X				
VBST 4-FS…						X	X				
VKK 4-FS						X	X				
VIOK 1,5…						X	X				
W 80/…							X				
ZDIK 1,5…		X									
ZDMTK 2,5…						X					
ZFK 6-DREHSI…						X					
ZFKK 2,5-MT…		X									
ZGSK 4								X			
ZPV 1,5/2,5		X	X	X	X						
ZRTK 4								X			
ZRV 8						X	X				
ZVIOK 1,5…		X									

Individual mounting is required if the terminal pitch is larger than the marker.

Cross-reference table

WAGO

	MF-W 9/4	MF-W 5/5 mini	MF-W 9/5	MF-W 9/5 F	MF-W 9/6
Feed-through terminals					
264-701/704/706		X			
264-711/714/716		X			
264-721/724/726		X			
264-731/734/736		X			
264-120/125/220/225		X			
279-101/104	X				
279-604/621	X				
279-626/826	X				
279-681…686	X				
279-831…836	X				
279-901…906	X				
279-989…995	X				
280-101/104	X				
280-601/602		X	X	X	
280-603/633/634		X	X	X	
280-604/621/826/626		X	X	X	
280-641/651/654		X	X	X	
280-646/656/946		X	X	X	
280-653/671/672		X	X	X	
280-681/684/650		X	X	X	
280-830…835		X	X	X	
280-901…906		X	X	X	
280-989…995		X	X	X	
280-996…999		X	X	X	
280-691		X	X	X	
281-101/104					X
281-601/604					X
281-631/651					X
281-652…654					X
281-663/664/668					X
281-678/681/684					X
281-901/902/904					X
281-992..994/998/691					X
282-101/104					X
282-601/604					X
282-681/682/684					X
282-901/902/904					X
282-992/993/691					X
283-101/104					X
283-601/604					X
283-671/672/674					X
283-901/902/904					X
283-992/998/691					X
284-101/104					X
284-601/604					X
284-621/624					X
284-681/682/684					X
284-691/992/993					X
284-901/902/904					X
285-194/195					X
285-601/604/607					X
285-634/635		X			X
285-691					X
285-992/995					X
290-861/864/867		X	X	X	
780-601/602/604			X	X	
780-631/651/654			X	X	
780-992/993			X	X	
781-601/604					X
781-631/651					X
781-992/993					X
782-601/604					X
782-992					X
783-601/604					X
783-992					X
784-601/604					X
784-992					X
785-601/604/613					X
792-… all		X			
812-140			X	X	X
859-…all		X			
870-681/682/684		X		X	
870-831/832/834		X		X	
870-901/902/904		X		X	
870-911/912/914		X		X	
880-661/662/664		X	X	X	

	MF-W 9/4	MF-W 5/5 mini	MF-W 9/5	MF-W 9/5 F	MF-W 9/6
880-681/682/684		X	X	X	
880-831/832/834		X	X	X	
880-901/902/904		X	X	X	
880-961/964/962		X	X	X	
Protective earth terminals					
264-727		X			
264-737		X			
279-687	X				
279-837	X				
279-907	X				
280-107		X	X	X	
280-607		X	X	X	
280-637		X	X	X	
280-677		X	X	X	
280-687		X	X	X	
280-837		X	X	X	
280-907		X	X	X	
281-107					X
281-607					X
281-637					X
281-657					X
281-687					X
281-907					X
282-107					X
282-607					X
282-687					X
282-907					X
283-607					X
283-609					X
283-677					X
283-907					X
284-107					X
284-607					X
284-687					X
284-907					X
285-197					X
285-607		X			X
285-637		X			X
780-607			X	X	
780-637			X	X	
780-637					X
781-607					X
782-607					X
783-607					X
784-607					X
785-607					
870-687		X		X	
870-837		X		X	
870-907		X		X	
870-917		X		X	
880-687		X	X	X	
880-837		X	X	X	
880-907		X	X	X	
Fuse terminals					
282-698					X
282-696					X
281-611/612/616/622					X
281-624/672					X
281-613/623					X
282-122					X
282-120					X
282-126					X
282-124					X
282-128					X
Two-tier terminals					
279-501/512/513	X				
279-504	X				
279-507	X				
279-508	X				
279-509	X				
279-517/527	X				
280-513		X	X	X	
280-517		X	X	X	
280-519/529		X	X	X	
280-520/530		X	X	X	

	MF-W 9/4	MF-W 5/5 mini	MF-W 9/5	MF-W 9/5 F	MF-W 9/6
280-521/525		X	X	X	
280-522/526		X	X	X	
280-523/533		X	X	X	
280-524/534		X	X	X	
280-527/537		X	X	X	
280-531		X	X	X	
280-532		X	X	X	
280-543		X	X	X	
281-619/629					X
281-620/630					X
870-101…104		X	X	X	
870-107		X	X	X	
870-108		X	X	X	
870-117/127		X	X	X	
870-501…504		X	X	X	
870-507		X	X	X	
870-508/509		X	X	X	
870-517/527		X	X	X	
870-531…534		X	X	X	
870-535/536		X	X	X	
870-537		X	X	X	
870-538/538		X	X	X	
870-826		X	X	X	
Three- and four-tier terminals					
280-549/551		X	X	X	
280-550		X	X	X	
280-552		X	X	X	
280-547/557/597		X	X	X	
280-548/558		X	X	X	
281-531/532					X
870-551/553		X		X	
870-556		X		X	
870-558/559/567/577		X		X	
870-557		X		X	
281-530					X
Routing and potential terminals					
727-… all					X
280-675			X		
Honeycomb elements					
726-… all			X		
Single terminals					
264-130/131		X			
264-230/231		X			
264-180/280		X			
Pluggable relays and bases					
286-… all	X				
786-… all	X				
788-… all			X		X
789-… all		X			
Multi-tier terminals					
775-641			X	X	
775-642/649			X	X	
775-646			X	X	
775-645			X	X	
777-641					X
777-642					X
777-646					X
777-645					X
777-648					X
777-647					X
777-649					X
777-651					X
777-650					X
777-652					X
776-641					X
776-645/646					X
776-649/642					X
776-650/651					X
Disconnect test terminals					
280-612/614			X	X	
280-622/623/627			X	X	

The markers must be mounted individually when the terminal pitch is larger than 6.2 mm.

WAGO

	MF-W 9/4	MF-W 5/5 mini	MF-W 9/5	MF-W 9/5 F	MF-W 9/6
280-649/676/685/695			X	X	
280-683			X	X	
280-805/836/829/839			X	X	
280-868/870/876/879		X	X		
280-869/871/880		X	X		
280-874/881/883/885		X	X		
280-875/882/884		X	X		
280-912…914			X		
281-659/660					X
281-666					X
281-683					X
281-912					X
282-131					X
282-133					X
282-135					X
282-138…141					X
282-694/699					X
282-811/821		X			X
282-860					X
282-865					X
282-866/695/697					X
282-870					X
781-613/623					X
781-643/653					X
782-613/623					X
783-613/623					X
784-613/623					X

Initiator terminals

270-560/564		X			
270-570/574		X			
270-572/577		X			
270-585/586		X			
280-553/560		X	X	X	
280-559		X	X	X	
280-561		X	X	X	
280-563		X	X	X	
280-564		X	X	X	
280-567		X	X	X	
280-570		X	X	X	
280-571		X	X	X	

	MF-W 9/4	MF-W 5/5 mini	MF-W 9/5	MF-W 9/5 F	MF-W 9/6
280-573		X	X	X	
280-574		X	X	X	
280-577		X	X	X	
280-580		X	X	X	
280-582		X	X	X	
280-583		X	X	X	
280-584		X	X	X	
280-588		X	X	X	

Actuator terminals

280-515		X	X	X	
280-554		X	X	X	
280-555		X	X	X	
280-556		X	X	X	
280-562		X	X	X	
280-565		X	X	X	
280-566		X	X	X	
280-568		X	X	X	
280-572		X	X	X	
280-575		X	X	X	
280-576		X	X	X	
280-578		X	X	X	
280-583		X	X	X	
280-585		X	X	X	
280-586		X	X	X	
280-592		X	X	X	
280-593		X	X	X	

Diode and LED terminals

279-620	X				
279-623	X				
279-624	X				
279-673	X				
279-674	X				
279-809	X				
279-815	X				
279-915	X				
280-613			X	X	
280-615			X	X	
280-623			X	X	
280-624			X	X	

	MF-W 9/4	MF-W 5/5 mini	MF-W 9/5	MF-W 9/5 F	MF-W 9/6
280-655			X	X	
280-658			X	X	
280-673			X	X	
280-809			X	X	
280-815			X	X	
280-915			X	X	
280-940			X	X	
280-941			X	X	
280-942			X	X	
280-943			X	X	
281-603					X
281-633					X
281-634					X
281-635					X
281-636					X
281-665					X
281-673					X
281-915					X
870-540		X	X	X	
870-541		X	X	X	
870-542		X	X	X	
870-543		X	X	X	
870-590		X	X	X	
870-593		X	X	X	
870-596		X	X	X	

X-Com system

769-… all		X			

WAGO I/O modules TOPLON

	MF-W 5/5 mini	MF 5/10	ESG 8/11
750-… all	X	X	X

Wago TOPJOB S

	MF-W 9/4,2 F	MF-W 9/5,2 F	MF-W 9/6,2 F
2001-12..	X		
2001-13..	X		
2001-14..	X		
2002-12..		X	
2002-13..		X	
2002-14..		X	
2002-16..		X	
2002-18..		X	
2002-22..		X	
2002-29..		X	
2002-32..		X	
2002-63..		X	
2002-64..		X	
2002-71..		X	
2003-76..		X	
2004-12..			X
2004-13..			X
2004-14..			X
2005-76..			X
2006-12..			X
2006-13..			X
2006-71..			X
2010-12..			X
2010-13..			X
2016-12..			X
2016-13..			X
2016-71..			X

The markers must be mounted individually when the terminal pitch is larger than 6.2 mm.

Cross-reference table

ABB-Stotz/ Entrelec

	MF-W 9/4	MF-W 9/5	MF-W 9/5 F	MF-W 9/6	MF-W 9/6.2 F	MF-W 5/5 mini	MF 10/5	MF 10/6	MF 10/8	MF 10/10
131 ET TM4…						x				
165 LT TM5…						x				
41 H LT…						x				
62 H…				x						
BADH				x						
BADL				x	x			x		
BADRL				x	x	x		x		
BAEH				x						
BAM…				x	x			x		
BAMH				x	x			x		
D 1,5/4…	x									
D 1,5/6…				x						
D 1,5/6…ADO…				x						
D 1,5/8…ADO				x						
D 1/5…ADO		x								
D 10/10…						x				
D 150/31…				x	x					
D 16/12…						x				
D 2,5/5.P…		x	x							
D 2,5/5…						x				
D 2,5/5…ADO		x								
D 2,5/6…						x				
D 2,5/8…						x				
D 2,5/8…ADO…				x						
D 240/36…				x	x					
D 35/16…						x				
D 4/6.P…				x	x			x		
D 4/6…						x				
D 4/6…ADO		x								
D 4/6…ADO				x						
D 4/8…				x						
D 4/8…ADO…				x						
D 6/10…				x	x			x	x	x
D 6/8.P				x	x				x	
D 6/8.ST…				x	x				x	
D 6/8…						x				
D 6/8…ADO…				x						
D 70/22…				x	x					
DB 1,5/6…						x				
DB 1/5…						x				
DB 2,5/5…						x				
DB 2,5/8…						x				
DB 4/6…						x				
DB 4/8…						x				
DF 6				x				x		
DH 1,5/6…						x				
DH 1/5…						x				
DH 2,5/5…						x				
DH 2,5/8…						x				
DH 4/6…						x				
DH 4/8…						x				
DL 10/17,5…						x				
DR 1,5/4…	x									
DR 1,5/5…						x				
DR 1,5/6…						x				
DR 1/5…						x				
DR 2,5/10…						x				
DR 2,5/5…						x				

	MF-W 9/4	MF-W 9/5	MF-W 9/5 F	MF-W 9/6	MF-W 9/6.2 F	MF-W 5/5 mini	MF 10/5	MF 10/6	MF 10/8	MF 10/10
DR 2,5/8…						x				
DR 4/6…						x				
DR 4/8…				x	x				x	
DR 4/8…ADO…						x				
DS 1,5/6…						x				
DS 1/5…						x				
DS 2,5/5…						x				
DS 2,5/8…						x				
DS 4/6…						x				
DS 4/8…						x				
HD 10/12…		x								
HD 120/30…		x								
HD 16/14…		x								
HD 185/36…		x								
HD 2,5/6…				x						
HD 35/16…		x								
HD 4/9…		x								
HD 6/14…				x						
HD 6/8…				x						
HD 6/9…				x						
HD 70/22…		x								
M 1,5/6…				x				x		
M 10/10…				x	x					x
M 10/16…				x	x			x	x	x
M 16/12.PE.N				x						
M 16/12…				x	x			x	x	x
M 2,5/6,5…						x				
M 2,5/6…						x				
M 35/16…				x	x			x	x	x
M 4/6…				x				x		
M 4/6…AP…				x						
M 4/7…				x	x			x		
M 4/8…				x	x				x	
M 6/12…				x						
M 6/13…				x						
M 6/8…				x	x				x	
M 70/22…				x	x			x	x	x
M 95/26…				x	x			x	x	x
MA 2,5/5…		x	x				x			
MB 10/10…				x	x					x
MB 10/12 SF….				x						
MB 10/22…		x								
MB 10/24…		x						X	X	X
MB 25/30…				x	x			x	x	x
MB 4/6…				x				x		
MB 6/8…				x	x				x	
MB 70/10…				x	x					x
ML 10/13…				x	x					x
MS 4/6…				x	x			x		
MS 6/8…				x	x				x	
MTC 6				x				x		
MU 10/13…				x	x					x
MU 10/14,5…				x	x					x
T 1,5/6…				x		X				
T 2,5/5…		x								
T 2,5/6…				x						
T 4/6…				x						

Wieland

	MF 8/5	MF 10/5	MF 12/5	MF 10/6
9700 A/5…	X	X	X	
9700 A/6…				X
9700 A/8…				X
9700 A/10…				X
9700 A/12…				X
9700 A/16…				X
9700 B…				X
9701 A/6…A/16				X
9708/2 …				X
9760 U…				X
9785 U…				X

	MF 8/5	MF 10/5	MF 12/5	MF 10/6
9786 U…				X
AKB…	X	X	X	
AKT…	X	X	X	
flare Move … (6,2mm)				X
Terminal adapter revos Basic	X	X	X	
Terminal adapter revos HD	X	X	X	
Terminal adapter revos Power	X	X	X	
RV2../…	X	X	X	
UET..	X	X	X	
WEB…	X	X	X	
WEF 1…				X

Individual mounting is required if the terminal pitch is larger than the marker.

Wieland

	MF 8/5	MF 10/5	MF 12/5	MF 10/6
WEG…	X	X	X	
WK 2,5…	X	X	X	
WK 2,5-4 KI…	X	X	X	
WK 2,5-4 KOI…	X	X	X	
WK 2,5-3 D…	X	X	X	
WK 2,5 U/D…	X	X	X	
WK 4…				X
WK 4 D…				X
WK 4 E…				X
WK 4/SI-D…				X
WK 4 TK…				X
WK 4 THSI …				X
WK 6…				X
WK 10/SI…				X
WKC 1 …	X	X		
WKC 2,5 …				X
WKC 1 TKG…	X	X		
WKC 2,5 TKG…				X
WKN 10…				X
WKN 16…				X
WKN 2,5 E…	X	X	X	
WKN 35…				X
WKN 4 …				X
WKN 70…				X
WK/3-6…				X
WK/4-8…				X
WKB 2,5…	X	X	X	
WKF 1,5 E…	X	X	X	
WKF 1,5 KOI…	X	X	X	
WKF 10...				X
WKF 16...				X
WKF 35…				X
WKF 2,5...	X	X	X	
WKF 2,5 D…	X	X	X	
WKF 2,5/M…	X	X	X	
WKF 4...				X
WKF 4 TK...				X
WKF 6...				X
WKFN 2,5…	X	X	X	
WKFN 2,5 E...	X	X	X	
WKFN 4…				X
WKFN 4 E…				X
WKI 10…				X
WKI 16…				X
WKI 35…				X
WKI 4…				X
WKIF 2,5 …	X	X	X	
WKM 2,5…	X	X	X	
WKMF 2,5../1,5	X	X	X	
WKM 4…				X

Cabur

	MF 10/5 Cabur	MF 12/5 Cabur
AFO.2…	X	X
CAM…	X	X
CBC.2… - CBC.35…	X	X
CBD.2… - CBD.70…	X	X
CBE.2…	X	
CBR.2…	X	X
CNT.16…	X	X
CNT.35…	X	X
CNT.6…	X	X
CVF.4…	X	X
DAS.4…	X	X
DBC.2…	X	
DSFA.4	X	
DSS.4…	X	
FDP.2…	X	X
FFS.4…	X	X
FPC.10…	X	X
FPL.10…	X	X
FVS.4…	X	X
MAC.6…	X	X
MPFA.4…	X	
MPS.2…	X	X
MPS.4…	X	X
NCS…	X	X
NCV…	X	X
PDF.2…	X	X
RFI.2…	X	
RN.2…	X	
RP.4…	X	
SCB.4…	X	X
SCB.6…	X	X
SFO.4…	X	X
SFR.4…	X	X
SFR.6…	X	X
TC/PO…	X	X
TDE.2…	X	X
TE.10…	X	X
TE.16…	X	X
TE.50…	X	X
TE.6…	X	X
TEC.10…	X	X
TEC.16…	X	X
TEC.35…	X	X
TEC.6…	X	X
TEC.70…	X	X
TED.4…	X	X
TEO.2…	X	X
TEO.4…	X	X
TLD.2…	X	X
TLE.2	X	X
TLS.2…	X	X
TR.2…	X	
TR.4…	X	X
VPC.2…	X	X

Individual mounting is required if the terminal pitch is larger than the marker.

Cross-reference table

Siemens

	MF-SI 8/5	MF-SI 10/5	MF-SI 8/6	MF-SI 10/6	MF-SI 7/5-6,5	MF-SI 10/5-6,5	MF 5/4	MF 5/5	MF 8/5	MF 10/5	MF 12/5	MF 5/6	MF 10/6	MF 10/8	MF 10/10
8WA1 011-0DG…			x	x											
8WA1 011-1BF…	x	x													
8WA1 011-1BG…			x	x											
8WA1 011-1BH…			x	x											
8WA1 011-1BK…			x	x											
8WA1 011-1BM…			x	x											
8WA1 011-1BP…			x	x											
8WA1 011-1DF…	x	x													
8WA1 011-1DG…			x	x											
8WA1 011-1DH…			x	x											
8WA1 011-1EE…			x	x											
8WA1 011-1EF…	x	x													
8WA1 011-1MH…			x	x											
8WA1 011-1NF…	x	x													
8WA1 011-1NG…			x	x											
8WA1 011-1NH…			x	x											
8WA1 011-1PF…	x	x													
8WA1 011-1PG…			x	x											
8WA1 011-1PH…			x	x											
8WA1 011-1PK…			x	x											
8WA1 011-1PM…			x	x											
8WA1 011-1SF…			x	x											
8WA1 011-2BG11					x	x									
8WA1 011-2DG11					x	x									
8WA1 011-3DF…	x	x													
8WA1 011-3DG…			x	x											
8WA1 011-3DH…			x	x											
8WA1 011-3JF…	x	x													
8WA1 011-6BG11					x	x									
8WA1 011-6DG11					x	x									
8WA1 011-6EG…					x	x									
8WA1 204			x	x											
8WA1 205			x	x											
8WA1 206			x	x											
8WA1 221	x	x													
8WA1 232			x	x											
8WA1 304			x	x											
8WA1 305			x	x											
8WA1 501	x	x													
8WA1 604			x	x											
8WA2 011-…NK23			x	x											
8WA2 011-1BF….	x	x													
8WA2 011-1BG…			x	x											
8WA2 011-1BH…			x	x											
8WA2 011-1BJ…			x	x											
8WA2 011-1BK…			x	x											
8WA2 011-1DF…	x	x													
8WA2 011-1DG…			x	x											
8WA2 011-1DH…			x	x											
8WA2 011-1DJ…			x	x											
8WA2 011-1DK…			x	x											
8WA2 011-1EF20	x	x													
8WA2 011-1LF20	x	x													
8WA2 011-1NG23			x	x											
8WA2 011-1NH23			x	x											
8WA2 011-1PF…	x	x													
8WA2 011-1PG…			x	x											
8WA2 011-1PH…			x	x											
8WA2 011-1PJ…			x	x											
8WA2 011-1PK…			x	x											
8WA2 011-1SG…			?	?											
8WA2 011-2BG…			x	x											
8WA2 011-2DG…			x	x											
8WA2 011-3JG…			x	x											
8WA2 011-3JH23			x	x											
8WA2 011-3KE	x	x													
8WA2 011-6EG…			x	x											
8WA9 200			x	x											
8WH1 000-0AN…					x	x									
8WH1 000-0AQ…					x	x									
8WH1 000-0AS…					x	x									
8WH1 000-0AU…					x	x									
8WH1 000-0CN…					x	x									
8WH1 000-0CQ…					x	x									
8WH1 001-0…K…															x
8WH1 001-0…M…															x
8WH1 001-0BJ…															x
8WH1 001-0BJ…															x

Individual mounting is required if the terminal pitch is larger than the marker.

Siemens

	MF-SI 8/5	MF-SI 10/5	MF-SI 8/6	MF-SI 10/6	MF-SI 7/5-6,5	MF-SI 10/5-6,5	MF 5/4	MF 5/5	MF 8/5	MF 10/5	MF 12/5	MF 5/6	MF 10/6	MF 10/8	MF 10/10
8WH1 001-0BJ…															x
8WH1 060-0A…00					x	x									
8WH1 070-0A…					x	x									
8WH2 …-6AF…								x	x	x					
8WH2 …-6AG…												x	x		
8WH2 …-6CF…								x	x	x					
8WH2 …-6CG…												x	x		
8WH2 00…-0AE…							x								
8WH2 00…-0AF…								x	x	x					
8WH2 00…-0AG…												x	x		
8WH2 00…-0CE…							x								
8WH2 00…-0CF…								x	x	x					
8WH2 00…-0CG…												x	x		
8WH2 00…-0AH…														x	
8WH2 00…-0AJ…														x	
8WH2 00…-0AK…														x	
8WH2 00…-0AM…														x	
8WH2 00…-0CH…														x	
8WH2 000-1AG…														x	
8WH2 000-1BG…														x	
8WH2 000-1GG…												x	x		
8WH2 000-1HG…														x	
8WH2 000-1JG…												x	x		
8WH2 000-1MG…												x	x		
8WH2 000-1NG…														x	
8WH2 000-1RG…														x	
8WH2 003-5…F…								x	x						
8WH2 02…-0AE…							x								
8WH2 02…-0AF…								x	x						
8WH2 02…-0AG…												x	x		
8WH2 02…-0CE…							x								
8WH2 02…-0CF…								x	x						
8WH2 02…-0CG…												x	x		
8WH2 02…-4…F…								x	x						
8WH2 020-5…F…								x	x						
8WH2 03…-0…F…								x	x						
8WH2 04…-0…F…								x	x						
8WH2 040-4L…								x	x						
8WH2 103-…BF…								x	x	x					
8WH2 103-…BG…												x	x		
8WH2 50…-0…F…								x	x						
8WH2 50…-0…G…												x	x		
8WH2 50…-0…H…														x	
8WH2 50…-6…F…								x	x						
8WH2 520-0…F…								x	x						
8WH2 520-0…G…												x	x		
8WH3 00…-0…E…								x	x	x					
8WH3 00…-0…F…												x	x		
8WH3 000-6AE…								x	x	x					
8WH3 000-6AF…												x	x		
8WH3 000-6CF…												x	x		
8WH3 020-…E…								x							
8WH3 1…-2…E…								x	x	x					
8WH3 1…-2…F…												x	x		
8WH3 1…-3…E…								x	x	x					
8WH3 1…-3…F…												x	x		
8WH4 00…-0…F…								x	x	x					
8WH4 00…-0…G…												x	x		
8WH4 00…-0…H…														x	
8WH4 001-…F…									x	x					
8WH5 00…-0…F…								x	x	x					
8WH5 10…-…F…								x	x	x					
8WH5 100-…KG…												x	x		
8WH5 103-6…F…								x	x	x					
8WH5 12…-…MF…								x							
8WH9 040-1AB…								x							
8WH9 040-1BB…								x							
8WH9 040-1CB…								x							
8WH9 040-1DB…								x							
8WH9 040-1EB…								x							
8WH9 040-1FB…								x							
8WH9 050-0AB…															
8WH9 050-0LB…								x							
8WH9 050-1KB…												x			
8WH9 050-1LB…												x			
8WH9 050-1MB…												x			
8WH9 150-0CA00					x	x									

Beckhoff

	MF-W 5/5 mini	ESG 8/11	MF 5/10
I/O modules	X	X	X

Adels

	MF 5/7,5
RKV Transformer terminal	X

Individual mounting is required if the terminal pitch is larger than the marker.

Cross-reference table

Allen-Bradley

	MF-WO 5/5	MF-WO 9/5	MF-WO 12/5	MF-WO 9/6	MF-WO 12/6	DEK 5/3,5	DEK 5/5	DEK 5/6	DEK 5/8	WS 12/3,5	WS 8/5	WS 10/5	WS 10/5 m.	WS 12/5	WS 15/5	WS 10/6	WS 10/6 m.	WS 12/6	WS 12/6,5	Ws 12/6,5	ZS 10/5	ZS 12/6	ZS 15/5
1492-J10…							X												X				
1492-J16…							X												X				
1492-J2Q…							X							X									
1492-J3…							X							X									
1492-J35…							X												X				
1492-J3F…							X							X									
1492-J3P…							X							X									
1492-J3PTP…							X							X									
1492-J3TW…							X							X									
1492-J4…								X										X					
1492-J4M…								X										X					
1492-J50…							X												X				
1492-J6…									X										X				
1492-J70…							X												X				
1492-JC3…							X							X									
1492-JD3…							X				X												
1492-JD3C…							X				X												
1492-JD3DF…							X				X												
1492-JD3DR…							X				X												
1492-JD3F…							X				X												
1492-JD3P…							X						X										
1492-JD3PSS…							X						X										
1492-JD3PSSTP							X						X										
1492-JD3PTP…							X						X										
1492-JD3RB…							X				X												
1492-JD3RC001							X				X												
1492-JD3SS…							X				X												
1492-JDC3…							X							X									
1492-JDG3…							X				X												
1492-JDG3C…							X				X												
1492-JDG3P…							X						X										
1492-JDG3PSS…							X						X										
1492-JDG3PSSTP							X						X										
1492-JDG3PTP…							X						X										
1492-JG10…									X										X				
1492-JG16…									X										X				
1492-JG2Q…							X							X									
1492-JG3…							X							X									
1492-JG35…									X										X				
1492-JG3TW…							X							X									
1492-JG4…								X										X					
1492-JG50…									X										X				
1492-JG6…									X										X				
1492-JG70…									X										X				
1492-JKD3…							X							X									
1492-JKD3TP…							X							X									
1492-JPO…								X										X					
1492-JTC3…							X							X									
1492-K2…													X										
1492-K3…																	X						
1492-KG2…													X										
1492-KG3…																	X						
1492-KW2…													X										
1492-KW3…																	X						
1492-L10…									X														X
1492-L16…									X										X				X
1492-L16D…									X										X				X
1492-L2…						X				X													
1492-L2Q…						X				X													
1492-L2T…						X				X													
1492-L3…							X					X									X		
1492-L35…									X										X				X
1492-L3P…							X					X											
1492-L3Q…							X					X									X		
1492-L3QS…							X					X											
1492-L3T…							X					X									X		
1492-L4…								X								X						X	
1492-L4Q…								X								X						X	
1492-L4T…								X								X						X	
1492-L6…									X									X				X	
1492-L6T…									X									X				X	
1492-LC3…							X					X											
1492-LD2…						X				x													
1492-LD2C…						X				X													
1492-LD3…							X					X											
1492-LD3C…							X					X											
1492-LD4…								X								X							
1492-LD4C…								X								X							

The markers must be mounted individually when the terminal pitch is larger than 6 mm.

Allen-Bradley

	MF-WO 5/5	MF-WO 9/5	MF-WO 12/5	MF-WO 9/6	MF-WO 12/6	DEK 5/3,5	DEK 5/5	DEK 5/6	DEK 5/8	WS 12/3,5	WS 8/5	WS 10/5	WS 10/5 m.	WS 12/5	WS 15/5	WS 10/6	WS 10/6 m.	WS 12/6	WS 12/6,5	Ws 12/6,5	ZS 10/5	ZS 12/6	ZS 15/5
1492-LD4DF…								X								X							
1492-LD4DR…								X								X							
1492-LD4RB…								X								X							
1492-LD4SS…								X								X							
1492-LDAG3…							X					X											
1492-LDC3…							X					X											
1492-LDG2…						X				X													
1492-LDG3…							X					X											
1492-LDG3P…							X					X											
1492-LDG4…								X								X							
1492-LG10…									X									X					X
1492-LG16…									X										X				X
1492-LG2…						X				X													
1492-LG3…							X					X									X		X
1492-LG35…									X										X				X
1492-LG4…								X								X					X	
1492-LG6…									X									X				X	
1492-LKD3…							X					X											
1492-LM3…							X					X									X		
1492-LM3Q…							X					X									X		
1492-LMG3…							X					X									X		
1492-LMJ3…							X						X								X		
1492-LMJG3…							X						X								X		
1492-LMP3…							X					X									X		
1492-LMP3Q…							X					X									X		
1492-LS…							X																
1492-LTF3…							X						X										
1492-W16S…					X																		
1492-W3…			X																				
1492-W4…					X																		
1492-W4TW…				X																			
1492-W6…					X																		
1492-WFB4			X	X																			
1492-WG10S…					X																		
1492-WG16S…					X																		
1492-WG4…					X																		
1492-WG6…					X																		
1492-WM3…	X																						
1492-WM4…				X																			
1492-WMD…	X																						
1492-WMG…				X																			
1492-WR3…		X																					
1492-WTF3…		X																					
1492-WTS3…		X																					

Télémecanique

	MF 8/5	MF 10/5	MF 12/5	MF 10/6
AB1 AA135U…	X	X	X	
AB1 AA235U…				X
AB1 AATP135U…	X	X	X	
AB1 AATP235U…				X
AB1 AASC…				X
AB1 AASF…				X
AB1 AAET135UGR	X	X	X	
AB1 AAET235…				X
AB1 RR235U…	X	X	X	
AB1 RR435U…				X
AB1 RR635U2				X
AB1 RR1035U2				X
AB1 RR1635U2				X
AB1 RRTP235U…	X	X	X	
AB1 RRTP435U…				X
AB1 RRTP635U2				X
AB1 RRTP1035U2				X
AB1 RRTP1635U2				X
AB1 RRSC435UGR				X
AB1 RRSF435U				X
AB1 RRET…	X	X	X	
AB1 VV235U	X	X	X	

	MF 8/5	MF 10/5	MF 12/5	MF 10/6
AB1 VV435U				X
AB1 VV635U				X
AB1 VVN…				X
AB1 TP…				X
AB1 SC435U				X
AB1 FUSE435U				X
AB1 SF435U				X
AB1 D11435U				X
AB1 F…				X
AB1 E…				X
AB1 D…				X
AB1 TR…				X
AB1 NEN…				X
AB1 BB…				X
AB1 BC…				X
AB1 VV215	X	X	X	
AB1 VV415				X
AB1 TP215				X
AB1 BV10235U				X
AB1 DV10235U				X
AB1 BCP20235U				X

The markers must be mounted individually when the terminal pitch is larger than 6 mm.

Cross-reference table

Woertz

	MF-WO 5/5	MF-WO 9/5	MF-WO 12/5	MF-WO 9/6	MF-WO 12/6
2711…	X				
2759…	X				
2760…	X				
3410…					X
3424…					X
3426…					X
3427…					X
3428…					X
3429…					X
3430…				X	
3436/4…					X
3436…					X
3436/10…					X
3437…					X
3438…					X
3440…					X
3450…					X
3452…					X
3452/10…					X
3452/16…					X
3472…					X
3473…					X
3477…					X
30003…					X
30005…					X
30008…					X
30009…					X
30041…					X
30123…					X
30124…					X
30125…					X
30127…					X
30128…					X
30130…					X
30137…					X
30138…					X
30143…					X
30146…					X
30150…		X			
30168…					X
30172…					X
30176…					X
30191…					X
30195…					X
30197…					X
30200…					X
30228…					X
30290…					X
30291…					X
30400…	X				
30403…	X				
30430…				X	
30431…				X	
30432…				X	
30544/4…					X
30544/6…					X
30544/10…					X
30544/16…					X
30550…					X
30800…					X
30810…		X			
30840…					X
30841…					X
30842…					X
30843…					X
30844…					X
30860…		X			
30870…		X			
30880…		X			
30890…				X	
30891…				X	
30902…				X	
30903…		X			
30904…				X	
30930…				X	
30950…				X	
30951…				X	
30952…				X	

	MF-WO 5/5	MF-WO 9/5	MF-WO 12/5	MF-WO 9/6	MF-WO 12/6
30973…		X			
45124…	X				
45136…	X				
45140…	X				
45148…	X				
45156…	X				
45163…	X				
45165…	X				
45170…	X				
45179…	X				
45200…	X				
45217…	X				
45218…	X				
45219…	X				
45220…	X				
45235…	X				
45305T…	X				
45306T…	X				
45307T…	X				
45308T…	X				
45309T…	X				
45310T…	X				
45311T…	X				
45312T…	X				
45313T…	X				
45314T…	X				
45315T…	X				
45316T…	X				
45323T…	X				
45329T…	X				
45372T…	X				
45373T…	X				
45374T…	X				
45375T…	X				
45376T…	X				
45377T…	X				
45378T…	X				
45385T…	X				
45387T…	X				
45388T…	X				
45389T…	X				
45393T…	X				
45394T…	X				
45441T…	X				
45442T…	X				
45443T…	X				
45444T…	X				
45445T…	X				

	MF 8/5	MF 10/5	MF 10/6
393 03			X
393 04			X
393 05			X
393 07			X
393 60	X	X	
393 61			X
393 62			X
393 64			X
393 66			X
393 68			X
393 70			X
393 71	X	X	
393 72			X
393 73			X
393 74			X
393 76			X
393 78			X
393 81			X
393 82			X
394 00			X
394 02			X
396 01	X	X	
396 02	X	X	
396 03	X	X	
396 04			X
396 11	X	X	
396 12	X	X	
396 13	X	X	
396 14			X
396 21	X	X	
396 24			X
396 23	X	X	

Legrand

	MF 8/5	MF 10/5	MF 10/6
390 60	X	X	
390 61			X
390 62			X
390 64			X
390 66			X
390 68			X
390 70			X
390 77	X	X	
390 78			X
390 76			X
390 80			X
390 81			X
390 84			X
390 85			X
390 86			X
393 00	X	X	
393 01			X
393 02			X

Festo

	MFF 10/6	MFF 9/4	ESG 10/17	ESG 9/20	ESG-M 8/20	ESG-M 9/17
CPE	X					
MZBH	X					
MOZBH	X					
MEBH	X					
MOEBH	X					
JMN2H, MN2H						X
JMN2H, MN1H				X		
JMT2H/MT2H-...-4,0				X		
JMT2H, MT2H-...-7,0			X			
MVH, MOVH, MDH, MODH				X		
MHA1, MHP1		X				
CPV10/14	X					
CPV18				X		
CP-E16	X					
CP-A08	X					
MV-BZ Typ 02				X		
KMYZ	X					
Pneumatic elements and valve clusters					X	

Murr

	ESG-M 9/17	ESG-M 8/20	ESG 9/20	MF 10/5	MF 12/5
MASI	X				
MVP	X				
Cube67		X			
M8 distributor				X	
MVK		X			
Optocoupler					X
Miro-Series					X

Cross-reference table

Markers

	MF 5/4	MF 5/5	MF 8/5	MF 10/5	MF 12/5	MF 4/5,2	MF 5/6	MF 10/6	MF 5/7,5	MF 10/8	MF 10/10	MF 5/7,5	MF-W 9/4	MF-W 9/4.2 F	MF-W 5/5 mini	MF-W 9/5	MF-W 9/5 F	MF-W 9/5.2 F	MF-W 9/6	MF-W 9/6.2 F	MF-SI 8/5	MF-SI 10/5	MF-SI 8/6	MF-SI 10/6	MF-SI 7/5-6,5	MF-SI 10/5-6,5	MF-WO 5/5	MF-WO 9/5	MF-WO 12/5	MF-WO 9/6	MF-WO 12/6	MF 10/5 Cabur	MF 12/5 Cabur	ESG 5/10	ESG 9/20	ESG-M 9/17	ESG-M 8/20	MFF 9/4	MFF 10/6	ESG 10/17
Phoenix																																								
UC-TM 5			X	X	X																																		
UC-TM 6								X																															
UC-TM 8										X																													
UC-TM 10											X																												
UC-TM 12											X																												
UC-TM 16											X																												
UC-TMF 4	X																																						
UC-TMF 5		X																																					
UC-TMF 6							X																																
ZBF 4	X																																						
ZBF 5		X																																					
ZBF 6							X																																
ZB 5			X	X	X																																		
ZB 6								X																															
ZB 8										X																													
ZB 10											X																												
BN ZB 5,2						X																																	
BN ZB 7,5									X																														
WAGO																																							
209-… (4 mm)													X	X																									
793-… (5 mm)																X	X	X																					
793-… (6 mm)																			X	X																			
248-… (5 mm)															X																								
Woertz																																							
RB/5x5																											X												
RB/5x9																												X											
RB/5x12																													X										
RB/6x9																														X									
RB/6x12																															X								
Cabur																																X	X						
CNU/8																																X	X						
ABB-Stotz / Entrelec																																							
RC55															X																								
RC410													X	X																									
RC510				X												X	X																						
RC610								X											X																				
RC810										X									X																				
Wieland																																							
9705 A/5…			X	X	X																																		
9705 A/6…								X																															
Télémecanique																																							
AB1-B5			X	X	X																																		
AB1-B6								X																															
Murr																																							
KPX 4/10	X																																						
KPX 5/10…				X																																			
KPX 6/10…								X																															
KPX 5/5-5 ZS		X																																					
KPX 6/5-6 ZS							X																																
KWI / KLG / KET 5/10…				X																																			
KWI / KET 6/10…								X																															
KSI 5/7																									X														
KSI 5/10																										X													
KSI 5/7-5																					X																		
KSI 5/10-5																						X																	
KSI 6/7-5																							X																
KSI 6/10-5																								X															
KAB 6/12																															X								
KAB 5/5,4-5																											X												
KAB 5/9-5																												X											
KAB 5/12-5																													X										
KAB 6/9-6																														X									
WGO 5/5-5															X																								
WGO 5/10-5																X			X																				
WGO 5/10-5 F																	X	X		X																			
TK 4,5-7,5									X																														
KS 5/10																																	X						
KES 20x8																																				X			
ABB 17-9																																			X				

Markers

	MF 5/4	MF 5/5	MF 8/5	MF 10/5	MF 12/5	MF 4/5,2	MF 5/6	MF 10/6	MF 5/7,5	MF 10/8	MF 10/10	MF 5/7,5	MF-W 9/4	MF-W 9/4.2 F	MF-W 5/5 mini	MF-W 9/5	MF-W 9/5 F	MF-W 9/5.2 F	MF-W 9/6	MF-W 9/6.2 F	MF-SI 8/5	MF-SI 10/5	MF-SI 8/6	MF-SI 10/6	MF-SI 7/5-6,5	MF-SI 10/5-6,5	MF-WO 5/5	MF-WO 9/5	MF-WO 12/5	MF-WO 9/6	MF-WO 12/6	MF 10/5 Cabur	MF 12/5 Cabur	ESG 5/10	ESG 9/20	ESG-M 9/17	ESG-M 8/20	MFF 9/4	MFF 10/6	ESG 10/17
Festo																																								
ISB-6x10																																						X	
MH-BZ-80X																																					X		
IBS-10x17																																							X
ISB-9x20																																		X					
IBS-8x20																																				X			
ISB-9x17																																			X				

Terminal marker WAD

- Top-quality and resistant printing with PrintJet printer
- WAD marker and cover for the terminals of the W-series and end brackets WEW 35/2 and ZEW 35/2
- Available as neutral marker, custom printing or with lightning flash
- Fast and easy assembling

The WAD-type markers can be printed by PrintJet printer. Colour printing with the PrintJet PRO, in particular, enables terminal strips to be labeled in a variety of noticeable manners.

Technical data

Material	Polyamide PA 66
Temperature range	–40° … +100 °C
Flammability rating	V2 according to UL 94
Suitable for	Feed-through terminal WDU 2.5, WDU 4, WDU 6 and WDU 10 End bracket WEW 35/2 and ZEW 35/2
Printable with	PrintJet and PrintJet PRO
Not printable with	SMark Laser and Plotter

Ordering data

Type	Colour	Qty.	Order No.
WAD 5 MC NE WS	white	48	**1112910000**
WAD 5 MC NE GE	yellow	48	**1112920000**
WAD 8 MC NE WS	white	48	**1112940000**
WAD 8 MC NE GE	yellow	48	**1112950000**
With lightning flash			
WAD 5 MC B GE/SW	yellow	48	**1120450000**
WAD 8 MC B GE/SW	yellow	48	**1120470000**
Custom printing			
WAD 5 MC SDR		12	**1112930000**
WAD 8 MC SDR		12	**1112970000**

This tag holder is specially conceived for the IDK 1.5N two-tier terminal of the I-series. The flexible hinge mechanism allows cross-connections to be connected or disconnected at little effort. It can be fitted with four DEK 5 tags or two WS 10/5 Middle connector markers.

Snap Mark

Technical specification

Material	Polyamide 66
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C
Material colour	white

Ordering data

Type	Length	Width	Qty	Order No.
Snap Mark I	23 mm	5 mm	50	**1805880000**

Accessories

Type	Length	Width	Qty	Order No.
DEK 5/5 MC	5 mm	5 mm	1000	**1609801044**
WS 10/5 MC middle	10 mm	5 mm	720	**1792000000**

The BZT tag carrier makes possible the clear labelling of the ZDU 2.5/4/6 and ZDUA terminal families. The BZT is used with the WS 10/5 terminal markers. By creating blocks of tag carriers, the ZA version offers the maximum stability.

BZT1 / BZT2

Technical specification

Material	Polyamide
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C
Material colour	beige

Ordering data

Type	Length	Width	Qty	Order No.
BZT 1	8 mm	5 mm	100	**1805490000**
BZT 1 ZA	8 mm	5 mm	100	**1805520000**
BZT 2	12 mm	5 mm	100	**1805480000**
BZT 2 ZA	12 mm	5 mm	100	**1805530000**

Accessories

Type	Length	Width	Qty	Order No.
WS 10/5 MC	10 mm	5 mm	720	**1635000000**

Tag carrier

The SCHT 5 & SCHT 5 S group marker carrier is clipped directly to the TS 32 DIN rail (G-rail) or the TS 35 DIN rail (top-hat rail). It is therefore possible to provide terminal strip labelling irrespective of the terminal and the type of terminal.

SchT 5 / SchT 5 S

Technical specification

Material	Polyamide 66
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C
Material colour	beige

Ordering data

Type	Length	Width	Qty	Order No.
SCHT 5	44.5 mm	19.5 mm	20	**0292460000**
SCHT 5 S	44.5 mm	9.5 mm	20	**1631930000**

Accessories

Type	Length	Width	No. per sheet	Qty	Order No.
ESO 5 white	40 mm	16.5 mm	60	10	**1607710000**
ESO 5 yellow	40 mm	16.5 mm	60	10	**1631350000**
ESO 5P white	40 mm	16.5 mm	60	10	**1670370000**
ESO 5P yellow	40 mm	16.5 mm	60	10	**1670380000**
ESO 5 S white	40 mm	7 mm	140	10	**1631920000**
STR 5 F.SCHT 5	40 mm	16.5 mm	20	20	**0294000000**
STR 5 S. F.SCHT 5 S	40 mm	7 mm	20	20	**1631940000**
ELS 7/40 MC NE GE				40	**1045650000**
ELS 7/40 MC NE WS				40	**1045640000**
ELS 16/40 MC NE GE				40	**1045630000**
ELS 16/40 MC NE WS				40	**1045620000**

The SCHT 7 is a hinged group marker carrier for inlay tags which still allows easy access to the clamping screw. To equip with ESO 7, 4 tags of DEK 5/5 or 2 tags of WS 10/5 Middle.

SCHT 7

Technical specification

Material	Polyamide 66
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C
Material colour	white

Ordering data

Type	Length	Width	Qty	Order No.
SCHT 7	39.3 mm	8 mm	20	**0517960000**

Accessories

Type	Length	Width	No. per sheet	Qty	Order No.
DEK 5/5 MC	5 mm	5 mm		1000	**1609801044**
ESO 7 white	27 mm	6.3 mm	240	10	**1607720000**
ESO 7 yellow	27 mm	6.3 mm	240	10	**1634780000**
ESO 7P white	27 mm	6.3 mm	240	10	**1670390000**
ESO 7P yellow	27 mm	6.3 mm	240	10	**1670400000**
STR 7 SCHT 7	27 mm	6.3 mm	20	20	**0515300000**
WS 10/5 MC middle	10 mm	5 mm		720	**1792000000**

SchT 9/4 and SchT 14/6 are hinged group tag holders for single dekafix and WS tags, allowing easy access to the clamping screws.

SCHT 9/4 / SCHT 14/6

Technical specification

Material	Polyamide 66
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C
Material colour	beige

Ordering data

Type	Length	Width	Qty	Order No.
SCHT 14/6	44.3 mm	6 mm	20	**1269060000**
SCHT 9/4	32 mm	4 mm	20	**1278460000**

Accessories

Type	Length	Width	Qty	Order No.
DEK 5/5 MC	5 mm	5 mm	1000	**1609801044**
WS 12/5 MC	12 mm	5 mm	720	**1609860000**



The ELS-type MultiCard marker can be printed on with PrintJet, plotter or SMark printer. Colour printing with the PrintJet PRO, in particular, enables cables and terminal strips to be labelled in a variety of noticeable manners.

ELS insertion tag

Technical specification

Material	Polyamide PA 66
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C
Suitable for	ELS 6/30: WKM 8/30 (1631910000) and EM 8/30 (1806120000) ELS 7/40 : SchT5S (1631930000) ELS 16/40: SchT5 (0292460000) and WKM 18/43 (1610700000)

Ordering data

Type	Colour	Qty.	Order No.
blank			
ELS 6/30 MC NE WS	white	80	**1045570000**
ELS 6/30 MC NE GE	yellow	80	**1045580000**
ELS 7/40 MC NE WS	white	40	**1045640000**
ELS 7/40 MC NE GE	yellow	40	**1045650000**
ELS 16/40 MC NE WS	white	40	**1045620000**
ELS 16/40 MC NE GE	yellow	40	**1045630000**
Custom printing			
ELS 6/30 MC SDR		16	**1045660000**
ELS 7/40 MC SDR		8	**1045700000**
ELS 16/40 MC SDR		8	**1045690000**

Tag carrier

The EM 8/30 end bracket marker is suitable for labelling the WEW 35/2 and ZEW 35/2 end brackets as well as marker carrier for W-series terminals. The EM 8/30 can be fitted with the ESO 7 and ESO 7P inlay tags. The pocket guarantees that the labelling is well protected against environmental influences.

EM 8/30

Technical specification

Material	Polypropylene
UL 94 flammability rating	HB
Min. temperature, continuous	-40 °C
Max. temperature, continuous	80 °C
Material colour	transparent

Ordering data

Type	Length	Width	Qty	Order No.
EM 8/30	30 mm	8 mm	50	**1806120000**

Accessories

Type	Length	Width	No. per sheet	Qty	Order No.
ESO 7 white	27 mm	6.3 mm	240	10	**1607720000**
ESO 7 yellow	27 mm	6.3 mm	240	10	**1634780000**
ESO 7P white	27 mm	6.3 mm	240	10	**1670390000**
ESO 7P yellow	27 mm	6.3 mm	240	10	**1670400000**

WGB group marker carrier for single dekafix and WS tags. The WGB also covers the cross-connection channels.

Blank WAD covers for labelling with STI pen, or a special printing for the W-series. Cross-connection channels are covered. Also available with lightning flash warning symbol to DIN 30600 (see page B.34).

WGB 5 / WGB 8 / WAD

Technical specification

Material	Polyamide 66
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C

Ordering data

Type	Length	Width	Material colour	Qty	Order No.
WGB 5	33.5 mm	5 mm	beige	50	**1050760000**
WGB 8	33.5 mm	7.7 mm	beige	50	**1050960000**
WAD 5	33.5 mm	5 mm	white	50	**1056060000**
WAD 5 lightning flash	33.5 mm	5 mm	yellow	50	**1053460000**
WAD 8	33.5 mm	8 mm	white	50	**1056160000**
WAD 8 lightning flash	33.5 mm	8 mm	yellow	50	**1053560000**
WAD 12	36.2 mm	12 mm	white	50	**1056260000**
WAD 12 lightning flash	36.2 mm	12 mm	yellow	50	**1055960000**
WAD 27	64 mm	27 mm	white	10	**1062960000**
WAD 27 lightning flash	64 mm	27 mm	yellow	10	**1062860000**

WAD Custom printing

Type	Length	Width	Material colour	Qty	Order No.
WAD 5	33.5 mm	5 mm	white	100	**1790060000**
WAD 8	33.5 mm	8 mm	white	50	**1667700000**

Accessories – WGB 5 / WGB 8

Type	Length	Width	Qty	Order No.
DEK 5/5 MC	5 mm	5 mm	1000	**1609801044**
DEK 5/30 MC	30 mm	5 mm	100	**1951920000**
DEK 5/30 MC SDR	5 mm	30 mm	40	**1025680000**
WS 12/5 MC	12 mm	5 mm	720	**1609860000**



The ZGB 15 / ZGB 30 is a hinged marker carrier. The tag holder can be fitted with the dekafix 5, WS 12/5 connector markers or with the push-in tag ESO 15 / ESO 7.

ZGB 15 / ZGB 30

Technical specification

Material	Polyamide 66
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C
Material colour	white

Ordering data

Type	Length	Width	Qty	Order No.
ZGB 15	15 mm	7 mm	20	**1636530000**
ZGB 30	32 mm	7 mm	20	**1611930000**

Accessories

Type	Length	Width	No. per sheet	Qty	Order No.
DEK 5/5 MC	5 mm	5 mm		1000	**1609801044**
DEK 5/30	30 mm	5 mm		100	**1951920000**
DEK 5/30 SDR	30 mm	5 mm		40	**1025680000**
ESO 7 white	27 mm	6.3 mm	240	10	**1607720000**
ESO 7 yellow	27 mm	6.3 mm	240	10	**1634780000**
ESO 7P white	27 mm	6.3 mm	240	10	**1670390000**
ESO 7P yellow	27 mm	6.3 mm	240	10	**1670400000**
ESO 15 white	15 mm	6 mm	120	1	**1636510000**
STR 7 SCHT 7	27 mm	6.3 mm	20	20	**0515300000**
STR 15 ZGB 15	15 mm	6.3 mm	20	20	**1636520000**
WS 12/5 MC	12 mm	5 mm		720	**1609860000**

Wire and cable markers

Wire and cable markers

Introduction	C.2
Overview	C.3
SlimFix	C.4
SlimFix Clip	C.6
Inlay tags	C.8
Transparent sleeves	C.10
TwinMark	C.14
WriteOn	C.17
CableLine® – Introduction	C.18
CableLine® – Blank markers	C.20
CableLine® – Special print	C.23
CableLine® – International colour code	C.26
CableLine® – Closed wire markers	C.28
CableLine® – Open wire markers	C.45
CableLine® – Cable markers and holders	C.49
CableLine® – Accessories	C.52
Stainless steel markers	C.55
Cable ties	C.58

Wire and cable markers

Weidmüller's range of wire and cable markers provides users with solutions for a wide variety of applications. The applications range from thin wires through to cables with large external diameters. Amongst others, the assortment includes combination systems with individual tags, transparent sleeves and markers that are fastened using cable ties.

Open and closed, printed or blank markers for individual printing are available.

Halogen-free and practically free of pollutants, Weidmüller's wire and cable markers comply with both European and inhouse standards of well-known system manufacturers. Systems are available for:

- Clip-on ready-to-use printed markers according to individual marking requirements
- Marking by digits from a standard set of characters
- Combination of individual pre-printed digits to form a character code
- Customer prints utilising one of the following options: SMark-Laser printer, PrintJet printer, laser printer, plotter, thermal transfer, Matrix printer or pen.

A sample selection is available in Weidmüller's sample bag of wire and cable markers: order no. **1640420000**.

Owing to the sheer number of possible applications and environmental influences such as moisture, radiation, gases or heat/cold to which the products can be exposed, Weidmüller accepts no liability for the suitability of products in all customer applications. Suitability tests for specific applications must therefore be carried out by the customer. However, Weidmüller will be happy to provide help and advice upon request.

Due to the different identification system available on the market, we wish to point out that Weidmüller does not guarantee industrial identification products if the Weidmüller components (markers – transparent sleeves – ink/toner/colour ink ribbons – printing systems) are combined with third-party products, unless Weidmüller has explicitly agreed for the purpose of an individual application.

Applications chart



* Non-binding reference values. Please take into consideration the external diameter of the insulation.

SlimFix

SlimFix are wire and cable markers featuring a space-saving design. The markers can also be attached to the wires after these have been installed. They are made from halogen-free material and fulfil V0/V2 flammability class requirements. SlimFix is an approved and listed marker for traffic engineering. Attaching even small markers is no problem when using the SF tool.

- Halogen-free material
- V0/V2 flammability class
- Approved and listed markers, includes traffic engineering
- Attach to conductor cross-sections greater than 16.0 mm² with cable ties
- Markers available in the proven MultiCard format
- Also available in flammability class V0. Contact Weidmüller for more information.



SFX 10/23

SFX 14/23

SFX 9/24

Technical data

SF/SFX	
Material	Wemid / Polyamide
Flammability class to UL94	V0/V2
Temperature range	V0: –5 °C ... 120 °C/V2: –40 °C ... 100 °C
Possible printing systems	SMark-Laser, PrintJet, Plotter MCP Plus oder MC-Mobilo
Colour	Other colours on reques
	● brown ● red ● orange ● yellow, ● green ● blue ● violet ● grey O white
Notes on mounting	SF: Slide onto unconnected wires; attach to connected wires using SlimFix tool SFX: Attach using cable ties

Ordering data

Minimum order quantity	1 pack
Special printing	Specify special printing and colours per diskette, Excel file or using the M-Print® PRO software.

Simply slip on the marker...



...or use the special SF tool





SlimFix made from V2 material is a conductor and cable marker system with a space-saving design. The SF V2 made from halogen free material exhibits good mechanical and printing characteristics. Arial is the recommended font when using the PrintJet. The SF tool permits easy installation.

- halogen free material
- flammability rating V2
- SFX attached with cable ties (3.6 mm wide)

SF - blank

Technical specification

Material	Polyamide 66
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C

Selection table

Type	Cond. ext. Ø. (max.) mm	Cond. cross-section mm²
SF 00	0.9 / 1.00 – 1.30	< 0.25
SF 0	1.20 – 1.60	0.25 – 0.50
SF 1	1.70 – 2.10	0.50 – 0.75
SF 2	2.20 – 2.90	0.75 – 1.50
SF 3	3.00 – 3.70	1.50 – 2.50
SF 4	3.60 – 6.00	2.50 – 4.00
SF 4.5	4.10 – 4.90	4.00 – 6.00
SF 5	4.80 – 7.40	6.00 – 10.00
SF 6	5.80 – 7.80	10.00 – 16.00
SFX	from 7.00	from 16.00

SFX only: max. width of cable tie = 3.60 mm

Ordering data

Type	Printing area	Length	Qty.	Order No. white	Order No. yellow	Order No. blue	Order No. red
SF 00/12	12x3.2 mm	12	400	**1919290000**	**1919260000**	**1919270000**	**1919280000**
SF 0/12	12x3.2 mm	12	400	**1919240000**	**1919210000**	**1919220000**	**1919230000**
SF 1/12	12x3.2 mm	12	400	**1919390000**	**1919340000**	**1919360000**	**1919320000**
SF 2/12	12x3.6 mm	12	400	**1919490000**	**1919470000**	**1919480000**	**1919460000**
SF 3/12	12x4.6 mm	12	320	**1919540000**	**1919520000**	**1919550000**	**1919530000**
SF 4/12	12x5.7 mm	12	128	**1919600000**	**1919580000**	**1919590000**	**1919570000**
SF 5/12	12x7.4 mm	12	160	**1919650000**	**1919620000**	**1919630000**	**1919640000**
SF 00/21	21x3.2 mm	21	400	**1918580000**	**1918560000**	**1918590000**	**1918570000**
SF 0/21	21x3.2 mm	21	400	**1918500000**	**1918480000**	**1918510000**	**1918490000**
SF 1/21	21x3.2 mm	21	400	**1918630000**	**1918610000**	**1918620000**	**1918600000**
SF 2/21	21x3.6 mm	21	400	**1918690000**	**1918660000**	**1918700000**	**1918670000**
SF 3/21	21x4.6 mm	21	320	**1918910000**	**1918890000**	**1918920000**	**1918900000**
SF 4/21	21x5.7 mm	21	192	**1919080000**	**1919060000**	**1919090000**	**1919070000**
SF 4,5/21	21x7.4 mm	21	96	**1919020000**	**1919000000**	**1919030000**	**1919010000**
SF 5/21	21x7.4 mm	21	160	**1919140000**	**1919120000**	**1919150000**	**1919130000**
SF 6/21	21x8.4 mm	21	160	**1919190000**	**1919170000**	**1919200000**	**1919180000**
SFX 10/23	23x5 mm	23	160	**1852390000**	**1852360000**	**1852400000**	**1852370000**
SFX 14/23	23x8.2 mm	23	160	**1852440000**	**1852410000**	**1852450000**	**1852420000**
SFX 9/24	23.9x9 mm	24	160	**1852490000**	**1852460000**	**1852500000**	**1852470000**
SFX 11/60	11x44 mm	60	60	**1860120000**	**1860150000**	**1051870000**	**1963650000**
SFX 30/60* n	30x45 mm	60	30	**1083230000**	**1083240000**		

*** Order No. for colour grey: 1083250000**

SF - Custom printing

Type	Printing area	Length	Qty.	Order No.
SF 00/12	12x3.2 mm	12	80	**1919300000**
SF 0/12	12x3.2 mm	12	80	**1919250000**
SF 1/12	12x3.2 mm	12	80	**1919420000**
SF 2/12	12x3.6 mm	12	80	**1919500000**
SF 3/12	12x4.6 mm	12	64	**1919510000**
SF 4/12	12x5.7 mm	12	32	**1919610000**
SF 5/12	12x7.4 mm	12	32	**1919660000**
SF 00/21	21x3.2 mm	21	80	**1918530000**
SF 0/21	21x3.2 mm	21	80	**1918470000**
SF 1/21	21x3.2 mm	21	80	**1918640000**
SF 2/21	21x3.6 mm	21	80	**1918650000**
SF 3/21	21x4.6 mm	21	64	**1918880000**
SF 4/21	21x5.7 mm	21	48	**1919050000**
SF 4,5/21	21x7.4 mm	21	32	**1918990000**
SF 5/21	21x7.4 mm	21	32	**1919110000**
SF 6/21	21x8.4 mm	21	32	**1919160000**
SFX 10/23	23x5 mm	23	32	**1852380000**
SFX 14/23	23x8.2 mm	24	32	**1852430000**
SFX 9/24	23.9x9 mm	24	32	**1852480000**
SFX 11/60	11x44 mm	60	12	**1860140000**
SFX 30/60 n	30x45 mm	60	30	**1083260000**

SF - accessory

Type	Qty.	Order No.
SF-Tool 00-6	10	**1950820000**
SF-Tool 1	10	**1782970000**
SF-Tool 2-3	10	**1782960000**
SF-Tool 4-5	10	**1782980000**
SF-Tool-Sortiment	1	**1770080000**

SlimFix Clip

The SlimFix Clip combines two advantages in one: its unique closure mechanism offers the reliability of a closed marker with ease of attaching an open marker. The Clip closure mechanism also allows quick, no fuss attachment of the markers after the wires have been installed. SlimFix Clip markers are suitable for wires and cables with external diameters up to 5 mm. Long sequences of characters are possible on the large marking surface – up to 30 mm.

- Halogen free, flammability class V2 material
- Rapid attachment without tools
- Five sizes for wire cross-sections from 0.5 – 10.0 mm²
- Available in lengths of 12, 21 and 30 mm
- Markers available in the proven MultiCard format
- Additional marking surface for precise assignment to projects
- Custom-printed markers supplied to your specifications
- Printing on the SFC 3 is not possible with the SMark Laser.
- Accessory plates must be used when printing on the SFC 2.5 and SFC 3 with the MCP Plus, MCP Basic and MC Mobilo (see right).



Technical data

Material	Polyamide 66, halogen-free
UL 94 flammability rating	V2
Temperature range	–40 °C to 100 °C

SFC 2.5 printing

MCP Plus / MCP Basic	Order No.
AP SF 4-6	1924310000
MC Mobilo	**Order No.**
AP SF 4-6	1924310000

SFC 3 printing

MCP Plus / MCP Basic	Order No.
AP SF 4-6	1924310000
Inlay SFC 3	1058090000
MC Mobilo	**Order No.**
AP SF 4-6	1802180000
Inlay SFC 3	1058090000

Ordering data

Type	Wire, ext. ø	Wire cross-section
SFC 0	1.5 - 2.5 mm	0.5 - 1.0 mm²
SFC 1	2.0 - 3.5 mm	0.75 - 2.5 mm²
SFC 2	2.5 - 5.0 mm	2.5 - 4.0 mm²
SFC 2,5	4.0 - 6.0 mm	4.0 - 10 mm²
SFC 3	3.5 - 7.0 mm	4.0 - 10 mm²
Colour	Available in all colours of the international colour code; for MC on request ● brown ● orange ● green ● violet ● grey	
Special printing	Specify special printing and colours per diskette, Excel file or using the M-Print® PRO software.	
Minimum order quantity	1 pack	

SFC - blank

Technical specification

Material	Polyamide
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C

Ordering data

Type	Printing area	Length	Qty.	Order No. white	Order No. yellow	Order No. blue	Order No. red
SFC 0/12	12x4.1 mm	12	200	**1813130000**	**1813160000**	**1813170000**	**1813150000**
SFC 1/12	12x4.1 mm	12	200	**1747320001**	**1747320004**	**1747320002**	**1747320003**
SFC 2/12	12x5.8 mm	12	120	**1758320001**	**1758320004**	**1758320002**	**1758320003**
SFC 2.5/12 n	12x5.8 mm	12	120	**1062000000**	**1062010000**	**1062030000**	**1062020000**
SFC 3/12	12x5 mm	12	80	**1025220000**	**1025230000**	**1025250000**	**1025240000**
SFC 0/21	21x4.1 mm	21	200	**1813190000**	**1813210000**	**1813220000**	**1813200000**
SFC 1/21	21x4.1 mm	21	200	**1779080001**	**1779080004**	**1779080002**	**1779080003**
SFC 2/21	21x5.8 mm	21	120	**1805810000**	**1805780000**	**1805770000**	**1805790000**
SFC 2.5/21 n	21x5.8 mm	21	120	**1062050000**	**1062070000**	**1062090000**	**1062080000**
SFC 3/21	21x5 mm	21	80	**1025260000**	**1025270000**	**1025300000**	**1025290000**
SFC 0/30	30x4.1 mm	30	150	**1813240000**	**1813260000**	**1813270000**	**1813250000**
SFC 1/30	30x4.1 mm	30	150	**1805760000**	**1805730000**	**1805720000**	**1805740000**
SFC 2/30	30x5.8 mm	30	90	**1805870000**	**1805830000**	**1805820000**	**1805850000**
SFC 3/30	30x5 mm	30	60	**1025310000**	**1025320000**	**1025340000**	**1025330000**

SFC - Custom printing

Type	Printing area	Length	Qty.	Order No.
SFC 0/12	12x4.1 mm	12	40	**1813180000**
SFC 1/12	12x4.1 mm	12	40	**1752720000**
SFC 2/12	12x5.8 mm	12	24	**1763480000**
SFC 2.5/12 n	12x5.8 mm	12	24	**1062040000**
SFC 3/12	12x5 mm	12	16	**1025550000**
SFC 0/21	21x4.1 mm	21	40	**1813230000**
SFC 1/21	21x4.1 mm	21	40	**1779090000**
SFC 2/21	21x5.8 mm	21	24	**1805800000**
SFC 2.5/21 n	21x5.8 mm	21	24	**1062110000**
SFC 3/21	21x5 mm	21	16	**1025560000**
SFC 0/30	30x4.1 mm	30	30	**1813280000**
SFC 1/30	30x4.1 mm	30	30	**1805750000**
SFC 2/30	30x5.8 mm	30	18	**1805860000**
SFC 3/30	30x5 mm	30	12	**1025570000**

TM-I

The special profile of the TM-I results in easy installation and secure marking. TM-I tags are compatible with many of the sleeves available on the market. Their MultiCard format means quick and convenient printing with the SMark-Laser, PrintJet, MCP Plus Plotter, MC-Mobilo or STI-S pen systems. Thanks to the project name panels on the MultiCards, the tags are easy to separate and mount. TM-I is an acknowledged and accredited marker for traffic engineering applications. Five different tag lengths are available for individual labelling with long character strings.

- Easily separated and mounted thanks to the project name panels
- Acknowledged and accredited marker for traffic engineering
- Fitting the sleeves first and inserting the labels later adds up to maximum flexibility
- Not suited for labelling with P-Ink or STI-S pen in connection with CLI T sleeves



Technical data

Material	Polyamide 66, halogen-free
UL 94 flammability rating	V2
Temperature range	–40 °C to 100 °C
Printing	black

Ordering data

Colour	Other colours on request		
	● brown	● red	● orange
	● yellow	● green	● blue
	● violet	● grey	O white
Special printing	Specify special printing and colours per diskette, Excel file or using the M-Print® PRO software.		
Minimum order quantity	1 pack		

TM-I blank

Technical specification

Material	Polyamide 66
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C

Ordering data

Type	Length	Width	Material colour	Qty	Order No.
TM-I 12 BLANK WS	12 mm	4 mm	white	320	**1718411044**
TM-I 12 BLANK GE	12 mm	4 mm	yellow	320	**1718411687**
TM-I 12 BLANK BL	12 mm	4 mm	Blue	320	**1718411693**
TM-I 12 BLANK RT	12 mm	4 mm	red	320	**1718411686**
TM-I 12 BLANK GN	12 mm	4 mm	green	320	**1718411688**
TM-I 15 BLANK RT	15 mm	4 mm	white	400	**1609981044**
TM-I 15 BLANK BL	15 mm	4 mm	yellow	400	**1609981687**
TM-I 15 NEUTRAL	15 mm	4 mm	Blue	400	**1609981693**
TM-I 15 BLANK GN	15 mm	4 mm	red	400	**1609981686**
TM-I 15 BLANK GE	15 mm	4 mm	green	400	**1609981688**
TM-I 18 BLANK WS	18 mm	4 mm	white	320	**1718431044**
TM-I 18 BLANK GE	18 mm	4 mm	yellow	320	**1718431687**
TM-I 18 BLANK BL	18 mm	4 mm	Blue	320	**1718431693**
TM-I 18 BLANK RT	18 mm	4 mm	red	320	**1718431686**
TM-I 18 BLANK GN	18 mm	4 mm	green	320	**1718431688**
TM-I 20 BLANK RT	20 mm	4 mm	white	400	**1680411044**
TM-I 20 BLANK BL	20 mm	4 mm	yellow	400	**1680411687**
TM-I 20 NEUTRAL	20 mm	4 mm	Blue	400	**1680411693**
TM-I 20 BLANK GN	20 mm	4 mm	red	400	**1680411686**
TM-I 20 BLANK GE	20 mm	4 mm	green	400	**1680411688**
TM-I 30 MC BLANK WS	30 mm	4 mm	white	300	**1876390000**
TM-I 30 MC BLANK GE	30 mm	4 mm	yellow	300	**1876370000**
TM-I 30 MC BLANK BL	30 mm	4 mm	Blue	300	**1876400000**
TM-I 30 MC BLANK RT	30 mm	4 mm	red	300	**1876380000**

TM-I Custom printing

Technical specification

Material	Polyamide 66
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C
Material colour	To customer specification

Type	Length	Width	Qty	Order No.
TM-I 12 CUSTOM PRINT	12 mm	4 mm	64	**1718420000**
TM-I 15 CUSTOM PRINT	15 mm	4 mm	80	**1609990000**
TM-I 18 CUSTOM PRINT	18 mm	4 mm	64	**1718440000**
TM-I 20 CUSTOM PRINT	20 mm	4 mm	80	**1680420000**
TM-I 30 MC CUSTOM PRINT	30 mm	4 mm	60	**1876320000**

CLI F inlay tags are made from a zero-halogen polyester material. The tags are supplied as an A4 sheet and are easy to separate thanks to the perforations. The ready-to-print material guarantees fast labelling with a laser printer or plotter.

- Suitable for CLI TM sleeves

CLI F inlay tags

Technical specification

Material	Polyester, PVC-free
UL 94 flammability rating	HB
Min. temperature, continuous	-30 °C
Max. temperature, continuous	120 °C
Material colour	white;yellow

Ordering data

Type	Length	Width	No. per sheet	Qty	Order No.
CLI F 1/20 WHITE/YELLOW	20 mm	4 mm	594	10	**1600740000**
CLI F 2/17.5 WHITE/YELLOW	17.5 mm	9 mm	352	10	**1764050000**

Transparent sleeves

The TM/HF sleeve is free from halogens and essentially free from other hazardous substances. The sleeves are fitted with the TM-I 12 or TM-I 18. They are suitable for a wide range of cables and conductors. This system has proved particularly beneficial in transport engineering. The slim design guarantees a firm attachment to the cable.

- halogen free,
- slim design guarantees firm attachment to cable.
- TMX 18 fixed with cable ties (3.6 mm wide)

TM/HF - sleeve

Technical specification

Material	Polyethylene LD
UL 94 flammability rating	HB
Min. temperature, continuous	-20 °C
Max. temperature, continuous	80 °C
Material colour	transparent

Ordering data

Type	Length	Insulation O.D.	Cond. cross-section	Qty	Order No.
TM 0/12 HF/HB	12 mm	1.3-2.0 mm	0.22-0.5 mm²	1000	**1719760000**
TM 0/18 HF/HB	18 mm	1.3-2.0 mm	0.22-0.5 mm²	1000	**1719770000**
TM 1/12 HF/HB	12 mm	1.8-2.5 mm	0.5-1.5 mm²	1000	**1719780000**
TM 1/18 HF/HB	18 mm	1.8-2.5 mm	0.5-1.5 mm²	1000	**1719790000**
TM 2/12 HF/HB	12 mm	2.5-4.0 mm	0.75-2.5 mm²	1000	**1719800000**
TM 2/18 HF/HB	18 mm	2.5-4.0 mm	0.75-2.5 mm²	1000	**1719810000**
TM 3/12 HF/HB	12 mm	4.0-6.5 mm	2.5-6 mm²	500	**1719820000**
TM 3/18 HF/HB	18 mm	4.0-6.5 mm	2.5-6 mm²	500	**1719830000**
TM 4/12 HF/HB	12 mm	6.0-10.0 mm	10-35 mm²	500	**1719840000**
TM 4/18 HF/HB	18 mm	6.0-10.0 mm	10-35 mm²	500	**1719850000**
TM 5/12 HF/HB	12 mm	9.0-15.0 mm	25-70 mm²	200	**1719860000**
TM 5/18 HF/HB	18 mm	9.0-15.0 mm	25-70 mm²	200	**1719870000**
TM 6/12 HF/HB	12 mm	15.0-24.0 mm	35-150 mm²	200	**1719880000**
TM 6/18 HF/HB	18 mm	15.0-24.0 mm	35-150 mm²	200	**1719890000**
TMX 18 HF/HB	18 mm	10.0-317.0 mm	16-150 mm²	500	**1748820000**

The twin sleeves provide the option of marking a cable on both sides. The sleeves can be fitted with two TM-I 18 tags so that, for example, the input and output designations of a cable can be read off at one position. The transparent, halogen free sleeves can be used on cables with an outside diameter of 1.3 to 4.0 mm.

TM/HF - Twin - SLEEVE

Technical specification

Material	Polyethylene LD
UL 94 flammability rating	HB
Min. temperature, continuous	-20 °C
Max. temperature, continuous	80 °C
Material colour	transparent

Ordering data

Type	Length	Insulation O.D.	Cond. cross-section	Qty	Order No.
TM 0/18 TWIN HF/HB	18 mm	1.3-2.6 mm	0.22-1.5 mm²	500	**1891810000**
TM 1/18 TWIN HF/HB	18 mm	2.4-4.0 mm	1.5-2.5 mm²	500	**1891780000**

CLI T connector markers are high-quality, transparent sleeves in different lengths for labelling cables with a cross-section of 0.2 mm² to 75 mm². The TM-I series is suitable as an inlay tag.
- Larger cross-section per sleeve,
- Large range of applications thanks to special bellows profile with spring effect,
- easy to insert the TM-I tag into the sleeve pocket before or after connecting the conductor,
- available in five lengths.
- Not suitable for labelling with P-Ink ink or with an STI-S pen.

CLI T sleeve

Technical specification

Material	PVC
UL 94 flammability rating	V0
Min. temperature, continuous	-30 °C
Max. temperature, continuous	80 °C
Material colour	transparent

Ordering data

Type	Length	Insulation O.D.	Cond. cross-section	Qty	Order No.
CLI T 02-12	12 mm	1.3-3.0 mm	0.22-1.5 mm²	200	**1764060000**
CLI T 02-15	15 mm	1.3-3.0 mm	0.22-1.5 mm²	200	**1764070000**
CLI T 02-18	18 mm	1.3-3.0 mm	0.22-1.5 mm²	200	**1764140000**
CLI T 02-20	20 mm	1.3-3.0 mm	0.22-1.5 mm²	200	**1764150000**
CLI T 02-30	30 mm	1.3-3.0 mm	0.22-1.5 mm²	200	**1889580000**
CLI T 1-12	12 mm	2.5-5.0 mm	0.75-6 mm²	200	**1764190000**
CLI T 1-15	15 mm	2.5-5.0 mm	0.75-6 mm²	200	**1764200000**
CLI T 1-18	18 mm	2.5-5.0 mm	0.75-6 mm²	200	**1764210000**
CLI T 1-20	20 mm	2.5-5.0 mm	0.75-6 mm²	200	**1764220000**
CLI T 1-30	30 mm	2.5-5.0 mm	0.75-6 mm²	200	**1889560000**
CLI T 2-12	12 mm	4.0-10.0 mm	4-35 mm²	100	**1764230000**
CLI T 2-15	15 mm	4.0-10.0 mm	4-35 mm²	100	**1764240000**
CLI T 2-18	18 mm	4.0-10.0 mm	4-35 mm²	100	**1764250000**
CLI T 2-20	20 mm	4.0-10.0 mm	4-35 mm²	100	**1764260000**
CLI T 2-30	30 mm	4.0-10.0 mm	4-35 mm²	100	**1889570000**
CLI T 3-12	12 mm	8.0-16.0 mm	25-75 mm²	100	**1764270000**
CLI T 3-15	15 mm	8.0-16.0 mm	25-75 mm²	100	**1764280000**
CLI T 3-18	18 mm	8.0-16.0 mm	25-75 mm²	100	**1764290000**
CLI T 3-20	20 mm	8.0-16.0 mm	25-75 mm²	100	**1764300000**
CLI T 3-30	30 mm	8.0-16.0 mm	25-75 mm²	100	**1889550000**

CLI TM is the right sleeve for large conductor cross-sections. The transparent pocket on the sleeve protects the inlay tags against outside influences. The transparent CLI TM sleeve is fixed with cable ties. The marking is carried out with TM-I 18 and CLI F1 for CLI TM 10/33 or ESG 9/17 and CLI F2 for CLI TM 20/33. Both types of inlay tags make use of the established MultiCard format and can be easily printed with the SMark laser, PrintJet, MCP Plus plotter or MC-Mobilo. The CLI F 2/17.5 tag is suitable for the CLI TM 20/66.
- Secure attachment thanks to cable ties,
- Professional marking results with the Weidmüller labelling system for MultiCards

CLI TM

Technical specification

Material	PVC
UL 94 flammability rating	V0
Min. temperature, continuous	-30 °C
Max. temperature, continuous	60 °C
Material colour	transparent

Ordering data

Type	Length	Width	Qty	Order No.
CLI TM 10-33	33 mm	6 mm	100	**1763270000**
CLI TM 20-33	33 mm	11.3 mm	100	**1763280000**
CLI TM 20-66	66 mm	11.3 mm	50	**1763390000**

Accessories

Technical specification

Type	Length	Width	No. per sheet	Qty	Order No.
CLI F 1/20 WHITE/YELLOW	20 mm	4 mm	594	10	**1600740000**
CLI F 2/17.5 WHITE/YELLOW	17.5 mm	9 mm	352	10	**1764050000**
TM-I 18 MC	18 mm	4 mm		320	**1718431044**
ESG 9/17 MC white	9 mm	17 mm		200	**1724760000**

Transparent sleeves



The range of TM sleeves is comprehensive and permits almost universal use: from thin conductors to cables with a large outside diameter, a wide range of applications is covered. The sleeves protect the printed inlay tags against external influences. TM sleeves also permit flexible installation. They are available in five different lengths (12, 15, 18, 20, 30 mm) and 11 sizes - one tag type for all sleeves.

- optimum protection for printed inlay tags,
- large range of applications for conductors and cables,
- one tag type for all cross-sections.
- TMX 30 fixed with cable-ties (width 4.6 mm)

TM - sleeve

Technical specification

Material	PVC
UL 94 flammability rating	V0
Min. temperature, continuous	-50 °C
Max. temperature, continuous	80 °C
Material colour	transparent

Ordering data

Type	Length	Insulation O.D.	Cond. cross-section	Qty	Order No.
TM 200/15 V0	15 mm	1.0-1.25 mm	0.22-1 mm²	1000	**1798650000**
TM 201/12 V0	12 mm	1.5-2.5 mm	0.25-1.5 mm²	1000	**1798640000**
TM 201/15 V0	15 mm	1.5-2.5 mm	0.25-1.5 mm²	1000	**1798620000**
TM 201/18 V0	18 mm	1.5-2.5 mm	0.25-1.5 mm²	1000	**1798600000**
TM 201/20 V0	20 mm	1.5-2.5 mm	0.25-1.5 mm²	1000	**1798580000**
TM 201/30 V0	30 mm	1.5-2.5 mm	0.25-1.5 mm²	500	**1874850000**
TM 202/12 V0	12 mm	2.0-4.0 mm	0.5-2.5 mm²	1000	**1798560000**
TM 202/15 V0	15 mm	2.0-4.0 mm	0.5-2.5 mm²	1000	**1798540000**
TM 202/18 V0	18 mm	2.0-4.0 mm	0.5-2.5 mm²	1000	**1798530000**
TM 202/20 V0	20 mm	2.0-4.0 mm	0.5-2.5 mm²	1000	**1798520000**
TM 202/30 V0	30 mm	2.0-4.0 mm	0.5-2.5 mm²	500	**1874760000**
TM 203/12 V0	12 mm	4.0-7.0 mm	2.5-10 mm²	500	**1798510000**
TM 203/15 V0	15 mm	4.0-7.0 mm	2.5-10 mm²	500	**1798490000**
TM 203/18 V0	18 mm	4.0-7.0 mm	2.5-10 mm²	500	**1798480000**
TM 203/20 V0	20 mm	4.0-7.0 mm	2.5-10 mm²	500	**1798470000**
TM 203/30 V0	30 mm	4.0-7.0 mm	2.5-10 mm²	200	**1874770000**
TM 204/12 V0	12 mm	6.0-10.0 mm	6-16 mm²	500	**1806180000**
TM 204/15 V0	15 mm	6.0-10.0 mm	6-16 mm²	500	**1806240000**
TM 204/18 V0	18 mm	6.0-10.0 mm	6-16 mm²	500	**1806300000**
TM 204/20 V0	20 mm	6.0-10.0 mm	6-16 mm²	500	**1806360000**
TM 204/30 V0	30 mm	6.0-10.0 mm	6-16 mm²	200	**1874780000**
TM 205/12 V0	12 mm	10.0-14.0 mm	16-35 mm²	200	**1806190000**
TM 205/15 V0	15 mm	10.0-14.0 mm	16-35 mm²	200	**1806250000**
TM 205/18 V0	18 mm	10.0-14.0 mm	16-35 mm²	200	**1806310000**
TM 205/20 V0	20 mm	10.0-14.0 mm	16-35 mm²	200	**1806370000**
TM 205/30 V0	30 mm	10.0-14.0 mm	16-35 mm²	200	**1874790000**
TM 206/12 V0	12 mm	14.0-22.0 mm	35-120 mm²	200	**1806200000**
TM 206/15 V0	15 mm	14.0-22.0 mm	35-120 mm²	200	**1806260000**
TM 206/18 V0	18 mm	14.0-22.0 mm	35-120 mm²	200	**1806320000**
TM 206/20 V0	20 mm	14.0-22.0 mm	35-120 mm²	200	**1806380000**
TM 206/30 V0	30 mm	14.0-22.0 mm	35-120 mm²	100	**1874800000**
TM 207/12 V0	12 mm	22.0-30.0 mm	120-240 mm²	50	**1806210000**
TM 207/15 V0	15 mm	22.0-30.0 mm	120-240 mm²	50	**1806270000**
TM 207/18 V0	18 mm	22.0-30.0 mm	120-240 mm²	50	**1806330000**
TM 207/20 V0	20 mm	22.0-30.0 mm	120-240 mm²	50	**1806390000**
TM 207/30 V0	30 mm	22.0-30.0 mm	120-240 mm²	50	**1874820000**
TM 208/12 V0	12 mm	30.0-35.0 mm	240-300 mm²	50	**1806220000**
TM 208/15 V0	15 mm	30.0-35.0 mm	240-300 mm²	50	**1806280000**
TM 208/18 V0	18 mm	30.0-35.0 mm	240-300 mm²	50	**1806340000**
TM 208/20 V0	20 mm	30.0-35.0 mm	240-300 mm²	50	**1806400000**
TM 208/30 V0	30 mm	30.0-35.0 mm	240-300 mm²	50	**1874830000**
TM 209/12 V0	12 mm	35.0-40.0 mm	300-500 mm²	50	**1806230000**
TM 209/15 V0	15 mm	35.0-40.0 mm	300-500 mm²	50	**1806290000**
TM 209/18 V0	18 mm	35.0-40.0 mm	300-500 mm²	50	**1806350000**
TM 209/20 V0	20 mm	35.0-40.0 mm	300-500 mm²	50	**1806410000**
TM 209/30 V0	30 mm	35.0-40.0 mm	300-500 mm²	50	**1874720000**
TMX 30 V0	30 mm	10.0-317.0 mm	16-150 mm²	400	**1866680000**

WKM

WKM is a marker for tough conditions, with a secure fixing on conductor or cable. The transparent pocket guarantees reliable protection of the labelling against outside influences. The fixing with cable ties permits virtually any size of conductor or cable to be marked. The WKM can be marked in many different ways, e.g. laser printer, dot-matrix printer or the STI pen, on paper or polyester labels.

- A multitude of labelling options,
- Flexible installation with cable ties for virtually any cross-section.

Halogen

Technical specification

Material	Polypropylene
UL 94 flammability rating	HB
Min. temperature, continuous	-40 °C
Max. temperature, continuous	80 °C
Material colour	transparent

Ordering data

Type	Length	Width	Qty	Order No.
WKM 8/20	20 mm	8 mm	50	**1753490000**
WKM 8/30	30 mm	8 mm	50	**1631910000**
WKM 18/43	43 mm	18 mm	50	**1610700000**

Accessories

Technical specification

ESO...P	= Polyester
ESO	= Paper

Ordering data

Type	Length	Width	No. per sheet	Qty	Order No.
ESO 5 white	40 mm	16.5 mm	60	10	**1607710000**
ESO 5 yellow	40 mm	16.5 mm	60	10	**1631350000**
ESO 5P white	40 mm	16.5 mm	60	10	**1670370000**
ESO 7 white	27 mm	6.3 mm	240	10	**1607720000**
ESO 5P yellow	40 mm	16.5 mm	60	10	**1670380000**
ESO 7 yellow	27 mm	6.3 mm	240	10	**1634780000**
ESO 7P white	27 mm	6.3 mm	240	10	**1670390000**
ESO 7P yellow	27 mm	6.3 mm	240	10	**1670400000**
ESG 7/20 Sirius white	7 mm	20 mm		200	**1736181044**
ESG 7/20 Sirius turquoise	7 mm	20 mm		200	**1736181696**
ESO 8/20 white	20 mm	7 mm	342	10	**1919890000**
ESO 8/20 yellow	20 mm	7 mm	342	10	**1919900000**
ESO 8/20P white	20 mm	7 mm	342	10	**1919870000**
ESO 8/20P yellow	20 mm	7 mm	342	10	**1919880000**

ELS insertion tag

The ELS-type MultiCard marker can be printed on with PrintJet, plotter or SMark printer. Colour printing with the PrintJet PRO, in particular, enables cables and terminal strips to be labelled in a variety of noticeable manners.

n

Halogen

Technical specification

Material	Polyamide PA 66
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C
Suitable for	ELS 6/30: WKM 8/30 (1631910000) ELS 16/40: WKM 18/43 (1610700000)

Ordering data

Type	Colour	Qty.	Order No.
blank			
ELS 6/30 MC NE WS	white	80	**1045570000**
ELS 6/30 MC NE GE	yellow	80	**1045580000**
ELS 16/40 MC NE WS	white	40	**1045620000**
ELS 16/40 MC NE GE	yellow	40	**1045630000**
Custom printing			
ELS 6/30 MC SDR		16	**1045660000**
ELS 16/40 MC SDR		8	**1045690000**

TwinMark – markers as heat shrinkable sleeves

TwinMark is a heat shrinkable sleeve for labelling and insulating conductors and cables with 1.2 to 24 mm diameter. Double-sided printing is also possible. TwinMark is available in two versions: the standard version (supplied folded), and the zero-halogens variation (supplied on reel).

Simply peel off the flexible heat shrinkable sleeve from its backing material and then slip it over the conductor to achieve a firm, tailor-made fitting.

Advantages:

- Can be used in extremely confined spaces
- Double-sided printing for improved legibility
- Printed sleeve on endless backing
- Standard hot-air guns can be used for heat-shrinking

Technical data

	Halogen-free variant HSS-HF...
Material	Polyolefin, halogen-free according to VDE 0472-815
Temperature ranges	–40 °C … +105 °C
Flammability	VDE 5510-2 drop-forming class ST2
	EN 50343; Fed. STD-228, method 5221
	ASTM-D 2671
Print durability	MIL-M-81531, MIL-STD-202, method 215J
	If printed with Weidmüller THM-Plus or
	THM TwinMark printer and ribbon R 83/300

Technical data

	Standard variant HSS...
Material	Polyolefin
Temperature ranges	–50 °C … +120 °C
Material specification	MIL-DTL-23053/5C (class 1)
Flammability	VDE 5510-2 drop-forming class ST2
	Fed. STD-228, Methode 5221,
	self-extinguishing within 60 seconds
Print durability	MIL-M-81531, MIL-STD-202, method 215J
	If printed with Weidmüller THM-Plus or
	THM TwinMark printer and ribbon WR 90/300

HSS-HF 50.8 mm

Technical data

Material	Polyolefin, halogen-free according to VDE 0472-815
Shrinkage rate	2:1

Selection table HSS-HF

Type	Suitable wire diameter	Suitable cond. cross-section [1]
HSS-HF1/8"1.8-2.8	1.8 – 2.8 mm	0.5 – 1.5 mm²
HSS-HF3/16"2.8-4.2	2.8 – 4.2 mm	1.5 – 4.0 mm²
HSS-HF1/4"4.2-5.8	4.2 – 5.8 mm	4.0 – 10.0 mm²
HSS-HF3/8"5.8-8.0	5.8 – 8.0 mm	10.0 – 16.0 mm²
HSS-HF1/2"8.0-11.0	8.0 – 11.0 mm	25.0 – 35.0 mm²
HSS-HF3/4"11.0-17.0	11.0 – 17.0 mm	35.0 – 70.0 mm²
HSS-HF1"17.0-23.0	17.0 – 23.0 mm	70.0 – 120.0 mm²

[1] Depending on the insulation thickness

Ordering data

Type	Max. outside diameter	Colour	Qty.	Order No.
HSS-HF1/8"1.8-2.8/50Y	1/8" / 3.2 mm	yellow	5000	**1961900000**
HSS-HF3/16"2.8-4.2/50Y	3/16" / 4.8 mm	yellow	4000	**1961910000**
HSS-HF1/4"4.2-5.8/50Y	1/4" / 6.4 mm	yellow	2500	**1961920000**
HSS-HF3/8"5.8-8.0/50Y	3/8" / 9.5 mm	yellow	2000	**1961930000**
HSS-HF1/2"8.0-11.0/50Y	1/2" / 12.7 mm	yellow	1500	**1961940000**
HSS-HF3/4"11.0-17.0/50Y	3/4" / 19.0 mm	yellow	1250	**1961950000**
HSS-HF1"17.0-23.0/50Y	1" / 25.4 mm	yellow	750	**1961960000**

Note: for printing with the THM-Plus or THM TwinMark printer

HSS-HF 25.4 mm

Ordering data

Type	Max. outside diameter	Colour	Qty.	Order No.
HSS-HF1/8"1.8-2.8/25Y	1/8" / 3.2 mm	yellow	10000	**1961970000**
HSS-HF3/16"2.8-4.2/25Y	3/16" / 4.8 mm	yellow	8000	**1961980000**
HSS-HF1/4"4.2-5.8/25Y	1/4" / 6.4 mm	yellow	5000	**1961990000**
HSS-HF3/8"5.8-8.0/25Y	3/8" / 9.5 mm	yellow	4000	**1962000000**
HSS-HF1/2"8.0-11.0/25Y	1/2" / 12.7 mm	yellow	3000	**1962010000**
HSS-HF3/4"11.0-17.0/25Y	3/4" / 19.0 mm	yellow	2500	**1962020000**
HSS-HF1"17.0-23.0/25Y	1" / 25.4 mm	yellow	1500	**1962030000**

Note: for printing with the THM-Plus or THM TwinMark printer



Ordering information



TwinMark

HSS 50.8 mm

Technical data

Material	Polyolefin according to VDE 0472-815
Shrinkage rate	3:1 (1" size = 2:1)

Selection table HSS

Type	Suitable wire diameter	Suitable cond. cross-section [1]
HSS1/8"1.2-2.8	1.2 – 2.8 mm	0.5 – 1.5 mm²
HSS1/4"2.4-5.5	2.4 – 5.5 mm	1.5 – 6.0 mm²
HSS3/8"3.2-8.1	3.2 – 8.1 mm	4.0 – 16.0 mm²
HSS1/2"4.8-11.4	4.8 – 11.4 mm	10.0 – 35.0 mm²
HSS1"11.4-24.1 [2]	11.4 – 24.1 mm	35.0 – 120.0 mm²

[1] Depending on the insulation thickness [2] shrinkage rate 2:1

Ordering data

Type		Max. outside diameter	Colour	Qty.	Order No.
HSS1/8"1.2-2.8/50W		1/8" / 3.2 mm	white	500	**1962040000**
HSS3/16"1.6-3.8/50W	n	3/16" / 4.8 mm	white	500	**1029840000**
HSS1/4"2.4-5.5/50W		1/4" / 6.4 mm	white	500	**1962050000**
HSS3/8"3.2-8.1/50W		3/8" / 9.5 mm	white	500	**1962060000**
HSS1/2"4.8-11.4/50W		1/2" / 12.7 mm	white	500	**1962070000**
HSS1"11.4-24.1/50W [2]		1" / 25.4 mm	white	500	**1962080000**
HSS1/8"1.2-2.8/50Y		1/8" / 3.2 mm	yellow	500	**1962090000**
HSS3/16"1.6-3.8/50Y	n	3/16" / 4.8 mm	yellow	500	**1029850000**
HSS1/4"2.4-5.5/50Y		1/4" / 6.4 mm	yellow	500	**1962100000**
HSS3/8"3.2-8.1/50Y		3/8" / 9.5 mm	yellow	500	**1962110000**
HSS1/2"4.8-11.4/50Y		1/2" / 12.7 mm	yellow	500	**1962120000**
HSS1"11.4-24.1/50Y [2]		1" / 25.4 mm	yellow	500	**1962130000**

[2] shrinkage rate 2:1 **Note:** for printing with the THM-Plus or THM TwinMark printer

HSS 25.4 mm

Ordering data

Type		Max. outside diameter	Colour	Qty.	Order No.
HSS1/8"1.2-2.8/25W		1/8" / 3.2 mm	white	1000	**1962140000**
HSS3/16"1.6-3.8/25W	n	3/16" / 4.8 mm	white	1000	**1029860000**
HSS1/4"2.4-5.5/25W		1/4" / 6.4 mm	white	1000	**1962150000**
HSS3/8"3.2-8.1/25W		3/8" / 9.5 mm	white	1000	**1962160000**
HSS1/2"4.8-11.4/25W		1/2" / 12.7 mm	white	1000	**1962170000**
HSS1"11.4-24.1/25W [2]		1" / 25.4 mm	white	1000	**1962180000**
HSS1/8"1.2-2.8/25Y		1/8" / 3.2 mm	yellow	1000	**1962190000**
HSS3/16"1.6-3.8/25Y	n	3/16" / 4.8 mm	yellow	1000	**1029870000**
HSS1/4"2.4-5.5/25Y		1/4" / 6.4 mm	yellow	1000	**1962200000**
HSS3/8"3.2-8.1/25Y		3/8" / 9.5 mm	yellow	1000	**1962210000**
HSS1/2"4.8-11.4/25Y		1/2" / 12.7 mm	yellow	1000	**1962220000**
HSS1"11.4-24.1/25Y [2]		1" / 25.4 mm	yellow	1000	**1962230000**

[2] shrinkage rate 2:1 **Note:** for printing with the THM-Plus or THM TwinMark printer



Ordering information

HSS 1/8" 1.2-2.8 / 50 Y

- **Y = Yellow (W=White)**
- **50.8 mm sleeve length (or 25.4 mm)**
- **suitable wire diameter 1.2 – 2.8 mm**
- **Max. outside diameter 1/8" (or 3.2 mm)**
- **HSS = Heat Shrinkable Sleeve**

LM WriteOn

WriteOn cable markers on A4 sheets are employed for labelling lines and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.
- Marking protected against dirt and abrasion by attaching the transparent adhesive strip.
- Labelling by means of A4 laser printer or STI pen.
- Quick and easy labelling.

Sheets

Technical specification

Material	Polyester film
UL 94 flammability rating	HB
Min. temperature, continuous	-40 °C
Max. temperature, continuous	125 °C

Ordering data

Type	Diameter (mm)	No. per item	Printing area (mm)	Length (mm)	Qty.	Order No. white	Order No. yellow
LM 15/70	8.2 - 14.3	30	15 x 30	70	10	**1759871044**	
LM 15/140	16.2 - 36.4	26	15 x 70	140	10	**1773880000**	
LM 18/34	5.0 - 7.0	88	18 x 12.7	34	10	**1695711044**	**1695711687**
LM 23/55	6.8 - 12.0	40	23 x 12.7	55	10	**1695721044**	**1695721687**
LM 25/68	8.2 - 14.3	28	25 x 17	68	10	**1695731044**	**1695731687**
LM 25/140	16.2 - 36.4	16	25 x 26	140	10	**1712491044**	**1712491687**
LM 25.4/57	9.5 - 22.3	35	25.4 x 18	57	10	**1768380000**	**1768390000**
LM 25.4/95	8.0 - 22.0	21	25.4 x 25	95	10	**1768400000**	**1768410000**
LM 36/93	9.5 - 22.3	15	36 x 25	93	10	**1695741044**	**1695741687**
LM 37/25	3.4 - 4.8	40	37 x 8	25	10		**1768430000**

THM WriteOn

WriteOn cable markers on reels are employed for identifying lines and cables with an outside diameter of up to 36 mm. The transparent adhesive strip fixes and protects the printing on the marker surface.
- Marking protected against dirt and abrasion by attaching the transparent adhesive strip.
- Labelling by means of high-quality THM Pro thermal transfer printer.
- Quick and easy labelling.

Reels

Technical specification

THM WriteOn

Material	Polyester, PVC-free
Min. temperature, continuous	-40 °C
Max. temperature, continuous	125 °C

THM WriteOn T

Material	Polyvinyl fluoride foil
Min. temperature, continuous	-40 °C
Max. temperature, continuous	107 °C

Ordering data

Type	Suitable for cable diameter (mm)	Number per role	Labelling field: width x height (mm)	Total length including lamination (mm)	Qty.	Order No. white	Order No. yellow
THM WriteOn 12/18	2.9	10000	12.0 x 9.0	18.0	1	**1856640000**	**1856630000**
THM WriteOn 17.8/34	6.7	3000	17.8 x 13.0	33.9	1	**1774380000**	
THM WriteOn T 24.5/62	11.8	2500	24.5 x 25.0	62.0	1	**1003420000**	
THM WriteOn T 24.5/100	23.9	2000	24.5 x 25.0	100.0	1	**1003380000**	
THM WriteOn 25/140		1050	25.0 x 26.0	140.0	1	**1751561044**	**1751561687**
THM WriteOn 25/76	19.4	1800	25.0 x 15.0	76.0	1	**1774350000**	**1774340000**
THM WriteOn 25.4/62	13.7	2500	25.4 x 19.0	62.0	1	**1109130000**	
THM WriteOn 25.4/95.25	22.3	1000	25.4 x 25.4	95.3	1	**1109140000**	
THM WriteOn 35.6/93	21.6	1500	35.6 x 25.0	93.0	1	**1774400000**	**1774410000**
THM WriteOn 49.5/57	12.1	1000	49.5 x 19.0	57.1	1	**1882900000**	
THM WriteOn 50.8/150	39.7	500	50.8 x 25.4	150.0	1	**1109150000**	**1109180000**
THM WriteOn 51/36	7.6	1000	50.8 x 12.7	36.5	1	**1934190000**	

CLI – CableLine® Laser-printed Identification



A complete assortment for all marking tasks

The CableLine® product programme consists of individual combination markers for cables and wires with cross-sections from 0.2 mm² to 70 mm². The programme makes marking of electrical cables both simple and flexible. The reason: the CableLine® assortment includes both closed and open markers that can be attached before or after the wire or cable has been connected.

Providing incomparable quality, the CableLine® markers are printed using a new laser technology. Manufactured from cadmium- and silicone-free PVC, all markers meet UL 94-VO requirements. Stainless steel versions also available.

The CableLine® programme comprises
- Wire markers
- Cable markers
- Standard or customer special print
- Accessories and tools
- Available in PVC or stainless steel versions

The laser printing method

All standard prints of the CableLine® markers are printed using a new laser technology. By changing the colour of the marker material, we are able to achieve printed characters that are both unique and indestructible. This laser technology enables us to print the markers in brilliant colours and excellent quality. As well as being suitable for extreme conditions, the perfectly legible, sharp contoured markings are tamper-proof. The printed characters successfully withstand all the usual market tests pertaining to resistance to smearing and scratching; the markers are even impervious to solvents such as acetone.



The material used for CableLine® markers is extremely robust and suitable for continuous operating temperatures between –40 °C to +80 °C. That means identification markings are also eminently suitable to withstand tough climatic conditions.
See for yourself – be convinced!

CableLine® packaging types



Technical data

	Type	Marker length mm	CD	MultiPack	Bag	Looped strip
	CLI C 02-3	3	500	1000 (5 x 200)	-	-
	CLI C 02-6	6	250	1000 (5 x 200)	-	1000
	CLI C 02-9	9	125	500 (5 x 100)	-	1000
	CLI C 02-12	12	-	-	-	1000
	CLI C 02-15	15	-	-	-	1000
	CLI C 02-18	18	-	-	-	1000
	CLI C 02-21	21	-	-	-	1000
	CLI C 1-3	3	500	1000 (5 x 200)	-	-
	CLI C 1-6	6	250	500 (5 x 100)	-	1000
	CLI C 1-9	9	125	500 (5 x 100)	-	1000
	CLI C 1-12	12	-	-	-	1000
	CLI C 1-15	15	-	-	-	1000
	CLI C 1-18	18	-	-	-	1000
	CLI C 1-21	21	-	-	-	1000
	CLI C 1-24	24	-	-	-	1000
	CLI C 1-33	33	-	-	-	1000
	CLI C 2-4	4	250	500 (5 x 100)	-	-
	CLI C 2-6	6	125	500 (5 x 100)	-	1000
	CLI C 2-9	9	125	500 (5 x 100)	-	1000
	CLI C 2-12	12	-	-	-	1000
	CLI C 2-15	15	-	-	-	1000
	CLI C 2-18	18	-	-	-	1000
	CLI C 2-21	21	-	-	-	1000
	CLI C 3-6	6	-	100 (5 x 20)	-	1000
	CLI C 3-9	9	-	100 (5 x 20)	-	1000
	CLI C 3-12	12	-	-	-	1000
	CLI C 3-15	15	-	-	-	1000
	CLI C 3-18	18	-	-	-	1000
	CLI C 3-21	21	-	-	-	1000
	CLI O 10-3	3	-	1000 (5 x 200)	-	-
	CLI O 10-6	6	-	1000 (5 x 200)	-	-
	CLI O 20-3	3	-	1000 (5 x 200)	-	-
	CLI O 20-6	6	-	1000 (5 x 200)	-	-
	CLI O 30-3	3	-	1000 (5 x 200)	-	-
	CLI M 2-4	4	500	500 (5 x 100)	-	-
	CLI M 2-6	6	250	500 (5 x 100)	-	1000
	CLI M 2-9	9	125	-	-	1000
	CLI M 2-12	12	-	-	-	1000
	CLI M 2-21	21	-	-	-	1000
	CLI M 2-25Q	25	-	-	-	1000
	CLI M 2-40Q	40	-	-	-	1000
	CLI MH-70	70	-	-	100	-
	CLI MH-110	110	-	-	100	-
	CLI T 02-12	12	-	-	200	-
	CLI T 02-15	15	-	-	200	-
	CLI T 02-18	18	-	-	200	-
	CLI T 02-20	20	-	-	200	-
	CLI T 02-30	30	-	-	200	-
	CLI T 1-12	12	-	-	200	-
	CLI T 1-15	15	-	-	200	-
	CLI T 1-18	18	-	-	200	-
	CLI T 1-20	20	-	-	200	-
	CLI T 1-30	30	-	-	200	-
	CLI T 2-12	12	-	-	100	-
	CLI T 2-15	15	-	-	100	-
	CLI T 2-18	18	-	-	100	-
	CLI T 2-20	20	-	-	100	-
	CLI T 2-30	30	-	-	100	-
	CLI T 3-12	12	-	-	100	-
	CLI T 3-15	15	-	-	100	-
	CLI T 3-18	18	-	-	100	-
	CLI T 3-20	20	-	-	100	-
	CLI T 3-30	30	-	-	100	-

CableLine® - blank markers

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI R 02

Fitting mandrel with CLI C 02

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm

Ordering data

Type	Colour	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI R 02-3	yellow	3	10	**0560001687**		

CLI R 1

Fitting mandrel with CLI C 1

Technical specification

Conductor cross-section	1.5 mm² - 4 mm²
Cond. ext. Ø	3.0 mm - 5.0 mm

Type	Colour	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI R 1-3	Blue	3	10	**0572900002**		
CLI R 1-3	yellow	3	10	**0572901687**		

CLI C 02

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm

Type	Colour	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI C 02-3	yellow	3	200	**0213811687**		
CLI C 02-3	yellow	3	500		**1568241058**	
CLI C 02-3	red	3	200	**0213811686**		
CLI C 02-3	red	3	500		**1568241686**	
CLI C 02-3	white	3	200	**0213811044**		
CLI C 02-3	white	3	500		**1869821044**	
CLI C 02-3	grey	3	200	**1869351691**		
CLI C 02-3	grey	3	500		**1878201691**	
CLI C 02-3	Blue	3	200	**0213811693**		
CLI C 02-3	Blue	3	500		**1878201693**	
CLI C 02-3	pink	3	500		**1568241695**	
CLI C 02-3	brown	3	500		**1568241692**	
CLI C 02-3	magenta	3	500		**1568241689**	
CLI C 02-3	black	3	500		**1568241694**	
CLI C 02-3	Orange	3	500		**1568241690**	
CLI C 02-3	green	3	500		**1568241688**	
CLI C 02-6	yellow	6	250		**1568241059**	
CLI C 02-9	yellow	9	125		**1568241060**	
CLI C 02-18	yellow	18	1000			**1873741687**
CLI C 02-18	white	18	1000			**1873741044**

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 1

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm

Ordering data

Type	Colour	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI C 1-3	yellow	3	200	**0171111687**		
CLI C 1-3	yellow	3	500		**1568251699**	
CLI C 1-3	Blue	3	200	**0171111693**		
CLI C 1-3	Blue	3	500		**1568251693**	
CLI C 1-3	grey	3	200	**0171111691**		
CLI C 1-3	grey	3	500		**1568251691**	
CLI C 1-3	green	3	200	**0171111688**		
CLI C 1-3	green	3	500		**1568251688**	
CLI C 1-3	red	3	200	**0171111686**		
CLI C 1-3	red	3	500		**1568251686**	
CLI C 1-3	white	3	200	**0171111044**		
CLI C 1-3	white	3	500		**1568251044**	
CLI C 1-3	pink	3	500		**1568251695**	
CLI C 1-3	magenta	3	500		**1568251689**	
CLI C 1-3	Orange	3	500		**1568251690**	
CLI C 1-3	brown	3	500		**1568251692**	
CLI C 1-3	black	3	500		**1568251694**	
CLI C 1-6	yellow	6	250		**1868811687**	
CLI C 1-9	yellow	9	125		**1868810004**	
CLI C 1-12	yellow	12	1000			**1871841687**
CLI C 1-12	white	12	1000			**1871841044**
CLI C 1-15	yellow	15	1000			**1871791687**
CLI C 1-15	white	15	1000			**1871791044**
CLI C 1-18	yellow	18	1000			**1871801687**
CLI C 1-18	white	18	1000			**1871801044**
CLI C 1-21	yellow	21	1000			**1913311687**
CLI C 1-24	white	24	1000			**1871811044**
CLI C 1-33	yellow	33	1000			**1871821687**

CLI C 2

Technical specification

Conductor cross-section	2.5 mm² - 16 mm²
Cond. ext. Ø	4.0 mm - 10.0 mm

Type	Colour	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI C 2-4	Blue	4	250		**0171301693**	
CLI C 2-4	yellow	4	100	**0171310000**		
CLI C 2-4	yellow	4	250		**0171301687**	
CLI C 2-4	green	4	250		**0171301688**	
CLI C 2-4	grey	4	250		**0171301691**	
CLI C 2-4	white	4	100	**0251311060**		
CLI C 2-4	white	4	250		**0171301044**	
CLI C 2-4	black	4	250		**0171301694**	
CLI C 2-4	brown	4	250		**0171301692**	
CLI C 2-4	red	4	250		**0171301686**	
CLI C 2-4	Orange	4	250		**0171301690**	
CLI C 2-4	magenta	4	250		**0171301689**	
CLI C 2-6	yellow	6	125		**1871901687**	
CLI C 2-9	yellow	9	125		**1871971687**	
CLI C 2-18	yellow	18	1000			**1871831687**
CLI C 2-18	white	18	1000			**1871831044**

CableLine® - blank markers

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 3

Technical specification

Conductor cross-section	16 mm² - 70 mm²
Cond. ext. Ø	8.0 mm - 16.0 mm

Ordering data

Type	Colour	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI C 3-6	yellow	6	20	**0240011687**		
CLI C 3-6	white	6	20	**0240011044**		
CLI C 3-6	black	6	20	**0240011694**		
CLI C 3-6	brown	6	20	**0240011692**		
CLI C 3-6	red	6	20	**0240011686**		
CLI C 3-6	Orange	6	20	**0240011690**		
CLI C 3-6	green	6	20	**0240011688**		
CLI C 3-6	Blue	6	20	**0240011693**		
CLI C 3-6	magenta	6	20	**0240011689**		
CLI C 3-6	grey	6	20	**0240011691**		
CLI C 3-18	yellow	18	1000			**1872671687**

CLI O 10

Technical specification

Conductor cross-section	0.4 mm² - 1.5 mm²
Cond. ext. Ø	2.0 mm - 3.0 mm

Type	Colour	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI O 10-3	yellow	3	200	**0689600000**		
CLI O 10-3	white	3	200	**1872681044**		

CLI O 20

Technical specification

Conductor cross-section	1.5 mm² - 2.5 mm²
Cond. ext. Ø	3.0 mm - 4.0 mm

Type	Colour	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI O 20-3	yellow	3	200	**0689700000**		
CLI O 20-3	white	3	200	**1872691044**		

CLI O 30

Technical specification

Conductor cross-section	2.5 mm² - 4 mm²
Cond. ext. Ø	4.0 mm - 5.0 mm

Type	Colour	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI O 30-3	yellow	3	200	**0689800000**		
CLI O 30-3	white	3	200	**1872701044**		

CLI M 2

Technical specification

Conductor cross-section	16 mm² - 500 mm²
Cond. ext. Ø	10.0 mm - 317.0 mm

Type	Colour	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI M 2-4	yellow	4	100	**1733650004**		
CLI M 2-4	yellow	4	500		**1568300001**	
CLI M 2-4	white	4	100	**1871371044**		
CLI M 2-4	white	4	500		**1568301051**	
CLI M 2-4	red	4	500		**1568301686**	
CLI M 2-4	green	4	500		**1568301688**	
CLI M 2-4	Blue	4	500		**1568301693**	
CLI M 2-4	magenta	4	500		**1568301689**	
CLI M 2-4	pink	4	500		**1568301701**	
CLI M 2-4	brown	4	500		**1568301692**	
CLI M 2-4	black	4	500		**1568301700**	
CLI M 2-25Q	yellow	25	1000			**1886531687**
CLI M 2-40Q	yellow	40	1000			**1886541687**

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI R 02

Fitting mandrel with CLI C 02

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm

Ordering data

Type	max. characters per marker	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI R 02-3	1	3	10	**0560009999**		

CLI R 1

Fitting mandrel with CLI C 1

Technical specification

Conductor cross-section	1.5 mm² - 4 mm²
Cond. ext. Ø	3.0 mm - 5.0 mm

Type	max. characters per marker	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI R 1-3	1	3	10	**0572909999**		

CLI C 02

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm

Type	max. characters per marker	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI C 02-3	1	3	500		**1568249999**	
CLI C 02-3	1	3	1			**1912550000**
CLI C 02-6	2	6	250		**1869999999**	
CLI C 02-6	2	6	1			**1912620000**
CLI C 02-9	3	9	125		**1899290000**	
CLI C 02-9	3	9	1			**1869829999**
CLI C 02-12	4	12	1			**1873330000**
CLI C 02-15	5	15	1			**0252509999**
CLI C 02-18	8	18	1			**1873749999**
CLI C 02-21	10	21	1			**1873340000**
CLI C 02-24	12	24	1			**1912500000**
CLI C 02-27	13	27	1			**1912510000**
CLI C 02-30	15	30	1			**1912580000**
CLI C 02-33	17	33	1			**1912590000**
CLI C 02-36	19	36	1			**1912600000**
CLI C 02-39	21	39	1			**1912610000**

CLI C 1

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm

Type	max. characters per marker	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI C 1-3	1	3	500		**1568259999**	
CLI C 1-3	1	3	1			**1912650000**
CLI C 1-6	2	6	250		**0252709999**	
CLI C 1-6	2	6	1			**1912700000**
CLI C 1-9	3	9	125		**0252809999**	
CLI C 1-9	3	9	1			**1868819999**
CLI C 1-12	4	12	1			**1873350000**
CLI C 1-15	5	15	1			**1873360000**
CLI C 1-18	8	18	1			**1871809999**
CLI C 1-21	10	21	1			**1873370000**
CLI C 1-24	12	24	1			**1912630000**
CLI C 1-27	13	27	1			**1912640000**
CLI C 1-30	15	30	1			**1912660000**
CLI C 1-33	17	33	1			**1912670000**
CLI C 1-36	19	36	1			**1912680000**
CLI C 1-39	21	39	1			**1912690000**

CableLine® - Special print

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 2

Technical specification

Conductor cross-section	2.5 mm² - 16 mm²
Cond. ext. Ø	4.0 mm - 10.0 mm

Ordering data

Type	max. characters per marker	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI C 2-4	1	4	250		**1568269999**	
CLI C 2-6	2	6	125		**1871909999**	
CLI C 2-9	3	9	100		**1899240000**	
CLI C 2-9	3	9	1			**1871979999**
CLI C 2-12	4	12	1			**1873380000**
CLI C 2-15	6	15	1			**1873390000**
CLI C 2-18	8	18	1			**1871839999**
CLI C 2-21	10	21	1			**1873400000**
CLI C 2-24	12	24	1			**1912710000**
CLI C 2-27	13	27	1			**1912720000**
CLI C 2-30	15	30	1			**1912730000**
CLI C 2-33	17	33	1			**1912740000**
CLI C 2-36	19	36	1			**1912750000**
CLI C 2-39	13	39	1			**1912760000**

CLI C 3

Technical specification

Conductor cross-section	16 mm² - 70 mm²
Cond. ext. Ø	8.0 mm - 16.0 mm

Type	max. characters per marker	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI C 3-6	2	6	1			**1872309999**
CLI C 3-9	3	9	1			**1872659999**
CLI C 3-12	4	12	1			**1873420000**
CLI C 3-15	5	15	1			**1873430000**
CLI C 3-18	8	18	1			**1872679999**
CLI C 3-21	10	21	1			**1873410000**
CLI C 3-24	12	24	1			**1912770000**
CLI C 3-27	13	27	1			**1912780000**
CLI C 3-30	15	30	1			**1912790000**
CLI C 3-33	17	33	1			**1912800000**
CLI C 3-36	19	36	1			**1912810000**
CLI C 3-39	21	39	1			**1912820000**

CLI O 10

Technical specification

Conductor cross-section	0.4 mm² - 1.5 mm²
Cond. ext. Ø	2.0 mm - 3.0 mm

Type	max. characters per marker	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI O 10-3	1	3	1000	**0648009999**		
CLI O 10-6	2	6	1000	**0660100000**		

CLI O 20

Technical specification

Conductor cross-section	1.5 mm² - 2.5 mm²
Cond. ext. Ø	3.0 mm - 4.0 mm

Type	max. characters per marker	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI O 20-3	1	3	1000	**0648109999**		
CLI O 20-6	2	6	1000	**0694700000**		

CLI O 30

Technical specification

Conductor cross-section	2.5 mm² - 4 mm²
Cond. ext. Ø	4.0 mm - 5.0 mm

Type	max. characters per marker	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI O 30-3	1	3	1000	**0648209999**		
CLI O 30-6	2	6	1000	**1873470000**		

Custom printing with details of colour and characters

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI M

Technical specification

Conductor cross-section	16 mm² - 500 mm²
Cond. ext. Ø	10.0 mm - 317.0 mm

Ordering data

Type	max. characters per marker	Length	Qty.	MultiPack Order No.	CD Order No.	Looped strip Order No.
CLI M 2-4	1	4	500		**1568309999**	
CLI M 2-4	1	4	1			**1912830000**
CLI M 2-6	2	6	250		**1871789999**	
CLI M 2-6	2	6	1			**1912840000**
CLI M 2-9	3	9	200		**1899250000**	
CLI M 2-9	3	9	1			**1873440000**
CLI M 2-12	4	12	1			**1873450000**
CLI M 2-15	5	15	1			**1899260000**
CLI M 2-18	8	18	1			**1899230000**
CLI M 2-21	10	21	1			**1873460000**
CLI M 2-24	12	24	1			**1912860000**
CLI M 2-27	13	27	1			**1912870000**
CLI M 2-30	15	30	1			**1912880000**
CLI M 2-33	17	33	1			**1912920000**
CLI M 2-36	19	36	1			**1912950000**
CLI M 2-39	21	39	1			**1912960000**
CLI M 2-25	12	25	1			**1579500000**
CLI M 2-40	21	40	1			**1634790000**

CableLine® - International colour code

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C - to +80 °C

CLI C 02-3

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm
Length	3 mm

Ordering data

Printing	Colour	Text colour	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.
0	black	white	0252111503	1568241503
1	brown	white	0252111506	1568241506
2	red	black	0252111509	1568241509
3	Orange	black	0252111512	1568241512
8	grey	black	0252111527	1568241527
4	yellow	black	0252111514	1568241514
5	green	black	0252111518	1568241518
6	Blue	black	0252111521	1568241521
7	magenta	black	0252111524	1568241524
9	white	black	0252111530	1568241530

CLI C 1-3

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	3 mm

Printing	Colour	Text colour	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.
0	black	white	0252611503	1568251503
1	brown	white	0252611506	1568251506
2	red	black	0252611509	1568251509
3	Orange	black	0252611512	1568251512
4	yellow	black	0252611514	1568251514
5	green	black	0252611518	1568251518
6	Blue	black	0252611521	1568251521
7	magenta	black	0252611524	1568251524
8	grey	black	0252611527	1568251527
9	white	black	0252611530	1568251530

CLI C 2-4

Technical specification

Conductor cross-section	2.5 mm² - 16 mm²
Cond. ext. Ø	4.0 mm - 10.0 mm
Length	4 mm

Printing	Colour	Text colour	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.
0	black	white	0251311503	1568261503
1	brown	white	0251311506	1568261506
2	red	black	0251311509	1568261509
3	Orange	black	0251311512	1568261512
4	yellow	black	0251311514	1568261514
5	green	black	0251311518	1568261518
6	Blue	black	0251311521	1568261521
7	magenta	black	0251311524	1568261524
8	grey	black	0251311527	1568261527
9	white	black	0251310009	1568261530

CLI C 3-6

Technical specification

Conductor cross-section	16 mm² - 70 mm²
Cond. ext. Ø	8.0 mm - 16.0 mm
Length	6 mm

Printing	Colour	Text colour	MultiPack Qty.=200 Order No.
0	black	white	0253411503
1	brown	white	0253411506
2	red	black	0253411509
3	Orange	black	0253411512
4	yellow	black	0253411514
5	green	black	0253411518
6	Blue	black	0253411521
7	magenta	black	0253411524
8	grey	black	0253411527
9	white	black	0253411530

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C - to +80 °C

CLI M 2-4

Technical specification

Conductor cross-section	16 mm² - 500 mm²
Cond. ext. Ø	10.0 mm - 317.0 mm
Length	4 mm

Ordering data

Printing	Colour	Text colour	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.
0	black	white	**1733651503**	**1568301503**
1	brown	white	**1733651506**	**1568301506**
2	red	black	**1733651509**	**1568301509**
3	Orange	black	**1733651512**	**1568301512**
4	yellow	black	**1733651514**	**1568301514**
5	green	black	**1733651518**	**1568301518**
6	Blue	black	**1733651521**	**1568301521**
7	magenta	black	**1733651524**	**1568301524**
8	grey	black	**1733651527**	**1568301527**
9	white	black	**1733651530**	**1568301530**

CLI R 02

Fitting mandrel with CLI C 02

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm
Length	3 mm

Printing	Colour	Text colour	Qty.	Order No.
0	black	white	10	**0560001503**
1	brown	white	10	**0560001506**
2	red	black	10	**0560001509**
3	Orange	black	10	**0560001512**
4	yellow	black	10	**0560001513**
5	green	black	10	**0560001518**
6	Blue	black	10	**0560001521**
7	magenta	black	10	**0560001524**
8	grey	black	10	**0560001527**
9	white	black	10	**0560001530**

CLI R 1

Fitting mandrel with CLI C 1

Technical specification

Conductor cross-section	1.5 mm² - 4 mm²
Cond. ext. Ø	3.0 mm - 5.0 mm
Length	3 mm

Printing	Colour	Text colour	Qty.	Order No.
0	black	white	10	**0572901502**
1	brown	white	10	**0572901505**
2	red	black	10	**0572901508**
3	Orange	black	10	**0572901511**
4	yellow	black	10	**0572901515**
5	green	black	10	**0572901517**
6	Blue	black	10	**0572901520**
7	magenta	black	10	**0572901523**
8	grey	black	10	**0572901526**
9	white	black	10	**0572901529**

Closed wire markers

CLI C wire markers are fitted to unconnected cables. Four different sizes are available to mark wire cross-sections from 0.5 mm² to maximum 70 mm². The markers are already printed and ready for use. Individual markings can be created by simply combining the individual markers.

Advantages

- Closed markers, secure and adjustable for unconnected cables
- Special resilient bellow profile ensures a wide application range
- Fast and easy to fit – in next to no time
- Compatible accessories take the strain off marking tasks
- Permanent high-quality markings
- Best contrast for optimum legibility

CLI C

Version	Closed markers made from soft PVC. Resilient bellow construction enables fast and easy attachment. Standard, special and international colour-code compliant prints available.
Material	Soft PVC, cadmium- and silicone-free
Temperature range	–30 °C to +80 °C.
Flammability classification	Corresponds to V0 to UL 94
Resistance	Highly resistant to oils and petrol as well as gamma and UV radiation
Printing	Laser marking

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 02-3

0 - 9

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm
Length	3 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.
0	0252111502	1568241502	0252111000	1869821502
1	0252111505	1568241505	0252110001	1869821505
2	0252111508	1568241508	0252110002	1869821508
3	0252111511	1568241511	0252110003	1869821511
4	0252111514	1568241514	0252110004	1869821514
5	0252111517	1568241517	0252110005	1869821517
6	0252111520	1568241520	0252110006	1869821520
7	0252111523	1568241523	0252110007	1869821523
8	0252111526	1568241526	0252110008	1869821526
9	0252111529	1568241529	0252111530	1568241530

CLI C 02-3

0 - 9

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm
Length	3 mm

	grey		black	
Printing	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
0	1869351502	1878201502		
1	1869351505	1878201505		
2	1869351508	1878201508		
3	1869351511	1878201511		
4	1869351514	1878201514		
5	1869351517	1878201517		
6	1869351520	1878201520		
7	1869351523	1878201523		
8	0252111527	1568241527		
9	1869351529	1878201529		

CLI C 02-3

A - Z

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm
Length	3 mm

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.
A	0252111637	1568241637	1869991637	1869821637
B	0252111639	1568241639	1869991639	1869821639
C	0252111641	1568241641	1869991641	1869821641
D	0252111643	1568241643	1869991643	1869821643
E	0252111645	1568241645	1869991645	1869821645
F	0252111647	1568241647	1869991647	1869821647
G	0252111649	1568241649	1869991649	1869821649
H	0252111651	1568241651	1869991651	1869821651
I	0252111653	1568241653	1869991653	1869821653
J	0252111655	1568241655	1869991655	1869821655
K	0252111657	1568241657	1869991657	1869821657
L	0252111659	1568241659	1869991659	1869821659
M	0252111661	1568241661	1869991661	1869821661
N	0252111663	1568241663	1869991663	1869821663
O	0252111665	1568241665	1869991665	1869821665
P	0252111667	1568241667	1869991667	1869821667
Q	0252111669	1568241669	1869991669	1869821669
R	0252111671	1568241671	1869991671	1869821671
S	0252111673	1568241673	1869991673	1869821673
T	0252111676	1568241676	1869991676	1869821676
U	0252111679	1568241679	1869991679	1869821679
V	0252111681	1568241681	1869991681	1869821681
W	0252111683	1568241683	1869991683	1869821683
X	0252111687	1568241687	1869991687	1869821687
Y	0252111696	1568241696	1869991696	1869821696
Z	0252111698	1568241698	1869991698	1869821698

CableLine® - CLI C 02-3

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 02-3

a - z

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm
Length	3 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.= Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
a	0252111700			
b	0252111701			
c	0252111702			
d	0252111703			
e	0252111704			
f	0252111705			
g	0252111706			
h	0252111707			
i	0252111708			
j	0252111709			
k	0252111710			
l	0252111711			
m	0252111712			
n	0252111713			
o	0252111714			
p	0252111715			
q	0252111716			
r	0252111717			
s	0252111718			
t	0252111719			
u	0252111720			
v	0252111721			
w	0252111722			
x	0252111723			
y	0252111724			
z	0252111725			

CLI C 02-3

Special characters

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm
Length	3 mm

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.
Ä	0252111697	1568241056	1869991697	1869821697
Å	0252111699	1568241055	1869991699	1869821699
Ö	0252111695	1568241057	1869991695	1869821695
/	0252111742	1568241742	1869991742	1869821742
+	0252111738	1568241738	1869991738	1869821738
-	0252111740	1568241740	1869991740	1869821740
.	0252111748	1568241748	1869991748	1869821748
:	0252111750	1568241750	1869991750	1869821750
=	0252111751	1568241751	1869991751	1869821751
~	0252111752	1568241752	1869991752	1869821752
⏚	0252111747	1568241747	1869991747	1869821747
⏚	0252111746	1568241746	1869991746	1869821746
Æ		1568241735		
Ø		1568241736		

CLI C 02-3

Special characters

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm
Length	3 mm

	blue		red	
Printing	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.
-	0252111741	1568241741		
N	0252111664	1568241664		
+			0252111737	1568241737

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 02-6

Special characters

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm
Length	6 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.=250 Order No.	MultiPack Qty.=200 Order No.	CD Qty.=250 Order No.
L1	0252111728	1568241728	1869991728	1869821728
L2	0252111729	1568241729	1869991729	1869821729
L3	0252111730	1568241730	1869991730	1869821730
A1	0252111726	1568241726	1869991726	1869821726
A2	0252111727	1568241727	1869991727	1869821727
VS		1568241731		

CLI C 02-9

Special characters

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm
Length	9 mm

	yellow		white	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=125 Order No.	MultiPack Qty.=100 Order No.	CD Qty.=125 Order No.
PEN	0252111734	1568241734	1869991734	1869821734

CableLine® - CLI C 1-3

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 1-3

0 - 9

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	3 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.
0	0252611502	1568251502	0252611000	1568251000
1	0252611505	1568251505	0252610001	1568250001
2	0252611508	1568251508	0252610002	1568250002
3	0252611511	1568251511	0252610003	1568250003
4	0252611514	1568251514	0252610004	1568250004
5	0252611517	1568251517	0252610005	1568250005
6	0252611520	1568251520	0252610006	1568250006
7	0252611523	1568251523	0252610007	1568250007
8	0252611526	1568251526	0252610008	1568250008
9	0252611529	1568251529	0252611530	1568251530

CLI C 1-3

0 - 9

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	3 mm

	grey		black	
Printing	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.	MultiPack Qty.=200 Order No.	CD Qty.= Order No.
0	1869181502	1878171502	0252611503	
1	1869181505	1878171505	1856620001	
2	1869181508	1878171508	1856620002	
3	1869181511	1878171511	1856620003	
4	1869181514	1878171514	1856620004	
5	1869181517	1878171517	1856620005	
6	1869181520	1878171520	1856620006	
7	1869181523	1878171523	1856620007	
8	0252611527	1568251527	1856620008	
9	1869181529	1878171529	1856620009	

CLI C 1-3

A - Z

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	3 mm

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.
A	0252611637	1568251637	0252611021	1568251021
B	0252611639	1568251639	0252611022	1568251022
C	0252611641	1568251641	0252611023	1568251023
D	0252611643	1568251643	0252611024	1568251024
E	0252611645	1568251645	0252611025	1568251025
F	0252611647	1568251647	0252611026	1568251026
G	0252611649	1568251649	0252611027	1568251027
H	0252611651	1568251651	0252611028	1568251028
I	0252611653	1568251653	0252611029	1568251029
J	0252611655	1568251655	0252611030	1568251030
K	0252611657	1568251657	0252611031	1568251031
L	0252611659	1568251659	0252611032	1568251032
M	0252611661	1568251661	0252611033	1568251033
N	0252611663	1568251663	0252611034	1568251034
O	0252611665	1568251665	0252611035	1568251035
P	0252611667	1568251667	0252611036	1568251036
Q	0252611669	1568251669	0252611037	1568251037
R	0252611671	1568251671	0252611038	1568251038
S	0252611673	1568251673	0252611039	1568251039
T	0252611676	1568251676	0252611040	1568251040
U	0252611679	1568251679	0252611041	1568251041
V	0252611681	1568251681	0252611042	1568251042
W	0252611683	1568251683	0252611043	1568251043
X	0252611687	1568251687	0252611044	1568251054
Y	0252611696	1568251696	0252611045	1568251045
Z	0252611698	1568251698	0252611046	1568251046

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 1-3

A - Z

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	3 mm

Bestelldaten

	grey		black	
Printing	MultiPack Qty.= Order No.	CD Qty.= Order No.	MultiPack Qty.=200 Order No.	CD Qty.= Order No.
A			1856620011	
B			1856620012	
C			1856620013	
D			1856620014	
E			1856620015	
F			1856620016	
G			1856620017	
H			1856620018	
I			1856620019	
J			1856620020	
K			1856620021	
L			1856620022	
M			1856620023	
N			1856620024	
O			1856620025	
P			1856620026	
Q			1856620027	
R			1856620028	
S			1856620029	
T			1856620030	
U			1856620031	
V			1856620032	
W			1856620033	
X			1856620034	
Y			1856620035	
Z			1856620036	

CLI C 1-3

a - z

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	3 mm

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
a	0252611700	1568251700		
b	0252611701	1568251701		
c	0252611702	1568251702		
d	0252611703	1568251703		
e	0252611704	1568251704		
f	0252611705	1568251705		
g	0252611706	1568251706		
h	0252611707	1568251707		
i	0252611708	1568251708		
j	0252611709	1568251709		
k	0252611710	1568251710		
l	0252611711	1568251711		
m	0252611712	1568251712		
n	0252611713	1568251713		
o	0252611714	1568251714		
p	0252611715	1568251715		
q	0252611716	1568251716		
r	0252611717	1568251717		
s	0252611718	1568251718		
t	0252611719	1568251719		
u	0252611720	1568251720		
v	0252611721	1568251721		
w	0252611722	1568251722		
x	0252611723	1568251723		
y	0252611724	1568251724		
z	0252611725	1568251725		

CableLine® - CLI C 1-3

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 1-3

Special characters

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	3 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.
Ä	0252611697	1568251797	0252611056	1568251056
Å	0252611699	1568251799	0252611055	1568251055
Ö	0252611695	1568251795	0252611057	1568251057
+	0252611738	1568251738	0252611048	1568251048
-	0252611740	1568251740	0252611049	1568251049
/	0252611742	1568251742	0252611050	1568251050
.	0252611748	1568251748	0252611047	1568251047
:	0252611750	1568251750	0252611051	1568251051
=	0252611751	1568251751	0252611052	1568251052
~	0252611752	1568251752	0252611059	1568251059
*		1568251753		
Ø		1568251736		
Æ		1568251735		
⏚	0252611747	1568251747	0252611058	1568251058
⏚	0252611746	1568251746	0252611053	1568251053

CLI C 1-3

Special characters

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	3 mm

	grey		black	
Printing	MultiPack Qty.=200 Order No.	CD Qty.= Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
-	1869181740			

CLI C 1-3

Special characters

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	3 mm

	blue		red	
Printing	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.	MultiPack Qty.=200 Order No.	CD Qty.=500 Order No.
-	0252611741	1568251741		
N	0252611664	1568251664		
+			0252611737	1568251737

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 1-6

01 - 60

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	6 mm

Ordering data

	yellow	
	MultiPack Qty.=100	CD Qty.=250
Printing	Order No.	Order No.
01	0252711522	1868811522
02	0252711523	1868811523
03	0252711524	1868811524
04	0252711525	1868811525
05	0252711526	1868811526
06	0252711527	1868811527
07	0252711528	1868811528
08	0252711529	1868811529
09	0252711530	1868811530
10	0252711531	1868811531
11	0252711532	1868811532
12	0252711533	1868811533
13	0252711534	1868811534
14	0252711535	1868811535
15	0252711536	1868811536
16	0252711537	1868811537
17	0252711538	1868811538
18	0252711539	1868811539
19	0252711540	1868811540
20	0252711541	1868811541
21	0252711542	1868811542
22	0252711543	1868811543
23	0252711544	1868811544
24	0252711545	1868811545
25	0252711546	1868811546
26	0252711547	1868811547
27	0252711548	1868811548
28	0252711549	1868811549
29	0252711550	1868811550
30	0252711551	1868811551
31	0252711552	1868811552
32	0252711553	1868811553
33	0252711554	1868811554
34	0252711555	1868811555
35	0252711556	1868811556
36	0252711557	1868811557
37	0252711558	1868811558
38	0252711559	1868811559
39	0252711560	1868811560
40	0252711561	1868811561
41	0252711562	1868811562
42	0252711563	1868811563
43	0252711564	1868811564
44	0252711565	1868811565
45	0252711566	1868811566
46	0252711567	1868811567
47	0252711568	1868811568
48	0252711569	1868811569
49	0252711570	1868811570
50	0252711571	1868811571
51	0252711572	1868811572
52	0252711573	1868811573
53	0252711574	1868811574
54	0252711575	1868811575
55	0252711576	1868811576
56	0252711577	1868811577
57	0252711578	1868811578
58	0252711579	1868811579
59	0252711580	1868811580
60	0252711581	1868811581

CableLine® - CLI C 1-6

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 1-6

61 - 99

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	6 mm

Ordering data

	yellow	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=250 Order No.
61	0252711582	1868811582
62	0252711583	1868811583
63	0252711584	1868811584
64	0252711585	1868811585
65	0252711586	1868811586
66	0252711587	1868811587
67	0252711588	1868811588
68	0252711589	1868811589
69	0252711590	1868811590
70	0252711591	1868811591
71	0252711592	1868811592
72	0252711593	1868811593
73	0252711594	1868811594
74	0252711595	1868811595
75	0252711596	1868811596
76	0252711597	1868811597
77	0252711598	1868811598
78	0252711599	1868811599
79	0252711600	1868811600
80	0252711601	1868811601
81	0252711602	1868811602
82	0252711603	1868811603
83	0252711604	1868811604
84	0252711605	1868811605
85	0252711606	1868811606
86	0252711607	1868811607
87	0252711608	1868811608
88	0252711609	1868811609
89	0252711610	1868811610
90	0252711611	1868811611
91	0252711612	1868811612
92	0252711613	1868811613
93	0252711614	1868811614
94	0252711615	1868811615
95	0252711616	1868811616
96	0252711617	1868811617
97	0252711618	1868811618
98	0252711619	1868811619
99	0252711620	1868811620

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 1-6

Special characters

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	6 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=250 Order No.	MultiPack Qty.=100 Order No.	CD Qty.=250 Order No.
L1	0252711728	1868811728	1871341728	1871351728
L2	0252711729	1868811729	1871341729	1871351729
L3	0252711730	1868811730	1871341730	1871351730
A1	0252711726	1868811726	1871341726	1871351726
A2	0252711727	1868811727	1871341727	1871351727
X1		1868811150		
X2		1868811151		
MP		1868811731		
PE	0252711733	1868811733		
I1		1868811739		
I2		1868811740		
U1		1868811735		
U2		1868811736		
U3		1868811737		
UN		1868811738		
IC		1868811741		

CLI C 1-6

Special characters

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	6 mm

	blue		red	
Printing	MultiPack Qty.=100 Order No.	CD Qty.= Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
MP	0252711732			

CLI C 1-6

Special characters

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	6 mm

	grey		black	
Printing	MultiPack Qty.=100 Order No.	CD Qty.= Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
L1	1878191728			
L2	1878191729			
L3	1878191730			

CLI C 1-9

Special characters

Technical specification

Conductor cross-section	0.5 mm² - 4 mm²
Cond. ext. Ø	1.8 mm - 5.0 mm
Length	9 mm

	yellow		white	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=125 Order No.	MultiPack Qty.=100 Order No.	CD Qty.=125 Order No.
PEN	0252711734	1868811734	1871341734	1871351734

CableLine® - CLI C 2-4

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 2-4

0 - 9

Technical specification

Conductor cross-section	2.5 mm² - 16 mm²
Cond. ext. Ø	4.0 mm - 10.0 mm
Length	4 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=250 Order No.	MultiPack Qty.=100 Order No.	CD Qty.=250 Order No.
0	0251311502	1568261502	0251311000	1871871502
1	0251311505	1568261505	0251310001	1871871505
2	0251311508	1568261508	0251310002	1871871508
3	0251311511	1568261511	0251310003	1871871511
4	0251311514	1568261514	0251310004	1871871514
5	0251311517	1568261517	0251310005	1871871517
6	0251311520	1568261520	0251310006	1871871520
7	0251311523	1568261523	0251310007	1871871523
8	0251311526	1568261526	0251310008	1871871526
9	0251311529	1568261529	0251310009	1568261530

CLI C 2-4

0 - 9

Technical specification

Conductor cross-section	2.5 mm² - 16 mm²
Cond. ext. Ø	4.0 mm - 10.0 mm
Length	4 mm

	grey		black	
Printing	MultiPack Qty.=100 Order No.	CD Qty.= Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
0	1871851502			
1	1871851505			
2	1871851508			
3	1871851511			
4	1871851514			
5	1871851517			
6	1871851520			
7	1871851523			
8	0251311527			
9	1871851529			

CLI C 2-4

A - Z

Technical specification

Conductor cross-section	2.5 mm² - 16 mm²
Cond. ext. Ø	4.0 mm - 10.0 mm
Length	4 mm

	yellow		white	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=250 Order No.	MultiPack Qty.=100 Order No.	CD Qty.=250 Order No.
A	0251311637	1568261637	0251311021	1871871637
B	0251311639	1568261639	0251311022	1871871639
C	0251311641	1568261641	0251311023	1871871641
D	0251311643	1568261643	0251311024	1871871643
E	0251311645	1568261645	0251311025	1871871645
F	0251311647	1568261647	0251311026	1871871647
G	0251311649	1568261649	0251311027	1871871649
H	0251311651	1568261651	0251311028	1871871651
I	0251311653	1568261653	0251311029	1871871653
J	0251311655	1568261655	0251311030	1871871655
K	0251311657	1568261657	0251311031	1871871657
L	0251311659	1568261659	0251311032	1871871659
M	0251311661	1568261661	0251311033	1871871661
N	0251311663	1568261663	0251311034	1871871663
O	0251311665	1568261665	0251311035	1871871665
P	0251311667	1568261667	0251311036	1871871667
Q	0251311669	1568261669	0251311037	1871871669
R	0251311671	1568261671	0251311038	1871871671
S	0251311673	1568261673	0251311039	1871871673
T	0251311676	1568261676	0251311040	1871871676
U	0251311679	1568261679	0251311041	1871871679
V	0251311681	1568261681	0251311042	1871871681
W	0251311683	1568261683	0251311043	1871871683
X	0251311687	1568261687	0251311044	1871871685
Y	0251311696	1568261696	0251311045	1871871696
Z	0251311698	1568261698	0251311046	1871871698

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 2-4

Special characters

Technical specification

Conductor cross-section	2.5 mm² - 16 mm²
Cond. ext. Ø	4.0 mm - 10.0 mm
Length	4 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=250 Order No.	MultiPack Qty.=100 Order No.	CD Qty.=250 Order No.
Ä	0251311697	1568261697	0251311056	1871871697
Å	0251311699	1568261699	0251311055	1871871699
Ö	0251311695	1568261695	0251311057	1871871695
+	0251311738	1568261738	0251311048	1871871738
-	0251311740	1568261740	0251311049	1871871740
/	0251311742	1568261742	0251311050	1871871742
.	0251311748	1568261748	0251311047	1871871748
:	0251311750	1568261750	0251311051	1871871750
=	0251311751	1568261751	0251311052	1871871751
~	0251311752	1568261752	0251311059	1871871752
Ø	0251311736	1568261736		
Æ	0251311735	1568261735		
⏚	0251311747	1568261747	0251311058	1871871747
⏚	0251311746	1568261746	0251311053	1871871746

CLI C 2-4

Special characters

Technical specification

Conductor cross-section	2.5 mm² - 16 mm²
Cond. ext. Ø	4.0 mm - 10.0 mm
Length	4 mm

	blue		red	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=250 Order No.	MultiPack Qty.=100 Order No.	CD Qty.=250 Order No.
-	0251311741	1568261741		
N	0251311664	1568261664		
+			0251311737	1568261737

CLI C 2-6

Special characters

Technical specification

Conductor cross-section	2.5 mm² - 16 mm²
Cond. ext. Ø	4.0 mm - 10.0 mm
Length	6 mm

	yellow		white	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=125 Order No.	MultiPack Qty.=100 Order No.	CD Qty.=125 Order No.
L1	1871891728	1871901728	1871921728	1871911728
L2	1871891729	1871901729	1871921729	1871911729
L3	1871891730	1871901730	1871921730	1871911730
PE		1871901731		

CLI C 2-9

Special characters

Technical specification

Conductor cross-section	4 mm² - 16 mm²
Cond. ext. Ø	4.0 mm - 10.0 mm
Length	9 mm

	yellow		white	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=125 Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
PEN	1872031734	1871971734		

CableLine® - CLI C 3-6

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 3-6

0 - 9

Technical specification

Conductor cross-section	16 mm² - 70 mm²
Cond. ext. Ø	8.0 mm - 16.0 mm
Length	6 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=20 Order No.	CD Qty.= Order No.	MultiPack Qty.=20 Order No.	CD Qty.= Order No.
0	0253411502		1872301502	
1	0253411505		1872301505	
2	0253411508		1872301508	
3	0253411511		1872301511	
4	0253411514		1872301514	
5	0253411517		1872301517	
6	0253411520		1872301520	
7	0253411523		1872301523	
8	0253411526		1872301526	
9	0253411529		0253411530	

CLI C 3-6

A - Z

Technical specification

Conductor cross-section	16 mm² - 70 mm²
Cond. ext. Ø	8.0 mm - 16.0 mm
Length	6 mm

	yellow		white	
Printing	MultiPack Qty.=20 Order No.	CD Qty.= Order No.	MultiPack Qty.=20 Order No.	CD Qty.= Order No.
A	0253411637		1872301637	
B	0253411639		1872301639	
C	0253411641		1872301641	
D	0253411643		1872301643	
E	0253411645		1872301645	
F	0253411647		1872301647	
G	0253411649		1872301649	
H	0253411651		1872301651	
I	0253411653		1872301653	
J	0253411655		1872301655	
K	0253411657		1872301657	
L	0253411659		1872301659	
M	0253411661		1872301661	
N	0253411663		1872301663	
O	0253411665		1872301665	
P	0253411667		1872301667	
Q	0253411669		1872301669	
R	0253411671		1872301671	
S	0253411673		1872301673	
T	0253411676		1872301676	
U	0253411679		1872301679	
V	0253411681		1872301681	
W	0253411683		1872301683	
X	0253411687		1872301687	
Y	0253411696		1872301696	
Z	0253411698		1872301698	

CLI C 3-6

Special characters

Technical specification

Conductor cross-section	16 mm² - 70 mm²
Cond. ext. Ø	8.0 mm - 16.0 mm
Length	6 mm

	yellow		white	
Printing	MultiPack Qty.=20 Order No.	CD Qty.= Order No.	MultiPack Qty.=20 Order No.	CD Qty.= Order No.
Ä	0253411697		1872301697	
Å	0253411699		1872301699	
Ö	0253411695		1872301695	
+	0253411738		1872301738	
-	0253411740		1872301740	
/	0253411742		1872301742	
.	0253411748		1872301748	
:	0253411750		1872301750	
=	0253411751		1872301751	
~	0253411752		1872301752	
⏚	0253411746		1872301746	

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI C 3-6

Special characters

Technical specification

Conductor cross-section	16 mm² - 70 mm²
Cond. ext. Ø	8.0 mm - 16.0 mm
Length	6 mm

Ordering data

	blue		red	
Printing	MultiPack Qty.=20 Order No.	CD Qty.= Order No.	MultiPack Qty.=20 Order No.	CD Qty.= Order No.
-	0253411741			
N	0253411664			
+			0253411737	

CLI C 3-9

Special characters

Technical specification

Conductor cross-section	16 mm² - 70 mm²
Cond. ext. Ø	8.0 mm - 16.0 mm
Length	9 mm

	yellow		white	
Printing	MultiPack Qty.=20 Order No.	CD Qty.= Order No.	MultiPack Qty.=20 Order No.	CD Qty.= Order No.
L1	0253511728		1872651728	
L2	0253511729		1872651729	
L3	0253511730		1872651730	
A1	0253511726		1872651726	
A2	0253511727		1872651727	
PE	0253511733			
SL	0253511735			
X1	0253511750			
X2	0253511751			
X3	0253511752			
PEN	1872661733		1872651734	

CableLine® - CLI R 02

The CLI R installation mandrels, fitted with CLI C 02 or CLI C 1 markers, are supplied ready to use.

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C - to +80 °C

CLI R 02

0 - 9

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm
Length	3 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=10 Order No.	CD Qty.= Order No.	MultiPack Qty.=10 Order No.	CD Qty.= Order No.
0	0560001501		1872711502	
1	0560001504		1872711505	
2	0560001507		1872711508	
3	0560001510		1872711511	
4	0560001513		1872711514	
5	0560001516		1872711517	
6	0560001519		1872711520	
7	0560001522		1872711523	
8	0560001525		1872711526	
9	0560001528		0560001530	

CLI R 02

A - Z

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm
Length	3 mm

	yellow		white	
Printing	MultiPack Qty.=10 Order No.	CD Qty.= Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
A	0560001638			
B	0560001640			
C	0560001642			
D	0560001644			
E	0560001646			
F	0560001648			
G	0560001650			
H	0560001652			
I	0560001654			
J	0560001656			
K	0560001658			
L	0560001660			
M	0560001662			
N	0560001664			
O	0560001666			
P	0560001668			
Q	0560001670			
R	0560001672			
S	0560001675			
T	0560001678			
U	0560001680			
V	0560001682			
W	0560001684			
X	0560001693			
Y	0560001697			
Z	0560001699			

CLI R 02

Special characters

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm
Length	3 mm

	yellow		white	
Printing	MultiPack Qty.=10 Order No.	CD Qty.= Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
Ä	0560001696			
Å	0560001698			
Ö	0560001695			
+	0560001738			
-	0560001740			
/	0560001743			
.	0560001749			
⏚	0560001745			

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C - to +80 °C

CLI R 02-3

Special characters

Technical specification

Conductor cross-section	0.5 mm² - 1.5 mm²
Cond. ext. Ø	1.0 mm - 3.0 mm
Length	3 mm

Ordering data

	blue		red	
Printing	MultiPack Qty.=10 Order No.	CD Qty.= Order No.	MultiPack Qty.=10 Order No.	CD Qty.= Order No.
+	0560001737		0560001739	
-	0560001741			
N	0560001746			

CLI R 1-3

0 - 9

Technical specification

Conductor cross-section	1.5 mm² - 4 mm²
Cond. ext. Ø	3.0 mm - 5.0 mm
Length	3 mm

	yellow		white	
Printing	MultiPack Qty.=10 Order No.	CD Qty.= Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
0	0572901503			
1	0572901506			
2	0572901509			
3	0572901512			
4	0572901515			
5	0572901518			
6	0572901521			
7	0572901524			
8	0572901527			
9	0572901530			

CLI R 1-3

A - Z

Technical specification

Conductor cross-section	1.5 mm² - 4 mm²
Cond. ext. Ø	3.0 mm - 5.0 mm
Length	3 mm

	yellow		white	
Printing	MultiPack Qty.=10 Order No.	CD Qty.= Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
A	0572901638			
B	0572901640			
C	0572901642			
D	0572901644			
E	0572901646			
F	0572901648			
G	0572901650			
H	0572901652			
I	0572901654			
J	0572901656			
K	0572901658			
L	0572901660			
M	0572901662			
N	0572901664			
O	0572901666			
P	0572901668			
Q	0572901670			
R	0572901672			
S	0572901675			
T	0572901678			
U	0572901680			
V	0572901682			
W	0572901684			
X	0572901693			
Y	0572901697			
Z	0572901699			

CableLine® - CLI R 1-3, 1-9, 1-12

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI R 1-3

Special characters

Technical specification

Conductor cross-section	1.5 mm² - 4 mm²
Cond. ext. Ø	3.0 mm - 5.0 mm
Length	3 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=10 Order No.	CD Qty.= Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
Ä	0572901696			
Å	0572901698			
Ö	0572901695			
+	0572901738			
-	0572901740			
/	0572901743			
.	0572901749			
⏚	0572901745			

CLI R 1-3

Special characters

Technical specification

Conductor cross-section	1.5 mm² - 4 mm²
Cond. ext. Ø	3.0 mm - 5.0 mm
Length	3 mm

	blue		red	
Printing	MultiPack Qty.=10 Order No.	CD Qty.= Order No.	MultiPack Qty.=10 Order No.	CD Qty.= Order No.
-	0572901741			
N	0572901746			
+			0572901739	

CLI R 1-9

Technical specification

Conductor cross-section	1.5 mm² - 4 mm²
Cond. ext. Ø	3.0 mm - 5.0 mm
Length	9 mm

Printing	Colour	Text colour	Qty.	Order No.
L1I	brown	white	10	1872761030
L2I	black	white	10	1872761031
L3I	white	black	10	1872761032
L1U	brown	white	10	1872761033
L2U	black	white	10	1872761034
L3U	white	black	10	1872761035
NJU	Blue	black	10	1872761036

CLI R 1-12

Technical specification

Conductor cross-section	1.5 mm² - 4 mm²
Cond. ext. Ø	3.0 mm - 5.0 mm
Length	12 mm

Printing	Colour	Text colour	Qty.	Order No.
L1JI	brown	black	10	1872751030
L2JI	black	black	10	1872751031
L3JI	white	black	10	1872751032
L1JI	Blue	black	10	1872751033
L2JI	Blue	black	10	1872751034
L3JI	Blue	black	10	1872751035

Open wire markers

CLI O wire markers are fitted to connected wires, which makes them suitable for updating existing facilities. Three different sizes are available to mark wire cross-sections from 0.4 mm^2 to maximum 4.0 mm^2. Profile and design guarantee the secure and permanent attachment of the individually combinable markers.

Advantages

- Open markers for connected wires
- Marker profile with anti-rotation safeguard for combination marking
- Perfect for all marking tasks of retrofitted wiring
- Extremely low space requirements
- Rapid clip-on attachment saves time

CLI O

Version	Open markers made from hard PVC. The flexible and sturdy barbed hooks guarantee secure attachment on the wire. Standard, special and international colour-code compliant prints available.
Material	Hard PVC, cadmium- and silicone-free
Temperature range	–30 °C to +80 °C.
Flammability classification	Corresponds to V0 to UL 94
Resistance	Highly resistant to oils and petrol as well as gamma and UV radiation
Printing	Laser marking

CableLine® - CLI O 10

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI O 10

0 - 9

Technical specification

Conductor cross-section	0.4 mm² - 1.5 mm²
Cond. ext. Ø	2.0 mm - 3.0 mm
Length	3 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.= Order No.	MultiPack Qty.=200 Order No.	CD Qty.= Order No.
0	0648001502		1872681502	
1	0648001505		1872681505	
2	0648001508		1872681508	
3	0648001511		1872681511	
4	0648001514		1872681514	
5	0648001517		1872681517	
6	0648001520		1872681520	
7	0648001523		1872681523	
8	0648001526		1872681526	
9	0648001529		1872681529	

CLI O 10

A - Z

Technical specification

Conductor cross-section	0.4 mm² - 1.5 mm²
Cond. ext. Ø	2.0 mm - 3.0 mm
Length	3 mm

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.= Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
A	0648001637			
B	0648001639			
C	0648001641			
D	0648001643			
E	0648001645			
F	0648001647			
G	0648001649			
H	0648001651			
I	0648001653			
J	0648001655			
K	0648001657			
L	0648001659			
M	0648001661			
N	0648001663			
O	0648001665			
P	0648001667			
Q	0648001669			
R	0648001671			
S	0648001673			
T	0648001676			
U	0648001679			
V	0648001681			
W	0648001683			
X	0648001687			
Y	0648001696			
Z	0648001698			

CLI O 10

Special characters

Technical specification

Conductor cross-section	0.4 mm² - 1.5 mm²
Cond. ext. Ø	2.0 mm - 3.0 mm
Length	3 mm

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.= Order No.	MultiPack Qty.=200 Order No.	CD Qty.= Order No.
Ä	0648001697			
Å	0648001699			
Ö	0648001695			
+	0648001738		1872681738	
-	0648001740		1872681740	
⏚	0648001746			

CLI O 10

Special characters

Technical specification

Conductor cross-section	0.4 mm² - 1.5 mm²
Cond. ext. Ø	2.0 mm - 3.0 mm
Length	3 mm

	blue		red	
Printing	MultiPack Qty.=200 Order No.	CD Qty.= Order No.	MultiPack Qty.=200 Order No.	CD Qty.= Order No.
-	0648001741			
+			0648001737	

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI O 20

0 - 9

Technical specification

Conductor cross-section	1.5 mm² - 2.5 mm²
Cond. ext. Ø	3.0 mm - 4.0 mm
Length	3 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.= Order No.	MultiPack Qty.=200 Order No.	CD Qty.= Order No.
0	0648101502		1872691502	
1	0648101505		1872691505	
2	0648101508		1872691508	
3	0648101511		1872691511	
4	0648101514		1872691514	
5	0648101517		1872691517	
6	0648101520		1872691520	
7	0648101523		1872691523	
8	0648101526		1872691526	
9	0648101529		1872691529	

CLI O 20

A - Z

Technical specification

Conductor cross-section	1.5 mm² - 2.5 mm²
Cond. ext. Ø	3.0 mm - 4.0 mm
Length	3 mm

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.= Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
A	0648101637			
B	0648101639			
C	0648101641			
D	0648101643			
E	0648101645			
F	0648101647			
G	0648101649			
H	0648101651			
I	0648101653			
J	0648101655			
K	0648101657			
L	0648101659			
M	0648101661			
N	0648101663			
O	0648101665			
P	0648101667			
Q	0648101669			
R	0648101671			
S	0648101673			
T	0648101676			
U	0648101679			
V	0648101681			
W	0648101683			
X	0648101687			
Y	0648101696			
Z	0648101698			

CLI O 20

Special characters

Technical specification

Conductor cross-section	1.5 mm² - 2.5 mm²
Cond. ext. Ø	3.0 mm - 4.0 mm
Length	3 mm

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.= Order No.	MultiPack Qty.=200 Order No.	CD Qty.= Order No.
Ä	0648101697			
Å	0648101699			
Ö	0648101695			
+	0648101738		1872691738	
-	0648101740		1872691740	
⏚	0648101746			

CLI O 20

Special characters

Technical specification

Conductor cross-section	1.5 mm² - 2.5 mm²
Cond. ext. Ø	3.0 mm - 4.0 mm
Length	3 mm

	blue		red	
Printing	MultiPack Qty.=200 Order No.	CD Qty.= Order No.	MultiPack Qty.=200 Order No.	CD Qty.= Order No.
-	0648101741			
+			0648101737	

CableLine® - CLI O 30

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI O 30

0 - 9

Technical specification

Conductor cross-section	2.5 mm² - 4 mm²
Cond. ext. Ø	4.0 mm - 5.0 mm
Length	3 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.= Order No.	MultiPack Qty.=200 Order No.	CD Qty.= Order No.
0	0648201502		1872701502	
1	0648201505		1872701505	
2	0648201508		1872701508	
3	0648201511		1872701511	
4	0648201514		1872701514	
5	0648201517		1872701517	
6	0648201520		1872701520	
7	0648201523		1872701523	
8	0648201526		1872701526	
9	0648201529		1872701529	

CLI O 30

A - Z

Technical specification

Conductor cross-section	2.5 mm² - 4 mm²
Cond. ext. Ø	4.0 mm - 5.0 mm
Length	3 mm

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.= Order No.	MultiPack Qty.= Order No.	CD Qty.= Order No.
A	0648201637			
B	0648201639			
C	0648201641			
D	0648201643			
E	0648201645			
F	0648201647			
G	0648201649			
H	0648201651			
I	0648201653			
J	0648201655			
K	0648201657			
L	0648201659			
M	0648201661			
N	0648201663			
O	0648201665			
P	0648201667			
Q	0648201669			
R	0648201671			
S	0648201673			
T	0648201676			
U	0648201679			
V	0648201681			
W	0648201683			
X	0648201687			
Y	0648201696			
Z	0648201698			

CLI O 30

Special characters

Technical specification

Conductor cross-section	2.5 mm² - 4 mm²
Cond. ext. Ø	4.0 mm - 5.0 mm
Length	3 mm

	yellow		white	
Printing	MultiPack Qty.=200 Order No.	CD Qty.= Order No.	MultiPack Qty.=200 Order No.	CD Qty.= Order No.
Ä	0648201697			
Å	0648201699			
Ö	0648201695			
+	0648201738		1872701738	
-	0648201740		1872701740	
⏚	0648201746			

CLI O 30

Special characters

Technical specification

Conductor cross-section	2.5 mm² - 4 mm²
Cond. ext. Ø	4.0 mm - 5.0 mm
Length	3 mm

	blue		red	
Printing	MultiPack Qty.=200 Order No.	CD Qty.= Order No.	MultiPack Qty.=200 Order No.	CD Qty.= Order No.
-	0648201741			
+			0648201737	

Cable markers and holders

CLI M identification markers are slid onto CLI MH carrier strips and secured by means of cable ties. CLI MH strips are available in two lengths. This system is particularly suitable for wires and cables with large cross-sections.

Advantages

- Combination markers for marking cables and conduits
- One size for all diameters from 16 mm²
- Unrestricted combination options
- Closed, captive marking
- Very good legibility

CLI MH

Version	CLI MH carrier strips for CLI M markers are available in lengths of 70 and 110 mm for 10 or 20 CLI M markers respectively. They are attached using one or two cable ties.
Material	PA 6.6
Temperature range	–30 °C to +80 °C
Flammability classification	V2 to UL 94
Resistance	Highly resistant to oils and petrol as well as gamma and UV radiation
Width of cable tie	Maximum 6.2 mm

CLI M

Version	Closed, oval combination markers. The markers are slid onto CLI MH holders and secured by means of cable ties. Standard, special and international colour-code compliant prints available.
Material	Soft PVC, cadmium- and silicone-free
Temperature range	–30 °C to +80 °C
Flammability classification	Corresponds to V0 to UL 94
Resistance	Highly resistant to oils and petrol as well as gamma and UV radiation
Printing	Laser marking

CableLine® - CLI M 2-4, 2-6

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI M 2-4

0 - 9

Technical specification

Conductor cross-section	16 mm² - 500 mm²
Cond. ext. Ø	10.0 mm - 317.0 mm
Length	4 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=500 Order No.	MultiPack Qty.=100 Order No.	CD Qty.=500 Order No.
0	1733651502	1568301502	1871371502	1568301000
1	1733651505	1568301505	1871371505	1568301697
2	1733651508	1568301508	1871371508	1568300002
3	1733651511	1568301511	1871371511	1568300003
4	1733651514	1568301514	1871371514	1568300004
5	1733651517	1568301517	1871371517	1568300005
6	1733651520	1568301520	1871371520	1568300006
7	1733651523	1568301523	1871371523	1568300007
8	1733651526	1568301526	1871371526	1568300008
9	1733651529	1568301529	1733651530	1568301530

CLI M 2-4

A - Z

Technical specification

Conductor cross-section	16 mm² - 500 mm²
Cond. ext. Ø	10.0 mm - 317.0 mm
Length	4 mm

	yellow		white	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=500 Order No.	MultiPack Qty.=100 Order No.	CD Qty.=500 Order No.
A	1733651637	1568301637	1871371637	1568301021
B	1733651639	1568301639	1871371639	1568301022
C	1733651641	1568301641	1871371641	1568301023
D	1733651643	1568301643	1871371643	1568301024
E	1733651645	1568301645	1871371645	1568301025
F	1733651647	1568301647	1871371647	1568301026
G	1733651649	1568301649	1871371649	1568301027
H	1733651651	1568301651	1871371651	1568301028
I	1733651653	1568301653	1871371653	1568301029
J	1733651655	1568301655	1871371655	1568301030
K	1733651657	1568301657	1871371657	1568301031
L	1733651659	1568301659	1871371659	1568301032
M	1733651661	1568301661	1871371661	1568301033
N	1733651663	1568301663	1871371663	1568301034
O	1733651665	1568301665	1871371665	1568301035
P	1733651667	1568301667	1871371667	1568301036
Q	1733651669	1568301669	1871371669	1568301037
R	1733651671	1568301671	1871371671	1568301038
S	1733651673	1568301673	1871371673	1568301039
T	1733651676	1568301676	1871371676	1568301040
U	1733651679	1568301679	1871371679	1568301041
V	1733651681	1568301681	1871371681	1568301042
W	1733651683	1568301683	1871371683	1568301043
X	1733651687	1568301687	1871371687	1568301044
Y	1733651696	1568301696	1871371696	1568301045
Z	1733651698	1568301698	1871371698	1568301046

Technical specification

Material	PVC, soft
UL 94 flammability rating	corresponds to V-0
Temperature range	-30 °C to +80 °C

CLI M 2-4

Special characters

Technical specification

Conductor cross-section	16 mm² - 500 mm²
Cond. ext. Ø	10.0 mm - 317.0 mm
Length	4 mm

Ordering data

	yellow		white	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=500 Order No.	MultiPack Qty.=100 Order No.	CD Qty.=500 Order No.
Ä	1733651697	1568301694	1871371697	1568301056
Å	1733651699	1568301699	1871371699	1568301055
Ö	1733651695	1568301695	1871371695	1568301057
+	1733651738	1568301738	1871371738	1568301048
-	1733651740	1568301740	1871371740	1568301049
/	1733651742	1568301742	1871371742	1568301050
.	1733651748	1568301748	1871371748	1568301047
:	1733651750	1568301750	1871371750	1568301054
=	1733651751	1568301751	1871371751	1568301052
~	1733651752	1568301752	1871371752	1568301059
⏚	1733651747	1568301747	1871371747	1568301058
⏚	1733651746	1568301746	1871371746	1568301053
Æ		1568301735		
Ø		1568301736		

CLI M 2-4

Special characters

Technical specification

Conductor cross-section	16 mm² - 500 mm²
Cond. ext. Ø	10.0 mm - 317.0 mm
Length	4 mm

	blue		red	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=500 Order No.	MultiPack Qty.=100 Order No.	CD Qty.=500 Order No.
-	1733651741	1568301741		
N	1733651664	1568301664		
+			1733651737	1568301737

CLI M 2-6

Special characters

Technical specification

Conductor cross-section	16 mm² - 500 mm²
Cond. ext. Ø	10.0 mm - 317.0 mm
Length	6 mm

	yellow		white	
Printing	MultiPack Qty.=100 Order No.	CD Qty.=250 Order No.	MultiPack Qty.=100 Order No.	CD Qty.=250 Order No.
L1	1871751728	1871781728	1871741728	1871771728
L2	1871751729	1871781729	1871741729	1871771729
L3	1871751730	1871781730	1871741730	1871771730

CableLine® - Accessories

The CLI MH fixing strip for CLI M markers is available in lengths of 70 and 100 mm for 10 or 20 CLI M 2-4. Hold in place with one or two cable ties.

Holder for CLI M markers

Technical specification

Material	Polyamide
Cond. cross-section	16 mm²

Ordering data

Type	Length	Material colour	Qty	Order No.
CLI MH 70	70 mm	black	100	**0524400000**
CLI MH 110	110 mm	black	100	**0189400000**

Steel cassette to accommodate
- 25 CDs with CLI C 02-3
- 21 CDs with CLI C 1-3
- 14 CDs with CLI C 2-4
- 11 CDs with CLI M 2-4

CLI CD-Box

Ordering data

Type	Qty	Order No.
CLI CD-Box	1	**1763290000**

CLI RH

Technical specification

Material	Polyamide

Ordering data

Type	Ordering data	Qty	Order No.
CLI RH 20-02	non-fitted	1	**0563700000**
CLI RH 20-1	non-fitted	1	**0563600000**



WSK 12

Ordering data

Type	Width	Ordering data	Qty	Order No.
WSK 12	250 mm	Empty	1	**0335900000**
WSK 12	250 mm	with 1000 CLI C 1-3, 0,9	1	**0336000000**

CLI RS

The CLI RS installation mandrels, which are made from metal, are ideal for assembling conductors.
- CLI RS 3 for CLI C 02
- CLI RS 4 for CLI C 1 (max. Ø 4.2 mm)
- CLI RS 5 for CLI C 1 (max. Ø 5 mm)

Technical specification

Material	steel

Ordering data

Type	Ordering data	Material colour	Qty	Order No.
CLI RS 3	non-fitted	silver	1	**0559200000**
CLI RS 4	non-fitted	silver	1	**0559300000**
CLI RS 5	non-fitted	silver	1	**0648300000**

CLI R

The CLI R installation mandrels are ideal for use with the CLI C for assembling conductors.
- CLI R 02 for CLI C 02-3
- CLI R 1 for CLI C 1-3

Technical specification

Material	POM

Ordering data

Type	Ordering data	Material colour	Qty	Order No.
CLI R 02 F. CLI C 02-3	non-fitted	red	20	**0559900000**
CLI R 1 F. CLI C 1-3	non-fitted	Blue	20	**0532100000**

CableLine® - Accessories

CLI R 02-3 as set with one each of installation mandrels 0-9, R, S, T; L, +, -, earth in yellow and neutral in grey.

CLI R 02-3

Ordering data

Type	Qty	Order No.
CLI R 02-3 SET	19	**0560001531**

CLI R 1-3 as set with one each of installation mandrels 0-9, R, S, T; L, +, -, earth in yellow, blank in grey.

CLI R 1-3

Ordering data

Type	Qty	Order No.
CLI R 1-3 SET	19	**0572901531**

Stainless steel markers

WSM is a complete marking system for cables, wires, conduits and components. It offers markings that last in conditions that no other markers can withstand. The range consists of stainless steel character tiles, holders and cable ties – available separately or complete in the WSM Set and Service Box.



Advantages

- Durable, embossed characters for optimum legibility
- Resistant to heat, cold, corrosion, acids, chemicals, fire and more
- Individual and multi-character markings can also be combined
- Rapid attachment
- Ideal for outdoor applications
- Easy attachment with cable ties

WSM

Version	Marker holders designed with raised profiles at both ends to ensure the cable ties slide through easily. Individual or combined, the single marker plates are inserted into the holder. Special printing available.
Material	Acid-resistant stainless steel grade SS 2348 (AISI-316)
Temperature range	–80 °C to +500 °C.
Resistance	Fireproof. Resistant to heat, cold, corrosion, acids, chemical substances, and so forth.
Printing	High-quality embossed. Alphanumeric and special characters
Fixing accessories	Stainless steel cable ties with ball-bearing lock

WSM stainless steel markers

- completely rustproof and acid-resistant
- embossed characters easily legible even after painting
- also available with special printing embossed on holder
- Contents of WSM Service Box: 40 each of 0-9, A-Ö, +, -, x, /, :, ., ~, =, ü, earth, neutral. 200 cable ties 200 mm. Stainless steel holders 30 pieces each of 48 mm and 60 mm, 20 pieces of 84 mm and 10 pieces of 108 mm and 288 mm.

WSM tiles

Technical specification

Material	Stainless steel 1.4404
Width	9.9 mm

Ordering data

Type	Printing	Length	Qty	Order No.
WSM 10		5.5 mm	200	**1712502000**
WSM 10 0	0	5.5 mm	200	**1712501000**
WSM 10 1	1	5.5 mm	200	**1712500001**
WSM 10 2	2	5.5 mm	200	**1712500002**
WSM 10 3	3	5.5 mm	200	**1712500003**
WSM 10 4	4	5.5 mm	200	**1712500004**
WSM 10 5	5	5.5 mm	200	**1712500005**
WSM 10 6	6	5.5 mm	200	**1712500006**
WSM 10 7	7	5.5 mm	200	**1712500007**
WSM 10 8	8	5.5 mm	200	**1712500008**
WSM 10 9	9	5.5 mm	200	**1712500009**
WSM 10 A	A	5.5 mm	200	**1712501637**
WSM 10 B	B	5.5 mm	200	**1712501639**
WSM 10 C	C	5.5 mm	200	**1712501641**
WSM 10 D	D	5.5 mm	200	**1712501643**
WSM 10 E	E	5.5 mm	200	**1712501645**
WSM 10 F	F	5.5 mm	200	**1712501647**
WSM 10 G	G	5.5 mm	200	**1712501649**
WSM 10 H	H	5.5 mm	200	**1712501651**
WSM 10 I	I	5.5 mm	200	**1712501653**
WSM 10 J	J	5.5 mm	200	**1712501655**
WSM 10 K	K	5.5 mm	200	**1712501657**
WSM 10 L	L	5.5 mm	200	**1712501659**
WSM 10 M	M	5.5 mm	200	**1712501661**
WSM 10 N	N	5.5 mm	200	**1712501663**
WSM 10 O	O	5.5 mm	200	**1712501665**
WSM 10 P	P	5.5 mm	200	**1712501667**
WSM 10 Q	Q	5.5 mm	200	**1712501669**
WSM 10 R	R	5.5 mm	200	**1712501671**
WSM 10 S	S	5.5 mm	200	**1712501673**
WSM 10 T	T	5.5 mm	200	**1712501676**
WSM 10 U	U	5.5 mm	200	**1712501679**
WSM 10 V	V	5.5 mm	200	**1712501681**
WSM 10 W	W	5.5 mm	200	**1712501683**
WSM 10 X	X	5.5 mm	200	**1712501687**
WSM 10 Y	Y	5.5 mm	200	**1712501696**
WSM 10 Z	Z	5.5 mm	200	**1712501698**
WSM 10 Ä	Ä	5.5 mm	200	**1712501054**
WSM 10 Å	Å	5.5 mm	200	**1712501700**
WSM 10 Ö	Ö	5.5 mm	200	**1712501055**
WSM 10 Ü	Ü	5.5 mm	200	**1712501699**
WSM 10 Æ	Æ	5.5 mm	200	**1712501672**
WSM 10 Ø	Ø	5.5 mm	200	**1712501670**
WSM 10 ⏚	⏚	5.5 mm	200	**1712501053**
WSM 10 +	+	5.5 mm	200	**1712501738**
WSM 10 -	-	5.5 mm	200	**1712501740**
WSM 10 /	/	5.5 mm	200	**1712501739**
WSM 10 :	:	5.5 mm	200	**1712501741**
WSM 10 =	=	5.5 mm	200	**1712501742**
WSM 10 .	.	5.5 mm	200	**1712501743**
WSM 10 ~	~	5.5 mm	200	**1712501056**
WSM 10 (	(	5.5 mm	200	**1712501744**
WSM Service Box	see text above		1	**1924930000**

WSM holder

Technical specification

Material	Stainless steel 1.4404
Width	11 mm

Ordering data

Type	character	Length	Qty	Order No.
WSMH 48mm	6	47 mm	50	**1774500000**
WSMH 60mm	8	65 mm	50	**1774510000**
WSMH 84mm	12	87 mm	50	**1774520000**
WSMH 108mm	16	109 mm	50	**1774530000**
WSMH 288mm	46	288 mm	50	**1774490000**

WSM holder, Custom printing

Technical specification

Material	Stainless steel 1.4404
Width	10 mm

Type	character	Length	Qty	Order No.
WSMC 1-5	1-5	53.5 mm	1	**1912170000**
WSMC 6-10	6-10	74 mm	1	**1891680000**
WSMC 11-15	11-15	93 mm	1	**1891670000**
WSMC 16-20	16-20	112 mm	1	**1912140000**
WSMC 21-25	21-25	131 mm	1	**1912150000**
WSMC 26-30	26-30	150 mm	1	**1912160000**

WeidSteel contains a comprehensive assortment of steel cable ties for extreme conditions such as high temperatures or severe chemical effects.

- Stainless steel to DIN AISI 304,
- patented closure enables easy, secure installation,
- patented rounded edges eliminate the risk of injury,
- ideal for use outdoors,
- radiation- and corrosion-resistant,
- anti-magnetic,
- no serrations, so no damage to the insulation.

WSM accessory - cable ties

Technical specification

Material	Stainless steel 1.4301

Ordering data

Type	Width	Length	Qty	Order No.
SCT 4.6/127	4.6 mm	127 mm	100	**1699800000**
SCT 4.6/201	4.6 mm	201 mm	100	**1699810000**
SCT 4.6/266	4.6 mm	266 mm	100	**1699900000**
SCT 4.6/360	4.6 mm	360 mm	100	**1699910000**
SCT 4.6/520	4.6 mm	520 mm	100	**1699920000**
SCT 4.6/679	4.6 mm	679 mm	100	**1699930000**
SCT 4.6/838	4.6 mm	838 mm	100	**1699940000**

The WSM Tool is a tool for tightening steel cable ties. Two different versions are available: the automatic version allows you to tighten the cable tie and cut off the surplus end in one operation; the manual version is used exclusively for tying steel cable ties, afterwards the tie can be cut back by twisting it through 90°.

WSM accessory - tool

Technical specification

Material	metal

Ordering data

Type	Weight	Length	Qty	Order No.
WSM TOOL AUTOMATIC	600 g	180 mm	1	**1774470000**
WSM TOOL MANUAL	500 g	210 mm	1	**1774480000**

Steel cable tie - SCT

- Fully coated stainless steel cable ties
- Efficient rollerball locking device for fast and easy installation
- It can be tightened by hand or by tool
- These ties are recommended against enviroment conditions and corrosion like salt spray weathering, strength or extreme temperatures

Steel coated

Technical specification

Material	Stainless steel
Temperature, min.	-80 °C
Temperature, max.	150 °C

Ordering data

Type	Length	Width	Group Ø mm	Qty	Order No.
SCT-C 4.6/100	100 mm	4.6 mm	21 mm	100	**1015220000**
SCT-C 4.6/125	125 mm	4.6 mm	27 mm	100	**1015230000**
SCT-C 4.6/150	150 mm	4.6 mm	35 mm	100	**1015240000**
SCT-C 4.6/200	200 mm	4.6 mm	50 mm	100	**1015250000**
SCT-C 4.6/360	360 mm	4.6 mm	100 mm	100	**1015270000**
SCT-C 4.6/520	520 mm	4.6 mm	150 mm	100	**1015280000**
SCT-C 4.6/680	680 mm	4.6 mm	200 mm	100	**1015290000**
SCT-C 4.6/840	840 mm	4.6 mm	250 mm	100	**1015300000**
SCT-C 7.9/200	200 mm	7.9 mm	50 mm	100	**1015310000**
SCT-C 7.9/360	360 mm	7.9 mm	100 mm	100	**1015320000**
SCT-C 7.9/520	520 mm	7.9 mm	150 mm	100	**1015330000**
SCT-C 7.9/680	680 mm	7.9 mm	200 mm	100	**1015340000**
SCT-C 7.9/840	840 mm	7.9 mm	250 mm	100	**1015350000**

CB cable ties provide fixings for cables and markers for special requirements. They are especially suitable for fixing CLI M, SFX, WKM and WKS cable markers. The material consists of unbreakable polyamide PA 6.6 with UL94 flammability rating V2.

Cable ties

Technical specification

Material:	Polyamide
Flammability class:	V2 acc. to UL 94
Colour:	natural and black

Temperature rage:

- Continuous operating temperature: (after assembly) –40 °C to +85 °C
- Installation temperature: (during assembly) –10 °C to +60 °C
- Short-term up to: +110 °C
- Melting point: +256 °C

Oxygen index (LOI): 27%

Approval according to EN 50 146
Halogen-free

Resistance to chemicals:

- Excellent resistance to alkalis, oils, grease, oil products, chlorate solvents
- Limited resistance to all acids
- No resistance to phenols

Approvals:

Ordering data

Type	Dimensions (LxW) mm	Qty.	Min. (mm) bundle-Ø	Max. (mm) bundle-Ø	Min. Tensile strength in N	Order No. natural	Order No. black
CB 98/2.5	98 x 2.5	100	1	21	80	**1278600000**	**1697890000**
CB 120/4.5	120 x 4.5	100	2,5	24	220	**7940006052**	**7940006053**
CB 120/7.8	120 x 7.8	100	3,5	24	540	**7940006062**	**7940006063**
CB 135/2.5	135 x 2.5	100	1	32	80	**7940006040**	**7940006047**
CB 140/3.6	140 x 3.6	100	2	35	130	**1278700000**	**1697900000**
CB 160/4.5	160 x 4.5	100	2,5	40	220	**1723540000**	**1723560000**
CB 160/2.6	160 x 2.6	100	1	40	80	**7940006048**	**7940006049**
CB 178/4.8	178 x 4.8	100	2	45	220	**1723550000**	**1723570000**
CB 200/4.8	200 x 4.8	100	3	50	220	**1278800000**	**1697910000**
CB 200/2.6	200 x 2.6	100	1	50	80	**7940006050**	**7940006051**
CB 200/3.6	200 x 3.6	100	2	50	130	**1720630000**	**1720660000**
CB 180/7.8	180 x 7.8	100	3,5	45	540	**7940006064**	**7940006065**
CB 225/12.5	225 x 12.5	100	7,5	57	1080	**7940006076**	**7940006077**
CB 240/7.8	240 x 7.8	100	3,5	63	540	**7940006066**	**7940006067**
CB 250/4.8	250 x 4.8	100	3	68	220	**7940006054**	**7940006055**
CB 290/3.6	290 x 3.6	100	2	80	130	**1720640000**	**1720650000**
CB 290/4.8	290 x 4.8	100	3,5	80	220	**1278900000**	**1697920000**
CB 300/7.8	300 x 7.8	100	4	80	540	**7940006068**	**7940006069**
CB 370/3.6	370 x 3.6	100	2	103	130	**7940006056**	**7940006057**
CB 360/4.8	360 x 4.8	100	3,5	103	220	**1279000000**	**1697930000**
CB 365/7.8	365 x 7.8	100	8	100	540	**1279100000**	**1697940000**
CB 390/4.8	390 x 4.8	100	3,5	106	220	**7940006058**	**7940006059**
CB 430/4.8	430 x 4.8	100	3,5	115	220	**7940006060**	**7940006061**
CB 450/7.8	450 x 7.8	100	35	130	540	**7940006070**	**7940006071**
CB 500/12.5	500 x 12,5	100	30	143	1080	**7940006078**	**7940006079**
CB 540/7.8	540 x 7,8	100	35	158	540	**7940006072**	**7940006073**
CB 750/7.8	750 x 7,8	100	35	220	540	**1720680000**	**1720670000**
CB 780/9.0	780 x 9,0	100	32	233	700	**7940006074**	**7940006075**
CB 850/12.5	850 x 12,5	100	40	255	1080	**7940006082**	
CB 1000/12.5	1000 x 12,5	100	40	302	1080	**7940006084**	**7940006085**



Plastic cable ties

Accessories - holders

CBDM	Cable tie direct mounting for cable harness max. Ø 50 mm,total length: 200 mm
CBH 8.1/6.2	Cable tie retainer for use on mounting plate Max. plate thickness 3.2 mm, hole Ø max. 6.2 mm
CBH 19/19	Cable tie retainer for sticking on, surface: 19 x 19 mm
CBH 27/27	Cable tie retainer for sticking on, surface: 27 x 27 mm
CB-R	Releasable cable ties

Ordering data

Type	Dimensions (LxW) mm	Qty.	Min. (mm) bundle-Ø	Max. (mm) bundle-Ø	Min. Tensile strength in N	Order No. natural	Order No. black
CB-R 200/7.5	200 x 7.5mm	100	6	50	220	**1059200000**	**1059210000**
CB-R 250/7.5	250 x 7.5mm	100	6	65	220	**1059220000**	**1059230000**
CB-R 350/7.5	350 x 7.5mm	100	6	100	220	**1059240000**	**1059250000**
CBH 8.1/6.2	8.1 x 6.2	100				**1279200000**	
CBH 19/19	19 x 19	100				**1289200000**	**1697950000**
CBH 27/27	27 x 27	100				**1289400000**	**1697960000**
CBDM 200/4.5	200 x 4.5	100	50	220		**1279300000**	



The RT 1 is a compact, pistol-shaped tool for fastening and cutting cable-ties in one operation.
The tension is widely adjustable, ranging from short to standard cable-ties.
The RT 1 is designed for bundles with a diameter of 1.6 mm to 100 m

Accessories - tools

Ordering data

Type	Length	Weight	Qty	Order No.
RT 1	160 mm	260 g	1	**1296000000**

Device markers

Device markers

Introduction	D.2
DMC	D.3
ESG - tags	D.4
SwitchMark SM	D.6
ClipCard CC	D.8
LogiMark	D.10
Blank labels	D.11
Printed labels	D.14

Markers for devices and installations

Device and installation markers round off the range of switchgear markers. By utilising Weidmüller's device markers, users comply with official regulations requiring marking of electrical equipment. Weidmüller offers corresponding markers for devices made by well-known manufactures. Mirroring their original counterparts, these tags are attached with the traditional adhesive or rapid clip-on techniques. By utilising the corresponding software and system-compatible printer or plotter system, users can print their own markings on these markers.

Weidmüller also offers ready-to-use printed labels in the form of a Symbol Packs or Service Packs.

A samples bag containing a selection of device and installation markers is available under the order no. **1646370000**.



	DMC	ESG	SwitchMark	ClipCard	Labels
	DMC	ESG	SwitchMark	ClipCard	Labels
Cable ducts				●	●
Automatic switchgear	●	●	●	●	●
Contactors	●	●	●		●
Electrical connections	●			●	●
Electrical devices	●			●	●
Machines					●
LED displays			●		
Keyboards			●	●	●
Lamps					
Murr valve plug		●			
Tubes				●	●
Circuit-breakers	●	●			●
Relays	●	●			●
Shelves					●
Switches		●	●	●	●
Control desk		●	●	●	●
Transformers	●	●			●
Valves				●	●

The DMC markers are used for labelling switching devices or components. The marking surface (12 x 27 mm) is large enough to hold information about the device and its function. The markers are fastened to a wire or cable by means of a simple clip-on mechanism. A DMC marker can be fastened to conductors in the cross-section range of 0.5 – 10 mm². In combination with MultiCards, markers can be printed using a plotter, PrintJet, SMark printer or MC Mobilo.

DMC 12/27

A single tag size for cable cross-sections from 0.5–10 mm² means they are equally suitable for use on multi-core control lines as well as single core cables.

The large marking surface provides ample space for supplementary information

Technical data

Material	Polyamide PA 66, halogen-free
Temperature range	–40 °C… +100 °C
UL94 flammability rating	V2
Marking surface	12 x 27 mm
Suitable for cable diameters	1.5 – 7.5 mm
And conductor cross-sections	0.5 – 10 mm²

Ordering data

Type	Colour	Qty.	Order No.
DMC 12/27 MC NE WS	white	50	**1016030000**
DMC 12/27 MC NE GE	yellow	50	**1018190000**
Custom printing			
DMC 12/27 SDR	white	10	**1038830000**

ESG - tags

ESG is the well-established marker in MultiCard format for many well-known devices. This is a high-quality device marker with a high-contrast appearance.
- For devices from ABB, Siemens, Moeller and Télémécanique.
- For universal use - available in self-adhesive and clip-on forms.
- Ideal for clipping to tag rails for marking rows of circuit-breakers or other equipment.
- Please do not use self-adhesive Multicard markers together with the SMark.

ESG - blank

Technical specification

UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C
Material	Polyamide 66

Ordering data

Type	Application	Width/Length	Qty	Order No.
ESG 5/10 MC white	Turck/Beckhoff SAI distributo	10 mm/5 mm	400	**1919940000**
ESG 6/15 K MC yellow	self-adhesive	15 mm/6 mm	200	**1880130000**
ESG 6/15 MC Riders. white	Riderserie SCM/SRC	15 mm/6 mm	200	**1881280000**
ESG 6/15 K MC white	self-adhesive	15 mm/6 mm	200	**1880100000**
ESG 6/15 F MC NE WS	Festo	15 mm/6 mm	200	**1136810000**
ESG 6/17 K MC yellow	self-adhesive	17 mm/6 mm	200	**1880110000**
ESG 6/17 K MC white	self-adhesive	17 mm/6 mm	200	**1880120000**
ESG 7/20 Sirius white	Siemens Sirius 3R/SCHS 3 u. 4	20 mm/7 mm	200	**1736181044**
ESG 7/20 Sirius yellow	Siemens Sirius 3R/SCHS 3 u. 4	20 mm/7 mm	200	**1736181687**
ESG 7/20 Sirius turquoise	Siemens Sirius 3R/SCHS 3 u. 4	20 mm/7 mm	200	**1736181696**
ESG 8/10 MC ASI white	Siemens AS interface	10 mm/8 mm	200	**1736190000**
ESG 8/11	BECKOFF/WAGO I/O MODULES	11 mm/8 mm	200	**1897570000**
ESG 8/13.5/43.3	WI SAI AKTIV UNIVERSAL	13.5 /43.3 mm/8 mm	5	**1912130000**
ESG 8/17 MC white	Télémécanique	17 mm/8 mm	200	**1674740000**
ESG 8/17 SCHS MC white	SCHS2	17 mm/8 mm	200	**1720610000**
ESG 8/17 Sys Pro M white	AEG/ABB-Stotz	17 mm/8 mm	200	**1755340000**
ESG 8/17 L MC white	Lumberg distributor	17 mm/8 mm	200	**1890470000**
ESG 8/19 MC white	AEG	19 mm/8 mm	200	**1652220000**
ESG-M 8/20 MC NE WS	Murr Cube67 & MVK MP	20 mm/8 mm	200	**1027290000**
ESG 9/6 MC white	WI SAI-Active series	6 mm/9 mm	400	**1888360000**
ESG 9/11K MC white	self-adhesive	11 mm/9 mm	200	**1857440000**
ESG 9/17 MC white	CLI TM sleeve	17 mm/9 mm	200	**1724760000**
ESG 9/17 K white	self-adhesive	17 mm/9 mm	200	**1674760000**
ESG 9/17 K yellow	self-adhesive	17 mm/9 mm	200	**1753500000**
ESG-M 9/17 MC NE WS	Murr MVP modules	17 mm/9 mm	200	**1027280000**
ESG 9/20 MC Universal white	Murr distr.+Festo CPV/CPI	20 mm/9 mm	200	**1856720000**
ESG 9/20 MC white w/o foot	TMC sleeve	20 mm/9 mm	200	**1770500000**
ESG 9/20 L MC white	Lumberg distributor	20 mm/9 mm	200	**1890460000**
ESG 9/20 L MC yellow	Lumberg distributor	20 mm/9 mm	200	**1010860000**
ESG 9/20 MC white	Siemens+Möller+WI SAI distributor	20 mm/9 mm	200	**1609940000**
ESG 9/20 MC yellow	Siemens+Möller+WI SAI distributor	20 mm/9 mm	200	**1766160000**
ESG 9/20 MC turquoise	Siemens+Möller+WI SAI distributor	20 mm/9 mm	200	**1866690000**
ESG 10/17 MC white	Allen Bradley/Festo MT	17 mm/10 mm	200	**1856700000**
ESG B&R X20 MC red	B&R X20 System	5 / 10 mm/2.5 mm	1120	**1001170001**
ESG B&R X20 MC orange	B&R X20 System	5 / 10 mm/2.5 mm	1120	**1001160001**
ESG B&R X20 MC white	B&R X20 System	5 / 10 mm/2.5 mm	1120	**1001140001**
ESG B&R X20 MC blue	B&R X20 System	5 / 10 mm/2.5 mm	1120	**1001150001**
ESG X20 10/7 MC red	B&R X20 System	7 mm/10 mm	240	**1026570000**
ESG X20 10/7 MC orange	B&R X20 System	7 mm/10 mm	240	**1026580000**
ESG X20 10/7 MC white	B&R X20 System	7 mm/10 mm	240	**1026550000**
ESG X20 10/7 MC blue	B&R X20 System	7 mm/10 mm	240	**1026560000**

ESG - Custom printing

Type	Width/Length	Qty	Order No.
ESG 5/10 MC	5 mm/10 mm	80	**1038840000**
ESG 6/15 K MC	15 mm/6 mm	40	**1880090000**
ESG 6/15 Riders.	15 mm/6 mm	40	**1881290000**
ESG 6/17 K MC	17 mm/6 mm	40	**1880080000**
ESG 8/11 MC	11 mm/8 mm	40	**1038850000**
ESG 8/13.5/43.3 SAI	13.5 /43.3 mm/8 mm	1	**1038860000**
ESG 8/17 Sys Pro M MC	17 mm/8 mm	40	**1755350000**
ESG 8/17 MC	17 mm/8 mm	40	**1674750000**
ESG 8/17 SCHS MC	17 mm/8 mm	40	**1766640000**
ESG 8/17 L MC	17 mm/8 mm	40	**1038870000**
ESG 8/19 MC	19 mm/8 mm	40	**1652230000**
ESG-M 8/20 MC	20 mm/8 mm	40	**1038910000**
ESG 9/11 K MC	11 mm/9 mm	40	**1857450000**
ESG 9/17 MC	17 mm/9 mm	40	**1770480000**
ESG 9/17 K MC	17 mm/9 mm	40	**1674770000**
ESG-M 9/17 MC	17 mm/9 mm	40	**1038920000**
ESG 9/20 Universal MC	20 mm/9 mm	40	**1856730000**
ESG 9/20 o. Foot MC	20 mm/9 mm	40	**1770510000**
ESG 9/20 MC	20 mm/9 mm	40	**1609950000**
ESG 10/17 MC	17 mm/10 mm	40	**1856710000**
ESG B&R X20 MC	5 /10 mm/2.5 mm	224	**1038890000**
ESG X20 10/7 MC	7 mm/10 mm	48	**1038930000**

ESG - accessory - tag carrier rail

Ordering data

Type	Application	Width/Length	Qty	Order No.
SCHS 1 black	ESO/protection strip	17 mm/1000 mm	1	**0138900000**
SCHS 2 self-adhesive black	ESG 8/17 SCH ; DEK ; WS	8 mm/1000 mm	1	**1720600000**
SCHS 2 black	ESG 8/17 SCH ; DEK ; WS	8 mm/1000 mm	1	**0337400000**
SCHS 3 self-adhesive black	ESG 7/20	10 mm/1000 mm	1	**1753480000**
SCHS 4 self-adhesive grey	ESG 7/20	10 mm/1000 mm	1	**1753460000**
STR SCHS 1 transparent		12.5 mm/500 mm	1	**0139200000**
ESO SCHS 1 white		12.5 mm/500 mm	1	**0139000000**

SwitchMark SM



SM is a marker system for control and signalling devices. The tags clip into the holder or are fixed with the adhesive tape already attached. Individual tags can be created with the SMark-Laser, PrintJet, Plotter or MC-Mobilo marking systems.

- Produce your own markers quickly and suit your needs.
- No need to keep stocks of expensive standard tags.
- Hardwearing printing quality with the PrintJet as a substitute or engraving.
- We recommend the ETO SM protective film for extreme applications.
- Holders can be used for the Ø 22 mm push-buttons from Siemens, ABB, Moeller and Télémécanique.

SM - blank

Technical specification

Material	Polyamide 66, halogen-free
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C

Ordering data

Type	Length (mm)	Qty.	Order No.				
			white	silver	grey	red	yellow
SM 27/8 MC	8	80	**1699820000**	**1713680000**	**1079470000**		**1131870000**
SM 27/12.5 MC	12.5	80	**1699840000**	**1713700000**	**1079490000**		**1131860000**
SM 27/18 MC	18	80	**1699860000**	**1713740000**	**1014640000**	**1906110000**	**1131850000**
SM 27/27 MC	27	60	**1773220000**	**1773230000**	**1079510000**		**1131840000**

SM - blank - self-adhesive

Technical specification

Material	Polyamide 66, halogen-free
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C

Ordering data

Type	Length (mm)	Qty.	Order No.				
			white	silver	grey	red	yellow
SM 22/22 K MC	22	80	**1877570000**	**1877590000**	**1014650000**		**1131830000**
SM 27/8 K MC	8	80	**1812630000**	**1771930000**	**1079480000**		**1131820000**
SM 27/12.5 K MC	12.5	80	**1699880000**	**1713720000**	**1027830000**		**1131810000**
SM 27/18 K MC	18	80	**1707270000**	**1713760000**	**1073340000**	**1906120000**	**1915340000**
SM 27/27 K MC	27	60	**1783000000**	**1782990000**	**1079520000**		**1131800000**

SM - Custom printing

Ordering data

Type	Length (mm)	Qty.	Order No.	
			Colour and print details	
SM 27/8	8	80	**1699830000**	
SM 27/8 K	8	80	**1713690000**	
SM 27/12.5	12.5	80	**1699850000**	
SM 27/12.5 K	12.5	80	**1699890000**	
SM 27/18	18	80	**1699870000**	
SM 27/18 K	18	80	**1707280000**	
SM 22/22 K	22	80	**1877580000**	
SM 27/27	27	60	**1773240000**	
SM 27/27 K	27	60	**1783010000**	

SM is a marker system for control and signalling devices. The tags clip into the holder or are fixed with the adhesive tape already attached. Individual tags can be created with the SMark-Laser, PrintJet, Plotter or MC-Mobilo marking systems.

- Produce your own markers quickly and suit your needs.
- No need to keep stocks of expensive standard tags.
- Hardwearing printing quality with the PrintJet as a substitute or engraving.
- We recommend the ETO SM protective film for extreme applications.
- Holders can be used for the Ø 22 mm push-buttons from Siemens, ABB, Moeller and Télémécanique.

SM - accessory - holder

Technical specification

Material	Polyamide 66, halogen-free
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C
Colour	black

Ordering data

Type	Length	width	Qty.	Order No.
SM-H 27/12.5	42 mm	27 mm	25	**1716640000**
SM-H 27/18	48 mm	27 mm	25	**1716630000**
SM-H 27/27	59 mm	27 mm	10	**1782710000**

SM - accessory - protective film

Technical specification

Material	Polyester film
UL 94 flammability rating	HB
Min. temperature, continuous	-20 °C
Max. temperature, continuous	80 °C
Colour	transparent

Ordering data

Type	Length	width	Labels per sheet	Qty.	Order No.
ETO SM 27/8	8 mm	27 mm	165	1	**1720570000**
ETO SM 27/12.5	12.5 mm	27 mm	100	1	**1720580000**
ETO SM 27/18	18 mm	27 mm	112	1	**1720590002**
ETO SM 22/22	22 mm	22 mm	117	1	**1880720000**
ETO SM 27/27	27 mm	27 mm	70	1	**1805840000**

ClipCard CC

The ClipCard device markers in MultiCard format represent an alternative to engraving. The range is used to identify electrical installations and switchgear. Thanks to the established MultiCard format, labelling with SMark-Laser, PrintJet, Plotter and MC-Mobilo is possible.

- Hardwearing printing quality with the PrintJet as a substitute for engraving
- Universal fixing
- Holder (fixed with screws or cable ties)
- Tag rail (self-adhesive or screwed)
- Self-adhesive tags

Technical data

Material	Polyamide 66, halogen-free
Flammability classification toUL94	V2
Temperature range °C	–40 … 100
Temperature range °C	–40 … 60 (self-adhesive)
Approved air humidity	Max. 60 %, only for screwable tags

ClipCard, blank



Ordering data

Type	Width x Length (mm)	Qty.	Order No. white	silver	grey	red	yellow
CC 15/17 MC	15 x 17	80	1876570000	1876610000	1079530000		1131930000
CC 15/27 MC	15 x 27	80	1876770000	1876760000	1079550000		1131940000
CC 15/49 MC	15 x 49	40	1877260000	1877240000	1079570000		1076970000
CC 15/60 MC	15 x 60	40	1877350000	1877340000	1072640000		1131960000
CC 30/60 MC	30 x 60	30	1934420000	1934400000	1072670000		1009320000
CC 85/54 MC n	54 x 85	10	1138400000		1138420000		1138410000

ClipCard, blank, self-adhesive

Ordering data

Type	Width x Length (mm)	Qty.	Order No. white	silver	grey	red	yellow
CC 15/17 K MC	15 x 17	80	1876590000	1876580000	1079540000		1131920000
CC 15/27 K MC	15 x 27	80	1876640000	1876780000	1079560000		1131910000
CC 15/49 K MC	15 x 49	40	1877220000	1877270000	1079580000		1131970000
CC 15/60 K MC	15 x 60	40	1877310000	1877360000	1072650000		1131890000
CC 30/60 K MC	30 x 60	30	1934390000	1934330000	1072680000	1085430000	1078320000
CC 85/54 K MC n	54 x 85	10	1138430000		1138450000		1138440000

Special print

Ordering data

Type	Width x Length (mm)	Qty.	Order No. Colour and print details
CC 15/17 MC	15 x 17	16	1876600000
CC 15/17 K MC	15 x 17	16	1876620000
CC 15/27 MC	15 x 27	16	1876750000
CC 15/27 K MC	15 x 27	16	1876630000
CC 15/49 MC	15 x 49	8	1877230000
CC 15/49 K MC	15 x 49	8	1877200000
CC 15/60 MC	15 x 60	8	1877320000
CC 15/60 K MC	15 x 60	8	1877300000
CC 30/60 MC	30 x 60	6	1934370000
CC 30/60 K MC	30 x 60	6	1934410000
CC 85/54 MC n	54 x 85	2	1138460000
CC 85/54 K MC n	54 x 85	2	1138470000

ClipCard, with hole, blank

Ordering data

Type	Width x Length (mm)	Qty.	Order No. white	silver	grey	yellow
CC 15/60 O4MM MC	15 x 60	40	1057580000	1059990000		1131880000
CC 30/60 O4MM MC	30 x 60	30	1083150000		1083170000	1083160000

ClipCard, with hole, special print

Ordering data

Type	Width x Length (mm)	Qty.	Order No. Colour and print details
CC 15/60 O4MM MC	15 x 60	8	1060010000
CC 30/60 O4MM MC	30 x 60	6	1083190000

Holder

Ordering data

Type	Qty.	Order No. black
CC-H 15/17	75	1790430000
CC-H 15/27	45	1790410000
CC-H 15/49	25	1790420000
CC-H 15/60	25	1878910000
CC-H 30/60	10	1934430000

Protective sleeve for holder

Ordering data

Type	Qty.	Order No. transparent
STR CC 15/17	80	1888310000
STR CC 15/27	80	1888290000
STR CC 15/49	40	1888300000
STR CC 15/60	40	1888280000
STR CC 30/60	10	1934450000

Protective foil

Ordering data

Type	Labels per sheet	Qty.	Order No. transparent
ETO CC 15/17	228	1	1880850000
ETO CC 15/27	133	1	1880810000
ETO CC 15/49	76	1	1880830000
ETO CC 15/60	57	1	1880840000
ETO CC 30/60	27	10	1934440000

Tag rail

Ordering data

	Qty.	Order No. black	transparent
CC-Rail 1000	1	1790150000	
CC-Rail 1000 transparent	1		1790160000

LogiMark

LogiMark is a marker that is used for identifying a wide range of electrical installations and switchgears. Numerous diverse fixing arrangements are possible due to the fixing in a holder, with cable tie or screw, and attaching a self-adhesive LogiMark-Card. Users can label the cards individually using highly resistant thermal transfer or plotter printing.

- high-contrast thermal transfer printing,
- cheque-card or 1/2-card format.

LogiMark - blank

Technical specification

Material	Polyamide 66
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C

Ordering data

Type	Length	Width	Material colour	Qty	Order No.
LogiMark 1/2 Wh	85.4 mm	27 mm	white	200	**1675111044**
LogiMark 1/2 GE	85.4 mm	27 mm	yellow	200	**1675111687**
LogiMark 1/2 BL	85.4 mm	27 mm	Blue	200	**1675111693**
LogiMark 1/2 RT	85.4 mm	27 mm	red	200	**1675111686**
LogiMark 1/2 GN	85.4 mm	27 mm	green	200	**1675111688**
LogiMark 1/2 VI	85.4 mm	27 mm	magenta	200	**1675111689**
LogiMark 1/2 OR	85.4 mm	27 mm	Orange	200	**1675111690**
LogiMark 1/2 GR	85.4 mm	27 mm	grey	200	**1675111691**
LogiMark 1/2 BR	85.4 mm	27 mm	brown	200	**1675111692**
LogiMark WS	85.4 mm	54 mm	white	100	**1607681044**
LogiMark GE	85.4 mm	54 mm	yellow	100	**1607681687**
LogiMark BL	85.4 mm	54 mm	Blue	100	**1607681693**
LogiMark RT	85.4 mm	54 mm	red	100	**1607681686**
LogiMark BR	85.4 mm	54 mm	brown	100	**1607681692**
LogiMark GN	85.4 mm	54 mm	green	100	**1607681688**
LogiMark GR	85.4 mm	54 mm	grey	100	**1607681691**
LogiMark OR	85.4 mm	54 mm	Orange	100	**1607681690**
LogiMark VI	85.4 mm	54 mm	magenta	100	**1607681689**

LogiMark - Custom printing

Type	Length	Width	Qty	Order No.
Logimark 1/2	85.4 mm	27 mm	2	**1675120000**
Logimark	85.4 mm	54 mm	1	**1607690000**

LogiMark - accessory - holder

Technical specification

Material	Polyamide 66
UL 94 flammability rating	V2
Min. temperature, continuous	-40 °C
Max. temperature, continuous	100 °C

Type	Length	Width	Material colour	Qty	Order No.
LogiMark holder ES 1/2	90 mm	31 mm	grey	40	**1675130002**
LogiMark holder ES 1/2	90 mm	31 mm	black	40	**1675130001**
LogiMark holder ES	90 mm	58 mm	beige	20	**1631640003**
LogiMark holder ES	90 mm	58 mm	grey	20	**1631640002**
LogiMark holder ES	90 mm	58 mm	black	20	**1631640001**
LogiMark holder	90 mm	58 mm	black	20	**1603290000**

LogiMark - for self-adhesive

Type	Length	Width	Qty	Order No.
LogiMark DKB 1/2	81 mm	23 mm	20	**1755100000**
LogiMark DKB	81 mm	50 mm	10	**1755110000**

LM MT 300

- self-adhesive polyester labels
- suitable for A4 laser printer,
- abrasion-resistant
- high heat resistance
- for marking all kinds of switchgear and equipment,
- can also be written on with a ballpoint pen of the STI marking pen

Technical specification

Material	Polyester, PVC-free
UL 94 flammability rating	HB
Min. temperature, continuous	-45 °C
Max. temperature, continuous	150 °C

Ordering data

Type	Length	No. per pcs	Qty.	Order No. white	Order No. yellow	Order No. silver
LM 12x6	12	322	10		**1882910000**	
LM 15/4.63	15	627	10	**1724141044**	**1724141687**	**1724140001**
LM 15/6	15.2	484	10	**1686361044**	**1686361687**	**1686360001**
LM 15/9	15	186	10		**1882890000**	
LM 17x6	17	10	10		**1835820000**	
LM 17/9	17.8	341	10	**1724151044**	**1724151687**	**1724150001**
LM 18/6.5	18	290	10	**1749321044**	**1749321687**	**1749320001**
LM 19.05x6.3	19.05	10	10		**1835830000**	
LM 20/8	20.3	264	10	**1686381044**	**1686381687**	**1686380001**
LM PA 20/8	20.3	264	10		**1874860000**	
LM 25.4/12.7	25.4	147	10	**1686391044**	**1686391687**	**1686390001**
LM 26/10	26	156	10	**1686401044**	**1686401687**	**1686400001**
LM 26,5/17,5	26.5	10	10			**1784340000**
LM 27/8	27	198	10		**1861510000**	
LM 27/18	27	90	10			**1873810000**
LM 30/20	30	78	10	**1724161044**	**1724161687**	**1724160001**
LM 40/6	40	90	10	**1760461044**		
LM 56/22	56	36	10	**1686421044**	**1686421687**	**1686420001**
LM 60/36	60	21	10	**1686431044**	**1686431687**	**1686430001**
LM 89/34	89	16	10	**1003400000**		
LM 105/105	105	4	10			**1975160000**
LM 105/148	105	4	10	**1724171044**	**1724171687**	**1724170001**
LM 202/12	202	22	10		**1915320000**	
LM 210/148	210	2	10	**1724181044**	**1724181687**	**1724180001**
LM 210/297	210	1	10	**1686441044**	**1686441687**	**1686440001**

Blank labels

The ThermoMark labels offer brilliant printing quality thanks to the thermal transfer technology. Different materials and the user-friendly printing system of THM Pro plus M-Print Pro optimises every marking requirement.

- High-quality polyester labels in various colours available,
- Automatic positioning of the labels in the printer for perfect centring of the printing on every label.
- The THM Pro printer ensures hardwearing printing output.

THM MT 30x – Polyester labels

Technical specification

Material	Polyester film
UL 94 flammability rating	HB
Min. temperature, continuous	-40 °C
Max. temperature, continuous	150 °C
Form of supply	Rolls, perforated

Ordering data

Type	Length x Width	No. per reel	Qty.	Order No. white	Order No. yellow	Order No. silver
THM 8/8	8x8	10000	1	**1954070000**		
THM 15/4	15x4	10000	1		**1072690000**	
THM 15/5.08	15x5.08	10000	1		**1964130000**	
THM 15/6	15x6	10000	1	**1753231044**	**1753231687**	**1753230001**
THM 16/7	16x7	10000	1		**1852520000**	
THM 17x8	17x8	10000	1		**1027620000**	
THM 17/9	17x9	10000	1	**1968130000**	**1856650000**	
THM 18/6	18x6	10000	1	**1753271044**	**1753271687**	**1753270001**
THM 18/9	18x9	10000	1	**1753251044**	**1753251687**	**1753250001**
THM 20/8	20x8	10000	1	**1753241044**	**1753241687**	**1753240001**
THM 25.9/7.1	25.9x7.1	5000	1	**1891770000**		
THM 25/12	25x12	10000	1	**1751751044**	**1751751687**	**1751750001**
THM 26/10	26x10	10000	1	**1751761044**	**1751761687**	**1751760001**
THM 26.5/17.5	26.5x17.5	10000	1			**1770090000**
THM 30/20	30x20	6000	1	**1753261044**	**1753261687**	**1753260001**
THM 30/52	30x52	2000	1			**1014680000**
THM 32/9	32x9	6000	1	**1751771044**		**1751770001**
THM 38/17	38x17	4000	1	**1011610000**		
THM 38/19	38x19	2000	1	**1751801044**	**1751801687**	**1751800001**
THM 38/32	38x32	1000	1			**1862350000**
THM 45/23	45x23	2000	1	**1751811044**	**1751811687**	**1751810001**
THM 57/27	57x27	2000	1			**1852540000**
THM 65/35	65x35	1000	1	**1751831044**	**1751831687**	**1751830001**
THM 89/60	89x60	1000	1			**1003410000**
THM 101/48	101x48	500	1	**1751821044**	**1751821687**	**1751820001**
THM 101/74	101x74	500	1		**1061810000**	**1762960001**
THM 101/150	101x150	250	1			**1778170000**



Textile labels are made of very flexible cotton fabric. The delivery form in rolls is made for using thermal transfer printers. Thus a ticker adhesive layer is possible as with labels on A4 sheets. Both, the flexible material and the ticker adhesive layer, offers a better adhesive power and allows the use for angled or round object like cables or tubes.

THM GEW – Textile labels

Reels

Technical specification

Material	Vinyl coated cotton fabric
Min. temperature, continuous	-29 °C
Max. temperature, continuous	80 °C
Form of supply	Rolls, perforated

Ordering data

Type	Length x Width	No. per reel	Qty.	Order No. white	Order No. yellow
THM GEW 15/6	15x6	10000	1	**1059780000**	**1059790000**
THM GEW 17/9	17x9	10000	1	**1059800000**	**1059810000**
THM GEW 18/6	18x6	10000	1	**1059820000**	**1059830000**
THM GEW 18/9	18x9	10000	1	**1059840000**	**1059850000**
THM GEW 20/8	20x8	10000	1	**1059870000**	**1059880000**

THM EL are self-adhesive endless labels for marking cable ducts and distribution boxes. The labels are in 15 mm, 24 mm and 38 mm width on rolls in the colour white. The needed lengths of the label can be designed individually with the M-Print® PRO Advanced software by the customer.
The printer THM Pro equipped with a cutting unit is the best solution for an optimum printing.

THM EL

Technical specification

Material	Vinyl film
Min. temperature,	-40 °C
Max. temperature,	80 °C
Form of supply	Roll

Ordering data

Type	Colour	Width	No. per sheet	Qty	Order No.
THM EL 15 WS	white	15 mm	5 x 15 mm lines	1	**1096170000**
THM EL 24 WS	white	24 mm	3 x 24 mm lines	1	**1105550000**
THM EL 38 WS	white	38 mm	2 x 38 mm lines	1	**1105560000**

THM ET S7 are non-adhesive labels on rolls for marking the Siemens Simatic 200S, S7-300 and S7-400 modules.

- The individual printing of the THM ET S7 will be done with the M-Print® PRO Software and a THM printer
- Easy separating of the THM ET S7 labels
- High resistant printing with the THM printers

THM ET S7

Technical specification

Material	Polyolefine, Polyester film
Min. temperature,	-40 °C
Max. temperature,	93 °C
Form of supply	Roll

Ordering data

Type	Length	Width	No. per sheet	Qty	Order No. yellow	Order No. turquoise
THM ET S7 50/12.5	50 mm	12.5 mm	2.000	1	**1161810000**	**1161790000**
THM ET S7 50/25	50 mm	25 mm	1.250	1	**1095590000**	**1161780000**
THM ET S7 300-1	103 mm	22.6 mm	1.000	1	**1161770000**	**1161750000**
THM ET S7 300-2	103.8 mm	17.3 mm	1.000	1	**1161740000**	**1161730000**
THM ET S7 400	251 mm	13.5 mm	500	1	**1161720000**	**1161710000**

The ET S7 non-adhesive labels in A4 format are used for labelling the Siemens S300, S400 and S7 modules. They can be printed with a laser printer to suit individual requirements by means of the Weidmüller M-Print Pro software.
- Background colour yellow or turquoise with black preprinted characters (boxes)
- labels easily prepared singly (non-adhesive)

ET S7 non-adhesive labels

Technical specification

Material	Polycarbonate
Min. temperature, continuous	-40 °C
Max. temperature, continuous	150 °C

Ordering data

Type	Length	Width	No. per sheet	Qty	Order No.
ET S7-12/50- yellow	50 mm	12 mm	84	10	**1804480000**
ET S7-12/50-turquoise	50 mm	12 mm	84	10	**1865440000**
ET S7-300- yellow-1	100 mm	22.6 mm	16	10	**1821020000**
ET S7-300- yellow-2	208 mm	17.3 mm	22	10	**1847650000**
ET S7-300-turquoise-1	100 mm	22.6 mm	16	10	**1865450000**
ET S7-300-turquoise-2	208 mm	17.3 mm	22	10	**1865460000**
ET S7-400- yellow-1	251 mm	11.5 mm	14	10	**1821040000**
ET S7-400- yellow-2	251 mm	11.5 mm	14	10	**1821030000**
ET S7-400- yellow-3	251 mm	13.5 mm	14	10	**1847640000**
ET S7-400-turquoise-1	251 mm	11.5 mm	14	10	**1865470000**
ET S7-400-turquoise-2	251 mm	11.5 mm	14	10	**1865480000**
ET S7-400-turquoise-3	251 mm	13.5 mm	14	10	**1865490000**

Printed labels



Symbol Pack is a pocket-sized package with preprinted electrical symbols on perforated sheets. The perfect solution for marking electrical systems, with good resistance to alkyl-alcohols and petrol.

Symbol Pack

Technical specification

Material	Acrylic-coated fibre webbing
Adhesive	Permanent acrylic copolymer
Min. temperature, continuous	-45 °C
Max. temperature, continuous	80 °C
Material colour	yellow
Quantity per pack:	10 sheets/pack

Ordering data

Type	Length	Height	Printing	No. per sheet	Qty	Order No.
Symbol Pack	9 mm	19 mm	Symbol 2	54	1	**1685700000**
Symbol Pack	14 mm	14 mm	Symbol 1	48	1	**1685690001**
Symbol Pack	14 mm	14 mm	⏚	48	1	**1685690002**
Symbol Pack	25 mm	25 mm	Lightning flash in triangle	12	1	**1741090000**
Symbol Pack	50 mm	50 mm	Lightning flash in triangle	4	1	**1741100000**
Symbol Pack	75 mm	75 mm	Lightning flash in triangle	2	1	**1741110000**

Service Pack is a pocket-sized package with preprinted electrical symbols on perforated sheets. The in situ solution for marking electrical systems, with good resistance to alkyl-alcohols and petrol.

Service Pack

Technical specification

Material	Acrylic-coated fibre webbing
Adhesive	Permanent acrylic copolymer
Min. temperature, continuous	-45 °C
Max. temperature, continuous	80 °C
Quantity per pack:	10 sheets/pack

Ordering data

Type	Colour	Size of labels	Printing	No. per sheet	Qty	Order No.
Service Pack L1	black	Ø 16 mm	L1	20	1	**1707350001**
Service Pack L2	black	Ø 16 mm	L2	20	1	**1707350002**
Service Pack L3	black	Ø 16 mm	L3	20	1	**1707350003**
Service Pack N	blue	Ø 16 mm	N	20	1	**1707350004**
Service Pack PE	yellow /green	Ø 16 mm	PE	20	1	**1707350006**
Service Pack Erde	yellow /green	Ø 16 mm	⏚	20	1	**1707350005**

Marko Cards are strips of labels printed with a lightning flash. This symbol is available in four different sizes. For marking electrical equipment, with good resistance to alkyl-alcohols and petrol.

Marko Cards

Technical specification

Material	Acrylic-coated fibre webbing
Adhesive	Permanent acrylic copolymer
Min. temperature, continuous	-29 °C
Max. temperature, continuous	80 °C
Material colour	yellow
Quantity per pack:	10 sheets

Ordering data

Type	Length	Height	Printing	No. per sheet	Qty	Order No.
Marko Card	100 mm	100 mm	Lightning flash in triangle	3	10	**1700550001**
Marko Card	200 mm	200 mm	Lightning flash in triangle	1	10	**1700560001**
Marko Card	25 mm	25 mm	Lightning flash in triangle	14	10	**1700530001**
Marko Card	50 mm	50 mm	Lightning flash in triangle	7	10	**1700540001**

PageTab are textile labels in sheet form made of PVC-free acrylic fabric. Except for the 8 x 20 version, all labels have a black border.

PageTab

Technical specification

Material	Acrylic-coated fibre webbing
Adhesive	Permanent acrylic copolymer
Min. temperature, continuous	-29 °C
Max. temperature, continuous	93 °C
Quantity per pack:	25 sheets

Ordering data

Type	Width	Length	No. per sheet	Qty	Order No.
PAGETAB 15X9	9 mm	15 mm	310	25	**1686160000**
PAGETAB 19X11	11 mm	19 mm	200	25	**1686170000**
PAGETAB 20X8	8 mm	20 mm	280	25	**1686180000**
PAGETAB 28X11	11 mm	28 mm	125	25	**1686190000**
PAGETAB 38X11	11 mm	38 mm	100	25	**1686200000**
PAGETAB 56X22	22 mm	56 mm	24	25	**1686210000**
PAGETAB 60X35	35 mm	60 mm	16	25	**1686220000**



TabPack consists of blank labels in a handy format for marking where required with the STI pen or a ballpoint pen.

TabPack

Technical specification

Material	Acrylic-coated fibre webbing
Adhesive	Permanent acrylic copolymer
Min. temperature, continuous	-29 °C
Max. temperature, continuous	93 °C
Quantity per pack:	10 sheets/pack

Ordering data

Type	Width	Length	No. per sheet	Qty	Order No.
TABPACK 14X9	9 mm	14 mm	84	1	**1686110000**
TABPACK 15X6	6 mm	15 mm	100	1	**1686120000**
TABPACK 19X11 M. RAND	11 mm	19 mm	44	1	**1686130000**
TABPACK 21X8	8 mm	21 mm	64	1	**1686140000**
TABPACK 38X11 M. RAND	11 mm	38 mm	22	1	**1686150000**

KSW

KSW marker strips are used for labelling multipole plug-in connectors. They can be printed individually by the user for any contact spacing.

- Wipe-proof labelling
- Strip width 2.5 mm and 4 mm
- Simply stick on – that's all!
- Optimum adhesion
- PVC-free

Technical data

Material	Polyester with smooth surface
Colour	White
Adhesive	Acrylate base
Adhesion (strip width 25 mm) to DIN 51221	On steel: 19 N, polypropylene: 12 N, Polyethylene: 10 N
Minimum adhesion temperature	+4 °C
Behaviour in fire	Self-extinguishing after 15 seconds, non-drip
Packaging unit	10 sheets (special print = 1 sheet)
Strip/sheet	20

KSW 2.5 15/5.08														
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
163006 0001														

1 unit = 1 sheet = 20 strips

Pitch 5.08 mm

Order example:
Order No. **163006 0001** = version
KSW 2.5 15/5.08 1-15

- 20 x 1-15 print
- 5.08 mm spacing
- 15 pole
- 2.5 mm strip width

Strip width 2.5 mm

Special print: length x pitch x no. of poles
Please state contact spacing

KSW 2,5 mm

Ordering data

Pitch 3.5mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 2.5 8/3.5	8	1-8	10	**1873620000**
KSW 2.5 14/3.5	14	1.3-27	10	**1849580000**
KSW 2.5 14/3.5	14	2,4-28	10	**1849590000**
KSW 2.5 16/3.5	16	1-16	10	**1652260001**
KSW 2.5 24/3.5	24	1-24	10	**1652250001**
KSW 2.5 24/3.5	24	25-48	10	**1652250025**

Pitch 3.81mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 2.5 8/3.81	8	1-8	10	**1873630000**
KSW 2.5 16/3.8	16	1-16	10	**1873610000**
KSW 2.5 24/3.81	24	1-24	10	**1873600000**

Pitch 5.0mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 2.5 8/5	8	1-8	10	**1700660001**
KSW 2.5 16/5	16	1-16	10	**1630070001**
KSW 2.5 20/5	20	1-20	10	**1630080001**
KSW 2.5 20/5	20	21-40	10	**1630080021**
KSW 2.5 20/5	20	41-60	10	**1630080041**
KSW 2.5 20/5	20	61-80	10	**1630080061**
KSW 2.5 24/5	24	1-24	10	**1713980001**

Pitch 5.08mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 2.5 8/5.08	8	1-8	10	**1630100001**
KSW 2.5 8/5.08	8	9-16	10	**1630100009**
KSW 2.5 8/5.08	8	19-26	10	**1895960000**
KSW 2.5 8/5.08	8	A-H	10	**1630101021**
KSW 2.5 10/5.08	10	1-10	10	**1630020001**
KSW 2.5 10/5.08	10	11-20	10	**1630020011**
KSW 2.5 10/5.08	10	9-18	10	**1895950000**
KSW 2.5 15/5.08	15	1.10-150	10	**1630050001**
KSW 2.5 15/5.08	15	151-300	10	**1630050151**
KSW 2.5 15/5.08	15	301-450	10	**1630050301**
KSW 2.5 15/5.08	15	1-15	10	**1630060001**
KSW 2.5 16/5.08	16	1-16	10	**1713970001**
KSW 2.5 16/5.08	16	17-32	10	**1713970017**
KSW 2.5 16/5.08	16	33-48	10	**1713970033**
KSW 2.5 24/5.08	24	1-24	10	**1713990001**

Pitch 7.5mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 2.5 8/7.5	8	1-8	10	**1873650000**
KSW 2.5 10/7.5	10	101-200	100	**1630030101**
KSW 2.5 10/7.5	10	201-300	100	**1630030201**
KSW 2.5 10/7.5	10	301-400	100	**1630030301**
KSW 2.5 10/7.5	10	401-500	100	**1630030401**
KSW 2.5 10/7.5	10	1-10	10	**1630040001**

Pitch 7.62mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 2.5 8/7.62	8	1-8	10	**1873640000**

Pitch 9.0mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 2.5 10/9 W	10	1-10	10	**1676710001**
KSW 2.5 10/9 W	10	11-20	10	**1676710011**
KSW 2.5 10/9 W	10	21-30	100	**1676710021**

Printed labels

Ordering data

blank

Type	No. of poles	Printing	Qty.	Order No.
KSW 2.5 < 50MM			1	**1629960000**
KSW 2.5 < 100MM			10	**1629980000**
KSW 2.5 < 150MM			10	**1630000000**

Custom printing

Type	No. of poles	Printing	Qty.	Order No.
KSW 2.5 < 50MM			1	**1629900000**
KSW 2.5 < 100MM			1	**1629920000**
KSW 2.5 < 150MM			1	**1629940000**

D

KSW 4 mm

Pitch 3.5mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 4 8/3.5	8	1-8	10	**1630190001**
KSW 4 16/3.5	16	1-16	10	**1630150001**
KSW 4 16/3.5	16	17-32	10	**1630150017**
KSW 4 24/3.5	24	1-24	10	**1640410001**

Pitch 5.0mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 4 8/5	8	1-8	10	**1700670001**
KSW 4 12/5	12	1-12	10	**1630130001**
KSW 4 12/5	12	13-24	10	**1630130013**
KSW 4 16/5	16	1-16	10	**1700700001**
KSW 4 18/5	18	1-18	10	**1630170001**
KSW 4 24/5	24	1-24	10	**1700710001**

Pitch 5.08mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 4 8/5.08	8	1-8	10	**1630200001**
KSW 4 8/5.08	8	9-16	10	**1630200009**
KSW 4 8/5.08	8	17-24	10	**1630200017**
KSW 4 8/5.08	8	25-32	10	**1630200025**
KSW 4 8/5.08	8	33-40	10	**1630200033**
KSW 4 8/5.08	8	41-48	10	**1630200041**
KSW 4 10/5.08	10	1-10	10	**1705820001**
KSW 4 10/5.08	10	11-20	10	**1705820011**
KSW 4 10/5.08	10	21-30	10	**1705820021**
KSW 4 10/5.08	10	31-40	10	**1705820031**
KSW 4 10/5.08	10	41-50	10	**1705820041**
KSW 4 10/5.08	10	51-60	10	**1705820051**
KSW 4 10/5.08	10	61-70	10	**1705820061**
KSW 4 10/5.08	10	71-80	10	**1705820071**
KSW 4 10/5.08	10	81-90	10	**1705820081**
KSW 4 10/5.08	10	91-100	10	**1705820091**
KSW 4 16/5.08	16	1-16	10	**1630160001**
KSW 4 16/5.08	16	17-32	10	**1630160017**
KSW 4 16/5.08	16	33-48	10	**1630160033**
KSW 4 16/5.08	16	49-64	10	**1630160049**
KSW 4 16/5.08	16	65-80	10	**1630160065**
KSW 4 16/5.08	16	81-96	10	**1630160081**
KSW 4 18/5.08	18	1.3-36	10	**1720530001**
KSW 4 24/5.08	24	1-24	10	**1630180001**

Pitch 7.0mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 4 5/7	5	1-5	10	**1670780001**
KSW 4 9/7	9	1-9	10	**1714060001**
KSW 4 10/7	10	1-10	10	**1714070001**

Ordering data

Pitch 7.5mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 4 8/7.5	8	1-8	10	**1700690001**
KSW 4 12/7.5	12	1-12	10	**1630140001**
KSW 4 12/7.5	12	13-24	10	**1630140013**
KSW 4 12/7.5	12	25-36	10	**1630140025**
KSW 4 12/7.5	12	37-48	100	**1630140037**
KSW 4 12/7.5	12	49-60	100	**1630140049**

Pitch 7.62mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 4 8/7.62	8	1-8	10	**1700680001**
KSW 4 12/7.62	12	1-12	10	**1652270001**
KSW 4 12/7.62	12	13-24	10	**1652270013**

Pitch 9.0mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 4 10/9	10	1-10	10	**1714080001**

Pitch 10.16mm

Type	No. of poles	Printing	Qty.	Order No.
KSW 2.5 4/10.16	4	1-4	10	**1630090001**

blank

Type	No. of poles	Printing	Qty.	Order No.
KSW 4 < 50MM			10	**1629970000**
KSW 4 < 100MM			10	**1629990000**
KSW 4 < 150MM			10	**1630010000**

Custom printing

Type	No. of poles	Printing	Qty.	Order No.
KSW 4 < 50MM			1	**1629910000**
KSW 4 < 100MM			1	**1629930000**
KSW 4 < 150MM			1	**1629950000**

Printing systems

Printing systems

Introduction	E.2
Inkjet printer PrintJet PRO	E.3
Plotter MCP Plus	E.4
Plotter MCP Basic	E.5
Plotter MCP – accessories	E.6
Plotter MC-Mobilo	E.7
Thermal transfer printer THM TwinMark	E.8
Thermal transfer printer THM Plus	E.9
Thermal transfer printer THM Pro	E.10
Thermal transfer printer THM Basic	E.11
Software M-Print® PRO	E.12

Printing systems and software

The Weidmüller labelling systems are the quick and efficient way of producing markers for connectors, wires, cables and devices, plus labels for general use. The **M-Print® PRO** software enables users to mark electrical equipment quickly and simply. For professional and fast design, printing and ordering of your marking requirements. Borders, barcodes, graphics or photos can all be easily integrated. The multitude of data conversion routines presents you with fast and flexible options for data integration. The Weidmüller **PrintJet PRO**, **MCP Plus**, **MCP Basic**, **MC-Mobilo** printers plus those of the ThermoMark series can be used for printing.

The **PrintJet PRO** is the reference model in industrial marking for high-resolution printing and maximum wipe and scratch resistance. The **MCP Plus** plotter provides you with good flexibility because with its positioning frame it can handle more than 160 different types of marker in the MultiCard format. The **MC-Mobilo** is the ideal printer for labelling on site without a PC and a mains power supply, directly during installation work. The printers of the ThermoMark series are ideal for printing labels and/or shrinkable sleeves in excellent quality.

	Printer						
Type of marker	**PrintJet PRO**	**Plotter MCP Plus**	**MCP Basic**	**MC Mobilo**	**THM TwinMark**	**THM Plus**	**THM Basic**
Technical data							
Technology	Inkjet process	Plotting technique	Plotting technique	Plotting technique	Thermal transfer	Thermal transfer	Thermal transfer
Voltage	AC 230 V or AC 115 V	AC 230/AC 115 V	AC 230/AC 115 V	AC 230/AC 115 V	AC 230/AC 115 V	AC 230/AC 115 V	AC 230/AC 115 V
Printing resolution	1.200 dpi				300 dpi	300 dpi	203 dpi
Interfaces	USB, LAN	Parallel Centronics, USB	USB	RS 232	RS 232, USB, LAN	RS 232, USB, LAN, Compact Flash	Parallel Centronics, USB, RS 232, LAN
Network interface card	●				●	●	●
Terminal markers							
DEK/WS/ZS/MF	●	●	●	●			
ELS	●	●	●	●			
WAD	●						
Cable and wire markers							
SF/SFX/SFC	●	●	●	●			
TM-I	●	●	●	●			
ELS	●	●	●	●			
Device markers							
DMC	●	●	●	●			
ESG	●	●	●	●			
SM/CC	●	●	●	●			
Labels							
THM MT						●	●
THM WriteOn						●	●
THM GEW						●	●
THM EL							●
THM ET S7						●	●
Shrink sleeves							
TwinMark					●	●	

PrintJet PRO

The **PrintJet PRO** inkjet printer prints markers for electric connectivity. These markers can be used for clear equipment identification on devices, cables and connectors. The labelling makes servicing, maintenance and troubleshooting much easier. Water-based ink is used for the black or spot colour printing. The print is crystal clear and resistant to environmental influences.
The **PrintJet PRO** prints plastic markers in **MultiCard** format. In combination with the user-friendly **M-Print® PRO** software and the attached loader, the printer becomes an essential part of the production.The inkjet process being used, the subsequent fusing, as well as the printer cartridge and ink have all been specially adapted by Weidmüller for industrial use. The printer has excellent long-term use capabilities, thanks to its integrated loader.

- Top-quality, resistant printing
- Spot colour print
- Perfect for constant use
- Integrated loader for 20 MultiCards
- Ideal for large quantities
- The display shows all relevant information
- Flexible connection options, from LAN ports to USB ports

Technical data

PrintJet PRO	
Type	PrintJet PRO
Application	Prints MultiCard markers
Technology	Inkjet process
Print quality	600 / 1.200 dpi
Printer drivers	Windows® 2000/XP/VISTA/7
Print software	M-Print® PRO
System requirements	Windows® 2000/XP/VISTA/7
Feed	Integrated loader
Fusing	Thermal fusing
Interface	USB, LAN
Power supply	AC 230 V or AC 115 V
Location	Office conditions
Ambient temperature	20° to 35 °C
Dimensions (L x W x H)	1060 x 500 x 310 mm
Weight	33 kg
Cartridge system	Ink cartridge, CMYK (up to 1.000.000 characters, Arial font size 6)
Scope of supply	PrintJet PRO, power cable, printer drivers, manuals (CD), Ink tank starter set colour, USB cable, M-Print® PRO software

Ordering data

PrintJet PRO

Type		Order No.
PrintJet PRO 115V		1024050000
PrintJet PRO 230V		1001180001
Accessories		
PJ PRO TNTK INK SET COL	Ink tank starter set, colour	1027110000
PJ PRO TNTK INK K	● Ink tank Black	1027040000
PJ PRO TNTK INK C	● Ink tank Cyan	1027050000
PJ PRO TNTK INK M	● Ink tank Magenta	1027060000
PJ PRO TNTK INK Y	● Ink tank Yellow	1027070000
PJ PRO TNAW	waste pad	1024140000
Ink tank PrintJet II		1858920000
Clean Unit PrintJet II		1858950000
Ink tank PrintJet		1797460000
Clean Unit PrintJet		4062150000

Plotter

MCP Plus

The plotter **MCP Plus** complements the Weimüller MultiCard concept. It is suitable for smaller quantities of markers and when only part of a MultiCard is to be printed on. The special positioning frame for five MultiCards increases productivity by 20 % over comparable systems. With the positioning frame for SlimFix markers sizes 4 to 6, printing on more than 160 MultiCard types for terminals, cables, wires and equipment is possible. Labels are printed with the MCP-Label positioning frame. Suitable for use with the Weidmüller **M-Print® PRO** software.

- 2 positioning frames for more than 160 MultiCard types
- MultiCards easily fitted into the frame
- Easy to use with partly used MultiCards
- Automatic pen activation function
- Safe storage of the plotter pens



Technical data

Type	MCP Plus
Application	printing of MultiCard markers and labels
Technology	plotting technique
Print software	M-Print® PRO
System requirements	Windows 2000/XP/VISTA/7
Interface	Parallel Centronics / USB
Power supply	230/115 V AC
Feed	manual
Location	office conditions
Ambient temperature	10 °C – 35 °C
Dimensions (L x W x H)	660 x 440 x 125 mm
Weight	approx. 8 kg
Scope of supply	MCP Plus with Centronics cable, USB cable, power pack (100-240 V AC/50-60 Hz), Euro and US plugs, MultiCard positioning frame, 0.25 P-Ink plotter pen, printer driver, M-Print® PRO software and manual

Ordering data

MCP Plus

Type	Order No.
MCP Plus plotter set	**1925000000**

MCP Basic

The **MCP Basic** plotter is a flexible and portable solution that allows you to print your labels on-site quickly and easily.

The **MCP Basic** is suited for printing small-scale labelling jobs, partial labels, or remaining quantities

- Small space-saving flat-bed plotter
- Positioning frame for 3 MultiCards
- Easily filled with MultiCard sheets
- Positioning frame for SlimFix, sizes 4 to 6 and a label positioning frame optionally available
- Works together with Weidmüller's **M-Print® PRO** software



Technical data

Type	MCP Basic
Application	Printing MultiCard markers and labels
Technology	plotting technique
Plotting speed	max. 40 mm/s
System requirements	Windows® 2000/XP/VISTA/7
Software	M-Print® PRO
Interfaces	USB
Voltage supply	100~240 V AC, 50-60 Hz
Voltage supply	Via external power supply unit with interchangeable adapters
Feed	manual
Location	office conditions
Ambient temperature	10°C – 35°C
Dimensions (L x W x H) mm	440 x 440 x 125
Weight	6 kg
Scope of supply	MCP Basic plotter, printer driver, power cord, USB cable, M-Print® PRO software, 0.25 P-Ink plotter pen, MultiCard positioning frame, power supply unit (100-240 V AC / 50-60 Hz), Euro and US plugs, user manual on CD, hand trolley-case

Ordering data

MCP Basic

Type	Order No.
MCP Basic	1139400000

Plotter MCP - accessories

MCP positioning frames

Ordering data

Type	for	Qty.	Order No.
MCP AP PLUS	MultiCards	1	**1924360000**
MCP AP BASIC	MultiCards	1	**1139880000**
MCP AP SF 4-6	SlimFix sizes 4 to 6	1	**1924310000**
MCP AP Labels	Labels	1	**1924370000**

MCP plotter pens

Type	for		Qty.	Order No.
Plotter Pen 0.18	Reusable pen		1	**1768570000**
Plotter Pen 0.25	Reusable pen		1	**1768540000**
Plotter Pen 0.25 P-Ink	Disposable pen 8 ml	Not for CLI T sleeves	1	**1920640000**
Plotter Pen 0.35	Reusable pen		1	**1768550000**
Plotter Pen 0.35 P-Ink	Disposable pen 8 ml	Not for CLI T sleeves	1	**1920650000**
Plotter Pen 0.50	Reusable pen		1	**1768560000**
Plotter Pen 0.50 P-Ink	Disposable pen 8 ml	Not for CLI T sleeves	1	**1005710000**
Plotter Pen 0.70	Reusable pen		1	**1011440000**
Plotter Pen 0.70 P-Ink	Disposable pen 8 ml	Not for CLI T sleeves	1	**1011450000**

MCP ink

Type	Contents		Qty.	Order No.
P- Ink	30 ml	Not for CLI T sleeves	1	**1924340000**
Ink 2000	25 ml		1	**1772120000**

MCP miscellaneous

Type	Contents	Qty.	Order No.
P cleaner	30 ml	1	**1924330000**
Cleaner Clean 2000	25 ml	1	**1772130000**
Inlay for MCP		1	**1935130000**
Inlay SFC 3		1	**1058090000**
MCP adhesive strips		5	**1924320000**
MCP Plus cover		1	**1924350000**
MCP TP-KOF Basic	Trolley MCP Basic	1	**1139890000**

Accessories - STI pen

The STI-S felt tip pen is suitable for labelling blank Weidmüller marking products. It can be used for handwritten labels or, in conjunction with the STI-S adapter, for a plotter printout. A black, waterproof ink is used.

Ordering data

Type		Qty	Order No.
Adapter aluminium STI pen		1	**1762440000**
STI pen SW	Not for CLI T sleeves	10	**0508401694**

MC-Mobilo

The MC-Mobilo allows users to work directly at place. There is no need for a PC and no need for a power supply so electrical equipment can be labelled anywhere, anytime. The rechargeable battery provides power for up to 3 hours. The universal inlay enables up to 120 different marker types of the MultiCard range to be processed.

Technical data

Type	Plotter
Application	Printing of MultiCard markers
Technology	Plotting technique
Print software	WM-Print
Interface	RS 232
Power supply	AC 230 / AC 115 V
Feed	manual
Location	can be used anywhere
Ambient temperature	15 – 30 °C
Dimensions (L x W x H)	380 x 190 x 68 mm
Weight	3 kg
Scope of supply	MC-Mobilo, universal power unit, including adapters (EURO, UK, USA), data cassette, operating instructions, PowerPack, PC connecting cable, WM-Print, universal MultiCard mounting frame, 0.25 plotter pen, carry case

Ordering data

MC-Mobilo

MC-Mobilo		Qty.	Order No.
MC-Mobilo 110/220 V		1	**1741260001**
MC-Mobilo Accessories			
Printkit (Ink 2000, Clean 2000, Plotter-Pen 0.25)		1	**1686920000**
Frame inlay SF 4-6		1	**1802180000**
Inlay SFC 3		1	**1058090000**
Accessories Plotter IP220/MC-Mobilo			
P-Ink 30 ml	Not suitable for CLI-T sleeves	1	**1924340000**
Ink 2000 25 ml		1	**1772120000**
P cleaner 30 ml		1	**1924330000**
Cleaner Clean 2000 25 ml		1	**1772130000**
Plotter Pen 0.18		1	**1768570000**
Plotter Pen 0.25		1	**1768540000**
Plotter Pen 0.25 P-Ink	Not suitable for CLI-T sleeves	1	**1920640000**
Plotter Pen 0.35		1	**1768550000**
Plotter Pen 0.35 P-Ink	Not suitable for CLI-T sleeves	1	**1920650000**
Plotter Pen 0.50		1	**1768560000**
Plotter Pen 0.50 P-Ink	Not suitable for CLI-T sleeves	1	**1005710000**
Plotter Pen 0.70		1	**1011440000**
Plotter Pen 0.70 P-Ink	Not suitable for CLI-T sleeves	1	**1011450000**
Accessories – STI pen			
Adapter aluminium STI pen		1	**1762440000**
STI pen SW	Not suitable for CLI-T sleeves	10	**0508401694**

Thermal transfer printer

THM TwinMark

The **THM TwinMark** printer takes advantage of thermal transfer technology and has two distinct printing heads. The two printing heads function independently and make it possible to print shrink sleeves on both sides. The printer is well suited for TwinMark roll-packaged shrink sleeves and delivers a brilliant quality print. The user-friendly system is operated together with the **M-Print® PRO** software.

- LCD-graphics display shows all key status information
- Automatic positioning with margin stop
- Top and bottom sides can be printed with similar or different data
- Works with Weidmüller's **M-Print® PRO** software

Technical data

Type	THM TwinMark
Application	Shrink sleeve printer
Technology	Thermal transfer
Printing speed	30, 40, 50, 75, 100, 125 mm/s
Printing resolution	300 dpi
Printer drivers	Windows® 2000/XP/VISTA/7
Software	M-Print® PRO
Interface	RS232 C serial, 1200 to 230400 baud/8-bit, USB 2.0 high-speed slave for PC connection, Ethernet 10/100-Base-T, USB master for external control panel, keyboard and scanner
Modes of operation	100 – 240 V AC 50/60 Hz
Buttons / LED display	Pause, feed, cancel, menu, enter, 4 cursors
LCD-graphics display	W x H 60 x 40mm, 4 lines á 20 caracters
Shown on display	Data receive, clock, calendar sheet, WLAN intensity, Ethernet status, user memory, input buffer, foil supply, printing head temperature
Power consumption	max. 300 Watt
Application site	Office conditions
Ambient temperature	10 – 35 °C
Dimensions (H x L x W)	395 x 554 x 248 mm
Weight	21 kg
Scope of supply	THM TwinMark printer, printer driver, power cord, USB cable, M-Print® PRO software, user manual on CD
Accessories – Ribbon R 83/300	
Colour	Black
Basis	Resin
Suitable for	Shrink sleeve TwinMark HSS-HF (halogen-free variants)
Width x length	83 mm x 300 metres

Ordering data

THM TwinMark

	Type	Material	Width (mm)	Order No.
Printer	THM TwinMark			**1140490000**
Ribbon	Ribbon R 83/300	Resin	83	**1962370000**

THM Plus

The **THM Plus** printer uses thermal transfer technology for the industrial printing of labels and shrink sleeves. A robust metal housing protects the printer against dust and dirt. The printer provides high-quality output and is suitable for printing on different materials. This user-friendly system functions with the Weidmüller **M-Print® PRO** software.

- Due to a special firmware this printer is particulary suitable for TwinMark shrink sleeves
- Easy exchange of materials and ribbons
- Memory card slot – Compact Flash type 1
- Easy calibration
- Suitable for both types of shrinkable sleeve and also Weidmüller labels on reels
- Easy to use with Weidmüllers M-Print® PRO

Technical data

Type	THM Plus
Application	Printing of labels and shrinkable sleeves
Technology	Thermal transfer
Printing speed	50 – 150 mm/s
Printing quality	300 dpi
Printer drivers	Windows® 2000/XP/VISTA/7
Software	M-Print® PRO
System requirements	Windows® 2000/XP/VISTA/7
Interface	Seriell RS232, Ethernet 10/100 Base T, USB, Compact Flash Typ 1
Power supply	100/240 V AC, 50-60 Hz, max. 250 W
Dimensions (W x L x H)	242 x 446 x 274 mm
Weight	9 kg
Scope of supply	THM Plus Printer, USB cable, power cable, printer drivers, manuals (CD), M-Print® PRO software
Accessories – Ribbon WR 90/300	
Colour	Black
Basis	Wax/resin
Suitable for	HSS (standard variants)
Width x length	90 mm x 300 metres
Accessories – Ribbon R 83/300	
Colour	Black
Basis	Resin
Suitable for	HSS-HF (halogen-free variants)
Width x length	83 mm x 300 metres

Ordering data

THM Plus

	Type	Application	Order No.
Printer	THM Plus Printer		**1962340000**
Ribbons	Ribbon R 83/300	Free from halogens	**1962370000**
	Ribbon WR 90/300	Standard	**1962360000**
	Hi Res ribbon, 280 m	Label	**1790650000**
Adapter	Centronic-USB2.0 Adapter		**1965140000**

Thermal transfer printer

THM Pro

The **THM Pro** printer uses thermal transfer technology for the industrial printing of labels. A robust metal housing protects the printer against dust and dirt. The printer provides high-quality output and is suitable for printing on different materials. This user-friendly system functions with the Weidmüller **M-Print® PRO** software.

- Printer for producing texts, graphics and barcodes
- Automatic positioning of labels in the printer for perfectly centred printing on every label
- Robust printing thanks to the HiRes ribbon
- Functions with the Weidmüller **M-Print® PRO** software

Technical data

Type	THM Pro
Application	Printing of labels
Technology	Thermal transfer
Printing speed	80 mm/s
Printing quality	204 dpi
Printer drivers	Windows® 2000/XP
Software	M-Print® PRO
System requirements	Windows® 2000/XP/VISTA
Interface	Parallel Centronics / USB
Power supply	220 V
Location	office conditions
Ambient temperature	–10 °C – +35 °C
Dimensions (W x H x L)	230 x 230 x 350
Scope of supply	ribbon (HiRes), printer drivers, power cable, parallel cable, USB cable, M-Print® PRO software

Ordering data

THM Pro

Type			Order No.
THM Pro Printer			1785240000
Printing foil	**Material**	**Width (mm)**	
HiRes ribbon, 280 m	Resin	110	1790650000

THM Basic

The **THM Basic** printer uses thermal transfer technology for industrial printing of labels. Its space-saving design makes it perfect for office use. The printer is well suited for labelling a variety of materials and delivers a brilliant quality print. The user-friendly system is operated together with the **M-Print® PRO** software.

- Small space-saving thermal-transfer printer
- Suitable for printing a variety of roll-packaged labels
- A variety of interfaces are available
- Works together with Weidmüller's **M-Print® PRO** software

Technical data

Type	THM Basic
Application	Printing of labels
Technology	Thermal transfer
Printing speed	75 – 100 mm/s
Printing quality	203 dpi
Printer drivers	Windows® 2000/XP/VISTA/7
Software	M-Print® PRO
Interface	Parallel Centronics / USB / Seriell RS 232 C / Ethernet 10/100 Base
Power supply	100~240 V
Location	office conditions
Ambient temperature	10 °C – 40 °C
Dimensions (H x L x W) mm	200 x 329 x 256
Weight	3,5 kg
Scope of supply	ribbon (HiRes), printer drivers, power cable, USB cable, M-Print® PRO software, manual (CD)

Ordering data

THM Basic

Type			Order No.
THM Basic			**1141340000**
Printing foil	**Material**	**Width (mm)**	
HiRes ribbon, 280 m	Resin	110	**1790650000**

M-Print® PRO Label Designer

Print and **ordering software** for markers and labels

M-Print® PRO is a professional software for printing and ordering Weidmüller markers and labels under Windows®. This software helps you to optimise your processes for marking electrical equipment. You can design, print and order your marking materials effortlessly, professionally and quickly: texts, frames, lines, graphics, barcodes, serial numbers and photos.



Technical data

Here is an overview of the main functions
Integrated product catalogue for all labels and markers, including images and links to the relevant web pages and product data sheets
Markers and labels can be designed in as many levels as required
Custom formatting of individual text characters (RTF)
Perform copy-and-paste functions with texts and their formats
Supports UNICODE for foreign-language texts, such as Russian, Chinese, Polish, etc.
Enter data on labels or worksheet
Permanent print preview: see how the printout will look during the design phase
Numeric and alphanumeric counts and sequences
Extensive range of image formats (*.bmp, *.wmf, *.png, *.ico, *.jpeg, *.tif, *.gif)
Image library including all the important symbols used in electrical engineering
Assign product to specific printer; for example, ESG 9/20 to PrintJet, LaserMark to laser printer, etc.
Output devices supported: PrintJet PRO, PrintJet I+II, SMark-Laser, ThermoCard, THM as well as standard printers with Windows® drivers, plotter MCP
Optimum and rapid adjustment of the output devices
Online update service via the Internet
Interface to RailDesigner®
Import assistant to create your own import filter for numerous file formats (*.txt, *.csv, *.xml etc.)
Imports data from CAE systems

Operating systems supported
WINDOWS® 2000/XP/VISTA/7

System requirements	
• RAM	> 64 MB
• Processor	> Pentium PIII or comparable model
• Graphics	> 800 x 600 pixels with 256 colours optimum: 1024 x 768 with 16-bit High Colour
• Hard drive	> 90 MB free storage
• Miscellaneous	mouse, keyboard, CD-ROM drive (to install the software)

M-Print® PRO is available in two editions:

- M-Print® PRO Standard Edition for professional printing results with all of Weidmüller's marking materials
- M-Print® PRO Advanced Edition for professional printing results with all of Weidmüller's marking materials plus labels to customer specification

Ordering data

M-Print® PRO

Type	Order No.
M-Print® PRO	1905490000
M-Print® PRO advanced	1905500000

Weidmüller Service

Weidmüller Service	Customer specific solutions: best advice, best solutions	V.2
	Overview of services	V.3
	Digital support: RailDesigner®, M-Print® PRO, Online catalogue	V.6

Best advice, best solutions

Services tailored to customers' needs

Service – at Weidmüller that means diversity. And it also means that you can take advantage of our comprehensive resources:

- Production of terminal rails and enclosures fitted with our modular terminals and other modules, and prewired
- Fitting of cable glands and the marking of terminals, conductors and enclosures according to your specification
- Competence in the processing of enclosure materials such as aluminium, plastics, sheet steel and stainless steel
- Flexibility in the product selection: besides Weidmüller products we can also integrate yours and even those of other manufacturers

This range of services enables Weidmüller to act as an external service provider to increase your capacities. And demanding standards guarantee a high level of quality every time.

The best advice for the best solutions

The start of a good partnership is always characterised by an intensive exchange of information to define the respective positions. Our contribution focuses on detailed advice with respect to:

- Optimum choice of products
- Practical pre-assembly
- Integration into your systems
- Consideration of requirements such as certification, classes of protection or hazard protection as required by your industry

That avoids mistakes right from the start – totally in keeping with the effective handling of the project, totally in keeping with perfect results. Our experience helps you create the foundation for good business and satisfied customers.

Overview of services



Production of terminal rails

Terminal rails are manufactured from steel, stainless steel, aluminium or copper to suit the diverse applications. And we can produce terminal rails with elongated or round holes, or in other forms to suit your requirements exactly. Terminal rails are fitted with modular terminals or electronic products, prewired and marked according to your specification.

The benefits for you

- No need to procure individual components
- No need to mount individual components
- No unnecessary stocks
- Just one order number for your pre-assembled terminal rail
- Constant high quality

Production of enclosures

High-tech brings benefits. Our state-of-the-art production methods open up new options for you:

- Inclusion of holes and threads in the enclosure
- Enclosure cover with hinges and other accessories if required
- More complex machining such as milling of contours or reaming of holes
- Special paint finishes: To protect against the effects of the weather, your enclosures can be painted individually. Simply specify the colour and printing you require. Special paint finishes and powder coating are also possible.

Enclosures are adapted to suit the intended application exactly. You get a tailored, individual product and the quality is guaranteed by our adherence to demanding standards. Does your product require a special approval? Our accredited laboratory can test the complete product and confirm that its design complies with the standards! With every delivery we document the corresponding approvals (e.g., ATEX, GL, UL, GOST, etc.).

The benefits for you

- Enclosures in various sizes and materials
- Inclusion of optional accessories such as hinges and locks
- Complex machining processes and special packaging
- Ready-to-use, certified products for all types of applications.

Overview of services

Electronics production

We manufacture according to your specifications: ranging from PCB assembly to 100%-tested component assemblies. We bring the individual parts together according to your documents: whether for materials procurement, provision, or withdrawal from our stock. All production processes and the entire range of qualified expertise are at our disposal: from hand assembly to SMD assembly. Our state-of-the-art production and testing facilities guarantee consistent quality.

The benefits for you

- Solutions for custom tasks
- Complex component assemblies including enclosures from a single-source supplier
- Reduction of your procurement and storage of individual parts

„RockStar“ heavy-duty connectors and cable assembly

To help ensure that your switchgear cabinets and installations are put into operation without delay, Weidmüller can supply pre-fabricated components such as heavy-duty connectors. These are assembled and prewired according to your specification and are supplied ready to connect. If required, we can also supply the finished enclosure with the heavy-duty connectors already integrated. An entire spectrum of application possibilities are available with our ConCept modular connector system. This modular system enables the flexible combination of diverse modules. Custom crimping and cabling is included on request! Do you prefer a personal touch? We can laser-label your company logo and article number onto our RockStars! In total compliance with your requirements.

The benefits for you

- Special requirements with respect to font, number of characters, material and printing durability for your markers
- Prewiring of connectors saves you valuable installation time
- Modular connector system can be ordered pre-crimped

Marking

Whether multi-line labelling, white or coloured terminal markers or group designations, the Weidmüller range can cater for every marking task – fast, clear and according to European standards. However, we can also supply you with preprinted markers to match your specification. Simply tell us the type of marker you require, the colour, the printing sequence and the text, and we'll look after the rest. If required, we can also install the finished markers during assembly.

Equipment labelling

Device markers are essential for marking your electrical installations. Therefore, Weidmüller can supply rating plates designed specially for your application. A wide range of different shapes, colours, materials and fixings – riveted, screwed or bonded with adhesive – are available from which to choose. And a whole range of different fonts mean that we can handle every request.

Integration of special accessories

IIn some cases it is necessary to integrate special accessories. This is no problem for Weidmüller because we can integrate buttons, switches, warning lamps, plugs or couplings – all properly planned, fitted, connected and tested. And that includes the products of other manufacturers as well as our own. We shall also be happy to advise you on standard accessories such as hinges.

The benefits for you

- Rating plates in various materials
- Individual printing or laser engraving
- Equipment and accessories to your specification

Digital support

RailDesigner®

RailDesigner® is a Weidmüller program for planning, assembling and ordering both terminal rails and enclosures. And it's so easy to use:

- Fast acquisition of all necessary data
- Realistic-looking graphic user interface and ideal conditions for simple assembly of your terminal rails and enclosures with all the necessary components
- Simply clip on all the products you need and add accessories such as markers or cross-connectors
- To configure an individual enclosure, simply choose an enclosure type from a standard range and then add holes and other accessories to suit your requirements

These parameters form the foundation for a perfect software assistant. You can view the enclosure on the screen complete with all the configured products, and print out a hardcopy, or simply send the file to Weidmüller via e-mail in the form of an order. RailDesigner® provides you with optimum planning security and clarity during the design phase. And hence simplifies the ordering process enormously.

M-Print® PRO label designer

The comprehensive range of Weidmüller services includes the M-Print® PRO software.
This is a professional-standard, Windows®-based program for printing and ordering labels and markers that is coordinated with our current printing systems and marking materials.

M-Print® PRO enables you to design your labelling materials professionally and quickly. Texts, borders, lines, graphics, barcodes, serial numbers and photographs are all possible. The interface to RailDesigner® or your CAE system enables the transfer of all your configured data.

Online catalogue

If you have questions about the specifications and details of our products, perhaps even outside normal business hours, then our online catalogue at **http://catalog.weidmueller.com** open 24 hours a day, 365 days a year – is the perfect source of information. Besides product features and part numbers, it contains extensive additional information on all product groups. And for further information, offers and your personal contact, simply consult the Weidmüller website at **www.weidmueller.com**.

Index

Index	Index Type / Index Order No.	X.2
	Addresses worldwide	X.26

Type	Order No.	Page
A		
ADAPTER ALU STI-S	1762440000	E.6
ADAPTER ALU STI-S	1762440000	E.7
B		
BZT 1 WS 10/5	1805490000	B.35
BZT 1 ZA WS 10/5	1805520000	B.35
BZT 2 WS 10/5	1805480000	B.35
BZT 2 ZA WS 10/5	1805530000	B.35
C		
CB 1000/12.5 BLACK	7940006085	C.59
CB 1000/12.5 NATUR	7940006084	C.59
CB 120/4.5 BLACK	7940006053	C.59
CB 120/4.8 natur	7940006052	C.59
CB 120/7.6 black	7940006063	C.59
CB 120/7.6 natur	7940006062	C.59
CB 135/2.5 BLACK	7940006047	C.59
CB 135/2.5 NATUR	7940006040	C.59
CB 140/3.6 BLACK	1697900000	C.59
CB 140/3.6 NATUR	1278700000	C.59
CB 160/2.6 BLACK	7940006049	C.59
CB 160/2.6 NATUR	7940006048	C.59
CB 160/4.5 NATUR	1723540000	C.59
CB 160/4.8 BLACK	1723560000	C.59
CB 178/4.8 BLACK	1723570000	C.59
CB 178/4.8 NATUR	1723550000	C.59
CB 180/7.8 BLACK	7940006065	C.59
CB 180/7.8 NATUR	7940006064	C.59
CB 200/2.6 BLACK	7940006051	C.59
CB 200/2.6 NATUR	7940006050	C.59
CB 200/3.6 BLACK	1720660000	C.59
CB 200/3.6 NATUR	1720630000	C.59
CB 200/4.8 BLACK	1697910000	C.59
CB 200/4.8 NATUR	1278800000	C.59
CB 230/12.7 black	7940006077	C.59
CB 230/12.7 natur	7940006076	C.59
CB 240/7.6 natur	7940006066	C.59
CB 240/7.8 BLACK	7940006067	C.59
CB 250/4.8 BLACK	7940006055	C.59
CB 250/4.8 NATUR	7940006054	C.59
CB 290/3.6 BLACK	1720650000	C.59
CB 290/3.6 NATUR	1720640000	C.59
CB 290/4.8 BLACK	1697920000	C.59
CB 290/4.8 NATUR	1278900000	C.59
CB 300/7.8 BLACK	7940006069	C.59
CB 300/7.8 NATUR	7940006068	C.59
CB 360/4.8 BLACK	1697930000	C.59
CB 360/4.8 NATUR	1279000000	C.59
CB 365/7.8 BLACK	1697940000	C.59
CB 365/7.8 NATUR	1279100000	C.59
CB 370/3.6 BLACK	7940006057	C.59
CB 370/3.6 NATUR	7940006056	C.59
CB 390/4.8 BLACK	7940006059	C.59
CB 390/4.8 NATUR	7940006058	C.59
CB 430/4.8 BLACK	7940006061	C.59
CB 430/4.8 NATUR	7940006060	C.59
CB 450/7.8 BLACK	7940006071	C.59
CB 450/7.8 NATUR	7940006070	C.59
CB 480/12.7 natur	7940006078	C.59
CB 500/12.5 BLACK	7940006079	C.59
CB 540/7.8 BLACK	7940006073	C.59
CB 540/7.8 NATUR	7940006072	C.59
CB 750/7.8 BLACK	1720670000	C.59
CB 750/7.8 NATUR	1720680000	C.59
CB 780/9.0 BLACK	7940006075	C.59
CB 780/9.0 NATUR	7940006074	C.59
CB 880/12.7 natur	7940006082	C.59
CB 98/2.5 BLACK	1697890000	C.59
CB 98/2.5 NATUR	1278600000	C.59
CBDM 203/4.8 NATUR	1279300000	C.60
CBH 19/19 BLACK	1697950000	C.60
CBH 19/19 NATUR	1289200000	C.60
CBH 26.3/26.3 BLACK	1697960000	C.60
CBH 27/27 NATUR	1289400000	C.60
CBH 8.1/6.2 NATUR	1279200000	C.60
CB-R 200/7.5 BLACK	1059210000	C.60
CB-R 200/7.5 NATUR	1059200000	C.60
CB-R 250/7.5 BLACK	1059230000	C.60
CB-R 250/7.5 NATUR	1059220000	C.60
CB-R 350/7.5 BLACK	1059250000	C.60
CB-R 350/7.5 NATUR	1059240000	C.60
CC 15/17 K MC NE GE	1131920000	D.8
CC 15/17 K MC NE GR	1079540000	D.8
CC 15/17 K MC NEUTR. SI	1876580000	D.8
CC 15/17 K MC NEUTR. WS	1876590000	D.8
CC 15/17 K MC SONDERD.	1876600000	D.8
CC 15/17 MC NE GE	1131930000	D.8
CC 15/17 MC NE GR	1079530000	D.8
CC 15/17 MC NEUTRAL SI	1876610000	D.8
CC 15/17 MC NEUTRAL WS	1876570000	D.8
CC 15/17 MC SONDERD.	1876620000	D.8
CC 15/27 K MC NE GE	1131910000	D.8
CC 15/27 K MC NE GR	1079560000	D.8
CC 15/27 K MC NEUTR. SI	1876780000	D.8
CC 15/27 K MC NEUTR. WS	1876640000	D.8
CC 15/27 K MC SONDERD.	1876750000	D.8
CC 15/27 MC NE GE	1131940000	D.8
CC 15/27 MC NE GR	1079550000	D.8
CC 15/27 MC NEUTRAL SI	1876760000	D.8
CC 15/27 MC NEUTRAL WS	1876770000	D.8
CC 15/27 MC SONDERD.	1876630000	D.8
CC 15/49 K MC NE GE	1131970000	D.8
CC 15/49 K MC NE GR	1079580000	D.8
CC 15/49 K MC NEUTR. SI	1877270000	D.8
CC 15/49 K MC NEUTR. WS	1877220000	D.8
CC 15/49 K MC SONDERD.	1877230000	D.8
CC 15/49 MC NE GE	1076970000	D.8
CC 15/49 MC NE GR	1079570000	D.8
CC 15/49 MC NEUTRAL SI	1877240000	D.8
CC 15/49 MC NEUTRAL WS	1877260000	D.8
CC 15/49 MC SONDERD.	1877200000	D.8
CC 15/60 04MM MC GE	1131880000	D.9
CC 15/60 K MC NE GE	1131890000	D.8
CC 15/60 K MC NE GR	1072650000	D.8
CC 15/60 K MC NEUTR. SI	1877360000	D.8
CC 15/60 K MC NEUTR. WS	1877310000	D.8
CC 15/60 K MC SONDERD.	1877320000	D.8
CC 15/60 MC NE GE	1131960000	D.8
CC 15/60 MC NE GR	1072640000	D.8
CC 15/60 MC NEUTRAL SI	1877340000	D.8
CC 15/60 MC NEUTRAL WS	1877350000	D.8
CC 15/60 MC SONDERD.	1877300000	D.8
CC 15/60 O4MM MC NE SI	1059990000	D.9
CC 15/60 O4MM MC NE WS	1057580000	D.9
CC 30/60 K MC NE GE	1078320000	D.8
CC 30/60 K MC NE GR	1072680000	D.8
CC 30/60 K MC NE RT	1085430000	D.8
CC 30/60 K MC NEUTRAL SI	1934330000	D.8
CC 30/60 K MC NEUTRAL WS	1934390000	D.8
CC 30/60 K MC SONDERDRUCK	1934370000	D.8
CC 30/60 MC NE GE	1009320000	D.8
CC 30/60 MC NE GR	1072670000	D.8
CC 30/60 MC NEUTRAL SI	1934400000	D.8
CC 30/60 MC NEUTRAL WS	1934420000	D.8
CC 30/60 MC SONDERDRUCK	1934410000	D.8
CC 30/60 O4MM MC NE GR	1083170000	D.9
CC 30/60 O4MM MC NE WS	1083150000	D.9
CC 85/54 K MC NE GE	1138440000	D.8
CC 85/54 K MC NE GR	1138450000	D.8
CC 85/54 K MC NE WS	1138430000	D.8
CC 85/54 K MC SDR	1138470000	D.8
CC 85/54 MC NE GE	1138410000	D.8
CC 85/54 MC NE GR	1138420000	D.8
CC 85/54 MC NE WS	1138400000	D.8
CC 85/54 MC SDR	1138460000	D.8
CC-H 15/17	1790430000	D.9
CC-H 15/27	1790410000	D.9
CC-H 15/49	1790420000	D.9
CC-H 15/60	1878910000	D.9
CC-H 30/60	1934430000	D.9
CC-RAIL 1000	1790150000	D.9
CC-RAIL TRANSPARENT1000	1790160000	D.9
CENTRONICS-USB2.0 ADAPT	1965140000	E.9
CleanUnit PrintJet II	1858950000	E.3
CLI C 02-12 SDR SG	1873330000	C.23
CLI C 02-15 SDR SG	0252509999	C.23
CLI C 02-18 GE NE SG	1873741687	C.20
CLI C 02-18 SDR SG	1873749999	C.23
CLI C 02-18 WS NE SG	1873741044	C.20
CLI C 02-21 SDR SG	1873340000	C.23
CLI C 02-24 SDR SG	1912500000	C.23
CLI C 02-27 SDR SG	1912510000	C.23
CLI C 02-3 BL NE MP	0213811693	C.20
CLI C 02-3 BL NE CD	1878201693	C.20
CLI C 02-3 BL/SW - CD	1568241741	C.30
CLI C 02-3 BL/SW - MP	0252111741	C.30
CLI C 02-3 BL/SW 6 CD	1568241521	C.26
CLI C 02-3 BL/SW 6 MP	0252111521	C.26
CLI C 02-3 BL/SW N CD	1568241664	C.30
CLI C 02-3 BL/SW N MP	0252111664	C.30
CLI C 02-3 BR NE CD	1568241692	C.20
CLI C 02-3 BR/WS 1 CD	1568241506	C.26
CLI C 02-3 BR/WS 1 MP	0252111506	C.26
CLI C 02-3 GE NE CD	1568241058	C.20
CLI C 02-3 GE NE MP	0213811687	C.20
CLI C 02-3 GE/SW / MP	0252111742	C.30
CLI C 02-3 GE/SW - CD	1568241740	C.30
CLI C 02-3 GE/SW - MP	0252111740	C.30
CLI C 02-3 GE/SW . CD	1568241748	C.30
CLI C 02-3 GE/SW . MP	0252111748	C.30
CLI C 02-3 GE/SW / CD	1568241742	C.30
CLI C 02-3 GE/SW : CD	1568241750	C.30
CLI C 02-3 GE/SW : MP	0252111750	C.30
CLI C 02-3 GE/SW + CD	1568241738	C.30
CLI C 02-3 GE/SW + MP	0252111738	C.30
CLI C 02-3 GE/SW = CD	1568241751	C.30
CLI C 02-3 GE/SW = MP	0252111751	C.30
CLI C 02-3 GE/SW 0 CD	1568241502	C.29
CLI C 02-3 GE/SW 0 MP	0252111502	C.29
CLI C 02-3 GE/SW 1 CD	1568241505	C.29
CLI C 02-3 GE/SW 1 MP	0252111505	C.29
CLI C 02-3 GE/SW 2 CD	1568241508	C.29
CLI C 02-3 GE/SW 2 MP	0252111508	C.29
CLI C 02-3 GE/SW 3 CD	1568241511	C.29
CLI C 02-3 GE/SW 3 MP	0252111511	C.29
CLI C 02-3 GE/SW 4 CD	1568241514	C.26
CLI C 02-3 GE/SW 4 CD	1568241514	C.29
CLI C 02-3 GE/SW 4 MP	0252111514	C.26
CLI C 02-3 GE/SW 4 MP	0252111514	C.29
CLI C 02-3 GE/SW 5 CD	1568241517	C.29
CLI C 02-3 GE/SW 5 MP	0252111517	C.29
CLI C 02-3 GE/SW 6 CD	1568241520	C.29
CLI C 02-3 GE/SW 6 MP	0252111520	C.29
CLI C 02-3 GE/SW 7 CD	1568241523	C.29
CLI C 02-3 GE/SW 7 MP	0252111523	C.29
CLI C 02-3 GE/SW 8 CD	1568241526	C.29
CLI C 02-3 GE/SW 8 MP	0252111526	C.29
CLI C 02-3 GE/SW 9 CD	1568241529	C.29
CLI C 02-3 GE/SW 9 MP	0252111529	C.29
CLI C 02-3 GE/SW A CD	1568241637	C.29
CLI C 02-3 GE/SW Ä CD	1568241056	C.30
CLI C 02-3 GE/SW Å CD	1568241055	C.30
CLI C 02-3 GE/SW A MP	0252111637	C.29
CLI C 02-3 GE/SW a MP	0252111700	C.30
CLI C 02-3 GE/SW Ä MP	0252111697	C.30
CLI C 02-3 GE/SW Å MP	0252111699	C.30
CLI C 02-3 GE/SW AC CD	1568241752	C.30
CLI C 02-3 GE/SW AC MP	0252111752	C.30
CLI C 02-3 GE/SW Æ CD	1568241735	C.30
CLI C 02-3 GE/SW B CD	1568241639	C.29
CLI C 02-3 GE/SW B MP	0252111639	C.29
CLI C 02-3 GE/SW b MP	0252111701	C.30
CLI C 02-3 GE/SW C CD	1568241641	C.29
CLI C 02-3 GE/SW C MP	0252111641	C.29
CLI C 02-3 GE/SW c MP	0252111702	C.30
CLI C 02-3 GE/SW D CD	1568241643	C.29
CLI C 02-3 GE/SW D MP	0252111643	C.29
CLI C 02-3 GE/SW d MP	0252111703	C.30
CLI C 02-3 GE/SW E CD	1568241645	C.29
CLI C 02-3 GE/SW E MP	0252111645	C.29
CLI C 02-3 GE/SW e MP	0252111704	C.30
CLI C 02-3 GE/SW ET CD	1568241746	C.30
CLI C 02-3 GE/SW ET MP	0252111746	C.30
CLI C 02-3 GE/SW F CD	1568241647	C.29
CLI C 02-3 GE/SW F MP	0252111647	C.29
CLI C 02-3 GE/SW f MP	0252111705	C.30
CLI C 02-3 GE/SW G CD	1568241649	C.29
CLI C 02-3 GE/SW G MP	0252111649	C.29
CLI C 02-3 GE/SW g MP	0252111706	C.30
CLI C 02-3 GE/SW H CD	1568241651	C.29
CLI C 02-3 GE/SW H MP	0252111651	C.29
CLI C 02-3 GE/SW h MP	0252111707	C.30
CLI C 02-3 GE/SW I CD	1568241653	C.29
CLI C 02-3 GE/SW I MP	0252111653	C.29
CLI C 02-3 GE/SW i MP	0252111708	C.30
CLI C 02-3 GE/SW J CD	1568241655	C.29
CLI C 02-3 GE/SW J MP	0252111655	C.29
CLI C 02-3 GE/SW j MP	0252111709	C.30
CLI C 02-3 GE/SW K CD	1568241657	C.29
CLI C 02-3 GE/SW K MP	0252111657	C.29
CLI C 02-3 GE/SW k MP	0252111710	C.30
CLI C 02-3 GE/SW L CD	1568241659	C.29
CLI C 02-3 GE/SW L MP	0252111659	C.29
CLI C 02-3 GE/SW l MP	0252111711	C.30
CLI C 02-3 GE/SW M CD	1568241661	C.29
CLI C 02-3 GE/SW M MP	0252111661	C.29
CLI C 02-3 GE/SW m MP	0252111712	C.30
CLI C 02-3 GE/SW N CD	1568241663	C.29
CLI C 02-3 GE/SW N MP	0252111663	C.29
CLI C 02-3 GE/SW n MP	0252111713	C.30
CLI C 02-3 GE/SW O CD	1568241665	C.29
CLI C 02-3 GE/SW Ö CD	1568241057	C.30
CLI C 02-3 GE/SW Ø CD	1568241736	C.30
CLI C 02-3 GE/SW O MP	0252111665	C.29
CLI C 02-3 GE/SW o MP	0252111714	C.30
CLI C 02-3 GE/SW Ö MP	0252111695	C.30
CLI C 02-3 GE/SW P CD	1568241667	C.29
CLI C 02-3 GE/SW P MP	0252111667	C.29
CLI C 02-3 GE/SW p MP	0252111715	C.30
CLI C 02-3 GE/SW PET. CD	1568241747	C.30
CLI C 02-3 GE/SW PET. MP	0252111747	C.30
CLI C 02-3 GE/SW Q CD	1568241669	C.29
CLI C 02-3 GE/SW Q MP	0252111669	C.29
CLI C 02-3 GE/SW q MP	0252111716	C.30
CLI C 02-3 GE/SW R CD	1568241671	C.29
CLI C 02-3 GE/SW R MP	0252111671	C.29
CLI C 02-3 GE/SW r MP	0252111717	C.30
CLI C 02-3 GE/SW S CD	1568241673	C.29
CLI C 02-3 GE/SW S MP	0252111673	C.29
CLI C 02-3 GE/SW s MP	0252111718	C.30
CLI C 02-3 GE/SW T CD	1568241676	C.29
CLI C 02-3 GE/SW T MP	0252111676	C.29
CLI C 02-3 GE/SW t MP	0252111719	C.30
CLI C 02-3 GE/SW U CD	1568241679	C.29
CLI C 02-3 GE/SW U MP	0252111679	C.29
CLI C 02-3 GE/SW u MP	0252111720	C.30
CLI C 02-3 GE/SW V CD	1568241681	C.29
CLI C 02-3 GE/SW V MP	0252111681	C.29
CLI C 02-3 GE/SW v MP	0252111721	C.30
CLI C 02-3 GE/SW W CD	1568241683	C.29
CLI C 02-3 GE/SW W MP	0252111683	C.29
CLI C 02-3 GE/SW w MP	0252111722	C.30
CLI C 02-3 GE/SW X CD	1568241687	C.29
CLI C 02-3 GE/SW X MP	0252111687	C.29
CLI C 02-3 GE/SW x MP	0252111723	C.30
CLI C 02-3 GE/SW Y CD	1568241696	C.29
CLI C 02-3 GE/SW Y MP	0252111696	C.29
CLI C 02-3 GE/SW y MP	0252111724	C.30
CLI C 02-3 GE/SW Z CD	1568241698	C.29
CLI C 02-3 GE/SW Z MP	0252111698	C.29
CLI C 02-3 GE/SW z MP	0252111725	C.30
CLI C 02-3 GN NE CD	1568241688	C.20
CLI C 02-3 GN/SW 5 CD	1568241518	C.26
CLI C 02-3 GN/SW 5 MP	0252111518	C.26
CLI C 02-3 GR NE CD	1878201691	C.20
CLI C 02-3 GR NE MP	1869351691	C.20
CLI C 02-3 GR/SW 0 CD	1878201502	C.29
CLI C 02-3 GR/SW 0 MP	1869351502	C.29
CLI C 02-3 GR/SW 1 CD	1878201505	C.29
CLI C 02-3 GR/SW 1 MP	1869351505	C.29
CLI C 02-3 GR/SW 2 CD	1878201508	C.29
CLI C 02-3 GR/SW 2 MP	1869351508	C.29
CLI C 02-3 GR/SW 3 CD	1878201511	C.29
CLI C 02-3 GR/SW 3 MP	1869351511	C.29
CLI C 02-3 GR/SW 4 CD	1878201514	C.29
CLI C 02-3 GR/SW 4 MP	1869351514	C.29
CLI C 02-3 GR/SW 5 CD	1878201517	C.29
CLI C 02-3 GR/SW 5 MP	1869351517	C.29
CLI C 02-3 GR/SW 6 CD	1878201520	C.29
CLI C 02-3 GR/SW 6 MP	1869351520	C.29
CLI C 02-3 GR/SW 7 CD	1878201523	C.29
CLI C 02-3 GR/SW 7 MP	1869351523	C.29
CLI C 02-3 GR/SW 8 CD	1568241527	C.26
CLI C 02-3 GR/SW 8 CD	1568241527	C.29
CLI C 02-3 GR/SW 8 MP	0252111527	C.26
CLI C 02-3 GR/SW 8 MP	0252111527	C.29
CLI C 02-3 GR/SW 9 CD	1878201529	C.29
CLI C 02-3 GR/SW 9 MP	1869351529	C.29
CLI C 02-3 OR NE CD	1568241690	C.20
CLI C 02-3 OR/SW 3 CD	1568241512	C.26
CLI C 02-3 OR/SW 3 MP	0252111512	C.26
CLI C 02-3 RS NE CD	1568241695	C.20
CLI C 02-3 RT NE CD	1568241686	C.20
CLI C 02-3 RT NE MP	0213811686	C.20
CLI C 02-3 RT/SW + CD	1568241737	C.30
CLI C 02-3 RT/SW + MP	0252111737	C.30
CLI C 02-3 RT/SW 2 CD	1568241509	C.26
CLI C 02-3 RT/SW 2 MP	0252111509	C.26
CLI C 02-3 SDR CD	1568249999	C.23
CLI C 02-3 SDR SG	1912550000	C.23
CLI C 02-3 SW NE CD	1568241694	C.20
CLI C 02-3 SW/WS 0 CD	1568241503	C.26
CLI C 02-3 SW/WS 0 MP	0252111503	C.26
CLI C 02-3 VI NE CD	1568241689	C.20
CLI C 02-3 VI/SW 7 CD	1568241524	C.26
CLI C 02-3 VI/SW 7 MP	0252111524	C.26
CLI C 02-3 WS NE CD	1869821044	C.20
CLI C 02-3 WS NE MP	0213811044	C.20
CLI C 02-3 WS/SW - CD	1869821740	C.30
CLI C 02-3 WS/SW - MP	1869991740	C.30
CLI C 02-3 WS/SW . CD	1869821748	C.30
CLI C 02-3 WS/SW . MP	1869991748	C.30
CLI C 02-3 WS/SW / CD	1869821742	C.30
CLI C 02-3 WS/SW / MP	1869991742	C.30
CLI C 02-3 WS/SW : CD	1869821750	C.30
CLI C 02-3 WS/SW : MP	1869991750	C.30
CLI C 02-3 WS/SW + CD	1869821738	C.30
CLI C 02-3 WS/SW + MP	1869991738	C.30
CLI C 02-3 WS/SW = CD	1869821751	C.30
CLI C 02-3 WS/SW = MP	1869991751	C.30
CLI C 02-3 WS/SW 0 CD	1869821502	C.29
CLI C 02-3 WS/SW 0 MP	0252111000	C.29
CLI C 02-3 WS/SW 1 CD	1869821505	C.29
CLI C 02-3 WS/SW 1 MP	0252110001	C.29
CLI C 02-3 WS/SW 2 CD	1869821508	C.29
CLI C 02-3 WS/SW 2 MP	0252110002	C.29
CLI C 02-3 WS/SW 3 CD	1869821511	C.29
CLI C 02-3 WS/SW 3 MP	0252110003	C.29
CLI C 02-3 WS/SW 4 CD	1869821514	C.29
CLI C 02-3 WS/SW 4 MP	0252110004	C.29
CLI C 02-3 WS/SW 5 CD	1869821517	C.29
CLI C 02-3 WS/SW 5 MP	0252110005	C.29
CLI C 02-3 WS/SW 6 CD	1869821520	C.29
CLI C 02-3 WS/SW 6 MP	0252110006	C.29
CLI C 02-3 WS/SW 7 CD	1869821523	C.29
CLI C 02-3 WS/SW 7 MP	0252110007	C.29
CLI C 02-3 WS/SW 8 CD	1869821526	C.29
CLI C 02-3 WS/SW 8 MP	0252110008	C.29
CLI C 02-3 WS/SW 9 CD	1568241530	C.26
CLI C 02-3 WS/SW 9 CD	1568241530	C.29
CLI C 02-3 WS/SW 9 MP	0252111530	C.26
CLI C 02-3 WS/SW 9 MP	0252111530	C.29
CLI C 02-3 WS/SW A CD	1869821637	C.29
CLI C 02-3 WS/SW Ä CD	1869821697	C.30
CLI C 02-3 WS/SW Å CD	1869821699	C.30
CLI C 02-3 WS/SW A MP	1869991637	C.29
CLI C 02-3 WS/SW Ä MP	1869991697	C.30
CLI C 02-3 WS/SW Å MP	1869991699	C.30
CLI C 02-3 WS/SW AC CD	1869821752	C.30
CLI C 02-3 WS/SW AC MP	1869991752	C.30
CLI C 02-3 WS/SW B CD	1869821639	C.29
CLI C 02-3 WS/SW B MP	1869991639	C.29
CLI C 02-3 WS/SW C CD	1869821641	C.29
CLI C 02-3 WS/SW C MP	1869991641	C.29
CLI C 02-3 WS/SW D CD	1869821643	C.29
CLI C 02-3 WS/SW D MP	1869991643	C.29

Type	Order No.	Page
CLI C 02-3 WS/SW E CD	1869821645	C.29
CLI C 02-3 WS/SW E MP	1869991645	C.29
CLI C 02-3 WS/SW ET CD	1869821746	C.30
CLI C 02-3 WS/SW ET MP	1869991746	C.30
CLI C 02-3 WS/SW F CD	1869821647	C.29
CLI C 02-3 WS/SW F MP	1869991647	C.29
CLI C 02-3 WS/SW G CD	1869821649	C.29
CLI C 02-3 WS/SW G MP	1869991649	C.29
CLI C 02-3 WS/SW H CD	1869821651	C.29
CLI C 02-3 WS/SW H MP	1869991651	C.29
CLI C 02-3 WS/SW I CD	1869821653	C.29
CLI C 02-3 WS/SW I MP	1869991653	C.29
CLI C 02-3 WS/SW J CD	1869821655	C.29
CLI C 02-3 WS/SW J MP	1869991655	C.29
CLI C 02-3 WS/SW K CD	1869821657	C.29
CLI C 02-3 WS/SW K MP	1869991657	C.29
CLI C 02-3 WS/SW L CD	1869821659	C.29
CLI C 02-3 WS/SW L MP	1869991659	C.29
CLI C 02-3 WS/SW M CD	1869821661	C.29
CLI C 02-3 WS/SW M MP	1869991661	C.29
CLI C 02-3 WS/SW N CD	1869821663	C.29
CLI C 02-3 WS/SW N MP	1869991663	C.29
CLI C 02-3 WS/SW O CD	1869821665	C.29
CLI C 02-3 WS/SW Ö CD	1869821695	C.30
CLI C 02-3 WS/SW O MP	1869991665	C.29
CLI C 02-3 WS/SW Ö MP	1869991695	C.30
CLI C 02-3 WS/SW P CD	1869821667	C.29
CLI C 02-3 WS/SW P MP	1869991667	C.29
CLI C 02-3 WS/SW PET. CD	1869821747	C.30
CLI C 02-3 WS/SW PET. MP	1869991747	C.30
CLI C 02-3 WS/SW Q CD	1869821669	C.29
CLI C 02-3 WS/SW Q MP	1869991669	C.29
CLI C 02-3 WS/SW R CD	1869821671	C.29
CLI C 02-3 WS/SW R MP	1869991671	C.29
CLI C 02-3 WS/SW S CD	1869821673	C.29
CLI C 02-3 WS/SW S MP	1869991673	C.29
CLI C 02-3 WS/SW T CD	1869821676	C.29
CLI C 02-3 WS/SW T MP	1869991676	C.29
CLI C 02-3 WS/SW U CD	1869821679	C.29
CLI C 02-3 WS/SW U MP	1869991679	C.29
CLI C 02-3 WS/SW V CD	1869821681	C.29
CLI C 02-3 WS/SW V MP	1869991681	C.29
CLI C 02-3 WS/SW W CD	1869821683	C.29
CLI C 02-3 WS/SW W MP	1869991683	C.29
CLI C 02-3 WS/SW X CD	1869821687	C.29
CLI C 02-3 WS/SW X MP	1869991687	C.29
CLI C 02-3 WS/SW Y CD	1869821696	C.29
CLI C 02-3 WS/SW Y MP	1869991696	C.29
CLI C 02-3 WS/SW Z CD	1869821698	C.29
CLI C 02-3 WS/SW Z MP	1869991698	C.29
CLI C 02-30 SDR SG	1912580000	C.23
CLI C 02-33 SDR SG	1912590000	C.23
CLI C 02-36 SDR SG	1912600000	C.23
CLI C 02-39 SDR SG	1912610000	C.23
CLI C 02-6 GE NE CD	1568241059	C.20
CLI C 02-6 GE/SW A1 CD	1568241726	C.31
CLI C 02-6 GE/SW A1 MP	0252111726	C.31
CLI C 02-6 GE/SW A2 CD	1568241727	C.31
CLI C 02-6 GE/SW A2 MP	0252111727	C.31
CLI C 02-6 GE/SW L1 CD	1568241728	C.31
CLI C 02-6 GE/SW L1 MP	0252111728	C.31
CLI C 02-6 GE/SW L2 CD	1568241729	C.31
CLI C 02-6 GE/SW L2 MP	0252111729	C.31
CLI C 02-6 GE/SW L3 CD	1568241730	C.31
CLI C 02-6 GE/SW L3 MP	0252111730	C.31
CLI C 02-6 GE/SW VS CD	1568241731	C.31
CLI C 02-6 SDR CD	1869999999	C.23
CLI C 02-6 SDR SG	1912620000	C.23
CLI C 02-6 WS/SW A1 CD	1869821726	C.31
CLI C 02-6 WS/SW A1 MP	1869991726	C.31
CLI C 02-6 WS/SW A2 CD	1869821727	C.31
CLI C 02-6 WS/SW A2 MP	1869991727	C.31
CLI C 02-6 WS/SW L1 CD	1869821728	C.31
CLI C 02-6 WS/SW L1 MP	1869991728	C.31
CLI C 02-6 WS/SW L2 CD	1869821729	C.31
CLI C 02-6 WS/SW L2 MP	1869991729	C.31
CLI C 02-6 WS/SW L3 CD	1869821730	C.31
CLI C 02-6 WS/SW L3 MP	1869991730	C.31
CLI C 02-9 GE NE CD	1568241060	C.20
CLI C 02-9 GE/SW PEN CD	1568241734	C.31
CLI C 02-9 GE/SW PEN MP	0252111734	C.31
CLI C 02-9 SDR CD	1899290000	C.23
CLI C 02-9 SDR SG	1869829999	C.23
CLI C 02-9 WS/SW PEN CD	1869821734	C.31
CLI C 02-9 WS/SW PEN MP	1869991734	C.31
CLI C 1-12 GE NE SG	1871841687	C.21
CLI C 1-12 SDR SG	1873350000	C.23
CLI C 1-12 WS NE SG	1871841044	C.21
CLI C 1-15 GE NE SG	1871791687	C.21
CLI C 1-15 SDR SG	1873360000	C.23
CLI C 1-15 WS NE SG	1871791044	C.21
CLI C 1-18 GE NE SG	1871801687	C.21
CLI C 1-18 SDR SG	1871809999	C.23
CLI C 1-18 WS NE SG	1871801044	C.21
CLI C 1-21 GE NE SG	1913311687	C.21
CLI C 1-21 SDR SG	1873370000	C.23
CLI C 1-24 SDR SG	1912630000	C.23
CLI C 1-24 WS NE SG	1871811044	C.21
CLI C 1-27 SDR SG	1912640000	C.23
CLI C 1-3 BL NE CD	1568251693	C.21
CLI C 1-3 BL NE MP	0171111693	C.21
CLI C 1-3 BL/SW - CD	1568251741	C.34
CLI C 1-3 BL/SW - MP	0252611741	C.34
CLI C 1-3 BL/SW 6 CD	1568251521	C.26
CLI C 1-3 BL/SW 6 MP	0252611521	C.26
CLI C 1-3 BL/SW N CD	1568251664	C.34
CLI C 1-3 BL/SW N MP	0252611664	C.34
CLI C 1-3 BR NE CD	1568251692	C.21
CLI C 1-3 BR/WS 1 CD	1568251506	C.26
CLI C 1-3 BR/WS 1 MP	0252611506	C.26
CLI C 1-3 GE NE CD	1568251699	C.21
CLI C 1-3 GE NE MP	0171111687	C.21
CLI C 1-3 GE/SW - CD	1568251740	C.34
CLI C 1-3 GE/SW - MP	0252611740	C.34
CLI C 1-3 GE/SW * CD	1568251753	C.34
CLI C 1-3 GE/SW . CD	1568251748	C.34
CLI C 1-3 GE/SW . MP	0252611748	C.34
CLI C 1-3 GE/SW / CD	1568251742	C.34
CLI C 1-3 GE/SW / MP	0252611742	C.34
CLI C 1-3 GE/SW : CD	1568251750	C.34
CLI C 1-3 GE/SW : MP	0252611750	C.34
CLI C 1-3 GE/SW + CD	1568251738	C.34
CLI C 1-3 GE/SW + MP	0252611738	C.34
CLI C 1-3 GE/SW = CD	1568251751	C.34
CLI C 1-3 GE/SW = MP	0252611751	C.34
CLI C 1-3 GE/SW 0 CD	1568251502	C.32
CLI C 1-3 GE/SW 0 MP	0252611502	C.32
CLI C 1-3 GE/SW 1 CD	1568251505	C.32
CLI C 1-3 GE/SW 1 MP	0252611505	C.32
CLI C 1-3 GE/SW 2 CD	1568251508	C.32
CLI C 1-3 GE/SW 2 MP	0252611508	C.32
CLI C 1-3 GE/SW 3 CD	1568251511	C.32
CLI C 1-3 GE/SW 3 MP	0252611511	C.32
CLI C 1-3 GE/SW 4 CD	1568251514	C.26
CLI C 1-3 GE/SW 4 CD	1568251514	C.32
CLI C 1-3 GE/SW 4 MP	0252611514	C.26
CLI C 1-3 GE/SW 4 MP	0252611514	C.32
CLI C 1-3 GE/SW 5 CD	1568251517	C.32
CLI C 1-3 GE/SW 5 MP	0252611517	C.32
CLI C 1-3 GE/SW 6 CD	1568251520	C.32
CLI C 1-3 GE/SW 6 MP	0252611520	C.32
CLI C 1-3 GE/SW 7 CD	1568251523	C.32
CLI C 1-3 GE/SW 7 MP	0252611523	C.32
CLI C 1-3 GE/SW 8 CD	1568251526	C.32
CLI C 1-3 GE/SW 8 MP	0252611526	C.32
CLI C 1-3 GE/SW 9 CD	1568251529	C.32
CLI C 1-3 GE/SW 9 MP	0252611529	C.32
CLI C 1-3 GE/SW A CD	1568251637	C.32
CLI C 1-3 GE/SW a CD	1568251700	C.33
CLI C 1-3 GE/SW Ä CD	1568251797	C.34
CLI C 1-3 GE/SW Å CD	1568251799	C.34
CLI C 1-3 GE/SW A MP	0252611637	C.32
CLI C 1-3 GE/SW a MP	0252611700	C.33
CLI C 1-3 GE/SW Ä MP	0252611697	C.34
CLI C 1-3 GE/SW Å MP	0252611699	C.34
CLI C 1-3 GE/SW AC CD	1568251752	C.34
CLI C 1-3 GE/SW AC MP	0252611752	C.34
CLI C 1-3 GE/SW Æ CD	1568251735	C.34
CLI C 1-3 GE/SW B CD	1568251639	C.32
CLI C 1-3 GE/SW b CD	1568251701	C.33
CLI C 1-3 GE/SW B MP	0252611639	C.32
CLI C 1-3 GE/SW b MP	0252611701	C.33
CLI C 1-3 GE/SW C CD	1568251641	C.32
CLI C 1-3 GE/SW c CD	1568251702	C.33
CLI C 1-3 GE/SW C MP	0252611641	C.32
CLI C 1-3 GE/SW c MP	0252611702	C.33
CLI C 1-3 GE/SW D CD	1568251643	C.32
CLI C 1-3 GE/SW d CD	1568251703	C.33
CLI C 1-3 GE/SW D MP	0252611643	C.32
CLI C 1-3 GE/SW d MP	0252611703	C.33
CLI C 1-3 GE/SW E CD	1568251645	C.32
CLI C 1-3 GE/SW e CD	1568251704	C.33
CLI C 1-3 GE/SW E MP	0252611645	C.32
CLI C 1-3 GE/SW e MP	0252611704	C.33
CLI C 1-3 GE/SW ET CD	1568251746	C.34
CLI C 1-3 GE/SW ET MP	0252611746	C.34
CLI C 1-3 GE/SW F CD	1568251647	C.32
CLI C 1-3 GE/SW f CD	1568251705	C.33
CLI C 1-3 GE/SW F MP	0252611647	C.32
CLI C 1-3 GE/SW f MP	0252611705	C.33
CLI C 1-3 GE/SW G CD	1568251649	C.32
CLI C 1-3 GE/SW g CD	1568251706	C.33
CLI C 1-3 GE/SW G MP	0252611649	C.32
CLI C 1-3 GE/SW g MP	0252611706	C.33
CLI C 1-3 GE/SW H CD	1568251651	C.32
CLI C 1-3 GE/SW h CD	1568251707	C.33
CLI C 1-3 GE/SW H MP	0252611651	C.32
CLI C 1-3 GE/SW h MP	0252611707	C.33
CLI C 1-3 GE/SW I CD	1568251653	C.32
CLI C 1-3 GE/SW i CD	1568251708	C.33
CLI C 1-3 GE/SW I MP	0252611653	C.32
CLI C 1-3 GE/SW i MP	0252611708	C.33
CLI C 1-3 GE/SW J CD	1568251655	C.32
CLI C 1-3 GE/SW j CD	1568251709	C.33
CLI C 1-3 GE/SW J MP	0252611655	C.32
CLI C 1-3 GE/SW j MP	0252611709	C.33
CLI C 1-3 GE/SW K CD	1568251657	C.32
CLI C 1-3 GE/SW k CD	1568251710	C.33
CLI C 1-3 GE/SW K MP	0252611657	C.32
CLI C 1-3 GE/SW k MP	0252611710	C.33
CLI C 1-3 GE/SW L CD	1568251659	C.32
CLI C 1-3 GE/SW l CD	1568251711	C.33
CLI C 1-3 GE/SW L MP	0252611659	C.32
CLI C 1-3 GE/SW l MP	0252611711	C.33
CLI C 1-3 GE/SW M CD	1568251661	C.32
CLI C 1-3 GE/SW m CD	1568251712	C.33
CLI C 1-3 GE/SW M MP	0252611661	C.32
CLI C 1-3 GE/SW m MP	0252611712	C.33
CLI C 1-3 GE/SW N CD	1568251663	C.32
CLI C 1-3 GE/SW n CD	1568251713	C.33
CLI C 1-3 GE/SW N MP	0252611663	C.32
CLI C 1-3 GE/SW n MP	0252611713	C.33
CLI C 1-3 GE/SW O CD	1568251665	C.32
CLI C 1-3 GE/SW o CD	1568251714	C.33
CLI C 1-3 GE/SW Ö CD	1568251795	C.34
CLI C 1-3 GE/SW Ø CD	1568251736	C.34
CLI C 1-3 GE/SW O MP	0252611665	C.32
CLI C 1-3 GE/SW o MP	0252611714	C.33
CLI C 1-3 GE/SW Ö MP	0252611695	C.34
CLI C 1-3 GE/SW P CD	1568251667	C.32
CLI C 1-3 GE/SW p CD	1568251715	C.33
CLI C 1-3 GE/SW P MP	0252611667	C.32
CLI C 1-3 GE/SW p MP	0252611715	C.33
CLI C 1-3 GE/SW PET. CD	1568251747	C.34
CLI C 1-3 GE/SW PET. MP	0252611747	C.34
CLI C 1-3 GE/SW Q CD	1568251669	C.32
CLI C 1-3 GE/SW q CD	1568251716	C.33
CLI C 1-3 GE/SW Q MP	0252611669	C.32
CLI C 1-3 GE/SW q MP	0252611716	C.33
CLI C 1-3 GE/SW R CD	1568251671	C.32
CLI C 1-3 GE/SW r CD	1568251717	C.33
CLI C 1-3 GE/SW R MP	0252611671	C.32
CLI C 1-3 GE/SW r MP	0252611717	C.33
CLI C 1-3 GE/SW S CD	1568251673	C.32
CLI C 1-3 GE/SW s CD	1568251718	C.33
CLI C 1-3 GE/SW S MP	0252611673	C.32
CLI C 1-3 GE/SW s MP	0252611718	C.33
CLI C 1-3 GE/SW T CD	1568251676	C.32
CLI C 1-3 GE/SW t CD	1568251719	C.33
CLI C 1-3 GE/SW T MP	0252611676	C.32
CLI C 1-3 GE/SW t MP	0252611719	C.33
CLI C 1-3 GE/SW U CD	1568251679	C.32
CLI C 1-3 GE/SW u CD	1568251720	C.33
CLI C 1-3 GE/SW U MP	0252611679	C.32
CLI C 1-3 GE/SW u MP	0252611720	C.33
CLI C 1-3 GE/SW V CD	1568251681	C.32
CLI C 1-3 GE/SW v CD	1568251721	C.33
CLI C 1-3 GE/SW V MP	0252611681	C.32
CLI C 1-3 GE/SW v MP	0252611721	C.33
CLI C 1-3 GE/SW W CD	1568251683	C.32
CLI C 1-3 GE/SW w CD	1568251722	C.33
CLI C 1-3 GE/SW W MP	0252611683	C.32
CLI C 1-3 GE/SW w MP	0252611722	C.33
CLI C 1-3 GE/SW X CD	1568251687	C.32
CLI C 1-3 GE/SW x CD	1568251723	C.33
CLI C 1-3 GE/SW X MP	0252611687	C.32
CLI C 1-3 GE/SW x MP	0252611723	C.33
CLI C 1-3 GE/SW Y CD	1568251696	C.32
CLI C 1-3 GE/SW y CD	1568251724	C.33
CLI C 1-3 GE/SW Y MP	0252611696	C.32
CLI C 1-3 GE/SW y MP	0252611724	C.33
CLI C 1-3 GE/SW Z CD	1568251698	C.32
CLI C 1-3 GE/SW z CD	1568251725	C.33
CLI C 1-3 GE/SW Z MP	0252611698	C.32
CLI C 1-3 GE/SW z MP	0252611725	C.33
CLI C 1-3 GN NE CD	1568251688	C.21
CLI C 1-3 GN NE MP	0171111688	C.21
CLI C 1-3 GN/SW 5 CD	1568251518	C.26
CLI C 1-3 GN/SW 5 MP	0252611518	C.26
CLI C 1-3 GR NE CD	1568251691	C.21
CLI C 1-3 GR NE MP	0171111691	C.21
CLI C 1-3 GR/SW - MP	1869181740	C.34
CLI C 1-3 GR/SW 0 CD	1878171502	C.32
CLI C 1-3 GR/SW 0 MP	1869181502	C.32
CLI C 1-3 GR/SW 1 CD	1878171505	C.32
CLI C 1-3 GR/SW 1 MP	1869181505	C.32
CLI C 1-3 GR/SW 2 CD	1878171508	C.32
CLI C 1-3 GR/SW 2 MP	1869181508	C.32
CLI C 1-3 GR/SW 3 CD	1878171511	C.32
CLI C 1-3 GR/SW 3 MP	1869181511	C.32
CLI C 1-3 GR/SW 4 CD	1878171514	C.32
CLI C 1-3 GR/SW 4 MP	1869181514	C.32
CLI C 1-3 GR/SW 5 CD	1878171517	C.32
CLI C 1-3 GR/SW 5 MP	1869181517	C.32
CLI C 1-3 GR/SW 6 CD	1878171520	C.32
CLI C 1-3 GR/SW 6 MP	1869181520	C.32
CLI C 1-3 GR/SW 7 CD	1878171523	C.32
CLI C 1-3 GR/SW 7 MP	1869181523	C.32
CLI C 1-3 GR/SW 8 CD	1568251527	C.26
CLI C 1-3 GR/SW 8 CD	1568251527	C.32
CLI C 1-3 GR/SW 8 MP	0252611527	C.26
CLI C 1-3 GR/SW 8 MP	0252611527	C.32
CLI C 1-3 GR/SW 9 CD	1878171529	C.32
CLI C 1-3 GR/SW 9 MP	1869181529	C.32
CLI C 1-3 OR NE CD	1568251690	C.21
CLI C 1-3 OR/SW 3 CD	1568251512	C.26
CLI C 1-3 OR/SW 3 MP	0252611512	C.26
CLI C 1-3 RS NE CD	1568251695	C.21
CLI C 1-3 RT NE CD	1568251686	C.21
CLI C 1-3 RT NE MP	0171111686	C.21
CLI C 1-3 RT/SW + CD	1568251737	C.34
CLI C 1-3 RT/SW + MP	0252611737	C.34
CLI C 1-3 RT/SW 2 CD	1568251509	C.26
CLI C 1-3 RT/SW 2 MP	0252611509	C.26
CLI C 1-3 SDR CD	1568259999	C.23
CLI C 1-3 SDR SG	1912650000	C.23
CLI C 1-3 SW NE CD	1568251694	C.21
CLI C 1-3 SW/WS 0 CD	1568251503	C.26
CLI C 1-3 SW/WS 0 MP	0252611503	C.26
CLI C 1-3 SW/WS 0 MP	0252611503	C.32
CLI C 1-3 SW/WS 1 MP	1856620001	C.32
CLI C 1-3 SW/WS 2 MP	1856620002	C.32
CLI C 1-3 SW/WS 3 MP	1856620003	C.32
CLI C 1-3 SW/WS 4 MP	1856620004	C.32
CLI C 1-3 SW/WS 5 MP	1856620005	C.32
CLI C 1-3 SW/WS 6 MP	1856620006	C.32
CLI C 1-3 SW/WS 7 MP	1856620007	C.32
CLI C 1-3 SW/WS 8 MP	1856620008	C.32
CLI C 1-3 SW/WS 9 MP	1856620009	C.32
CLI C 1-3 SW/WS A MP	1856620011	C.33
CLI C 1-3 SW/WS B MP	1856620012	C.33
CLI C 1-3 SW/WS C MP	1856620013	C.33
CLI C 1-3 SW/WS D MP	1856620014	C.33
CLI C 1-3 SW/WS E MP	1856620015	C.33
CLI C 1-3 SW/WS F MP	1856620016	C.33
CLI C 1-3 SW/WS G MP	1856620017	C.33
CLI C 1-3 SW/WS H MP	1856620018	C.33
CLI C 1-3 SW/WS I MP	1856620019	C.33
CLI C 1-3 SW/WS J MP	1856620020	C.33
CLI C 1-3 SW/WS K MP	1856620021	C.33
CLI C 1-3 SW/WS L MP	1856620022	C.33
CLI C 1-3 SW/WS M MP	1856620023	C.33
CLI C 1-3 SW/WS N MP	1856620024	C.33
CLI C 1-3 SW/WS O MP	1856620025	C.33
CLI C 1-3 SW/WS P MP	1856620026	C.33
CLI C 1-3 SW/WS Q MP	1856620027	C.33
CLI C 1-3 SW/WS R MP	1856620028	C.33
CLI C 1-3 SW/WS S MP	1856620029	C.33
CLI C 1-3 SW/WS T MP	1856620030	C.33
CLI C 1-3 SW/WS U MP	1856620031	C.33
CLI C 1-3 SW/WS V MP	1856620032	C.33
CLI C 1-3 SW/WS W MP	1856620033	C.33
CLI C 1-3 SW/WS X MP	1856620034	C.33
CLI C 1-3 SW/WS Y MP	1856620035	C.33
CLI C 1-3 SW/WS Z MP	1856620036	C.33
CLI C 1-3 VI NE CD	1568251689	C.21
CLI C 1-3 VI/SW 7 CD	1568251524	C.26
CLI C 1-3 VI/SW 7 MP	0252611524	C.26
CLI C 1-3 WS NE CD	1568251044	C.21
CLI C 1-3 WS NE MP	0171111044	C.21
CLI C 1-3 WS/SW - CD	1568251049	C.34
CLI C 1-3 WS/SW - MP	0252611049	C.34
CLI C 1-3 WS/SW . CD	1568251047	C.34
CLI C 1-3 WS/SW . MP	0252611047	C.34
CLI C 1-3 WS/SW / CD	1568251050	C.34
CLI C 1-3 WS/SW / MP	0252611050	C.34
CLI C 1-3 WS/SW : CD	1568251051	C.34
CLI C 1-3 WS/SW : MP	0252611051	C.34
CLI C 1-3 WS/SW ? CD	1568251055	C.34
CLI C 1-3 WS/SW + CD	1568251048	C.34
CLI C 1-3 WS/SW + MP	0252611048	C.34
CLI C 1-3 WS/SW = CD	1568251052	C.34
CLI C 1-3 WS/SW = MP	0252611052	C.34
CLI C 1-3 WS/SW 0 CD	1568251000	C.32
CLI C 1-3 WS/SW 0 MP	0252611000	C.32
CLI C 1-3 WS/SW 1 CD	1568250001	C.32
CLI C 1-3 WS/SW 1 MP	0252610001	C.32
CLI C 1-3 WS/SW 2 CD	1568250002	C.32
CLI C 1-3 WS/SW 2 MP	0252610002	C.32
CLI C 1-3 WS/SW 3 CD	1568250003	C.32
CLI C 1-3 WS/SW 3 MP	0252610003	C.32
CLI C 1-3 WS/SW 4 CD	1568250004	C.32
CLI C 1-3 WS/SW 4 MP	0252610004	C.32
CLI C 1-3 WS/SW 5 CD	1568250005	C.32
CLI C 1-3 WS/SW 5 MP	0252610005	C.32
CLI C 1-3 WS/SW 6 CD	1568250006	C.32
CLI C 1-3 WS/SW 6 MP	0252610006	C.32
CLI C 1-3 WS/SW 7 CD	1568250007	C.32
CLI C 1-3 WS/SW 7 MP	0252610007	C.32
CLI C 1-3 WS/SW 8 CD	1568250008	C.32
CLI C 1-3 WS/SW 8 MP	0252610008	C.32
CLI C 1-3 WS/SW 9 CD	1568251530	C.26
CLI C 1-3 WS/SW 9 CD	1568251530	C.32
CLI C 1-3 WS/SW 9 MP	0252611530	C.26
CLI C 1-3 WS/SW 9 MP	0252611530	C.32
CLI C 1-3 WS/SW A CD	1568251021	C.32
CLI C 1-3 WS/SW Ä CD	1568251056	C.34
CLI C 1-3 WS/SW A MP	0252611021	C.32
CLI C 1-3 WS/SW Ä MP	0252611056	C.34
CLI C 1-3 WS/SW Å MP	0252611055	C.34
CLI C 1-3 WS/SW AC CD	1568251059	C.34
CLI C 1-3 WS/SW AC MP	0252611059	C.34
CLI C 1-3 WS/SW B CD	1568251022	C.32
CLI C 1-3 WS/SW B MP	0252611022	C.32
CLI C 1-3 WS/SW C CD	1568251023	C.32
CLI C 1-3 WS/SW C MP	0252611023	C.32
CLI C 1-3 WS/SW D CD	1568251024	C.32
CLI C 1-3 WS/SW D MP	0252611024	C.32
CLI C 1-3 WS/SW E CD	1568251025	C.32
CLI C 1-3 WS/SW E MP	0252611025	C.32

Type	Order No.	Page
CLI C 1-3 WS/SW ET CD	1568251053	C.34
CLI C 1-3 WS/SW ET MP	0252611053	C.34
CLI C 1-3 WS/SW F CD	1568251026	C.32
CLI C 1-3 WS/SW F MP	0252611026	C.32
CLI C 1-3 WS/SW G CD	1568251027	C.32
CLI C 1-3 WS/SW G MP	0252611027	C.32
CLI C 1-3 WS/SW H CD	1568251028	C.32
CLI C 1-3 WS/SW H MP	0252611028	C.32
CLI C 1-3 WS/SW I CD	1568251029	C.32
CLI C 1-3 WS/SW I MP	0252611029	C.32
CLI C 1-3 WS/SW J CD	1568251030	C.32
CLI C 1-3 WS/SW J MP	0252611030	C.32
CLI C 1-3 WS/SW K CD	1568251031	C.32
CLI C 1-3 WS/SW K MP	0252611031	C.32
CLI C 1-3 WS/SW L CD	1568251032	C.32
CLI C 1-3 WS/SW L MP	0252611032	C.32
CLI C 1-3 WS/SW M CD	1568251033	C.32
CLI C 1-3 WS/SW M MP	0252611033	C.32
CLI C 1-3 WS/SW N CD	1568251034	C.32
CLI C 1-3 WS/SW N MP	0252611034	C.32
CLI C 1-3 WS/SW O CD	1568251035	C.32
CLI C 1-3 WS/SW Ö CD	1568251057	C.34
CLI C 1-3 WS/SW O MP	0252611035	C.32
CLI C 1-3 WS/SW Ö MP	0252611057	C.34
CLI C 1-3 WS/SW P CD	1568251036	C.32
CLI C 1-3 WS/SW P MP	0252611036	C.32
CLI C 1-3 WS/SW PET. CD	1568251058	C.34
CLI C 1-3 WS/SW PET. MP	0252611058	C.34
CLI C 1-3 WS/SW Q CD	1568251037	C.32
CLI C 1-3 WS/SW Q MP	0252611037	C.32
CLI C 1-3 WS/SW R CD	1568251038	C.32
CLI C 1-3 WS/SW R MP	0252611038	C.32
CLI C 1-3 WS/SW S CD	1568251039	C.32
CLI C 1-3 WS/SW S MP	0252611039	C.32
CLI C 1-3 WS/SW T CD	1568251040	C.32
CLI C 1-3 WS/SW T MP	0252611040	C.32
CLI C 1-3 WS/SW U CD	1568251041	C.32
CLI C 1-3 WS/SW U MP	0252611041	C.32
CLI C 1-3 WS/SW V CD	1568251042	C.32
CLI C 1-3 WS/SW V MP	0252611042	C.32
CLI C 1-3 WS/SW W CD	1568251043	C.32
CLI C 1-3 WS/SW W MP	0252611043	C.32
CLI C 1-3 WS/SW X CD	1568251054	C.32
CLI C 1-3 WS/SW X MP	0252611044	C.32
CLI C 1-3 WS/SW Y CD	1568251045	C.32
CLI C 1-3 WS/SW Y MP	0252611045	C.32
CLI C 1-3 WS/SW Z CD	1568251046	C.32
CLI C 1-3 WS/SW Z MP	0252611046	C.32
CLI C 1-30 SDR SG	1912660000	C.23
CLI C 1-33 GE NE SG	1871821687	C.21
CLI C 1-33 SDR SG	1912670000	C.23
CLI C 1-36 SDR SG	1912680000	C.23
CLI C 1-39 SDR SG	1912690000	C.23
CLI C 1-6 BL/SW MP MP	0252711732	C.37
CLI C 1-6 GE NE CD	1868811687	C.21
CLI C 1-6 GE/SW 01 CD	1868811522	C.35
CLI C 1-6 GE/SW 01 MP	0252711522	C.35
CLI C 1-6 GE/SW 02 CD	1868811523	C.35
CLI C 1-6 GE/SW 02 MP	0252711523	C.35
CLI C 1-6 GE/SW 03 CD	1868811524	C.35
CLI C 1-6 GE/SW 03 MP	0252711524	C.35
CLI C 1-6 GE/SW 04 CD	1868811525	C.35
CLI C 1-6 GE/SW 04 MP	0252711525	C.35
CLI C 1-6 GE/SW 05 CD	1868811526	C.35
CLI C 1-6 GE/SW 05 MP	0252711526	C.35
CLI C 1-6 GE/SW 06 CD	1868811527	C.35
CLI C 1-6 GE/SW 06 MP	0252711527	C.35
CLI C 1-6 GE/SW 07 CD	1868811528	C.35
CLI C 1-6 GE/SW 07 MP	0252711528	C.35
CLI C 1-6 GE/SW 08 CD	1868811529	C.35
CLI C 1-6 GE/SW 08 MP	0252711529	C.35
CLI C 1-6 GE/SW 09 CD	1868811530	C.35
CLI C 1-6 GE/SW 09 MP	0252711530	C.35
CLI C 1-6 GE/SW 10 CD	1868811531	C.35
CLI C 1-6 GE/SW 10 MP	0252711531	C.35
CLI C 1-6 GE/SW 11 CD	1868811532	C.35
CLI C 1-6 GE/SW 11 MP	0252711532	C.35
CLI C 1-6 GE/SW 12 CD	1868811533	C.35
CLI C 1-6 GE/SW 12 MP	0252711533	C.35
CLI C 1-6 GE/SW 13 CD	1868811534	C.35
CLI C 1-6 GE/SW 13 MP	0252711534	C.35
CLI C 1-6 GE/SW 14 CD	1868811535	C.35
CLI C 1-6 GE/SW 14 MP	0252711535	C.35
CLI C 1-6 GE/SW 15 CD	1868811536	C.35
CLI C 1-6 GE/SW 15 MP	0252711536	C.35
CLI C 1-6 GE/SW 16 CD	1868811537	C.35
CLI C 1-6 GE/SW 16 MP	0252711537	C.35
CLI C 1-6 GE/SW 17 CD	1868811538	C.35
CLI C 1-6 GE/SW 17 MP	0252711538	C.35
CLI C 1-6 GE/SW 18 CD	1868811539	C.35
CLI C 1-6 GE/SW 18 MP	0252711539	C.35
CLI C 1-6 GE/SW 19 CD	1868811540	C.35
CLI C 1-6 GE/SW 19 MP	0252711540	C.35
CLI C 1-6 GE/SW 20 CD	1868811541	C.35
CLI C 1-6 GE/SW 20 MP	0252711541	C.35
CLI C 1-6 GE/SW 21 CD	1868811542	C.35
CLI C 1-6 GE/SW 21 MP	0252711542	C.35
CLI C 1-6 GE/SW 22 CD	1868811543	C.35
CLI C 1-6 GE/SW 22 MP	0252711543	C.35
CLI C 1-6 GE/SW 23 CD	1868811544	C.35
CLI C 1-6 GE/SW 23 MP	0252711544	C.35
CLI C 1-6 GE/SW 24 CD	1868811545	C.35
CLI C 1-6 GE/SW 24 MP	0252711545	C.35
CLI C 1-6 GE/SW 25 CD	1868811546	C.35
CLI C 1-6 GE/SW 25 MP	0252711546	C.35
CLI C 1-6 GE/SW 26 CD	1868811547	C.35
CLI C 1-6 GE/SW 26 MP	0252711547	C.35
CLI C 1-6 GE/SW 27 CD	1868811548	C.35
CLI C 1-6 GE/SW 27 MP	0252711548	C.35
CLI C 1-6 GE/SW 28 CD	1868811549	C.35
CLI C 1-6 GE/SW 28 MP	0252711549	C.35
CLI C 1-6 GE/SW 29 CD	1868811550	C.35
CLI C 1-6 GE/SW 29 MP	0252711550	C.35
CLI C 1-6 GE/SW 30 CD	1868811551	C.35
CLI C 1-6 GE/SW 30 MP	0252711551	C.35
CLI C 1-6 GE/SW 31 CD	1868811552	C.35
CLI C 1-6 GE/SW 31 MP	0252711552	C.35
CLI C 1-6 GE/SW 32 CD	1868811553	C.35
CLI C 1-6 GE/SW 32 MP	0252711553	C.35
CLI C 1-6 GE/SW 33 CD	1868811554	C.35
CLI C 1-6 GE/SW 33 MP	0252711554	C.35
CLI C 1-6 GE/SW 34 CD	1868811555	C.35
CLI C 1-6 GE/SW 34 MP	0252711555	C.35
CLI C 1-6 GE/SW 35 CD	1868811556	C.35
CLI C 1-6 GE/SW 35 MP	0252711556	C.35
CLI C 1-6 GE/SW 36 CD	1868811557	C.35
CLI C 1-6 GE/SW 36 MP	0252711557	C.35
CLI C 1-6 GE/SW 37 CD	1868811558	C.35
CLI C 1-6 GE/SW 37 MP	0252711558	C.35
CLI C 1-6 GE/SW 38 CD	1868811559	C.35
CLI C 1-6 GE/SW 38 MP	0252711559	C.35
CLI C 1-6 GE/SW 39 CD	1868811560	C.35
CLI C 1-6 GE/SW 39 MP	0252711560	C.35
CLI C 1-6 GE/SW 40 CD	1868811561	C.35
CLI C 1-6 GE/SW 40 MP	0252711561	C.35
CLI C 1-6 GE/SW 41 CD	1868811562	C.35
CLI C 1-6 GE/SW 41 MP	0252711562	C.35
CLI C 1-6 GE/SW 42 CD	1868811563	C.35
CLI C 1-6 GE/SW 42 MP	0252711563	C.35
CLI C 1-6 GE/SW 43 CD	1868811564	C.35
CLI C 1-6 GE/SW 43 MP	0252711564	C.35
CLI C 1-6 GE/SW 44 CD	1868811565	C.35
CLI C 1-6 GE/SW 44 MP	0252711565	C.35
CLI C 1-6 GE/SW 45 CD	1868811566	C.35
CLI C 1-6 GE/SW 45 MP	0252711566	C.35
CLI C 1-6 GE/SW 46 CD	1868811567	C.35
CLI C 1-6 GE/SW 46 MP	0252711567	C.35
CLI C 1-6 GE/SW 47 CD	1868811568	C.35
CLI C 1-6 GE/SW 47 MP	0252711568	C.35
CLI C 1-6 GE/SW 48 CD	1868811569	C.35
CLI C 1-6 GE/SW 48 MP	0252711569	C.35
CLI C 1-6 GE/SW 49 CD	1868811570	C.35
CLI C 1-6 GE/SW 49 MP	0252711570	C.35
CLI C 1-6 GE/SW 50 CD	1868811571	C.35
CLI C 1-6 GE/SW 50 MP	0252711571	C.35
CLI C 1-6 GE/SW 51 CD	1868811572	C.35
CLI C 1-6 GE/SW 51 MP	0252711572	C.35
CLI C 1-6 GE/SW 52 CD	1868811573	C.35
CLI C 1-6 GE/SW 52 MP	0252711573	C.35
CLI C 1-6 GE/SW 53 CD	1868811574	C.35
CLI C 1-6 GE/SW 53 MP	0252711574	C.35
CLI C 1-6 GE/SW 54 CD	1868811575	C.35
CLI C 1-6 GE/SW 54 MP	0252711575	C.35
CLI C 1-6 GE/SW 55 CD	1868811576	C.35
CLI C 1-6 GE/SW 55 MP	0252711576	C.35
CLI C 1-6 GE/SW 56 CD	1868811577	C.35
CLI C 1-6 GE/SW 56 MP	0252711577	C.35
CLI C 1-6 GE/SW 57 CD	1868811578	C.35
CLI C 1-6 GE/SW 57 MP	0252711578	C.35
CLI C 1-6 GE/SW 58 CD	1868811579	C.35
CLI C 1-6 GE/SW 58 MP	0252711579	C.35
CLI C 1-6 GE/SW 59 CD	1868811580	C.35
CLI C 1-6 GE/SW 59 MP	0252711580	C.35
CLI C 1-6 GE/SW 60 CD	1868811581	C.35
CLI C 1-6 GE/SW 60 MP	0252711581	C.35
CLI C 1-6 GE/SW 61 CD	1868811582	C.36
CLI C 1-6 GE/SW 61 MP	0252711582	C.36
CLI C 1-6 GE/SW 62 CD	1868811583	C.36
CLI C 1-6 GE/SW 62 MP	0252711583	C.36
CLI C 1-6 GE/SW 63 CD	1868811584	C.36
CLI C 1-6 GE/SW 63 MP	0252711584	C.36
CLI C 1-6 GE/SW 64 CD	1868811585	C.36
CLI C 1-6 GE/SW 64 MP	0252711585	C.36
CLI C 1-6 GE/SW 65 CD	1868811586	C.36
CLI C 1-6 GE/SW 65 MP	0252711586	C.36
CLI C 1-6 GE/SW 66 CD	1868811587	C.36
CLI C 1-6 GE/SW 66 MP	0252711587	C.36
CLI C 1-6 GE/SW 67 CD	1868811588	C.36
CLI C 1-6 GE/SW 67 MP	0252711588	C.36
CLI C 1-6 GE/SW 68 CD	1868811589	C.36
CLI C 1-6 GE/SW 68 MP	0252711589	C.36
CLI C 1-6 GE/SW 69 CD	1868811590	C.36
CLI C 1-6 GE/SW 69 MP	0252711590	C.36
CLI C 1-6 GE/SW 70 CD	1868811591	C.36
CLI C 1-6 GE/SW 70 MP	0252711591	C.36
CLI C 1-6 GE/SW 71 CD	1868811592	C.36
CLI C 1-6 GE/SW 71 MP	0252711592	C.36
CLI C 1-6 GE/SW 72 CD	1868811593	C.36
CLI C 1-6 GE/SW 72 MP	0252711593	C.36
CLI C 1-6 GE/SW 73 CD	1868811594	C.36
CLI C 1-6 GE/SW 73 MP	0252711594	C.36
CLI C 1-6 GE/SW 74 CD	1868811595	C.36
CLI C 1-6 GE/SW 74 MP	0252711595	C.36
CLI C 1-6 GE/SW 75 CD	1868811596	C.36
CLI C 1-6 GE/SW 75 MP	0252711596	C.36
CLI C 1-6 GE/SW 76 CD	1868811597	C.36
CLI C 1-6 GE/SW 76 MP	0252711597	C.36
CLI C 1-6 GE/SW 77 CD	1868811598	C.36
CLI C 1-6 GE/SW 77 MP	0252711598	C.36
CLI C 1-6 GE/SW 78 CD	1868811599	C.36
CLI C 1-6 GE/SW 78 MP	0252711599	C.36
CLI C 1-6 GE/SW 79 CD	1868811600	C.36
CLI C 1-6 GE/SW 79 MP	0252711600	C.36
CLI C 1-6 GE/SW 80 CD	1868811601	C.36
CLI C 1-6 GE/SW 80 MP	0252711601	C.36
CLI C 1-6 GE/SW 81 CD	1868811602	C.36
CLI C 1-6 GE/SW 81 MP	0252711602	C.36
CLI C 1-6 GE/SW 82 CD	1868811603	C.36
CLI C 1-6 GE/SW 82 MP	0252711603	C.36
CLI C 1-6 GE/SW 83 CD	1868811604	C.36
CLI C 1-6 GE/SW 83 MP	0252711604	C.36
CLI C 1-6 GE/SW 84 CD	1868811605	C.36
CLI C 1-6 GE/SW 84 MP	0252711605	C.36
CLI C 1-6 GE/SW 85 CD	1868811606	C.36
CLI C 1-6 GE/SW 85 MP	0252711606	C.36
CLI C 1-6 GE/SW 86 CD	1868811607	C.36
CLI C 1-6 GE/SW 86 MP	0252711607	C.36
CLI C 1-6 GE/SW 87 CD	1868811608	C.36
CLI C 1-6 GE/SW 87 MP	0252711608	C.36
CLI C 1-6 GE/SW 88 CD	1868811609	C.36
CLI C 1-6 GE/SW 88 MP	0252711609	C.36
CLI C 1-6 GE/SW 89 CD	1868811610	C.36
CLI C 1-6 GE/SW 89 MP	0252711610	C.36
CLI C 1-6 GE/SW 90 CD	1868811611	C.36
CLI C 1-6 GE/SW 90 MP	0252711611	C.36
CLI C 1-6 GE/SW 91 CD	1868811612	C.36
CLI C 1-6 GE/SW 91 MP	0252711612	C.36
CLI C 1-6 GE/SW 92 CD	1868811613	C.36
CLI C 1-6 GE/SW 92 MP	0252711613	C.36
CLI C 1-6 GE/SW 93 CD	1868811614	C.36
CLI C 1-6 GE/SW 93 MP	0252711614	C.36
CLI C 1-6 GE/SW 94 CD	1868811615	C.36
CLI C 1-6 GE/SW 94 MP	0252711615	C.36
CLI C 1-6 GE/SW 95 CD	1868811616	C.36
CLI C 1-6 GE/SW 95 MP	0252711616	C.36
CLI C 1-6 GE/SW 96 CD	1868811617	C.36
CLI C 1-6 GE/SW 96 MP	0252711617	C.36
CLI C 1-6 GE/SW 97 CD	1868811618	C.36
CLI C 1-6 GE/SW 97 MP	0252711618	C.36
CLI C 1-6 GE/SW 98 CD	1868811619	C.36
CLI C 1-6 GE/SW 98 MP	0252711619	C.36
CLI C 1-6 GE/SW 99 CD	1868811620	C.36
CLI C 1-6 GE/SW 99 MP	0252711620	C.36
CLI C 1-6 GE/SW A1 CD	1868811726	C.37
CLI C 1-6 GE/SW A1 MP	0252711726	C.37
CLI C 1-6 GE/SW A2 CD	1868811727	C.37
CLI C 1-6 GE/SW A2 MP	0252711727	C.37
CLI C 1-6 GE/SW I1 CD	1868811739	C.37
CLI C 1-6 GE/SW I2 CD	1868811740	C.37
CLI C 1-6 GE/SW IC CD	1868811741	C.37
CLI C 1-6 GE/SW L1 CD	1868811728	C.37
CLI C 1-6 GE/SW L1 MP	0252711728	C.37
CLI C 1-6 GE/SW L2 CD	1868811729	C.37
CLI C 1-6 GE/SW L2 MP	0252711729	C.37
CLI C 1-6 GE/SW L3 CD	1868811730	C.37
CLI C 1-6 GE/SW L3 MP	0252711730	C.37
CLI C 1-6 GE/SW MP CD	1868811731	C.37
CLI C 1-6 GE/SW PE CD	1868811733	C.37
CLI C 1-6 GE/SW PE MP	0252711733	C.37
CLI C 1-6 GE/SW U1 CD	1868811735	C.37
CLI C 1-6 GE/SW U2 CD	1868811736	C.37
CLI C 1-6 GE/SW U3 CD	1868811737	C.37
CLI C 1-6 GE/SW UN CD	1868811738	C.37
CLI C 1-6 GE/SW X1 CD	1868811150	C.37
CLI C 1-6 GE/SW X2 CD	1868811151	C.37
CLI C 1-6 GR/SW L1 MP	1878191728	C.37
CLI C 1-6 GR/SW L2 MP	1878191729	C.37
CLI C 1-6 GR/SW L3 MP	1878191730	C.37
CLI C 1-6 SDR CD	0252709999	C.23
CLI C 1-6 SDR SG	1912700000	C.23
CLI C 1-6 WS/SW A1 CD	1871351726	C.37
CLI C 1-6 WS/SW A1 MP	1871341726	C.37
CLI C 1-6 WS/SW A2 CD	1871351727	C.37
CLI C 1-6 WS/SW A2 MP	1871341727	C.37
CLI C 1-6 WS/SW L1 CD	1871351728	C.37
CLI C 1-6 WS/SW L1 MP	1871341728	C.37
CLI C 1-6 WS/SW L2 CD	1871351729	C.37
CLI C 1-6 WS/SW L2 MP	1871341729	C.37
CLI C 1-6 WS/SW L3 CD	1871351730	C.37
CLI C 1-6 WS/SW L3 MP	1871341730	C.37
CLI C 1-9 GE NE CD	1868810004	C.21
CLI C 1-9 GE/SW PEN CD	1868811734	C.37
CLI C 1-9 GE/SW PEN MP	0252711734	C.37
CLI C 1-9 SDR CD	0252809999	C.23
CLI C 1-9 SDR SG	1868819999	C.23
CLI C 1-9 WS/SW PEN CD	1871351734	C.37
CLI C 1-9 WS/SW PEN MP	1871341734	C.37
CLI C 2-12 SDR SG	1873380000	C.24
CLI C 2-15 SDR SG	1873390000	C.24
CLI C 2-18 GE NE SG	1871831687	C.21
CLI C 2-18 SDR SG	1871839999	C.24
CLI C 2-18 WS NE SG	1871831044	C.21
CLI C 2-21 SDR SG	1873400000	C.24
CLI C 2-24 SDR SG	1912710000	C.24
CLI C 2-27 SDR SG	1912720000	C.24
CLI C 2-30 SDR SG	1912730000	C.24
CLI C 2-33 SDR SG	1912740000	C.24
CLI C 2-36 SDR SG	1912750000	C.24
CLI C 2-39 SDR SG	1912760000	C.24
CLI C 2-4 BL NE CD	0171301693	C.21
CLI C 2-4 BL/SW - CD	1568261741	C.39
CLI C 2-4 BL/SW - MP	0251311741	C.39
CLI C 2-4 BL/SW 6 CD	1568261521	C.26
CLI C 2-4 BL/SW 6 MP	0251311521	C.26
CLI C 2-4 BL/SW N CD	1568261664	C.39
CLI C 2-4 BL/SW N MP	0251311664	C.39
CLI C 2-4 BR NE CD	0171301692	C.21
CLI C 2-4 BR/WS 1 CD	1568261506	C.26
CLI C 2-4 BR/WS 1 MP	0251311506	C.26
CLI C 2-4 GE NE CD	0171301687	C.21
CLI C 2-4 GE NE MP	0171310000	C.21
CLI C 2-4 GE/SW - CD	1568261740	C.39
CLI C 2-4 GE/SW - MP	0251311740	C.39
CLI C 2-4 GE/SW . CD	1568261748	C.39
CLI C 2-4 GE/SW . MP	0251311748	C.39
CLI C 2-4 GE/SW / CD	1568261742	C.39
CLI C 2-4 GE/SW / MP	0251311742	C.39
CLI C 2-4 GE/SW : CD	1568261750	C.39
CLI C 2-4 GE/SW : MP	0251311750	C.39
CLI C 2-4 GE/SW + CD	1568261738	C.39
CLI C 2-4 GE/SW + MP	0251311738	C.39
CLI C 2-4 GE/SW = CD	1568261751	C.39
CLI C 2-4 GE/SW = MP	0251311751	C.39
CLI C 2-4 GE/SW 0 CD	1568261502	C.38
CLI C 2-4 GE/SW 0 MP	0251311502	C.38
CLI C 2-4 GE/SW 1 CD	1568261505	C.38
CLI C 2-4 GE/SW 1 MP	0251311505	C.38
CLI C 2-4 GE/SW 2 CD	1568261508	C.38
CLI C 2-4 GE/SW 2 MP	0251311508	C.38
CLI C 2-4 GE/SW 3 CD	1568261511	C.38
CLI C 2-4 GE/SW 3 MP	0251311511	C.38
CLI C 2-4 GE/SW 4 CD	1568261514	C.26
CLI C 2-4 GE/SW 4 CD	1568261514	C.38
CLI C 2-4 GE/SW 4 MP	0251311514	C.26
CLI C 2-4 GE/SW 4 MP	0251311514	C.38
CLI C 2-4 GE/SW 5 CD	1568261517	C.38
CLI C 2-4 GE/SW 5 MP	0251311517	C.38
CLI C 2-4 GE/SW 6 CD	1568261520	C.38
CLI C 2-4 GE/SW 6 MP	0251311520	C.38
CLI C 2-4 GE/SW 7 CD	1568261523	C.38
CLI C 2-4 GE/SW 7 MP	0251311523	C.38
CLI C 2-4 GE/SW 8 CD	1568261526	C.38
CLI C 2-4 GE/SW 8 MP	0251311526	C.38
CLI C 2-4 GE/SW 9 CD	1568261529	C.38
CLI C 2-4 GE/SW 9 MP	0251311529	C.38
CLI C 2-4 GE/SW A CD	1568261637	C.38
CLI C 2-4 GE/SW Ä CD	1568261697	C.39
CLI C 2-4 GE/SW Å CD	1568261699	C.39
CLI C 2-4 GE/SW A MP	0251311637	C.38
CLI C 2-4 GE/SW Ä MP	0251311697	C.39
CLI C 2-4 GE/SW Å MP	0251311699	C.39
CLI C 2-4 GE/SW AC CD	1568261752	C.39
CLI C 2-4 GE/SW AC MP	0251311752	C.39
CLI C 2-4 GE/SW Æ CD	1568261735	C.39
CLI C 2-4 GE/SW Æ MP	0251311735	C.39
CLI C 2-4 GE/SW B CD	1568261639	C.38
CLI C 2-4 GE/SW B MP	0251311639	C.38
CLI C 2-4 GE/SW C CD	1568261641	C.38
CLI C 2-4 GE/SW C MP	0251311641	C.38
CLI C 2-4 GE/SW D CD	1568261643	C.38
CLI C 2-4 GE/SW D MP	0251311643	C.38
CLI C 2-4 GE/SW E CD	1568261645	C.38
CLI C 2-4 GE/SW E MP	0251311645	C.38
CLI C 2-4 GE/SW ET CD	1568261746	C.39
CLI C 2-4 GE/SW ET MP	0251311746	C.39
CLI C 2-4 GE/SW F CD	1568261647	C.38
CLI C 2-4 GE/SW F MP	0251311647	C.38
CLI C 2-4 GE/SW G CD	1568261649	C.38
CLI C 2-4 GE/SW G MP	0251311649	C.38
CLI C 2-4 GE/SW H CD	1568261651	C.38
CLI C 2-4 GE/SW H MP	0251311651	C.38
CLI C 2-4 GE/SW I CD	1568261653	C.38
CLI C 2-4 GE/SW I MP	0251311653	C.38
CLI C 2-4 GE/SW J CD	1568261655	C.38
CLI C 2-4 GE/SW J MP	0251311655	C.38
CLI C 2-4 GE/SW K CD	1568261657	C.38
CLI C 2-4 GE/SW K MP	0251311657	C.38
CLI C 2-4 GE/SW L CD	1568261659	C.38
CLI C 2-4 GE/SW L MP	0251311659	C.38
CLI C 2-4 GE/SW M CD	1568261661	C.38
CLI C 2-4 GE/SW M MP	0251311661	C.38
CLI C 2-4 GE/SW N CD	1568261663	C.38
CLI C 2-4 GE/SW N MP	0251311663	C.38
CLI C 2-4 GE/SW O CD	1568261665	C.38
CLI C 2-4 GE/SW Ö CD	1568261695	C.39
CLI C 2-4 GE/SW Ø CD	1568261736	C.39
CLI C 2-4 GE/SW O MP	0251311665	C.38
CLI C 2-4 GE/SW Ö MP	0251311695	C.39
CLI C 2-4 GE/SW Ø MP	0251311736	C.39
CLI C 2-4 GE/SW P CD	1568261667	C.38

Type	Order No.	Page
CLI C 2-4 GE/SW P MP	0251311667	C.38
CLI C 2-4 GE/SW PET. CD	1568261747	C.39
CLI C 2-4 GE/SW PET. MP	0251311747	C.39
CLI C 2-4 GE/SW Q CD	1568261669	C.38
CLI C 2-4 GE/SW Q MP	0251311669	C.38
CLI C 2-4 GE/SW R CD	1568261671	C.38
CLI C 2-4 GE/SW R MP	0251311671	C.38
CLI C 2-4 GE/SW S CD	1568261673	C.38
CLI C 2-4 GE/SW S MP	0251311673	C.38
CLI C 2-4 GE/SW T CD	1568261676	C.38
CLI C 2-4 GE/SW T MP	0251311676	C.38
CLI C 2-4 GE/SW U CD	1568261679	C.38
CLI C 2-4 GE/SW U MP	0251311679	C.38
CLI C 2-4 GE/SW V CD	1568261681	C.38
CLI C 2-4 GE/SW V MP	0251311681	C.38
CLI C 2-4 GE/SW W CD	1568261683	C.38
CLI C 2-4 GE/SW W MP	0251311683	C.38
CLI C 2-4 GE/SW X CD	1568261687	C.38
CLI C 2-4 GE/SW X MP	0251311687	C.38
CLI C 2-4 GE/SW Y CD	1568261696	C.38
CLI C 2-4 GE/SW Y MP	0251311696	C.38
CLI C 2-4 GE/SW Z CD	1568261698	C.38
CLI C 2-4 GE/SW Z MP	0251311698	C.38
CLI C 2-4 GN NE CD	0171301688	C.21
CLI C 2-4 GN/SW 5 CD	1568261518	C.26
CLI C 2-4 GN/SW 5 MP	0251311518	C.26
CLI C 2-4 GR NE CD	0171301691	C.21
CLI C 2-4 GR/SW 0 MP	1871851502	C.38
CLI C 2-4 GR/SW 1 MP	1871851505	C.38
CLI C 2-4 GR/SW 2 MP	1871851508	C.38
CLI C 2-4 GR/SW 3 MP	1871851511	C.38
CLI C 2-4 GR/SW 4 MP	1871851514	C.38
CLI C 2-4 GR/SW 5 MP	1871851517	C.38
CLI C 2-4 GR/SW 6 MP	1871851520	C.38
CLI C 2-4 GR/SW 7 MP	1871851523	C.38
CLI C 2-4 GR/SW 8 CD	1568261527	C.26
CLI C 2-4 GR/SW 8 MP	0251311527	C.26
CLI C 2-4 GR/SW 8 MP	0251311527	C.38
CLI C 2-4 GR/SW 9 MP	1871851529	C.38
CLI C 2-4 OR NE CD	0171301690	C.21
CLI C 2-4 OR/SW 3 CD	1568261512	C.26
CLI C 2-4 OR/SW 3 MP	0251311512	C.26
CLI C 2-4 RT NE CD	0171301686	C.21
CLI C 2-4 RT/SW + CD	1568261737	C.39
CLI C 2-4 RT/SW + MP	0251311737	C.39
CLI C 2-4 RT/SW 2 CD	1568261509	C.26
CLI C 2-4 RT/SW 2 MP	0251311509	C.26
CLI C 2-4 SDR CD	1568269999	C.24
CLI C 2-4 SW NE CD	0171301694	C.21
CLI C 2-4 SW/WS 0 CD	1568261503	C.26
CLI C 2-4 SW/WS 0 MP	0251311503	C.26
CLI C 2-4 VI NE CD	0171301689	C.21
CLI C 2-4 VI/SW 7 CD	1568261524	C.26
CLI C 2-4 VI/SW 7 MP	0251311524	C.26
CLI C 2-4 WS NE CD	0171301044	C.21
CLI C 2-4 WS NE MP	0251311060	C.21
CLI C 2-4 WS/SW - CD	1871871740	C.39
CLI C 2-4 WS/SW - MP	0251311049	C.39
CLI C 2-4 WS/SW . CD	1871871748	C.39
CLI C 2-4 WS/SW . MP	0251311047	C.39
CLI C 2-4 WS/SW / CD	1871871742	C.39
CLI C 2-4 WS/SW / MP	0251311050	C.39
CLI C 2-4 WS/SW : CD	1871871750	C.39
CLI C 2-4 WS/SW : MP	0251311051	C.39
CLI C 2-4 WS/SW ? CD	1871871699	C.39
CLI C 2-4 WS/SW + CD	1871871738	C.39
CLI C 2-4 WS/SW + MP	0251311048	C.39
CLI C 2-4 WS/SW = CD	1871871751	C.39
CLI C 2-4 WS/SW = MP	0251311052	C.39
CLI C 2-4 WS/SW 0 CD	1871871502	C.38
CLI C 2-4 WS/SW 0 MP	0251311000	C.38
CLI C 2-4 WS/SW 1 CD	1871871505	C.38
CLI C 2-4 WS/SW 1 MP	0251310001	C.38
CLI C 2-4 WS/SW 2 CD	1871871508	C.38
CLI C 2-4 WS/SW 2 MP	0251310002	C.38
CLI C 2-4 WS/SW 3 CD	1871871511	C.38
CLI C 2-4 WS/SW 3 MP	0251310003	C.38
CLI C 2-4 WS/SW 4 CD	1871871514	C.38
CLI C 2-4 WS/SW 4 MP	0251310004	C.38
CLI C 2-4 WS/SW 5 CD	1871871517	C.38
CLI C 2-4 WS/SW 5 MP	0251310005	C.38
CLI C 2-4 WS/SW 6 CD	1871871520	C.38
CLI C 2-4 WS/SW 6 MP	0251310006	C.38
CLI C 2-4 WS/SW 7 CD	1871871523	C.38
CLI C 2-4 WS/SW 7 MP	0251310007	C.38
CLI C 2-4 WS/SW 8 CD	1871871526	C.38
CLI C 2-4 WS/SW 8 MP	0251310008	C.38
CLI C 2-4 WS/SW 9 CD	1568261530	C.26
CLI C 2-4 WS/SW 9 CD	1568261530	C.38
CLI C 2-4 WS/SW 9 MP	0251310009	C.26
CLI C 2-4 WS/SW 9 MP	0251310009	C.38
CLI C 2-4 WS/SW A CD	1871871637	C.38
CLI C 2-4 WS/SW Ä CD	1871871697	C.39
CLI C 2-4 WS/SW A MP	0251311021	C.38
CLI C 2-4 WS/SW Ä MP	0251311056	C.39
CLI C 2-4 WS/SW Å MP	0251311055	C.39
CLI C 2-4 WS/SW AC CD	1871871752	C.39
CLI C 2-4 WS/SW AC MP	0251311059	C.39
CLI C 2-4 WS/SW B CD	1871871639	C.38
CLI C 2-4 WS/SW B MP	0251311022	C.38
CLI C 2-4 WS/SW C CD	1871871641	C.38
CLI C 2-4 WS/SW C MP	0251311023	C.38
CLI C 2-4 WS/SW D CD	1871871643	C.38
CLI C 2-4 WS/SW D MP	0251311024	C.38
CLI C 2-4 WS/SW E CD	1871871645	C.38
CLI C 2-4 WS/SW E MP	0251311025	C.38
CLI C 2-4 WS/SW ET CD	1871871746	C.39
CLI C 2-4 WS/SW ET MP	0251311053	C.39
CLI C 2-4 WS/SW F CD	1871871647	C.38
CLI C 2-4 WS/SW F MP	0251311026	C.38
CLI C 2-4 WS/SW G CD	1871871649	C.38
CLI C 2-4 WS/SW G MP	0251311027	C.38
CLI C 2-4 WS/SW H CD	1871871651	C.38
CLI C 2-4 WS/SW H MP	0251311028	C.38
CLI C 2-4 WS/SW I CD	1871871653	C.38
CLI C 2-4 WS/SW I MP	0251311029	C.38
CLI C 2-4 WS/SW J CD	1871871655	C.38
CLI C 2-4 WS/SW J MP	0251311030	C.38
CLI C 2-4 WS/SW K CD	1871871657	C.38
CLI C 2-4 WS/SW K MP	0251311031	C.38
CLI C 2-4 WS/SW L CD	1871871659	C.38
CLI C 2-4 WS/SW L MP	0251311032	C.38
CLI C 2-4 WS/SW M CD	1871871661	C.38
CLI C 2-4 WS/SW M MP	0251311033	C.38
CLI C 2-4 WS/SW N CD	1871871663	C.38
CLI C 2-4 WS/SW N MP	0251311034	C.38
CLI C 2-4 WS/SW O CD	1871871665	C.38
CLI C 2-4 WS/SW Ö CD	1871871695	C.39
CLI C 2-4 WS/SW O MP	0251311035	C.38
CLI C 2-4 WS/SW Ö MP	0251311057	C.39
CLI C 2-4 WS/SW P CD	1871871667	C.38
CLI C 2-4 WS/SW P MP	0251311036	C.38
CLI C 2-4 WS/SW PET. CD	1871871747	C.39
CLI C 2-4 WS/SW PET. MP	0251311058	C.39
CLI C 2-4 WS/SW Q CD	1871871669	C.38
CLI C 2-4 WS/SW Q MP	0251311037	C.38
CLI C 2-4 WS/SW R CD	1871871671	C.38
CLI C 2-4 WS/SW R MP	0251311038	C.38
CLI C 2-4 WS/SW S CD	1871871673	C.38
CLI C 2-4 WS/SW S MP	0251311039	C.38
CLI C 2-4 WS/SW T CD	1871871676	C.38
CLI C 2-4 WS/SW T MP	0251311040	C.38
CLI C 2-4 WS/SW U CD	1871871679	C.38
CLI C 2-4 WS/SW U MP	0251311041	C.38
CLI C 2-4 WS/SW V CD	1871871681	C.38
CLI C 2-4 WS/SW V MP	0251311042	C.38
CLI C 2-4 WS/SW W CD	1871871683	C.38
CLI C 2-4 WS/SW W MP	0251311043	C.38
CLI C 2-4 WS/SW X CD	1871871685	C.38
CLI C 2-4 WS/SW X MP	0251311044	C.38
CLI C 2-4 WS/SW Y CD	1871871696	C.38
CLI C 2-4 WS/SW Y MP	0251311045	C.38
CLI C 2-4 WS/SW Z CD	1871871698	C.38
CLI C 2-4 WS/SW Z MP	0251311046	C.38
CLI C 2-6 GE NE CD	1871901687	C.21
CLI C 2-6 GE/SW L1 CD	1871901728	C.39
CLI C 2-6 GE/SW L1 MP	1871891728	C.39
CLI C 2-6 GE/SW L2 CD	1871901729	C.39
CLI C 2-6 GE/SW L2 MP	1871891729	C.39
CLI C 2-6 GE/SW L3 CD	1871901730	C.39
CLI C 2-6 GE/SW L3 MP	1871891730	C.39
CLI C 2-6 GE/SW PE CD	1871901731	C.39
CLI C 2-6 SDR CD	1871909999	C.24
CLI C 2-6 WS/SW L1 CD	1871911728	C.39
CLI C 2-6 WS/SW L1 MP	1871921728	C.39
CLI C 2-6 WS/SW L2 CD	1871911729	C.39
CLI C 2-6 WS/SW L2 MP	1871921729	C.39
CLI C 2-6 WS/SW L3 CD	1871911730	C.39
CLI C 2-6 WS/SW L3 MP	1871921730	C.39
CLI C 2-9 GE NE CD	1871971687	C.21
CLI C 2-9 GE/SW PEN CD	1871971734	C.39
CLI C 2-9 GE/SW PEN MP	1872031734	C.39
CLI C 2-9 SDR CD	1899240000	C.24
CLI C 2-9 SDR SG	1871979999	C.24
CLI C 3-12 SDR SG	1873420000	C.24
CLI C 3-15 SDR SG	1873430000	C.24
CLI C 3-18 GE NE SG	1872671687	C.22
CLI C 3-18 SDR SG	1872679999	C.24
CLI C 3-21 SDR SG	1873410000	C.24
CLI C 3-24 SDR SG	1912770000	C.24
CLI C 3-27 SDR SG	1912780000	C.24
CLI C 3-30 SDR SG	1912790000	C.24
CLI C 3-33 SDR SG	1912800000	C.24
CLI C 3-36 SDR SG	1912810000	C.24
CLI C 3-39 SDR SG	1912820000	C.24
CLI C 3-6 BL NE MP	0240011693	C.22
CLI C 3-6 BL/SW - MP	0253411741	C.41
CLI C 3-6 BL/SW 6 MP	0253411521	C.26
CLI C 3-6 BL/SW N MP	0253411664	C.41
CLI C 3-6 BR NE MP	0240011692	C.22
CLI C 3-6 BR/WS 1 MP	0253411506	C.26
CLI C 3-6 GE NE MP	0240011687	C.22
CLI C 3-6 GE/SW / MP	0253411742	C.40
CLI C 3-6 GE/SW - MP	0253411740	C.40
CLI C 3-6 GE/SW . MP	0253411748	C.40
CLI C 3-6 GE/SW : MP	0253411750	C.40
CLI C 3-6 GE/SW + MP	0253411738	C.40
CLI C 3-6 GE/SW = MP	0253411751	C.40
CLI C 3-6 GE/SW 0 MP	0253411502	C.40
CLI C 3-6 GE/SW 1 MP	0253411505	C.40
CLI C 3-6 GE/SW 2 MP	0253411508	C.40
CLI C 3-6 GE/SW 3 MP	0253411511	C.40
CLI C 3-6 GE/SW 4 MP	0253411514	C.26
CLI C 3-6 GE/SW 4 MP	0253411514	C.40
CLI C 3-6 GE/SW 5 MP	0253411517	C.40
CLI C 3-6 GE/SW 6 MP	0253411520	C.40
CLI C 3-6 GE/SW 7 MP	0253411523	C.40
CLI C 3-6 GE/SW 8 MP	0253411526	C.40
CLI C 3-6 GE/SW 9 MP	0253411529	C.40
CLI C 3-6 GE/SW A MP	0253411637	C.40
CLI C 3-6 GE/SW Ä MP	0253411697	C.40
CLI C 3-6 GE/SW Å MP	0253411699	C.40
CLI C 3-6 GE/SW AC MP	0253411752	C.40
CLI C 3-6 GE/SW B MP	0253411639	C.40
CLI C 3-6 GE/SW C MP	0253411641	C.40
CLI C 3-6 GE/SW D MP	0253411643	C.40
CLI C 3-6 GE/SW E MP	0253411645	C.40
CLI C 3-6 GE/SW ET MP	0253411746	C.40
CLI C 3-6 GE/SW F MP	0253411647	C.40
CLI C 3-6 GE/SW G MP	0253411649	C.40
CLI C 3-6 GE/SW H MP	0253411651	C.40
CLI C 3-6 GE/SW I MP	0253411653	C.40
CLI C 3-6 GE/SW J MP	0253411655	C.40
CLI C 3-6 GE/SW K MP	0253411657	C.40
CLI C 3-6 GE/SW L MP	0253411659	C.40
CLI C 3-6 GE/SW M MP	0253411661	C.40
CLI C 3-6 GE/SW N MP	0253411663	C.40
CLI C 3-6 GE/SW O MP	0253411665	C.40
CLI C 3-6 GE/SW Ö MP	0253411695	C.40
CLI C 3-6 GE/SW P MP	0253411667	C.40
CLI C 3-6 GE/SW Q MP	0253411669	C.40
CLI C 3-6 GE/SW R MP	0253411671	C.40
CLI C 3-6 GE/SW S MP	0253411673	C.40
CLI C 3-6 GE/SW T MP	0253411676	C.40
CLI C 3-6 GE/SW U MP	0253411679	C.40
CLI C 3-6 GE/SW V MP	0253411681	C.40
CLI C 3-6 GE/SW W MP	0253411683	C.40
CLI C 3-6 GE/SW X MP	0253411687	C.40
CLI C 3-6 GE/SW Y MP	0253411696	C.40
CLI C 3-6 GE/SW Z MP	0253411698	C.40
CLI C 3-6 GN NE MP	0240011688	C.22
CLI C 3-6 GN/SW 5 MP	0253411518	C.26
CLI C 3-6 GR NE MP	0240011691	C.22
CLI C 3-6 GR/SW 8 MP	0253411527	C.26
CLI C 3-6 OR NE MP	0240011690	C.22
CLI C 3-6 OR/SW 3 MP	0253411512	C.26
CLI C 3-6 RT NE MP	0240011686	C.22
CLI C 3-6 RT/SW + MP	0253411737	C.41
CLI C 3-6 RT/SW 2 MP	0253411509	C.26
CLI C 3-6 SDR SG	1872309999	C.24
CLI C 3-6 SW NE MP	0240011694	C.22
CLI C 3-6 SW/WS 0 MP	0253411503	C.26
CLI C 3-6 VI NE MP	0240011689	C.22
CLI C 3-6 VI/SW 7 MP	0253411524	C.26
CLI C 3-6 WS NE MP	0240011044	C.22
CLI C 3-6 WS/SW - MP	1872301740	C.40
CLI C 3-6 WS/SW . MP	1872301748	C.40
CLI C 3-6 WS/SW / MP	1872301742	C.40
CLI C 3-6 WS/SW : MP	1872301750	C.40
CLI C 3-6 WS/SW + MP	1872301738	C.40
CLI C 3-6 WS/SW = MP	1872301751	C.40
CLI C 3-6 WS/SW 0 MP	1872301502	C.40
CLI C 3-6 WS/SW 1 MP	1872301505	C.40
CLI C 3-6 WS/SW 2 MP	1872301508	C.40
CLI C 3-6 WS/SW 3 MP	1872301511	C.40
CLI C 3-6 WS/SW 4 MP	1872301514	C.40
CLI C 3-6 WS/SW 5 MP	1872301517	C.40
CLI C 3-6 WS/SW 6 MP	1872301520	C.40
CLI C 3-6 WS/SW 7 MP	1872301523	C.40
CLI C 3-6 WS/SW 8 MP	1872301526	C.40
CLI C 3-6 WS/SW 9 MP	0253411530	C.26
CLI C 3-6 WS/SW 9 MP	0253411530	C.40
CLI C 3-6 WS/SW A MP	1872301637	C.40
CLI C 3-6 WS/SW Ä MP	1872301697	C.40
CLI C 3-6 WS/SW Å MP	1872301699	C.40
CLI C 3-6 WS/SW A1 MP	1872651726	C.41
CLI C 3-6 WS/SW AC MP	1872301752	C.40
CLI C 3-6 WS/SW B MP	1872301639	C.40
CLI C 3-6 WS/SW C MP	1872301641	C.40
CLI C 3-6 WS/SW D MP	1872301643	C.40
CLI C 3-6 WS/SW E MP	1872301645	C.40
CLI C 3-6 WS/SW ET MP	1872301746	C.40
CLI C 3-6 WS/SW F MP	1872301647	C.40
CLI C 3-6 WS/SW G MP	1872301649	C.40
CLI C 3-6 WS/SW H MP	1872301651	C.40
CLI C 3-6 WS/SW I MP	1872301653	C.40
CLI C 3-6 WS/SW J MP	1872301655	C.40
CLI C 3-6 WS/SW K MP	1872301657	C.40
CLI C 3-6 WS/SW L MP	1872301659	C.40
CLI C 3-6 WS/SW M MP	1872301661	C.40
CLI C 3-6 WS/SW N MP	1872301663	C.40
CLI C 3-6 WS/SW O MP	1872301665	C.40
CLI C 3-6 WS/SW Ö MP	1872301695	C.40
CLI C 3-6 WS/SW P MP	1872301667	C.40
CLI C 3-6 WS/SW Q MP	1872301669	C.40
CLI C 3-6 WS/SW R MP	1872301671	C.40
CLI C 3-6 WS/SW S MP	1872301673	C.40
CLI C 3-6 WS/SW T MP	1872301676	C.40
CLI C 3-6 WS/SW U MP	1872301679	C.40
CLI C 3-6 WS/SW V MP	1872301681	C.40
CLI C 3-6 WS/SW W MP	1872301683	C.40
CLI C 3-6 WS/SW X MP	1872301687	C.40
CLI C 3-6 WS/SW Y MP	1872301696	C.40
CLI C 3-6 WS/SW Z MP	1872301698	C.40
CLI C 3-9 GE/SW A1 MP	0253511726	C.41
CLI C 3-9 GE/SW A2 MP	0253511727	C.41
CLI C 3-9 GE/SW L1 MP	0253511728	C.41
CLI C 3-9 GE/SW L2 MP	0253511729	C.41
CLI C 3-9 GE/SW L3 MP	0253511730	C.41
CLI C 3-9 GE/SW PE MP	0253511733	C.41
CLI C 3-9 GE/SW PEN MP	1872661733	C.41
CLI C 3-9 GE/SW SL MP	0253511735	C.41
CLI C 3-9 GE/SW X1 MP	0253511750	C.41
CLI C 3-9 GE/SW X2 MP	0253511751	C.41
CLI C 3-9 GE/SW X3 MP	0253511752	C.41
CLI C 3-9 SDR SG	1872659999	C.24
CLI C 3-9 WS/SW A2 MP	1872651727	C.41
CLI C 3-9 WS/SW L1 MP	1872651728	C.41
CLI C 3-9 WS/SW L2 MP	1872651729	C.41
CLI C 3-9 WS/SW L3 MP	1872651730	C.41
CLI C 3-9 WS/SW PEN MP	1872651734	C.41
CLI CD-BOX	1763290000	C.52
CLI F 1-20 WS/GE NE	1600740000	C.11
CLI F 1-20 WS/GE NE	1600740000	C.9
CLI F 2-17,5 WS/GE NE	1764050000	C.11
CLI F 2-17,5 WS/GE NE	1764050000	C.9
CLI M 2-12 SDR SG	1873450000	C.25
CLI M 2-15 SDR SG	1899260000	C.25
CLI M 2-18 SDR SG	1899230000	C.25
CLI M 2-21 SDR SG	1873460000	C.25
CLI M 2-24 SDR SG	1912860000	C.25
CLI M 2-25Q GE NEUT SG	1886531687	C.22
CLI M 2-25Q SDR SG	1579500000	C.25
CLI M 2-27 SDR SG	1912870000	C.25
CLI M 2-30 SDR SG	1912880000	C.25
CLI M 2-33 SDR SG	1912920000	C.25
CLI M 2-36 SDR SG	1912950000	C.25
CLI M 2-39 SDR SG	1912960000	C.25
CLI M 2-4 BL NE CD	1568301693	C.22
CLI M 2-4 BL/SW - CD	1568301741	C.51
CLI M 2-4 BL/SW - MP	1733651741	C.51
CLI M 2-4 BL/SW 6 CD	1568301521	C.27
CLI M 2-4 BL/SW 6 MP	1733651521	C.27
CLI M 2-4 BL/SW N CD	1568301664	C.51
CLI M 2-4 BL/SW N MP	1733651664	C.51
CLI M 2-4 BR NE CD	1568301692	C.22
CLI M 2-4 BR/WS 1 CD	1568301506	C.27
CLI M 2-4 BR/WS 1 MP	1733651506	C.27
CLI M 2-4 GE NE CD	1568300001	C.22
CLI M 2-4 GE NE MP	1733650004	C.22
CLI M 2-4 GE/SW / CD	1568301742	C.51
CLI M 2-4 GE/SW / MP	1733651742	C.51
CLI M 2-4 GE/SW - CD	1568301740	C.51
CLI M 2-4 GE/SW - MP	1733651740	C.51
CLI M 2-4 GE/SW . CD	1568301748	C.51
CLI M 2-4 GE/SW . MP	1733651748	C.51
CLI M 2-4 GE/SW : CD	1568301750	C.51
CLI M 2-4 GE/SW : MP	1733651750	C.51
CLI M 2-4 GE/SW + CD	1568301738	C.51
CLI M 2-4 GE/SW + MP	1733651738	C.51
CLI M 2-4 GE/SW = CD	1568301751	C.51
CLI M 2-4 GE/SW = MP	1733651751	C.51
CLI M 2-4 GE/SW 0 CD	1568301502	C.50
CLI M 2-4 GE/SW 0 MP	1733651502	C.50
CLI M 2-4 GE/SW 1 CD	1568301505	C.50
CLI M 2-4 GE/SW 1 MP	1733651505	C.50
CLI M 2-4 GE/SW 2 CD	1568301508	C.50
CLI M 2-4 GE/SW 2 MP	1733651508	C.50
CLI M 2-4 GE/SW 3 CD	1568301511	C.50
CLI M 2-4 GE/SW 3 MP	1733651511	C.50
CLI M 2-4 GE/SW 4 CD	1568301514	C.27
CLI M 2-4 GE/SW 4 CD	1568301514	C.50
CLI M 2-4 GE/SW 4 MP	1733651514	C.27
CLI M 2-4 GE/SW 4 MP	1733651514	C.50
CLI M 2-4 GE/SW 5 CD	1568301517	C.50
CLI M 2-4 GE/SW 5 MP	1733651517	C.50
CLI M 2-4 GE/SW 6 CD	1568301520	C.50
CLI M 2-4 GE/SW 6 MP	1733651520	C.50
CLI M 2-4 GE/SW 7 CD	1568301523	C.50
CLI M 2-4 GE/SW 7 MP	1733651523	C.50
CLI M 2-4 GE/SW 8 CD	1568301526	C.50
CLI M 2-4 GE/SW 8 MP	1733651526	C.50
CLI M 2-4 GE/SW 9 CD	1568301529	C.50
CLI M 2-4 GE/SW 9 MP	1733651529	C.50
CLI M 2-4 GE/SW A CD	1568301637	C.50
CLI M 2-4 GE/SW Ä CD	1568301694	C.51
CLI M 2-4 GE/SW Å CD	1568301699	C.51
CLI M 2-4 GE/SW A MP	1733651637	C.50
CLI M 2-4 GE/SW Ä MP	1733651697	C.51
CLI M 2-4 GE/SW Å MP	1733651699	C.51
CLI M 2-4 GE/SW AC CD	1568301752	C.51
CLI M 2-4 GE/SW AC MP	1733651752	C.51
CLI M 2-4 GE/SW Æ CD	1568301735	C.51
CLI M 2-4 GE/SW B CD	1568301639	C.50
CLI M 2-4 GE/SW B MP	1733651639	C.50
CLI M 2-4 GE/SW C CD	1568301641	C.50
CLI M 2-4 GE/SW C MP	1733651641	C.50
CLI M 2-4 GE/SW D CD	1568301643	C.50
CLI M 2-4 GE/SW D MP	1733651643	C.50
CLI M 2-4 GE/SW E CD	1568301645	C.50

Type	Order No.	Page
CLI M 2-4 GE/SW E MP	1733651645	C.50
CLI M 2-4 GE/SW ET CD	1568301746	C.51
CLI M 2-4 GE/SW ET MP	1733651746	C.51
CLI M 2-4 GE/SW F CD	1568301647	C.50
CLI M 2-4 GE/SW F MP	1733651647	C.50
CLI M 2-4 GE/SW G CD	1568301649	C.50
CLI M 2-4 GE/SW G MP	1733651649	C.50
CLI M 2-4 GE/SW H CD	1568301651	C.50
CLI M 2-4 GE/SW H MP	1733651651	C.50
CLI M 2-4 GE/SW I CD	1568301653	C.50
CLI M 2-4 GE/SW I MP	1733651653	C.50
CLI M 2-4 GE/SW J CD	1568301655	C.50
CLI M 2-4 GE/SW J MP	1733651655	C.50
CLI M 2-4 GE/SW K CD	1568301657	C.50
CLI M 2-4 GE/SW K MP	1733651657	C.50
CLI M 2-4 GE/SW L CD	1568301659	C.50
CLI M 2-4 GE/SW L MP	1733651659	C.50
CLI M 2-4 GE/SW M CD	1568301661	C.50
CLI M 2-4 GE/SW M MP	1733651661	C.50
CLI M 2-4 GE/SW N CD	1568301663	C.50
CLI M 2-4 GE/SW N MP	1733651663	C.50
CLI M 2-4 GE/SW O CD	1568301665	C.50
CLI M 2-4 GE/SW Ö CD	1568301695	C.51
CLI M 2-4 GE/SW Ø CD	1568301736	C.51
CLI M 2-4 GE/SW O MP	1733651665	C.50
CLI M 2-4 GE/SW Ö MP	1733651695	C.51
CLI M 2-4 GE/SW P CD	1568301667	C.50
CLI M 2-4 GE/SW P MP	1733651667	C.50
CLI M 2-4 GE/SW PET. CD	1568301747	C.51
CLI M 2-4 GE/SW PET. MP	1733651747	C.51
CLI M 2-4 GE/SW Q CD	1568301669	C.50
CLI M 2-4 GE/SW Q MP	1733651669	C.50
CLI M 2-4 GE/SW R CD	1568301671	C.50
CLI M 2-4 GE/SW R MP	1733651671	C.50
CLI M 2-4 GE/SW S CD	1568301673	C.50
CLI M 2-4 GE/SW S MP	1733651673	C.50
CLI M 2-4 GE/SW T CD	1568301676	C.50
CLI M 2-4 GE/SW T MP	1733651676	C.50
CLI M 2-4 GE/SW U CD	1568301679	C.50
CLI M 2-4 GE/SW U MP	1733651679	C.50
CLI M 2-4 GE/SW V CD	1568301681	C.50
CLI M 2-4 GE/SW V MP	1733651681	C.50
CLI M 2-4 GE/SW W CD	1568301683	C.50
CLI M 2-4 GE/SW W MP	1733651683	C.50
CLI M 2-4 GE/SW X CD	1568301687	C.50
CLI M 2-4 GE/SW X MP	1733651687	C.50
CLI M 2-4 GE/SW Y CD	1568301696	C.50
CLI M 2-4 GE/SW Y MP	1733651696	C.50
CLI M 2-4 GE/SW Z CD	1568301698	C.50
CLI M 2-4 GE/SW Z MP	1733651698	C.50
CLI M 2-4 GN NE CD	1568301688	C.22
CLI M 2-4 GN/SW 5 CD	1568301518	C.27
CLI M 2-4 GN/SW 5 MP	1733651518	C.27
CLI M 2-4 GR/SW 8 CD	1568301527	C.27
CLI M 2-4 GR/SW 8 MP	1733651527	C.27
CLI M 2-4 OR/SW 3 CD	1568301512	C.27
CLI M 2-4 OR/SW 3 MP	1733651512	C.27
CLI M 2-4 RS NE CD	1568301701	C.22
CLI M 2-4 RT NE CD	1568301686	C.22
CLI M 2-4 RT/SW + CD	1568301737	C.51
CLI M 2-4 RT/SW + MP	1733651737	C.51
CLI M 2-4 RT/SW 2 CD	1568301509	C.27
CLI M 2-4 RT/SW 2 MP	1733651509	C.27
CLI M 2-4 SDR CD	1568309999	C.25
CLI M 2-4 SDR SG	1912830000	C.25
CLI M 2-4 SW NE CD	1568301700	C.22
CLI M 2-4 SW/WS 0 CD	1568301503	C.27
CLI M 2-4 SW/WS 0 MP	1733651503	C.27
CLI M 2-4 VI NE CD	1568301689	C.22
CLI M 2-4 VI/SW 7 CD	1568301524	C.27
CLI M 2-4 VI/SW 7 MP	1733651524	C.27
CLI M 2-4 WS NE CD	1568301051	C.22
CLI M 2-4 WS NE MP	1871371044	C.22
CLI M 2-4 WS/SW / CD	1568301050	C.51
CLI M 2-4 WS/SW - CD	1568301049	C.51
CLI M 2-4 WS/SW - MP	1871371740	C.51
CLI M 2-4 WS/SW . CD	1568301047	C.51
CLI M 2-4 WS/SW . MP	1871371748	C.51
CLI M 2-4 WS/SW / MP	1871371742	C.51
CLI M 2-4 WS/SW : CD	1568301054	C.51
CLI M 2-4 WS/SW : MP	1871371750	C.51
CLI M 2-4 WS/SW ? CD	1568301055	C.51
CLI M 2-4 WS/SW + CD	1568301048	C.51
CLI M 2-4 WS/SW + MP	1871371738	C.51
CLI M 2-4 WS/SW = CD	1568301052	C.51
CLI M 2-4 WS/SW = MP	1871371751	C.51
CLI M 2-4 WS/SW 0 CD	1568301000	C.50
CLI M 2-4 WS/SW 0 MP	1871371502	C.50
CLI M 2-4 WS/SW 1 CD	1568301697	C.50
CLI M 2-4 WS/SW 1 MP	1871371505	C.50
CLI M 2-4 WS/SW 2 CD	1568300002	C.50
CLI M 2-4 WS/SW 2 MP	1871371508	C.50
CLI M 2-4 WS/SW 3 CD	1568300003	C.50
CLI M 2-4 WS/SW 3 MP	1871371511	C.50
CLI M 2-4 WS/SW 4 CD	1568300004	C.50
CLI M 2-4 WS/SW 4 MP	1871371514	C.50
CLI M 2-4 WS/SW 5 CD	1568300005	C.50
CLI M 2-4 WS/SW 5 MP	1871371517	C.50
CLI M 2-4 WS/SW 6 CD	1568300006	C.50
CLI M 2-4 WS/SW 6 MP	1871371520	C.50
CLI M 2-4 WS/SW 7 CD	1568300007	C.50
CLI M 2-4 WS/SW 7 MP	1871371523	C.50
CLI M 2-4 WS/SW 8 CD	1568300008	C.50
CLI M 2-4 WS/SW 8 MP	1871371526	C.50
CLI M 2-4 WS/SW 9 CD	1568301530	C.27
CLI M 2-4 WS/SW 9 CD	1568301530	C.50
CLI M 2-4 WS/SW 9 MP	1733651530	C.27
CLI M 2-4 WS/SW 9 MP	1733651530	C.50
CLI M 2-4 WS/SW A CD	1568301021	C.50
CLI M 2-4 WS/SW Ä CD	1568301056	C.51
CLI M 2-4 WS/SW A MP	1871371637	C.50
CLI M 2-4 WS/SW Ä MP	1871371697	C.51
CLI M 2-4 WS/SW Å MP	1871371699	C.51
CLI M 2-4 WS/SW AC CD	1568301059	C.51
CLI M 2-4 WS/SW AC MP	1871371752	C.51
CLI M 2-4 WS/SW B CD	1568301022	C.50
CLI M 2-4 WS/SW B MP	1871371639	C.50
CLI M 2-4 WS/SW C CD	1568301023	C.50
CLI M 2-4 WS/SW C MP	1871371641	C.50
CLI M 2-4 WS/SW D CD	1568301024	C.50
CLI M 2-4 WS/SW D MP	1871371643	C.50
CLI M 2-4 WS/SW E CD	1568301025	C.50
CLI M 2-4 WS/SW E MP	1871371645	C.50
CLI M 2-4 WS/SW ET CD	1568301053	C.51
CLI M 2-4 WS/SW ET MP	1871371746	C.51
CLI M 2-4 WS/SW F CD	1568301026	C.50
CLI M 2-4 WS/SW F MP	1871371647	C.50
CLI M 2-4 WS/SW G CD	1568301027	C.50
CLI M 2-4 WS/SW G MP	1871371649	C.50
CLI M 2-4 WS/SW H CD	1568301028	C.50
CLI M 2-4 WS/SW H MP	1871371651	C.50
CLI M 2-4 WS/SW I CD	1568301029	C.50
CLI M 2-4 WS/SW I MP	1871371653	C.50
CLI M 2-4 WS/SW J CD	1568301030	C.50
CLI M 2-4 WS/SW J MP	1871371655	C.50
CLI M 2-4 WS/SW K CD	1568301031	C.50
CLI M 2-4 WS/SW K MP	1871371657	C.50
CLI M 2-4 WS/SW L CD	1568301032	C.50
CLI M 2-4 WS/SW L MP	1871371659	C.50
CLI M 2-4 WS/SW M CD	1568301033	C.50
CLI M 2-4 WS/SW M MP	1871371661	C.50
CLI M 2-4 WS/SW N CD	1568301034	C.50
CLI M 2-4 WS/SW N MP	1871371663	C.50
CLI M 2-4 WS/SW O CD	1568301035	C.50
CLI M 2-4 WS/SW Ö CD	1568301057	C.51
CLI M 2-4 WS/SW O MP	1871371665	C.50
CLI M 2-4 WS/SW Ö MP	1871371695	C.51
CLI M 2-4 WS/SW P CD	1568301036	C.50
CLI M 2-4 WS/SW P MP	1871371667	C.50
CLI M 2-4 WS/SW PET. CD	1568301058	C.51
CLI M 2-4 WS/SW PET. MP	1871371747	C.51
CLI M 2-4 WS/SW Q CD	1568301037	C.50
CLI M 2-4 WS/SW Q MP	1871371669	C.50
CLI M 2-4 WS/SW R CD	1568301038	C.50
CLI M 2-4 WS/SW R MP	1871371671	C.50
CLI M 2-4 WS/SW S CD	1568301039	C.50
CLI M 2-4 WS/SW S MP	1871371673	C.50
CLI M 2-4 WS/SW T CD	1568301040	C.50
CLI M 2-4 WS/SW T MP	1871371676	C.50
CLI M 2-4 WS/SW U CD	1568301041	C.50
CLI M 2-4 WS/SW U MP	1871371679	C.50
CLI M 2-4 WS/SW V CD	1568301042	C.50
CLI M 2-4 WS/SW V MP	1871371681	C.50
CLI M 2-4 WS/SW W CD	1568301043	C.50
CLI M 2-4 WS/SW W MP	1871371683	C.50
CLI M 2-4 WS/SW X CD	1568301044	C.50
CLI M 2-4 WS/SW X MP	1871371687	C.50
CLI M 2-4 WS/SW Y CD	1568301045	C.50
CLI M 2-4 WS/SW Y MP	1871371696	C.50
CLI M 2-4 WS/SW Z CD	1568301046	C.50
CLI M 2-4 WS/SW Z MP	1871371698	C.50
CLI M 2-40Q GE NEUT SG	1886541687	C.22
CLI M 2-40Q SDR SG	1634790000	C.25
CLI M 2-6 GE/SW L1 CD	1871781728	C.51
CLI M 2-6 GE/SW L1 MP	1871751728	C.51
CLI M 2-6 GE/SW L2 CD	1871781729	C.51
CLI M 2-6 GE/SW L2 MP	1871751729	C.51
CLI M 2-6 GE/SW L3 CD	1871781730	C.51
CLI M 2-6 GE/SW L3 MP	1871751730	C.51
CLI M 2-6 SDR CD	1871789999	C.25
CLI M 2-6 SDR SG	1912840000	C.25
CLI M 2-6 WS/SW L1 CD	1871771728	C.51
CLI M 2-6 WS/SW L1 MP	1871741728	C.51
CLI M 2-6 WS/SW L2 CD	1871771729	C.51
CLI M 2-6 WS/SW L2 MP	1871741729	C.51
CLI M 2-6 WS/SW L3 CD	1871771730	C.51
CLI M 2-6 WS/SW L3 MP	1871741730	C.51
CLI M 2-9 SDR CD	1899250000	C.25
CLI M 2-9 SDR SG	1873440000	C.25
CLI MH 110 HSTR	0189400000	C.52
CLI MH 70 HSTR	0524400000	C.52
CLI O 10-3 BL/SW - MP	0648001741	C.46
CLI O 10-3 GE NE MP	0689600000	C.22
CLI O 10-3 GE/SW - MP	0648001740	C.46
CLI O 10-3 GE/SW + MP	0648001738	C.46
CLI O 10-3 GE/SW 0 MP	0648001502	C.46
CLI O 10-3 GE/SW 1 MP	0648001505	C.46
CLI O 10-3 GE/SW 2 MP	0648001508	C.46
CLI O 10-3 GE/SW 3 MP	0648001511	C.46
CLI O 10-3 GE/SW 4 MP	0648001514	C.46
CLI O 10-3 GE/SW 5 MP	0648001517	C.46
CLI O 10-3 GE/SW 6 MP	0648001520	C.46
CLI O 10-3 GE/SW 7 MP	0648001523	C.46
CLI O 10-3 GE/SW 8 MP	0648001526	C.46
CLI O 10-3 GE/SW 9 MP	0648001529	C.46
CLI O 10-3 GE/SW A MP	0648001637	C.46
CLI O 10-3 GE/SW Ä MP	0648001697	C.46
CLI O 10-3 GE/SW Å MP	0648001699	C.46
CLI O 10-3 GE/SW B MP	0648001639	C.46
CLI O 10-3 GE/SW C MP	0648001641	C.46
CLI O 10-3 GE/SW D MP	0648001643	C.46
CLI O 10-3 GE/SW E MP	0648001645	C.46
CLI O 10-3 GE/SW ET MP	0648001746	C.46
CLI O 10-3 GE/SW F MP	0648001647	C.46
CLI O 10-3 GE/SW G MP	0648001649	C.46
CLI O 10-3 GE/SW H MP	0648001651	C.46
CLI O 10-3 GE/SW I MP	0648001653	C.46
CLI O 10-3 GE/SW J MP	0648001655	C.46
CLI O 10-3 GE/SW K MP	0648001657	C.46
CLI O 10-3 GE/SW L MP	0648001659	C.46
CLI O 10-3 GE/SW M MP	0648001661	C.46
CLI O 10-3 GE/SW N MP	0648001663	C.46
CLI O 10-3 GE/SW O MP	0648001665	C.46
CLI O 10-3 GE/SW Ö MP	0648001695	C.46
CLI O 10-3 GE/SW P MP	0648001667	C.46
CLI O 10-3 GE/SW Q MP	0648001669	C.46
CLI O 10-3 GE/SW R MP	0648001671	C.46
CLI O 10-3 GE/SW S MP	0648001673	C.46
CLI O 10-3 GE/SW T MP	0648001676	C.46
CLI O 10-3 GE/SW U MP	0648001679	C.46
CLI O 10-3 GE/SW V MP	0648001681	C.46
CLI O 10-3 GE/SW W MP	0648001683	C.46
CLI O 10-3 GE/SW X MP	0648001687	C.46
CLI O 10-3 GE/SW Y MP	0648001696	C.46
CLI O 10-3 GE/SW Z MP	0648001698	C.46
CLI O 10-3 RT/SW + MP	0648001737	C.46
CLI O 10-3 SDR MP	0648009999	C.24
CLI O 10-3 WS NE MP	1872681044	C.22
CLI O 10-3 WS/SW - MP	1872681740	C.46
CLI O 10-3 WS/SW + MP	1872681738	C.46
CLI O 10-3 WS/SW 0 MP	1872681502	C.46
CLI O 10-3 WS/SW 1 MP	1872681505	C.46
CLI O 10-3 WS/SW 2 MP	1872681508	C.46
CLI O 10-3 WS/SW 3 MP	1872681511	C.46
CLI O 10-3 WS/SW 4 MP	1872681514	C.46
CLI O 10-3 WS/SW 5 MP	1872681517	C.46
CLI O 10-3 WS/SW 6 MP	1872681520	C.46
CLI O 10-3 WS/SW 7 MP	1872681523	C.46
CLI O 10-3 WS/SW 8 MP	1872681526	C.46
CLI O 10-3 WS/SW 9 MP	1872681529	C.46
CLI O 10-6 SDR MP	0660100000	C.24
CLI O 20-3 BL/SW - MP	0648101741	C.47
CLI O 20-3 GE NE MP	0689700000	C.22
CLI O 20-3 GE/SW - MP	0648101740	C.47
CLI O 20-3 GE/SW + MP	0648101738	C.47
CLI O 20-3 GE/SW 0 MP	0648101502	C.47
CLI O 20-3 GE/SW 1 MP	0648101505	C.47
CLI O 20-3 GE/SW 2 MP	0648101508	C.47
CLI O 20-3 GE/SW 3 MP	0648101511	C.47
CLI O 20-3 GE/SW 4 MP	0648101514	C.47
CLI O 20-3 GE/SW 5 MP	0648101517	C.47
CLI O 20-3 GE/SW 6 MP	0648101520	C.47
CLI O 20-3 GE/SW 7 MP	0648101523	C.47
CLI O 20-3 GE/SW 8 MP	0648101526	C.47
CLI O 20-3 GE/SW 9 MP	0648101529	C.47
CLI O 20-3 GE/SW A MP	0648101637	C.47
CLI O 20-3 GE/SW Ä MP	0648101697	C.47
CLI O 20-3 GE/SW Å MP	0648101699	C.47
CLI O 20-3 GE/SW B MP	0648101639	C.47
CLI O 20-3 GE/SW C MP	0648101641	C.47
CLI O 20-3 GE/SW D MP	0648101643	C.47
CLI O 20-3 GE/SW E MP	0648101645	C.47
CLI O 20-3 GE/SW ET MP	0648101746	C.47
CLI O 20-3 GE/SW F MP	0648101647	C.47
CLI O 20-3 GE/SW G MP	0648101649	C.47
CLI O 20-3 GE/SW H MP	0648101651	C.47
CLI O 20-3 GE/SW I MP	0648101653	C.47
CLI O 20-3 GE/SW J MP	0648101655	C.47
CLI O 20-3 GE/SW K MP	0648101657	C.47
CLI O 20-3 GE/SW L MP	0648101659	C.47
CLI O 20-3 GE/SW M MP	0648101661	C.47
CLI O 20-3 GE/SW N MP	0648101663	C.47
CLI O 20-3 GE/SW O MP	0648101665	C.47
CLI O 20-3 GE/SW Ö MP	0648101695	C.47
CLI O 20-3 GE/SW P MP	0648101667	C.47
CLI O 20-3 GE/SW Q MP	0648101669	C.47
CLI O 20-3 GE/SW R MP	0648101671	C.47
CLI O 20-3 GE/SW S MP	0648101673	C.47
CLI O 20-3 GE/SW T MP	0648101676	C.47
CLI O 20-3 GE/SW U MP	0648101679	C.47
CLI O 20-3 GE/SW V MP	0648101681	C.47
CLI O 20-3 GE/SW W MP	0648101683	C.47
CLI O 20-3 GE/SW X MP	0648101687	C.47
CLI O 20-3 GE/SW Y MP	0648101696	C.47
CLI O 20-3 GE/SW Z MP	0648101698	C.47
CLI O 20-3 RT/SW + MP	0648101737	C.47
CLI O 20-3 SDR MP	0648109999	C.24
CLI O 20-3 WS NE MP	1872691044	C.22
CLI O 20-3 WS/SW - MP	1872691740	C.47
CLI O 20-3 WS/SW + MP	1872691738	C.47
CLI O 20-3 WS/SW 0 MP	1872691502	C.47
CLI O 20-3 WS/SW 1 MP	1872691505	C.47
CLI O 20-3 WS/SW 2 MP	1872691508	C.47
CLI O 20-3 WS/SW 3 MP	1872691511	C.47
CLI O 20-3 WS/SW 4 MP	1872691514	C.47
CLI O 20-3 WS/SW 5 MP	1872691517	C.47
CLI O 20-3 WS/SW 6 MP	1872691520	C.47
CLI O 20-3 WS/SW 7 MP	1872691523	C.47
CLI O 20-3 WS/SW 8 MP	1872691526	C.47
CLI O 20-3 WS/SW 9 MP	1872691529	C.47
CLI O 20-6 SDR MP	0694700000	C.24
CLI O 30-3 BL/SW - MP	0648201741	C.48
CLI O 30-3 GE NE MP	0689800000	C.22
CLI O 30-3 GE/SW - MP	0648201740	C.48
CLI O 30-3 GE/SW + MP	0648201738	C.48
CLI O 30-3 GE/SW 0 MP	0648201502	C.48
CLI O 30-3 GE/SW 1 MP	0648201505	C.48
CLI O 30-3 GE/SW 2 MP	0648201508	C.48
CLI O 30-3 GE/SW 3 MP	0648201511	C.48
CLI O 30-3 GE/SW 4 MP	0648201514	C.48
CLI O 30-3 GE/SW 5 MP	0648201517	C.48
CLI O 30-3 GE/SW 6 MP	0648201520	C.48
CLI O 30-3 GE/SW 7 MP	0648201523	C.48
CLI O 30-3 GE/SW 8 MP	0648201526	C.48
CLI O 30-3 GE/SW 9 MP	0648201529	C.48
CLI O 30-3 GE/SW A MP	0648201637	C.48
CLI O 30-3 GE/SW Ä MP	0648201697	C.48
CLI O 30-3 GE/SW Å MP	0648201699	C.48
CLI O 30-3 GE/SW B MP	0648201639	C.48
CLI O 30-3 GE/SW C MP	0648201641	C.48
CLI O 30-3 GE/SW D MP	0648201643	C.48
CLI O 30-3 GE/SW E MP	0648201645	C.48
CLI O 30-3 GE/SW ET MP	0648201746	C.48
CLI O 30-3 GE/SW F MP	0648201647	C.48
CLI O 30-3 GE/SW G MP	0648201649	C.48
CLI O 30-3 GE/SW H MP	0648201651	C.48
CLI O 30-3 GE/SW I MP	0648201653	C.48
CLI O 30-3 GE/SW J MP	0648201655	C.48
CLI O 30-3 GE/SW K MP	0648201657	C.48
CLI O 30-3 GE/SW L MP	0648201659	C.48
CLI O 30-3 GE/SW M MP	0648201661	C.48
CLI O 30-3 GE/SW N MP	0648201663	C.48
CLI O 30-3 GE/SW O MP	0648201665	C.48
CLI O 30-3 GE/SW Ö MP	0648201695	C.48
CLI O 30-3 GE/SW P MP	0648201667	C.48
CLI O 30-3 GE/SW Q MP	0648201669	C.48
CLI O 30-3 GE/SW R MP	0648201671	C.48
CLI O 30-3 GE/SW S MP	0648201673	C.48
CLI O 30-3 GE/SW T MP	0648201676	C.48
CLI O 30-3 GE/SW U MP	0648201679	C.48
CLI O 30-3 GE/SW V MP	0648201681	C.48
CLI O 30-3 GE/SW W MP	0648201683	C.48
CLI O 30-3 GE/SW X MP	0648201687	C.48
CLI O 30-3 GE/SW Y MP	0648201696	C.48
CLI O 30-3 GE/SW Z MP	0648201698	C.48
CLI O 30-3 RT/SW + MP	0648201737	C.48
CLI O 30-3 SDR MP	0648209999	C.24
CLI O 30-3 WS NE MP	1872701044	C.22
CLI O 30-3 WS/SW - MP	1872701740	C.48
CLI O 30-3 WS/SW + MP	1872701738	C.48
CLI O 30-3 WS/SW 0 MP	1872701502	C.48
CLI O 30-3 WS/SW 1 MP	1872701505	C.48
CLI O 30-3 WS/SW 2 MP	1872701508	C.48
CLI O 30-3 WS/SW 3 MP	1872701511	C.48
CLI O 30-3 WS/SW 4 MP	1872701514	C.48
CLI O 30-3 WS/SW 5 MP	1872701517	C.48
CLI O 30-3 WS/SW 6 MP	1872701520	C.48
CLI O 30-3 WS/SW 7 MP	1872701523	C.48
CLI O 30-3 WS/SW 8 MP	1872701526	C.48
CLI O 30-3 WS/SW 9 MP	1872701529	C.48
CLI O 30-6 SDR MP	1873470000	C.24
CLI R 02 F. CLI C 02-3	0559900000	C.53
CLI R 02-3 BL/SW -	0560001741	C.43
CLI R 02-3 BL/SW +	0560001737	C.43
CLI R 02-3 BL/SW 6	0560001521	C.27
CLI R 02-3 BL/SW N	0560001746	C.43
CLI R 02-3 BR/WS 1	0560001506	C.27
CLI R 02-3 GE NE	0560001687	C.20
CLI R 02-3 GE/SW -	0560001740	C.42
CLI R 02-3 GE/SW .	0560001749	C.42
CLI R 02-3 GE/SW /	0560001743	C.42
CLI R 02-3 GE/SW +	0560001738	C.42
CLI R 02-3 GE/SW 0	0560001501	C.42
CLI R 02-3 GE/SW 1	0560001504	C.42
CLI R 02-3 GE/SW 2	0560001507	C.42
CLI R 02-3 GE/SW 3	0560001510	C.42
CLI R 02-3 GE/SW 4	0560001513	C.27
CLI R 02-3 GE/SW 4	0560001513	C.42
CLI R 02-3 GE/SW 5	0560001516	C.42
CLI R 02-3 GE/SW 6	0560001519	C.42
CLI R 02-3 GE/SW 7	0560001522	C.42
CLI R 02-3 GE/SW 8	0560001525	C.42
CLI R 02-3 GE/SW 9	0560001528	C.42
CLI R 02-3 GE/SW A	0560001638	C.42
CLI R 02-3 GE/SW Ä	0560001696	C.42
CLI R 02-3 GE/SW Å	0560001698	C.42
CLI R 02-3 GE/SW B	0560001640	C.42
CLI R 02-3 GE/SW C	0560001642	C.42
CLI R 02-3 GE/SW D	0560001644	C.42
CLI R 02-3 GE/SW E	0560001646	C.42

Type	Order No.	Page
CLI R 02-3 GE/SW ET	0560001745	C.42
CLI R 02-3 GE/SW F	0560001648	C.42
CLI R 02-3 GE/SW G	0560001650	C.42
CLI R 02-3 GE/SW H	0560001652	C.42
CLI R 02-3 GE/SW I	0560001654	C.42
CLI R 02-3 GE/SW J	0560001656	C.42
CLI R 02-3 GE/SW K	0560001658	C.42
CLI R 02-3 GE/SW L	0560001660	C.42
CLI R 02-3 GE/SW M	0560001662	C.42
CLI R 02-3 GE/SW N	0560001664	C.42
CLI R 02-3 GE/SW O	0560001666	C.42
CLI R 02-3 GE/SW Ö	0560001695	C.42
CLI R 02-3 GE/SW P	0560001668	C.42
CLI R 02-3 GE/SW Q	0560001670	C.42
CLI R 02-3 GE/SW R	0560001672	C.42
CLI R 02-3 GE/SW S	0560001675	C.42
CLI R 02-3 GE/SW T	0560001678	C.42
CLI R 02-3 GE/SW U	0560001680	C.42
CLI R 02-3 GE/SW V	0560001682	C.42
CLI R 02-3 GE/SW W	0560001684	C.42
CLI R 02-3 GE/SW X	0560001693	C.42
CLI R 02-3 GE/SW Y	0560001697	C.42
CLI R 02-3 GE/SW Z	0560001699	C.42
CLI R 02-3 GN/SW 5	0560001518	C.27
CLI R 02-3 GR/SW 8	0560001527	C.27
CLI R 02-3 OR/SW 3	0560001512	C.27
CLI R 02-3 RT/SW +	0560001739	C.43
CLI R 02-3 RT/SW 2	0560001509	C.27
CLI R 02-3 SDR	0560009999	C.23
CLI R 02-3 SET 0-9,R,S, T TO GR NEUT	0560001531	C.54
CLI R 02-3 SW/WS 0	0560001503	C.27
CLI R 02-3 VI/SW 7	0560001524	C.27
CLI R 02-3 WS/SW 0	1872711502	C.42
CLI R 02-3 WS/SW 1	1872711505	C.42
CLI R 02-3 WS/SW 2	1872711508	C.42
CLI R 02-3 WS/SW 3	1872711511	C.42
CLI R 02-3 WS/SW 4	1872711514	C.42
CLI R 02-3 WS/SW 5	1872711517	C.42
CLI R 02-3 WS/SW 6	1872711520	C.42
CLI R 02-3 WS/SW 7	1872711523	C.42
CLI R 02-3 WS/SW 8	1872711526	C.42
CLI R 02-3 WS/SW 9	0560001530	C.27
CLI R 02-3 WS/SW 9	0560001530	C.42
CLI R 1 F. CLI C 1-3	0532100000	C.53
CLI R 1-12 BL/SW L1JI	1872751033	C.44
CLI R 1-12 BL/SW L2JI	1872751034	C.44
CLI R 1-12 BL/SW L3JI	1872751035	C.44
CLI R 1-12 BR/WS L1JI	1872751030	C.44
CLI R 1-12 SW/WS L2JI	1872751031	C.44
CLI R 1-12 WS/SW L3JI	1872751032	C.44
CLI R 1-3 BL NE	0572900002	C.20
CLI R 1-3 BL/SW -	0572901741	C.44
CLI R 1-3 BL/SW 6	0572901520	C.27
CLI R 1-3 BL/SW N	0572901746	C.44
CLI R 1-3 BR/WS 1	0572901505	C.27
CLI R 1-3 GE NE	0572901687	C.20
CLI R 1-3 GE/SW -	0572901740	C.44
CLI R 1-3 GE/SW .	0572901749	C.44
CLI R 1-3 GE/SW /	0572901743	C.44
CLI R 1-3 GE/SW +	0572901738	C.44
CLI R 1-3 GE/SW 0	0572901503	C.43
CLI R 1-3 GE/SW 1	0572901506	C.43
CLI R 1-3 GE/SW 2	0572901509	C.43
CLI R 1-3 GE/SW 3	0572901512	C.43
CLI R 1-3 GE/SW 4	0572901515	C.27
CLI R 1-3 GE/SW 4	0572901515	C.43
CLI R 1-3 GE/SW 5	0572901518	C.43
CLI R 1-3 GE/SW 6	0572901521	C.43
CLI R 1-3 GE/SW 7	0572901524	C.43
CLI R 1-3 GE/SW 8	0572901527	C.43
CLI R 1-3 GE/SW 9	0572901530	C.43
CLI R 1-3 GE/SW A	0572901638	C.43
CLI R 1-3 GE/SW Ä	0572901696	C.44
CLI R 1-3 GE/SW Å	0572901698	C.44
CLI R 1-3 GE/SW B	0572901640	C.43
CLI R 1-3 GE/SW C	0572901642	C.43
CLI R 1-3 GE/SW D	0572901644	C.43
CLI R 1-3 GE/SW E	0572901646	C.43
CLI R 1-3 GE/SW ET	0572901745	C.44
CLI R 1-3 GE/SW F	0572901648	C.43
CLI R 1-3 GE/SW G	0572901650	C.43
CLI R 1-3 GE/SW H	0572901652	C.43
CLI R 1-3 GE/SW I	0572901654	C.43
CLI R 1-3 GE/SW J	0572901656	C.43
CLI R 1-3 GE/SW K	0572901658	C.43
CLI R 1-3 GE/SW L	0572901660	C.43
CLI R 1-3 GE/SW M	0572901662	C.43
CLI R 1-3 GE/SW N	0572901664	C.43
CLI R 1-3 GE/SW O	0572901666	C.43
CLI R 1-3 GE/SW Ö	0572901695	C.44
CLI R 1-3 GE/SW P	0572901668	C.43
CLI R 1-3 GE/SW Q	0572901670	C.43
CLI R 1-3 GE/SW R	0572901672	C.43
CLI R 1-3 GE/SW S	0572901675	C.43
CLI R 1-3 GE/SW T	0572901678	C.43
CLI R 1-3 GE/SW U	0572901680	C.43
CLI R 1-3 GE/SW V	0572901682	C.43
CLI R 1-3 GE/SW W	0572901684	C.43
CLI R 1-3 GE/SW X	0572901693	C.43
CLI R 1-3 GE/SW Y	0572901697	C.43
CLI R 1-3 GE/SW Z	0572901699	C.43
CLI R 1-3 GN/SW 5	0572901517	C.27
CLI R 1-3 GR/SW 8	0572901526	C.27
CLI R 1-3 OR/SW 3	0572901511	C.27
CLI R 1-3 RT/SW +	0572901739	C.44
CLI R 1-3 RT/SW 2	0572901508	C.27
CLI R 1-3 SDR	0572909999	C.23
CLI R 1-3 SET 0-9,R,S, T TO GR NEUT	0572901531	C.54
CLI R 1-3 SW/WS 0	0572901502	C.27
CLI R 1-3 VI/SW 7	0572901523	C.27
CLI R 1-3 WS/SW 9	0572901529	C.27
CLI R 1-9 BL/SW NJU	1872761036	C.44
CLI R 1-9 BR/WS L1I	1872761030	C.44
CLI R 1-9 BR/WS L1U	1872761033	C.44
CLI R 1-9 SW/WS L2I	1872761031	C.44
CLI R 1-9 SW/WS L2U	1872761034	C.44
CLI R 1-9 WS/SW L3I	1872761032	C.44
CLI R 1-9 WS/SW L3U	1872761035	C.44
CLI RH 20-02 CLI R 02	0563700000	C.52
CLI RH 20-10 CLI R 10	0563600000	C.52
CLI RS 3 MDCLI C 02	0559200000	C.53
CLI RS 4 MDCLI C1+02	0559300000	C.53
CLI RS 5 MDCLI C 1	0648300000	C.53
CLI T 02-12	1764060000	C.11
CLI T 02-15	1764070000	C.11
CLI T 02-18	1764140000	C.11
CLI T 02-20	1764150000	C.11
CLI T 02-30	1889580000	C.11
CLI T 1-12	1764190000	C.11
CLI T 1-15	1764200000	C.11
CLI T 1-18	1764210000	C.11
CLI T 1-20	1764220000	C.11
CLI T 1-30	1889560000	C.11
CLI T 2-12	1764230000	C.11
CLI T 2-15	1764240000	C.11
CLI T 2-18	1764250000	C.11
CLI T 2-20	1764260000	C.11
CLI T 2-30	1889570000	C.11
CLI T 3-12	1764270000	C.11
CLI T 3-15	1764280000	C.11
CLI T 3-18	1764290000	C.11
CLI T 3-20	1764300000	C.11
CLI T 3-30	1889550000	C.11
CLI TM 10-33	1763270000	C.11
CLI TM 20-33	1763280000	C.11
CLI TM 20-66	1763390000	C.11

D

Type	Order No.	Page
DEK 5 BL NEUTRAL	0473391693	B.7
DEK 5 BR NEUTRAL	0473391692	B.7
DEK 5 FS 101-150	0473560101	B.7
DEK 5 FS 1-50	0473560001	B.7
DEK 5 FS 151-200	0473560151	B.7
DEK 5 FS 201-250	0473560201	B.7
DEK 5 FS 251-300	0473560251	B.7
DEK 5 FS 301-350	0473560301	B.7
DEK 5 FS 351-400	0473560351	B.7
DEK 5 FS 401-450	0473560401	B.7
DEK 5 FS 451-500	0473560451	B.7
DEK 5 FS 501-550	0473560501	B.7
DEK 5 FS 51-100	0473560051	B.7
DEK 5 FS 551-600	0473560551	B.7
DEK 5 FS 601-650	0473560601	B.7
DEK 5 FS 651-700	0473560651	B.7
DEK 5 FS 701-750	0473560701	B.7
DEK 5 FS 751-800	0473560751	B.7
DEK 5 FS 801-850	0473560801	B.7
DEK 5 FS 851-900	0473560851	B.7
DEK 5 FS 901-950	0473560901	B.7
DEK 5 FS 951-999	0473560951	B.7
DEK 5 FSZ 1-10	0460660001	B.7
DEK 5 FSZ 11-20	0460660011	B.7
DEK 5 FSZ 21-30	0460660021	B.7
DEK 5 FSZ 31-40	0460660031	B.7
DEK 5 FSZ 41-50	0460660041	B.7
DEK 5 FSZ 51-60	0460660051	B.7
DEK 5 FSZ 61-70	0460660061	B.7
DEK 5 FSZ 71-80	0460660071	B.7
DEK 5 FSZ 81-90	0460660081	B.7
DEK 5 FSZ 91-100	0460660091	B.7
DEK 5 FW 1,3,5,...99	1358460000	B.7
DEK 5 FW 101-150	0473460101	B.7
DEK 5 FW 10-500	0132660010	B.7
DEK 5 FW 1-50	0473460001	B.7
DEK 5 FW 151-200	0473460151	B.7
DEK 5 FW 2,4,...100	1358560000	B.7
DEK 5 FW 201-250	0473460201	B.7
DEK 5 FW 251-300	0473460251	B.7
DEK 5 FW 301-350	0473460301	B.7
DEK 5 FW 351-400	0473460351	B.7
DEK 5 FW 401-450	0473460401	B.7
DEK 5 FW 451-500	0473460451	B.7
DEK 5 FW 501-550	0473460501	B.7
DEK 5 FW 51-100	0473460051	B.7
DEK 5 FW 551-600	0473460551	B.7
DEK 5 FW 601-650	0473460601	B.7
DEK 5 FW 651-700	0473460651	B.7
DEK 5 FW 701-750	0473460701	B.7
DEK 5 FW 751-800	0473460751	B.7
DEK 5 FW 801-850	0473460801	B.7
DEK 5 FW 851-900	0473460851	B.7
DEK 5 FW 901-950	0473460901	B.7
DEK 5 FW 951-999	0473460951	B.7
DEK 5 FW U1-PE1	0133161114	B.7
DEK 5 FW U2-PE2	0133161115	B.7
DEK 5 FW U3-PE3	0133161116	B.7
DEK 5 FW U4-PE4	0133161117	B.7
DEK 5 FW U5-PE5	0133161118	B.7
DEK 5 FW U6-PE6	0133161119	B.7
DEK 5 FW U7-PE7	0133161120	B.7
DEK 5 FW U8-PE8	0133161121	B.7
DEK 5 FW U9-PE9	0133161122	B.7
DEK 5 FW X10-Z10	0133261159	B.7
DEK 5 FW X1-Z1	0133261150	B.7
DEK 5 FW X2-Z2	0133261151	B.7
DEK 5 FW X3-Z3	0133261152	B.7
DEK 5 FW X4-Z4	0133261153	B.7
DEK 5 FW X5-Z5	0133261154	B.7
DEK 5 FW X6-Z6	0133261155	B.7
DEK 5 FW X7-Z7	0133261156	B.7
DEK 5 FW X8-Z8	0133261157	B.7
DEK 5 FW X9-Z9	0133261158	B.7
DEK 5 FWZ 1,3,5-19	0235860000	B.7
DEK 5 FWZ 1-10	0523060001	B.7
DEK 5 FWZ 11-20	0523060011	B.7
DEK 5 FWZ 1-9	1572000000	B.7
DEK 5 FWZ 2,4,6-20	0236160000	B.7
DEK 5 FWZ 21,23,25-39	0235960000	B.7
DEK 5 FWZ 21-30	0523060021	B.7
DEK 5 FWZ 22,24,26-40	0236260000	B.7
DEK 5 FWZ 31-40	0523060031	B.7
DEK 5 FWZ 41,43,45-59	0236060000	B.7
DEK 5 FWZ 41-50	0523060041	B.7
DEK 5 FWZ 42,44,46-60	0236360000	B.7
DEK 5 FWZ 51-60	0523060051	B.7
DEK 5 FWZ 61-70	0523060061	B.7
DEK 5 FWZ 71-80	0523060071	B.7
DEK 5 FWZ 81-90	0523060081	B.7
DEK 5 FWZ 91-100	0523060091	B.7
DEK 5 FWZ L1-EIK	0354361203	B.7
DEK 5 FWZ L1-PE	0354361187	B.7
DEK 5 FWZ U,V,W,N,PE	0558360000	B.7
DEK 5 GE NEUTRAL	0473391687	B.7
DEK 5 GN NEUTRAL	0473391688	B.7
DEK 5 GR NEUTRAL	0473391691	B.7
DEK 5 GS A	0132961021	B.7
DEK 5 GS B	0132961022	B.7
DEK 5 GS C	0132961023	B.7
DEK 5 GS D	0132961024	B.7
DEK 5 GS E	0132961025	B.7
DEK 5 GS ERDE	0157261202	B.7
DEK 5 GS ERDE IM KREIS	0157261203	B.7
DEK 5 GS F	0132961026	B.7
DEK 5 GS G	0132961027	B.7
DEK 5 GS H	0132961028	B.7
DEK 5 GS I	0132961029	B.7
DEK 5 GS J	0132961030	B.7
DEK 5 GS K	0132961031	B.7
DEK 5 GS L	0132961032	B.7
DEK 5 GS M	0132961033	B.7
DEK 5 GS N	0132961034	B.7
DEK 5 GS O	0132961035	B.7
DEK 5 GS P	0132961036	B.7
DEK 5 GS PE	0157261187	B.7
DEK 5 GS Q	0132961037	B.7
DEK 5 GS R	0132961038	B.7
DEK 5 GS S	0132961039	B.7
DEK 5 GS T	0132961040	B.7
DEK 5 GS U	0132961041	B.7
DEK 5 GS V	0132961042	B.7
DEK 5 GS W	0132961043	B.7
DEK 5 GS X	0132961044	B.7
DEK 5 GS Y	0132961045	B.7
DEK 5 GS Z	0132961046	B.7
DEK 5 GW	0576260000	B.7
DEK 5 GW -	0576261199	B.8
DEK 5 GW +	0576261198	B.8
DEK 5 GW 1	0522660001	B.7
DEK 5 GW 10	0522660010	B.7
DEK 5 GW 100	0522660100	B.7
DEK 5 GW 101	0522660101	B.7
DEK 5 GW 102	0522660102	B.7
DEK 5 GW 103	0522660103	B.7
DEK 5 GW 104	0522660104	B.7
DEK 5 GW 105	0522660105	B.7
DEK 5 GW 106	0522660106	B.7
DEK 5 GW 107	0522660107	B.7
DEK 5 GW 108	0522660108	B.7
DEK 5 GW 109	0522660109	B.7
DEK 5 GW 11	0522660011	B.7
DEK 5 GW 110	0522660110	B.7
DEK 5 GW 111	0522660111	B.7
DEK 5 GW 112	0522660112	B.7
DEK 5 GW 113	0522660113	B.7
DEK 5 GW 114	0522660114	B.7
DEK 5 GW 115	0522660115	B.7
DEK 5 GW 116	0522660116	B.7
DEK 5 GW 117	0522660117	B.7
DEK 5 GW 118	0522660118	B.7
DEK 5 GW 119	0522660119	B.7
DEK 5 GW 12	0522660012	B.7
DEK 5 GW 120	0522660120	B.7
DEK 5 GW 121	0522660121	B.7
DEK 5 GW 122	0522660122	B.7
DEK 5 GW 123	0522660123	B.7
DEK 5 GW 124	0522660124	B.7
DEK 5 GW 125	0522660125	B.7
DEK 5 GW 126	0522660126	B.7
DEK 5 GW 127	0522660127	B.7
DEK 5 GW 128	0522660128	B.7
DEK 5 GW 129	0522660129	B.7
DEK 5 GW 13	0522660013	B.7
DEK 5 GW 130	0522660130	B.7
DEK 5 GW 131	0522660131	B.7
DEK 5 GW 132	0522660132	B.7
DEK 5 GW 133	0522660133	B.7
DEK 5 GW 134	0522660134	B.7
DEK 5 GW 135	0522660135	B.7
DEK 5 GW 136	0522660136	B.7
DEK 5 GW 137	0522660137	B.7
DEK 5 GW 138	0522660138	B.7
DEK 5 GW 139	0522660139	B.7
DEK 5 GW 14	0522660014	B.7
DEK 5 GW 140	0522660140	B.7
DEK 5 GW 141	0522660141	B.7
DEK 5 GW 142	0522660142	B.7
DEK 5 GW 143	0522660143	B.7
DEK 5 GW 144	0522660144	B.7
DEK 5 GW 145	0522660145	B.7
DEK 5 GW 146	0522660146	B.7
DEK 5 GW 147	0522660147	B.7
DEK 5 GW 148	0522660148	B.7
DEK 5 GW 149	0522660149	B.7
DEK 5 GW 15	0522660015	B.7
DEK 5 GW 150	0522660150	B.7
DEK 5 GW 151	0522660151	B.7
DEK 5 GW 152	0522660152	B.7
DEK 5 GW 153	0522660153	B.7
DEK 5 GW 154	0522660154	B.7
DEK 5 GW 155	0522660155	B.7
DEK 5 GW 156	0522660156	B.7
DEK 5 GW 157	0522660157	B.7
DEK 5 GW 158	0522660158	B.7
DEK 5 GW 159	0522660159	B.7
DEK 5 GW 16	0522660016	B.7
DEK 5 GW 160	0522660160	B.7
DEK 5 GW 161	0522660161	B.7
DEK 5 GW 162	0522660162	B.7
DEK 5 GW 163	0522660163	B.7
DEK 5 GW 164	0522660164	B.7
DEK 5 GW 165	0522660165	B.7
DEK 5 GW 166	0522660166	B.7
DEK 5 GW 167	0522660167	B.7
DEK 5 GW 168	0522660168	B.7
DEK 5 GW 169	0522660169	B.7
DEK 5 GW 17	0522660017	B.7
DEK 5 GW 170	0522660170	B.7
DEK 5 GW 171	0522660171	B.7
DEK 5 GW 172	0522660172	B.7
DEK 5 GW 173	0522660173	B.7
DEK 5 GW 174	0522660174	B.7
DEK 5 GW 175	0522660175	B.7
DEK 5 GW 176	0522660176	B.7
DEK 5 GW 177	0522660177	B.7
DEK 5 GW 178	0522660178	B.7
DEK 5 GW 179	0522660179	B.7
DEK 5 GW 18	0522660018	B.7
DEK 5 GW 180	0522660180	B.7
DEK 5 GW 181	0522660181	B.7
DEK 5 GW 182	0522660182	B.7
DEK 5 GW 183	0522660183	B.7
DEK 5 GW 184	0522660184	B.7
DEK 5 GW 185	0522660185	B.7
DEK 5 GW 186	0522660186	B.7
DEK 5 GW 187	0522660187	B.7
DEK 5 GW 188	0522660188	B.7
DEK 5 GW 189	0522660189	B.7
DEK 5 GW 19	0522660019	B.7
DEK 5 GW 190	0522660190	B.7
DEK 5 GW 191	0522660191	B.7
DEK 5 GW 192	0522660192	B.7
DEK 5 GW 193	0522660193	B.7
DEK 5 GW 194	0522660194	B.7
DEK 5 GW 195	0522660195	B.7
DEK 5 GW 196	0522660196	B.7
DEK 5 GW 197	0522660197	B.7
DEK 5 GW 198	0522660198	B.7
DEK 5 GW 199	0522660199	B.7
DEK 5 GW 2	0522660002	B.7
DEK 5 GW 20	0522660020	B.7
DEK 5 GW 200	0522660200	B.7
DEK 5 GW 21	0522660021	B.7
DEK 5 GW 22	0522660022	B.7
DEK 5 GW 23	0522660023	B.7
DEK 5 GW 24	0522660024	B.7
DEK 5 GW 25	0522660025	B.7
DEK 5 GW 26	0522660026	B.7

Type	Order No.	Page
DEK 5 GW 27	0522660027	B.7
DEK 5 GW 28	0522660028	B.7
DEK 5 GW 29	0522660029	B.7
DEK 5 GW 3	0522660003	B.7
DEK 5 GW 30	0522660030	B.7
DEK 5 GW 31	0522660031	B.7
DEK 5 GW 32	0522660032	B.7
DEK 5 GW 33	0522660033	B.7
DEK 5 GW 34	0522660034	B.7
DEK 5 GW 35	0522660035	B.7
DEK 5 GW 36	0522660036	B.7
DEK 5 GW 37	0522660037	B.7
DEK 5 GW 38	0522660038	B.7
DEK 5 GW 39	0522660039	B.7
DEK 5 GW 4	0522660004	B.7
DEK 5 GW 40	0522660040	B.7
DEK 5 GW 41	0522660041	B.7
DEK 5 GW 42	0522660042	B.7
DEK 5 GW 43	0522660043	B.7
DEK 5 GW 44	0522660044	B.7
DEK 5 GW 45	0522660045	B.7
DEK 5 GW 46	0522660046	B.7
DEK 5 GW 47	0522660047	B.7
DEK 5 GW 48	0522660048	B.7
DEK 5 GW 49	0522660049	B.7
DEK 5 GW 5	0522660005	B.7
DEK 5 GW 50	0522660050	B.7
DEK 5 GW 51	0522660051	B.7
DEK 5 GW 52	0522660052	B.7
DEK 5 GW 53	0522660053	B.7
DEK 5 GW 54	0522660054	B.7
DEK 5 GW 55	0522660055	B.7
DEK 5 GW 56	0522660056	B.7
DEK 5 GW 57	0522660057	B.7
DEK 5 GW 58	0522660058	B.7
DEK 5 GW 59	0522660059	B.7
DEK 5 GW 6	0522660006	B.7
DEK 5 GW 60	0522660060	B.7
DEK 5 GW 61	0522660061	B.7
DEK 5 GW 62	0522660062	B.7
DEK 5 GW 63	0522660063	B.7
DEK 5 GW 64	0522660064	B.7
DEK 5 GW 65	0522660065	B.7
DEK 5 GW 66	0522660066	B.7
DEK 5 GW 67	0522660067	B.7
DEK 5 GW 68	0522660068	B.7
DEK 5 GW 69	0522660069	B.7
DEK 5 GW 7	0522660007	B.7
DEK 5 GW 70	0522660070	B.7
DEK 5 GW 71	0522660071	B.7
DEK 5 GW 72	0522660072	B.7
DEK 5 GW 73	0522660073	B.7
DEK 5 GW 74	0522660074	B.7
DEK 5 GW 75	0522660075	B.7
DEK 5 GW 76	0522660076	B.7
DEK 5 GW 77	0522660077	B.7
DEK 5 GW 78	0522660078	B.7
DEK 5 GW 79	0522660079	B.7
DEK 5 GW 8	0522660008	B.7
DEK 5 GW 80	0522660080	B.7
DEK 5 GW 81	0522660081	B.7
DEK 5 GW 82	0522660082	B.7
DEK 5 GW 83	0522660083	B.7
DEK 5 GW 84	0522660084	B.7
DEK 5 GW 85	0522660085	B.7
DEK 5 GW 86	0522660086	B.7
DEK 5 GW 87	0522660087	B.7
DEK 5 GW 88	0522660088	B.7
DEK 5 GW 89	0522660089	B.7
DEK 5 GW 9	0522660009	B.7
DEK 5 GW 90	0522660090	B.7
DEK 5 GW 91	0522660091	B.7
DEK 5 GW 92	0522660092	B.7
DEK 5 GW 93	0522660093	B.7
DEK 5 GW 94	0522660094	B.7
DEK 5 GW 95	0522660095	B.7
DEK 5 GW 96	0522660096	B.7
DEK 5 GW 97	0522660097	B.7
DEK 5 GW 98	0522660098	B.7
DEK 5 GW 99	0522660099	B.7
DEK 5 GW A	0522761021	B.7
DEK 5 GW B	0522761022	B.7
DEK 5 GW BL/SW -	0576291741	B.7
DEK 5 GW C	0522761023	B.7
DEK 5 GW D	0522761024	B.7
DEK 5 GW E	0522761025	B.7
DEK 5 GW ERDE	0576261202	B.8
DEK 5 GW ERDE I.KR.	0576261203	B.8
DEK 5 GW F	0522761026	B.7
DEK 5 GW G	0522761027	B.7
DEK 5 GW H	0522761028	B.7
DEK 5 GW I	0522761029	B.7
DEK 5 GW J	0522761030	B.7
DEK 5 GW K	0522761031	B.7
DEK 5 GW L	0522761032	B.7
DEK 5 GW L1	0522361075	B.7
DEK 5 GW L2	0522361076	B.7
DEK 5 GW L3	0522361077	B.7
DEK 5 GW M	0522761033	B.7
DEK 5 GW Mp	0537261235	B.8

Type	Order No.	Page
DEK 5 GW N	0522761034	B.8
DEK 5 GW O	0522761035	B.8
DEK 5 GW P	0522761036	B.8
DEK 5 GW PE	0537261187	B.8
DEK 5 GW PEN	0537261188	B.8
DEK 5 GW Q	0522761037	B.8
DEK 5 GW R	0522761038	B.8
DEK 5 GW RT/SW +	0576291737	B.8
DEK 5 GW S	0522761039	B.8
DEK 5 GW T	0522761040	B.8
DEK 5 GW U	0522761041	B.8
DEK 5 GW V	0522761042	B.8
DEK 5 GW W	0522761043	B.8
DEK 5 GW W-STROM	0576261215	B.8
DEK 5 GW X	0522761044	B.8
DEK 5 GW Y	0522761045	B.8
DEK 5 GW Z	0522761046	B.8
DEK 5 NEUTRAL	0473360000	B.8
DEK 5 OR NEUTRAL	0473391690	B.8
DEK 5 RT NEUTRAL	0473391686	B.8
DEK 5 SW NEUTRAL	0473391694	B.8
DEK 5 VI NEUTRAL	0473391689	B.8
DEK 5/3,5 MC bedruckt	1767730000	B.11
DEK 5/3,5 MC FSZ 101-110	1762320101	B.8
DEK 5/3,5 MC FSZ 1-10	1762320001	B.8
DEK 5/3,5 MC FSZ 111-120	1762320111	B.8
DEK 5/3,5 MC FSZ 11-20	1762320011	B.8
DEK 5/3,5 MC FSZ 121-130	1762320121	B.8
DEK 5/3,5 MC FSZ 131-140	1762320131	B.8
DEK 5/3,5 MC FSZ 141-150	1762320141	B.8
DEK 5/3,5 MC FSZ 21-30	1762320021	B.8
DEK 5/3,5 MC FSZ 31-40	1762320031	B.8
DEK 5/3,5 MC FSZ 41-50	1762320041	B.8
DEK 5/3,5 MC FSZ 51-60	1762320051	B.8
DEK 5/3,5 MC FSZ 61-70	1762320061	B.8
DEK 5/3,5 MC FSZ 71-80	1762320071	B.8
DEK 5/3,5 MC FSZ 81-90	1762320081	B.8
DEK 5/3,5 MC FSZ 91-100	1762320091	B.8
DEK 5/3,5 MC GW 0	1755281000	B.8
DEK 5/3,5 MC GW 1	1755280001	B.8
DEK 5/3,5 MC GW 2	1755280002	B.8
DEK 5/3,5 MC GW 3	1755280003	B.8
DEK 5/3,5 MC GW 4	1755280004	B.8
DEK 5/3,5 MC GW 5	1755280005	B.8
DEK 5/3,5 MC GW 6	1755280006	B.8
DEK 5/3,5 MC GW 7	1755280007	B.8
DEK 5/3,5 MC GW 8	1755280008	B.8
DEK 5/3,5 MC GW 9	1755280009	B.8
DEK 5/3,5 MC NEUTRAL	1755270000	B.11
DEK 5/30 MC NEUTRAL	1951920000	B.38
DEK 5/30 MC NEUTRAL	1951920000	B.39
DEK 5/30 MC SDR	1025680000	B.38
DEK 5/30 MC SDR	1025680000	B.39
DEK 5/5 MC BEDRUCKT	1609810000	B.11
DEK 5/5 MC-10 NEUT. BL	1609801693	B.11
DEK 5/5 MC-10 NEUT. GE	1609801687	B.11
DEK 5/5 MC-10 NEUT. GN	1609801688	B.11
DEK 5/5 MC-10 NEUT. GR	1609801691	B.11
DEK 5/5 MC-10 NEUT. RT	1609801686	B.11
DEK 5/5 MC-10 NEUT. WS	1609801044	B.11
DEK 5/5 MC-10 NEUT. WS	1609801044	B.35
DEK 5/5 MC-10 NEUT. WS	1609801044	B.36
DEK 5/5 MC-10 NEUT. WS	1609801044	B.37
DEK 5/5 MC-10 NEUT. WS	1609801044	B.38
DEK 5/5 MC-10 NEUT. WS	1609801044	B.39
DEK 5/5 PLUS MC GE	1907520000	B.11
DEK 5/5 PLUS MC NEUTRAL	1854490000	B.11
DEK 5/5 PLUS MC SONDERDR.	1854500000	B.11
DEK 5/6 MC BEDRUCKT	1609830000	B.11
DEK 5/6 MC NEUTRAL	1609820000	B.11
DEK 5/6 PLUS MC NE WS	1011320000	B.11
DEK 5/6 PLUS MC SDR	1038650000	B.11
DEK 5/6,5 MC BEDRUCKT	1609850000	B.11
DEK 5/6,5 MC NEUTRAL	1609840000	B.11
DEK 5/6.5 PLUS MC NE WS	1046340000	B.11
DEK 5/6.5 PLUS MC SDR	1046360000	B.11
DEK 5/7.5 MC NEUTRAL	1720620000	B.11
DEK 5/7.5 MC SONDERDR.	1770490000	B.11
DEK 5/8 MC Neutral	1856740000	B.11
DEK 5/8 MC Sonderdruck	1856750000	B.11
DEK 5/8 PLUS MC NE WS	1046350000	B.11
DEK 5/8 PLUS MC SDR	1046370000	B.11
DEK 6 BL NEUTRAL	0468591693	B.8
DEK 6 BR NEUTRAL	0468591692	B.8
DEK 6 FS 101-150	0468760101	B.8
DEK 6 FS 1-50	0468760001	B.8
DEK 6 FS 151-200	0468760151	B.8
DEK 6 FS 201-250	0468760201	B.8
DEK 6 FS 251-300	0468760251	B.8
DEK 6 FS 301-350	0468760301	B.8
DEK 6 FS 351-400	0468760351	B.8
DEK 6 FS 401-450	0468760401	B.8
DEK 6 FS 451-500	0468760451	B.8
DEK 6 FS 501-550	0468760501	B.8
DEK 6 FS 51-100	0468760051	B.8
DEK 6 FS 551-600	0468760551	B.8
DEK 6 FS 601-650	0468760601	B.8
DEK 6 FS 651-700	0468760651	B.8
DEK 6 FS 701-750	0468760701	B.8
DEK 6 FS 751-800	0468760751	B.8

Type	Order No.	Page
DEK 6 FS 801-850	0468760801	B.8
DEK 6 FS 851-900	0468760851	B.8
DEK 6 FS 901-950	0468760901	B.8
DEK 6 FS 951-999	0468760951	B.8
DEK 6 FSZ 1-10	0133360001	B.8
DEK 6 FSZ 11-20	0133360011	B.8
DEK 6 FSZ 21-30	0133360021	B.8
DEK 6 FSZ 31-40	0133360031	B.8
DEK 6 FSZ 41-50	0133360041	B.8
DEK 6 FSZ 51-60	0133360051	B.8
DEK 6 FSZ 61-70	0133360061	B.8
DEK 6 FSZ 71-80	0133360071	B.8
DEK 6 FSZ 81-90	0133360081	B.8
DEK 6 FSZ 91-100	0133360091	B.8
DEK 6 FW 1,3,5...99	1358660000	B.8
DEK 6 FW 101-150	0468660101	B.8
DEK 6 FW 1-5 (10X)	0688660000	B.8
DEK 6 FW 1-50	0468660001	B.8
DEK 6 FW 151-200	0468660151	B.8
DEK 6 FW 2,4,...100	1358760000	B.8
DEK 6 FW 201-250	0468660201	B.8
DEK 6 FW 251-300	0468660251	B.8
DEK 6 FW 301-350	0468660301	B.8
DEK 6 FW 351-400	0468660351	B.8
DEK 6 FW 401-450	0468660401	B.8
DEK 6 FW 451-500	0468660451	B.8
DEK 6 FW 501-550	0468660501	B.8
DEK 6 FW 51-100	0468660051	B.8
DEK 6 FW 551-600	0468660551	B.8
DEK 6 FW 601-650	0468660601	B.8
DEK 6 FW 651-700	0468660651	B.8
DEK 6 FW 701-750	0468660701	B.8
DEK 6 FW 751-800	0468660751	B.8
DEK 6 FW 801-850	0468660801	B.8
DEK 6 FW 851-900	0468660851	B.8
DEK 6 FW 901-950	0468660901	B.8
DEK 6 FW 951-999	0468660951	B.8
DEK 6 FW L,N,PE	0632560000	B.8
DEK 6 FWZ 101-110	0518960101	B.8
DEK 6 FWZ 1-10	0518960001	B.8
DEK 6 FWZ 111-120	0518960111	B.8
DEK 6 FWZ 11-20	0518960011	B.8
DEK 6 FWZ 121-130	0518960121	B.8
DEK 6 FWZ 131-140	0518960131	B.8
DEK 6 FWZ 141-150	0518960141	B.8
DEK 6 FWZ 151-160	0518960151	B.8
DEK 6 FWZ 161-170	0518960161	B.8
DEK 6 FWZ 171-180	0518960171	B.8
DEK 6 FWZ 181-190	0518960181	B.8
DEK 6 FWZ 191-200	0518960191	B.8
DEK 6 FWZ 201-210	0518960201	B.8
DEK 6 FWZ 21-30	0518960021	B.8
DEK 6 FWZ 31-40	0518960031	B.8
DEK 6 FWZ 41-50	0518960041	B.8
DEK 6 FWZ 51-60	0518960051	B.8
DEK 6 FWZ 61-70	0518960061	B.8
DEK 6 FWZ 71-80	0518960071	B.8
DEK 6 FWZ 81-90	0518960081	B.8
DEK 6 FWZ 91-100	0518960091	B.8
DEK 6 FWZ L1-ERDE I.KRE	0631961203	B.8
DEK 6 FWZ L1-PE	0631961187	B.8
DEK 6 FWZ R,S,T,N,ERDE	0631860000	B.8
DEK 6 GE NEUTRAL	0468591687	B.8
DEK 6 GN NEUTRAL	0468591688	B.8
DEK 6 GR NEUTRAL	0468591691	B.8
DEK 6 GW -	1318061199	B.8
DEK 6 GW +	1318061198	B.8
DEK 6 GW 0	0526961000	B.8
DEK 6 GW 1	0526960001	B.8
DEK 6 GW 10	0526960010	B.8
DEK 6 GW 100	0526960100	B.8
DEK 6 GW 11	0526960011	B.8
DEK 6 GW 12	0526960012	B.8
DEK 6 GW 13	0526960013	B.8
DEK 6 GW 14	0526960014	B.8
DEK 6 GW 15	0526960015	B.8
DEK 6 GW 16	0526960016	B.8
DEK 6 GW 17	0526960017	B.8
DEK 6 GW 18	0526960018	B.8
DEK 6 GW 19	0526960019	B.8
DEK 6 GW 2	0526960002	B.8
DEK 6 GW 20	0526960020	B.8
DEK 6 GW 21	0526960021	B.8
DEK 6 GW 22	0526960022	B.8
DEK 6 GW 23	0526960023	B.8
DEK 6 GW 24	0526960024	B.8
DEK 6 GW 25	0526960025	B.8
DEK 6 GW 26	0526960026	B.8
DEK 6 GW 27	0526960027	B.8
DEK 6 GW 28	0526960028	B.8
DEK 6 GW 29	0526960029	B.8
DEK 6 GW 3	0526960003	B.8
DEK 6 GW 30	0526960030	B.8
DEK 6 GW 31	0526960031	B.8
DEK 6 GW 32	0526960032	B.8
DEK 6 GW 33	0526960033	B.8
DEK 6 GW 34	0526960034	B.8
DEK 6 GW 35	0526960035	B.8
DEK 6 GW 36	0526960036	B.8
DEK 6 GW 37	0526960037	B.8

Type	Order No.	Page
DEK 6 GW 38	0526960038	B.8
DEK 6 GW 39	0526960039	B.8
DEK 6 GW 4	0526960004	B.8
DEK 6 GW 40	0526960040	B.8
DEK 6 GW 41	0526960041	B.8
DEK 6 GW 42	0526960042	B.8
DEK 6 GW 43	0526960043	B.8
DEK 6 GW 44	0526960044	B.8
DEK 6 GW 45	0526960045	B.8
DEK 6 GW 46	0526960046	B.8
DEK 6 GW 47	0526960047	B.8
DEK 6 GW 48	0526960048	B.8
DEK 6 GW 49	0526960049	B.8
DEK 6 GW 5	0526960005	B.8
DEK 6 GW 50	0526960050	B.8
DEK 6 GW 51	0526960051	B.8
DEK 6 GW 52	0526960052	B.8
DEK 6 GW 53	0526960053	B.8
DEK 6 GW 54	0526960054	B.8
DEK 6 GW 55	0526960055	B.8
DEK 6 GW 56	0526960056	B.8
DEK 6 GW 57	0526960057	B.8
DEK 6 GW 58	0526960058	B.8
DEK 6 GW 59	0526960059	B.8
DEK 6 GW 6	0526960006	B.8
DEK 6 GW 60	0526960060	B.8
DEK 6 GW 61	0526960061	B.8
DEK 6 GW 62	0526960062	B.8
DEK 6 GW 63	0526960063	B.8
DEK 6 GW 64	0526960064	B.8
DEK 6 GW 65	0526960065	B.8
DEK 6 GW 66	0526960066	B.8
DEK 6 GW 67	0526960067	B.8
DEK 6 GW 68	0526960068	B.8
DEK 6 GW 69	0526960069	B.8
DEK 6 GW 7	0526960007	B.8
DEK 6 GW 70	0526960070	B.8
DEK 6 GW 71	0526960071	B.8
DEK 6 GW 72	0526960072	B.8
DEK 6 GW 73	0526960073	B.8
DEK 6 GW 74	0526960074	B.8
DEK 6 GW 75	0526960075	B.8
DEK 6 GW 76	0526960076	B.8
DEK 6 GW 77	0526960077	B.8
DEK 6 GW 78	0526960078	B.8
DEK 6 GW 79	0526960079	B.8
DEK 6 GW 8	0526960008	B.8
DEK 6 GW 80	0526960080	B.8
DEK 6 GW 81	0526960081	B.8
DEK 6 GW 82	0526960082	B.8
DEK 6 GW 83	0526960083	B.8
DEK 6 GW 84	0526960084	B.8
DEK 6 GW 85	0526960085	B.8
DEK 6 GW 86	0526960086	B.8
DEK 6 GW 87	0526960087	B.8
DEK 6 GW 88	0526960088	B.8
DEK 6 GW 89	0526960089	B.8
DEK 6 GW 9	0526960009	B.8
DEK 6 GW 90	0526960090	B.8
DEK 6 GW 91	0526960091	B.8
DEK 6 GW 92	0526960092	B.8
DEK 6 GW 93	0526960093	B.8
DEK 6 GW 94	0526960094	B.8
DEK 6 GW 95	0526960095	B.8
DEK 6 GW 96	0526960096	B.8
DEK 6 GW 97	0526960097	B.8
DEK 6 GW 98	0526960098	B.8
DEK 6 GW 99	0526960099	B.8
DEK 6 GW BL/SW -	1318091741	B.8
DEK 6 GW ERDE	1318061202	B.8
DEK 6 GW ERDE I.KR.	1318061203	B.8
DEK 6 GW PE	1318061187	B.8
DEK 6 GW RT/SW +	1318091737	B.8
DEK 6 NEUTRAL	0468560000	B.8
DEK 6 OR NEUTRAL	0468591690	B.8
DEK 6 RT NEUTRAL	0468591686	B.8
DEK 6 SW NEUTRAL	0468591694	B.8
DEK 6 VI NEUTRAL	0468591689	B.8
DEK 6,5 BL NEUTRAL	0468091693	B.8
DEK 6,5 FS 101-150	0468260101	B.8
DEK 6,5 FS 1-50	0468260001	B.8
DEK 6,5 FS 51-100	0468260051	B.8
DEK 6,5 FSZ 1-10	0407360001	B.8
DEK 6,5 FSZ 11-20	0407360011	B.8
DEK 6,5 FSZ 21-30	0407360021	B.8
DEK 6,5 FSZ 31-40	0407360031	B.8
DEK 6,5 FSZ 41-50	0407360041	B.8
DEK 6,5 FSZ 51-60	0407360051	B.8
DEK 6,5 FSZ 61-70	0407360061	B.8
DEK 6,5 FSZ 71-80	0407360071	B.8
DEK 6,5 FSZ 81-90	0407360081	B.8
DEK 6,5 FSZ 91-100	0407360091	B.8
DEK 6,5 FW 101-150	0468160101	B.8
DEK 6,5 FW 1-50	0468160001	B.8
DEK 6,5 FW 151-200	0468160151	B.8
DEK 6,5 FW 201-250	0468160201	B.8
DEK 6,5 FW 251-300	0468160251	B.8
DEK 6,5 FW 301-350	0468160301	B.8
DEK 6,5 FW 351-400	0468160351	B.8
DEK 6,5 FW 401-450	0468160401	B.8

Type	Order No.	Page
DEK 6,5 FW 451-500	0468160451	B.8
DEK 6,5 FW 501-550	0468160501	B.8
DEK 6,5 FW 51-100	0468160051	B.8
DEK 6,5 FW L1-ERDE I.KR	0632161203	B.8
DEK 6,5 FW L1-PE	0632161187	B.8
DEK 6,5 FWZ 1-10	0519060001	B.8
DEK 6,5 FWZ 11-20	0519060011	B.8
DEK 6,5 FWZ 21-30	0519060021	B.8
DEK 6,5 FWZ 31-40	0519060031	B.8
DEK 6,5 FWZ 41-50	0519060041	B.8
DEK 6,5 FWZ 51-60	0519060051	B.8
DEK 6,5 FWZ 61-70	0519060061	B.8
DEK 6,5 FWZ 71-80	0519060071	B.8
DEK 6,5 FWZ 81-90	0519060081	B.8
DEK 6,5 FWZ 91-100	0519060091	B.8
DEK 6,5 FWZ R,S,T,N,ERD	0632060000	B.8
DEK 6,5 GE NEUTRAL	0468091687	B.8
DEK 6,5 GN NEUTRAL	0468091688	B.8
DEK 6,5 NEUTRAL	0468060000	B.8
DEK 6,5 OR NEUTRAL	0468091690	B.8
DEK 6,5 RT NEUTRAL	0468091686	B.8
DEK 6,5 SW NEUTRAL	0468091694	B.8
DEK 6,5 VI NEUTRAL	0468091689	B.8
DEK 8 BEDR./FARBIG	1289690000	B.8
DEK 8 FS 1-50 TAMPOPR.	1653350001	B.8
DEK 8 FS 51-100 TAMPOP.	1653350051	B.8
DEK 8 FSZ 1-10	1289660001	B.8
DEK 8 FSZ 11-20	1289660011	B.8
DEK 8 FSZ 21-30	1289660021	B.8
DEK 8 FSZ 31-40	1289660031	B.8
DEK 8 FSZ 41-50	1289660041	B.8
DEK 8 FSZ 51-60	1289660051	B.8
DEK 8 FSZ 61-70	1289660061	B.8
DEK 8 FSZ 71-80	1289660071	B.8
DEK 8 FSZ 81-90	1289660081	B.8
DEK 8 FSZ 91-100	1289660091	B.8
DEK 8 FW 1-50 TAMPOPR.	1653340001	B.8
DEK 8 FW 51-100 TAMPOP.	1653340051	B.8
DEK 8 FWZ 101-110	1276960101	B.8
DEK 8 FWZ 1-10	1276960001	B.8
DEK 8 FWZ 111-120	1276960111	B.8
DEK 8 FWZ 11-20	1276960011	B.8
DEK 8 FWZ 121-130	1276960121	B.8
DEK 8 FWZ 131-140	1276960131	B.8
DEK 8 FWZ 141-150	1276960141	B.8
DEK 8 FWZ 21-30	1276960021	B.8
DEK 8 FWZ 31-40	1276960031	B.8
DEK 8 FWZ 41-50	1276960041	B.8
DEK 8 FWZ 51-60	1276960051	B.8
DEK 8 FWZ 61-70	1276960061	B.8
DEK 8 FWZ 71-80	1276960071	B.8
DEK 8 FWZ 81-90	1276960081	B.8
DEK 8 FWZ 91-100	1276960091	B.8
DEK 8 GE NEUTRAL	1277091687	B.8
DEK 8 GN NEUTRAL	1277091688	B.8
DEK 8 NEUTRAL	1277060000	B.8
DEK 8 OR NEUTRAL	1277091690	B.8
DEK 8 RT NEUTRAL	1277091686	B.8
DEK 8 SONDERDR.WEISS	1326660000	B.8
DEK 8 VI NEUTRAL	1277091689	B.8
DMC 12/27 MC NE GE	1018190000	D.3
DMC 12/27 MC NE WS	1016030000	D.3
DMC 12/27 MC SDR	1038830000	D.3

E

ELS 16/40 MC GE	1045630000	B.36
ELS 16/40 MC GE	1045630000	B.37
ELS 16/40 MC GE	1045630000	C.13
ELS 16/40 MC SDR	1045690000	B.37
ELS 16/40 MC SDR	1045690000	C.13
ELS 16/40 MC WS	1045620000	B.36
ELS 16/40 MC WS	1045620000	B.37
ELS 16/40 MC WS	1045620000	C.13
ELS 6/30 MC GE	1045580000	B.37
ELS 6/30 MC GE	1045580000	C.13
ELS 6/30 MC SDR	1045660000	B.37
ELS 6/30 MC SDR	1045660000	C.13
ELS 6/30 MC WS	1045570000	B.37
ELS 6/30 MC WS	1045570000	C.13
ELS 7/40 MC GE	1045650000	B.36
ELS 7/40 MC GE	1045650000	B.37
ELS 7/40 MC SDR	1045700000	B.37
ELS 7/40 MC WS	1045640000	B.36
ELS 7/40 MC WS	1045640000	B.37
EM 8/30	1806120000	B.38
ESG 10/17 MC Neutral	1856700000	D.4
ESG 10/17 Sonderdruck	1856710000	D.4
ESG 5/10 MC NEUTRAL WS	1919940000	D.4
ESG 5/10 MC SDR	1038840000	D.4
ESG 6/15 F MC NE WS	1136810000	D.4
ESG 6/15 K MC NEUTR. GE	1880130000	D.4
ESG 6/15 K MC NEUTR. WS	1880100000	D.4
ESG 6/15 K SONDERDRUCK	1880090000	D.4
ESG 6/15 MC RIDERSERIES	1881280000	D.4
ESG 6/15 RIDERS SONDERD	1881290000	D.4
ESG 6/17 K MC NEUTR. GE	1880110000	D.4
ESG 6/17 K MC NEUTR. WS	1880120000	D.4
ESG 6/17 K SONDERDRUCK	1880080000	D.4
ESG 7/20 SIRIUS GE	1736181687	D.4
ESG 7/20 SIRIUS TUERKIS	1736181696	C.13
ESG 7/20 SIRIUS TUERKIS	1736181696	D.4
ESG 7/20 SIRIUS WS	1736181044	C.13
ESG 7/20 SIRIUS WS	1736181044	D.4
ESG 8/10 ASI	1736190000	D.4
ESG 8/11	1897570000	D.4
ESG 8/11 MC SDR	1038850000	D.4
ESG 8/13.5/43.3 SAI AU	1912130000	D.4
ESG 8/13.5/43.3 SAI SDR	1038860000	D.4
ESG 8/17 L MC NEUTRAL	1890470000	D.4
ESG 8/17 L MC SDR	1038870000	D.4
ESG 8/17 MC BEDRUCKT	1674750000	D.4
ESG 8/17 MC NEUTRAL	1674740000	D.4
ESG 8/17 SCHS MC BEDR.	1766640000	D.4
ESG 8/17 SCHS MC NEUTR.	1720610000	D.4
ESG 8/17 SYS PRO M	1755340000	D.4
ESG 8/17 SYS PRO M BED.	1755350000	D.4
ESG 8/19 MC BEDRUCKT	1652230000	D.4
ESG 8/19 MC NEUTRAL	1652220000	D.4
ESG 9/11 K SONDERDRUCK	1857450000	D.4
ESG 9/11K MC NEUTRAL	1857440000	D.4
ESG 9/17 K NEUTRAL/GE	1753500000	D.4
ESG 9/17 K NEUTRAL/WS	1674760000	D.4
ESG 9/17 K SONDERDRUCK	1674770000	D.4
ESG 9/17 MC BEDRUCKT	1770480000	D.4
ESG 9/17 MC NEUTRAL	1724760000	C.11
ESG 9/17 MC NEUTRAL	1724760000	D.4
ESG 9/20 L MC NE GE	1010860000	D.4
ESG 9/20 L MC NEUTRAL	1890460000	D.4
ESG 9/20 MC BEDRUCKT	1609950000	D.4
ESG 9/20 MC NEUTRAL GE	1766160000	D.4
ESG 9/20 MC NEUTRAL O. FUSS	1770500000	D.4
ESG 9/20 MC NEUTRAL WS	1609940000	D.4
ESG 9/20 MC O.F. SONDER	1770510000	D.4
ESG 9/20 MC TUERKIS	1866690000	D.4
ESG 9/20 MC Universal	1856720000	D.4
ESG 9/20 Univ. Sonderdr	1856730000	D.4
ESG 9/6 MC NEUTRAL	1888360000	D.4
ESG B&R X20 MC NE BL	1001150001	D.4
ESG B&R X20 MC NE OR	1001160001	D.4
ESG B&R X20 MC NE RT	1001170001	D.4
ESG B&R X20 MC NE WS	1001140001	D.4
ESG B&R X20 MC SDR	1038890000	D.4
ESG X20 10/7 MC NE BL	1026560000	D.4
ESG X20 10/7 MC NE OR	1026580000	D.4
ESG X20 10/7 MC NE RT	1026570000	D.4
ESG X20 10/7 MC NE WS	1026550000	D.4
ESG X20 10/7 MC SDR	1038930000	D.4
ESG-M 8/20 MC NE WS	1027290000	D.4
ESG-M 8/20 MC SDR	1038910000	D.4
ESG-M 9/17 MC NE WS	1027280000	D.4
ESG-M 9/17 MC SDR	1038920000	D.4
ESO 15 BOGEN DIN A4	1636510000	B.39
ESO 5 DIN A4 GELB BOG.	1631350000	B.36
ESO 5 DIN A4 GELB BOG.	1631350000	C.13
ESO 5 DIN A4 WEISS BOG.	1607710000	B.36
ESO 5 DIN A4 WEISS BOG.	1607710000	C.13
ESO 5 POLY.GELB A4-BOG.	1670380000	B.36
ESO 5 POLY.GELB A4-BOG.	1670380000	C.13
ESO 5 POLY.WEISS A4-BOG.	1670370000	B.36
ESO 5 POLY.WEISS A4-BOG.	1670370000	C.13
ESO 5 S DIN A4-BOGEN	1631920000	B.36
ESO 7 A4-BOGEN GELB	1634780000	B.36
ESO 7 A4-BOGEN GELB	1634780000	B.38
ESO 7 A4-BOGEN GELB	1634780000	B.39
ESO 7 A4-BOGEN GELB	1634780000	C.13
ESO 7 A4-BOGEN WEISS	1607720000	B.36
ESO 7 A4-BOGEN WEISS	1607720000	B.38
ESO 7 A4-BOGEN WEISS	1607720000	B.39
ESO 7 A4-BOGEN WEISS	1607720000	C.13
ESO 7 POLY.GELB A4-BOG.	1670400000	B.36
ESO 7 POLY.GELB A4-BOG.	1670400000	B.38
ESO 7 POLY.GELB A4-BOG.	1670400000	B.39
ESO 7 POLY.GELB A4-BOG.	1670400000	C.13
ESO 7 POLY.WEISS A4-BOG.	1670390000	B.36
ESO 7 POLY.WEISS A4-BOG.	1670390000	B.38
ESO 7 POLY.WEISS A4-BOG.	1670390000	B.39
ESO 7 POLY.WEISS A4-BOG.	1670390000	C.13
ESO 8/20 GE	1919900000	C.13
ESO 8/20 WS	1919890000	C.13
ESO 8/20P GE	1919880000	C.13
ESO 8/20P WS	1919870000	C.13
ESO/SCHS1 500X12,5X0,3	0139000000	D.5
ET S7 / 12/50 ge A4	1804480000	D.13
ET S7-12/50-TU-A4	1865440000	D.13
ET S7-300-GE-A4-1	1821020000	D.13
ET S7-300-GE-A4-2	1847650000	D.13
ET S7-300-TU-A4-1	1865450000	D.13
ET S7-300-TU-A4-2	1865460000	D.13
ET S7-400-GE-A4-1	1821040000	D.13
ET S7-400-GE-A4-2	1821030000	D.13
ET S7-400-GE-A4-3	1847640000	D.13
ET S7-400-TU-A4-1	1865470000	D.13
ET S7-400-TU-A4-2	1865480000	D.13
ET S7-400-TU-A4-3	1865490000	D.13
ETO CC 15/17 TRANSPAR.	1880850000	D.9
ETO CC 15/27 TRANSPAR.	1880810000	D.9
ETO CC 15/49 TRANSPAR.	1880830000	D.9
ETO CC 15/60 TRANSPAR.	1880840000	D.9
ETO CC 30/60 TRANSPAR.	1934440000	D.9
ETO SM 22/22 TRANSPAR.	1880720000	D.7
ETO SM 27/12,5	1720580000	D.7
ETO SM 27/18 TRANSPAR.	1720590002	D.7
ETO SM 27/8	1720570000	D.7
ETO SM 27x27	1805840000	D.7

H

HSS1 11,4-24,1/50Y	1962130000	C.16
HSS1"11,4-24,1/25W	1962180000	C.16
HSS1"11,4-24,1/25Y	1962230000	C.16
HSS1"11,4-24,1/50W	1962080000	C.16
HSS1/2"4,8-11,4/25W	1962170000	C.16
HSS1/2"4,8-11,4/25Y	1962220000	C.16
HSS1/2"4,8-11,4/50W	1962070000	C.16
HSS1/2"4,8-11,4/50Y	1962120000	C.16
HSS1/4"2,4-5,5/25W	1962150000	C.16
HSS1/4"2,4-5,5/25Y	1962200000	C.16
HSS1/4"2,4-5,5/50W	1962050000	C.16
HSS1/4"2,4-5,5/50Y	1962100000	C.16
HSS1/8 1,2-2,8/25W	1962140000	C.16
HSS1/8"1,2-2,8/25Y	1962190000	C.16
HSS1/8"1,2-2,8/50W	1962040000	C.16
HSS1/8"1,2-2,8/50Y	1962090000	C.16
HSS3/16"1,6-3,8/25W	1029860000	C.16
HSS3/16"1,6-3,8/25Y	1029870000	C.16
HSS3/16"1,6-3,8/50W	1029840000	C.16
HSS3/16"1,6-3,8/50Y	1029850000	C.16
HSS3/8"3,2-8,1/25W	1962160000	C.16
HSS3/8"3,2-8,1/25Y	1962210000	C.16
HSS3/8"3,2-8,1/50W	1962060000	C.16
HSS3/8"3,2-8,1/50Y	1962110000	C.16
HSS-HF1"17,0-23,0/25Y	1962030000	C.15
HSS-HF1"17,0-23,0/50Y	1961960000	C.15
HSS-HF1/2"8,0-11,0/25Y	1962010000	C.15
HSS-HF1/2"8,0-11,0/50Y	1961940000	C.15
HSS-HF1/4"4,2-5,8/25Y	1961990000	C.15
HSS-HF1/4"4,2-5,8/50Y	1961920000	C.15
HSS-HF1/8"1,8-2,8/25Y	1961970000	C.15
HSS-HF1/8"1,8-2,8/50Y	1961900000	C.15
HSS-HF3/16"2,8-4,2/25Y	1961980000	C.15
HSS-HF3/16"2,8-4,2/50Y	1961910000	C.15
HSS-HF3/4"11,0-17,0/25Y	1962020000	C.15
HSS-HF3/4"11,0-17,0/50Y	1961950000	C.15
HSS-HF3/8"5,8-8,0/25Y	1962000000	C.15
HSS-HF3/8"5,8-8,0/50Y	1961930000	C.15

K

KABELBINDERZANGE RT-1	1296000000	C.60
KSW 2,5 <100MM NEUTRAL	1629980000	D.18
KSW 2,5 <100MM SONDDR.	1629920000	D.18
KSW 2,5 <150MM NEUTRAL	1630000000	D.18
KSW 2,5 <150MM SONDDR.	1629940000	D.18
KSW 2,5 <50MM NEUTRAL	1629960000	D.18
KSW 2,5 10/5,08 1-10	1630020001	D.17
KSW 2,5 10/5,08 11-20	1630020011	D.17
KSW 2,5 10/5,08 W 9-18	1895950000	D.17
KSW 2,5 10/7,5 101-200	1630030101	D.17
KSW 2,5 10/7,5 1-10 FWZ	1630040001	D.17
KSW 2,5 10/7,5 201-300	1630030201	D.17
KSW 2,5 10/7,5 301-400	1630030301	D.17
KSW 2,5 10/7,5 401-500	1630030401	D.17
KSW 2,5 10/9 W 1-10	1676710001	D.17
KSW 2,5 10/9 W 11-20	1676710011	D.17
KSW 2,5 10/9 W 21-30	1676710021	D.17
KSW 2,5 14/3,5 1,3,5...27	1849580000	D.17
KSW 2,5 14/3,5 2,4,6...28	1849590000	D.17
KSW 2,5 15/5,08 1-150	1630050001	D.17
KSW 2,5 15/5,08 1-15FWZ	1630060001	D.17
KSW 2,5 15/5,08 151-300	1630050151	D.17
KSW 2,5 15/5,08 301-450	1630050301	D.17
KSW 2,5 16/3,5 1-16	1652260001	D.17
KSW 2,5 16/3,81 W 1-16	1873610000	D.17
KSW 2,5 16/5 1-16	1630070001	D.17
KSW 2,5 16/5,08 W 1-16	1713970001	D.17
KSW 2,5 16/5,08 W 17-32	1713970017	D.17
KSW 2,5 16/5,08 W 33-48	1713970033	D.17
KSW 2,5 20/5 1-20	1630080001	D.17
KSW 2,5 20/5 21-40	1630080021	D.17
KSW 2,5 20/5 41-60	1630080041	D.17
KSW 2,5 20/5 61-80	1630080061	D.17
KSW 2,5 24/3,5 1-24	1652250001	D.17
KSW 2,5 24/3,5 25-48	1652250025	D.17
KSW 2,5 24/3,81 W 1-24	1873600000	D.17
KSW 2,5 24/5,00 W 1-24	1713980001	D.17
KSW 2,5 24/5,08 W 1-24	1713990001	D.17
KSW 2,5 4/10,16 1-4	1630090001	D.19
KSW 2,5 8/3,5 W 1-8	1873620000	D.17
KSW 2,5 8/3,81 W 1-8	1873630000	D.17
KSW 2,5 8/5,00 W 1-8	1700660001	D.17
KSW 2,5 8/5,08 1-8	1630100001	D.17
KSW 2,5 8/5,08 9-16	1630100009	D.17
KSW 2,5 8/5,08 A-H	1630101021	D.17
KSW 2,5 8/5,08 W 19-26	1895960000	D.17
KSW 2,5 8/7,5 W 1-8	1873650000	D.17
KSW 2,5 8/7,62 W 1-8	1873640000	D.17
KSW 2.5 < 50MM SDR	1629900000	D.18
KSW 4 < 100MM SDR	1629930000	D.19
KSW 4 < 50MM SDR	1629910000	D.19
KSW 4 <100MM NEUTRAL	1629990000	D.19
KSW 4 <150MM NEUTRAL	1630010000	D.19
KSW 4 <150MM SONDDR.	1629950000	D.19
KSW 4 <50MM NEUTRAL	1629970000	D.19
KSW 4 10/5,08 W 1-10	1705820001	D.18
KSW 4 10/5,08 W 11-20	1705820011	D.18
KSW 4 10/5,08 W 21-30	1705820021	D.18
KSW 4 10/5,08 W 31-40	1705820031	D.18
KSW 4 10/5,08 W 41-50	1705820041	D.18
KSW 4 10/5,08 W 51-60	1705820051	D.18
KSW 4 10/5,08 W 61-70	1705820061	D.18
KSW 4 10/5,08 W 71-80	1705820071	D.18
KSW 4 10/5,08 W 81-90	1705820081	D.18
KSW 4 10/5,08 W 91-100	1705820091	D.18
KSW 4 10/7,00 W 1-10	1714070001	D.18
KSW 4 10/9,00 W 1-10	1714080001	D.19
KSW 4 12/5 1-12	1630130001	D.18
KSW 4 12/5 W 13-24	1630130013	D.18
KSW 4 12/7,5 1-12	1630140001	D.19
KSW 4 12/7,5 13-24	1630140013	D.19
KSW 4 12/7,5 25-36	1630140025	D.19
KSW 4 12/7,5 37-48	1630140037	D.19
KSW 4 12/7,5 49-60	1630140049	D.19
KSW 4 12/7,62 1-12	1652270001	D.19
KSW 4 12/7,62 13-24	1652270013	D.19
KSW 4 16/3,5 1-16	1630150001	D.18
KSW 4 16/3,5 17-32	1630150017	D.18
KSW 4 16/5,00 W 1-16	1700700001	D.18
KSW 4 16/5,08 1-16	1630160001	D.18
KSW 4 16/5,08 17-32	1630160017	D.18
KSW 4 16/5,08 33-48	1630160033	D.18
KSW 4 16/5,08 49-64	1630160049	D.18
KSW 4 16/5,08 65-80	1630160065	D.18
KSW 4 16/5,08 81-96	1630160081	D.18
KSW 4 18/5 1-18	1630170001	D.18
KSW 4 18/5,08 W 1-36	1720530001	D.18
KSW 4 24/3,5 W 1-24	1640410001	D.18
KSW 4 24/5,00 W 1-24	1700710001	D.18
KSW 4 24/5,08 1-24	1630180001	D.18
KSW 4 5/7 W 1-5	1670780001	D.18
KSW 4 8/3,5 1-8	1630190001	D.18
KSW 4 8/5,00 W 1-8	1700670001	D.18
KSW 4 8/5,08 17-24	1630200017	D.18
KSW 4 8/5,08 1-8	1630200001	D.18
KSW 4 8/5,08 25-32	1630200025	D.18
KSW 4 8/5,08 33-40	1630200033	D.18
KSW 4 8/5,08 41-48	1630200041	D.18
KSW 4 8/5,08 9-16	1630200009	D.18
KSW 4 8/7,5 W 1-8	1700690001	D.19
KSW 4 8/7,62 W 1-8	1700680001	D.19
KSW 4 9/7,00 W 1-9	1714060001	D.18

L

LM MT300 105X105 SI	1975160000	D.11
LM MT300 105X148 GE	1724171687	D.11
LM MT300 105X148 SI	1724170001	D.11
LM MT300 105X148 WS	1724171044	D.11
LM MT300 12X6 GE	1882910000	D.11
LM MT300 15X4,63 GE	1724141687	D.11
LM MT300 15X4,63 SI	1724140001	D.11
LM MT300 15X4,63 WS	1724141044	D.11
LM MT300 15X6 GE	1686361687	D.11
LM MT300 15X6 SI I	1686360001	D.11
LM MT300 15X6 WS	1686361044	D.11
LM MT300 15X9 GE	1882890000	D.11
LM MT300 17x6 GE	1835820000	D.11
LM MT300 17X9 GE	1724151687	D.11
LM MT300 17X9 SI	1724150001	D.11
LM MT300 17X9 WS	1724151044	D.11
LM MT300 18X6,5 GE	1749321687	D.11
LM MT300 18X6,5 SI	1749320001	D.11
LM MT300 18X6,5 WS	1749321044	D.11
LM MT300 19.05x6.3 GE	1835830000	D.11
LM MT300 202x12 GE	1915320000	D.11
LM MT300 20X8 GE	1686381687	D.11
LM MT300 20X8 SI	1686380001	D.11
LM MT300 20X8 WS	1686381044	D.11
LM MT300 210X148 GE	1724181687	D.11
LM MT300 210X148 SI	1724180001	D.11
LM MT300 210X148 WS	1724181044	D.11
LM MT300 210X297 GE	1686441687	D.11
LM MT300 210X297 SI	1686440001	D.11
LM MT300 210X297 WS	1686441044	D.11
LM MT300 25,4X12,7 GE	1686391687	D.11
LM MT300 25,4X12,7 SI	1686390001	D.11
LM MT300 25,4X12,7 WS	1686391044	D.11
LM MT300 26,5/17,5 SI	1784340000	D.11
LM MT300 26X10 GE	1686401687	D.11
LM MT300 26X10 SI	1686400001	D.11
LM MT300 26X10 WS	1686401044	D.11
LM MT300 27/8 GE	1861510000	D.11
LM MT300 27x18 SI	1873810000	D.11
LM MT300 30X20 GE	1724161687	D.11
LM MT300 30X20 SI	1724160001	D.11
LM MT300 30X20 WS	1724161044	D.11
LM MT300 40X6 WS	1760461044	D.11
LM MT300 56X22 GE	1686421687	D.11
LM MT300 56X22 SI	1686420001	D.11
LM MT300 56X22 WS	1686421044	D.11

Type	Order No.	Page
LM MT300 60X36 GE	1686431687	D.11
LM MT300 60X36 SI	1686430001	D.11
LM MT300 60X36 WS	1686431044	D.11
LM MT300 89X34 WS	1003400000	D.11
LM MT300 PA 20x8 GE	1874860000	D.11
LM WRITE ON 15X70 WS	1759871044	C.17
LM WRITE ON 18X34 GE	1695711687	C.17
LM WRITE ON 18X34 WS	1695711044	C.17
LM WRITE ON 23X55 GE	1695721687	C.17
LM WRITE ON 23X55 WS	1695721044	C.17
LM WRITE ON 25X140 GE	1712491687	C.17
LM WRITE ON 25X140 WS	1712491044	C.17
LM WRITE ON 25X68 GE	1695731687	C.17
LM WRITE ON 25X68 WS	1695731044	C.17
LM WRITE ON 36X93 GE	1695741687	C.17
LM WRITE ON 36X93 WS	1695741044	C.17
LM WriteOn 15x140 WS	1773880000	C.17
LM WriteOn 25,4x57 GE	1768390000	C.17
LM WriteOn 25,4x57 WS	1768380000	C.17
LM WriteOn 25,4x95 GE	1768410000	C.17
LM WriteOn 25,4x95 WS	1768400000	C.17
LM WriteOn 37x25 GE	1768430000	C.17
LOGIM.KARTE 1/2 BEDR.	1675120000	D.10
LOGIM.KARTE 1/2 BL NEUT	1675111693	D.10
LOGIM.KARTE 1/2 BR NEUT	1675111692	D.10
LOGIM.KARTE 1/2 GE NEUT	1675111687	D.10
LOGIM.KARTE 1/2 GN NEUT	1675111688	D.10
LOGIM.KARTE 1/2 GR NEUT	1675111691	D.10
LOGIM.KARTE 1/2 OR NEUT	1675111690	D.10
LOGIM.KARTE 1/2 RT NEUT	1675111686	D.10
LOGIM.KARTE 1/2 VI NEUT	1675111689	D.10
LOGIM.KARTE 1/2 WS NEUT	1675111044	D.10
LOGIMARK DKB 81/23	1755100000	D.10
LOGIMARK DKB 81/50	1755110000	D.10
LOGIMARKHALTER 1/2 GRAU	1675130002	D.10
LOGIMARKHALTER 1/2 SW	1675130001	D.10
LOGIMARK-K.HALTER ES	1631640003	D.10
LOGIMARK-K.HALTER ES	1631640002	D.10
LOGIMARK-K.HALTER ES	1631640001	D.10
LOGIMARK-KARTE BEDRUCKT	1607690000	D.10
LOGIMARK-KARTE NEUTR.BL	1607681693	D.10
LOGIMARK-KARTE NEUTR.BR	1607681692	D.10
LOGIMARK-KARTE NEUTR.GE	1607681687	D.10
LOGIMARK-KARTE NEUTR.GN	1607681688	D.10
LOGIMARK-KARTE NEUTR.GR	1607681691	D.10
LOGIMARK-KARTE NEUTR.OR	1607681690	D.10
LOGIMARK-KARTE NEUTR.RT	1607681686	D.10
LOGIMARK-KARTE NEUTR.VI	1607681689	D.10
LOGIMARK-KARTE NEUTR.WS	1607681044	D.10
LOGIMARK-KARTENHALTER	1603290000	D.10

M

MARKO-C. 25X25X25 B/DR.	1700530001	D.14
MARKO-C. 50X50X50 B/DR.	1700540001	D.14
MARKO-C.100X100X100 B/DR	1700550001	D.14
MARKO-C.200X200X200 B/DR	1700560001	D.14
MC-Mobilo 110V/220V	1741260001	E.7
MC-MOBILO AUFN. SF 4-6	1802180000	C.6
MC-MOBILO AUFN. SF 4-6	1802180000	E.7
MCP AP	1924360000	E.6
MCP AP BASIC	1139880000	E.6
MCP AP LABLES	1924370000	E.6
MCP AP SF4-6	1924310000	C.6
MCP AP SF4-6	1924310000	E.6
MCP BASIC	1139400000	E.5
MCP COVER	1924350000	E.6
MCP EP	1935130000	E.6
MCP EP SFC 3	1058090000	C.6
MCP EP SFC 3	1058090000	E.6
MCP EP SFC 3	1058090000	E.7
MCP KLEBESTREIFEN	1924320000	E.6
MCP PLUS	1925000000	E.4
MCP TP-KOF BASIC	1139890000	E.6
MF 10/10 MC NEUTRAL	1856760000	B.19
MF 10/10 MC SONDERDRUCK	1856770000	B.19
MF 10/5 MC CABUR	1854510000	B.18
MF 10/5 MC CABUR SDR	1038660000	B.18
MF 10/5 MC NEUTRAL	1677160000	B.18
MF 10/5 MC SONDERDRUCK	1677170000	B.18
MF 10/6 MC NEUTRAL	1677220000	B.19
MF 10/6 MC SONDERDRUCK	1677230000	B.19
MF 10/8 MC NEUTRAL	1868440000	B.19
MF 10/8 MC SONDERDRUCK	1868430000	B.19
MF 12/5 MC CABUR	1854520000	B.18
MF 12/5 MC CABUR SDR	1038670000	B.18
MF 12/5 MC NEUTRAL	1677180000	B.18
MF 12/5 MC SONDERDRUCK	1677190000	B.18
MF 4/5.2 MC NEUTRAL	1907530000	B.18
MF 4/5.2 MC SDR	1038690000	B.18
MF 5/10 MC NEUTRAL	1954050000	B.19
MF 5/10 MC SDR	1038730000	B.19
MF 5/4 MC NEUTRAL	1877690000	B.18
MF 5/4 MC SONDERDRUCK	1877670000	B.18
MF 5/5 MC NEUTRAL	1816250000	B.18
MF 5/5 MC SONDERDRUCK	1816320000	B.18
MF 5/6 MC NEUTRAL	1816260000	B.19
MF 5/6 MC SONDERDRUCK	1816330000	B.19
MF 5/7,5 MC NEUTRAL	1877680000	B.19
MF 5/7,5 MC SONDERDRUCK	1877660000	B.19
MF 8/5 MC NEUTRAL	1677140000	B.18
MF 8/5 MC SONDERDRUCK	1677150000	B.18
MFF 10/6 MC NEUTRAL	1856780000	B.19
MFF 10/6 MC SONDERDRUCK	1856790000	B.19
MFF 9/4 MC NEUTRAL	1877720000	B.18
MFF 9/4 MC SONDERDRUCK	1877700000	B.18
MF-SI 10/5 MC NEUTRAL	1889190000	B.18
MF-SI 10/5 MC SONDERDRUCK	1889170000	B.18
MF-SI 10/5-6,5 MC NEUTRAL	1889800000	B.19
MF-SI 10/5-6,5 MC SONDERDR.	1889790000	B.19
MF-SI 10/6 MC NEUTRAL	1889260000	B.19
MF-SI 10/6 MC SONDERDRUCK	1889250000	B.19
MF-SI 7/5-6,5 MC NEUTRAL	1889780000	B.19
MF-SI 7/5-6,5 MC SONDERDR.	1889770000	B.19
MF-SI 8/5 MC NEUTRAL	1889180000	B.18
MF-SI 8/5 MC SONDERDRUCK	1886270000	B.18
MF-SI 8/6 MC NEUTRAL	1889240000	B.19
MF-SI 8/6 MC SONDERDRUCK	1889230000	B.19
MF-W 5/5 MINI MC BL	1924270000	B.18
MF-W 5/5 MINI MC GE	1924280000	B.18
MF-W 5/5 MINI MC GN	1924290000	B.18
MF-W 5/5 MINI MC NEUTR.	1816240000	B.18
MF-W 5/5 MINI MC RT	1924260000	B.18
MF-W 5/5 MINI MC S.DR.	1816310000	B.18
MF-W 9/4 MC NEUTRAL	1877730000	B.18
MF-W 9/4 MC SONDERDRUCK	1877710000	B.18
MF-W 9/4.2F MC NE WS	1011430000	B.18
MF-W 9/4.2F MC SDR	1038750000	B.18
MF-W 9/5 MC NEUTRAL	1816270000	B.18
MF-W 9/5 MC SONDERDRUCK	1816340000	B.18
MF-W 9/5.2F MC NE WS	1011410000	B.18
MF-W 9/5.2F MC SDR	1038760000	B.18
MF-W 9/5F MC NEUTRAL	1816280000	B.18
MF-W 9/5F MC SONDERDR.	1816350000	B.18
MF-W 9/6 MC NEUTRAL	1816290000	B.19
MF-W 9/6 MC SONDERDRUCK	1816360000	B.19
MF-W 9/6.2F MC NE WS	1011420000	B.19
MF-W 9/6.2F MC SDR	1038770000	B.19
MF-WO 12/5 MC NEUTRAL	1692270000	B.18
MF-WO 12/5 MC SONDERDR.	1692280000	B.18
MF-WO 12/6 MC NEUTRAL	1692290000	B.19
MF-WO 12/6 MC SONDERDR.	1692300000	B.19
MF-WO 5/5 MC NEUTRAL	1716800000	B.18
MF-WO 5/5 MC SONDERDR.	1716810000	B.18
MF-WO 9/5 MC NEUTRAL	1716840000	B.18
MF-WO 9/5 MC SONDERDR.	1716850000	B.18
MF-WO 9/6 MC NEUTRAL	1716820000	B.19
MF-WO 9/6 MC SONDERDR.	1716830000	B.19
M-PRINT PRO	1905490000	E.12
M-PRINT PRO ADVANCED	1905500000	E.12

P

PAGETAB 15X9	1686160000	D.15
PAGETAB 19X11	1686170000	D.15
PAGETAB 20X8	1686180000	D.15
PAGETAB 28X11	1686190000	D.15
PAGETAB 38X11	1686200000	D.15
PAGETAB 56X22	1686210000	D.15
PAGETAB 60X35	1686220000	D.15
P-CLEANER	1924330000	E.6
P-CLEANER	1924330000	E.7
P-INK	1924340000	E.6
P-INK	1924340000	E.7
PJ PRO TNAW	1024140000	E.3
PJ PRO TNTK INK C	1027050000	E.3
PJ PRO TNTK INK K	1027040000	E.3
PJ PRO TNTK INK M	1027060000	E.3
PJ PRO TNTK INK Y	1027070000	E.3
PJ-Clean Unit	4062150000	E.3
PJ-PRO TNTK INK SET COL	1027110000	E.3
PLOTTER PEN 0.25 P-INK	1920640000	E.6
PLOTTER PEN 0.25 P-INK	1920640000	E.7
PLOTTER PEN 0.35 P-INK	1920650000	E.6
PLOTTER PEN 0.35 P-INK	1920650000	E.7
PLOTTER PEN 0.50 P-INK	1005710000	E.6
PLOTTER PEN 0.50 P-INK	1005710000	E.7
PLOTTER PEN 0.70 P-INK	1011450000	E.6
PLOTTER PEN 0.70 P-INK	1011450000	E.7
Plotterpen 0,18	1768570000	E.6
Plotterpen 0,18	1768570000	E.7
Plotterpen 0,25	1768540000	E.6
Plotterpen 0,25	1768540000	E.7
Plotterpen 0,35	1768550000	E.6
Plotterpen 0,35	1768550000	E.7
Plotterpen 0,5	1768560000	E.6
Plotterpen 0,5	1768560000	E.7
Plotterpen 0,7	1011440000	E.6
Plotterpen 0,7	1011440000	E.7
PRINT KIT	1686920000	E.7
PRINTJET PRO 115V	1024050000	E.3
PRINTJET PRO 230V	1001180001	E.3

R

Reiniger 2000 25ml	1772130000	E.6
Reiniger 2000 25ml	1772130000	E.7
Ribbon HSS R 83/300	1962370000	E.8
Ribbon HSS R 83/300	1962370000	E.9
Ribbon HSS WR 90/300	1962360000	E.9

S

SCHS 1 SCHWARZ	0138900000	D.5
SCHS 2 F.BS SCHILDER	0337400000	D.5
SCHS 2 SK F. ESG	1720600000	D.5
SCHS3 K	1753480000	D.5
SCHS4 K	1753460000	D.5
SCHT 14/6	1269060000	B.37
SCHT 5	0292460000	B.36
SCHT 5 S	1631930000	B.36
SCHT 7	0517960000	B.36
SCHT 9/4	1278460000	B.37
SCT 4 ,6/127 C	1699800000	C.57
SCT 4,6/201 C	1699810000	C.57
SCT 4,6/266C	1699900000	C.57
SCT 4,6/360 C	1699910000	C.57
SCT 4,6/520	1699920000	C.57
SCT 4,6/679	1699930000	C.57
SCT 4,6/838	1699940000	C.57
SCT-C 4.6/100	1015220000	C.58
SCT-C 4.6/125	1015230000	C.58
SCT-C 4.6/150	1015240000	C.58
SCT-C 4.6/200	1015250000	C.58
SCT-C 4.6/360	1015270000	C.58
SCT-C 4.6/520	1015280000	C.58
SCT-C 4.6/680	1015290000	C.58
SCT-C 4.6/840	1015300000	C.58
SCT-C 7.9/200	1015310000	C.58
SCT-C 7.9/360	1015320000	C.58
SCT-C 7.9/520	1015330000	C.58
SCT-C 7.9/680	1015340000	C.58
SCT-C 7.9/840	1015350000	C.58
SERV-P. DIAM16 L1 SW/WS	1707350001	D.14
SERV-P. DIAM16 L2 SW/WS	1707350002	D.14
SERV-P. DIAM16 L3 SW/WS	1707350003	D.14
SERV-P. DIAM16 N BL/WS	1707350004	D.14
SERV-P. DIAM16 PE GE/GN	1707350006	D.14
SERV-P.DIAM16ERDE GE/GN	1707350005	D.14
SF 0/12 NEUTRAL BL V2	1919220000	C.5
SF 0/12 NEUTRAL GE V2	1919210000	C.5
SF 0/12 NEUTRAL RT V2	1919230000	C.5
SF 0/12 NEUTRAL WS V2	1919240000	C.5
SF 0/12 SONDERDRUCK V2	1919250000	C.5
SF 0/21 NEUTRAL BL V2	1918510000	C.5
SF 0/21 NEUTRAL GE V2	1918480000	C.5
SF 0/21 NEUTRAL RT V2	1918490000	C.5
SF 0/21 NEUTRAL WS V2	1918500000	C.5
SF 0/21 SONDERDRUCK V2	1918470000	C.5
SF 00/12 NEUTRAL BL V2	1919270000	C.5
SF 00/12 NEUTRAL GE V2	1919260000	C.5
SF 00/12 NEUTRAL RT V2	1919280000	C.5
SF 00/12 NEUTRAL WS V2	1919290000	C.5
SF 00/12 SONDERDRUCK V2	1919300000	C.5
SF 00/21 NEUTRAL BL V2	1918590000	C.5
SF 00/21 NEUTRAL GE V2	1918560000	C.5
SF 00/21 NEUTRAL RT V2	1918570000	C.5
SF 00/21 NEUTRAL WS V2	1918580000	C.5
SF 00/21 SONDERDRUCK V2	1918530000	C.5
SF 1/12 NEUTRAL BL V2	1919360000	C.5
SF 1/12 NEUTRAL GE V2	1919340000	C.5
SF 1/12 NEUTRAL RT V2	1919320000	C.5
SF 1/12 NEUTRAL WS V2	1919390000	C.5
SF 1/12 SONDERDRUCK V2	1919420000	C.5
SF 1/21 NEUTRAL BL V2	1918620000	C.5
SF 1/21 NEUTRAL GE V2	1918610000	C.5
SF 1/21 NEUTRAL RT V2	1918600000	C.5
SF 1/21 NEUTRAL WS V2	1918630000	C.5
SF 1/21 SONDERDRUCK V2	1918640000	C.5
SF 2/12 NEUTRAL BL V2	1919480000	C.5
SF 2/12 NEUTRAL GE V2	1919470000	C.5
SF 2/12 NEUTRAL RT V2	1919460000	C.5
SF 2/12 NEUTRAL WS V2	1919490000	C.5
SF 2/12 SONDERDRUCK V2	1919500000	C.5
SF 2/21 NEUTRAL BL V2	1918700000	C.5
SF 2/21 NEUTRAL GE V2	1918660000	C.5
SF 2/21 NEUTRAL RT V2	1918670000	C.5
SF 2/21 NEUTRAL WS V2	1918690000	C.5
SF 2/21 SONDERDRUCK V2	1918650000	C.5
SF 3/12 NEUTRAL BL V2	1919550000	C.5
SF 3/12 NEUTRAL GE V2	1919520000	C.5
SF 3/12 NEUTRAL RT V2	1919530000	C.5
SF 3/12 NEUTRAL WS V2	1919540000	C.5
SF 3/12 SONDERDRUCK V2	1919510000	C.5
SF 3/21 NEUTRAL BL V2	1918920000	C.5
SF 3/21 NEUTRAL GE V2	1918890000	C.5
SF 3/21 NEUTRAL RT V2	1918900000	C.5
SF 3/21 NEUTRAL WS V2	1918910000	C.5
SF 3/21 SONDERDRUCK V2	1918880000	C.5
SF 4,5/21 NEUTRAL BL V2	1919030000	C.5
SF 4,5/21 NEUTRAL GE V2	1919000000	C.5
SF 4,5/21 NEUTRAL RT V2	1919010000	C.5
SF 4,5/21 NEUTRAL WS V2	1919020000	C.5
SF 4,5/21 SONDERDRUCK V2	1918990000	C.5
SF 4/12 NEUTRAL BL V2	1919590000	C.5
SF 4/12 NEUTRAL GE V2	1919580000	C.5
SF 4/12 NEUTRAL RT V2	1919570000	C.5
SF 4/12 NEUTRAL WS V2	1919600000	C.5
SF 4/12 SONDERDRUCK V2	1919610000	C.5
SF 4/21 NEUTRAL BL V2	1919090000	C.5
SF 4/21 NEUTRAL GE V2	1919060000	C.5
SF 4/21 NEUTRAL RT V2	1919070000	C.5
SF 4/21 NEUTRAL WS V2	1919080000	C.5
SF 4/21 SONDERDRUCK V2	1919050000	C.5
SF 5/12 NEUTRAL BL V2	1919630000	C.5
SF 5/12 NEUTRAL GE V2	1919620000	C.5
SF 5/12 NEUTRAL RT V2	1919640000	C.5
SF 5/12 NEUTRAL WS V2	1919650000	C.5
SF 5/12 SONDERDRUCK V2	1919660000	C.5
SF 5/21 NEUTRAL BL V2	1919150000	C.5
SF 5/21 NEUTRAL GE V2	1919120000	C.5
SF 5/21 NEUTRAL RT V2	1919130000	C.5
SF 5/21 NEUTRAL WS V2	1919140000	C.5
SF 5/21 SONDERDRUCK V2	1919110000	C.5
SF 6/21 NEUTRAL BL V2	1919200000	C.5
SF 6/21 NEUTRAL GE V2	1919170000	C.5
SF 6/21 NEUTRAL RT V2	1919180000	C.5
SF 6/21 NEUTRAL WS V2	1919190000	C.5
SF 6/21 SONDERDRUCK V2	1919160000	C.5
SFC 0/12 NEUTRAL BL	1813170000	C.7
SFC 0/12 NEUTRAL GE	1813160000	C.7
SFC 0/12 NEUTRAL RT	1813150000	C.7
SFC 0/12 NEUTRAL WS	1813130000	C.7
SFC 0/12 SONDERDRUCK	1813180000	C.7
SFC 0/21 NEUTRAL BL	1813220000	C.7
SFC 0/21 NEUTRAL GE	1813210000	C.7
SFC 0/21 NEUTRAL RT	1813200000	C.7
SFC 0/21 NEUTRAL WS	1813190000	C.7
SFC 0/21 SONDERDRUCK	1813230000	C.7
SFC 0/30 NEUTRAL BL	1813270000	C.7
SFC 0/30 NEUTRAL GE	1813260000	C.7
SFC 0/30 NEUTRAL RT	1813250000	C.7
SFC 0/30 NEUTRAL WS	1813240000	C.7
SFC 0/30 SONDERDRUCK	1813280000	C.7
SFC 1/12 NEUTRAL BL	1747320002	C.7
SFC 1/12 NEUTRAL GE	1747320004	C.7
SFC 1/12 NEUTRAL RT	1747320003	C.7
SFC 1/12 NEUTRAL WS	1747320001	C.7
SFC 1/12 SONDERDRUCK	1752720000	C.7
SFC 1/21 NEUTRAL BL	1779080002	C.7
SFC 1/21 NEUTRAL GE	1779080004	C.7
SFC 1/21 NEUTRAL RT	1779080003	C.7
SFC 1/21 NEUTRAL WS	1779080001	C.7
SFC 1/21 SONDERDRUCK	1779090000	C.7
SFC 1/30 NEUTRAL BL	1805720000	C.7
SFC 1/30 NEUTRAL GE	1805730000	C.7
SFC 1/30 NEUTRAL RT	1805740000	C.7
SFC 1/30 NEUTRAL WS	1805760000	C.7
SFC 1/30 SONDERDRUCK	1805750000	C.7
SFC 2/12 BEDR./FARBIG	1763480000	C.7
SFC 2/12 NEUTRAL BL	1758320002	C.7
SFC 2/12 NEUTRAL GE	1758320004	C.7
SFC 2/12 NEUTRAL RT	1758320003	C.7
SFC 2/12 NEUTRAL WS	1758320001	C.7
SFC 2/21 NEUTRAL BL	1805770000	C.7
SFC 2/21 NEUTRAL GE	1805780000	C.7
SFC 2/21 NEUTRAL RT	1805790000	C.7
SFC 2/21 NEUTRAL WS	1805810000	C.7
SFC 2/21 SONDERDRUCK	1805800000	C.7
SFC 2/30 NEUTRAL BL	1805820000	C.7
SFC 2/30 NEUTRAL GE	1805830000	C.7
SFC 2/30 NEUTRAL RT	1805850000	C.7
SFC 2/30 NEUTRAL WS	1805870000	C.7
SFC 2/30 SONDERDRUCK	1805860000	C.7
SFC 3/12 MC NE BL	1025250000	C.7
SFC 3/12 MC NE GE	1025230000	C.7
SFC 3/12 MC NE RT	1025240000	C.7
SFC 3/12 MC NE WS	1025220000	C.7
SFC 3/12 MC SDR	1025550000	C.7
SFC 3/21 MC NE BL	1025300000	C.7
SFC 3/21 MC NE GE	1025270000	C.7
SFC 3/21 MC NE RT	1025290000	C.7
SFC 3/21 MC NE WS	1025260000	C.7
SFC 3/21 MC SDR	1025560000	C.7
SFC 3/30 MC NE BL	1025340000	C.7
SFC 3/30 MC NE GE	1025320000	C.7
SFC 3/30 MC NE RT	1025330000	C.7
SFC 3/30 MC NE WS	1025310000	C.7
SFC 3/30 MC SDR	1025570000	C.7
SF-TOOL 00-6	1950820000	C.5
SF-TOOL 1	1782970000	C.5
SF-TOOL 2-3	1782960000	C.5
SF-TOOL 4-5	1782980000	C.5
SF-Tool-Sortiment	1770080000	C.5
SFX 10/23 NEUTRAL BL V2	1852400000	C.5
SFX 10/23 NEUTRAL GE V2	1852360000	C.5
SFX 10/23 NEUTRAL RT V2	1852370000	C.5
SFX 10/23 NEUTRAL WS V2	1852390000	C.5
SFX 10/23 SONDERDRUCK V2	1852380000	C.5
SFX 11/60 MC NE BL	1051870000	C.5
SFX 11/60 MC NEUTRAL GE	1860150000	C.5
SFX 11/60 MC NEUTRAL RT	1963650000	C.5
SFX 11/60 MC NEUTRAL WS	1860120000	C.5
SFX 11/60 SONDERDRUCK	1860140000	C.5
SFX 14/23 NEUTRAL BL V2	1852450000	C.5
SFX 14/23 NEUTRAL GE V2	1852410000	C.5
SFX 14/23 NEUTRAL RT V2	1852420000	C.5
SFX 14/23 NEUTRAL WS V2	1852440000	C.5
SFX 14/23 SONDERDR. V2	1852430000	C.5
SFX 30/60 MC NE GE	1083240000	C.5
SFX 30/60 MC NE WS	1083230000	C.5

Type	Order No.	Page
SFX 30/60 MC SDR	1083260000	C.5
SFX 9/24 NEUTRAL BL V2	1852500000	C.5
SFX 9/24 NEUTRAL GE V2	1852460000	C.5
SFX 9/24 NEUTRAL RT V2	1852470000	C.5
SFX 9/24 NEUTRAL WS V2	1852490000	C.5
SFX 9/24 SONDERDRUCK V2	1852480000	C.5
SM 22/22 K MC NE GE	1131830000	D.6
SM 22/22 K MC NE GR	1014650000	D.6
SM 22/22 K MC NEUTR. SI	1877590000	D.6
SM 22/22 K MC NEUTR. WS	1877570000	D.6
SM 22/22 K MC SONDERD.	1877580000	D.6
SM 27/12.5 K MC NE GE	1131810000	D.6
SM 27/12.5 K MC NE GR	1027830000	D.6
SM 27/12.5 K SI NEUTRAL	1713720000	D.6
SM 27/12.5 K SONDERDRUCK	1699890000	D.6
SM 27/12.5 K WS NEUTR.	1699880000	D.6
SM 27/12.5 MC NE GE	1131860000	D.6
SM 27/12.5 MC NE GR	1079490000	D.6
SM 27/12.5 NEUTRAL SI	1713700000	D.6
SM 27/12.5 NEUTRAL WS	1699840000	D.6
SM 27/12.5 SONDERDRUCK	1699850000	D.6
SM 27/18 K MC NE GR	1073340000	D.6
SM 27/18 K NEUTRAL GE	1915340000	D.6
SM 27/18 K NEUTRAL ROT	1906120000	D.6
SM 27/18 K NEUTRAL SI	1713760000	D.6
SM 27/18 K SONDERDRUCK	1707280000	D.6
SM 27/18 K WS NEUTR.	1707270000	D.6
SM 27/18 MC NE GE	1131850000	D.6
SM 27/18 MC NE GR	1014640000	D.6
SM 27/18 NEUTRAL ROT	1906110000	D.6
SM 27/18 NEUTRAL SI	1713740000	D.6
SM 27/18 NEUTRAL WS	1699860000	D.6
SM 27/18 SONDERDRUCK	1699870000	D.6
SM 27/27 K MC NE GE	1131800000	D.6
SM 27/27 K MC NE GR	1079520000	D.6
SM 27/27 K SI NEUTRAL	1782990000	D.6
SM 27/27 K SONDERDRUCK	1783010000	D.6
SM 27/27 K WS NEUTRAL	1783000000	D.6
SM 27/27 MC NE GE	1131840000	D.6
SM 27/27 MC NE GR	1079510000	D.6
SM 27/27 NEUTRAL SI	1773230000	D.6
SM 27/27 NEUTRAL WS	1773220000	D.6
SM 27/27 SONDERDRUCK	1773240000	D.6
SM 27/8 K MC NE GE	1131820000	D.6
SM 27/8 K MC NE GR	1079480000	D.6
SM 27/8 K SI NEUTRAL	1771930000	D.6
SM 27/8 K SONDERDRUCK	1713690000	D.6
SM 27/8 K WS NEUTRAL	1812630000	D.6
SM 27/8 MC NE GE	1131870000	D.6
SM 27/8 MC NE GR	1079470000	D.6
SM 27/8 NEUTRAL SI	1713680000	D.6
SM 27/8 NEUTRAL WS	1699820000	D.6
SM 27/8 SONDERDRUCK	1699830000	D.6
SM-H 27/12.5 SW	1716640000	D.7
SM-H 27/18 SW	1716630000	D.7
SM-H 27/27 SW	1782710000	D.7
SNAPMARK I	1805880000	B.35
STI Waterproof schwarz	0508401694	E.6
STI Waterproof schwarz	0508401694	E.7
STR 15 F. ZGB 15	1636520000	B.39
STR 5 F.SCHT 5	0294000000	B.36
STR 5 S F.SCHT 5 S	1631940000	B.36
STR 7 F.SCHT 7	0515300000	B.36
STR 7 F.SCHT 7	0515300000	B.39
STR CC 15/17 TRANSPARENT	1888310000	D.9
STR CC 15/27 TRANSPARENT	1888290000	D.9
STR CC 15/49 TRANSPARENT	1888300000	D.9
STR CC 15/60 TRANSPARENT	1888280000	D.9
STR CC 30/60 TRANSPARENT	1934450000	D.9
STR F.SCHS	0139200000	D.5
SYMBOL-P. 25X25X25 B/DR	1741090000	D.14
SYMBOL-P. 50X50X50 B/DR	1741100000	D.14
SYMBOL-P. 75X75X75 B/DR	1741110000	D.14
SYMBOL-PACK 14X14 ERDE	1685690002	D.14
SYMBOL-PACK 14X14 SYMB.	1685690001	D.14
SYMBOL-PACK 9X19 SYMB.	1685700000	D.14

T

TABPACK 14X9	1686110000	D.15
TABPACK 15X6	1686120000	D.15
TABPACK 19X11 M. RAND	1686130000	D.15
TABPACK 21X8	1686140000	D.15
TABPACK 38X11 M. RAND	1686150000	D.15
THM BASIC	1141340000	E.11
THM DRUCKER PRO	1785240000	E.10
THM EL 15 WS	1096170000	D.13
THM EL 24 WS	1105550000	D.13
THM EL 38 WS	1105560000	D.13
THM ET S7 300-1 GE	1161770000	D.13
THM ET S7 300-1 TU	1161750000	D.13
THM ET S7 300-2 GE	1161740000	D.13
THM ET S7 300-2 TU	1161730000	D.13
THM ET S7 400 GE	1161720000	D.13
THM ET S7 400 TU	1161710000	D.13
THM ET S7 50/12,5 GE	1161810000	D.13
THM ET S7 50/12,5 TU	1161790000	D.13
THM ET S7 50/25 GE	1095590000	D.13
THM ET S7 50/25 TU	1161780000	D.13
THM GEW 15/6 GE	1059790000	D.12
THM GEW 15/6 WS	1059780000	D.12
THM GEW 17/9 GE	1059810000	D.12
THM GEW 17/9 WS	1059800000	D.12
THM GEW 18/6 GE	1059830000	D.12
THM GEW 18/6 WS	1059820000	D.12
THM GEW 18/9 GE	1059850000	D.12
THM GEW 18/9 WS	1059840000	D.12
THM GEW 20/8 GE	1059880000	D.12
THM GEW 20/8 WS	1059870000	D.12
THM MT30x 101/150 SI/G	1778170000	D.12
THM MT30X 101/48 GE/M	1751821687	D.12
THM MT30X 101/48 SI/M	1751820001	D.12
THM MT30X 101/48 WS/M	1751821044	D.12
THM MT30x 101/74 GE	1061810000	D.12
THM MT30x 101/74 si	1762960001	D.12
THM MT30X 15/4 GE/M	1072690000	D.12
THM MT30x 15/5,08 GE	1964130000	D.12
THM MT30X 15/6 GE/M	1753231687	D.12
THM MT30X 15/6 SI/M	1753230001	D.12
THM MT30X 15/6 WS/M	1753231044	D.12
THM MT30x 16/7 GE	1852520000	D.12
THM MT30x 17/8 GE	1027620000	D.12
THM MT30X 17/9 GE/M	1856650000	D.12
THM MT30x 17/9 WS	1968130000	D.12
THM MT30X 18/6 GE/M	1753271687	D.12
THM MT30X 18/6 SI/M	1753270001	D.12
THM MT30X 18/6 WS/M	1753271044	D.12
THM MT30X 18/9 GE/M	1753251687	D.12
THM MT30X 18/9 SI/M	1753250001	D.12
THM MT30X 18/9 WS/M	1753251044	D.12
THM MT30X 20/8 GE/M	1753241687	D.12
THM MT30X 20/8 SI/M	1753240001	D.12
THM MT30X 20/8 WS/M	1753241044	D.12
THM MT30X 25,9/7,1 WS	1891770000	D.12
THM MT30X 25/12 GE/M	1751751687	D.12
THM MT30X 25/12 SI/M	1751750001	D.12
THM MT30X 25/12 WS/M	1751751044	D.12
THM MT30x 26,5/17,5 SI/M	1770090000	D.12
THM MT30X 26/10 GE/M	1751761687	D.12
THM MT30X 26/10 SI/M	1751760001	D.12
THM MT30X 26/10 WS/M	1751761044	D.12
THM MT30X 30/20 GE/M	1753261687	D.12
THM MT30X 30/20 SI/M	1753260001	D.12
THM MT30X 30/20 WS/M	1753261044	D.12
THM MT30x 30/52 SI	1014680000	D.12
THM MT30X 32/9 SI/M	1751770001	D.12
THM MT30X 32/9 WS/M	1751771044	D.12
THM MT30x 38,1/31,75 SI	1862350000	D.12
THM MT30x 38/17 WS	1011610000	D.12
THM MT30X 38/19 GE/M	1751801687	D.12
THM MT30X 38/19 SI/M	1751800001	D.12
THM MT30X 38/19 WS/M	1751801044	D.12
THM MT30X 45/23 GE/M	1751811687	D.12
THM MT30X 45/23 SI/M	1751810001	D.12
THM MT30X 45/23 WS/M	1751811044	D.12
THM MT30x 57/27 SI	1852540000	D.12
THM MT30X 65/35 GE/M	1751831687	D.12
THM MT30X 65/35 SI/M	1751830001	D.12
THM MT30X 65/35 WS/M	1751831044	D.12
THM MT30x 8/8 WS	1954070000	D.12
THM MT30x 89/60 SI	1003410000	D.12
THM pro HiRes	1790650000	E.10
THM pro HiRes	1790650000	E.11
THM pro HiRes	1790650000	E.9
THM WRITE ON 12/18 GE	1856630000	C.17
THM WRITE ON 12/18 WS	1856640000	C.17
THM WRITE ON 25/76 GE	1774340000	C.17
THM WRITE ON 25/76 WS	1774350000	C.17
THM WRITE ON 35,6/93 GE	1774410000	C.17
THM WRITE ON 35,6/93 WS	1774400000	C.17
THM WRITE ON 49,5/57 WS	1882900000	C.17
THM WRITEON 17,8/34WS	1774380000	C.17
THM WRITEON 25,4/62 WS	1109130000	C.17
THM WRITEON 25,4/92,5WS	1109140000	C.17
THM WRITEON 25/140 GE	1751561687	C.17
THM WRITEON 25/140 WS	1751561044	C.17
THM WRITEON 50,8/150 GE	1109180000	C.17
THM WRITEON 50,8/150 WS	1109150000	C.17
THM WRITEON 51/36 WS	1934190000	C.17
THM WRITEON T 24.5/100 WS	1003380000	C.17
THM WRITEON T 24.5/62 WS	1003420000	C.17
THM-PLUS PRINTER	1962340000	E.9
THM-TWINMARK	1140490000	E.8
Tinte 2000 25ml	1772120000	E.6
Tinte 2000 25ml	1772120000	E.7
Tintenpatrone PrintJet	1797460000	E.3
Tintentank PrintJet II	1858920000	E.3
TM 0/12 HF/HB	1719760000	C.10
TM 0/18 HF/HB	1719770000	C.10
TM 0/18 TWIN HF/HB	1891810000	C.10
TM 1/12 HF/HB	1719780000	C.10
TM 1/18 HF/HB	1719790000	C.10
TM 1/18 TWIN HF/HB	1891780000	C.10
TM 2/12 HF/HB	1719800000	C.10
TM 2/18 HF/HB	1719810000	C.10
TM 200/15 V0	1798650000	C.12
TM 201/12 V0	1798640000	C.12
TM 201/15 V0	1798620000	C.12
TM 201/18 V0	1798600000	C.12
TM 201/20 V0	1798580000	C.12
TM 201/30 V0	1874850000	C.12
TM 202/12 V0	1798560000	C.12
TM 202/15 V0	1798540000	C.12
TM 202/18 V0	1798530000	C.12
TM 202/20 V0	1798520000	C.12
TM 202/30 V0	1874760000	C.12
TM 203/12 V0	1798510000	C.12
TM 203/15 V0	1798490000	C.12
TM 203/18 V0	1798480000	C.12
TM 203/20 V0	1798470000	C.12
TM 203/30 V0	1874770000	C.12
TM 204/12 V0	1806180000	C.12
TM 204/15 V0	1806240000	C.12
TM 204/18 V0	1806300000	C.12
TM 204/20 V0	1806360000	C.12
TM 204/30 V0	1874780000	C.12
TM 205/12 V0	1806190000	C.12
TM 205/15 V0	1806250000	C.12
TM 205/18 V0	1806310000	C.12
TM 205/20 V0	1806370000	C.12
TM 205/30 V0	1874790000	C.12
TM 206/12 V0	1806200000	C.12
TM 206/15 V0	1806260000	C.12
TM 206/18 V0	1806320000	C.12
TM 206/20 V0	1806380000	C.12
TM 206/30 V0	1874800000	C.12
TM 207/12 V0	1806210000	C.12
TM 207/15 V0	1806270000	C.12
TM 207/18 V0	1806330000	C.12
TM 207/20 V0	1806390000	C.12
TM 207/30 V0	1874820000	C.12
TM 208/12 V0	1806220000	C.12
TM 208/15 V0	1806280000	C.12
TM 208/18 V0	1806340000	C.12
TM 208/20 V0	1806400000	C.12
TM 208/30 V0	1874830000	C.12
TM 209/12 V0	1806230000	C.12
TM 209/15 V0	1806290000	C.12
TM 209/18 V0	1806350000	C.12
TM 209/20 V0	1806410000	C.12
TM 209/30 V0	1874720000	C.12
TM 3/12 HF/HB	1719820000	C.10
TM 3/18 HF/HB	1719830000	C.10
TM 4/12 HF/HB	1719840000	C.10
TM 4/18 HF/HB	1719850000	C.10
TM 5/12 HF/HB	1719860000	C.10
TM 5/18 HF/HB	1719870000	C.10
TM 6/12 HF/HB	1719880000	C.10
TM 6/18 HF/HB	1719890000	C.10
TM-I 12 NEUTRAL BL	1718411693	C.9
TM-I 12 NEUTRAL GE	1718411687	C.9
TM-I 12 NEUTRAL GN	1718411688	C.9
TM-I 12 NEUTRAL RT	1718411686	C.9
TM-I 12 NEUTRAL WS	1718411044	C.9
TM-I 12 SONDERDRUCK	1718420000	C.9
TM-I 15 NEUTRAL BL	1609981693	C.9
TM-I 15 NEUTRAL GE	1609981687	C.9
TM-I 15 NEUTRAL GN	1609981688	C.9
TM-I 15 NEUTRAL RT	1609981686	C.9
TM-I 15 NEUTRAL WS	1609981044	C.9
TM-I 15 SONDERDRUCK	1609990000	C.9
TM-I 18 NEUTRAL BL	1718431693	C.9
TM-I 18 NEUTRAL GE	1718431687	C.9
TM-I 18 NEUTRAL GN	1718431688	C.9
TM-I 18 NEUTRAL RT	1718431686	C.9
TM-I 18 NEUTRAL WS	1718431044	C.11
TM-I 18 NEUTRAL WS	1718431044	C.9
TM-I 18 SONDERDRUCK	1718440000	C.9
TM-I 20 NEUTRAL BL	1680411693	C.9
TM-I 20 NEUTRAL GE	1680411687	C.9
TM-I 20 NEUTRAL GN	1680411688	C.9
TM-I 20 NEUTRAL RT	1680411686	C.9
TM-I 20 NEUTRAL WS	1680411044	C.9
TM-I 20 SONDERDRUCK	1680420000	C.9
TM-I 30 MC NEUTRAL BL	1876400000	C.9
TM-I 30 MC NEUTRAL GE	1876370000	C.9
TM-I 30 MC NEUTRAL RT	1876380000	C.9
TM-I 30 MC NEUTRAL WS	1876390000	C.9
TM-I 30 MC SONDERDRUCK	1876320000	C.9
TMX 18 HF/HB	1748820000	C.10
TMX 30 V0	1866680000	C.12

W

WAD 12 M. BL.	1055960000	B.38
WAD 12 NEUTRAL	1056260000	B.38
WAD 27 M. BL.	1062860000	B.38
WAD 27 NEUTRAL	1062960000	B.38
WAD 5 M. BL.	1053460000	B.38
WAD 5 MC B GE/SW	1120450000	B.34
WAD 5 MC NE GE	1112920000	B.34
WAD 5 MC NE WS	1112910000	B.34
WAD 5 MC SDR	1112930000	B.34
WAD 5 NEUTRAL	1056060000	B.38
WAD 5 Sonderdruck	1790060000	B.38
WAD 8 M. BL.	1053560000	B.38
WAD 8 MC B GE/SW	1120470000	B.34
WAD 8 MC NE GE	1112950000	B.34
WAD 8 MC NE WS	1112940000	B.34
WAD 8 MC SDR	1112970000	B.34
WAD 8 NEUTRAL	1056160000	B.38
WAD 8 SONDERDRUCK	1667700000	B.38
WGB 5 ABDG.M.GRUPPENBEZ	1050760000	B.38
WGB 8 ABDG.M.GRUPPENBEZ	1050960000	B.38
WKM 18/43	1610700000	C.13
WKM 8/20	1753490000	C.13
WKM 8/30	1631910000	C.13
WS 10/12 MC NEUTRAL	1905970000	B.15
WS 10/12 MC SONDERDRUCK	1906060000	B.15
WS 10/15 MC Neutr.	1854090000	B.15
WS 10/15 MC Sonderdruck	1854100000	B.15
WS 10/5 MC BEDRUCKT	1635010000	B.14
WS 10/5 MC Midd. Neutr.	1792000000	B.14
WS 10/5 MC Midd. Neutr.	1792000000	B.35
WS 10/5 MC Midd. Neutr.	1792000000	B.36
WS 10/5 MC Midd. Sonder	1792010000	B.14
WS 10/5 MC NEUTRAL	1635000000	B.14
WS 10/5 MC NEUTRAL	1635000000	B.35
WS 10/5 MC neutral BL	1773531693	B.14
WS 10/5 MC neutral GE	1773531687	B.14
WS 10/5 MC neutral RT	1773531686	B.14
WS 10/5 PLUS MC NE WS	1046380000	B.14
WS 10/5 PLUS MC SDR	1046320000	B.14
WS 10/6 MC Midd. Neutr.	1818400000	B.14
WS 10/6 MC Midd. Sonder	1818410000	B.15
WS 10/6 MC MIDDLE GE	1917430000	B.14
WS 10/6 MC MIDDLE GN	1917420000	B.14
WS 10/6 MC MIDDLE OR	1917410000	B.14
WS 10/6 MC MIDDLE RT	1917440000	B.14
WS 10/6 MC NEUTRAL	1828450000	B.14
WS 10/6 MC Sonderdruck	1828460000	B.15
WS 10/6 PLUS MC NE WS	1046390000	B.14
WS 10/6 PLUS MC SDR	1046330000	B.15
WS 10/8 MC NEUTRAL	1905950000	B.15
WS 10/8 MC SONDERDRUCK	1906030000	B.15
WS 12/3,5 MC neutral	1778270000	B.14
WS 12/3,5 MC Sonderdr.	1778280000	B.14
WS 12/5 MC BEDRUCKT	1609870000	B.14
WS 12/5 MC NEUTRAL	1609860000	B.14
WS 12/5 MC NEUTRAL	1609860000	B.37
WS 12/5 MC NEUTRAL	1609860000	B.38
WS 12/5 MC NEUTRAL	1609860000	B.39
WS 12/5 MC neutral BL	1773541693	B.14
WS 12/5 MC neutral GE	1773541687	B.14
WS 12/5 MC neutral OR	1773541690	B.14
WS 12/5 MC neutral RT	1773541686	B.14
WS 12/5 PLUS MC NEUTRAL	1927510000	B.14
WS 12/5 PLUS SONDERDRUCK	1927520000	B.14
WS 12/6 MC BEDRUCKT	1609910000	B.15
WS 12/6 MC NEUTRAL	1609900000	B.14
WS 12/6 MC neutral BL	1773551693	B.14
WS 12/6 MC neutral BR	1773551692	B.14
WS 12/6 MC neutral GE	1773551687	B.14
WS 12/6 MC neutral OR	1773551690	B.14
WS 12/6 MC neutral RT	1773551686	B.14
WS 12/6 MC neutral VI	1773551689	B.14
WS 12/6 PLUS MC NEUTRAL	1927530000	B.14
WS 12/6 PLUS SONDERDRUCK	1927540000	B.15
WS 12/6,5 MC BEDRUCKT	1609930000	B.15
WS 12/6,5 MC NEUTRAL	1609920000	B.15
WS 12/6,5 MC neutral BL	1773561693	B.15
WS 12/6,5 MC neutral GE	1773561687	B.15
WS 12/6,5 MC neutral GN	1773561688	B.15
WS 12/6,5 MC neutral RT	1773561686	B.15
WS 12/8 MC NEUTRAL	1906000000	B.15
WS 12/8 MC SONDERDRUCK	1906010000	B.15
WS 14/5 MC NEUTRAL	1768090000	B.14
WS 15/5 MC BEDRUCKT	1609890000	B.14
WS 15/5 MC NEUTRAL	1609880000	B.14
WS 15/5 MC neutral GE	1773571687	B.14
WS 8/5 MC BEDRUCKT	1640750000	B.14
WS 8/5 MC NEUTRAL	1640740000	B.14
WS 8/5 MC neutral BL	1773521693	B.14
WS 8/5 MC neutral GE	1773521687	B.14
WS 8/5 MC neutral OR	1773521690	B.14
WS 8/5 MC neutral RT	1773521686	B.14
WS 8/5 PLUS MC NEUTRAL	1951870000	B.14
WS 8/5 PLUS MC SDR	1038790000	B.14
WS 8/6 PLUS MC NEUTRAL	1951880000	B.14
WS 8/6 PLUS MC SDR	1038820000	B.15
WSK 12 , LEER	0335900000	C.53
WSK12 m. CLI C 1-3 GE/SW Bez. 0-9	0336000000	C.53
WSM 10 -	1712501740	C.56
WSM 10 (	1712501744	C.56
WSM 10 .	1712501743	C.56
WSM 10 /	1712501739	C.56
WSM 10 :	1712501741	C.56
WSM 10 ~	1712501056	C.56
WSM 10 +	1712501738	C.56
WSM 10 =	1712501742	C.56
WSM 10 0	1712501000	C.56
WSM 10 1	1712500001	C.56
WSM 10 2	1712500002	C.56
WSM 10 3	1712500003	C.56
WSM 10 4	1712500004	C.56
WSM 10 5	1712500005	C.56
WSM 10 6	1712500006	C.56
WSM 10 7	1712500007	C.56
WSM 10 8	1712500008	C.56

Type	Order No.	Page
WSM 10 9	1712500009	C.56
WSM 10 A	1712501637	C.56
WSM 10 Ä	1712501054	C.56
WSM 10 Å	1712501700	C.56
WSM 10 Æ	1712501672	C.56
WSM 10 B	1712501639	C.56
WSM 10 C	1712501641	C.56
WSM 10 D	1712501643	C.56
WSM 10 E	1712501645	C.56
WSM 10 ERDE	1712501053	C.56
WSM 10 F	1712501647	C.56
WSM 10 G	1712501649	C.56
WSM 10 H	1712501651	C.56
WSM 10 I	1712501653	C.56
WSM 10 J	1712501655	C.56
WSM 10 K	1712501657	C.56
WSM 10 L	1712501659	C.56
WSM 10 M	1712501661	C.56
WSM 10 N	1712501663	C.56
WSM 10 NEUTRAL	1712502000	C.56
WSM 10 O	1712501665	C.56
WSM 10 Ö	1712501055	C.56
WSM 10 Ø	1712501670	C.56
WSM 10 P	1712501667	C.56
WSM 10 Q	1712501669	C.56
WSM 10 R	1712501671	C.56
WSM 10 S	1712501673	C.56
WSM 10 T	1712501676	C.56
WSM 10 U	1712501679	C.56
WSM 10 Ü	1712501699	C.56
WSM 10 V	1712501681	C.56
WSM 10 W	1712501683	C.56
WSM 10 X	1712501687	C.56
WSM 10 Y	1712501696	C.56
WSM 10 Z	1712501698	C.56
WSM SERVICE BOX KOMP.	1924930000	C.56
WSM TOOL AUTOMATIK	1774470000	C.57
WSM TOOL MANUELL	1774480000	C.57
WSMC 11-15	1891670000	C.57
WSMC 1-5	1912170000	C.57
WSMC 16-20	1912140000	C.57
WSMC 21-25	1912150000	C.57
WSMC 26-30	1912160000	C.57
WSMC 6-10	1891680000	C.57
WSMH 108mm	1774530000	C.57
WSMH 288mm	1774490000	C.57
WSMH 48mm	1774500000	C.57
WSMH 60mm	1774510000	C.57
WSMH 84mm	1774520000	C.57

Z

ZGB 15	1636530000	B.39
ZGB 30	1611930000	B.39
ZS 10/5 MC BEDRUCKT	1610010000	B.15
ZS 10/5 MC NEUTRAL	1610000000	B.15
ZS 12/6 BEDRUCKT	1610030000	B.15
ZS 12/6 MC NEUTRAL	1610020000	B.15
ZS 15/5 MC BEDRUCKT	1646640000	B.15
ZS 15/5 MC NEUTRAL	1646630000	B.15

Order No.	Type	Page
0130000000		
0132660010	DEK 5 FW 10-500	B.7
0132961021	DEK 5 GS A	B.7
0132961022	DEK 5 GS B	B.7
0132961023	DEK 5 GS C	B.7
0132961024	DEK 5 GS D	B.7
0132961025	DEK 5 GS E	B.7
0132961026	DEK 5 GS F	B.7
0132961027	DEK 5 GS G	B.7
0132961028	DEK 5 GS H	B.7
0132961029	DEK 5 GS I	B.7
0132961030	DEK 5 GS J	B.7
0132961031	DEK 5 GS K	B.7
0132961032	DEK 5 GS L	B.7
0132961033	DEK 5 GS M	B.7
0132961034	DEK 5 GS N	B.7
0132961035	DEK 5 GS O	B.7
0132961036	DEK 5 GS P	B.7
0132961037	DEK 5 GS Q	B.7
0132961038	DEK 5 GS R	B.7
0132961039	DEK 5 GS S	B.7
0132961040	DEK 5 GS T	B.7
0132961041	DEK 5 GS U	B.7
0132961042	DEK 5 GS V	B.7
0132961043	DEK 5 GS W	B.7
0132961044	DEK 5 GS X	B.7
0132961045	DEK 5 GS Y	B.7
0132961046	DEK 5 GS Z	B.7
0133161114	DEK 5 FW U1-PE1	B.7
0133161115	DEK 5 FW U2-PE2	B.7
0133161116	DEK 5 FW U3-PE3	B.7
0133161117	DEK 5 FW U4-PE4	B.7
0133161118	DEK 5 FW U5-PE5	B.7
0133161119	DEK 5 FW U6-PE6	B.7
0133161120	DEK 5 FW U7-PE7	B.7
0133161121	DEK 5 FW U8-PE8	B.7
0133161122	DEK 5 FW U9-PE9	B.7
0133261150	DEK 5 FW X1-Z1	B.7
0133261151	DEK 5 FW X2-Z2	B.7
0133261152	DEK 5 FW X3-Z3	B.7
0133261153	DEK 5 FW X4-Z4	B.7
0133261154	DEK 5 FW X5-Z5	B.7
0133261155	DEK 5 FW X6-Z6	B.7
0133261156	DEK 5 FW X7-Z7	B.7
0133261157	DEK 5 FW X8-Z8	B.7
0133261158	DEK 5 FW X9-Z9	B.7
0133261159	DEK 5 FW X10-Z10	B.7
0133360001	DEK 6 FSZ 1-10	B.8
0133360011	DEK 6 FSZ 11-20	B.8
0133360021	DEK 6 FSZ 21-30	B.8
0133360031	DEK 6 FSZ 31-40	B.8
0133360041	DEK 6 FSZ 41-50	B.8
0133360051	DEK 6 FSZ 51-60	B.8
0133360061	DEK 6 FSZ 61-70	B.8
0133360071	DEK 6 FSZ 71-80	B.8
0133360081	DEK 6 FSZ 81-90	B.8
0133360091	DEK 6 FSZ 91-100	B.8
0138900000	SCHS 1 SCHWARZ	D.5
0139000000	ESO/SCHS1 500X12,5X0,3	D.5
0139200000	STR F.SCHS	D.5
0150000000		
0157261187	DEK 5 GS PE	B.7
0157261202	DEK 5 GS ERDE	B.7
0157261203	DEK 5 GS ERDE IM KREIS	B.7
0170000000		
0171111044	CLI C 1-3 WS NE MP	C.21
0171111686	CLI C 1-3 RT NE MP	C.21
0171111687	CLI C 1-3 GE NE MP	C.21
0171111688	CLI C 1-3 GN NE MP	C.21
0171111691	CLI C 1-3 GR NE MP	C.21
0171111693	CLI C 1-3 BL NE MP	C.21
0171301044	CLI C 2-4 WS NE CD	C.21
0171301686	CLI C 2-4 RT NE CD	C.21
0171301687	CLI C 2-4 GE NE CD	C.21
0171301688	CLI C 2-4 GN NE CD	C.21
0171301689	CLI C 2-4 VI NE CD	C.21
0171301690	CLI C 2-4 OR NE CD	C.21
0171301691	CLI C 2-4 GR NE CD	C.21
0171301692	CLI C 2-4 BR NE CD	C.21
0171301693	CLI C 2-4 BL NE CD	C.21
0171301694	CLI C 2-4 SW NE CD	C.21
0171310000	CLI C 2-4 GE NE MP	C.21
0180000000		
0189400000	CLI MH 110 HSTR	C.52
0210000000		
0213811044	CLI C 02-3 WS NE MP	C.20
0213811686	CLI C 02-3 RT NE MP	C.20
0213811687	CLI C 02-3 GE NE MP	C.20
0213811693	CLI C 02-3 BL NE MP	C.20

Order No.	Type	Page
0230000000		
0235860000	DEK 5 FWZ 1,3,5-19	B.7
0235960000	DEK 5 FWZ 21,23,25-39	B.7
0236060000	DEK 5 FWZ 41,43,45-59	B.7
0236160000	DEK 5 FWZ 2,4,6-20	B.7
0236260000	DEK 5 FWZ 22,24,26-40	B.7
0236360000	DEK 5 FWZ 42,44,46-60	B.7
0240000000		
0240011044	CLI C 3-6 WS NE MP	C.22
0240011686	CLI C 3-6 RT NE MP	C.22
0240011687	CLI C 3-6 GE NE MP	C.22
0240011688	CLI C 3-6 GN NE MP	C.22
0240011689	CLI C 3-6 VI NE MP	C.22
0240011690	CLI C 3-6 OR NE MP	C.22
0240011691	CLI C 3-6 GR NE MP	C.22
0240011692	CLI C 3-6 BR NE MP	C.22
0240011693	CLI C 3-6 BL NE MP	C.22
0240011694	CLI C 3-6 SW NE MP	C.22
0250000000		
0251310001	CLI C 2-4 WS/SW 1 MP	C.38
0251310002	CLI C 2-4 WS/SW 2 MP	C.38
0251310003	CLI C 2-4 WS/SW 3 MP	C.38
0251310004	CLI C 2-4 WS/SW 4 MP	C.38
0251310005	CLI C 2-4 WS/SW 5 MP	C.38
0251310006	CLI C 2-4 WS/SW 6 MP	C.38
0251310007	CLI C 2-4 WS/SW 7 MP	C.38
0251310008	CLI C 2-4 WS/SW 8 MP	C.38
0251310009	CLI C 2-4 WS/SW 9 MP	C.26
0251310009	CLI C 2-4 WS/SW 9 MP	C.38
0251311000	CLI C 2-4 WS/SW 0 MP	C.38
0251311021	CLI C 2-4 WS/SW A MP	C.38
0251311022	CLI C 2-4 WS/SW B MP	C.38
0251311023	CLI C 2-4 WS/SW C MP	C.38
0251311024	CLI C 2-4 WS/SW D MP	C.38
0251311025	CLI C 2-4 WS/SW E MP	C.38
0251311026	CLI C 2-4 WS/SW F MP	C.38
0251311027	CLI C 2-4 WS/SW G MP	C.38
0251311028	CLI C 2-4 WS/SW H MP	C.38
0251311029	CLI C 2-4 WS/SW I MP	C.38
0251311030	CLI C 2-4 WS/SW J MP	C.38
0251311031	CLI C 2-4 WS/SW K MP	C.38
0251311032	CLI C 2-4 WS/SW L MP	C.38
0251311033	CLI C 2-4 WS/SW M MP	C.38
0251311034	CLI C 2-4 WS/SW N MP	C.38
0251311035	CLI C 2-4 WS/SW O MP	C.38
0251311036	CLI C 2-4 WS/SW P MP	C.38
0251311037	CLI C 2-4 WS/SW Q MP	C.38
0251311038	CLI C 2-4 WS/SW R MP	C.38
0251311039	CLI C 2-4 WS/SW S MP	C.38
0251311040	CLI C 2-4 WS/SW T MP	C.38
0251311041	CLI C 2-4 WS/SW U MP	C.38
0251311042	CLI C 2-4 WS/SW V MP	C.38
0251311043	CLI C 2-4 WS/SW W MP	C.38
0251311044	CLI C 2-4 WS/SW X MP	C.38
0251311045	CLI C 2-4 WS/SW Y MP	C.38
0251311046	CLI C 2-4 WS/SW Z MP	C.38
0251311047	CLI C 2-4 WS/SW . MP	C.39
0251311048	CLI C 2-4 WS/SW + MP	C.39
0251311049	CLI C 2-4 WS/SW - MP	C.39
0251311050	CLI C 2-4 WS/SW / MP	C.39
0251311051	CLI C 2-4 WS/SW : MP	C.39
0251311052	CLI C 2-4 WS/SW = MP	C.39
0251311053	CLI C 2-4 WS/SW ET MP	C.39
0251311055	CLI C 2-4 WS/SW Å MP	C.39
0251311056	CLI C 2-4 WS/SW Ä MP	C.39
0251311057	CLI C 2-4 WS/SW Ö MP	C.39
0251311058	CLI C 2-4 WS/SW PET. MP	C.39
0251311059	CLI C 2-4 WS/SW AC MP	C.39
0251311060	CLI C 2-4 WS NE MP	C.21
0251311502	CLI C 2-4 GE/SW 0 MP	C.38
0251311503	CLI C 2-4 SW/WS 0 MP	C.26
0251311505	CLI C 2-4 GE/SW 1 MP	C.38
0251311506	CLI C 2-4 BR/WS 1 MP	C.26
0251311508	CLI C 2-4 GE/SW 2 MP	C.38
0251311509	CLI C 2-4 RT/SW 2 MP	C.26
0251311511	CLI C 2-4 GE/SW 3 MP	C.38
0251311512	CLI C 2-4 OR/SW 3 MP	C.26
0251311514	CLI C 2-4 GE/SW 4 MP	C.26
0251311514	CLI C 2-4 GE/SW 4 MP	C.38
0251311517	CLI C 2-4 GE/SW 5 MP	C.38
0251311518	CLI C 2-4 GN/SW 5 MP	C.26
0251311520	CLI C 2-4 GE/SW 6 MP	C.38
0251311521	CLI C 2-4 BL/SW 6 MP	C.26
0251311523	CLI C 2-4 GE/SW 7 MP	C.38
0251311524	CLI C 2-4 VI/SW 7 MP	C.26
0251311526	CLI C 2-4 GE/SW 8 MP	C.38
0251311527	CLI C 2-4 GR/SW 8 MP	C.26
0251311527	CLI C 2-4 GR/SW 8 MP	C.38
0251311529	CLI C 2-4 GE/SW 9 MP	C.38
0251311637	CLI C 2-4 GE/SW A MP	C.38
0251311639	CLI C 2-4 GE/SW B MP	C.38
0251311641	CLI C 2-4 GE/SW C MP	C.38
0251311643	CLI C 2-4 GE/SW D MP	C.38
0251311645	CLI C 2-4 GE/SW E MP	C.38
0251311647	CLI C 2-4 GE/SW F MP	C.38

Order No.	Type	Page
0251311649	CLI C 2-4 GE/SW G MP	C.38
0251311651	CLI C 2-4 GE/SW H MP	C.38
0251311653	CLI C 2-4 GE/SW I MP	C.38
0251311655	CLI C 2-4 GE/SW J MP	C.38
0251311657	CLI C 2-4 GE/SW K MP	C.38
0251311659	CLI C 2-4 GE/SW L MP	C.38
0251311661	CLI C 2-4 GE/SW M MP	C.38
0251311663	CLI C 2-4 GE/SW N MP	C.38
0251311664	CLI C 2-4 BL/SW N MP	C.39
0251311665	CLI C 2-4 GE/SW O MP	C.38
0251311667	CLI C 2-4 GE/SW P MP	C.38
0251311669	CLI C 2-4 GE/SW Q MP	C.38
0251311671	CLI C 2-4 GE/SW R MP	C.38
0251311673	CLI C 2-4 GE/SW S MP	C.38
0251311676	CLI C 2-4 GE/SW T MP	C.38
0251311679	CLI C 2-4 GE/SW U MP	C.38
0251311681	CLI C 2-4 GE/SW V MP	C.38
0251311683	CLI C 2-4 GE/SW W MP	C.38
0251311687	CLI C 2-4 GE/SW X MP	C.38
0251311695	CLI C 2-4 GE/SW Ö MP	C.39
0251311696	CLI C 2-4 GE/SW Y MP	C.38
0251311697	CLI C 2-4 GE/SW Ä MP	C.39
0251311698	CLI C 2-4 GE/SW Z MP	C.38
0251311699	CLI C 2-4 GE/SW Å MP	C.39
0251311735	CLI C 2-4 GE/SW Æ MP	C.39
0251311736	CLI C 2-4 GE/SW Ø MP	C.39
0251311737	CLI C 2-4 RT/SW + MP	C.39
0251311738	CLI C 2-4 GE/SW + MP	C.39
0251311740	CLI C 2-4 GE/SW - MP	C.39
0251311741	CLI C 2-4 BL/SW - MP	C.39
0251311742	CLI C 2-4 GE/SW / MP	C.39
0251311746	CLI C 2-4 GE/SW ET MP	C.39
0251311747	CLI C 2-4 GE/SW PET. MP	C.39
0251311748	CLI C 2-4 GE/SW . MP	C.39
0251311750	CLI C 2-4 GE/SW : MP	C.39
0251311751	CLI C 2-4 GE/SW = MP	C.39
0251311752	CLI C 2-4 GE/SW AC MP	C.39
0252110001	CLI C 02-3 WS/SW 1 MP	C.29
0252110002	CLI C 02-3 WS/SW 2 MP	C.29
0252110003	CLI C 02-3 WS/SW 3 MP	C.29
0252110004	CLI C 02-3 WS/SW 4 MP	C.29
0252110005	CLI C 02-3 WS/SW 5 MP	C.29
0252110006	CLI C 02-3 WS/SW 6 MP	C.29
0252110007	CLI C 02-3 WS/SW 7 MP	C.29
0252110008	CLI C 02-3 WS/SW 8 MP	C.29
0252111000	CLI C 02-3 WS/SW 0 MP	C.29
0252111502	CLI C 02-3 GE/SW 0 MP	C.29
0252111503	CLI C 02-3 SW/WS 0 MP	C.26
0252111505	CLI C 02-3 GE/SW 1 MP	C.29
0252111506	CLI C 02-3 BR/WS 1 MP	C.26
0252111508	CLI C 02-3 GE/SW 2 MP	C.29
0252111509	CLI C 02-3 RT/SW 2 MP	C.26
0252111511	CLI C 02-3 GE/SW 3 MP	C.29
0252111512	CLI C 02-3 OR/SW 3 MP	C.26
0252111514	CLI C 02-3 GE/SW 4 MP	C.26
0252111514	CLI C 02-3 GE/SW 4 MP	C.29
0252111517	CLI C 02-3 GE/SW 5 MP	C.29
0252111518	CLI C 02-3 GN/SW 5 MP	C.26
0252111520	CLI C 02-3 GE/SW 6 MP	C.29
0252111521	CLI C 02-3 BL/SW 6 MP	C.26
0252111523	CLI C 02-3 GE/SW 7 MP	C.29
0252111524	CLI C 02-3 VI/SW 7 MP	C.26
0252111526	CLI C 02-3 GE/SW 8 MP	C.29
0252111527	CLI C 02-3 GR/SW 8 MP	C.26
0252111527	CLI C 02-3 GR/SW 8 MP	C.29
0252111529	CLI C 02-3 GE/SW 9 MP	C.29
0252111530	CLI C 02-3 WS/SW 9 MP	C.26
0252111530	CLI C 02-3 WS/SW 9 MP	C.29
0252111637	CLI C 02-3 GE/SW A MP	C.29
0252111639	CLI C 02-3 GE/SW B MP	C.29
0252111641	CLI C 02-3 GE/SW C MP	C.29
0252111643	CLI C 02-3 GE/SW D MP	C.29
0252111645	CLI C 02-3 GE/SW E MP	C.29
0252111647	CLI C 02-3 GE/SW F MP	C.29
0252111649	CLI C 02-3 GE/SW G MP	C.29
0252111651	CLI C 02-3 GE/SW H MP	C.29
0252111653	CLI C 02-3 GE/SW I MP	C.29
0252111655	CLI C 02-3 GE/SW J MP	C.29
0252111657	CLI C 02-3 GE/SW K MP	C.29
0252111659	CLI C 02-3 GE/SW L MP	C.29
0252111661	CLI C 02-3 GE/SW M MP	C.29
0252111663	CLI C 02-3 GE/SW N MP	C.29
0252111664	CLI C 02-3 BL/SW N MP	C.30
0252111665	CLI C 02-3 GE/SW O MP	C.29
0252111667	CLI C 02-3 GE/SW P MP	C.29
0252111669	CLI C 02-3 GE/SW Q MP	C.29
0252111671	CLI C 02-3 GE/SW R MP	C.29
0252111673	CLI C 02-3 GE/SW S MP	C.29
0252111676	CLI C 02-3 GE/SW T MP	C.29
0252111679	CLI C 02-3 GE/SW U MP	C.29
0252111681	CLI C 02-3 GE/SW V MP	C.29
0252111683	CLI C 02-3 GE/SW W MP	C.29
0252111687	CLI C 02-3 GE/SW X MP	C.29
0252111695	CLI C 02-3 GE/SW Ö MP	C.30
0252111696	CLI C 02-3 GE/SW Y MP	C.29
0252111697	CLI C 02-3 GE/SW Ä MP	C.30
0252111698	CLI C 02-3 GE/SW Z MP	C.29
0252111699	CLI C 02-3 GE/SW Å MP	C.30
0252111700	CLI C 02-3 GE/SW a MP	C.30
0252111701	CLI C 02-3 GE/SW b MP	C.30

Order No.	Type	Page
0252111702	CLI C 02-3 GE/SW c MP	C.30
0252111703	CLI C 02-3 GE/SW d MP	C.30
0252111704	CLI C 02-3 GE/SW e MP	C.30
0252111705	CLI C 02-3 GE/SW f MP	C.30
0252111706	CLI C 02-3 GE/SW g MP	C.30
0252111707	CLI C 02-3 GE/SW h MP	C.30
0252111708	CLI C 02-3 GE/SW i MP	C.30
0252111709	CLI C 02-3 GE/SW j MP	C.30
0252111710	CLI C 02-3 GE/SW k MP	C.30
0252111711	CLI C 02-3 GE/SW l MP	C.30
0252111712	CLI C 02-3 GE/SW m MP	C.30
0252111713	CLI C 02-3 GE/SW n MP	C.30
0252111714	CLI C 02-3 GE/SW o MP	C.30
0252111715	CLI C 02-3 GE/SW p MP	C.30
0252111716	CLI C 02-3 GE/SW q MP	C.30
0252111717	CLI C 02-3 GE/SW r MP	C.30
0252111718	CLI C 02-3 GE/SW s MP	C.30
0252111719	CLI C 02-3 GE/SW t MP	C.30
0252111720	CLI C 02-3 GE/SW u MP	C.30
0252111721	CLI C 02-3 GE/SW v MP	C.30
0252111722	CLI C 02-3 GE/SW w MP	C.30
0252111723	CLI C 02-3 GE/SW x MP	C.30
0252111724	CLI C 02-3 GE/SW y MP	C.30
0252111725	CLI C 02-3 GE/SW z MP	C.30
0252111726	CLI C 02-6 GE/SW A1 MP	C.31
0252111727	CLI C 02-6 GE/SW A2 MP	C.31
0252111728	CLI C 02-6 GE/SW L1 MP	C.31
0252111729	CLI C 02-6 GE/SW L2 MP	C.31
0252111730	CLI C 02-6 GE/SW L3 MP	C.31
0252111734	CLI C 02-9 GE/SW PEN MP	C.31
0252111737	CLI C 02-3 RT/SW + MP	C.30
0252111738	CLI C 02-3 GE/SW + MP	C.30
0252111740	CLI C 02-3 GE/SW - MP	C.30
0252111741	CLI C 02-3 BL/SW - MP	C.30
0252111742	CLI C 02-3 GE/SW / MP	C.30
0252111746	CLI C 02-3 GE/SW ET MP	C.30
0252111747	CLI C 02-3 GE/SW PET. MP	C.30
0252111748	CLI C 02-3 GE/SW . MP	C.30
0252111750	CLI C 02-3 GE/SW : MP	C.30
0252111751	CLI C 02-3 GE/SW = MP	C.30
0252111752	CLI C 02-3 GE/SW AC MP	C.30
0252509999	CLI C 02-15 SDR SG	C.23
0252610001	CLI C 1-3 WS/SW 1 MP	C.32
0252610002	CLI C 1-3 WS/SW 2 MP	C.32
0252610003	CLI C 1-3 WS/SW 3 MP	C.32
0252610004	CLI C 1-3 WS/SW 4 MP	C.32
0252610005	CLI C 1-3 WS/SW 5 MP	C.32
0252610006	CLI C 1-3 WS/SW 6 MP	C.32
0252610007	CLI C 1-3 WS/SW 7 MP	C.32
0252610008	CLI C 1-3 WS/SW 8 MP	C.32
0252611000	CLI C 1-3 WS/SW 0 MP	C.32
0252611021	CLI C 1-3 WS/SW A MP	C.32
0252611022	CLI C 1-3 WS/SW B MP	C.32
0252611023	CLI C 1-3 WS/SW C MP	C.32
0252611024	CLI C 1-3 WS/SW D MP	C.32
0252611025	CLI C 1-3 WS/SW E MP	C.32
0252611026	CLI C 1-3 WS/SW F MP	C.32
0252611027	CLI C 1-3 WS/SW G MP	C.32
0252611028	CLI C 1-3 WS/SW H MP	C.32
0252611029	CLI C 1-3 WS/SW I MP	C.32
0252611030	CLI C 1-3 WS/SW J MP	C.32
0252611031	CLI C 1-3 WS/SW K MP	C.32
0252611032	CLI C 1-3 WS/SW L MP	C.32
0252611033	CLI C 1-3 WS/SW M MP	C.32
0252611034	CLI C 1-3 WS/SW N MP	C.32
0252611035	CLI C 1-3 WS/SW O MP	C.32
0252611036	CLI C 1-3 WS/SW P MP	C.32
0252611037	CLI C 1-3 WS/SW Q MP	C.32
0252611038	CLI C 1-3 WS/SW R MP	C.32
0252611039	CLI C 1-3 WS/SW S MP	C.32
0252611040	CLI C 1-3 WS/SW T MP	C.32
0252611041	CLI C 1-3 WS/SW U MP	C.32
0252611042	CLI C 1-3 WS/SW V MP	C.32
0252611043	CLI C 1-3 WS/SW W MP	C.32
0252611044	CLI C 1-3 WS/SW X MP	C.32
0252611045	CLI C 1-3 WS/SW Y MP	C.32
0252611046	CLI C 1-3 WS/SW Z MP	C.32
0252611047	CLI C 1-3 WS/SW . MP	C.34
0252611048	CLI C 1-3 WS/SW + MP	C.34
0252611049	CLI C 1-3 WS/SW - MP	C.34
0252611050	CLI C 1-3 WS/SW / MP	C.34
0252611051	CLI C 1-3 WS/SW : MP	C.34
0252611052	CLI C 1-3 WS/SW = MP	C.34
0252611053	CLI C 1-3 WS/SW ET MP	C.34
0252611055	CLI C 1-3 WS/SW Å MP	C.34
0252611056	CLI C 1-3 WS/SW Ä MP	C.34
0252611057	CLI C 1-3 WS/SW Ö MP	C.34
0252611058	CLI C 1-3 WS/SW PET. MP	C.34
0252611059	CLI C 1-3 WS/SW AC MP	C.34
0252611502	CLI C 1-3 GE/SW 0 MP	C.32
0252611503	CLI C 1-3 SW/WS 0 MP	C.26
0252611503	CLI C 1-3 SW/WS 0 MP	C.32
0252611505	CLI C 1-3 GE/SW 1 MP	C.32
0252611506	CLI C 1-3 BR/WS 1 MP	C.26
0252611508	CLI C 1-3 GE/SW 2 MP	C.32
0252611509	CLI C 1-3 RT/SW 2 MP	C.26
0252611511	CLI C 1-3 GE/SW 3 MP	C.32
0252611512	CLI C 1-3 OR/SW 3 MP	C.26
0252611514	CLI C 1-3 GE/SW 4 MP	C.26
0252611514	CLI C 1-3 GE/SW 4 MP	C.32

Order No.	Type	Page
0252611517	CLI C 1-3 GE/SW 5 MP	C.32
0252611518	CLI C 1-3 GN/SW 5 MP	C.26
0252611520	CLI C 1-3 GE/SW 6 MP	C.32
0252611521	CLI C 1-3 BL/SW 6 MP	C.26
0252611523	CLI C 1-3 GE/SW 7 MP	C.32
0252611524	CLI C 1-3 VI/SW 7 MP	C.26
0252611526	CLI C 1-3 GE/SW 8 MP	C.32
0252611527	CLI C 1-3 GR/SW 8 MP	C.26
0252611527	CLI C 1-3 GR/SW 8 MP	C.32
0252611529	CLI C 1-3 GE/SW 9 MP	C.32
0252611530	CLI C 1-3 WS/SW 9 MP	C.26
0252611530	CLI C 1-3 WS/SW 9 MP	C.32
0252611637	CLI C 1-3 GE/SW A MP	C.32
0252611639	CLI C 1-3 GE/SW B MP	C.32
0252611641	CLI C 1-3 GE/SW C MP	C.32
0252611643	CLI C 1-3 GE/SW D MP	C.32
0252611645	CLI C 1-3 GE/SW E MP	C.32
0252611647	CLI C 1-3 GE/SW F MP	C.32
0252611649	CLI C 1-3 GE/SW G MP	C.32
0252611651	CLI C 1-3 GE/SW H MP	C.32
0252611653	CLI C 1-3 GE/SW I MP	C.32
0252611655	CLI C 1-3 GE/SW J MP	C.32
0252611657	CLI C 1-3 GE/SW K MP	C.32
0252611659	CLI C 1-3 GE/SW L MP	C.32
0252611661	CLI C 1-3 GE/SW M MP	C.32
0252611663	CLI C 1-3 GE/SW N MP	C.32
0252611664	CLI C 1-3 BL/SW N MP	C.34
0252611665	CLI C 1-3 GE/SW O MP	C.32
0252611667	CLI C 1-3 GE/SW P MP	C.32
0252611669	CLI C 1-3 GE/SW Q MP	C.32
0252611671	CLI C 1-3 GE/SW R MP	C.32
0252611673	CLI C 1-3 GE/SW S MP	C.32
0252611676	CLI C 1-3 GE/SW T MP	C.32
0252611679	CLI C 1-3 GE/SW U MP	C.32
0252611681	CLI C 1-3 GE/SW V MP	C.32
0252611683	CLI C 1-3 GE/SW W MP	C.32
0252611687	CLI C 1-3 GE/SW X MP	C.32
0252611695	CLI C 1-3 GE/SW Ö MP	C.34
0252611696	CLI C 1-3 GE/SW Y MP	C.32
0252611697	CLI C 1-3 GE/SW Ä MP	C.34
0252611698	CLI C 1-3 GE/SW Z MP	C.32
0252611699	CLI C 1-3 GE/SW Å MP	C.34
0252611700	CLI C 1-3 GE/SW a MP	C.33
0252611701	CLI C 1-3 GE/SW b MP	C.33
0252611702	CLI C 1-3 GE/SW c MP	C.33
0252611703	CLI C 1-3 GE/SW d MP	C.33
0252611704	CLI C 1-3 GE/SW e MP	C.33
0252611705	CLI C 1-3 GE/SW f MP	C.33
0252611706	CLI C 1-3 GE/SW g MP	C.33
0252611707	CLI C 1-3 GE/SW h MP	C.33
0252611708	CLI C 1-3 GE/SW i MP	C.33
0252611709	CLI C 1-3 GE/SW j MP	C.33
0252611710	CLI C 1-3 GE/SW k MP	C.33
0252611711	CLI C 1-3 GE/SW l MP	C.33
0252611712	CLI C 1-3 GE/SW m MP	C.33
0252611713	CLI C 1-3 GE/SW n MP	C.33
0252611714	CLI C 1-3 GE/SW o MP	C.33
0252611715	CLI C 1-3 GE/SW p MP	C.33
0252611716	CLI C 1-3 GE/SW q MP	C.33
0252611717	CLI C 1-3 GE/SW r MP	C.33
0252611718	CLI C 1-3 GE/SW s MP	C.33
0252611719	CLI C 1-3 GE/SW t MP	C.33
0252611720	CLI C 1-3 GE/SW u MP	C.33
0252611721	CLI C 1-3 GE/SW v MP	C.33
0252611722	CLI C 1-3 GE/SW w MP	C.33
0252611723	CLI C 1-3 GE/SW x MP	C.33
0252611724	CLI C 1-3 GE/SW y MP	C.33
0252611725	CLI C 1-3 GE/SW z MP	C.33
0252611737	CLI C 1-3 RT/SW + MP	C.34
0252611738	CLI C 1-3 GE/SW + MP	C.34
0252611740	CLI C 1-3 GE/SW - MP	C.34
0252611741	CLI C 1-3 BL/SW - MP	C.34
0252611742	CLI C 1-3 GE/SW / MP	C.34
0252611746	CLI C 1-3 GE/SW ET MP	C.34
0252611747	CLI C 1-3 GE/SW PET. MP	C.34
0252611748	CLI C 1-3 GE/SW . MP	C.34
0252611750	CLI C 1-3 GE/SW : MP	C.34
0252611751	CLI C 1-3 GE/SW = MP	C.34
0252611752	CLI C 1-3 GE/SW AC MP	C.34
0252709999	CLI C 1-6 SDR CD	C.23
0252711522	CLI C 1-6 GE/SW 01 MP	C.35
0252711523	CLI C 1-6 GE/SW 02 MP	C.35
0252711524	CLI C 1-6 GE/SW 03 MP	C.35
0252711525	CLI C 1-6 GE/SW 04 MP	C.35
0252711526	CLI C 1-6 GE/SW 05 MP	C.35
0252711527	CLI C 1-6 GE/SW 06 MP	C.35
0252711528	CLI C 1-6 GE/SW 07 MP	C.35
0252711529	CLI C 1-6 GE/SW 08 MP	C.35
0252711530	CLI C 1-6 GE/SW 09 MP	C.35
0252711531	CLI C 1-6 GE/SW 10 MP	C.35
0252711532	CLI C 1-6 GE/SW 11 MP	C.35
0252711533	CLI C 1-6 GE/SW 12 MP	C.35
0252711534	CLI C 1-6 GE/SW 13 MP	C.35
0252711535	CLI C 1-6 GE/SW 14 MP	C.35
0252711536	CLI C 1-6 GE/SW 15 MP	C.35
0252711537	CLI C 1-6 GE/SW 16 MP	C.35
0252711538	CLI C 1-6 GE/SW 17 MP	C.35
0252711539	CLI C 1-6 GE/SW 18 MP	C.35
0252711540	CLI C 1-6 GE/SW 19 MP	C.35
0252711541	CLI C 1-6 GE/SW 20 MP	C.35
0252711542	CLI C 1-6 GE/SW 21 MP	C.35
0252711543	CLI C 1-6 GE/SW 22 MP	C.35
0252711544	CLI C 1-6 GE/SW 23 MP	C.35
0252711545	CLI C 1-6 GE/SW 24 MP	C.35
0252711546	CLI C 1-6 GE/SW 25 MP	C.35
0252711547	CLI C 1-6 GE/SW 26 MP	C.35
0252711548	CLI C 1-6 GE/SW 27 MP	C.35
0252711549	CLI C 1-6 GE/SW 28 MP	C.35
0252711550	CLI C 1-6 GE/SW 29 MP	C.35
0252711551	CLI C 1-6 GE/SW 30 MP	C.35
0252711552	CLI C 1-6 GE/SW 31 MP	C.35
0252711553	CLI C 1-6 GE/SW 32 MP	C.35
0252711554	CLI C 1-6 GE/SW 33 MP	C.35
0252711555	CLI C 1-6 GE/SW 34 MP	C.35
0252711556	CLI C 1-6 GE/SW 35 MP	C.35
0252711557	CLI C 1-6 GE/SW 36 MP	C.35
0252711558	CLI C 1-6 GE/SW 37 MP	C.35
0252711559	CLI C 1-6 GE/SW 38 MP	C.35
0252711560	CLI C 1-6 GE/SW 39 MP	C.35
0252711561	CLI C 1-6 GE/SW 40 MP	C.35
0252711562	CLI C 1-6 GE/SW 41 MP	C.35
0252711563	CLI C 1-6 GE/SW 42 MP	C.35
0252711564	CLI C 1-6 GE/SW 43 MP	C.35
0252711565	CLI C 1-6 GE/SW 44 MP	C.35
0252711566	CLI C 1-6 GE/SW 45 MP	C.35
0252711567	CLI C 1-6 GE/SW 46 MP	C.35
0252711568	CLI C 1-6 GE/SW 47 MP	C.35
0252711569	CLI C 1-6 GE/SW 48 MP	C.35
0252711570	CLI C 1-6 GE/SW 49 MP	C.35
0252711571	CLI C 1-6 GE/SW 50 MP	C.35
0252711572	CLI C 1-6 GE/SW 51 MP	C.35
0252711573	CLI C 1-6 GE/SW 52 MP	C.35
0252711574	CLI C 1-6 GE/SW 53 MP	C.35
0252711575	CLI C 1-6 GE/SW 54 MP	C.35
0252711576	CLI C 1-6 GE/SW 55 MP	C.35
0252711577	CLI C 1-6 GE/SW 56 MP	C.35
0252711578	CLI C 1-6 GE/SW 57 MP	C.35
0252711579	CLI C 1-6 GE/SW 58 MP	C.35
0252711580	CLI C 1-6 GE/SW 59 MP	C.35
0252711581	CLI C 1-6 GE/SW 60 MP	C.35
0252711582	CLI C 1-6 GE/SW 61 MP	C.36
0252711583	CLI C 1-6 GE/SW 62 MP	C.36
0252711584	CLI C 1-6 GE/SW 63 MP	C.36
0252711585	CLI C 1-6 GE/SW 64 MP	C.36
0252711586	CLI C 1-6 GE/SW 65 MP	C.36
0252711587	CLI C 1-6 GE/SW 66 MP	C.36
0252711588	CLI C 1-6 GE/SW 67 MP	C.36
0252711589	CLI C 1-6 GE/SW 68 MP	C.36
0252711590	CLI C 1-6 GE/SW 69 MP	C.36
0252711591	CLI C 1-6 GE/SW 70 MP	C.36
0252711592	CLI C 1-6 GE/SW 71 MP	C.36
0252711593	CLI C 1-6 GE/SW 72 MP	C.36
0252711594	CLI C 1-6 GE/SW 73 MP	C.36
0252711595	CLI C 1-6 GE/SW 74 MP	C.36
0252711596	CLI C 1-6 GE/SW 75 MP	C.36
0252711597	CLI C 1-6 GE/SW 76 MP	C.36
0252711598	CLI C 1-6 GE/SW 77 MP	C.36
0252711599	CLI C 1-6 GE/SW 78 MP	C.36
0252711600	CLI C 1-6 GE/SW 79 MP	C.36
0252711601	CLI C 1-6 GE/SW 80 MP	C.36
0252711602	CLI C 1-6 GE/SW 81 MP	C.36
0252711603	CLI C 1-6 GE/SW 82 MP	C.36
0252711604	CLI C 1-6 GE/SW 83 MP	C.36
0252711605	CLI C 1-6 GE/SW 84 MP	C.36
0252711606	CLI C 1-6 GE/SW 85 MP	C.36
0252711607	CLI C 1-6 GE/SW 86 MP	C.36
0252711608	CLI C 1-6 GE/SW 87 MP	C.36
0252711609	CLI C 1-6 GE/SW 88 MP	C.36
0252711610	CLI C 1-6 GE/SW 89 MP	C.36
0252711611	CLI C 1-6 GE/SW 90 MP	C.36
0252711612	CLI C 1-6 GE/SW 91 MP	C.36
0252711613	CLI C 1-6 GE/SW 92 MP	C.36
0252711614	CLI C 1-6 GE/SW 93 MP	C.36
0252711615	CLI C 1-6 GE/SW 94 MP	C.36
0252711616	CLI C 1-6 GE/SW 95 MP	C.36
0252711617	CLI C 1-6 GE/SW 96 MP	C.36
0252711618	CLI C 1-6 GE/SW 97 MP	C.36
0252711619	CLI C 1-6 GE/SW 98 MP	C.36
0252711620	CLI C 1-6 GE/SW 99 MP	C.36
0252711726	CLI C 1-6 GE/SW A1 MP	C.37
0252711727	CLI C 1-6 GE/SW A2 MP	C.37
0252711728	CLI C 1-6 GE/SW L1 MP	C.37
0252711729	CLI C 1-6 GE/SW L2 MP	C.37
0252711730	CLI C 1-6 GE/SW L3 MP	C.37
0252711732	CLI C 1-6 BL/SW MP MP	C.37
0252711733	CLI C 1-6 GE/SW PE MP	C.37
0252711734	CLI C 1-9 GE/SW PEN MP	C.37
0252809999	CLI C 1-9 SDR CD	C.23
0253411502	CLI C 3-6 GE/SW 0 MP	C.40
0253411503	CLI C 3-6 SW/WS 0 MP	C.26
0253411505	CLI C 3-6 GE/SW 1 MP	C.40
0253411506	CLI C 3-6 BR/WS 1 MP	C.26
0253411508	CLI C 3-6 GE/SW 2 MP	C.40
0253411509	CLI C 3-6 RT/SW 2 MP	C.26
0253411511	CLI C 3-6 GE/SW 3 MP	C.40
0253411512	CLI C 3-6 OR/SW 3 MP	C.26
0253411514	CLI C 3-6 GE/SW 4 MP	C.26
0253411514	CLI C 3-6 GE/SW 4 MP	C.40
0253411517	CLI C 3-6 GE/SW 5 MP	C.40
0253411518	CLI C 3-6 GN/SW 5 MP	C.26
0253411520	CLI C 3-6 GE/SW 6 MP	C.40
0253411521	CLI C 3-6 BL/SW 6 MP	C.26
0253411523	CLI C 3-6 GE/SW 7 MP	C.40
0253411524	CLI C 3-6 VI/SW 7 MP	C.26
0253411526	CLI C 3-6 GE/SW 8 MP	C.40
0253411527	CLI C 3-6 GR/SW 8 MP	C.26
0253411529	CLI C 3-6 GE/SW 9 MP	C.40
0253411530	CLI C 3-6 WS/SW 9 MP	C.26
0253411530	CLI C 3-6 WS/SW 9 MP	C.40
0253411637	CLI C 3-6 GE/SW A MP	C.40
0253411639	CLI C 3-6 GE/SW B MP	C.40
0253411641	CLI C 3-6 GE/SW C MP	C.40
0253411643	CLI C 3-6 GE/SW D MP	C.40
0253411645	CLI C 3-6 GE/SW E MP	C.40
0253411647	CLI C 3-6 GE/SW F MP	C.40
0253411649	CLI C 3-6 GE/SW G MP	C.40
0253411651	CLI C 3-6 GE/SW H MP	C.40
0253411653	CLI C 3-6 GE/SW I MP	C.40
0253411655	CLI C 3-6 GE/SW J MP	C.40
0253411657	CLI C 3-6 GE/SW K MP	C.40
0253411659	CLI C 3-6 GE/SW L MP	C.40
0253411661	CLI C 3-6 GE/SW M MP	C.40
0253411663	CLI C 3-6 GE/SW N MP	C.40
0253411664	CLI C 3-6 BL/SW N MP	C.41
0253411665	CLI C 3-6 GE/SW O MP	C.40
0253411667	CLI C 3-6 GE/SW P MP	C.40
0253411669	CLI C 3-6 GE/SW Q MP	C.40
0253411671	CLI C 3-6 GE/SW R MP	C.40
0253411673	CLI C 3-6 GE/SW S MP	C.40
0253411676	CLI C 3-6 GE/SW T MP	C.40
0253411679	CLI C 3-6 GE/SW U MP	C.40
0253411681	CLI C 3-6 GE/SW V MP	C.40
0253411683	CLI C 3-6 GE/SW W MP	C.40
0253411687	CLI C 3-6 GE/SW X MP	C.40
0253411695	CLI C 3-6 GE/SW Ö MP	C.40
0253411696	CLI C 3-6 GE/SW Y MP	C.40
0253411697	CLI C 3-6 GE/SW Ä MP	C.40
0253411698	CLI C 3-6 GE/SW Z MP	C.40
0253411699	CLI C 3-6 GE/SW Å MP	C.40
0253411737	CLI C 3-6 RT/SW + MP	C.41
0253411738	CLI C 3-6 GE/SW + MP	C.40
0253411740	CLI C 3-6 GE/SW - MP	C.40
0253411741	CLI C 3-6 BL/SW - MP	C.41
0253411742	CLI C 3-6 GE/SW / MP	C.40
0253411746	CLI C 3-6 GE/SW ET MP	C.40
0253411748	CLI C 3-6 GE/SW . MP	C.40
0253411750	CLI C 3-6 GE/SW : MP	C.40
0253411751	CLI C 3-6 GE/SW = MP	C.40
0253411752	CLI C 3-6 GE/SW AC MP	C.40
0253511726	CLI C 3-9 GE/SW A1 MP	C.41
0253511727	CLI C 3-9 GE/SW A2 MP	C.41
0253511728	CLI C 3-9 GE/SW L1 MP	C.41
0253511729	CLI C 3-9 GE/SW L2 MP	C.41
0253511730	CLI C 3-9 GE/SW L3 MP	C.41
0253511733	CLI C 3-9 GE/SW PE MP	C.41
0253511735	CLI C 3-9 GE/SW SL MP	C.41
0253511750	CLI C 3-9 GE/SW X1 MP	C.41
0253511751	CLI C 3-9 GE/SW X2 MP	C.41
0253511752	CLI C 3-9 GE/SW X3 MP	C.41
0290000000		
0292460000	SCHT 5	B.36
0294000000	STR 5 F.SCHT 5	B.36
0330000000		
0335900000	WSK 12 , LEER	C.53
0336000000	WSK12 m. CLI C 1-3 GE/SW Bez. 0-9	C.53
0337400000	SCHS 2 F.BS SCHILDER	D.5
0350000000		
0354361187	DEK 5 FWZ L1-PE	B.7
0354361203	DEK 5 FWZ L1-EIK	B.7
0400000000		
0407360001	DEK 6,5 FSZ 1-10	B.8
0407360011	DEK 6,5 FSZ 11-20	B.8
0407360021	DEK 6,5 FSZ 21-30	B.8
0407360031	DEK 6,5 FSZ 31-40	B.8
0407360041	DEK 6,5 FSZ 41-50	B.8
0407360051	DEK 6,5 FSZ 51-60	B.8
0407360061	DEK 6,5 FSZ 61-70	B.8
0407360071	DEK 6,5 FSZ 71-80	B.8
0407360081	DEK 6,5 FSZ 81-90	B.8
0407360091	DEK 6,5 FSZ 91-100	B.8
0460000000		
0460660001	DEK 5 FSZ 1-10	B.7
0460660011	DEK 5 FSZ 11-20	B.7
0460660021	DEK 5 FSZ 21-30	B.7
0460660031	DEK 5 FSZ 31-40	B.7
0460660041	DEK 5 FSZ 41-50	B.7
0460660051	DEK 5 FSZ 51-60	B.7
0460660061	DEK 5 FSZ 61-70	B.7
0460660071	DEK 5 FSZ 71-80	B.7
0460660081	DEK 5 FSZ 81-90	B.7
0460660091	DEK 5 FSZ 91-100	B.7
0468060000	DEK 6,5 NEUTRAL	B.8
0468091686	DEK 6,5 RT NEUTRAL	B.8
0468091687	DEK 6,5 GE NEUTRAL	B.8
0468091688	DEK 6,5 GN NEUTRAL	B.8
0468091689	DEK 6,5 VI NEUTRAL	B.8
0468091690	DEK 6,5 OR NEUTRAL	B.8
0468091693	DEK 6,5 BL NEUTRAL	B.8
0468091694	DEK 6,5 SW NEUTRAL	B.8
0468160001	DEK 6,5 FW 1-50	B.8
0468160051	DEK 6,5 FW 51-100	B.8
0468160101	DEK 6,5 FW 101-150	B.8
0468160151	DEK 6,5 FW 151-200	B.8
0468160201	DEK 6,5 FW 201-250	B.8
0468160251	DEK 6,5 FW 251-300	B.8
0468160301	DEK 6,5 FW 301-350	B.8
0468160351	DEK 6,5 FW 351-400	B.8
0468160401	DEK 6,5 FW 401-450	B.8
0468160451	DEK 6,5 FW 451-500	B.8
0468160501	DEK 6,5 FW 501-550	B.8
0468260001	DEK 6,5 FS 1-50	B.8
0468260051	DEK 6,5 FS 51-100	B.8
0468260101	DEK 6,5 FS 101-150	B.8
0468560000	DEK 6 NEUTRAL	B.8
0468591686	DEK 6 RT NEUTRAL	B.8
0468591687	DEK 6 GE NEUTRAL	B.8
0468591688	DEK 6 GN NEUTRAL	B.8
0468591689	DEK 6 VI NEUTRAL	B.8
0468591690	DEK 6 OR NEUTRAL	B.8
0468591691	DEK 6 GR NEUTRAL	B.8
0468591692	DEK 6 BR NEUTRAL	B.8
0468591693	DEK 6 BL NEUTRAL	B.8
0468591694	DEK 6 SW NEUTRAL	B.8
0468660001	DEK 6 FW 1-50	B.8
0468660051	DEK 6 FW 51-100	B.8
0468660101	DEK 6 FW 101-150	B.8
0468660151	DEK 6 FW 151-200	B.8
0468660201	DEK 6 FW 201-250	B.8
0468660251	DEK 6 FW 251-300	B.8
0468660301	DEK 6 FW 301-350	B.8
0468660351	DEK 6 FW 351-400	B.8
0468660401	DEK 6 FW 401-450	B.8
0468660451	DEK 6 FW 451-500	B.8
0468660501	DEK 6 FW 501-550	B.8
0468660551	DEK 6 FW 551-600	B.8
0468660601	DEK 6 FW 601-650	B.8
0468660651	DEK 6 FW 651-700	B.8
0468660701	DEK 6 FW 701-750	B.8
0468660751	DEK 6 FW 751-800	B.8
0468660801	DEK 6 FW 801-850	B.8
0468660851	DEK 6 FW 851-900	B.8
0468660901	DEK 6 FW 901-950	B.8
0468660951	DEK 6 FW 951-999	B.8
0468760001	DEK 6 FS 1-50	B.8
0468760051	DEK 6 FS 51-100	B.8
0468760101	DEK 6 FS 101-150	B.8
0468760151	DEK 6 FS 151-200	B.8
0468760201	DEK 6 FS 201-250	B.8
0468760251	DEK 6 FS 251-300	B.8
0468760301	DEK 6 FS 301-350	B.8
0468760351	DEK 6 FS 351-400	B.8
0468760401	DEK 6 FS 401-450	B.8
0468760451	DEK 6 FS 451-500	B.8
0468760501	DEK 6 FS 501-550	B.8
0468760551	DEK 6 FS 551-600	B.8
0468760601	DEK 6 FS 601-650	B.8
0468760651	DEK 6 FS 651-700	B.8
0468760701	DEK 6 FS 701-750	B.8
0468760751	DEK 6 FS 751-800	B.8
0468760801	DEK 6 FS 801-850	B.8
0468760851	DEK 6 FS 851-900	B.8
0468760901	DEK 6 FS 901-950	B.8
0468760951	DEK 6 FS 951-999	B.8
0470000000		
0473360000	DEK 5 NEUTRAL	B.8
0473391686	DEK 5 RT NEUTRAL	B.8
0473391687	DEK 5 GE NEUTRAL	B.7
0473391688	DEK 5 GN NEUTRAL	B.7
0473391689	DEK 5 VI NEUTRAL	B.8
0473391690	DEK 5 OR NEUTRAL	B.8
0473391691	DEK 5 GR NEUTRAL	B.7
0473391692	DEK 5 BR NEUTRAL	B.7
0473391693	DEK 5 BL NEUTRAL	B.7
0473391694	DEK 5 SW NEUTRAL	B.8
0473460001	DEK 5 FW 1-50	B.7
0473460051	DEK 5 FW 51-100	B.7
0473460101	DEK 5 FW 101-150	B.7
0473460151	DEK 5 FW 151-200	B.7
0473460201	DEK 5 FW 201-250	B.7
0473460251	DEK 5 FW 251-300	B.7
0473460301	DEK 5 FW 301-350	B.7
0473460351	DEK 5 FW 351-400	B.7
0473460401	DEK 5 FW 401-450	B.7
0473460451	DEK 5 FW 451-500	B.7
0473460501	DEK 5 FW 501-550	B.7
0473460551	DEK 5 FW 551-600	B.7
0473460601	DEK 5 FW 601-650	B.7

Order No.	Type	Page
0473460651	DEK 5 FW 651-700	B.7
0473460701	DEK 5 FW 701-750	B.7
0473460751	DEK 5 FW 751-800	B.7
0473460801	DEK 5 FW 801-850	B.7
0473460851	DEK 5 FW 851-900	B.7
0473460901	DEK 5 FW 901-950	B.7
0473460951	DEK 5 FW 951-999	B.7
0473560001	DEK 5 FS 1-50	B.7
0473560051	DEK 5 FS 51-100	B.7
0473560101	DEK 5 FS 101-150	B.7
0473560151	DEK 5 FS 151-200	B.7
0473560201	DEK 5 FS 201-250	B.7
0473560251	DEK 5 FS 251-300	B.7
0473560301	DEK 5 FS 301-350	B.7
0473560351	DEK 5 FS 351-400	B.7
0473560401	DEK 5 FS 401-450	B.7
0473560451	DEK 5 FS 451-500	B.7
0473560501	DEK 5 FS 501-550	B.7
0473560551	DEK 5 FS 551-600	B.7
0473560601	DEK 5 FS 601-650	B.7
0473560651	DEK 5 FS 651-700	B.7
0473560701	DEK 5 FS 701-750	B.7
0473560751	DEK 5 FS 751-800	B.7
0473560801	DEK 5 FS 801-850	B.7
0473560851	DEK 5 FS 851-900	B.7
0473560901	DEK 5 FS 901-950	B.7
0473560951	DEK 5 FS 951-999	B.7

0500000000

0508401694	STI Waterproof schwarz	E.6
0508401694	STI Waterproof schwarz	E.7

0510000000

0515300000	STR 7 F.SCHT 7	B.36
0515300000	STR 7 F.SCHT 7	B.39
0517960000	SCHT 7	B.36
0518960001	DEK 6 FWZ 1-10	B.8
0518960011	DEK 6 FWZ 11-20	B.8
0518960021	DEK 6 FWZ 21-30	B.8
0518960031	DEK 6 FWZ 31-40	B.8
0518960041	DEK 6 FWZ 41-50	B.8
0518960051	DEK 6 FWZ 51-60	B.8
0518960061	DEK 6 FWZ 61-70	B.8
0518960071	DEK 6 FWZ 71-80	B.8
0518960081	DEK 6 FWZ 81-90	B.8
0518960091	DEK 6 FWZ 91-100	B.8
0518960101	DEK 6 FWZ 101-110	B.8
0518960111	DEK 6 FWZ 111-120	B.8
0518960121	DEK 6 FWZ 121-130	B.8
0518960131	DEK 6 FWZ 131-140	B.8
0518960141	DEK 6 FWZ 141-150	B.8
0518960151	DEK 6 FWZ 151-160	B.8
0518960161	DEK 6 FWZ 161-170	B.8
0518960171	DEK 6 FWZ 171-180	B.8
0518960181	DEK 6 FWZ 181-190	B.8
0518960191	DEK 6 FWZ 191-200	B.8
0518960201	DEK 6 FWZ 201-210	B.8
0519060001	DEK 6,5 FWZ 1-10	B.8
0519060011	DEK 6,5 FWZ 11-20	B.8
0519060021	DEK 6,5 FWZ 21-30	B.8
0519060031	DEK 6,5 FWZ 31-40	B.8
0519060041	DEK 6,5 FWZ 41-50	B.8
0519060051	DEK 6,5 FWZ 51-60	B.8
0519060061	DEK 6,5 FWZ 61-70	B.8
0519060071	DEK 6,5 FWZ 71-80	B.8
0519060081	DEK 6,5 FWZ 81-90	B.8
0519060091	DEK 6,5 FWZ 91-100	B.8

0520000000

0522361075	DEK 5 GW L1	B.7
0522361076	DEK 5 GW L2	B.7
0522361077	DEK 5 GW L3	B.7
0522660001	DEK 5 GW 1	B.7
0522660002	DEK 5 GW 2	B.7
0522660003	DEK 5 GW 3	B.7
0522660004	DEK 5 GW 4	B.7
0522660005	DEK 5 GW 5	B.7
0522660006	DEK 5 GW 6	B.7
0522660007	DEK 5 GW 7	B.7
0522660008	DEK 5 GW 8	B.7
0522660009	DEK 5 GW 9	B.7
0522660010	DEK 5 GW 10	B.7
0522660011	DEK 5 GW 11	B.7
0522660012	DEK 5 GW 12	B.7
0522660013	DEK 5 GW 13	B.7
0522660014	DEK 5 GW 14	B.7
0522660015	DEK 5 GW 15	B.7
0522660016	DEK 5 GW 16	B.7
0522660017	DEK 5 GW 17	B.7
0522660018	DEK 5 GW 18	B.7
0522660019	DEK 5 GW 19	B.7
0522660020	DEK 5 GW 20	B.7
0522660021	DEK 5 GW 21	B.7
0522660022	DEK 5 GW 22	B.7
0522660023	DEK 5 GW 23	B.7
0522660024	DEK 5 GW 24	B.7
0522660025	DEK 5 GW 25	B.7
0522660026	DEK 5 GW 26	B.7
0522660027	DEK 5 GW 27	B.7
0522660028	DEK 5 GW 28	B.7
0522660029	DEK 5 GW 29	B.7
0522660030	DEK 5 GW 30	B.7
0522660031	DEK 5 GW 31	B.7
0522660032	DEK 5 GW 32	B.7
0522660033	DEK 5 GW 33	B.7
0522660034	DEK 5 GW 34	B.7
0522660035	DEK 5 GW 35	B.7
0522660036	DEK 5 GW 36	B.7
0522660037	DEK 5 GW 37	B.7
0522660038	DEK 5 GW 38	B.7
0522660039	DEK 5 GW 39	B.7
0522660040	DEK 5 GW 40	B.7
0522660041	DEK 5 GW 41	B.7
0522660042	DEK 5 GW 42	B.7
0522660043	DEK 5 GW 43	B.7
0522660044	DEK 5 GW 44	B.7
0522660045	DEK 5 GW 45	B.7
0522660046	DEK 5 GW 46	B.7
0522660047	DEK 5 GW 47	B.7
0522660048	DEK 5 GW 48	B.7
0522660049	DEK 5 GW 49	B.7
0522660050	DEK 5 GW 50	B.7
0522660051	DEK 5 GW 51	B.7
0522660052	DEK 5 GW 52	B.7
0522660053	DEK 5 GW 53	B.7
0522660054	DEK 5 GW 54	B.7
0522660055	DEK 5 GW 55	B.7
0522660056	DEK 5 GW 56	B.7
0522660057	DEK 5 GW 57	B.7
0522660058	DEK 5 GW 58	B.7
0522660059	DEK 5 GW 59	B.7
0522660060	DEK 5 GW 60	B.7
0522660061	DEK 5 GW 61	B.7
0522660062	DEK 5 GW 62	B.7
0522660063	DEK 5 GW 63	B.7
0522660064	DEK 5 GW 64	B.7
0522660065	DEK 5 GW 65	B.7
0522660066	DEK 5 GW 66	B.7
0522660067	DEK 5 GW 67	B.7
0522660068	DEK 5 GW 68	B.7
0522660069	DEK 5 GW 69	B.7
0522660070	DEK 5 GW 70	B.7
0522660071	DEK 5 GW 71	B.7
0522660072	DEK 5 GW 72	B.7
0522660073	DEK 5 GW 73	B.7
0522660074	DEK 5 GW 74	B.7
0522660075	DEK 5 GW 75	B.7
0522660076	DEK 5 GW 76	B.7
0522660077	DEK 5 GW 77	B.7
0522660078	DEK 5 GW 78	B.7
0522660079	DEK 5 GW 79	B.7
0522660080	DEK 5 GW 80	B.7
0522660081	DEK 5 GW 81	B.7
0522660082	DEK 5 GW 82	B.7
0522660083	DEK 5 GW 83	B.7
0522660084	DEK 5 GW 84	B.7
0522660085	DEK 5 GW 85	B.7
0522660086	DEK 5 GW 86	B.7
0522660087	DEK 5 GW 87	B.7
0522660088	DEK 5 GW 88	B.7
0522660089	DEK 5 GW 89	B.7
0522660090	DEK 5 GW 90	B.7
0522660091	DEK 5 GW 91	B.7
0522660092	DEK 5 GW 92	B.7
0522660093	DEK 5 GW 93	B.7
0522660094	DEK 5 GW 94	B.7
0522660095	DEK 5 GW 95	B.7
0522660096	DEK 5 GW 96	B.7
0522660097	DEK 5 GW 97	B.7
0522660098	DEK 5 GW 98	B.7
0522660099	DEK 5 GW 99	B.7
0522660100	DEK 5 GW 100	B.7
0522660101	DEK 5 GW 101	B.7
0522660102	DEK 5 GW 102	B.7
0522660103	DEK 5 GW 103	B.7
0522660104	DEK 5 GW 104	B.7
0522660105	DEK 5 GW 105	B.7
0522660106	DEK 5 GW 106	B.7
0522660107	DEK 5 GW 107	B.7
0522660108	DEK 5 GW 108	B.7
0522660109	DEK 5 GW 109	B.7
0522660110	DEK 5 GW 110	B.7
0522660111	DEK 5 GW 111	B.7
0522660112	DEK 5 GW 112	B.7
0522660113	DEK 5 GW 113	B.7
0522660114	DEK 5 GW 114	B.7
0522660115	DEK 5 GW 115	B.7
0522660116	DEK 5 GW 116	B.7
0522660117	DEK 5 GW 117	B.7
0522660118	DEK 5 GW 118	B.7
0522660119	DEK 5 GW 119	B.7
0522660120	DEK 5 GW 120	B.7
0522660121	DEK 5 GW 121	B.7
0522660122	DEK 5 GW 122	B.7
0522660123	DEK 5 GW 123	B.7
0522660124	DEK 5 GW 124	B.7
0522660125	DEK 5 GW 125	B.7
0522660126	DEK 5 GW 126	B.7
0522660127	DEK 5 GW 127	B.7
0522660128	DEK 5 GW 128	B.7
0522660129	DEK 5 GW 129	B.7
0522660130	DEK 5 GW 130	B.7
0522660131	DEK 5 GW 131	B.7
0522660132	DEK 5 GW 132	B.7
0522660133	DEK 5 GW 133	B.7
0522660134	DEK 5 GW 134	B.7
0522660135	DEK 5 GW 135	B.7
0522660136	DEK 5 GW 136	B.7
0522660137	DEK 5 GW 137	B.7
0522660138	DEK 5 GW 138	B.7
0522660139	DEK 5 GW 139	B.7
0522660140	DEK 5 GW 140	B.7
0522660141	DEK 5 GW 141	B.7
0522660142	DEK 5 GW 142	B.7
0522660143	DEK 5 GW 143	B.7
0522660144	DEK 5 GW 144	B.7
0522660145	DEK 5 GW 145	B.7
0522660146	DEK 5 GW 146	B.7
0522660147	DEK 5 GW 147	B.7
0522660148	DEK 5 GW 148	B.7
0522660149	DEK 5 GW 149	B.7
0522660150	DEK 5 GW 150	B.7
0522660151	DEK 5 GW 151	B.7
0522660152	DEK 5 GW 152	B.7
0522660153	DEK 5 GW 153	B.7
0522660154	DEK 5 GW 154	B.7
0522660155	DEK 5 GW 155	B.7
0522660156	DEK 5 GW 156	B.7
0522660157	DEK 5 GW 157	B.7
0522660158	DEK 5 GW 158	B.7
0522660159	DEK 5 GW 159	B.7
0522660160	DEK 5 GW 160	B.7
0522660161	DEK 5 GW 161	B.7
0522660162	DEK 5 GW 162	B.7
0522660163	DEK 5 GW 163	B.7
0522660164	DEK 5 GW 164	B.7
0522660165	DEK 5 GW 165	B.7
0522660166	DEK 5 GW 166	B.7
0522660167	DEK 5 GW 167	B.7
0522660168	DEK 5 GW 168	B.7
0522660169	DEK 5 GW 169	B.7
0522660170	DEK 5 GW 170	B.7
0522660171	DEK 5 GW 171	B.7
0522660172	DEK 5 GW 172	B.7
0522660173	DEK 5 GW 173	B.7
0522660174	DEK 5 GW 174	B.7
0522660175	DEK 5 GW 175	B.7
0522660176	DEK 5 GW 176	B.7
0522660177	DEK 5 GW 177	B.7
0522660178	DEK 5 GW 178	B.7
0522660179	DEK 5 GW 179	B.7
0522660180	DEK 5 GW 180	B.7
0522660181	DEK 5 GW 181	B.7
0522660182	DEK 5 GW 182	B.7
0522660183	DEK 5 GW 183	B.7
0522660184	DEK 5 GW 184	B.7
0522660185	DEK 5 GW 185	B.7
0522660186	DEK 5 GW 186	B.7
0522660187	DEK 5 GW 187	B.7
0522660188	DEK 5 GW 188	B.7
0522660189	DEK 5 GW 189	B.7
0522660190	DEK 5 GW 190	B.7
0522660191	DEK 5 GW 191	B.7
0522660192	DEK 5 GW 192	B.7
0522660193	DEK 5 GW 193	B.7
0522660194	DEK 5 GW 194	B.7
0522660195	DEK 5 GW 195	B.7
0522660196	DEK 5 GW 196	B.7
0522660197	DEK 5 GW 197	B.7
0522660198	DEK 5 GW 198	B.7
0522660199	DEK 5 GW 199	B.7
0522660200	DEK 5 GW 200	B.7
0522761021	DEK 5 GW A	B.7
0522761022	DEK 5 GW B	B.7
0522761023	DEK 5 GW C	B.7
0522761024	DEK 5 GW D	B.7
0522761025	DEK 5 GW E	B.7
0522761026	DEK 5 GW F	B.7
0522761027	DEK 5 GW G	B.7
0522761028	DEK 5 GW H	B.7
0522761029	DEK 5 GW I	B.7
0522761030	DEK 5 GW J	B.7
0522761031	DEK 5 GW K	B.7
0522761032	DEK 5 GW L	B.7
0522761033	DEK 5 GW M	B.7
0522761034	DEK 5 GW N	B.8
0522761035	DEK 5 GW O	B.8
0522761036	DEK 5 GW P	B.8
0522761037	DEK 5 GW Q	B.8
0522761038	DEK 5 GW R	B.8
0522761039	DEK 5 GW S	B.8
0522761040	DEK 5 GW T	B.8
0522761041	DEK 5 GW U	B.8
0522761042	DEK 5 GW V	B.8
0522761043	DEK 5 GW W	B.8
0522761044	DEK 5 GW X	B.8
0522761045	DEK 5 GW Y	B.8
0522761046	DEK 5 GW Z	B.8
0523060001	DEK 5 FWZ 1-10	B.7
0523060011	DEK 5 FWZ 11-20	B.7
0523060021	DEK 5 FWZ 21-30	B.7
0523060031	DEK 5 FWZ 31-40	B.7
0523060041	DEK 5 FWZ 41-50	B.7
0523060051	DEK 5 FWZ 51-60	B.7
0523060061	DEK 5 FWZ 61-70	B.7
0523060071	DEK 5 FWZ 71-80	B.7
0523060081	DEK 5 FWZ 81-90	B.7
0523060091	DEK 5 FWZ 91-100	B.7
0524400000	CLI MH 70 HSTR	C.52
0526960001	DEK 6 GW 1	B.8
0526960002	DEK 6 GW 2	B.8
0526960003	DEK 6 GW 3	B.8
0526960004	DEK 6 GW 4	B.8
0526960005	DEK 6 GW 5	B.8
0526960006	DEK 6 GW 6	B.8
0526960007	DEK 6 GW 7	B.8
0526960008	DEK 6 GW 8	B.8
0526960009	DEK 6 GW 9	B.8
0526960010	DEK 6 GW 10	B.8
0526960011	DEK 6 GW 11	B.8
0526960012	DEK 6 GW 12	B.8
0526960013	DEK 6 GW 13	B.8
0526960014	DEK 6 GW 14	B.8
0526960015	DEK 6 GW 15	B.8
0526960016	DEK 6 GW 16	B.8
0526960017	DEK 6 GW 17	B.8
0526960018	DEK 6 GW 18	B.8
0526960019	DEK 6 GW 19	B.8
0526960020	DEK 6 GW 20	B.8
0526960021	DEK 6 GW 21	B.8
0526960022	DEK 6 GW 22	B.8
0526960023	DEK 6 GW 23	B.8
0526960024	DEK 6 GW 24	B.8
0526960025	DEK 6 GW 25	B.8
0526960026	DEK 6 GW 26	B.8
0526960027	DEK 6 GW 27	B.8
0526960028	DEK 6 GW 28	B.8
0526960029	DEK 6 GW 29	B.8
0526960030	DEK 6 GW 30	B.8
0526960031	DEK 6 GW 31	B.8
0526960032	DEK 6 GW 32	B.8
0526960033	DEK 6 GW 33	B.8
0526960034	DEK 6 GW 34	B.8
0526960035	DEK 6 GW 35	B.8
0526960036	DEK 6 GW 36	B.8
0526960037	DEK 6 GW 37	B.8
0526960038	DEK 6 GW 38	B.8
0526960039	DEK 6 GW 39	B.8
0526960040	DEK 6 GW 40	B.8
0526960041	DEK 6 GW 41	B.8
0526960042	DEK 6 GW 42	B.8
0526960043	DEK 6 GW 43	B.8
0526960044	DEK 6 GW 44	B.8
0526960045	DEK 6 GW 45	B.8
0526960046	DEK 6 GW 46	B.8
0526960047	DEK 6 GW 47	B.8
0526960048	DEK 6 GW 48	B.8
0526960049	DEK 6 GW 49	B.8
0526960050	DEK 6 GW 50	B.8
0526960051	DEK 6 GW 51	B.8
0526960052	DEK 6 GW 52	B.8
0526960053	DEK 6 GW 53	B.8
0526960054	DEK 6 GW 54	B.8
0526960055	DEK 6 GW 55	B.8
0526960056	DEK 6 GW 56	B.8
0526960057	DEK 6 GW 57	B.8
0526960058	DEK 6 GW 58	B.8
0526960059	DEK 6 GW 59	B.8
0526960060	DEK 6 GW 60	B.8
0526960061	DEK 6 GW 61	B.8
0526960062	DEK 6 GW 62	B.8
0526960063	DEK 6 GW 63	B.8
0526960064	DEK 6 GW 64	B.8
0526960065	DEK 6 GW 65	B.8
0526960066	DEK 6 GW 66	B.8
0526960067	DEK 6 GW 67	B.8
0526960068	DEK 6 GW 68	B.8
0526960069	DEK 6 GW 69	B.8
0526960070	DEK 6 GW 70	B.8
0526960071	DEK 6 GW 71	B.8
0526960072	DEK 6 GW 72	B.8
0526960073	DEK 6 GW 73	B.8
0526960074	DEK 6 GW 74	B.8
0526960075	DEK 6 GW 75	B.8
0526960076	DEK 6 GW 76	B.8
0526960077	DEK 6 GW 77	B.8
0526960078	DEK 6 GW 78	B.8
0526960079	DEK 6 GW 79	B.8
0526960080	DEK 6 GW 80	B.8
0526960081	DEK 6 GW 81	B.8
0526960082	DEK 6 GW 82	B.8
0526960083	DEK 6 GW 83	B.8
0526960084	DEK 6 GW 84	B.8
0526960085	DEK 6 GW 85	B.8
0526960086	DEK 6 GW 86	B.8
0526960087	DEK 6 GW 87	B.8
0526960088	DEK 6 GW 88	B.8

Order No.	Type	Page
0526960089	DEK 6 GW 89	B.8
0526960090	DEK 6 GW 90	B.8
0526960091	DEK 6 GW 91	B.8
0526960092	DEK 6 GW 92	B.8
0526960093	DEK 6 GW 93	B.8
0526960094	DEK 6 GW 94	B.8
0526960095	DEK 6 GW 95	B.8
0526960096	DEK 6 GW 96	B.8
0526960097	DEK 6 GW 97	B.8
0526960098	DEK 6 GW 98	B.8
0526960099	DEK 6 GW 99	B.8
0526960100	DEK 6 GW 100	B.8
0526961000	DEK 6 GW 0	B.8

0530000000

0532100000	CLI R 1 F. CLI C 1-3	C.53
0537261187	DEK 5 GW PE	B.8
0537261188	DEK 5 GW PEN	B.8
0537261235	DEK 5 GW Mp	B.8

0550000000

0558360000	DEK 5 FWZ U,V,W,N,PE	B.7
0559200000	CLI RS 3 MDCLI C 02	C.53
0559300000	CLI RS 4 MDCLI C1+02	C.53
0559900000	CLI R 02 F. CLI C 02-3	C.53

0560000000

0560001501	CLI R 02-3 GE/SW 0	C.42
0560001503	CLI R 02-3 SW/WS 0	C.27
0560001504	CLI R 02-3 GE/SW 1	C.42
0560001506	CLI R 02-3 BR/WS 1	C.27
0560001507	CLI R 02-3 GE/SW 2	C.42
0560001509	CLI R 02-3 RT/SW 2	C.27
0560001510	CLI R 02-3 GE/SW 3	C.42
0560001512	CLI R 02-3 OR/SW 3	C.27
0560001513	CLI R 02-3 GE/SW 4	C.27
0560001513	CLI R 02-3 GE/SW 4	C.42
0560001516	CLI R 02-3 GE/SW 5	C.42
0560001518	CLI R 02-3 GN/SW 5	C.27
0560001519	CLI R 02-3 GE/SW 6	C.42
0560001521	CLI R 02-3 BL/SW 6	C.27
0560001522	CLI R 02-3 GE/SW 7	C.42
0560001524	CLI R 02-3 VI/SW 7	C.27
0560001525	CLI R 02-3 GE/SW 8	C.42
0560001527	CLI R 02-3 GR/SW 8	C.27
0560001528	CLI R 02-3 GE/SW 9	C.42
0560001530	CLI R 02-3 WS/SW 9	C.27
0560001530	CLI R 02-3 WS/SW 9	C.42
0560001531	CLI R 02-3 SET 0-9,R,S, T TO GR NEUT	C.54
0560001638	CLI R 02-3 GE/SW A	C.42
0560001640	CLI R 02-3 GE/SW B	C.42
0560001642	CLI R 02-3 GE/SW C	C.42
0560001644	CLI R 02-3 GE/SW D	C.42
0560001646	CLI R 02-3 GE/SW E	C.42
0560001648	CLI R 02-3 GE/SW F	C.42
0560001650	CLI R 02-3 GE/SW G	C.42
0560001652	CLI R 02-3 GE/SW H	C.42
0560001654	CLI R 02-3 GE/SW I	C.42
0560001656	CLI R 02-3 GE/SW J	C.42
0560001658	CLI R 02-3 GE/SW K	C.42
0560001660	CLI R 02-3 GE/SW L	C.42
0560001662	CLI R 02-3 GE/SW M	C.42
0560001664	CLI R 02-3 GE/SW N	C.42
0560001666	CLI R 02-3 GE/SW O	C.42
0560001668	CLI R 02-3 GE/SW P	C.42
0560001670	CLI R 02-3 GE/SW Q	C.42
0560001672	CLI R 02-3 GE/SW R	C.42
0560001675	CLI R 02-3 GE/SW S	C.42
0560001678	CLI R 02-3 GE/SW T	C.42
0560001680	CLI R 02-3 GE/SW U	C.42
0560001682	CLI R 02-3 GE/SW V	C.42
0560001684	CLI R 02-3 GE/SW W	C.42
0560001687	CLI R 02-3 GE NE	C.20
0560001693	CLI R 02-3 GE/SW X	C.42
0560001695	CLI R 02-3 GE/SW Ö	C.42
0560001696	CLI R 02-3 GE/SW Ä	C.42
0560001697	CLI R 02-3 GE/SW Y	C.42
0560001698	CLI R 02-3 GE/SW Å	C.42
0560001699	CLI R 02-3 GE/SW Z	C.42
0560001737	CLI R 02-3 BL/SW +	C.43
0560001738	CLI R 02-3 GE/SW +	C.42
0560001739	CLI R 02-3 RT/SW +	C.43
0560001740	CLI R 02-3 GE/SW -	C.42
0560001741	CLI R 02-3 BL/SW -	C.43
0560001743	CLI R 02-3 GE/SW /	C.42
0560001745	CLI R 02-3 GE/SW ET	C.42
0560001746	CLI R 02-3 BL/SW N	C.43
0560001749	CLI R 02-3 GE/SW .	C.42
0560009999	CLI R 02-3 SDR	C.23
0563600000	CLI RH 20-10 CLI R 10	C.52
0563700000	CLI RH 20-02 CLI R 02	C.52

0570000000

0572900002	CLI R 1-3 BL NE	C.20
0572901502	CLI R 1-3 SW/WS 0	C.27
0572901503	CLI R 1-3 GE/SW 0	C.43
0572901505	CLI R 1-3 BR/WS 1	C.27
0572901506	CLI R 1-3 GE/SW 1	C.43
0572901508	CLI R 1-3 RT/SW 2	C.27
0572901509	CLI R 1-3 GE/SW 2	C.43
0572901511	CLI R 1-3 OR/SW 3	C.27
0572901512	CLI R 1-3 GE/SW 3	C.43
0572901515	CLI R 1-3 GE/SW 4	C.27
0572901515	CLI R 1-3 GE/SW 4	C.43
0572901517	CLI R 1-3 GN/SW 5	C.27
0572901518	CLI R 1-3 GE/SW 5	C.43
0572901520	CLI R 1-3 BL/SW 6	C.27
0572901521	CLI R 1-3 GE/SW 6	C.43
0572901523	CLI R 1-3 VI/SW 7	C.27
0572901524	CLI R 1-3 GE/SW 7	C.43
0572901526	CLI R 1-3 GR/SW 8	C.27
0572901527	CLI R 1-3 GE/SW 8	C.43
0572901529	CLI R 1-3 WS/SW 9	C.27
0572901530	CLI R 1-3 GE/SW 9	C.43
0572901531	CLI R 1-3 SET 0-9,R,S, T TO GR NEUT	C.54
0572901638	CLI R 1-3 GE/SW A	C.43
0572901640	CLI R 1-3 GE/SW B	C.43
0572901642	CLI R 1-3 GE/SW C	C.43
0572901644	CLI R 1-3 GE/SW D	C.43
0572901646	CLI R 1-3 GE/SW E	C.43
0572901648	CLI R 1-3 GE/SW F	C.43
0572901650	CLI R 1-3 GE/SW G	C.43
0572901652	CLI R 1-3 GE/SW H	C.43
0572901654	CLI R 1-3 GE/SW I	C.43
0572901656	CLI R 1-3 GE/SW J	C.43
0572901658	CLI R 1-3 GE/SW K	C.43
0572901660	CLI R 1-3 GE/SW L	C.43
0572901662	CLI R 1-3 GE/SW M	C.43
0572901664	CLI R 1-3 GE/SW N	C.43
0572901666	CLI R 1-3 GE/SW O	C.43
0572901668	CLI R 1-3 GE/SW P	C.43
0572901670	CLI R 1-3 GE/SW Q	C.43
0572901672	CLI R 1-3 GE/SW R	C.43
0572901675	CLI R 1-3 GE/SW S	C.43
0572901678	CLI R 1-3 GE/SW T	C.43
0572901680	CLI R 1-3 GE/SW U	C.43
0572901682	CLI R 1-3 GE/SW V	C.43
0572901684	CLI R 1-3 GE/SW W	C.43
0572901687	CLI R 1-3 GE NE	C.20
0572901693	CLI R 1-3 GE/SW X	C.43
0572901695	CLI R 1-3 GE/SW Ö	C.44
0572901696	CLI R 1-3 GE/SW Ä	C.44
0572901697	CLI R 1-3 GE/SW Y	C.43
0572901698	CLI R 1-3 GE/SW Å	C.44
0572901699	CLI R 1-3 GE/SW Z	C.43
0572901738	CLI R 1-3 GE/SW +	C.44
0572901739	CLI R 1-3 RT/SW +	C.44
0572901740	CLI R 1-3 GE/SW -	C.44
0572901741	CLI R 1-3 BL/SW -	C.44
0572901743	CLI R 1-3 GE/SW /	C.44
0572901745	CLI R 1-3 GE/SW ET	C.44
0572901746	CLI R 1-3 BL/SW N	C.44
0572901749	CLI R 1-3 GE/SW .	C.44
0572909999	CLI R 1-3 SDR	C.23
0576260000	DEK 5 GW	B.7
0576261198	DEK 5 GW +	B.8
0576261199	DEK 5 GW -	B.8
0576261202	DEK 5 GW ERDE	B.8
0576261203	DEK 5 GW ERDE I.KR.	B.8
0576261215	DEK 5 GW W-STROM	B.8
0576291737	DEK 5 GW RT/SW +	B.8
0576291741	DEK 5 GW BL/SW -	B.7

0630000000

0631860000	DEK 6 FWZ R,S,T,N,ERDE	B.8
0631961187	DEK 6 FWZ L1-PE	B.8
0631961203	DEK 6 FWZ L1-ERDE I.KRE	B.8
0632060000	DEK 6,5 FWZ R,S,T,N,ERD	B.8
0632161187	DEK 6,5 FW L1-PE	B.8
0632161203	DEK 6,5 FW L1-ERDE I.KR	B.8
0632560000	DEK 6 FW L,N,PE	B.8

0640000000

0648001502	CLI O 10-3 GE/SW 0 MP	C.46
0648001505	CLI O 10-3 GE/SW 1 MP	C.46
0648001508	CLI O 10-3 GE/SW 2 MP	C.46
0648001511	CLI O 10-3 GE/SW 3 MP	C.46
0648001514	CLI O 10-3 GE/SW 4 MP	C.46
0648001517	CLI O 10-3 GE/SW 5 MP	C.46
0648001520	CLI O 10-3 GE/SW 6 MP	C.46
0648001523	CLI O 10-3 GE/SW 7 MP	C.46
0648001526	CLI O 10-3 GE/SW 8 MP	C.46
0648001529	CLI O 10-3 GE/SW 9 MP	C.46
0648001637	CLI O 10-3 GE/SW A MP	C.46
0648001639	CLI O 10-3 GE/SW B MP	C.46
0648001641	CLI O 10-3 GE/SW C MP	C.46
0648001643	CLI O 10-3 GE/SW D MP	C.46
0648001645	CLI O 10-3 GE/SW E MP	C.46
0648001647	CLI O 10-3 GE/SW F MP	C.46
0648001649	CLI O 10-3 GE/SW G MP	C.46
0648001651	CLI O 10-3 GE/SW H MP	C.46
0648001653	CLI O 10-3 GE/SW I MP	C.46
0648001655	CLI O 10-3 GE/SW J MP	C.46
0648001657	CLI O 10-3 GE/SW K MP	C.46
0648001659	CLI O 10-3 GE/SW L MP	C.46
0648001661	CLI O 10-3 GE/SW M MP	C.46
0648001663	CLI O 10-3 GE/SW N MP	C.46
0648001665	CLI O 10-3 GE/SW O MP	C.46
0648001667	CLI O 10-3 GE/SW P MP	C.46
0648001669	CLI O 10-3 GE/SW Q MP	C.46
0648001671	CLI O 10-3 GE/SW R MP	C.46
0648001673	CLI O 10-3 GE/SW S MP	C.46
0648001676	CLI O 10-3 GE/SW T MP	C.46
0648001679	CLI O 10-3 GE/SW U MP	C.46
0648001681	CLI O 10-3 GE/SW V MP	C.46
0648001683	CLI O 10-3 GE/SW W MP	C.46
0648001687	CLI O 10-3 GE/SW X MP	C.46
0648001695	CLI O 10-3 GE/SW Ö MP	C.46
0648001696	CLI O 10-3 GE/SW Y MP	C.46
0648001697	CLI O 10-3 GE/SW Ä MP	C.46
0648001698	CLI O 10-3 GE/SW Z MP	C.46
0648001699	CLI O 10-3 GE/SW Å MP	C.46
0648001737	CLI O 10-3 RT/SW + MP	C.46
0648001738	CLI O 10-3 GE/SW + MP	C.46
0648001740	CLI O 10-3 GE/SW - MP	C.46
0648001741	CLI O 10-3 BL/SW - MP	C.46
0648001746	CLI O 10-3 GE/SW ET MP	C.46
0648009999	CLI O 10-3 SDR MP	C.24
0648101502	CLI O 20-3 GE/SW 0 MP	C.47
0648101505	CLI O 20-3 GE/SW 1 MP	C.47
0648101508	CLI O 20-3 GE/SW 2 MP	C.47
0648101511	CLI O 20-3 GE/SW 3 MP	C.47
0648101514	CLI O 20-3 GE/SW 4 MP	C.47
0648101517	CLI O 20-3 GE/SW 5 MP	C.47
0648101520	CLI O 20-3 GE/SW 6 MP	C.47
0648101523	CLI O 20-3 GE/SW 7 MP	C.47
0648101526	CLI O 20-3 GE/SW 8 MP	C.47
0648101529	CLI O 20-3 GE/SW 9 MP	C.47
0648101637	CLI O 20-3 GE/SW A MP	C.47
0648101639	CLI O 20-3 GE/SW B MP	C.47
0648101641	CLI O 20-3 GE/SW C MP	C.47
0648101643	CLI O 20-3 GE/SW D MP	C.47
0648101645	CLI O 20-3 GE/SW E MP	C.47
0648101647	CLI O 20-3 GE/SW F MP	C.47
0648101649	CLI O 20-3 GE/SW G MP	C.47
0648101651	CLI O 20-3 GE/SW H MP	C.47
0648101653	CLI O 20-3 GE/SW I MP	C.47
0648101655	CLI O 20-3 GE/SW J MP	C.47
0648101657	CLI O 20-3 GE/SW K MP	C.47
0648101659	CLI O 20-3 GE/SW L MP	C.47
0648101661	CLI O 20-3 GE/SW M MP	C.47
0648101663	CLI O 20-3 GE/SW N MP	C.47
0648101665	CLI O 20-3 GE/SW O MP	C.47
0648101667	CLI O 20-3 GE/SW P MP	C.47
0648101669	CLI O 20-3 GE/SW Q MP	C.47
0648101671	CLI O 20-3 GE/SW R MP	C.47
0648101673	CLI O 20-3 GE/SW S MP	C.47
0648101676	CLI O 20-3 GE/SW T MP	C.47
0648101679	CLI O 20-3 GE/SW U MP	C.47
0648101681	CLI O 20-3 GE/SW V MP	C.47
0648101683	CLI O 20-3 GE/SW W MP	C.47
0648101687	CLI O 20-3 GE/SW X MP	C.47
0648101695	CLI O 20-3 GE/SW Ö MP	C.47
0648101696	CLI O 20-3 GE/SW Y MP	C.47
0648101697	CLI O 20-3 GE/SW Ä MP	C.47
0648101698	CLI O 20-3 GE/SW Z MP	C.47
0648101699	CLI O 20-3 GE/SW Å MP	C.47
0648101737	CLI O 20-3 RT/SW + MP	C.47
0648101738	CLI O 20-3 GE/SW + MP	C.47
0648101740	CLI O 20-3 GE/SW - MP	C.47
0648101741	CLI O 20-3 BL/SW - MP	C.47
0648101746	CLI O 20-3 GE/SW ET MP	C.47
0648109999	CLI O 20-3 SDR MP	C.24
0648201502	CLI O 30-3 GE/SW 0 MP	C.48
0648201505	CLI O 30-3 GE/SW 1 MP	C.48
0648201508	CLI O 30-3 GE/SW 2 MP	C.48
0648201511	CLI O 30-3 GE/SW 3 MP	C.48
0648201514	CLI O 30-3 GE/SW 4 MP	C.48
0648201517	CLI O 30-3 GE/SW 5 MP	C.48
0648201520	CLI O 30-3 GE/SW 6 MP	C.48
0648201523	CLI O 30-3 GE/SW 7 MP	C.48
0648201526	CLI O 30-3 GE/SW 8 MP	C.48
0648201529	CLI O 30-3 GE/SW 9 MP	C.48
0648201637	CLI O 30-3 GE/SW A MP	C.48
0648201639	CLI O 30-3 GE/SW B MP	C.48
0648201641	CLI O 30-3 GE/SW C MP	C.48
0648201643	CLI O 30-3 GE/SW D MP	C.48
0648201645	CLI O 30-3 GE/SW E MP	C.48
0648201647	CLI O 30-3 GE/SW F MP	C.48
0648201649	CLI O 30-3 GE/SW G MP	C.48
0648201651	CLI O 30-3 GE/SW H MP	C.48
0648201653	CLI O 30-3 GE/SW I MP	C.48
0648201655	CLI O 30-3 GE/SW J MP	C.48
0648201657	CLI O 30-3 GE/SW K MP	C.48
0648201659	CLI O 30-3 GE/SW L MP	C.48
0648201661	CLI O 30-3 GE/SW M MP	C.48
0648201663	CLI O 30-3 GE/SW N MP	C.48
0648201665	CLI O 30-3 GE/SW O MP	C.48
0648201667	CLI O 30-3 GE/SW P MP	C.48
0648201669	CLI O 30-3 GE/SW Q MP	C.48
0648201671	CLI O 30-3 GE/SW R MP	C.48
0648201673	CLI O 30-3 GE/SW S MP	C.48
0648201676	CLI O 30-3 GE/SW T MP	C.48
0648201679	CLI O 30-3 GE/SW U MP	C.48
0648201681	CLI O 30-3 GE/SW V MP	C.48
0648201683	CLI O 30-3 GE/SW W MP	C.48
0648201687	CLI O 30-3 GE/SW X MP	C.48
0648201695	CLI O 30-3 GE/SW Ö MP	C.48
0648201696	CLI O 30-3 GE/SW Y MP	C.48
0648201697	CLI O 30-3 GE/SW Ä MP	C.48
0648201698	CLI O 30-3 GE/SW Z MP	C.48
0648201699	CLI O 30-3 GE/SW Å MP	C.48
0648201737	CLI O 30-3 RT/SW + MP	C.48
0648201738	CLI O 30-3 GE/SW + MP	C.48
0648201740	CLI O 30-3 GE/SW - MP	C.48
0648201741	CLI O 30-3 BL/SW - MP	C.48
0648201746	CLI O 30-3 GE/SW ET MP	C.48
0648209999	CLI O 30-3 SDR MP	C.24
0648300000	CLI RS 5 MDCLI C 1	C.53

0660000000

0660100000	CLI O 10-6 SDR MP	C.24

0680000000

0688660000	DEK 6 FW 1-5 (10X)	B.8
0689600000	CLI O 10-3 GE NE MP	C.22
0689700000	CLI O 20-3 GE NE MP	C.22
0689800000	CLI O 30-3 GE NE MP	C.22

0690000000

0694700000	CLI O 20-6 SDR MP	C.24

1000000000

1001140001	ESG B&R X20 MC NE WS	D.4
1001150001	ESG B&R X20 MC NE BL	D.4
1001160001	ESG B&R X20 MC NE OR	D.4
1001170001	ESG B&R X20 MC NE RT	D.4
1001180001	PRINTJET PRO 230V	E.3
1003380000	THM WRITEON T 24.5/100 WS	C.17
1003400000	LM MT300 89X34 WS	D.11
1003410000	THM MT30x 89/60 SI	D.12
1003420000	THM WRITEON T 24.5/62 WS	C.17
1005710000	PLOTTER PEN 0.50 P-INK	E.6
1005710000	PLOTTER PEN 0.50 P-INK	E.7
1009320000	CC 30/60 MC NE GE	D.8

1010000000

1010860000	ESG 9/20 L MC NE GE	D.4
1011320000	DEK 5/6 PLUS MC NE WS	B.11
1011410000	MF-W 9/5.2F MC NE WS	B.18
1011420000	MF-W 9/6.2F MC NE WS	B.19
1011430000	MF-W 9/4.2F MC NE WS	B.18
1011440000	Plotterpen 0,7	E.6
1011440000	Plotterpen 0,7	E.7
1011450000	PLOTTER PEN 0.70 P-INK	E.6
1011450000	PLOTTER PEN 0.70 P-INK	E.7
1011610000	THM MT30x 38/17 WS	D.12
1014640000	SM 27/18 MC NE GR	D.6
1014650000	SM 22/22 K MC NE GR	D.6
1014680000	THM MT30x 30/52 SI	D.12
1015220000	SCT-C 4.6/100	C.58
1015230000	SCT-C 4.6/125	C.58
1015240000	SCT-C 4.6/150	C.58
1015250000	SCT-C 4.6/200	C.58
1015270000	SCT-C 4.6/360	C.58
1015280000	SCT-C 4.6/520	C.58
1015290000	SCT-C 4.6/680	C.58
1015300000	SCT-C 4.6/840	C.58
1015310000	SCT-C 7.9/200	C.58
1015320000	SCT-C 7.9/360	C.58
1015330000	SCT-C 7.9/520	C.58
1015340000	SCT-C 7.9/680	C.58
1015350000	SCT-C 7.9/840	C.58
1016030000	DMC 12/27 MC NE WS	D.3
1018190000	DMC 12/27 MC NE GE	D.3

1020000000

1024050000	PRINTJET PRO 115V	E.3
1024140000	PJ PRO TNAW	E.3
1025220000	SFC 3/12 MC NE WS	C.7
1025230000	SFC 3/12 MC NE GE	C.7
1025240000	SFC 3/12 MC NE RT	C.7
1025250000	SFC 3/12 MC NE BL	C.7
1025260000	SFC 3/21 MC NE WS	C.7
1025270000	SFC 3/21 MC NE GE	C.7
1025290000	SFC 3/21 MC NE RT	C.7
1025300000	SFC 3/21 MC NE BL	C.7
1025310000	SFC 3/30 MC NE WS	C.7
1025320000	SFC 3/30 MC NE GE	C.7
1025330000	SFC 3/30 MC NE RT	C.7
1025340000	SFC 3/30 MC NE BL	C.7
1025550000	SFC 3/12 MC SDR	C.7
1025560000	SFC 3/21 MC SDR	C.7
1025570000	SFC 3/30 MC SDR	C.7
1025680000	DEK 5/30 MC SDR	B.38
1025680000	DEK 5/30 MC SDR	B.39

Order No.	Type	Page
1026550000	ESG X20 10/7 MC NE WS	D.4
1026560000	ESG X20 10/7 MC NE BL	D.4
1026570000	ESG X20 10/7 MC NE RT	D.4
1026580000	ESG X20 10/7 MC NE OR	D.4
1027040000	PJ PRO TNTK INK K	E.3
1027050000	PJ PRO TNTK INK C	E.3
1027060000	PJ PRO TNTK INK M	E.3
1027070000	PJ PRO TNTK INK Y	E.3
1027110000	PJ-PRO TNTK INK SET COL	E.3
1027280000	ESG-M 9/17 MC NE WS	D.4
1027290000	ESG-M 8/20 MC NE WS	D.4
1027620000	THM MT30x 17/8 GE	D.12
1027830000	SM 27/12.5 K MC NE GR	D.6
1029840000	HSS3/16*1,6-3,8/50W	C.16
1029850000	HSS3/16*1,6-3,8/50Y	C.16
1029860000	HSS3/16*1,6-3,8/25W	C.16
1029870000	HSS3/16*1,6-3,8/25Y	C.16
1030000000		
1038650000	DEK 5/6 PLUS MC SDR	B.11
1038660000	MF 10/5 MC CABUR SDR	B.18
1038670000	MF 12/5 MC CABUR SDR	B.18
1038690000	MF 4/5.2 MC SDR	B.18
1038730000	MF 5/10 MC SDR	B.19
1038750000	MF-W 9/4.2F MC SDR	B.18
1038760000	MF-W 9/5.2F MC SDR	B.18
1038770000	MF-W 9/6.2F MC SDR	B.19
1038790000	WS 8/5 PLUS MC SDR	B.14
1038820000	WS 8/6 PLUS MC SDR	B.15
1038830000	DMC 12/27 MC SDR	D.3
1038840000	ESG 5/10 MC SDR	D.4
1038850000	ESG 8/11 MC SDR	D.4
1038860000	ESG 8/13.5/43.3 SAI SDR	D.4
1038870000	ESG 8/17 L MC SDR	D.4
1038890000	ESG B&R X20 MC SDR	D.4
1038910000	ESG-M 8/20 MC SDR	D.4
1038920000	ESG-M 9/17 MC SDR	D.4
1038930000	ESG X20 10/7 MC SDR	D.4
1040000000		
1045570000	ELS 6/30 MC WS	B.37
1045570000	ELS 6/30 MC WS	C.13
1045580000	ELS 6/30 MC GE	B.37
1045580000	ELS 6/30 MC GE	C.13
1045620000	ELS 16/40 MC WS	B.36
1045620000	ELS 16/40 MC WS	B.37
1045620000	ELS 16/40 MC WS	C.13
1045630000	ELS 16/40 MC GE	B.36
1045630000	ELS 16/40 MC GE	B.37
1045630000	ELS 16/40 MC GE	C.13
1045640000	ELS 7/40 MC WS	B.36
1045640000	ELS 7/40 MC WS	B.37
1045650000	ELS 7/40 MC GE	B.36
1045650000	ELS 7/40 MC GE	B.37
1045660000	ELS 6/30 MC SDR	B.37
1045660000	ELS 6/30 MC SDR	C.13
1045690000	ELS 16/40 MC SDR	B.37
1045690000	ELS 16/40 MC SDR	C.13
1045700000	ELS 7/40 MC SDR	B.37
1046320000	WS 10/5 PLUS MC SDR	B.14
1046330000	WS 10/6 PLUS MC SDR	B.15
1046340000	DEK 5/6.5 PLUS MC NE WS	B.11
1046350000	DEK 5/8 PLUS MC NE WS	B.11
1046360000	DEK 5/6.5 PLUS MC SDR	B.11
1046370000	DEK 5/8 PLUS MC SDR	B.11
1046380000	WS 10/5 PLUS MC NE WS	B.14
1046390000	WS 10/6 PLUS MC NE WS	B.14
1050000000		
1050760000	WGB 5 ABDG.M.GRUPPENBEZ	B.38
1050960000	WGB 8 ABDG.M.GRUPPENBEZ	B.38
1051870000	SFX 11/60 MC NE BL	C.5
1053460000	WAD 5 M. BL.	B.38
1053560000	WAD 8 M. BL.	B.38
1055960000	WAD 12 M. BL.	B.38
1056060000	WAD 5 NEUTRAL	B.38
1056160000	WAD 8 NEUTRAL	B.38
1056260000	WAD 12 NEUTRAL	B.38
1057580000	CC 15/60 O4MM MC NE WS	D.9
1058090000	MCP EP SFC 3	C.6
1058090000	MCP EP SFC 3	E.6
1058090000	MCP EP SFC 3	E.7
1059200000	CB-R 200/7.5 NATUR	C.60
1059210000	CB-R 200/7.5 BLACK	C.60
1059220000	CB-R 250/7.5 NATUR	C.60
1059230000	CB-R 250/7.5 BLACK	C.60
1059240000	CB-R 350/7.5 NATUR	C.60
1059250000	CB-R 350/7.5 BLACK	C.60
1059780000	THM GEW 15/6 WS	D.12
1059790000	THM GEW 15/6 GE	D.12
1059800000	THM GEW 17/9 WS	D.12
1059810000	THM GEW 17/9 GE	D.12
1059820000	THM GEW 18/6 WS	D.12
1059830000	THM GEW 18/6 GE	D.12
1059840000	THM GEW 18/9 WS	D.12
1059850000	THM GEW 18/9 GE	D.12
1059870000	THM GEW 20/8 WS	D.12
1059880000	THM GEW 20/8 GE	D.12
1059990000	CC 15/60 O4MM MC NE SI	D.9
1060000000		
1061810000	THM MT30x 101/74 GE	D.12
1062860000	WAD 27 M. BL.	B.38
1062960000	WAD 27 NEUTRAL	B.38
1070000000		
1072640000	CC 15/60 MC NE GR	D.8
1072650000	CC 15/60 K MC NE GR	D.8
1072670000	CC 30/60 MC NE GR	D.8
1072680000	CC 30/60 K MC NE GR	D.8
1072690000	THM MT30X 15/4 GE/M	D.12
1073340000	SM 27/18 K MC NE GR	D.6
1076970000	CC 15/49 MC NE GE	D.8
1078320000	CC 30/60 K MC NE GE	D.8
1079470000	SM 27/8 MC NE GR	D.6
1079480000	SM 27/8 K MC NE GR	D.6
1079490000	SM 27/12.5 MC NE GR	D.6
1079510000	SM 27/27 MC NE GR	D.6
1079520000	SM 27/27 K MC NE GR	D.6
1079530000	CC 15/17 MC NE GR	D.8
1079540000	CC 15/17 K MC NE GR	D.8
1079550000	CC 15/27 MC NE GR	D.8
1079560000	CC 15/27 K MC NE GR	D.8
1079570000	CC 15/49 MC NE GR	D.8
1079580000	CC 15/49 K MC NE GR	D.8
1080000000		
1083150000	CC 30/60 O4MM MC NE WS	D.9
1083170000	CC 30/60 O4MM MC NE GR	D.9
1083230000	SFX 30/60 MC NE WS	C.5
1083240000	SFX 30/60 MC NE GE	C.5
1083260000	SFX 30/60 MC SDR	C.5
1085430000	CC 30/60 K MC NE RT	D.8
1090000000		
1095590000	THM ET S7 50/25 GE	D.13
1096170000	THM EL 15 WS	D.13
1100000000		
1105550000	THM EL 24 WS	D.13
1105560000	THM EL 38 WS	D.13
1109130000	THM WRITEON 25,4/62 WS	C.17
1109140000	THM WRITEON 25,4/92,5WS	C.17
1109150000	THM WRITEON 50,8/150 WS	C.17
1109180000	THM WRITEON 50,8/150 GE	C.17
1110000000		
1112910000	WAD 5 MC NE WS	B.34
1112920000	WAD 5 MC NE GE	B.34
1112930000	WAD 5 MC SDR	B.34
1112940000	WAD 8 MC NE WS	B.34
1112950000	WAD 8 MC NE GE	B.34
1112970000	WAD 8 MC SDR	B.34
1120000000		
1120450000	WAD 5 MC B GE/SW	B.34
1120470000	WAD 8 MC B GE/SW	B.34
1130000000		
1131800000	SM 27/27 K MC NE GE	D.6
1131810000	SM 27/12.5 K MC NE GE	D.6
1131820000	SM 27/8 K MC NE GE	D.6
1131830000	SM 22/22 K MC NE GE	D.6
1131840000	SM 27/27 MC NE GE	D.6
1131850000	SM 27/18 MC NE GE	D.6
1131860000	SM 27/12.5 MC NE GE	D.6
1131870000	SM 27/8 MC NE GE	D.6
1131880000	CC 15/60 04MM MC GE	D.9
1131890000	CC 15/60 K MC NE GE	D.8
1131910000	CC 15/27 K MC NE GE	D.8
1131920000	CC 15/17 K MC NE GE	D.8
1131930000	CC 15/17 MC NE GE	D.8
1131940000	CC 15/27 MC NE GE	D.8
1131960000	CC 15/60 MC NE GE	D.8
1131970000	CC 15/49 K MC NE GE	D.8
1136810000	ESG 6/15 F MC NE WS	D.4
1138400000	CC 85/54 MC NE WS	D.8
1138410000	CC 85/54 MC NE GE	D.8
1138420000	CC 85/54 MC NE GR	D.8
1138430000	CC 85/54 K MC NE WS	D.8
1138440000	CC 85/54 K MC NE GE	D.8
1138450000	CC 85/54 K MC NE GR	D.8
1138460000	CC 85/54 MC SDR	D.8
1138470000	CC 85/54 K MC SDR	D.8
1139400000	MCP BASIC	E.5
1139880000	MCP AP BASIC	E.6
1139890000	MCP TP-KOF BASIC	E.6
1140000000		
1140490000	THM-TWINMARK	E.8
1141340000	THM BASIC	E.11
1160000000		
1161710000	THM ET S7 400 TU	D.13
1161720000	THM ET S7 400 GE	D.13
1161730000	THM ET S7 300-2 TU	D.13
1161740000	THM ET S7 300-2 GE	D.13
1161750000	THM ET S7 300-1 TU	D.13
1161770000	THM ET S7 300-1 GE	D.13
1161780000	THM ET S7 50/25 TU	D.13
1161790000	THM ET S7 50/12,5 TU	D.13
1161810000	THM ET S7 50/12,5 GE	D.13
1260000000		
1269060000	SCHT 14/6	B.37
1270000000		
1276960001	DEK 8 FWZ 1-10	B.8
1276960011	DEK 8 FWZ 11-20	B.8
1276960021	DEK 8 FWZ 21-30	B.8
1276960031	DEK 8 FWZ 31-40	B.8
1276960041	DEK 8 FWZ 41-50	B.8
1276960051	DEK 8 FWZ 51-60	B.8
1276960061	DEK 8 FWZ 61-70	B.8
1276960071	DEK 8 FWZ 71-80	B.8
1276960081	DEK 8 FWZ 81-90	B.8
1276960091	DEK 8 FWZ 91-100	B.8
1276960101	DEK 8 FWZ 101-110	B.8
1276960111	DEK 8 FWZ 111-120	B.8
1276960121	DEK 8 FWZ 121-130	B.8
1276960131	DEK 8 FWZ 131-140	B.8
1276960141	DEK 8 FWZ 141-150	B.8
1277060000	DEK 8 NEUTRAL	B.8
1277091686	DEK 8 RT NEUTRAL	B.8
1277091687	DEK 8 GE NEUTRAL	B.8
1277091688	DEK 8 GN NEUTRAL	B.8
1277091689	DEK 8 VI NEUTRAL	B.8
1277091690	DEK 8 OR NEUTRAL	B.8
1278460000	SCHT 9/4	B.37
1278600000	CB 98/2.5 NATUR	C.59
1278700000	CB 140/3.6 NATUR	C.59
1278800000	CB 200/4.8 NATUR	C.59
1278900000	CB 290/4.8 NATUR	C.59
1279000000	CB 360/4.8 NATUR	C.59
1279100000	CB 365/7.8 NATUR	C.59
1279200000	CBH 8.1/6.2 NATUR	C.60
1279300000	CBDM 203/4.8 NATUR	C.60
1280000000		
1289200000	CBH 19/19 NATUR	C.60
1289400000	CBH 27/27 NATUR	C.60
1289660001	DEK 8 FSZ 1-10	B.8
1289660011	DEK 8 FSZ 11-20	B.8
1289660021	DEK 8 FSZ 21-30	B.8
1289660031	DEK 8 FSZ 31-40	B.8
1289660041	DEK 8 FSZ 41-50	B.8
1289660051	DEK 8 FSZ 51-60	B.8
1289660061	DEK 8 FSZ 61-70	B.8
1289660071	DEK 8 FSZ 71-80	B.8
1289660081	DEK 8 FSZ 81-90	B.8
1289660091	DEK 8 FSZ 91-100	B.8
1289690000	DEK 8 BEDR./FARBIG	B.8
1290000000		
1296000000	KABELBINDERZANGE RT-1	C.60
1310000000		
1318061187	DEK 6 GW PE	B.8
1318061198	DEK 6 GW +	B.8
1318061199	DEK 6 GW -	B.8
1318061202	DEK 6 GW ERDE	B.8
1318061203	DEK 6 GW ERDE I.KR.	B.8
1318091737	DEK 6 GW RT/SW +	B.8
1318091741	DEK 6 GW BL/SW -	B.8
1320000000		
1326660000	DEK 8 SONDERDR.WEISS	B.8
1350000000		
1358460000	DEK 5 FW 1,3,5,...99	B.7
1358560000	DEK 5 FW 2,4,...100	B.7
1358660000	DEK 6 FW 1,3,5...99	B.8
1358760000	DEK 6 FW 2,4,...100	B.8
1560000000		
1568241055	CLI C 02-3 GE/SW Å CD	C.30
1568241056	CLI C 02-3 GE/SW Ä CD	C.30
1568241057	CLI C 02-3 GE/SW Ö CD	C.30
1568241058	CLI C 02-3 GE NE CD	C.20
1568241059	CLI C 02-6 GE NE CD	C.20
1568241060	CLI C 02-9 GE NE CD	C.20
1568241502	CLI C 02-3 GE/SW 0 CD	C.29
1568241503	CLI C 02-3 SW/WS 0 CD	C.26
1568241505	CLI C 02-3 GE/SW 1 CD	C.29
1568241506	CLI C 02-3 BR/WS 1 CD	C.26
1568241508	CLI C 02-3 GE/SW 2 CD	C.29
1568241509	CLI C 02-3 RT/SW 2 CD	C.26
1568241511	CLI C 02-3 GE/SW 3 CD	C.29
1568241512	CLI C 02-3 OR/SW 3 CD	C.26
1568241514	CLI C 02-3 GE/SW 4 CD	C.26
1568241514	CLI C 02-3 GE/SW 4 CD	C.29
1568241517	CLI C 02-3 GE/SW 5 CD	C.29
1568241518	CLI C 02-3 GN/SW 5 CD	C.26
1568241520	CLI C 02-3 GE/SW 6 CD	C.29
1568241521	CLI C 02-3 BL/SW 6 CD	C.26
1568241523	CLI C 02-3 GE/SW 7 CD	C.29
1568241524	CLI C 02-3 VI/SW 7 CD	C.26
1568241526	CLI C 02-3 GE/SW 8 CD	C.29
1568241527	CLI C 02-3 GR/SW 8 CD	C.26
1568241527	CLI C 02-3 GR/SW 8 CD	C.29
1568241529	CLI C 02-3 GE/SW 9 CD	C.29
1568241530	CLI C 02-3 WS/SW 9 CD	C.26
1568241530	CLI C 02-3 WS/SW 9 CD	C.29
1568241637	CLI C 02-3 GE/SW A CD	C.29
1568241639	CLI C 02-3 GE/SW B CD	C.29
1568241641	CLI C 02-3 GE/SW C CD	C.29
1568241643	CLI C 02-3 GE/SW D CD	C.29
1568241645	CLI C 02-3 GE/SW E CD	C.29
1568241647	CLI C 02-3 GE/SW F CD	C.29
1568241649	CLI C 02-3 GE/SW G CD	C.29
1568241651	CLI C 02-3 GE/SW H CD	C.29
1568241653	CLI C 02-3 GE/SW I CD	C.29
1568241655	CLI C 02-3 GE/SW J CD	C.29
1568241657	CLI C 02-3 GE/SW K CD	C.29
1568241659	CLI C 02-3 GE/SW L CD	C.29
1568241661	CLI C 02-3 GE/SW M CD	C.29
1568241663	CLI C 02-3 GE/SW N CD	C.29
1568241664	CLI C 02-3 BL/SW N CD	C.30
1568241665	CLI C 02-3 GE/SW O CD	C.29
1568241667	CLI C 02-3 GE/SW P CD	C.29
1568241669	CLI C 02-3 GE/SW Q CD	C.29
1568241671	CLI C 02-3 GE/SW R CD	C.29
1568241673	CLI C 02-3 GE/SW S CD	C.29
1568241676	CLI C 02-3 GE/SW T CD	C.29
1568241679	CLI C 02-3 GE/SW U CD	C.29
1568241681	CLI C 02-3 GE/SW V CD	C.29
1568241683	CLI C 02-3 GE/SW W CD	C.29
1568241686	CLI C 02-3 RT NE CD	C.20
1568241687	CLI C 02-3 GE/SW X CD	C.29
1568241688	CLI C 02-3 GN NE CD	C.20
1568241689	CLI C 02-3 VI NE CD	C.20
1568241690	CLI C 02-3 OR NE CD	C.20
1568241692	CLI C 02-3 BR NE CD	C.20
1568241694	CLI C 02-3 SW NE CD	C.20
1568241695	CLI C 02-3 RS NE CD	C.20
1568241696	CLI C 02-3 GE/SW Y CD	C.29
1568241698	CLI C 02-3 GE/SW Z CD	C.29
1568241726	CLI C 02-6 GE/SW A1 CD	C.31
1568241727	CLI C 02-6 GE/SW A2 CD	C.31
1568241728	CLI C 02-6 GE/SW L1 CD	C.31
1568241729	CLI C 02-6 GE/SW L2 CD	C.31
1568241730	CLI C 02-6 GE/SW L3 CD	C.31
1568241731	CLI C 02-6 GE/SW VS CD	C.31
1568241734	CLI C 02-9 GE/SW PEN CD	C.31
1568241735	CLI C 02-3 GE/SW Æ CD	C.30
1568241736	CLI C 02-3 GE/SW Ø CD	C.30
1568241737	CLI C 02-3 RT/SW + CD	C.30
1568241738	CLI C 02-3 GE/SW + CD	C.30
1568241740	CLI C 02-3 GE/SW - CD	C.30
1568241741	CLI C 02-3 BL/SW - CD	C.30
1568241742	CLI C 02-3 GE/SW / CD	C.30
1568241746	CLI C 02-3 GE/SW ET CD	C.30
1568241747	CLI C 02-3 GE/SW PET. CD	C.30
1568241748	CLI C 02-3 GE/SW . CD	C.30
1568241750	CLI C 02-3 GE/SW : CD	C.30
1568241751	CLI C 02-3 GE/SW = CD	C.30
1568241752	CLI C 02-3 GE/SW AC CD	C.30
1568249999	CLI C 02-3 SDR CD	C.23
1568250001	CLI C 1-3 WS/SW 1 CD	C.32
1568250002	CLI C 1-3 WS/SW 2 CD	C.32
1568250003	CLI C 1-3 WS/SW 3 CD	C.32
1568250004	CLI C 1-3 WS/SW 4 CD	C.32
1568250005	CLI C 1-3 WS/SW 5 CD	C.32
1568250006	CLI C 1-3 WS/SW 6 CD	C.32
1568250007	CLI C 1-3 WS/SW 7 CD	C.32
1568250008	CLI C 1-3 WS/SW 8 CD	C.32
1568251000	CLI C 1-3 WS/SW 0 CD	C.32
1568251021	CLI C 1-3 WS/SW A CD	C.32
1568251022	CLI C 1-3 WS/SW B CD	C.32
1568251023	CLI C 1-3 WS/SW C CD	C.32
1568251024	CLI C 1-3 WS/SW D CD	C.32
1568251025	CLI C 1-3 WS/SW E CD	C.32
1568251026	CLI C 1-3 WS/SW F CD	C.32
1568251027	CLI C 1-3 WS/SW G CD	C.32
1568251028	CLI C 1-3 WS/SW H CD	C.32
1568251029	CLI C 1-3 WS/SW I CD	C.32
1568251030	CLI C 1-3 WS/SW J CD	C.32
1568251031	CLI C 1-3 WS/SW K CD	C.32

Order No.	Type	Page
1568251032	CLI C 1-3 WS/SW L CD	C.32
1568251033	CLI C 1-3 WS/SW M CD	C.32
1568251034	CLI C 1-3 WS/SW N CD	C.32
1568251035	CLI C 1-3 WS/SW O CD	C.32
1568251036	CLI C 1-3 WS/SW P CD	C.32
1568251037	CLI C 1-3 WS/SW Q CD	C.32
1568251038	CLI C 1-3 WS/SW R CD	C.32
1568251039	CLI C 1-3 WS/SW S CD	C.32
1568251040	CLI C 1-3 WS/SW T CD	C.32
1568251041	CLI C 1-3 WS/SW U CD	C.32
1568251042	CLI C 1-3 WS/SW V CD	C.32
1568251043	CLI C 1-3 WS/SW W CD	C.32
1568251044	CLI C 1-3 WS NE CD	C.21
1568251045	CLI C 1-3 WS/SW Y CD	C.32
1568251046	CLI C 1-3 WS/SW Z CD	C.32
1568251047	CLI C 1-3 WS/SW . CD	C.34
1568251048	CLI C 1-3 WS/SW + CD	C.34
1568251049	CLI C 1-3 WS/SW - CD	C.34
1568251050	CLI C 1-3 WS/SW / CD	C.34
1568251051	CLI C 1-3 WS/SW : CD	C.34
1568251052	CLI C 1-3 WS/SW = CD	C.34
1568251053	CLI C 1-3 WS/SW ET CD	C.34
1568251054	CLI C 1-3 WS/SW X CD	C.32
1568251055	CLI C 1-3 WS/SW ? CD	C.34
1568251056	CLI C 1-3 WS/SW Ä CD	C.34
1568251057	CLI C 1-3 WS/SW Ö CD	C.34
1568251058	CLI C 1-3 WS/SW PET. CD	C.34
1568251059	CLI C 1-3 WS/SW AC CD	C.34
1568251502	CLI C 1-3 GE/SW 0 CD	C.32
1568251503	CLI C 1-3 SW/WS 0 CD	C.26
1568251505	CLI C 1-3 GE/SW 1 CD	C.32
1568251506	CLI C 1-3 BR/WS 1 CD	C.26
1568251508	CLI C 1-3 GE/SW 2 CD	C.32
1568251509	CLI C 1-3 RT/SW 2 CD	C.26
1568251511	CLI C 1-3 GE/SW 3 CD	C.32
1568251512	CLI C 1-3 OR/SW 3 CD	C.26
1568251514	CLI C 1-3 GE/SW 4 CD	C.26
1568251514	CLI C 1-3 GE/SW 4 CD	C.32
1568251517	CLI C 1-3 GE/SW 5 CD	C.32
1568251518	CLI C 1-3 GN/SW 5 CD	C.26
1568251520	CLI C 1-3 GE/SW 6 CD	C.32
1568251521	CLI C 1-3 BL/SW 6 CD	C.26
1568251523	CLI C 1-3 GE/SW 7 CD	C.32
1568251524	CLI C 1-3 VI/SW 7 CD	C.26
1568251526	CLI C 1-3 GE/SW 8 CD	C.32
1568251527	CLI C 1-3 GR/SW 8 CD	C.26
1568251527	CLI C 1-3 GR/SW 8 CD	C.32
1568251529	CLI C 1-3 GE/SW 9 CD	C.32
1568251530	CLI C 1-3 WS/SW 9 CD	C.26
1568251530	CLI C 1-3 WS/SW 9 CD	C.32
1568251637	CLI C 1-3 GE/SW A CD	C.32
1568251639	CLI C 1-3 GE/SW B CD	C.32
1568251641	CLI C 1-3 GE/SW C CD	C.32
1568251643	CLI C 1-3 GE/SW D CD	C.32
1568251645	CLI C 1-3 GE/SW E CD	C.32
1568251647	CLI C 1-3 GE/SW F CD	C.32
1568251649	CLI C 1-3 GE/SW G CD	C.32
1568251651	CLI C 1-3 GE/SW H CD	C.32
1568251653	CLI C 1-3 GE/SW I CD	C.32
1568251655	CLI C 1-3 GE/SW J CD	C.32
1568251657	CLI C 1-3 GE/SW K CD	C.32
1568251659	CLI C 1-3 GE/SW L CD	C.32
1568251661	CLI C 1-3 GE/SW M CD	C.32
1568251663	CLI C 1-3 GE/SW N CD	C.32
1568251664	CLI C 1-3 BL/SW N CD	C.34
1568251665	CLI C 1-3 GE/SW O CD	C.32
1568251667	CLI C 1-3 GE/SW P CD	C.32
1568251669	CLI C 1-3 GE/SW Q CD	C.32
1568251671	CLI C 1-3 GE/SW R CD	C.32
1568251673	CLI C 1-3 GE/SW S CD	C.32
1568251676	CLI C 1-3 GE/SW T CD	C.32
1568251679	CLI C 1-3 GE/SW U CD	C.32
1568251681	CLI C 1-3 GE/SW V CD	C.32
1568251683	CLI C 1-3 GE/SW W CD	C.32
1568251686	CLI C 1-3 RT NE CD	C.21
1568251687	CLI C 1-3 GE/SW X CD	C.32
1568251688	CLI C 1-3 GN NE CD	C.21
1568251689	CLI C 1-3 VI NE CD	C.21
1568251690	CLI C 1-3 OR NE CD	C.21
1568251691	CLI C 1-3 GR NE CD	C.21
1568251692	CLI C 1-3 BR NE CD	C.21
1568251693	CLI C 1-3 BL NE CD	C.21
1568251694	CLI C 1-3 SW NE CD	C.21
1568251695	CLI C 1-3 RS NE CD	C.21
1568251696	CLI C 1-3 GE/SW Y CD	C.32
1568251698	CLI C 1-3 GE/SW Z CD	C.32
1568251699	CLI C 1-3 GE NE CD	C.21
1568251700	CLI C 1-3 GE/SW a CD	C.33
1568251701	CLI C 1-3 GE/SW b CD	C.33
1568251702	CLI C 1-3 GE/SW c CD	C.33
1568251703	CLI C 1-3 GE/SW d CD	C.33
1568251704	CLI C 1-3 GE/SW e CD	C.33
1568251705	CLI C 1-3 GE/SW f CD	C.33
1568251706	CLI C 1-3 GE/SW g CD	C.33
1568251707	CLI C 1-3 GE/SW h CD	C.33
1568251708	CLI C 1-3 GE/SW i CD	C.33
1568251709	CLI C 1-3 GE/SW j CD	C.33
1568251710	CLI C 1-3 GE/SW k CD	C.33
1568251711	CLI C 1-3 GE/SW l CD	C.33
1568251712	CLI C 1-3 GE/SW m CD	C.33
1568251713	CLI C 1-3 GE/SW n CD	C.33
1568251714	CLI C 1-3 GE/SW o CD	C.33
1568251715	CLI C 1-3 GE/SW p CD	C.33
1568251716	CLI C 1-3 GE/SW q CD	C.33
1568251717	CLI C 1-3 GE/SW r CD	C.33
1568251718	CLI C 1-3 GE/SW s CD	C.33
1568251719	CLI C 1-3 GE/SW t CD	C.33
1568251720	CLI C 1-3 GE/SW u CD	C.33
1568251721	CLI C 1-3 GE/SW v CD	C.33
1568251722	CLI C 1-3 GE/SW w CD	C.33
1568251723	CLI C 1-3 GE/SW x CD	C.33
1568251724	CLI C 1-3 GE/SW y CD	C.33
1568251725	CLI C 1-3 GE/SW z CD	C.33
1568251735	CLI C 1-3 GE/SW Æ CD	C.34
1568251736	CLI C 1-3 GE/SW Ø CD	C.34
1568251737	CLI C 1-3 RT/SW + CD	C.34
1568251738	CLI C 1-3 GE/SW + CD	C.34
1568251740	CLI C 1-3 GE/SW - CD	C.34
1568251741	CLI C 1-3 BL/SW - CD	C.34
1568251742	CLI C 1-3 GE/SW / CD	C.34
1568251746	CLI C 1-3 GE/SW ET CD	C.34
1568251747	CLI C 1-3 GE/SW PET. CD	C.34
1568251748	CLI C 1-3 GE/SW . CD	C.34
1568251750	CLI C 1-3 GE/SW : CD	C.34
1568251751	CLI C 1-3 GE/SW = CD	C.34
1568251752	CLI C 1-3 GE/SW AC CD	C.34
1568251753	CLI C 1-3 GE/SW * CD	C.34
1568251795	CLI C 1-3 GE/SW Ö CD	C.34
1568251797	CLI C 1-3 GE/SW Ä CD	C.34
1568251799	CLI C 1-3 GE/SW Å CD	C.34
1568259999	CLI C 1-3 SDR CD	C.23
1568261502	CLI C 2-4 GE/SW 0 CD	C.38
1568261503	CLI C 2-4 SW/WS 0 CD	C.26
1568261505	CLI C 2-4 GE/SW 1 CD	C.38
1568261506	CLI C 2-4 BR/WS 1 CD	C.26
1568261508	CLI C 2-4 GE/SW 2 CD	C.38
1568261509	CLI C 2-4 RT/SW 2 CD	C.26
1568261511	CLI C 2-4 GE/SW 3 CD	C.38
1568261512	CLI C 2-4 OR/SW 3 CD	C.26
1568261514	CLI C 2-4 GE/SW 4 CD	C.26
1568261514	CLI C 2-4 GE/SW 4 CD	C.38
1568261517	CLI C 2-4 GE/SW 5 CD	C.38
1568261518	CLI C 2-4 GN/SW 5 CD	C.26
1568261520	CLI C 2-4 GE/SW 6 CD	C.38
1568261521	CLI C 2-4 BL/SW 6 CD	C.26
1568261523	CLI C 2-4 GE/SW 7 CD	C.38
1568261524	CLI C 2-4 VI/SW 7 CD	C.26
1568261526	CLI C 2-4 GE/SW 8 CD	C.38
1568261527	CLI C 2-4 GR/SW 8 CD	C.26
1568261529	CLI C 2-4 GE/SW 9 CD	C.38
1568261530	CLI C 2-4 WS/SW 9 CD	C.26
1568261530	CLI C 2-4 WS/SW 9 CD	C.38
1568261637	CLI C 2-4 GE/SW A CD	C.38
1568261639	CLI C 2-4 GE/SW B CD	C.38
1568261641	CLI C 2-4 GE/SW C CD	C.38
1568261643	CLI C 2-4 GE/SW D CD	C.38
1568261645	CLI C 2-4 GE/SW E CD	C.38
1568261647	CLI C 2-4 GE/SW F CD	C.38
1568261649	CLI C 2-4 GE/SW G CD	C.38
1568261651	CLI C 2-4 GE/SW H CD	C.38
1568261653	CLI C 2-4 GE/SW I CD	C.38
1568261655	CLI C 2-4 GE/SW J CD	C.38
1568261657	CLI C 2-4 GE/SW K CD	C.38
1568261659	CLI C 2-4 GE/SW L CD	C.38
1568261661	CLI C 2-4 GE/SW M CD	C.38
1568261663	CLI C 2-4 GE/SW N CD	C.38
1568261664	CLI C 2-4 BL/SW N CD	C.39
1568261665	CLI C 2-4 GE/SW O CD	C.38
1568261667	CLI C 2-4 GE/SW P CD	C.38
1568261669	CLI C 2-4 GE/SW Q CD	C.38
1568261671	CLI C 2-4 GE/SW R CD	C.38
1568261673	CLI C 2-4 GE/SW S CD	C.38
1568261676	CLI C 2-4 GE/SW T CD	C.38
1568261679	CLI C 2-4 GE/SW U CD	C.38
1568261681	CLI C 2-4 GE/SW V CD	C.38
1568261683	CLI C 2-4 GE/SW W CD	C.38
1568261687	CLI C 2-4 GE/SW X CD	C.38
1568261695	CLI C 2-4 GE/SW Ö CD	C.39
1568261696	CLI C 2-4 GE/SW Y CD	C.38
1568261697	CLI C 2-4 GE/SW Ä CD	C.39
1568261698	CLI C 2-4 GE/SW Z CD	C.38
1568261699	CLI C 2-4 GE/SW Å CD	C.39
1568261735	CLI C 2-4 GE/SW Æ CD	C.39
1568261736	CLI C 2-4 GE/SW Ø CD	C.39
1568261737	CLI C 2-4 RT/SW + CD	C.39
1568261738	CLI C 2-4 GE/SW + CD	C.39
1568261740	CLI C 2-4 GE/SW - CD	C.39
1568261741	CLI C 2-4 BL/SW - CD	C.39
1568261742	CLI C 2-4 GE/SW / CD	C.39
1568261746	CLI C 2-4 GE/SW ET CD	C.39
1568261747	CLI C 2-4 GE/SW PET. CD	C.39
1568261748	CLI C 2-4 GE/SW . CD	C.39
1568261750	CLI C 2-4 GE/SW : CD	C.39
1568261751	CLI C 2-4 GE/SW = CD	C.39
1568261752	CLI C 2-4 GE/SW AC CD	C.39
1568269999	CLI C 2-4 SDR CD	C.24
1568300001	CLI M 2-4 GE NE CD	C.22
1568300002	CLI M 2-4 WS/SW 2 CD	C.50
1568300003	CLI M 2-4 WS/SW 3 CD	C.50
1568300004	CLI M 2-4 WS/SW 4 CD	C.50
1568300005	CLI M 2-4 WS/SW 5 CD	C.50
1568300006	CLI M 2-4 WS/SW 6 CD	C.50
1568300007	CLI M 2-4 WS/SW 7 CD	C.50
1568300008	CLI M 2-4 WS/SW 8 CD	C.50
1568301000	CLI M 2-4 WS/SW 0 CD	C.50
1568301021	CLI M 2-4 WS/SW A CD	C.50
1568301022	CLI M 2-4 WS/SW B CD	C.50
1568301023	CLI M 2-4 WS/SW C CD	C.50
1568301024	CLI M 2-4 WS/SW D CD	C.50
1568301025	CLI M 2-4 WS/SW E CD	C.50
1568301026	CLI M 2-4 WS/SW F CD	C.50
1568301027	CLI M 2-4 WS/SW G CD	C.50
1568301028	CLI M 2-4 WS/SW H CD	C.50
1568301029	CLI M 2-4 WS/SW I CD	C.50
1568301030	CLI M 2-4 WS/SW J CD	C.50
1568301031	CLI M 2-4 WS/SW K CD	C.50
1568301032	CLI M 2-4 WS/SW L CD	C.50
1568301033	CLI M 2-4 WS/SW M CD	C.50
1568301034	CLI M 2-4 WS/SW N CD	C.50
1568301035	CLI M 2-4 WS/SW O CD	C.50
1568301036	CLI M 2-4 WS/SW P CD	C.50
1568301037	CLI M 2-4 WS/SW Q CD	C.50
1568301038	CLI M 2-4 WS/SW R CD	C.50
1568301039	CLI M 2-4 WS/SW S CD	C.50
1568301040	CLI M 2-4 WS/SW T CD	C.50
1568301041	CLI M 2-4 WS/SW U CD	C.50
1568301042	CLI M 2-4 WS/SW V CD	C.50
1568301043	CLI M 2-4 WS/SW W CD	C.50
1568301044	CLI M 2-4 WS/SW X CD	C.50
1568301045	CLI M 2-4 WS/SW Y CD	C.50
1568301046	CLI M 2-4 WS/SW Z CD	C.50
1568301047	CLI M 2-4 WS/SW . CD	C.51
1568301048	CLI M 2-4 WS/SW + CD	C.51
1568301049	CLI M 2-4 WS/SW - CD	C.51
1568301050	CLI M 2-4 WS/SW / CD	C.51
1568301051	CLI M 2-4 WS NE CD	C.22
1568301052	CLI M 2-4 WS/SW = CD	C.51
1568301053	CLI M 2-4 WS/SW ET CD	C.51
1568301054	CLI M 2-4 WS/SW : CD	C.51
1568301055	CLI M 2-4 WS/SW ? CD	C.51
1568301056	CLI M 2-4 WS/SW Ä CD	C.51
1568301057	CLI M 2-4 WS/SW Ö CD	C.51
1568301058	CLI M 2-4 WS/SW PET. CD	C.51
1568301059	CLI M 2-4 WS/SW AC CD	C.51
1568301502	CLI M 2-4 GE/SW 0 CD	C.50
1568301503	CLI M 2-4 SW/WS 0 CD	C.27
1568301505	CLI M 2-4 GE/SW 1 CD	C.50
1568301506	CLI M 2-4 BR/WS 1 CD	C.27
1568301508	CLI M 2-4 GE/SW 2 CD	C.50
1568301509	CLI M 2-4 RT/SW 2 CD	C.27
1568301511	CLI M 2-4 GE/SW 3 CD	C.50
1568301512	CLI M 2-4 OR/SW 3 CD	C.27
1568301514	CLI M 2-4 GE/SW 4 CD	C.27
1568301514	CLI M 2-4 GE/SW 4 CD	C.50
1568301517	CLI M 2-4 GE/SW 5 CD	C.50
1568301518	CLI M 2-4 GN/SW 5 CD	C.27
1568301520	CLI M 2-4 GE/SW 6 CD	C.50
1568301521	CLI M 2-4 BL/SW 6 CD	C.27
1568301523	CLI M 2-4 GE/SW 7 CD	C.50
1568301524	CLI M 2-4 VI/SW 7 CD	C.27
1568301526	CLI M 2-4 GE/SW 8 CD	C.50
1568301527	CLI M 2-4 GR/SW 8 CD	C.27
1568301529	CLI M 2-4 GE/SW 9 CD	C.50
1568301530	CLI M 2-4 WS/SW 9 CD	C.27
1568301530	CLI M 2-4 WS/SW 9 CD	C.50
1568301637	CLI M 2-4 GE/SW A CD	C.50
1568301639	CLI M 2-4 GE/SW B CD	C.50
1568301641	CLI M 2-4 GE/SW C CD	C.50
1568301643	CLI M 2-4 GE/SW D CD	C.50
1568301645	CLI M 2-4 GE/SW E CD	C.50
1568301647	CLI M 2-4 GE/SW F CD	C.50
1568301649	CLI M 2-4 GE/SW G CD	C.50
1568301651	CLI M 2-4 GE/SW H CD	C.50
1568301653	CLI M 2-4 GE/SW I CD	C.50
1568301655	CLI M 2-4 GE/SW J CD	C.50
1568301657	CLI M 2-4 GE/SW K CD	C.50
1568301659	CLI M 2-4 GE/SW L CD	C.50
1568301661	CLI M 2-4 GE/SW M CD	C.50
1568301663	CLI M 2-4 GE/SW N CD	C.50
1568301664	CLI M 2-4 BL/SW N CD	C.51
1568301665	CLI M 2-4 GE/SW O CD	C.50
1568301667	CLI M 2-4 GE/SW P CD	C.50
1568301669	CLI M 2-4 GE/SW Q CD	C.50
1568301671	CLI M 2-4 GE/SW R CD	C.50
1568301673	CLI M 2-4 GE/SW S CD	C.50
1568301676	CLI M 2-4 GE/SW T CD	C.50
1568301679	CLI M 2-4 GE/SW U CD	C.50
1568301681	CLI M 2-4 GE/SW V CD	C.50
1568301683	CLI M 2-4 GE/SW W CD	C.50
1568301686	CLI M 2-4 RT NE CD	C.22
1568301687	CLI M 2-4 GE/SW X CD	C.50
1568301688	CLI M 2-4 GN NE CD	C.22
1568301689	CLI M 2-4 VI NE CD	C.22
1568301692	CLI M 2-4 BR NE CD	C.22
1568301693	CLI M 2-4 BL NE CD	C.22
1568301694	CLI M 2-4 GE/SW Ä CD	C.51
1568301695	CLI M 2-4 GE/SW Ö CD	C.51
1568301696	CLI M 2-4 GE/SW Y CD	C.50
1568301697	CLI M 2-4 WS/SW 1 CD	C.50
1568301698	CLI M 2-4 GE/SW Z CD	C.50
1568301699	CLI M 2-4 GE/SW Å CD	C.51
1568301700	CLI M 2-4 SW NE CD	C.22
1568301701	CLI M 2-4 RS NE CD	C.22
1568301735	CLI M 2-4 GE/SW Æ CD	C.51
1568301736	CLI M 2-4 GE/SW Ø CD	C.51
1568301737	CLI M 2-4 RT/SW + CD	C.51
1568301738	CLI M 2-4 GE/SW + CD	C.51
1568301740	CLI M 2-4 GE/SW - CD	C.51
1568301741	CLI M 2-4 BL/SW - CD	C.51
1568301742	CLI M 2-4 GE/SW / CD	C.51
1568301746	CLI M 2-4 GE/SW ET CD	C.51
1568301747	CLI M 2-4 GE/SW PET. CD	C.51
1568301748	CLI M 2-4 GE/SW . CD	C.51
1568301750	CLI M 2-4 GE/SW : CD	C.51
1568301751	CLI M 2-4 GE/SW = CD	C.51
1568301752	CLI M 2-4 GE/SW AC CD	C.51
1568309999	CLI M 2-4 SDR CD	C.25

1570000000

1572000000	DEK 5 FWZ 1-9	B.7
1579500000	CLI M 2-25Q SDR SG	C.25

1600000000

1600740000	CLI F 1-20 WS/GE NE	C.11
1600740000	CLI F 1-20 WS/GE NE	C.9
1603290000	LOGIMARK-KARTENHALTER	D.10
1607681044	LOGIMARK-KARTE NEUTR.WS	D.10
1607681686	LOGIMARK-KARTE NEUTR.RT	D.10
1607681687	LOGIMARK-KARTE NEUTR.GE	D.10
1607681688	LOGIMARK-KARTE NEUTR.GN	D.10
1607681689	LOGIMARK-KARTE NEUTR.VI	D.10
1607681690	LOGIMARK-KARTE NEUTR.OR	D.10
1607681691	LOGIMARK-KARTE NEUTR.GR	D.10
1607681692	LOGIMARK-KARTE NEUTR.BR	D.10
1607681693	LOGIMARK-KARTE NEUTR.BL	D.10
1607690000	LOGIMARK-KARTE BEDRUCKT	D.10
1607710000	ESO 5 DIN A4 WEISS BOG.	B.36
1607710000	ESO 5 DIN A4 WEISS BOG.	C.13
1607720000	ESO 7 A4-BOGEN WEISS	B.36
1607720000	ESO 7 A4-BOGEN WEISS	B.38
1607720000	ESO 7 A4-BOGEN WEISS	B.39
1607720000	ESO 7 A4-BOGEN WEISS	C.13
1609801044	DEK 5/5 MC-10 NEUT. WS	B.11
1609801044	DEK 5/5 MC-10 NEUT. WS	B.35
1609801044	DEK 5/5 MC-10 NEUT. WS	B.36
1609801044	DEK 5/5 MC-10 NEUT. WS	B.37
1609801044	DEK 5/5 MC-10 NEUT. WS	B.38
1609801044	DEK 5/5 MC-10 NEUT. WS	B.39
1609801686	DEK 5/5 MC-10 NEUT. RT	B.11
1609801687	DEK 5/5 MC-10 NEUT. GE	B.11
1609801688	DEK 5/5 MC-10 NEUT. GN	B.11
1609801691	DEK 5/5 MC-10 NEUT. GR	B.11
1609801693	DEK 5/5 MC-10 NEUT. BL	B.11
1609810000	DEK 5/5 MC BEDRUCKT	B.11
1609820000	DEK 5/6 MC NEUTRAL	B.11
1609830000	DEK 5/6 MC BEDRUCKT	B.11
1609840000	DEK 5/6,5 MC NEUTRAL	B.11
1609850000	DEK 5/6,5 MC BEDRUCKT	B.11
1609860000	WS 12/5 MC NEUTRAL	B.14
1609860000	WS 12/5 MC NEUTRAL	B.37
1609860000	WS 12/5 MC NEUTRAL	B.38
1609860000	WS 12/5 MC NEUTRAL	B.39
1609870000	WS 12/5 MC BEDRUCKT	B.14
1609880000	WS 15/5 MC NEUTRAL	B.14
1609890000	WS 15/5 MC BEDRUCKT	B.14
1609900000	WS 12/6 MC NEUTRAL	B.14
1609910000	WS 12/6 MC BEDRUCKT	B.15
1609920000	WS 12/6,5 MC NEUTRAL	B.15
1609930000	WS 12/6,5 MC BEDRUCKT	B.15
1609940000	ESG 9/20 MC NEUTRAL WS	D.4
1609950000	ESG 9/20 MC BEDRUCKT	D.4
1609981044	TM-I 15 NEUTRAL WS	C.9
1609981686	TM-I 15 NEUTRAL RT	C.9
1609981687	TM-I 15 NEUTRAL GE	C.9
1609981688	TM-I 15 NEUTRAL GN	C.9
1609981693	TM-I 15 NEUTRAL BL	C.9
1609990000	TM-I 15 SONDERDRUCK	C.9

1610000000

1610000000	ZS 10/5 MC NEUTRAL	B.15
1610010000	ZS 10/5 MC BEDRUCKT	B.15
1610020000	ZS 12/6 MC NEUTRAL	B.15
1610030000	ZS 12/6 BEDRUCKT	B.15
1610700000	WKM 18/43	C.13
1611930000	ZGB 30	B.39

1620000000

1629900000	KSW 2.5 < 50MM SDR	D.18
1629910000	KSW 4 < 50MM SDR	D.19
1629920000	KSW 2,5 <100MM SONDDR.	D.18
1629930000	KSW 4 < 100MM SDR	D.19
1629940000	KSW 2,5 <150MM SONDDR.	D.18
1629950000	KSW 4 <150MM SONDDR.	D.19
1629960000	KSW 2,5 <50MM NEUTRAL	D.18
1629970000	KSW 4 <50MM NEUTRAL	D.19
1629980000	KSW 2,5 <100MM NEUTRAL	D.18

Order No.	Type	Page
1629990000	KSW 4 <100MM NEUTRAL	D.19

1630000000

1630000000	KSW 2,5 <150MM NEUTRAL	D.18
1630010000	KSW 4 <150MM NEUTRAL	D.19
1630020001	KSW 2,5 10/5,08 1-10	D.17
1630020011	KSW 2,5 10/5,08 11-20	D.17
1630030101	KSW 2,5 10/7,5 101-200	D.17
1630030201	KSW 2,5 10/7,5 201-300	D.17
1630030301	KSW 2,5 10/7,5 301-400	D.17
1630030401	KSW 2,5 10/7,5 401-500	D.17
1630040001	KSW 2,5 10/7,5 1-10 FWZ	D.17
1630050001	KSW 2,5 15/5,08 1-150	D.17
1630050151	KSW 2,5 15/5,08 151-300	D.17
1630050301	KSW 2,5 15/5,08 301-450	D.17
1630060001	KSW 2,5 15/5,08 1-15FWZ	D.17
1630070001	KSW 2,5 16/5 1-16	D.17
1630080001	KSW 2,5 20/5 1-20	D.17
1630080021	KSW 2,5 20/5 21-40	D.17
1630080041	KSW 2,5 20/5 41-60	D.17
1630080061	KSW 2,5 20/5 61-80	D.17
1630090001	KSW 2,5 4/10,16 1-4	D.19
1630100001	KSW 2,5 8/5,08 1-8	D.17
1630100009	KSW 2,5 8/5,08 9-16	D.17
1630101021	KSW 2,5 8/5,08 A-H	D.17
1630130001	KSW 4 12/5 1-12	D.18
1630130013	KSW 4 12/5 W 13-24	D.18
1630140001	KSW 4 12/7,5 1-12	D.19
1630140013	KSW 4 12/7,5 13-24	D.19
1630140025	KSW 4 12/7,5 25-36	D.19
1630140037	KSW 4 12/7,5 37-48	D.19
1630140049	KSW 4 12/7,5 49-60	D.19
1630150001	KSW 4 16/3,5 1-16	D.18
1630150017	KSW 4 16/3,5 17-32	D.18
1630160001	KSW 4 16/5,08 1-16	D.18
1630160017	KSW 4 16/5,08 17-32	D.18
1630160033	KSW 4 16/5,08 33-48	D.18
1630160049	KSW 4 16/5,08 49-64	D.18
1630160065	KSW 4 16/5,08 65-80	D.18
1630160081	KSW 4 16/5,08 81-96	D.18
1630170001	KSW 4 18/5 1-18	D.18
1630180001	KSW 4 24/5,08 1-24	D.18
1630190001	KSW 4 8/3,5 1-8	D.18
1630200001	KSW 4 8/5,08 1-8	D.18
1630200009	KSW 4 8/5,08 9-16	D.18
1630200017	KSW 4 8/5,08 17-24	D.18
1630200025	KSW 4 8/5,08 25-32	D.18
1630200033	KSW 4 8/5,08 33-40	D.18
1630200041	KSW 4 8/5,08 41-48	D.18
1631350000	ESO 5 DIN A4 GELB BOG.	B.36
1631350000	ESO 5 DIN A4 GELB BOG.	C.13
1631640001	LOGIMARK-K.HALTER ES	D.10
1631640002	LOGIMARK-K.HALTER ES	D.10
1631640003	LOGIMARK-K.HALTER ES	D.10
1631910000	WKM 8/30	C.13
1631920000	ESO 5 S DIN A4-BOGEN	B.36
1631930000	SCHT 5 S	B.36
1631940000	STR 5 S F.SCHT 5 S	B.36
1634780000	ESO 7 A4-BOGEN GELB	B.36
1634780000	ESO 7 A4-BOGEN GELB	B.38
1634780000	ESO 7 A4-BOGEN GELB	B.39
1634780000	ESO 7 A4-BOGEN GELB	C.13
1634790000	CLI M 2-40Q SDR SG	C.25
1635000000	WS 10/5 MC NEUTRAL	B.14
1635000000	WS 10/5 MC NEUTRAL	B.35
1635010000	WS 10/5 MC BEDRUCKT	B.14
1636510000	ESO 15 BOGEN DIN A4	B.39
1636520000	STR 15 F. ZGB 15	B.39
1636530000	ZGB 15	B.39

1640000000

1640410001	KSW 4 24/3,5 W 1-24	D.18
1640740000	WS 8/5 MC NEUTRAL	B.14
1640750000	WS 8/5 MC BEDRUCKT	B.14
1646630000	ZS 15/5 MC NEUTRAL	B.15
1646640000	ZS 15/5 MC BEDRUCKT	B.15

1650000000

1652220000	ESG 8/19 MC NEUTRAL	D.4
1652230000	ESG 8/19 MC BEDRUCKT	D.4
1652250001	KSW 2,5 24/3,5 1-24	D.17
1652250025	KSW 2,5 24/3,5 25-48	D.17
1652260001	KSW 2,5 16/3,5 1-16	D.17
1652270001	KSW 4 12/7,62 1-12	D.19
1652270013	KSW 4 12/7,62 13-24	D.19
1653340001	DEK 8 FW 1-50 TAMPOPR.	B.8
1653340051	DEK 8 FW 51-100 TAMPOP.	B.8
1653350001	DEK 8 FS 1-50 TAMPOPR.	B.8
1653350051	DEK 8 FS 51-100 TAMPOP.	B.8

1660000000

1667700000	WAD 8 SONDERDRUCK	B.38

1670000000

1670370000	ESO 5 POLY.WEISS A4-BOG.	B.36
1670370000	ESO 5 POLY.WEISS A4-BOG.	C.13
1670380000	ESO 5 POLY.GELB A4-BOG.	B.36
1670380000	ESO 5 POLY.GELB A4-BOG.	C.13
1670390000	ESO 7 POLY.WEISS A4-BOG.	B.36
1670390000	ESO 7 POLY.WEISS A4-BOG.	B.38
1670390000	ESO 7 POLY.WEISS A4-BOG.	B.39
1670390000	ESO 7 POLY.WEISS A4-BOG.	C.13
1670400000	ESO 7 POLY.GELB A4-BOG.	B.36
1670400000	ESO 7 POLY.GELB A4-BOG.	B.38
1670400000	ESO 7 POLY.GELB A4-BOG.	B.39
1670400000	ESO 7 POLY.GELB A4-BOG.	C.13
1670780001	KSW 4 5/7 W 1-5	D.18
1674740000	ESG 8/17 MC NEUTRAL	D.4
1674750000	ESG 8/17 MC BEDRUCKT	D.4
1674760000	ESG 9/17 K NEUTRAL/WS	D.4
1674770000	ESG 9/17 K SONDERDRUCK	D.4
1675111044	LOGIM.KARTE 1/2 WS NEUT	D.10
1675111686	LOGIM.KARTE 1/2 RT NEUT	D.10
1675111687	LOGIM.KARTE 1/2 GE NEUT	D.10
1675111688	LOGIM.KARTE 1/2 GN NEUT	D.10
1675111689	LOGIM.KARTE 1/2 VI NEUT	D.10
1675111690	LOGIM.KARTE 1/2 OR NEUT	D.10
1675111691	LOGIM.KARTE 1/2 GR NEUT	D.10
1675111692	LOGIM.KARTE 1/2 BR NEUT	D.10
1675111693	LOGIM.KARTE 1/2 BL NEUT	D.10
1675120000	LOGIM.KARTE 1/2 BEDR.	D.10
1675130001	LOGIMARKHALTER 1/2 SW	D.10
1675130002	LOGIMARKHALTER 1/2 GRAU	D.10
1676710001	KSW 2,5 10/9 W 1-10	D.17
1676710011	KSW 2,5 10/9 W 11-20	D.17
1676710021	KSW 2,5 10/9 W 21-30	D.17
1677140000	MF 8/5 MC NEUTRAL	B.18
1677150000	MF 8/5 MC SONDERDRUCK	B.18
1677160000	MF 10/5 MC NEUTRAL	B.18
1677170000	MF 10/5 MC SONDERDRUCK	B.18
1677180000	MF 12/5 MC NEUTRAL	B.18
1677190000	MF 12/5 MC SONDERDRUCK	B.18
1677220000	MF 10/6 MC NEUTRAL	B.19
1677230000	MF 10/6 MC SONDERDRUCK	B.19

1680000000

1680411044	TM-I 20 NEUTRAL WS	C.9
1680411686	TM-I 20 NEUTRAL RT	C.9
1680411687	TM-I 20 NEUTRAL GE	C.9
1680411688	TM-I 20 NEUTRAL GN	C.9
1680411693	TM-I 20 NEUTRAL BL	C.9
1680420000	TM-I 20 SONDERDRUCK	C.9
1685690001	SYMBOL-PACK 14X14 SYMB.	D.14
1685690002	SYMBOL-PACK 14X14 ERDE	D.14
1685700000	SYMBOL-PACK 9X19 SYMB.	D.14
1686110000	TABPACK 14X9	D.15
1686120000	TABPACK 15X6	D.15
1686130000	TABPACK 19X11 M. RAND	D.15
1686140000	TABPACK 21X8	D.15
1686150000	TABPACK 38X11 M. RAND	D.15
1686160000	PAGETAB 15X9	D.15
1686170000	PAGETAB 19X11	D.15
1686180000	PAGETAB 20X8	D.15
1686190000	PAGETAB 28X11	D.15
1686200000	PAGETAB 38X11	D.15
1686210000	PAGETAB 56X22	D.15
1686220000	PAGETAB 60X35	D.15
1686360001	LM MT300 15X6 SI I	D.11
1686361044	LM MT300 15X6 WS	D.11
1686361687	LM MT300 15X6 GE	D.11
1686380001	LM MT300 20X8 SI	D.11
1686381044	LM MT300 20X8 WS	D.11
1686381687	LM MT300 20X8 GE	D.11
1686390001	LM MT300 25,4X12,7 SI	D.11
1686391044	LM MT300 25,4X12,7 WS	D.11
1686391687	LM MT300 25,4X12,7 GE	D.11
1686400001	LM MT300 26X10 SI	D.11
1686401044	LM MT300 26X10 WS	D.11
1686401687	LM MT300 26X10 GE	D.11
1686420001	LM MT300 56X22 SI	D.11
1686421044	LM MT300 56X22 WS	D.11
1686421687	LM MT300 56X22 GE	D.11
1686430001	LM MT300 60X36 SI	D.11
1686431044	LM MT300 60X36 WS	D.11
1686431687	LM MT300 60X36 GE	D.11
1686440001	LM MT300 210X297 SI	D.11
1686441044	LM MT300 210X297 WS	D.11
1686441687	LM MT300 210X297 GE	D.11
1686920000	PRINT KIT	E.7
1686920000	PRINT KIT	E.7

1690000000

1692270000	MF-WO 12/5 MC NEUTRAL	B.18
1692280000	MF-WO 12/5 MC SONDERDR.	B.18
1692290000	MF-WO 12/6 MC NEUTRAL	B.19
1692300000	MF-WO 12/6 MC SONDERDR.	B.19
1695711044	LM WRITE ON 18X34 WS	C.17
1695711687	LM WRITE ON 18X34 GE	C.17
1695721044	LM WRITE ON 23X55 WS	C.17
1695721687	LM WRITE ON 23X55 GE	C.17
1695731044	LM WRITE ON 25X68 WS	C.17
1695731687	LM WRITE ON 25X68 GE	C.17
1695741044	LM WRITE ON 36X93 WS	C.17
1695741687	LM WRITE ON 36X93 GE	C.17
1697890000	CB 98/2.5 BLACK	C.59
1697900000	CB 140/3.6 BLACK	C.59
1697910000	CB 200/4.8 BLACK	C.59
1697920000	CB 290/4.8 BLACK	C.59
1697930000	CB 360/4.8 BLACK	C.59
1697940000	CB 365/7.8 BLACK	C.59
1697950000	CBH 19/19 BLACK	C.60
1697960000	CBH 26.3/26.3 BLACK	C.60
1699800000	SCT 4 ,6/127 C	C.57
1699810000	SCT 4,6/201 C	C.57
1699820000	SM 27/8 NEUTRAL WS	D.6
1699830000	SM 27/8 SONDERDRUCK	D.6
1699840000	SM 27/12.5 NEUTRAL WS	D.6
1699850000	SM 27/12.5 SONDERDRUCK	D.6
1699860000	SM 27/18 NEUTRAL WS	D.6
1699870000	SM 27/18 SONDERDRUCK	D.6
1699880000	SM 27/12.5 K WS NEUTR.	D.6
1699890000	SM 27/12.5 K SONDERDRUCK	D.6
1699900000	SCT 4,6/266C	C.57
1699910000	SCT 4,6/360 C	C.57
1699920000	SCT 4,6/520	C.57
1699930000	SCT 4,6/679	C.57
1699940000	SCT 4,6/838	C.57

1700000000

1700530001	MARKO-C. 25X25X25 B/DR.	D.14
1700540001	MARKO-C. 50X50X50 B/DR.	D.14
1700550001	MARKO-C.100X100X100 B/DR	D.14
1700560001	MARKO-C.200X200X200 B/DR	D.14
1700660001	KSW 2,5 8/5,00 W 1-8	D.17
1700670001	KSW 4 8/5,00 W 1-8	D.18
1700680001	KSW 4 8/7,62 W 1-8	D.19
1700690001	KSW 4 8/7,5 W 1-8	D.19
1700700001	KSW 4 16/5,00 W 1-16	D.18
1700710001	KSW 4 24/5,00 W 1-24	D.18
1705820001	KSW 4 10/5,08 W 1-10	D.18
1705820011	KSW 4 10/5,08 W 11-20	D.18
1705820021	KSW 4 10/5,08 W 21-30	D.18
1705820031	KSW 4 10/5,08 W 31-40	D.18
1705820041	KSW 4 10/5,08 W 41-50	D.18
1705820051	KSW 4 10/5,08 W 51-60	D.18
1705820061	KSW 4 10/5,08 W 61-70	D.18
1705820071	KSW 4 10/5,08 W 71-80	D.18
1705820081	KSW 4 10/5,08 W 81-90	D.18
1705820091	KSW 4 10/5,08 W 91-100	D.18
1707270000	SM 27/18 K WS NEUTR.	D.6
1707280000	SM 27/18 K SONDERDRUCK	D.6
1707350001	SERV-P. DIAM16 L1 SW/WS	D.14
1707350002	SERV-P. DIAM16 L2 SW/WS	D.14
1707350003	SERV-P. DIAM16 L3 SW/WS	D.14
1707350004	SERV-P. DIAM16 N BL/WS	D.14
1707350005	SERV-P.DIAM16ERDE GE/GN	D.14
1707350006	SERV-P. DIAM16 PE GE/GN	D.14

1710000000

1712491044	LM WRITE ON 25X140 WS	C.17
1712491687	LM WRITE ON 25X140 GE	C.17
1712500001	WSM 10 1	C.56
1712500002	WSM 10 2	C.56
1712500003	WSM 10 3	C.56
1712500004	WSM 10 4	C.56
1712500005	WSM 10 5	C.56
1712500006	WSM 10 6	C.56
1712500007	WSM 10 7	C.56
1712500008	WSM 10 8	C.56
1712500009	WSM 10 9	C.56
1712501000	WSM 10 0	C.56
1712501053	WSM 10 ERDE	C.56
1712501054	WSM 10 Ä	C.56
1712501055	WSM 10 Ö	C.56
1712501056	WSM 10 ~	C.56
1712501637	WSM 10 A	C.56
1712501639	WSM 10 B	C.56
1712501641	WSM 10 C	C.56
1712501643	WSM 10 D	C.56
1712501645	WSM 10 E	C.56
1712501647	WSM 10 F	C.56
1712501649	WSM 10 G	C.56
1712501651	WSM 10 H	C.56
1712501653	WSM 10 I	C.56
1712501655	WSM 10 J	C.56
1712501657	WSM 10 K	C.56
1712501659	WSM 10 L	C.56
1712501661	WSM 10 M	C.56
1712501663	WSM 10 N	C.56
1712501665	WSM 10 O	C.56
1712501667	WSM 10 P	C.56
1712501669	WSM 10 Q	C.56
1712501670	WSM 10 Ø	C.56
1712501671	WSM 10 R	C.56
1712501672	WSM 10 Æ	C.56
1712501673	WSM 10 S	C.56
1712501676	WSM 10 T	C.56
1712501679	WSM 10 U	C.56
1712501681	WSM 10 V	C.56
1712501683	WSM 10 W	C.56
1712501687	WSM 10 X	C.56
1712501696	WSM 10 Y	C.56
1712501698	WSM 10 Z	C.56
1712501699	WSM 10 Ü	C.56
1712501700	WSM 10 Å	C.56
1712501738	WSM 10 +	C.56
1712501739	WSM 10 /	C.56
1712501740	WSM 10 -	C.56
1712501741	WSM 10 :	C.56
1712501742	WSM 10 =	C.56
1712501743	WSM 10 .	C.56
1712501744	WSM 10 (	C.56
1712502000	WSM 10 NEUTRAL	C.56
1713680000	SM 27/8 NEUTRAL SI	D.6
1713690000	SM 27/8 K SONDERDRUCK	D.6
1713700000	SM 27/12.5 NEUTRAL SI	D.6
1713720000	SM 27/12.5 K SI NEUTRAL	D.6
1713740000	SM 27/18 NEUTRAL SI	D.6
1713760000	SM 27/18 K NEUTRAL SI	D.6
1713970001	KSW 2,5 16/5,08 W 1-16	D.17
1713970017	KSW 2,5 16/5,08 W 17-32	D.17
1713970033	KSW 2,5 16/5,08 W 33-48	D.17
1713980001	KSW 2,5 24/5,00 W 1-24	D.17
1713990001	KSW 2,5 24/5,08 W 1-24	D.17
1714060001	KSW 4 9/7,00 W 1-9	D.18
1714070001	KSW 4 10/7,00 W 1-10	D.18
1714080001	KSW 4 10/9,00 W 1-10	D.19
1716630000	SM-H 27/18 SW	D.7
1716640000	SM-H 27/12.5 SW	D.7
1716800000	MF-WO 5/5 MC NEUTRAL	B.18
1716810000	MF-WO 5/5 MC SONDERDR.	B.18
1716820000	MF-WO 9/6 MC NEUTRAL	B.19
1716830000	MF-WO 9/6 MC SONDERDR.	B.19
1716840000	MF-WO 9/5 MC NEUTRAL	B.18
1716850000	MF-WO 9/5 MC SONDERDR.	B.18
1718411044	TM-I 12 NEUTRAL WS	C.9
1718411686	TM-I 12 NEUTRAL RT	C.9
1718411687	TM-I 12 NEUTRAL GE	C.9
1718411688	TM-I 12 NEUTRAL GN	C.9
1718411693	TM-I 12 NEUTRAL BL	C.9
1718420000	TM-I 12 SONDERDRUCK	C.9
1718431044	TM-I 18 NEUTRAL WS	C.11
1718431044	TM-I 18 NEUTRAL WS	C.9
1718431686	TM-I 18 NEUTRAL RT	C.9
1718431687	TM-I 18 NEUTRAL GE	C.9
1718431688	TM-I 18 NEUTRAL GN	C.9
1718431693	TM-I 18 NEUTRAL BL	C.9
1718440000	TM-I 18 SONDERDRUCK	C.9
1719760000	TM 0/12 HF/HB	C.10
1719770000	TM 0/18 HF/HB	C.10
1719780000	TM 1/12 HF/HB	C.10
1719790000	TM 1/18 HF/HB	C.10
1719800000	TM 2/12 HF/HB	C.10
1719810000	TM 2/18 HF/HB	C.10
1719820000	TM 3/12 HF/HB	C.10
1719830000	TM 3/18 HF/HB	C.10
1719840000	TM 4/12 HF/HB	C.10
1719850000	TM 4/18 HF/HB	C.10
1719860000	TM 5/12 HF/HB	C.10
1719870000	TM 5/18 HF/HB	C.10
1719880000	TM 6/12 HF/HB	C.10
1719890000	TM 6/18 HF/HB	C.10

1720000000

1720530001	KSW 4 18/5,08 W 1-36	D.18
1720570000	ETO SM 27/8	D.7
1720580000	ETO SM 27/12,5	D.7
1720590002	ETO SM 27/18 TRANSPAR.	D.7
1720600000	SCHS 2 SK F. ESG	D.5
1720610000	ESG 8/17 SCHS MC NEUTR.	D.4
1720620000	DEK 5/7.5 MC NEUTRAL	B.11
1720630000	CB 200/3.6 NATUR	C.59
1720640000	CB 290/3.6 NATUR	C.59
1720650000	CB 290/3.6 BLACK	C.59
1720660000	CB 200/3.6 BLACK	C.59
1720670000	CB 750/7.8 BLACK	C.59
1720680000	CB 750/7.8 NATUR	C.59
1723540000	CB 160/4.5 NATUR	C.59
1723550000	CB 178/4.8 NATUR	C.59
1723560000	CB 160/4.8 BLACK	C.59
1723570000	CB 178/4.8 BLACK	C.59
1724140001	LM MT300 15X4,63 SI	D.11
1724141044	LM MT300 15X4,63 WS	D.11
1724141687	LM MT300 15X4,63 GE	D.11
1724150001	LM MT300 17X9 SI	D.11
1724151044	LM MT300 17X9 WS	D.11
1724151687	LM MT300 17X9 GE	D.11
1724160001	LM MT300 30X20 SI	D.11
1724161044	LM MT300 30X20 WS	D.11
1724161687	LM MT300 30X20 GE	D.11
1724170001	LM MT300 105X148 SI	D.11
1724171044	LM MT300 105X148 WS	D.11
1724171687	LM MT300 105X148 GE	D.11
1724180001	LM MT300 210X148 SI	D.11
1724181044	LM MT300 210X148 WS	D.11
1724181687	LM MT300 210X148 GE	D.11
1724760000	ESG 9/17 MC NEUTRAL	C.11
1724760000	ESG 9/17 MC NEUTRAL	D.4

Order No.	Type	Page

1730000000

1733650004	CLI M 2-4 GE NE MP	C.22
1733651502	CLI M 2-4 GE/SW 0 MP	C.50
1733651503	CLI M 2-4 SW/WS 0 MP	C.27
1733651505	CLI M 2-4 GE/SW 1 MP	C.50
1733651506	CLI M 2-4 BR/WS 1 MP	C.27
1733651508	CLI M 2-4 GE/SW 2 MP	C.50
1733651509	CLI M 2-4 RT/SW 2 MP	C.27
1733651511	CLI M 2-4 GE/SW 3 MP	C.50
1733651512	CLI M 2-4 OR/SW 3 MP	C.27
1733651514	CLI M 2-4 GE/SW 4 MP	C.27
1733651514	CLI M 2-4 GE/SW 4 MP	C.50
1733651517	CLI M 2-4 GE/SW 5 MP	C.50
1733651518	CLI M 2-4 GN/SW 5 MP	C.27
1733651520	CLI M 2-4 GE/SW 6 MP	C.50
1733651521	CLI M 2-4 BL/SW 6 MP	C.27
1733651523	CLI M 2-4 GE/SW 7 MP	C.50
1733651524	CLI M 2-4 VI/SW 7 MP	C.27
1733651526	CLI M 2-4 GE/SW 8 MP	C.50
1733651527	CLI M 2-4 GR/SW 8 MP	C.27
1733651529	CLI M 2-4 GE/SW 9 MP	C.50
1733651530	CLI M 2-4 WS/SW 9 MP	C.27
1733651530	CLI M 2-4 WS/SW 9 MP	C.50
1733651637	CLI M 2-4 GE/SW A MP	C.50
1733651639	CLI M 2-4 GE/SW B MP	C.50
1733651641	CLI M 2-4 GE/SW C MP	C.50
1733651643	CLI M 2-4 GE/SW D MP	C.50
1733651645	CLI M 2-4 GE/SW E MP	C.50
1733651647	CLI M 2-4 GE/SW F MP	C.50
1733651649	CLI M 2-4 GE/SW G MP	C.50
1733651651	CLI M 2-4 GE/SW H MP	C.50
1733651653	CLI M 2-4 GE/SW I MP	C.50
1733651655	CLI M 2-4 GE/SW J MP	C.50
1733651657	CLI M 2-4 GE/SW K MP	C.50
1733651659	CLI M 2-4 GE/SW L MP	C.50
1733651661	CLI M 2-4 GE/SW M MP	C.50
1733651663	CLI M 2-4 GE/SW N MP	C.50
1733651664	CLI M 2-4 BL/SW N MP	C.51
1733651665	CLI M 2-4 GE/SW O MP	C.50
1733651667	CLI M 2-4 GE/SW P MP	C.50
1733651669	CLI M 2-4 GE/SW Q MP	C.50
1733651671	CLI M 2-4 GE/SW R MP	C.50
1733651673	CLI M 2-4 GE/SW S MP	C.50
1733651676	CLI M 2-4 GE/SW T MP	C.50
1733651679	CLI M 2-4 GE/SW U MP	C.50
1733651681	CLI M 2-4 GE/SW V MP	C.50
1733651683	CLI M 2-4 GE/SW W MP	C.50
1733651687	CLI M 2-4 GE/SW X MP	C.50
1733651695	CLI M 2-4 GE/SW Ö MP	C.51
1733651696	CLI M 2-4 GE/SW Y MP	C.50
1733651697	CLI M 2-4 GE/SW Ä MP	C.51
1733651698	CLI M 2-4 GE/SW Z MP	C.50
1733651699	CLI M 2-4 GE/SW Å MP	C.51
1733651737	CLI M 2-4 RT/SW + MP	C.51
1733651738	CLI M 2-4 GE/SW + MP	C.51
1733651740	CLI M 2-4 GE/SW - MP	C.51
1733651741	CLI M 2-4 BL/SW - MP	C.51
1733651742	CLI M 2-4 GE/SW / MP	C.51
1733651746	CLI M 2-4 GE/SW ET MP	C.51
1733651747	CLI M 2-4 GE/SW PET. MP	C.51
1733651748	CLI M 2-4 GE/SW . MP	C.51
1733651750	CLI M 2-4 GE/SW : MP	C.51
1733651751	CLI M 2-4 GE/SW = MP	C.51
1733651752	CLI M 2-4 GE/SW AC MP	C.51
1736181044	ESG 7/20 SIRIUS WS	C.13
1736181044	ESG 7/20 SIRIUS WS	D.4
1736181687	ESG 7/20 SIRIUS GE	D.4
1736181696	ESG 7/20 SIRIUS TUERKIS	C.13
1736181696	ESG 7/20 SIRIUS TUERKIS	D.4
1736190000	ESG 8/10 ASI	D.4

1740000000

1741090000	SYMBOL-P. 25X25X25 B/DR	D.14
1741100000	SYMBOL-P. 50X50X50 B/DR	D.14
1741110000	SYMBOL-P. 75X75X75 B/DR	D.14
1741260001	MC-Mobilo 110V/220V	E.7
1747320001	SFC 1/12 NEUTRAL WS	C.7
1747320002	SFC 1/12 NEUTRAL BL	C.7
1747320003	SFC 1/12 NEUTRAL RT	C.7
1747320004	SFC 1/12 NEUTRAL GE	C.7
1748820000	TMX 18 HF/HB	C.10
1749320001	LM MT300 18X6,5 SI	D.11
1749321044	LM MT300 18X6,5 WS	D.11
1749321687	LM MT300 18X6,5 GE	D.11

1750000000

1751561044	THM WRITEON 25/140 WS	C.17
1751561687	THM WRITEON 25/140 GE	C.17
1751750001	THM MT30X 25/12 SI/M	D.12
1751751044	THM MT30X 25/12 WS/M	D.12
1751751687	THM MT30X 25/12 GE/M	D.12
1751760001	THM MT30X 26/10 SI/M	D.12
1751761044	THM MT30X 26/10 WS/M	D.12
1751761687	THM MT30X 26/10 GE/M	D.12
1751770001	THM MT30X 32/9 SI/M	D.12
1751771044	THM MT30X 32/9 WS/M	D.12
1751800001	THM MT30X 38/19 SI/M	D.12
1751801044	THM MT30X 38/19 WS/M	D.12
1751801687	THM MT30X 38/19 GE/M	D.12
1751810001	THM MT30X 45/23 SI/M	D.12
1751811044	THM MT30X 45/23 WS/M	D.12
1751811687	THM MT30X 45/23 GE/M	D.12
1751820001	THM MT30X 101/48 SI/M	D.12
1751821044	THM MT30X 101/48 WS/M	D.12
1751821687	THM MT30X 101/48 GE/M	D.12
1751830001	THM MT30X 65/35 SI/M	D.12
1751831044	THM MT30X 65/35 WS/M	D.12
1751831687	THM MT30X 65/35 GE/M	D.12
1752720000	SFC 1/12 SONDERDRUCK	C.7
1753230001	THM MT30X 15/6 SI/M	D.12
1753231044	THM MT30X 15/6 WS/M	D.12
1753231687	THM MT30X 15/6 GE/M	D.12
1753240001	THM MT30X 20/8 SI/M	D.12
1753241044	THM MT30X 20/8 WS/M	D.12
1753241687	THM MT30X 20/8 GE/M	D.12
1753250001	THM MT30X 18/9 SI/M	D.12
1753251044	THM MT30X 18/9 WS/M	D.12
1753251687	THM MT30X 18/9 GE/M	D.12
1753260001	THM MT30X 30/20 SI/M	D.12
1753261044	THM MT30X 30/20 WS/M	D.12
1753261687	THM MT30X 30/20 GE/M	D.12
1753270001	THM MT30X 18/6 SI/M	D.12
1753271044	THM MT30X 18/6 WS/M	D.12
1753271687	THM MT30X 18/6 GE/M	D.12
1753460000	SCHS4 K	D.5
1753480000	SCHS3 K	D.5
1753490000	WKM 8/20	C.13
1753500000	ESG 9/17 K NEUTRAL/GE	D.4
1755100000	LOGIMARK DKB 81/23	D.10
1755110000	LOGIMARK DKB 81/50	D.10
1755270000	DEK 5/3,5 MC NEUTRAL	B.11
1755280001	DEK 5/3,5 MC GW 1	B.8
1755280002	DEK 5/3,5 MC GW 2	B.8
1755280003	DEK 5/3,5 MC GW 3	B.8
1755280004	DEK 5/3,5 MC GW 4	B.8
1755280005	DEK 5/3,5 MC GW 5	B.8
1755280006	DEK 5/3,5 MC GW 6	B.8
1755280007	DEK 5/3,5 MC GW 7	B.8
1755280008	DEK 5/3,5 MC GW 8	B.8
1755280009	DEK 5/3,5 MC GW 9	B.8
1755281000	DEK 5/3,5 MC GW 0	B.8
1755340000	ESG 8/17 SYS PRO M	D.4
1755350000	ESG 8/17 SYS PRO M BED.	D.4
1758320001	SFC 2/12 NEUTRAL WS	C.7
1758320002	SFC 2/12 NEUTRAL BL	C.7
1758320003	SFC 2/12 NEUTRAL RT	C.7
1758320004	SFC 2/12 NEUTRAL GE	C.7
1759871044	LM WRITE ON 15X70 WS	C.17

1760000000

1760461044	LM MT300 40X6 WS	D.11
1762320001	DEK 5/3,5 MC FSZ 1-10	B.8
1762320011	DEK 5/3,5 MC FSZ 11-20	B.8
1762320021	DEK 5/3,5 MC FSZ 21-30	B.8
1762320031	DEK 5/3,5 MC FSZ 31-40	B.8
1762320041	DEK 5/3,5 MC FSZ 41-50	B.8
1762320051	DEK 5/3,5 MC FSZ 51-60	B.8
1762320061	DEK 5/3,5 MC FSZ 61-70	B.8
1762320071	DEK 5/3,5 MC FSZ 71-80	B.8
1762320081	DEK 5/3,5 MC FSZ 81-90	B.8
1762320091	DEK 5/3,5 MC FSZ 91-100	B.8
1762320101	DEK 5/3,5 MC FSZ 101-110	B.8
1762320111	DEK 5/3,5 MC FSZ 111-120	B.8
1762320121	DEK 5/3,5 MC FSZ 121-130	B.8
1762320131	DEK 5/3,5 MC FSZ 131-140	B.8
1762320141	DEK 5/3,5 MC FSZ 141-150	B.8
1762440000	ADAPTER ALU STI-S	E.6
1762440000	ADAPTER ALU STI-S	E.7
1762960001	THM MT30x 101/74 si	D.12
1763270000	CLI TM 10-33	C.11
1763280000	CLI TM 20-33	C.11
1763290000	CLI CD-BOX	C.52
1763390000	CLI TM 20-66	C.11
1763480000	SFC 2/12 BEDR./FARBIG	C.7
1764050000	CLI F 2-17,5 WS/GE NE	C.11
1764050000	CLI F 2-17,5 WS/GE NE	C.9
1764060000	CLI T 02-12	C.11
1764070000	CLI T 02-15	C.11
1764140000	CLI T 02-18	C.11
1764150000	CLI T 02-20	C.11
1764190000	CLI T 1-12	C.11
1764200000	CLI T 1-15	C.11
1764210000	CLI T 1-18	C.11
1764220000	CLI T 1-20	C.11
1764230000	CLI T 2-12	C.11
1764240000	CLI T 2-15	C.11
1764250000	CLI T 2-18	C.11
1764260000	CLI T 2-20	C.11
1764270000	CLI T 3-12	C.11
1764280000	CLI T 3-15	C.11
1764290000	CLI T 3-18	C.11
1764300000	CLI T 3-20	C.11
1766160000	ESG 9/20 MC NEUTRAL GE	D.4
1766640000	ESG 8/17 SCHS MC BEDR.	D.4
1767730000	DEK 5/3,5 MC bedruckt	B.11
1768090000	WS 14/5 MC NEUTRAL	B.14
1768380000	LM WriteOn 25,4x57 WS	C.17
1768390000	LM WriteOn 25,4x57 GE	C.17
1768400000	LM WriteOn 25,4x95 WS	C.17
1768410000	LM WriteOn 25,4x95 GE	C.17
1768430000	LM WriteOn 37x25 GE	C.17
1768540000	Plotterpen 0,25	E.6
1768540000	Plotterpen 0,25	E.7
1768550000	Plotterpen 0,35	E.6
1768550000	Plotterpen 0,35	E.7
1768560000	Plotterpen 0,5	E.6
1768560000	Plotterpen 0,5	E.7
1768570000	Plotterpen 0,18	E.6
1768570000	Plotterpen 0,18	E.7

1770000000

1770080000	SF-Tool-Sortiment	C.5
1770090000	THM MT30x 26,5/17,5 SI/M	D.12
1770480000	ESG 9/17 MC BEDRUCKT	D.4
1770490000	DEK 5/7.5 MC SONDERDR.	B.11
1770500000	ESG 9/20 MC NEUTRAL O. FUSS	D.4
1770510000	ESG 9/20 MC O.F. SONDER	D.4
1771930000	SM 27/8 K SI NEUTRAL	D.6
1772120000	Tinte 2000 25ml	E.6
1772120000	Tinte 2000 25ml	E.7
1772130000	Reiniger 2000 25ml	E.6
1772130000	Reiniger 2000 25ml	E.7
1773220000	SM 27/27 NEUTRAL WS	D.6
1773230000	SM 27/27 NEUTRAL SI	D.6
1773240000	SM 27/27 SONDERDRUCK	D.6
1773521686	WS 8/5 MC neutral RT	B.14
1773521687	WS 8/5 MC neutral GE	B.14
1773521690	WS 8/5 MC neutral OR	B.14
1773521693	WS 8/5 MC neutral BL	B.14
1773531686	WS 10/5 MC neutral RT	B.14
1773531687	WS 10/5 MC neutral GE	B.14
1773531693	WS 10/5 MC neutral BL	B.14
1773541686	WS 12/5 MC neutral RT	B.14
1773541687	WS 12/5 MC neutral GE	B.14
1773541690	WS 12/5 MC neutral OR	B.14
1773541693	WS 12/5 MC neutral BL	B.14
1773551686	WS 12/6 MC neutral RT	B.14
1773551687	WS 12/6 MC neutral GE	B.14
1773551689	WS 12/6 MC neutral VI	B.14
1773551690	WS 12/6 MC neutral OR	B.14
1773551692	WS 12/6 MC neutral BR	B.14
1773551693	WS 12/6 MC neutral BL	B.14
1773561686	WS 12/6,5 MC neutral RT	B.15
1773561687	WS 12/6,5 MC neutral GE	B.15
1773561688	WS 12/6,5 MC neutral GN	B.15
1773561693	WS 12/6,5 MC neutral BL	B.15
1773571687	WS 15/5 MC neutral GE	B.14
1773880000	LM WriteOn 15x140 WS	C.17
1774340000	THM WRITE ON 25/76 GE	C.17
1774350000	THM WRITE ON 25/76 WS	C.17
1774380000	THM WRITEON 17,8/34WS	C.17
1774400000	THM WRITE ON 35,6/93 WS	C.17
1774410000	THM WRITE ON 35,6/93 GE	C.17
1774470000	WSM TOOL AUTOMATIK	C.57
1774480000	WSM TOOL MANUELL	C.57
1774490000	WSMH 288mm	C.57
1774500000	WSMH 48mm	C.57
1774510000	WSMH 60mm	C.57
1774520000	WSMH 84mm	C.57
1774530000	WSMH 108mm	C.57
1778170000	THM MT30x 101/150 SI/G	D.12
1778270000	WS 12/3,5 MC neutral	B.14
1778280000	WS 12/3,5 MC Sonderdr.	B.14
1779080001	SFC 1/21 NEUTRAL WS	C.7
1779080002	SFC 1/21 NEUTRAL BL	C.7
1779080003	SFC 1/21 NEUTRAL RT	C.7
1779080004	SFC 1/21 NEUTRAL GE	C.7
1779090000	SFC 1/21 SONDERDRUCK	C.7

1780000000

1782710000	SM-H 27/27 SW	D.7
1782960000	SF-TOOL 2-3	C.5
1782970000	SF-TOOL 1	C.5
1782980000	SF-TOOL 4-5	C.5
1782990000	SM 27/27 K SI NEUTRAL	D.6
1783000000	SM 27/27 K WS NEUTRAL	D.6
1783010000	SM 27/27 K SONDERDRUCK	D.6
1784340000	LM MT300 26,5/17,5 SI	D.11
1785240000	THM DRUCKER PRO	E.10

1790000000

1790060000	WAD 5 Sonderdruck	B.38
1790150000	CC-RAIL 1000	D.9
1790160000	CC-RAIL TRANSPARENT1000	D.9
1790410000	CC-H 15/27	D.9
1790420000	CC-H 15/49	D.9
1790430000	CC-H 15/17	D.9
1790650000	THM pro HiRes	E.10
1790650000	THM pro HiRes	E.11
1790650000	THM pro HiRes	E.9
1792000000	WS 10/5 MC Midd. Neutr.	B.14
1792000000	WS 10/5 MC Midd. Neutr.	B.35
1792000000	WS 10/5 MC Midd. Neutr.	B.36
1792010000	WS 10/5 MC Midd. Sonder	B.14
1797460000	Tintenpatrone PrintJet	E.3
1798470000	TM 203/20 V0	C.12
1798480000	TM 203/18 V0	C.12
1798490000	TM 203/15 V0	C.12
1798510000	TM 203/12 V0	C.12
1798520000	TM 202/20 V0	C.12
1798530000	TM 202/18 V0	C.12
1798540000	TM 202/15 V0	C.12
1798560000	TM 202/12 V0	C.12
1798580000	TM 201/20 V0	C.12
1798600000	TM 201/18 V0	C.12
1798620000	TM 201/15 V0	C.12
1798640000	TM 201/12 V0	C.12
1798650000	TM 200/15 V0	C.12

1800000000

1802180000	MC-MOBILO AUFN. SF 4-6	C.6
1802180000	MC-MOBILO AUFN. SF 4-6	E.7
1804480000	ET S7 / 12/50 ge A4	D.13
1805480000	BZT 2 WS 10/5	B.35
1805490000	BZT 1 WS 10/5	B.35
1805520000	BZT 1 ZA WS 10/5	B.35
1805530000	BZT 2 ZA WS 10/5	B.35
1805720000	SFC 1/30 NEUTRAL BL	C.7
1805730000	SFC 1/30 NEUTRAL GE	C.7
1805740000	SFC 1/30 NEUTRAL RT	C.7
1805750000	SFC 1/30 SONDERDRUCK	C.7
1805760000	SFC 1/30 NEUTRAL WS	C.7
1805770000	SFC 2/21 NEUTRAL BL	C.7
1805780000	SFC 2/21 NEUTRAL GE	C.7
1805790000	SFC 2/21 NEUTRAL RT	C.7
1805800000	SFC 2/21 SONDERDRUCK	C.7
1805810000	SFC 2/21 NEUTRAL WS	C.7
1805820000	SFC 2/30 NEUTRAL BL	C.7
1805830000	SFC 2/30 NEUTRAL GE	C.7
1805840000	ETO SM 27x27	D.7
1805850000	SFC 2/30 NEUTRAL RT	C.7
1805860000	SFC 2/30 SONDERDRUCK	C.7
1805870000	SFC 2/30 NEUTRAL WS	C.7
1805880000	SNAPMARK I	B.35
1806120000	EM 8/30	B.38
1806180000	TM 204/12 V0	C.12
1806190000	TM 205/12 V0	C.12
1806200000	TM 206/12 V0	C.12
1806210000	TM 207/12 V0	C.12
1806220000	TM 208/12 V0	C.12
1806230000	TM 209/12 V0	C.12
1806240000	TM 204/15 V0	C.12
1806250000	TM 205/15 V0	C.12
1806260000	TM 206/15 V0	C.12
1806270000	TM 207/15 V0	C.12
1806280000	TM 208/15 V0	C.12
1806290000	TM 209/15 V0	C.12
1806300000	TM 204/18 V0	C.12
1806310000	TM 205/18 V0	C.12
1806320000	TM 206/18 V0	C.12
1806330000	TM 207/18 V0	C.12
1806340000	TM 208/18 V0	C.12
1806350000	TM 209/18 V0	C.12
1806360000	TM 204/20 V0	C.12
1806370000	TM 205/20 V0	C.12
1806380000	TM 206/20 V0	C.12
1806390000	TM 207/20 V0	C.12
1806400000	TM 208/20 V0	C.12
1806410000	TM 209/20 V0	C.12

1810000000

1812630000	SM 27/8 K WS NEUTRAL	D.6
1813130000	SFC 0/12 NEUTRAL WS	C.7
1813150000	SFC 0/12 NEUTRAL RT	C.7
1813160000	SFC 0/12 NEUTRAL GE	C.7
1813170000	SFC 0/12 NEUTRAL BL	C.7
1813180000	SFC 0/12 SONDERDRUCK	C.7
1813190000	SFC 0/21 NEUTRAL WS	C.7
1813200000	SFC 0/21 NEUTRAL RT	C.7
1813210000	SFC 0/21 NEUTRAL GE	C.7
1813220000	SFC 0/21 NEUTRAL BL	C.7
1813230000	SFC 0/21 SONDERDRUCK	C.7
1813240000	SFC 0/30 NEUTRAL WS	C.7
1813250000	SFC 0/30 NEUTRAL RT	C.7
1813260000	SFC 0/30 NEUTRAL GE	C.7
1813270000	SFC 0/30 NEUTRAL BL	C.7
1813280000	SFC 0/30 SONDERDRUCK	C.7
1816240000	MF-W 5/5 MINI MC NEUTR.	B.18
1816250000	MF 5/5 MC NEUTRAL	B.18
1816260000	MF 5/6 MC NEUTRAL	B.19
1816270000	MF-W 9/5 MC NEUTRAL	B.18
1816280000	MF-W 9/5F MC NEUTRAL	B.18
1816290000	MF-W 9/6 MC NEUTRAL	B.19
1816310000	MF-W 5/5 MINI MC S.DR.	B.18
1816320000	MF 5/5 MC SONDERDRUCK	B.18
1816330000	MF 5/6 MC SONDERDRUCK	B.19
1816340000	MF-W 9/5 MC SONDERDRUCK	B.18
1816350000	MF-W 9/5F MC SONDERDR.	B.18
1816360000	MF-W 9/6 MC SONDERDRUCK	B.19
1818400000	WS 10/6 MC Midd. Neutr.	B.14
1818410000	WS 10/6 MC Midd. Sonder	B.15

Order No.	Type	Page

1820000000

1821020000	ET S7-300-GE-A4-1	D.13
1821030000	ET S7-400-GE-A4-2	D.13
1821040000	ET S7-400-GE-A4-1	D.13
1828450000	WS 10/6 MC NEUTRAL	B.14
1828460000	WS 10/6 MC Sonderdruck	B.15

1830000000

1835820000	LM MT300 17x6 GE	D.11
1835830000	LM MT300 19.05x6.3 GE	D.11

1840000000

1847640000	ET S7-400-GE-A4-3	D.13
1847650000	ET S7-300-GE-A4-2	D.13
1849580000	KSW 2,5 14/3,5 1,3,5...27	D.17
1849590000	KSW 2,5 14/3,5 2,4,6...28	D.17

1850000000

1852360000	SFX 10/23 NEUTRAL GE V2	C.5
1852370000	SFX 10/23 NEUTRAL RT V2	C.5
1852380000	SFX 10/23 SONDERDRUCK V2	C.5
1852390000	SFX 10/23 NEUTRAL WS V2	C.5
1852400000	SFX 10/23 NEUTRAL BL V2	C.5
1852410000	SFX 14/23 NEUTRAL GE V2	C.5
1852420000	SFX 14/23 NEUTRAL RT V2	C.5
1852430000	SFX 14/23 SONDERDR. V2	C.5
1852440000	SFX 14/23 NEUTRAL WS V2	C.5
1852450000	SFX 14/23 NEUTRAL BL V2	C.5
1852460000	SFX 9/24 NEUTRAL GE V2	C.5
1852470000	SFX 9/24 NEUTRAL RT V2	C.5
1852480000	SFX 9/24 SONDERDRUCK V2	C.5
1852490000	SFX 9/24 NEUTRAL WS V2	C.5
1852500000	SFX 9/24 NEUTRAL BL V2	C.5
1852520000	THM MT30x 16/7 GE	D.12
1852540000	THM MT30x 57/27 SI	D.12
1854090000	WS 10/15 MC Neutr.	B.15
1854100000	WS 10/15 MC Sonderdruck	B.15
1854490000	DEK 5/5 PLUS MC NEUTRAL	B.11
1854500000	DEK 5/5 PLUS MC SONDERDR.	B.11
1854510000	MF 10/5 MC CABUR	B.18
1854520000	MF 12/5 MC CABUR	B.18
1856620001	CLI C 1-3 SW/WS 1 MP	C.32
1856620002	CLI C 1-3 SW/WS 2 MP	C.32
1856620003	CLI C 1-3 SW/WS 3 MP	C.32
1856620004	CLI C 1-3 SW/WS 4 MP	C.32
1856620005	CLI C 1-3 SW/WS 5 MP	C.32
1856620006	CLI C 1-3 SW/WS 6 MP	C.32
1856620007	CLI C 1-3 SW/WS 7 MP	C.32
1856620008	CLI C 1-3 SW/WS 8 MP	C.32
1856620009	CLI C 1-3 SW/WS 9 MP	C.32
1856620011	CLI C 1-3 SW/WS A MP	C.33
1856620012	CLI C 1-3 SW/WS B MP	C.33
1856620013	CLI C 1-3 SW/WS C MP	C.33
1856620014	CLI C 1-3 SW/WS D MP	C.33
1856620015	CLI C 1-3 SW/WS E MP	C.33
1856620016	CLI C 1-3 SW/WS F MP	C.33
1856620017	CLI C 1-3 SW/WS G MP	C.33
1856620018	CLI C 1-3 SW/WS H MP	C.33
1856620019	CLI C 1-3 SW/WS I MP	C.33
1856620020	CLI C 1-3 SW/WS J MP	C.33
1856620021	CLI C 1-3 SW/WS K MP	C.33
1856620022	CLI C 1-3 SW/WS L MP	C.33
1856620023	CLI C 1-3 SW/WS M MP	C.33
1856620024	CLI C 1-3 SW/WS N MP	C.33
1856620025	CLI C 1-3 SW/WS O MP	C.33
1856620026	CLI C 1-3 SW/WS P MP	C.33
1856620027	CLI C 1-3 SW/WS Q MP	C.33
1856620028	CLI C 1-3 SW/WS R MP	C.33
1856620029	CLI C 1-3 SW/WS S MP	C.33
1856620030	CLI C 1-3 SW/WS T MP	C.33
1856620031	CLI C 1-3 SW/WS U MP	C.33
1856620032	CLI C 1-3 SW/WS V MP	C.33
1856620033	CLI C 1-3 SW/WS W MP	C.33
1856620034	CLI C 1-3 SW/WS X MP	C.33
1856620035	CLI C 1-3 SW/WS Y MP	C.33
1856620036	CLI C 1-3 SW/WS Z MP	C.33
1856630000	THM WRITE ON 12/18 GE	C.17
1856640000	THM WRITE ON 12/18 WS	C.17
1856650000	THM MT30X 17/9 GE/M	D.12
1856700000	ESG 10/17 MC Neutral	D.4
1856710000	ESG 10/17 Sonderdruck	D.4
1856720000	ESG 9/20 MC Universal	D.4
1856730000	ESG 9/20 Univ. Sonderdr	D.4
1856740000	DEK 5/8 MC Neutral	B.11
1856750000	DEK 5/8 MC Sonderdruck	B.11
1856760000	MF 10/10 MC NEUTRAL	B.19
1856770000	MF 10/10 MC SONDERDRUCK	B.19
1856780000	MFF 10/6 MC NEUTRAL	B.19
1856790000	MFF 10/6 MC SONDERDRUCK	B.19
1857440000	ESG 9/11K MC NEUTRAL	D.4
1857450000	ESG 9/11 K SONDERDRUCK	D.4
1858920000	Tintentank PrintJet II	E.3
1858950000	CleanUnit PrintJet II	E.3

Order No.	Type	Page

1860000000

1860120000	SFX 11/60 MC NEUTRAL WS	C.5
1860140000	SFX 11/60 SONDERDRUCK	C.5
1860150000	SFX 11/60 MC NEUTRAL GE	C.5
1861510000	LM MT300 27/8 GE	D.11
1862350000	THM MT30x 38,1/31,75 SI	D.12
1865440000	ET S7-12/50-TU-A4	D.13
1865450000	ET S7-300-TU-A4-1	D.13
1865460000	ET S7-300-TU-A4-2	D.13
1865470000	ET S7-400-TU-A4-1	D.13
1865480000	ET S7-400-TU-A4-2	D.13
1865490000	ET S7-400-TU-A4-3	D.13
1866680000	TMX 30 V0	C.12
1866690000	ESG 9/20 MC TUERKIS	D.4
1868430000	MF 10/8 MC SONDERDRUCK	B.19
1868440000	MF 10/8 MC NEUTRAL	B.19
1868810004	CLI C 1-9 GE NE CD	C.21
1868811150	CLI C 1-6 GE/SW X1 CD	C.37
1868811151	CLI C 1-6 GE/SW X2 CD	C.37
1868811522	CLI C 1-6 GE/SW 01 CD	C.35
1868811523	CLI C 1-6 GE/SW 02 CD	C.35
1868811524	CLI C 1-6 GE/SW 03 CD	C.35
1868811525	CLI C 1-6 GE/SW 04 CD	C.35
1868811526	CLI C 1-6 GE/SW 05 CD	C.35
1868811527	CLI C 1-6 GE/SW 06 CD	C.35
1868811528	CLI C 1-6 GE/SW 07 CD	C.35
1868811529	CLI C 1-6 GE/SW 08 CD	C.35
1868811530	CLI C 1-6 GE/SW 09 CD	C.35
1868811531	CLI C 1-6 GE/SW 10 CD	C.35
1868811532	CLI C 1-6 GE/SW 11 CD	C.35
1868811533	CLI C 1-6 GE/SW 12 CD	C.35
1868811534	CLI C 1-6 GE/SW 13 CD	C.35
1868811535	CLI C 1-6 GE/SW 14 CD	C.35
1868811536	CLI C 1-6 GE/SW 15 CD	C.35
1868811537	CLI C 1-6 GE/SW 16 CD	C.35
1868811538	CLI C 1-6 GE/SW 17 CD	C.35
1868811539	CLI C 1-6 GE/SW 18 CD	C.35
1868811540	CLI C 1-6 GE/SW 19 CD	C.35
1868811541	CLI C 1-6 GE/SW 20 CD	C.35
1868811542	CLI C 1-6 GE/SW 21 CD	C.35
1868811543	CLI C 1-6 GE/SW 22 CD	C.35
1868811544	CLI C 1-6 GE/SW 23 CD	C.35
1868811545	CLI C 1-6 GE/SW 24 CD	C.35
1868811546	CLI C 1-6 GE/SW 25 CD	C.35
1868811547	CLI C 1-6 GE/SW 26 CD	C.35
1868811548	CLI C 1-6 GE/SW 27 CD	C.35
1868811549	CLI C 1-6 GE/SW 28 CD	C.35
1868811550	CLI C 1-6 GE/SW 29 CD	C.35
1868811551	CLI C 1-6 GE/SW 30 CD	C.35
1868811552	CLI C 1-6 GE/SW 31 CD	C.35
1868811553	CLI C 1-6 GE/SW 32 CD	C.35
1868811554	CLI C 1-6 GE/SW 33 CD	C.35
1868811555	CLI C 1-6 GE/SW 34 CD	C.35
1868811556	CLI C 1-6 GE/SW 35 CD	C.35
1868811557	CLI C 1-6 GE/SW 36 CD	C.35
1868811558	CLI C 1-6 GE/SW 37 CD	C.35
1868811559	CLI C 1-6 GE/SW 38 CD	C.35
1868811560	CLI C 1-6 GE/SW 39 CD	C.35
1868811561	CLI C 1-6 GE/SW 40 CD	C.35
1868811562	CLI C 1-6 GE/SW 41 CD	C.35
1868811563	CLI C 1-6 GE/SW 42 CD	C.35
1868811564	CLI C 1-6 GE/SW 43 CD	C.35
1868811565	CLI C 1-6 GE/SW 44 CD	C.35
1868811566	CLI C 1-6 GE/SW 45 CD	C.35
1868811567	CLI C 1-6 GE/SW 46 CD	C.35
1868811568	CLI C 1-6 GE/SW 47 CD	C.35
1868811569	CLI C 1-6 GE/SW 48 CD	C.35
1868811570	CLI C 1-6 GE/SW 49 CD	C.35
1868811571	CLI C 1-6 GE/SW 50 CD	C.35
1868811572	CLI C 1-6 GE/SW 51 CD	C.35
1868811573	CLI C 1-6 GE/SW 52 CD	C.35
1868811574	CLI C 1-6 GE/SW 53 CD	C.35
1868811575	CLI C 1-6 GE/SW 54 CD	C.35
1868811576	CLI C 1-6 GE/SW 55 CD	C.35
1868811577	CLI C 1-6 GE/SW 56 CD	C.35
1868811578	CLI C 1-6 GE/SW 57 CD	C.35
1868811579	CLI C 1-6 GE/SW 58 CD	C.35
1868811580	CLI C 1-6 GE/SW 59 CD	C.35
1868811581	CLI C 1-6 GE/SW 60 CD	C.35
1868811582	CLI C 1-6 GE/SW 61 CD	C.36
1868811583	CLI C 1-6 GE/SW 62 CD	C.36
1868811584	CLI C 1-6 GE/SW 63 CD	C.36
1868811585	CLI C 1-6 GE/SW 64 CD	C.36
1868811586	CLI C 1-6 GE/SW 65 CD	C.36
1868811587	CLI C 1-6 GE/SW 66 CD	C.36
1868811588	CLI C 1-6 GE/SW 67 CD	C.36
1868811589	CLI C 1-6 GE/SW 68 CD	C.36
1868811590	CLI C 1-6 GE/SW 69 CD	C.36
1868811591	CLI C 1-6 GE/SW 70 CD	C.36
1868811592	CLI C 1-6 GE/SW 71 CD	C.36
1868811593	CLI C 1-6 GE/SW 72 CD	C.36
1868811594	CLI C 1-6 GE/SW 73 CD	C.36
1868811595	CLI C 1-6 GE/SW 74 CD	C.36
1868811596	CLI C 1-6 GE/SW 75 CD	C.36
1868811597	CLI C 1-6 GE/SW 76 CD	C.36
1868811598	CLI C 1-6 GE/SW 77 CD	C.36
1868811599	CLI C 1-6 GE/SW 78 CD	C.36
1868811600	CLI C 1-6 GE/SW 79 CD	C.36
1868811601	CLI C 1-6 GE/SW 80 CD	C.36

Order No.	Type	Page
1868811602	CLI C 1-6 GE/SW 81 CD	C.36
1868811603	CLI C 1-6 GE/SW 82 CD	C.36
1868811604	CLI C 1-6 GE/SW 83 CD	C.36
1868811605	CLI C 1-6 GE/SW 84 CD	C.36
1868811606	CLI C 1-6 GE/SW 85 CD	C.36
1868811607	CLI C 1-6 GE/SW 86 CD	C.36
1868811608	CLI C 1-6 GE/SW 87 CD	C.36
1868811609	CLI C 1-6 GE/SW 88 CD	C.36
1868811610	CLI C 1-6 GE/SW 89 CD	C.36
1868811611	CLI C 1-6 GE/SW 90 CD	C.36
1868811612	CLI C 1-6 GE/SW 91 CD	C.36
1868811613	CLI C 1-6 GE/SW 92 CD	C.36
1868811614	CLI C 1-6 GE/SW 93 CD	C.36
1868811615	CLI C 1-6 GE/SW 94 CD	C.36
1868811616	CLI C 1-6 GE/SW 95 CD	C.36
1868811617	CLI C 1-6 GE/SW 96 CD	C.36
1868811618	CLI C 1-6 GE/SW 97 CD	C.36
1868811619	CLI C 1-6 GE/SW 98 CD	C.36
1868811620	CLI C 1-6 GE/SW 99 CD	C.36
1868811687	CLI C 1-6 GE NE CD	C.21
1868811726	CLI C 1-6 GE/SW A1 CD	C.37
1868811727	CLI C 1-6 GE/SW A2 CD	C.37
1868811728	CLI C 1-6 GE/SW L1 CD	C.37
1868811729	CLI C 1-6 GE/SW L2 CD	C.37
1868811730	CLI C 1-6 GE/SW L3 CD	C.37
1868811731	CLI C 1-6 GE/SW MP CD	C.37
1868811733	CLI C 1-6 GE/SW PE CD	C.37
1868811734	CLI C 1-9 GE/SW PEN CD	C.37
1868811735	CLI C 1-6 GE/SW U1 CD	C.37
1868811736	CLI C 1-6 GE/SW U2 CD	C.37
1868811737	CLI C 1-6 GE/SW U3 CD	C.37
1868811738	CLI C 1-6 GE/SW UN CD	C.37
1868811739	CLI C 1-6 GE/SW I1 CD	C.37
1868811740	CLI C 1-6 GE/SW I2 CD	C.37
1868811741	CLI C 1-6 GE/SW IC CD	C.37
1868819999	CLI C 1-9 SDR SG	C.23
1869181502	CLI C 1-3 GR/SW 0 MP	C.32
1869181505	CLI C 1-3 GR/SW 1 MP	C.32
1869181508	CLI C 1-3 GR/SW 2 MP	C.32
1869181511	CLI C 1-3 GR/SW 3 MP	C.32
1869181514	CLI C 1-3 GR/SW 4 MP	C.32
1869181517	CLI C 1-3 GR/SW 5 MP	C.32
1869181520	CLI C 1-3 GR/SW 6 MP	C.32
1869181523	CLI C 1-3 GR/SW 7 MP	C.32
1869181529	CLI C 1-3 GR/SW 9 MP	C.32
1869181740	CLI C 1-3 GR/SW - MP	C.34
1869351502	CLI C 02-3 GR/SW 0 MP	C.29
1869351505	CLI C 02-3 GR/SW 1 MP	C.29
1869351508	CLI C 02-3 GR/SW 2 MP	C.29
1869351511	CLI C 02-3 GR/SW 3 MP	C.29
1869351514	CLI C 02-3 GR/SW 4 MP	C.29
1869351517	CLI C 02-3 GR/SW 5 MP	C.29
1869351520	CLI C 02-3 GR/SW 6 MP	C.29
1869351523	CLI C 02-3 GR/SW 7 MP	C.29
1869351529	CLI C 02-3 GR/SW 9 MP	C.29
1869351691	CLI C 02-3 GR NE MP	C.20
1869821044	CLI C 02-3 WS NE CD	C.20
1869821502	CLI C 02-3 WS/SW 0 CD	C.29
1869821505	CLI C 02-3 WS/SW 1 CD	C.29
1869821508	CLI C 02-3 WS/SW 2 CD	C.29
1869821511	CLI C 02-3 WS/SW 3 CD	C.29
1869821514	CLI C 02-3 WS/SW 4 CD	C.29
1869821517	CLI C 02-3 WS/SW 5 CD	C.29
1869821520	CLI C 02-3 WS/SW 6 CD	C.29
1869821523	CLI C 02-3 WS/SW 7 CD	C.29
1869821526	CLI C 02-3 WS/SW 8 CD	C.29
1869821637	CLI C 02-3 WS/SW A CD	C.29
1869821639	CLI C 02-3 WS/SW B CD	C.29
1869821641	CLI C 02-3 WS/SW C CD	C.29
1869821643	CLI C 02-3 WS/SW D CD	C.29
1869821645	CLI C 02-3 WS/SW E CD	C.29
1869821647	CLI C 02-3 WS/SW F CD	C.29
1869821649	CLI C 02-3 WS/SW G CD	C.29
1869821651	CLI C 02-3 WS/SW H CD	C.29
1869821653	CLI C 02-3 WS/SW I CD	C.29
1869821655	CLI C 02-3 WS/SW J CD	C.29
1869821657	CLI C 02-3 WS/SW K CD	C.29
1869821659	CLI C 02-3 WS/SW L CD	C.29
1869821661	CLI C 02-3 WS/SW M CD	C.29
1869821663	CLI C 02-3 WS/SW N CD	C.29
1869821665	CLI C 02-3 WS/SW O CD	C.29
1869821667	CLI C 02-3 WS/SW P CD	C.29
1869821669	CLI C 02-3 WS/SW Q CD	C.29
1869821671	CLI C 02-3 WS/SW R CD	C.29
1869821673	CLI C 02-3 WS/SW S CD	C.29
1869821676	CLI C 02-3 WS/SW T CD	C.29
1869821679	CLI C 02-3 WS/SW U CD	C.29
1869821681	CLI C 02-3 WS/SW V CD	C.29
1869821683	CLI C 02-3 WS/SW W CD	C.29
1869821687	CLI C 02-3 WS/SW X CD	C.29
1869821695	CLI C 02-3 WS/SW Ö CD	C.30
1869821696	CLI C 02-3 WS/SW Y CD	C.29
1869821697	CLI C 02-3 WS/SW Ä CD	C.30
1869821698	CLI C 02-3 WS/SW Z CD	C.29
1869821699	CLI C 02-3 WS/SW Å CD	C.30
1869821726	CLI C 02-6 WS/SW A1 CD	C.31
1869821727	CLI C 02-6 WS/SW A2 CD	C.31
1869821728	CLI C 02-6 WS/SW L1 CD	C.31
1869821729	CLI C 02-6 WS/SW L2 CD	C.31
1869821730	CLI C 02-6 WS/SW L3 CD	C.31

Order No.	Type	Page
1869821734	CLI C 02-9 WS/SW PEN CD	C.31
1869821738	CLI C 02-3 WS/SW + CD	C.30
1869821740	CLI C 02-3 WS/SW - CD	C.30
1869821742	CLI C 02-3 WS/SW / CD	C.30
1869821746	CLI C 02-3 WS/SW ET CD	C.30
1869821747	CLI C 02-3 WS/SW PET. CD	C.30
1869821748	CLI C 02-3 WS/SW . CD	C.30
1869821750	CLI C 02-3 WS/SW : CD	C.30
1869821751	CLI C 02-3 WS/SW = CD	C.30
1869821752	CLI C 02-3 WS/SW AC CD	C.30
1869829999	CLI C 02-9 SDR SG	C.23
1869991637	CLI C 02-3 WS/SW A MP	C.29
1869991639	CLI C 02-3 WS/SW B MP	C.29
1869991641	CLI C 02-3 WS/SW C MP	C.29
1869991643	CLI C 02-3 WS/SW D MP	C.29
1869991645	CLI C 02-3 WS/SW E MP	C.29
1869991647	CLI C 02-3 WS/SW F MP	C.29
1869991649	CLI C 02-3 WS/SW G MP	C.29
1869991651	CLI C 02-3 WS/SW H MP	C.29
1869991653	CLI C 02-3 WS/SW I MP	C.29
1869991655	CLI C 02-3 WS/SW J MP	C.29
1869991657	CLI C 02-3 WS/SW K MP	C.29
1869991659	CLI C 02-3 WS/SW L MP	C.29
1869991661	CLI C 02-3 WS/SW M MP	C.29
1869991663	CLI C 02-3 WS/SW N MP	C.29
1869991665	CLI C 02-3 WS/SW O MP	C.29
1869991667	CLI C 02-3 WS/SW P MP	C.29
1869991669	CLI C 02-3 WS/SW Q MP	C.29
1869991671	CLI C 02-3 WS/SW R MP	C.29
1869991673	CLI C 02-3 WS/SW S MP	C.29
1869991676	CLI C 02-3 WS/SW T MP	C.29
1869991679	CLI C 02-3 WS/SW U MP	C.29
1869991681	CLI C 02-3 WS/SW V MP	C.29
1869991683	CLI C 02-3 WS/SW W MP	C.29
1869991687	CLI C 02-3 WS/SW X MP	C.29
1869991695	CLI C 02-3 WS/SW Ö MP	C.30
1869991696	CLI C 02-3 WS/SW Y MP	C.29
1869991697	CLI C 02-3 WS/SW Ä MP	C.30
1869991698	CLI C 02-3 WS/SW Z MP	C.29
1869991699	CLI C 02-3 WS/SW Å MP	C.30
1869991726	CLI C 02-6 WS/SW A1 MP	C.31
1869991727	CLI C 02-6 WS/SW A2 MP	C.31
1869991728	CLI C 02-6 WS/SW L1 MP	C.31
1869991729	CLI C 02-6 WS/SW L2 MP	C.31
1869991730	CLI C 02-6 WS/SW L3 MP	C.31
1869991734	CLI C 02-9 WS/SW PEN MP	C.31
1869991738	CLI C 02-3 WS/SW + MP	C.30
1869991740	CLI C 02-3 WS/SW - MP	C.30
1869991742	CLI C 02-3 WS/SW / MP	C.30
1869991746	CLI C 02-3 WS/SW ET MP	C.30
1869991747	CLI C 02-3 WS/SW PET. MP	C.30
1869991748	CLI C 02-3 WS/SW . MP	C.30
1869991750	CLI C 02-3 WS/SW : MP	C.30
1869991751	CLI C 02-3 WS/SW = MP	C.30
1869991752	CLI C 02-3 WS/SW AC MP	C.30
1869999999	CLI C 02-6 SDR CD	C.23

1870000000

1871341726	CLI C 1-6 WS/SW A1 MP	C.37
1871341727	CLI C 1-6 WS/SW A2 MP	C.37
1871341728	CLI C 1-6 WS/SW L1 MP	C.37
1871341729	CLI C 1-6 WS/SW L2 MP	C.37
1871341730	CLI C 1-6 WS/SW L3 MP	C.37
1871341734	CLI C 1-9 WS/SW PEN MP	C.37
1871351726	CLI C 1-6 WS/SW A1 CD	C.37
1871351727	CLI C 1-6 WS/SW A2 CD	C.37
1871351728	CLI C 1-6 WS/SW L1 CD	C.37
1871351729	CLI C 1-6 WS/SW L2 CD	C.37
1871351730	CLI C 1-6 WS/SW L3 CD	C.37
1871351734	CLI C 1-9 WS/SW PEN CD	C.37
1871371044	CLI M 2-4 WS NE MP	C.22
1871371502	CLI M 2-4 WS/SW 0 MP	C.50
1871371505	CLI M 2-4 WS/SW 1 MP	C.50
1871371508	CLI M 2-4 WS/SW 2 MP	C.50
1871371511	CLI M 2-4 WS/SW 3 MP	C.50
1871371514	CLI M 2-4 WS/SW 4 MP	C.50
1871371517	CLI M 2-4 WS/SW 5 MP	C.50
1871371520	CLI M 2-4 WS/SW 6 MP	C.50
1871371523	CLI M 2-4 WS/SW 7 MP	C.50
1871371526	CLI M 2-4 WS/SW 8 MP	C.50
1871371637	CLI M 2-4 WS/SW A MP	C.50
1871371639	CLI M 2-4 WS/SW B MP	C.50
1871371641	CLI M 2-4 WS/SW C MP	C.50
1871371643	CLI M 2-4 WS/SW D MP	C.50
1871371645	CLI M 2-4 WS/SW E MP	C.50
1871371647	CLI M 2-4 WS/SW F MP	C.50
1871371649	CLI M 2-4 WS/SW G MP	C.50
1871371651	CLI M 2-4 WS/SW H MP	C.50
1871371653	CLI M 2-4 WS/SW I MP	C.50
1871371655	CLI M 2-4 WS/SW J MP	C.50
1871371657	CLI M 2-4 WS/SW K MP	C.50
1871371659	CLI M 2-4 WS/SW L MP	C.50
1871371661	CLI M 2-4 WS/SW M MP	C.50
1871371663	CLI M 2-4 WS/SW N MP	C.50
1871371665	CLI M 2-4 WS/SW O MP	C.50
1871371667	CLI M 2-4 WS/SW P MP	C.50
1871371669	CLI M 2-4 WS/SW Q MP	C.50
1871371671	CLI M 2-4 WS/SW R MP	C.50
1871371673	CLI M 2-4 WS/SW S MP	C.50

Order No.	Type	Page
1871371676	CLI M 2-4 WS/SW T MP	C.50
1871371679	CLI M 2-4 WS/SW U MP	C.50
1871371681	CLI M 2-4 WS/SW V MP	C.50
1871371683	CLI M 2-4 WS/SW W MP	C.50
1871371687	CLI M 2-4 WS/SW X MP	C.50
1871371695	CLI M 2-4 WS/SW Ö MP	C.51
1871371696	CLI M 2-4 WS/SW Y MP	C.50
1871371697	CLI M 2-4 WS/SW Ä MP	C.51
1871371698	CLI M 2-4 WS/SW Z MP	C.50
1871371699	CLI M 2-4 WS/SW Å MP	C.51
1871371738	CLI M 2-4 WS/SW + MP	C.51
1871371740	CLI M 2-4 WS/SW - MP	C.51
1871371742	CLI M 2-4 WS/SW / MP	C.51
1871371746	CLI M 2-4 WS/SW ET MP	C.51
1871371747	CLI M 2-4 WS/SW PET. MP	C.51
1871371748	CLI M 2-4 WS/SW . MP	C.51
1871371750	CLI M 2-4 WS/SW : MP	C.51
1871371751	CLI M 2-4 WS/SW = MP	C.51
1871371752	CLI M 2-4 WS/SW AC MP	C.51
1871741728	CLI M 2-6 WS/SW L1 MP	C.51
1871741729	CLI M 2-6 WS/SW L2 MP	C.51
1871741730	CLI M 2-6 WS/SW L3 MP	C.51
1871751728	CLI M 2-6 GE/SW L1 MP	C.51
1871751729	CLI M 2-6 GE/SW L2 MP	C.51
1871751730	CLI M 2-6 GE/SW L3 MP	C.51
1871771728	CLI M 2-6 WS/SW L1 CD	C.51
1871771729	CLI M 2-6 WS/SW L2 CD	C.51
1871771730	CLI M 2-6 WS/SW L3 CD	C.51
1871781728	CLI M 2-6 GE/SW L1 CD	C.51
1871781729	CLI M 2-6 GE/SW L2 CD	C.51
1871781730	CLI M 2-6 GE/SW L3 CD	C.51
1871789999	CLI M 2-6 SDR CD	C.25
1871791044	CLI C 1-15 WS NE SG	C.21
1871791687	CLI C 1-15 GE NE SG	C.21
1871801044	CLI C 1-18 WS NE SG	C.21
1871801687	CLI C 1-18 GE NE SG	C.21
1871809999	CLI C 1-18 SDR SG	C.23
1871811044	CLI C 1-24 WS NE SG	C.21
1871821687	CLI C 1-33 GE NE SG	C.21
1871831044	CLI C 2-18 WS NE SG	C.21
1871831687	CLI C 2-18 GE NE SG	C.21
1871839999	CLI C 2-18 SDR SG	C.24
1871841044	CLI C 1-12 WS NE SG	C.21
1871841687	CLI C 1-12 GE NE SG	C.21
1871851502	CLI C 2-4 GR/SW 0 MP	C.38
1871851505	CLI C 2-4 GR/SW 1 MP	C.38
1871851508	CLI C 2-4 GR/SW 2 MP	C.38
1871851511	CLI C 2-4 GR/SW 3 MP	C.38
1871851514	CLI C 2-4 GR/SW 4 MP	C.38
1871851517	CLI C 2-4 GR/SW 5 MP	C.38
1871851520	CLI C 2-4 GR/SW 6 MP	C.38
1871851523	CLI C 2-4 GR/SW 7 MP	C.38
1871851529	CLI C 2-4 GR/SW 9 MP	C.38
1871871502	CLI C 2-4 WS/SW 0 CD	C.38
1871871505	CLI C 2-4 WS/SW 1 CD	C.38
1871871508	CLI C 2-4 WS/SW 2 CD	C.38
1871871511	CLI C 2-4 WS/SW 3 CD	C.38
1871871514	CLI C 2-4 WS/SW 4 CD	C.38
1871871517	CLI C 2-4 WS/SW 5 CD	C.38
1871871520	CLI C 2-4 WS/SW 6 CD	C.38
1871871523	CLI C 2-4 WS/SW 7 CD	C.38
1871871526	CLI C 2-4 WS/SW 8 CD	C.38
1871871637	CLI C 2-4 WS/SW A CD	C.38
1871871639	CLI C 2-4 WS/SW B CD	C.38
1871871641	CLI C 2-4 WS/SW C CD	C.38
1871871643	CLI C 2-4 WS/SW D CD	C.38
1871871645	CLI C 2-4 WS/SW E CD	C.38
1871871647	CLI C 2-4 WS/SW F CD	C.38
1871871649	CLI C 2-4 WS/SW G CD	C.38
1871871651	CLI C 2-4 WS/SW H CD	C.38
1871871653	CLI C 2-4 WS/SW I CD	C.38
1871871655	CLI C 2-4 WS/SW J CD	C.38
1871871657	CLI C 2-4 WS/SW K CD	C.38
1871871659	CLI C 2-4 WS/SW L CD	C.38
1871871661	CLI C 2-4 WS/SW M CD	C.38
1871871663	CLI C 2-4 WS/SW N CD	C.38
1871871665	CLI C 2-4 WS/SW O CD	C.38
1871871667	CLI C 2-4 WS/SW P CD	C.38
1871871669	CLI C 2-4 WS/SW Q CD	C.38
1871871671	CLI C 2-4 WS/SW R CD	C.38
1871871673	CLI C 2-4 WS/SW S CD	C.38
1871871676	CLI C 2-4 WS/SW T CD	C.38
1871871679	CLI C 2-4 WS/SW U CD	C.38
1871871681	CLI C 2-4 WS/SW V CD	C.38
1871871683	CLI C 2-4 WS/SW W CD	C.38
1871871685	CLI C 2-4 WS/SW X CD	C.38
1871871695	CLI C 2-4 WS/SW Ö CD	C.39
1871871696	CLI C 2-4 WS/SW Y CD	C.38
1871871697	CLI C 2-4 WS/SW Ä CD	C.39
1871871698	CLI C 2-4 WS/SW Z CD	C.38
1871871699	CLI C 2-4 WS/SW ? CD	C.39
1871871738	CLI C 2-4 WS/SW + CD	C.39
1871871740	CLI C 2-4 WS/SW - CD	C.39
1871871742	CLI C 2-4 WS/SW / CD	C.39
1871871746	CLI C 2-4 WS/SW ET CD	C.39
1871871747	CLI C 2-4 WS/SW PET. CD	C.39
1871871748	CLI C 2-4 WS/SW . CD	C.39
1871871750	CLI C 2-4 WS/SW : CD	C.39
1871871751	CLI C 2-4 WS/SW = CD	C.39
1871871752	CLI C 2-4 WS/SW AC CD	C.39
1871891728	CLI C 2-6 GE/SW L1 MP	C.39
1871891729	CLI C 2-6 GE/SW L2 MP	C.39
1871891730	CLI C 2-6 GE/SW L3 MP	C.39
1871901687	CLI C 2-6 GE NE CD	C.21
1871901728	CLI C 2-6 GE/SW L1 CD	C.39
1871901729	CLI C 2-6 GE/SW L2 CD	C.39
1871901730	CLI C 2-6 GE/SW L3 CD	C.39
1871901731	CLI C 2-6 GE/SW PE CD	C.39
1871909999	CLI C 2-6 SDR CD	C.24
1871911728	CLI C 2-6 WS/SW L1 CD	C.39
1871911729	CLI C 2-6 WS/SW L2 CD	C.39
1871911730	CLI C 2-6 WS/SW L3 CD	C.39
1871921728	CLI C 2-6 WS/SW L1 MP	C.39
1871921729	CLI C 2-6 WS/SW L2 MP	C.39
1871921730	CLI C 2-6 WS/SW L3 MP	C.39
1871971687	CLI C 2-9 GE NE CD	C.21
1871971734	CLI C 2-9 GE/SW PEN CD	C.39
1871979999	CLI C 2-9 SDR SG	C.24
1872031734	CLI C 2-9 GE/SW PEN MP	C.39
1872301502	CLI C 3-6 WS/SW 0 MP	C.40
1872301505	CLI C 3-6 WS/SW 1 MP	C.40
1872301508	CLI C 3-6 WS/SW 2 MP	C.40
1872301511	CLI C 3-6 WS/SW 3 MP	C.40
1872301514	CLI C 3-6 WS/SW 4 MP	C.40
1872301517	CLI C 3-6 WS/SW 5 MP	C.40
1872301520	CLI C 3-6 WS/SW 6 MP	C.40
1872301523	CLI C 3-6 WS/SW 7 MP	C.40
1872301526	CLI C 3-6 WS/SW 8 MP	C.40
1872301637	CLI C 3-6 WS/SW A MP	C.40
1872301639	CLI C 3-6 WS/SW B MP	C.40
1872301641	CLI C 3-6 WS/SW C MP	C.40
1872301643	CLI C 3-6 WS/SW D MP	C.40
1872301645	CLI C 3-6 WS/SW E MP	C.40
1872301647	CLI C 3-6 WS/SW F MP	C.40
1872301649	CLI C 3-6 WS/SW G MP	C.40
1872301651	CLI C 3-6 WS/SW H MP	C.40
1872301653	CLI C 3-6 WS/SW I MP	C.40
1872301655	CLI C 3-6 WS/SW J MP	C.40
1872301657	CLI C 3-6 WS/SW K MP	C.40
1872301659	CLI C 3-6 WS/SW L MP	C.40
1872301661	CLI C 3-6 WS/SW M MP	C.40
1872301663	CLI C 3-6 WS/SW N MP	C.40
1872301665	CLI C 3-6 WS/SW O MP	C.40
1872301667	CLI C 3-6 WS/SW P MP	C.40
1872301669	CLI C 3-6 WS/SW Q MP	C.40
1872301671	CLI C 3-6 WS/SW R MP	C.40
1872301673	CLI C 3-6 WS/SW S MP	C.40
1872301676	CLI C 3-6 WS/SW T MP	C.40
1872301679	CLI C 3-6 WS/SW U MP	C.40
1872301681	CLI C 3-6 WS/SW V MP	C.40
1872301683	CLI C 3-6 WS/SW W MP	C.40
1872301687	CLI C 3-6 WS/SW X MP	C.40
1872301695	CLI C 3-6 WS/SW Ö MP	C.40
1872301696	CLI C 3-6 WS/SW Y MP	C.40
1872301697	CLI C 3-6 WS/SW Ä MP	C.40
1872301698	CLI C 3-6 WS/SW Z MP	C.40
1872301699	CLI C 3-6 WS/SW Å MP	C.40
1872301738	CLI C 3-6 WS/SW + MP	C.40
1872301740	CLI C 3-6 WS/SW - MP	C.40
1872301742	CLI C 3-6 WS/SW / MP	C.40
1872301746	CLI C 3-6 WS/SW ET MP	C.40
1872301748	CLI C 3-6 WS/SW . MP	C.40
1872301750	CLI C 3-6 WS/SW : MP	C.40
1872301751	CLI C 3-6 WS/SW = MP	C.40
1872301752	CLI C 3-6 WS/SW AC MP	C.40
1872309999	CLI C 3-6 SDR SG	C.24
1872651726	CLI C 3-6 WS/SW A1 MP	C.41
1872651727	CLI C 3-9 WS/SW A2 MP	C.41
1872651728	CLI C 3-9 WS/SW L1 MP	C.41
1872651729	CLI C 3-9 WS/SW L2 MP	C.41
1872651730	CLI C 3-9 WS/SW L3 MP	C.41
1872651734	CLI C 3-9 WS/SW PEN MP	C.41
1872659999	CLI C 3-9 SDR SG	C.24
1872661733	CLI C 3-9 GE/SW PEN MP	C.41
1872671687	CLI C 3-18 GE NE SG	C.22
1872679999	CLI C 3-18 SDR SG	C.24
1872681044	CLI O 10-3 WS NE MP	C.22
1872681502	CLI O 10-3 WS/SW 0 MP	C.46
1872681505	CLI O 10-3 WS/SW 1 MP	C.46
1872681508	CLI O 10-3 WS/SW 2 MP	C.46
1872681511	CLI O 10-3 WS/SW 3 MP	C.46
1872681514	CLI O 10-3 WS/SW 4 MP	C.46
1872681517	CLI O 10-3 WS/SW 5 MP	C.46
1872681520	CLI O 10-3 WS/SW 6 MP	C.46
1872681523	CLI O 10-3 WS/SW 7 MP	C.46
1872681526	CLI O 10-3 WS/SW 8 MP	C.46
1872681529	CLI O 10-3 WS/SW 9 MP	C.46
1872681738	CLI O 10-3 WS/SW + MP	C.46
1872681740	CLI O 10-3 WS/SW - MP	C.46
1872691044	CLI O 20-3 WS NE MP	C.22
1872691502	CLI O 20-3 WS/SW 0 MP	C.47
1872691505	CLI O 20-3 WS/SW 1 MP	C.47
1872691508	CLI O 20-3 WS/SW 2 MP	C.47
1872691511	CLI O 20-3 WS/SW 3 MP	C.47
1872691514	CLI O 20-3 WS/SW 4 MP	C.47
1872691517	CLI O 20-3 WS/SW 5 MP	C.47
1872691520	CLI O 20-3 WS/SW 6 MP	C.47
1872691523	CLI O 20-3 WS/SW 7 MP	C.47
1872691526	CLI O 20-3 WS/SW 8 MP	C.47
1872691529	CLI O 20-3 WS/SW 9 MP	C.47
1872691738	CLI O 20-3 WS/SW + MP	C.47
1872691740	CLI O 20-3 WS/SW - MP	C.47
1872701044	CLI O 30-3 WS NE MP	C.22
1872701502	CLI O 30-3 WS/SW 0 MP	C.48
1872701505	CLI O 30-3 WS/SW 1 MP	C.48
1872701508	CLI O 30-3 WS/SW 2 MP	C.48
1872701511	CLI O 30-3 WS/SW 3 MP	C.48
1872701514	CLI O 30-3 WS/SW 4 MP	C.48
1872701517	CLI O 30-3 WS/SW 5 MP	C.48
1872701520	CLI O 30-3 WS/SW 6 MP	C.48
1872701523	CLI O 30-3 WS/SW 7 MP	C.48
1872701526	CLI O 30-3 WS/SW 8 MP	C.48
1872701529	CLI O 30-3 WS/SW 9 MP	C.48
1872701738	CLI O 30-3 WS/SW + MP	C.48
1872701740	CLI O 30-3 WS/SW - MP	C.48
1872711502	CLI R 02-3 WS/SW 0	C.42
1872711505	CLI R 02-3 WS/SW 1	C.42
1872711508	CLI R 02-3 WS/SW 2	C.42
1872711511	CLI R 02-3 WS/SW 3	C.42
1872711514	CLI R 02-3 WS/SW 4	C.42
1872711517	CLI R 02-3 WS/SW 5	C.42
1872711520	CLI R 02-3 WS/SW 6	C.42
1872711523	CLI R 02-3 WS/SW 7	C.42
1872711526	CLI R 02-3 WS/SW 8	C.42
1872751030	CLI R 1-12 BR/WS L1JI	C.44
1872751031	CLI R 1-12 SW/WS L2JI	C.44
1872751032	CLI R 1-12 WS/SW L3JI	C.44
1872751033	CLI R 1-12 BL/SW L1JI	C.44
1872751034	CLI R 1-12 BL/SW L2JI	C.44
1872751035	CLI R 1-12 BL/SW L3JI	C.44
1872761030	CLI R 1-9 BR/WS L1I	C.44
1872761031	CLI R 1-9 SW/WS L2I	C.44
1872761032	CLI R 1-9 WS/SW L3I	C.44
1872761033	CLI R 1-9 BR/WS L1U	C.44
1872761034	CLI R 1-9 SW/WS L2U	C.44
1872761035	CLI R 1-9 WS/SW L3U	C.44
1872761036	CLI R 1-9 BL/SW NJU	C.44
1873330000	CLI C 02-12 SDR SG	C.23
1873340000	CLI C 02-21 SDR SG	C.23
1873350000	CLI C 1-12 SDR SG	C.23
1873360000	CLI C 1-15 SDR SG	C.23
1873370000	CLI C 1-21 SDR SG	C.23
1873380000	CLI C 2-12 SDR SG	C.24
1873390000	CLI C 2-15 SDR SG	C.24
1873400000	CLI C 2-21 SDR SG	C.24
1873410000	CLI C 3-21 SDR SG	C.24
1873420000	CLI C 3-12 SDR SG	C.24
1873430000	CLI C 3-15 SDR SG	C.24
1873440000	CLI M 2-9 SDR SG	C.25
1873450000	CLI M 2-12 SDR SG	C.25
1873460000	CLI M 2-21 SDR SG	C.25
1873470000	CLI O 30-6 SDR MP	C.24
1873600000	KSW 2,5 24/3,81 W 1-24	D.17
1873610000	KSW 2,5 16/3,81 W 1-16	D.17
1873620000	KSW 2,5 8/3,5 W 1-8	D.17
1873630000	KSW 2,5 8/3,81 W 1-8	D.17
1873640000	KSW 2,5 8/7,62 W 1-8	D.17
1873650000	KSW 2,5 8/7,5 W 1-8	D.17
1873741044	CLI C 02-18 WS NE SG	C.20
1873741687	CLI C 02-18 GE NE SG	C.20
1873749999	CLI C 02-18 SDR SG	C.23
1873810000	LM MT300 27x18 SI	D.11
1874720000	TM 209/30 V0	C.12
1874760000	TM 202/30 V0	C.12
1874770000	TM 203/30 V0	C.12
1874780000	TM 204/30 V0	C.12
1874790000	TM 205/30 V0	C.12
1874800000	TM 206/30 V0	C.12
1874820000	TM 207/30 V0	C.12
1874830000	TM 208/30 V0	C.12
1874850000	TM 201/30 V0	C.12
1874860000	LM MT300 PA 20x8 GE	D.11
1876320000	TM-I 30 MC SONDERDRUCK	C.9
1876370000	TM-I 30 MC NEUTRAL GE	C.9
1876380000	TM-I 30 MC NEUTRAL RT	C.9
1876390000	TM-I 30 MC NEUTRAL WS	C.9
1876400000	TM-I 30 MC NEUTRAL BL	C.9
1876570000	CC 15/17 MC NEUTRAL WS	D.8
1876580000	CC 15/17 K MC NEUTR. SI	D.8
1876590000	CC 15/17 K MC NEUTR. WS	D.8
1876600000	CC 15/17 K MC SONDERD.	D.8
1876610000	CC 15/17 MC NEUTRAL SI	D.8
1876620000	CC 15/17 MC SONDERD.	D.8
1876630000	CC 15/27 MC SONDERD.	D.8
1876640000	CC 15/27 K MC NEUTR. WS	D.8
1876750000	CC 15/27 K MC SONDERD.	D.8
1876760000	CC 15/27 MC NEUTRAL SI	D.8
1876770000	CC 15/27 MC NEUTRAL WS	D.8
1876780000	CC 15/27 K MC NEUTR. SI	D.8
1877200000	CC 15/49 MC SONDERD.	D.8
1877220000	CC 15/49 K MC NEUTR. WS	D.8
1877230000	CC 15/49 K MC SONDERD.	D.8
1877240000	CC 15/49 MC NEUTRAL SI	D.8
1877260000	CC 15/49 MC NEUTRAL WS	D.8
1877270000	CC 15/49 K MC NEUTR. SI	D.8
1877300000	CC 15/60 MC SONDERD.	D.8
1877310000	CC 15/60 K MC NEUTR. WS	D.8
1877320000	CC 15/60 K MC SONDERD.	D.8
1877340000	CC 15/60 MC NEUTRAL SI	D.8
1877350000	CC 15/60 MC NEUTRAL WS	D.8
1877360000	CC 15/60 K MC NEUTR. SI	D.8
1877570000	SM 22/22 K MC NEUTR. WS	D.6
1877580000	SM 22/22 K MC SONDERD.	D.6
1877590000	SM 22/22 K MC NEUTR. SI	D.6
1877660000	MF 5/7,5 MC SONDERDRUCK	B.19
1877670000	MF 5/4 MC SONDERDRUCK	B.18
1877680000	MF 5/7,5 MC NEUTRAL	B.19
1877690000	MF 5/4 MC NEUTRAL	B.18
1877700000	MFF 9/4 MC SONDERDRUCK	B.18
1877710000	MF-W 9/4 MC SONDERDRUCK	B.18
1877720000	MFF 9/4 MC NEUTRAL	B.18
1877730000	MF-W 9/4 MC NEUTRAL	B.18
1878171502	CLI C 1-3 GR/SW 0 CD	C.32
1878171505	CLI C 1-3 GR/SW 1 CD	C.32
1878171508	CLI C 1-3 GR/SW 2 CD	C.32
1878171511	CLI C 1-3 GR/SW 3 CD	C.32
1878171514	CLI C 1-3 GR/SW 4 CD	C.32
1878171517	CLI C 1-3 GR/SW 5 CD	C.32
1878171520	CLI C 1-3 GR/SW 6 CD	C.32
1878171523	CLI C 1-3 GR/SW 7 CD	C.32
1878171529	CLI C 1-3 GR/SW 9 CD	C.32
1878191728	CLI C 1-6 GR/SW L1 MP	C.37
1878191729	CLI C 1-6 GR/SW L2 MP	C.37
1878191730	CLI C 1-6 GR/SW L3 MP	C.37
1878201502	CLI C 02-3 GR/SW 0 CD	C.29
1878201505	CLI C 02-3 GR/SW 1 CD	C.29
1878201508	CLI C 02-3 GR/SW 2 CD	C.29
1878201511	CLI C 02-3 GR/SW 3 CD	C.29
1878201514	CLI C 02-3 GR/SW 4 CD	C.29
1878201517	CLI C 02-3 GR/SW 5 CD	C.29
1878201520	CLI C 02-3 GR/SW 6 CD	C.29
1878201523	CLI C 02-3 GR/SW 7 CD	C.29
1878201529	CLI C 02-3 GR/SW 9 CD	C.29
1878201691	CLI C 02-3 GR NE CD	C.20
1878201693	CLI C 02-3 BL NE CD	C.20
1878910000	CC-H 15/60	D.9

1880000000

Order No.	Type	Page
1880080000	ESG 6/17 K SONDERDRUCK	D.4
1880090000	ESG 6/15 K SONDERDRUCK	D.4
1880100000	ESG 6/15 K MC NEUTR. WS	D.4
1880110000	ESG 6/17 K MC NEUTR. GE	D.4
1880120000	ESG 6/17 K MC NEUTR. WS	D.4
1880130000	ESG 6/15 K MC NEUTR. GE	D.4
1880720000	ETO SM 22/22 TRANSPAR.	D.7
1880810000	ETO CC 15/27 TRANSPAR.	D.9
1880830000	ETO CC 15/49 TRANSPAR.	D.9
1880840000	ETO CC 15/60 TRANSPAR.	D.9
1880850000	ETO CC 15/17 TRANSPAR.	D.9
1881280000	ESG 6/15 MC RIDERSERIES	D.4
1881290000	ESG 6/15 RIDERS SONDERD	D.4
1882890000	LM MT300 15X9 GE	D.11
1882900000	THM WRITE ON 49,5/57 WS	C.17
1882910000	LM MT300 12X6 GE	D.11
1886270000	MF-SI 8/5 MC SONDERDRUCK	B.18
1886531687	CLI M 2-25Q GE NEUT SG	C.22
1886541687	CLI M 2-40Q GE NEUT SG	C.22
1888280000	STR CC 15/60 TRANSPARENT	D.9
1888290000	STR CC 15/27 TRANSPARENT	D.9
1888300000	STR CC 15/49 TRANSPARENT	D.9
1888310000	STR CC 15/17 TRANSPARENT	D.9
1888360000	ESG 9/6 MC NEUTRAL	D.4
1889170000	MF-SI 10/5 MC SONDERDRUCK	B.18
1889180000	MF-SI 8/5 MC NEUTRAL	B.18
1889190000	MF-SI 10/5 MC NEUTRAL	B.18
1889230000	MF-SI 8/6 MC SONDERDRUCK	B.19
1889240000	MF-SI 8/6 MC NEUTRAL	B.19
1889250000	MF-SI 10/6 MC SONDERDRUCK	B.19
1889260000	MF-SI 10/6 MC NEUTRAL	B.19
1889550000	CLI T 3-30	C.11
1889560000	CLI T 1-30	C.11
1889570000	CLI T 2-30	C.11
1889580000	CLI T 02-30	C.11
1889770000	MF-SI 7/5-6,5 MC SONDERDR.	B.19
1889780000	MF-SI 7/5-6,5 MC NEUTRAL	B.19
1889790000	MF-SI 10/5-6,5 MC SONDERDR.	B.19
1889800000	MF-SI 10/5-6,5 MC NEUTRAL	B.19

1890000000

Order No.	Type	Page
1890460000	ESG 9/20 L MC NEUTRAL	D.4
1890470000	ESG 8/17 L MC NEUTRAL	D.4
1891670000	WSMC 11-15	C.57
1891680000	WSMC 6-10	C.57
1891770000	THM MT30X 25,9/7,1 WS	D.12
1891780000	TM 1/18 TWIN HF/HB	C.10
1891810000	TM 0/18 TWIN HF/HB	C.10
1895950000	KSW 2,5 10/5,08 W 9-18	D.17
1895960000	KSW 2,5 8/5,08 W 19-26	D.17
1897570000	ESG 8/11	D.4
1899230000	CLI M 2-18 SDR SG	C.25
1899240000	CLI C 2-9 SDR CD	C.24
1899250000	CLI M 2-9 SDR CD	C.25
1899260000	CLI M 2-15 SDR SG	C.25
1899290000	CLI C 02-9 SDR CD	C.23

Order No.	Type	Page

1900000000

1905490000	M-PRINT PRO	E.12
1905500000	M-PRINT PRO ADVANCED	E.12
1905950000	WS 10/8 MC NEUTRAL	B.15
1905970000	WS 10/12 MC NEUTRAL	B.15
1906000000	WS 12/8 MC NEUTRAL	B.15
1906010000	WS 12/8 MC SONDERDRUCK	B.15
1906030000	WS 10/8 MC SONDERDRUCK	B.15
1906060000	WS 10/12 MC SONDERDRUCK	B.15
1906110000	SM 27/18 NEUTRAL ROT	D.6
1906120000	SM 27/18 K NEUTRAL ROT	D.6
1907520000	DEK 5/5 PLUS MC GE	B.11
1907530000	MF 4/5.2 MC NEUTRAL	B.18

1910000000

1912130000	ESG 8/13.5/43.3 SAI AU	D.4
1912140000	WSMC 16-20	C.57
1912150000	WSMC 21-25	C.57
1912160000	WSMC 26-30	C.57
1912170000	WSMC 1-5	C.57
1912500000	CLI C 02-24 SDR SG	C.23
1912510000	CLI C 02-27 SDR SG	C.23
1912550000	CLI C 02-3 SDR SG	C.23
1912580000	CLI C 02-30 SDR SG	C.23
1912590000	CLI C 02-33 SDR SG	C.23
1912600000	CLI C 02-36 SDR SG	C.23
1912610000	CLI C 02-39 SDR SG	C.23
1912620000	CLI C 02-6 SDR SG	C.23
1912630000	CLI C 1-24 SDR SG	C.23
1912640000	CLI C 1-27 SDR SG	C.23
1912650000	CLI C 1-3 SDR SG	C.23
1912660000	CLI C 1-30 SDR SG	C.23
1912670000	CLI C 1-33 SDR SG	C.23
1912680000	CLI C 1-36 SDR SG	C.23
1912690000	CLI C 1-39 SDR SG	C.23
1912700000	CLI C 1-6 SDR SG	C.23
1912710000	CLI C 2-24 SDR SG	C.24
1912720000	CLI C 2-27 SDR SG	C.24
1912730000	CLI C 2-30 SDR SG	C.24
1912740000	CLI C 2-33 SDR SG	C.24
1912750000	CLI C 2-36 SDR SG	C.24
1912760000	CLI C 2-39 SDR SG	C.24
1912770000	CLI C 3-24 SDR SG	C.24
1912780000	CLI C 3-27 SDR SG	C.24
1912790000	CLI C 3-30 SDR SG	C.24
1912800000	CLI C 3-33 SDR SG	C.24
1912810000	CLI C 3-36 SDR SG	C.24
1912820000	CLI C 3-39 SDR SG	C.24
1912830000	CLI M 2-4 SDR SG	C.25
1912840000	CLI M 2-6 SDR SG	C.25
1912860000	CLI M 2-24 SDR SG	C.25
1912870000	CLI M 2-27 SDR SG	C.25
1912880000	CLI M 2-30 SDR SG	C.25
1912920000	CLI M 2-33 SDR SG	C.25
1912950000	CLI M 2-36 SDR SG	C.25
1912960000	CLI M 2-39 SDR SG	C.25
1913311687	CLI C 1-21 GE NE SG	C.21
1915320000	LM MT300 202x12 GE	D.11
1915340000	SM 27/18 K NEUTRAL GE	D.6
1917410000	WS 10/6 MC MIDDLE OR	B.14
1917420000	WS 10/6 MC MIDDLE GN	B.14
1917430000	WS 10/6 MC MIDDLE GE	B.14
1917440000	WS 10/6 MC MIDDLE RT	B.14
1918470000	SF 0/21 SONDERDRUCK V2	C.5
1918480000	SF 0/21 NEUTRAL GE V2	C.5
1918490000	SF 0/21 NEUTRAL RT V2	C.5
1918500000	SF 0/21 NEUTRAL WS V2	C.5
1918510000	SF 0/21 NEUTRAL BL V2	C.5
1918530000	SF 00/21 SONDERDRUCK V2	C.5
1918560000	SF 00/21 NEUTRAL GE V2	C.5
1918570000	SF 00/21 NEUTRAL RT V2	C.5
1918580000	SF 00/21 NEUTRAL WS V2	C.5
1918590000	SF 00/21 NEUTRAL BL V2	C.5
1918600000	SF 1/21 NEUTRAL RT V2	C.5
1918610000	SF 1/21 NEUTRAL GE V2	C.5
1918620000	SF 1/21 NEUTRAL BL V2	C.5
1918630000	SF 1/21 NEUTRAL WS V2	C.5
1918640000	SF 1/21 SONDERDRUCK V2	C.5
1918650000	SF 2/21 SONDERDRUCK V2	C.5
1918660000	SF 2/21 NEUTRAL GE V2	C.5
1918670000	SF 2/21 NEUTRAL RT V2	C.5
1918690000	SF 2/21 NEUTRAL WS V2	C.5
1918700000	SF 2/21 NEUTRAL BL V2	C.5
1918880000	SF 3/21 SONDERDRUCK V2	C.5
1918890000	SF 3/21 NEUTRAL GE V2	C.5
1918900000	SF 3/21 NEUTRAL RT V2	C.5
1918910000	SF 3/21 NEUTRAL WS V2	C.5
1918920000	SF 3/21 NEUTRAL BL V2	C.5
1918990000	SF 4,5/21 SONDERDRUCK V2	C.5
1919000000	SF 4,5/21 NEUTRAL GE V2	C.5
1919010000	SF 4,5/21 NEUTRAL RT V2	C.5
1919020000	SF 4,5/21 NEUTRAL WS V2	C.5
1919030000	SF 4,5/21 NEUTRAL BL V2	C.5
1919050000	SF 4/21 SONDERDRUCK V2	C.5
1919060000	SF 4/21 NEUTRAL GE V2	C.5
1919070000	SF 4/21 NEUTRAL RT V2	C.5
1919080000	SF 4/21 NEUTRAL WS V2	C.5
1919090000	SF 4/21 NEUTRAL BL V2	C.5

Order No.	Type	Page
1919110000	SF 5/21 SONDERDRUCK V2	C.5
1919120000	SF 5/21 NEUTRAL GE V2	C.5
1919130000	SF 5/21 NEUTRAL RT V2	C.5
1919140000	SF 5/21 NEUTRAL WS V2	C.5
1919150000	SF 5/21 NEUTRAL BL V2	C.5
1919160000	SF 6/21 SONDERDRUCK V2	C.5
1919170000	SF 6/21 NEUTRAL GE V2	C.5
1919180000	SF 6/21 NEUTRAL RT V2	C.5
1919190000	SF 6/21 NEUTRAL WS V2	C.5
1919200000	SF 6/21 NEUTRAL BL V2	C.5
1919210000	SF 0/12 NEUTRAL GE V2	C.5
1919220000	SF 0/12 NEUTRAL BL V2	C.5
1919230000	SF 0/12 NEUTRAL RT V2	C.5
1919240000	SF 0/12 NEUTRAL WS V2	C.5
1919250000	SF 0/12 SONDERDRUCK V2	C.5
1919260000	SF 00/12 NEUTRAL GE V2	C.5
1919270000	SF 00/12 NEUTRAL BL V2	C.5
1919280000	SF 00/12 NEUTRAL RT V2	C.5
1919290000	SF 00/12 NEUTRAL WS V2	C.5
1919300000	SF 00/12 SONDERDRUCK V2	C.5
1919320000	SF 1/12 NEUTRAL RT V2	C.5
1919340000	SF 1/12 NEUTRAL GE V2	C.5
1919360000	SF 1/12 NEUTRAL BL V2	C.5
1919390000	SF 1/12 NEUTRAL WS V2	C.5
1919420000	SF 1/12 SONDERDRUCK V2	C.5
1919460000	SF 2/12 NEUTRAL RT V2	C.5
1919470000	SF 2/12 NEUTRAL GE V2	C.5
1919480000	SF 2/12 NEUTRAL BL V2	C.5
1919490000	SF 2/12 NEUTRAL WS V2	C.5
1919500000	SF 2/12 SONDERDRUCK V2	C.5
1919510000	SF 3/12 SONDERDRUCK V2	C.5
1919520000	SF 3/12 NEUTRAL GE V2	C.5
1919530000	SF 3/12 NEUTRAL RT V2	C.5
1919540000	SF 3/12 NEUTRAL WS V2	C.5
1919550000	SF 3/12 NEUTRAL BL V2	C.5
1919570000	SF 4/12 NEUTRAL RT V2	C.5
1919580000	SF 4/12 NEUTRAL GE V2	C.5
1919590000	SF 4/12 NEUTRAL BL V2	C.5
1919600000	SF 4/12 NEUTRAL WS V2	C.5
1919610000	SF 4/12 SONDERDRUCK V2	C.5
1919620000	SF 5/12 NEUTRAL GE V2	C.5
1919630000	SF 5/12 NEUTRAL BL V2	C.5
1919640000	SF 5/12 NEUTRAL RT V2	C.5
1919650000	SF 5/12 NEUTRAL WS V2	C.5
1919660000	SF 5/12 SONDERDRUCK V2	C.5
1919870000	ESO 8/20P WS	C.13
1919880000	ESO 8/20P GE	C.13
1919890000	ESO 8/20 WS	C.13
1919900000	ESO 8/20 GE	C.13
1919940000	ESG 5/10 MC NEUTRAL WS	D.4

1920000000

1920640000	PLOTTER PEN 0.25 P-INK	E.6
1920640000	PLOTTER PEN 0.25 P-INK	E.7
1920650000	PLOTTER PEN 0.35 P-INK	E.6
1920650000	PLOTTER PEN 0.35 P-INK	E.7
1924260000	MF-W 5/5 MINI MC RT	B.18
1924270000	MF-W 5/5 MINI MC BL	B.18
1924280000	MF-W 5/5 MINI MC GE	B.18
1924290000	MF-W 5/5 MINI MC GN	B.18
1924310000	MCP AP SF4-6	C.6
1924310000	MCP AP SF4-6	E.6
1924320000	MCP KLEBESTREIFEN	E.6
1924330000	P-CLEANER	E.6
1924330000	P-CLEANER	E.7
1924340000	P-INK	E.6
1924340000	P-INK	E.7
1924350000	MCP COVER	E.6
1924360000	MCP AP	E.6
1924370000	MCP AP LABLES	E.6
1924930000	WSM SERVICE BOX KOMP.	C.56
1925000000	MCP PLUS	E.4
1927510000	WS 12/5 PLUS MC NEUTRAL	B.14
1927520000	WS 12/5 PLUS SONDERDRUCK	B.14
1927530000	WS 12/6 PLUS MC NEUTRAL	B.14
1927540000	WS 12/6 PLUS SONDERDRUCK	B.15

1930000000

1934190000	THM WRITEON 51/36 WS	C.17
1934330000	CC 30/60 K MC NEUTRAL SI	D.8
1934370000	CC 30/60 K MC SONDERDRUCK	D.8
1934390000	CC 30/60 K MC NEUTRAL WS	D.8
1934400000	CC 30/60 MC NEUTRAL SI	D.8
1934410000	CC 30/60 MC SONDERDRUCK	D.8
1934420000	CC 30/60 MC NEUTRAL WS	D.8
1934430000	CC-H 30/60	D.9
1934440000	ETO CC 30/60 TRANSPAR.	D.9
1934450000	STR CC 30/60 TRANSPARENT	D.9
1935130000	MCP EP	E.6

1950000000

1950820000	SF-TOOL 00-6	C.5
1951870000	WS 8/5 PLUS MC NEUTRAL	B.14
1951880000	WS 8/6 PLUS MC NEUTRAL	B.14
1951920000	DEK 5/30 MC NEUTRAL	B.38
1951920000	DEK 5/30 MC NEUTRAL	B.39
1954050000	MF 5/10 MC NEUTRAL	B.19
1954070000	THM MT30x 8/8 WS	D.12

1960000000

1961900000	HSS-HF1/8"1,8-2,8/50Y	C.15
1961910000	HSS-HF3/16"2,8-4,2/50Y	C.15
1961920000	HSS-HF1/4"4,2-5,8/50Y	C.15
1961930000	HSS-HF3/8"5,8-8,0/50Y	C.15
1961940000	HSS-HF1/2"8,0-11,0/50Y	C.15
1961950000	HSS-HF3/4"11,0-17,0/50Y	C.15
1961960000	HSS-HF1"17,0-23,0/50Y	C.15
1961970000	HSS-HF1/8"1,8-2,8/25Y	C.15
1961980000	HSS-HF3/16"2,8-4,2/25Y	C.15
1961990000	HSS-HF1/4"4,2-5,8/25Y	C.15
1962000000	HSS-HF3/8"5,8-8,0/25Y	C.15
1962010000	HSS-HF1/2"8,0-11,0/25Y	C.15
1962020000	HSS-HF3/4"11,0-17,0/25Y	C.15
1962030000	HSS-HF1"17,0-23,0/25Y	C.15
1962040000	HSS1/8"1,2-2,8/50W	C.16
1962050000	HSS1/4"2,4-5,5/50W	C.16
1962060000	HSS3/8"3,2-8,1/50W	C.16
1962070000	HSS1/2"4,8-11,4/50W	C.16
1962080000	HSS1"11,4-24,1/50W	C.16
1962090000	HSS1/8"1,2-2,8/50Y	C.16
1962100000	HSS1/4"2,4-5,5/50Y	C.16
1962110000	HSS3/8"3,2-8,1/50Y	C.16
1962120000	HSS1/2"4,8-11,4/50Y	C.16
1962130000	HSS1 11,4-24,1/50Y	C.16
1962140000	HSS1/8 1,2-2,8/25W	C.16
1962150000	HSS1/4"2,4-5,5/25W	C.16
1962160000	HSS3/8"3,2-8,1/25W	C.16
1962170000	HSS1/2"4,8-11,4/25W	C.16
1962180000	HSS1"11,4-24,1/25W	C.16
1962190000	HSS1/8"1,2-2,8/25Y	C.16
1962200000	HSS1/4"2,4-5,5/25Y	C.16
1962210000	HSS3/8"3,2-8,1/25Y	C.16
1962220000	HSS1/2"4,8-11,4/25Y	C.16
1962230000	HSS1"11,4-24,1/25Y	C.16
1962340000	THM-PLUS PRINTER	E.9
1962360000	Ribbon HSS WR 90/300	E.9
1962370000	Ribbon HSS R 83/300	E.8
1962370000	Ribbon HSS R 83/300	E.9
1963650000	SFX 11/60 MC NEUTRAL RT	C.5
1964130000	THM MT30x 15/5,08 GE	D.12
1965140000	CENTRONICS-USB2.0 ADAPT	E.9
1968130000	THM MT30x 17/9 WS	D.12

1970000000

1975160000	LM MT300 105X105 SI	D.11

4060000000

4062150000	PJ-Clean Unit	E.3

7940000000

7940006040	CB 135/2.5 NATUR	C.59
7940006047	CB 135/2.5 BLACK	C.59
7940006048	CB 160/2.6 NATUR	C.59
7940006049	CB 160/2.6 BLACK	C.59
7940006050	CB 200/2.6 NATUR	C.59
7940006051	CB 200/2.6 BLACK	C.59
7940006052	CB 120/4.8 natur	C.59
7940006053	CB 120/4.5 BLACK	C.59
7940006054	CB 250/4.8 NATUR	C.59
7940006055	CB 250/4.8 BLACK	C.59
7940006056	CB 370/3.6 NATUR	C.59
7940006057	CB 370/3.6 BLACK	C.59
7940006058	CB 390/4.8 NATUR	C.59
7940006059	CB 390/4.8 BLACK	C.59
7940006060	CB 430/4.8 NATUR	C.59
7940006061	CB 430/4.8 BLACK	C.59
7940006062	CB 120/7.6 natur	C.59
7940006063	CB 120/7.6 black	C.59
7940006064	CB 180/7.8 NATUR	C.59
7940006065	CB 180/7.8 BLACK	C.59
7940006066	CB 240/7.6 natur	C.59
7940006067	CB 240/7.8 BLACK	C.59
7940006068	CB 300/7.8 NATUR	C.59
7940006069	CB 300/7.8 BLACK	C.59
7940006070	CB 450/7.8 NATUR	C.59
7940006071	CB 450/7.8 BLACK	C.59
7940006072	CB 540/7.8 NATUR	C.59
7940006073	CB 540/7.8 BLACK	C.59
7940006074	CB 780/9.0 NATUR	C.59
7940006075	CB 780/9.0 BLACK	C.59
7940006076	CB 230/12.7 natur	C.59
7940006077	CB 230/12.7 black	C.59
7940006078	CB 480/12.7 natur	C.59
7940006079	CB 500/12.5 BLACK	C.59
7940006082	CB 880/12.7 natur	C.59
7940006084	CB 1000/12.5 NATUR	C.59
7940006085	CB 1000/12.5 BLACK	C.59

Addresses worldwide

AE **United Arab Emirates**
Weidmuller Middle East FZE
P.O. Box 8591
SAIF-Zone
Sharjah – U. A. E.
Phone +971 6 5572723
Fax +971 6 5572724
wme.info@weidmueller.com

AR **Argentina**
CPI SA
Bauness 2660
1431 Buenos Aires
Phone +54 11 45238008
Fax + 54 11 45220546
info@cpi.com.ar
www.cpi.com.ar

AT **Austria**
Weidmüller GmbH.
Industriezentrum Nö Süd
Straße 2, Objekt M2
2355 Wiener Neudorf
Phone +43 2236 6708-0
Fax +43 2236 6708-199
office.at@weidmueller.com

AU **Australia**
Weidmüller Pty. Ltd.
P.O.Box 6944
Huntingwood Drive 43
Huntingwood,
NSW, 2148
Phone +61 2 9671-9999
Fax +61 2 9671-9911
info@weidmueller.com.au
www.weidmueller.com.au

AZ **Azerbaijan**
West Industries Ltd.
Caspian Plaza, 5-th Floor
44 J. Jabbarly Str., Baku
Phone +99412 499 15 15
Fax +99412 499 14 93
sales@west-i.com

BA **Bosnia and Herzegovina**
BH ES ELEKTROSISTEM d.o.o.
ul. J. Veselinovica 18
78000 BiH Banja Luka
Phone +387 51 317500
Fax +387 51 304638
elsist@inecco.net
www.elektrosistem.co.yu

BE **Belgium**
Weidmüller Benelux B.V.
Mechelseesteenweg 519 bus 6 en 7
1930 Nossegem
Phone +32 (0)16 39 5990
Fax +32 (0)16 40 1051
info@weidmueller.be
www.weidmueller.be

BG **Bulgaria**
Weid-Bul EOOD
1113 Sofia
33A Nezabravka, bl.
315, fl.3, ap. 10
Phone +359 2 9632560
Fax +359 2 9631098
weidbul@nat.bg
www.weidbul.com

BH **Bahrain**
Khayber Trading Company
P.O. Box 1976 Manama,
Phone +973 720747
Fax +973 720331
khayber@batelco.com.bh

BR **Brazil**
Conexel Conexoes Elétricas Ltda.
Rua Garcia Lorca, 176
09695-900, Sao Paulo SP
Phone +55 11 43669600
Fax +55 11 43621677
vendas@conexel.com.br
www.conexel.com.br

BY **Belarus**
TECHNIKON Ltd.
Oktyabrskaya Str. 16/5
Apt. 704, Minsk 220801
Phone +375 17 2275830
Fax +375 17 2275830
technikon@belsonet.net

CA **Canada**
W Interconnections CANADA Ltd.
10 Spy Court, Markham,
Ontario L3 R5 H6
Phone +1 905 475-1507
Fax +1 905 475-2798
info1@weidmuller.ca
www.weidmuller.ca

CH **Switzerland**
Weidmüller Schweiz AG
Rundbuckstraße 2
8212 Neuhausen am Rheinfall
Phone +41 52 6740707
Fax +41 52 6740708
info@weidmueller.ch
www.weidmueller.ch

CL **Chile**
Felipe Bahamondes S.A./ATS AGRO
Maria Luisa Santander 0475
Casilla 3425
Santiago
Phone +56 2 341-1271
Fax +56 2 341-1275
felipe@atsintech.com

CN **China**
Weidmüller Interface International
Trading (Shanghai) Co., Ltd.
12 F, Century Ba-Shi Building,
No. 398 Huaihai Road (M)
Shanghai 200020
P.R. China
Phone +86 21 63868188
Fax +86 21 63867177
www.cnweidmuller.com

CO **Colombia**
Automatización Avanzada S. A.
Carrera 97 No.24c, 23 B4
4 Bogotá D. C.
Phone +57 1 5478510
Fax +57 1 4223044
comercial@
automatizacionavanzada.com
www.automatizacionavanzada.com

CR **Costa Rica**
ELVATRON S.A.
la Uruca 400 Norte
Banco Costa Rica
San José Costa Rica
Phone +506 2 961060
Fax +506 5 200609
dirk.haase@elvatron.com
www.elvatron.com

CS **Serbia-Montenegro**
ES-YU Elektrosistem
Pariske komune 41
11070 Novi Beograd, Serbia
Phone +381 11 2693608
Fax +381 11 3018660
esyu@eunet.yu
www.elektrosistem.co.yu

CZ **Czech Republic**
Weidmüller s. r. o.
Lomnického 5/1705
14000 Praha 4
Phone +420 2 44001400
Fax +420 2 44001499
office@weidmueller.cz
www.weidmueller.cz

DE **Germany**
Weidmüller GmbH & Co. KG
P.O. Box 3054
32720 Detmold
Ohmstraße 9
32758 Detmold
Phone +49 5231 1428-0
Fax +49 5231 1428-116
weidmueller@weidmueller.de
www.weidmueller.de

DK **Denmark**
Wexøe A/S
Lejrvej 31
3500 Vaerloese
Phone +45 45465800
Fax +45 45465801
wexoe@wexoe.dk
www.wexoe.dk

EC **Ecuador**
Elsystec S. A. Electricidad
Sistemas y Tecnología
Vasco de Contreras N35-25
y Mañosca, Quito
Phone +593 2 2456510
Fax +593 2 2456755
Elsystec@uio.satnet.net

EE **Estonia**
Alter Electric OÜ
Gaasi 4A
11415 Tallinn
Phone +372 6519666
Fax +372 6519667
alter@alter.ee
www.alter.ee

EG **Egypt**
Standard Electric (OMEGA)
87, Mohamed Farid Street
Heliopolis, Cairo
Phone +20 26422977
Fax +20 26422955
stdelec@rite.com

ES **Spain**
Weidmüller S. A.
Narcis Monturiol 11-13
Pol.Ind. N 1 Sudoeste
8960 Sant Just Desvern
Barcelona
Phone +34 93 3722061
Fax +34 93 3718055
weidmuller@weidmuller.es
www.weidmuller.es

FI **Finland**
JUHA-ELEKTRO OY
P. O. Box 57, 641 Helsinki
Kylvöpolku 6, 680 Helsinki
Phone +358 10 8328 100
Fax +358 10 8328 109
info@juha-elektro.fi
www.juha-elektro.fi

FR **France**
Weidmüller E. U. R. L.
12, Chaussée Jules César
B.P. 263 Osny
95523 Cergy Pontoise Cedex
Phone +33 1 34245500
Fax +33 1 34245501
mail@weidmuller.fr

GB **Great Britain**
Weidmüller Ltd.
1 Abbey Wood Road
West Malling, Kings Hill
ME19 4YT
Phone +44 1732 877000
Fax +44 1732 874296

GR **Greece**
Electrorama S.A.
1 An. Martali Str.
41335 Larissa
Phone +30 2410 552533188
Fax +30 2410 283463189
valvizos@electrorama.com.gr

HK **Hong Kong**
United Equity Limited
Suite B, 11/F International Industrial
Centre
2-8 Kwei Tei Street, Fotan, Shatin
Phone +852 26876739
Fax +852 26876735
united_equity@sinatown.com

HR **Croatia**
Elektro Partner d.o.o.
Slavonska Avenija 24/6
10000 Zagreb
Phone +385 1 6184793
Fax +385 1 6184795
elektropartner@zg.t-com.hr

HU **Hungary**
Weidmüller Kereskedelmi Kft
Mádi utca 50
1104 Budapest
Phone +36 1 464-7888
Fax +36 1 3827701
info@weidmueller.hu

ID **Indonesia**
PT. Nego Electrindo
Ruko Mega Grosir Cempaka Mas,
Blok I No 20 – 22
Jl. Let.Jend. Suprato –
Jakarta 10640
Phone +62 21 42882255
Fax +62 21 42882266
sales@negoelectrindo.co.id

IE **Ireland**
Please contact Weidmüller Ltd. in
Great Britain

IL **Israel**
A.U.Shay Ltd.
P.O. Box 10049
Embar Street 23/25
Petch-Tikwa 49222
Phone +972 3 9233601
Fax +972 3 9234601

Israel
ATEKA Ltd.
23 Hayetzira St.
Kiryat Aryeh
49130 Petach-Tikva, Israel
Phone +972 3 9392344
Fax +972 3 9243273
marketing@ateka.co.il
www.ateka.co.il

IN **India**
Weidmuller Electronics India Pvt. Ltd
Plot # 32, 3rd Floor , North Court
Lane North Avenue , Opp Jogger's Park
Kalyani Nagar, Maharastra
411006 Pune
Phone +91 9049800960
Nitish.Rajan@weidmueller.de

IR **Iran**
Tamin Ehtiajat Fani Tehran (TAF Co.)
72, Iranshahr Ave.(Unit # 5)
15816 Tehran
Phone +98 21 8831-7851
Fax +98 21 8882-0268
tafco@safineh.net

IS **Iceland**
Samey Automation Center
Lyngas 13, 210 Garoabaer,
Phone +354 510 5200
Fax +354 510 5201
samey@samey.is

IT **Italy**
Weidmüller S.R.L.
Via Albert Einstein 4
20092 Cinisello Balsamo
Milano
Phone +39 02 660681
Fax +39 02 6124945
weidmuller@weidmuller.it
www.weidmuller.it

JO **Jordan**
HORIZONS
P.O.Box: 330607
Amman Jordan 11133
Phone +962 6 4882114
Fax +962 6 4882115
horizons@go.com.jo

JP **Japan**
Nihon Weidmüller Co. Ltd.
Sphere Tower Tennoz,
2-2-8 Higashi-Shinagawa,
Shinagawa-Ku, Tokyo 140-0002
Phone +81 3 6711-5300
Fax +81 3 6711-5333
www.weidmuller.co.jp

KR **Korea**
Weidmüller Korea Co., Ltd.
6floor, Sukyoung building, 242-54
Nonhyun-dong, Kangnam-Gu
Seoul, Korea
Zip: 135-830
Phone +82 2 5160003
Fax +82 2 5160090
info@weidmuller.co.kr

Group companies DE

Agency abroad DE

Without own Agency DE

KW **Kuwait**
KANA CONTROLS General Trading & Cont. CO. W.L.L.
Al Rai Industrial Area,
Plot 28-30, St. 31
P.O.Box: 25593
Safat, 13016
Phone +966-474 1373/4
Fax +966-474 1537
info@kanacontrols.com

KZ **Kazakhstan**
Please contact our Weidmüller branch office in Moscow, Russia

LB **Lebanon**
Progress Engineering & Trading Enterprises
Al Nahr Street
Beirut
Phone +961 1 444664
Fax +961 1 561880
progress@inco.com.lb

LT **Lithuania**
ELEKTROS IRANGA
Tinklu g.29a, 5319 Panevezys
Phone +370 45582828
Fax +370 45582727
info@eliranga.lt

LU **Luxembourg**
Please contact Weidmüller Benelux B.V. in the Netherlands

LV **Latvia**
Please contact our Weidmüller branch office in Estonia

MD **Moldova**
BERHORD A&D srl
44, srt. Sarmizegetusa 37/3
Off 414. b-dul Decebal, 3,
Chisinau, MD 2001
Phone +373 22 507137
Fax +373 22 507134
atiuleanu@berhord.com

MK **Macedonia**
ELEKTRO – SMK dooel
UL. III Makedonska brigada b.b.
1000 Skopje
Phone +389 22 460 295
Fax +389 22 460 298
Elektro-smk@telekabel.net.mk

MT **Malta**
E. S. S., Electrical Supplies & Services Ltd
104 J. Sciberras Str.
Hamrun HMR 08
Phone +356 21 255 777
Fax +356 21 255 999
robert@ess.com.mt

MX **Mexico**
W Interconnections, S.A. DE C.V.
Blvd. Hermanos Serdán No. 698
Col. San Rafael Oriente
Puebla, C.P. 72029
Phone +52 222 22686227
clientes@weidmuller.com.mx

MY **Malaysia**
Connect Plus Technology Sdn Bhd
No. 43, Jalan PJS 11/22,
Bandar Sunway, 46150 Petaling Jaya
Selangor Darul Ehsan
Phone +60 3 5633 7363
Fax +60 3-5633 6562
paul@cptech.com.my
www.cptech.com.my

NL **Netherlands**
Weidmüller Benelux B.V.
Franciscusweg 221
1216 SE Hilversum
Postbus 1505
1200 BM Hilversum
Phone +31 35 6261261
Fax +31 35 6232044
info@weidmuller.nl

NO **Norway**
Siv. Ing. J. F. Knudtzen A/S
Billingstadsletta 97
P.O. Box 160
1378 Nesbru
Phone +47 66 983350
Fax +47 66 980955

NZ **New Zealand**
Cuthbert S. Steward Limited
27 Te Puni Street
POB 38496
Petone, Wellington
Phone +64 4 5686156
Fax +64 4 5686056
info@weidmueller.de

OM **Oman**
DAN INTERNATIONAL LLC.
PO.BOX 2901
111 Seeb
Phone +968 503 677
Fax +968 503 755
yedu@danintl.com

PE **Peru**
TECNOLOGÍA ELÉCTRICA Y SOLUCIONES S.A.C.
Calle Huandoy 501, Lima 32, Peru
Phone / Fax +51 1 562-0004
info@tecsol-peru.com

PH **Philippines**
Enclosure Systems Specialists Inc
W-15 La Fuerza Compound
2241 Don Chino Roces Avenue
Makati City 1231
Phone +63 2 813 8580
Fax +63 2 813 8596
sales_encsys@pldtdsl.net

PK **Pakistan**
Kana Controls (Pak)
Apartment No. 33 C III
Chenab Block,
Allama Iqbal Town
Lahore, Pakistan
Phone +92 42 5419948
+92 42 7845160
Fax +92 42 5422895
nadeem@kanapak.com
www.kanapak.com

PL **Poland**
Weidmüller Sp. z o.o.
Ul. Gołędzinowska 10
03-302 Warszawa
Phone +48 22 5100940
Fax +48 22 5100941
biuro@weidmuller.com.pl
www.weidmuller.pl

PT **Portugal**
Weidmüller Sistemas de Interface S. A.
Estrada Outeiro Polima, R. Augusto Dias da Silva, Lote B, Esct. 2
2785-515 Abóboda -São Domingos de Rana
Phone +351 21 4459191
Fax +351 21 4455871
www.weidmueller.pt

QA **Qatar**
Doha Motors Trading Co.
(Technical Division)
Post Box No. 145
Airport Road
Doha - Qatar
Phone +974 465 1441
Fax +974 465 0925
dmtctech@qatar.net.qa

RO **Romania**
Rominterface Impex SRL
Str. Gh. Dem Teodorescu 30 A
30916 Bucuresti - sector 3
Phone +40 21 3220230
Fax + 40 21 3228857
office@rominterface.ro

RU **Russia**
Weidmüller Interface GmbH & Co. KG
Representative Office
Ul. Shabolovka 2
119049 Moscow, Russia
Phone +7 4 95 771-6940
Fax +7 4 95 771-6941
info@weidmueller.ru
www.weidmueller.ru

SA **Saudi Arabia**
Al Abdulkarim Holding Co.
P.O Box. 4
Dammam 31411
Phone +9668337110
Fax +9668338242
salehsk@akh.com.sa
www.akte.com.sa

Saudi Electric Supply Co.
P.O. Box 3298
Al Khobar 31952
Phone +966 3 882 9546227
Fax +966 3 882 9547
Safdar.malik@sesco-ge.com

SE **Sweden**
Weidmüller AB
Axel Daniessons väg 271
P.O. box 31025
200 49 Malmö
Phone +46 (0) 7 71 43 00 44
Fax +46 (0) 40 37 48 60
info@weidmuller.se
www.weidmuller.se

SG **Singapore**
Weidmuller Pte. Ltd.
70 Bendemeer Road
#04-03 Luzerne
Singapore 339940
Phone +65 6841 5311
Fax +65 6841 5377
info@weidmuller.com.sg
www.weidmuller.com.sg

SI **Slovenia**
ELEKTROSPOJI d.o.o.
Stegne 25, 1000 Ljubljana
Phone +386 15113810
Fax +386 15111604
info@elektrospoji.si
www.elektrospoji.si

SK **Slovakia**
ELEKTRIS s.r.o.
Elektrárenská 1
83104 Bratislava
Phone +421 2 49200113
Fax +421 2 49200119
weidmueller@computel.sk

TH **Thailand**
Pisanu Engineering Co., Ltd
800/2 Asoke Dindaeng Road,
Dindaeng, Bangkok 10400
Phone +66 2 245 9113
Fax +66 2 2463214
pisanu@kanit.co.th
www.pisanu.co.th

TN **Tunisia**
Please contact Weidmüller E.U.R.L. in France

TR **Turkey**
Weidmüller Elektronik Ticaret Ltd. Sirketi
Kavacik Mah. Orhan Veli Kanik Caddesi 9/1
34810 Beykoz – İstanbul
Phone +90 216 5371070 (Pbx)
Fax +90 216 5371077
info@weidmuller.com.tr
www.weidmuller.com.tr

TW **Taiwan**
Fittatek Co., Ltd.
12F No. 185 Fu-Kuo Road,
Tso Ying Dist
Kaohsiung
Phone +886 7 556 0858
Fax +886 7 556 3279
stanley@fittatek.com.tw
www.fittatek.com.tw

Taiwan
Eucan Enterprise Ltd.
No. 145 He Ping 2nd Rd
Kaohsiung
Phone +886 7 715 6610
Fax +886 7 715 8748
mark@eucan.com.tw
www.eucan.com.tw

UA **Ukraine**
TEKO INTERFACE ooo
ul. Lewanewskogo 6
03058 Kiev
Phone +38 044 401 09 90
Fax +38 044 401 08 64
weidmueller@tekointerface.com
www.tekointerface.com.ua

US **United States**
W-Interconnections Inc.
821 Southlake Boulevard,
Virginia - Richmond 23236
Phone +1 804 7942877
Fax +1 804 3792593
info@weidmuller.com
www.weidmuller.com

UY **Uruguay**
REWO Uruguay S.A
Av. Bolivia 2001 Esq Rocafuerte
Carrasco Montevideo 11300
Phone / Fax +598 260 48439
clorda@rewouruguay.com.uy

UZ **Uzbekistan**
OOO "Elektro Potential"
Gani Mavljanova str., 2B
100084 Tashkent
Phone +998 98-3003821
Fax +998 71-1249286
mz1958@yandex.ru

VE **Venezuela**
Somerinca C.A.
Quinta Sagrado Corazon de Jesus - 3ra Transversal - Los Dos Caminos,
Caracas 1070 - A
Phone +58 212 2352748
Fax +58 212 2399341
klocmoeller@cantv.net
www.kmsomerinca.com.ve

VN **Vietnam**
AUMI Co., Ltd
E1, La Thanh Hotel,
218 Doi Can Street,
Lieu Giai Ward, Ba Dinh District,
Hanoi City
Phone +84 4762 8601
Fax +84 4266 1391
aumi@aumi.com.vn

Linh Kim Hai Co,. Ltd
78 Hoa Cuc Street Ward 7,
Phu Bhuan District,
Ho Chi Minh City
Phone +84 8517 1717
Fax +84 8517 1818
lkh@linhkimhai.com.vn

New Sky Co., Ltd
44/28 Tan Hai Street,
Ward 13, Tan Binh District,
Ho Chi Minh City
Phone +84 8812 6593
Fax +84 8812 6594
newsky-e@hcm.vnn.vn
www.newsky-e.com

ZA **South Africa**
Phambili Interface (Pty) Ltd
P.O. Box 193, 1609 Johannesburg
5 Bundo Road, Sebenza
1610 Johannesburg, Endenvale
Phone +27 11 452 1930
Fax +27 11 452 6455
sales@weidmuller.co.za
www.radinterface.co.za

DE **Other countries**
Weidmüller Interface GmbH & Co. KG
Postfach 3030
32720 Detmold
Klingenbergstraße 16
32758 Detmold
Phone +49 5231 14-0
Fax +49 5231 14-2083
info@weidmueller.de
www.weidmueller.com

We cannot guarantee that there are no mistakes in the publications or software provided by us to the customer for the purpose of making orders. We try our best to quickly correct errors in our printed media.

All orders are based on our general terms of delivery, which can be reviewed on the websites of our group companies where you place your order. On demand we can also send the general terms of delivery to you.