




AD6025(T) SERIES

External Dimensions



Frame: Plastic(UL:94V-0)
Impeller: Plastic(UL:94V-0)
Lead wire: UL1007AWG24

Specifications(Nominal)


*Noise is measured at the distance of one (1) meter from the axis of intake.

Bearing type: ◎=Ball ※=Sleeve ●=Hypro bearing

Frame size (mm)	Model No.	Bearing System Type	Rated Voltage (VDC)	Current (A)	Power (W)	Rated Speed (rpm)	Maximum AirFlow (CMM) (CFM)	Maximum Pressure (InAq) (mmAq)	*Noise Level (dB/A)	Weight (g)
60x60x25	AD06005LB257000	◎ ※ ●	5	0.07	0.35	2500	0.360 12.710	0.080 1.930	15.9	53.0
	AD06005MB257000	◎ ※ ●	5	0.14	0.70	3500	0.490 17.340	0.130 3.330	26.9	
	AD06005HB257000	◎ ※ ●	5	0.28	1.40	4500	0.660 23.340	0.230 5.920	33.8	
	AD06012DB257000	◎ ※ ●	12	0.03	0.36	2000	0.280 9.980	0.050 1.240	12.4	
	AD06012LB257000	◎ ※ ●	12	0.04	0.48	2500	0.360 12.710	0.080 1.930	15.9	
	AD06012MB257000	◎ ※ ●	12	0.06	0.72	3500	0.490 17.340	0.130 3.330	26.9	
	AD06012HB257000	◎ ※ ●	12	0.12	1.44	4500	0.660 23.340	0.230 5.920	33.8	
	AD06012UB257000	◎ ※ ●	12	0.18	2.16	5000	0.740 25.970	0.280 7.190	37.1	
	AD06024MB257000	◎ ※ ●	24	0.03	0.72	3500	0.490 17.340	0.130 3.330	26.9	
	AD06024HB257000	◎ ※ ●	24	0.06	1.44	4500	0.660 23.340	0.230 5.920	33.8	
	AD06024UB257000	◎ ※ ●	24	0.08	1.92	5000	0.740 25.970	0.280 7.190	37.1	
	AD06024XB257000	◎ ※ ●	24	0.14	3.36	6000	0.890 31.380	0.370 9.300	42.8	

Specifications subject to change without notice.

The specification for bearing type is for reference only , for more bearing types information, please contact with your ADDA sales representative, thanks!!
(網頁上呈現產品軸承資訊均以2Ball為主，若需其他產品資訊請聯絡您在ADDA的業務代表，謝謝!!)



*Motor protective circuit and third lead wire functions

0	1	2	3	4	6	7	8	9	A	B
✓					✓					

*Safety approvals

UL	cUL	SP	UL	CE
✓	✓		✓	✓

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[ADDA:](#)

[AD0624HS-A76GL\(R1\)-LF](#) [AD0612HB-A72GL\(T\)-LF](#) [AD0624HB-A76GL-LF](#) [AD0624UB-A71GL-LF](#)