


Double-Pole Round Rocker Switch

RR Series



Features

- Single Pole and Double pole configurations
- Lighted and non-lighted options
- Industry standard cutout
- Mechanical life: min. 100,000 operations

Electrical Ratings				
Switch Series	EN61058 Rating	UL1054 Rating	Electrical Life at Rated Load	
			According to VDE (Min. Operations)	According to UL (Min. Operations)
RR	10(4)A, 250V~ T125/55	10A 125VAC 1/4HP 8A 250VAC 1/4HP	10,000	6,000

Electrical Specifications		Material Specifications	
Ratings:	10A, 125VAC 1/4HP 8A 250VAC 1/4HP; (cULus) 10(4)A, 250V~ T125/55 (VDE)	Actuator:	Nylon 66 94V-2
Dielectric Strength:	1000VAC for 1 minute	Base:	Nylon 66 94V-2
Insulation Resistance:	100M ohms min at 500VDC	Spring:	Steel Wire
Initial Contact Resistance:	0.020 ohms max	Contacts:	Silver Alloy
Temperature Range:	-20°C to + 65°C	Movable Arm:	Copper Alloy
		Terminals:	Tin-Plated Copper Alloy

RoHS Compliant
UL File No: E23301




Specifications subject to change without notice.




Single-Pole Rocker Switch

RR Series

Dimensions inches



Recommended Panel Cut-Out Dimensions
Inches(mm)
0.039 to 0.078 (1.0 to 2.0)



Ordering Information

RR		A		2		2		3		F		B		B		N		N							
Series				Code		Circuitry		Code		Switch Function		Code		Actuator Type		Code		Housing Color		Code		Lighted			
				2		Single Pole		2		On - Off		3		Round				B		Black		N		Non-Lighted	
				3		Double Pole												E		Charcoal Grey		L		Lighted (Bulb 125VAC)	
																		W		White		E		Lighted (Bulb 250VAC)	
																		Y		Grey		G		Lighted 6VDC Incandescent	
																						H		Lighted 12VDC Incandescent	
Code		Contact Rating																							
A		10A 125VAC 1/4 HP 8A 250VAC 1/4HP cULus 10(4)A 250V ~ T125/55 VDE																							
				Code		Terminal type inches (mm)																			
				H		0.187 (4.8) QC																			
				L		PC Thru-Hole Right Angle																			
				M		PC Thru-Hole Straight																			
								Code		Actuator Marking															
								B		Blank															
								D																	
								E		O															
								F		O															
								G		.															
												Code		Actuator Color											
												A		Amber											
												B		Black											
												E		Charcoal Grey											
												G		Green											
												R		Red											
												W		White											
												Y		Grey											
																Code		Splashproof							
																N		No Rocker Boot							

Examples of Common Part Numbers and Descriptions inches (mm)

Part Number	Circuitry	Switch Function	Terminal Type	Actuator/ Housing Color	Legend Marking
RRA22H3BBBNN		On - Off	0.187 (4.8) Quick-Connect	Black/ Black	
RRA22H3FBBNN		On - Off	0.187 (4.8) Quick-Connect	Black/ Black	
RRA22H3BWWNN		On - Off	0.187 (4.8) Quick-Connect	White/ White	
RRA22H3FBRNN		On - Off	0.187 (4.8) Quick-Connect	Red/ Black	
RRA22H3BBRLN		On - Off/Lighted	0.187 (4.8) Quick-Connect	Red/ Black	
RRA22H3BBRLN		On - Off/Lighted	0.187 (4.8) Quick-Connect	Red/ Black	

Contact

Call, fax or visit our
Website for more information.

ZF Electronics Corporation
11200 88th Avenue
Pleasant Prairie, WI 53158

Phone: 262.942.6500
Web: www.cherrycorp.com
Email: cep_sales@zf.com
Fax: 262.942.6566

The manufacturer accepts no
liability for errors or non-availability,
and reserves the right to change
specifications without prior notice.

Technical data relates to product
specifications only. Features may
differ from those described. Only
drawings combined with product
specifications shall be deemed
binding.

© 2007 ZF Electronics Corporation

Last Updated: 10/01/12

