



MICRO SWITCH
FREEPORT ILLINOIS U.S.A.
A DIVISION OF HONEYWELL
FED. MFG. CODE 91929

SWITCH - ENCLOSED


CATALOG LISTING
41EN46-2



CIRCUIT DIAGRAM



CHARACTERISTICS



NOTES

- 1 - CORROSION RESISTANT STEEL ENCLOSURE
- 2 - SWITCH SEALED PER MIL-PRF-8805 SYMBOL 4
- 3 - CIRCUIT DIAGRAM AND CAT. LIST. ARE SHOWN ON NAMEPLATE
- 4 - UNIT PROVIDES NO SHAFT RESTORING TORQUE. THE ACTUATING DEVICE MUST CONTROL MOVEMENT OF SHAFT
- 5 - SHIELDING OF LEADS NO. 2 AND NO. 3 IS NOT ATTACHED TO SWITCH
- 6 - MARKED WITH CIRCUIT IDENTIFICATION (16C, 11NC, ETC) PER MIL-W-5088
- 7 - HARDWARE MAY BE PACKAGED UNASSEMBLED PER MIL-PRF-8805

THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF MICRO SWITCH, A DIVISION OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE APPROVAL OF MICRO SWITCH.

THIRD ANGLE PROJECTION

SCALE FULL

DO NOT SCALE PRINT

TOLERANCES
APPLY TO DESIGN UNITS. CONVERSIONS ARE ONLY FOR REFERENCE. UNLESS NOTED, TOLERANCES ARE ±

DIM.	TOL.	DIM.	TOL.
mm	mm/in	in	mm/in
NO PLACES	X	1/04	
ONE PLACE	X,X	0.4/018	X,X
TWO PLACES	X,XX	0.15/006	X,XX
THREE PLACES	X,XXX		X,XXX
ANGLES			

SI METRIC ☐ US CUSTOMARY ☒

RAW MATERIAL - COMMERCIAL STANDARD
MICRO SWITCH STANDARDS APPLY
DIMENSIONS ARE TO BE MET BEFORE
PROTECTIVE COATINGS ARE APPLIED

WEIGHT

CHARACTERISTICS

OPERATING TORQUE - - - - 3 IN. LB MAX

PRETRAVEL
DIFFERENTIAL TRAVEL
OVERTRAVEL
FREE POSITION

SEE DETAIL

ELECTRICAL DATA

CONTACT ARRANGEMENT
SPDT (1) SPNO (1)

LOAD	28 VDC	
	SEA LEVEL	50,000 FT.
RES	4	4
IND	3	1
MOTOR	4	-
LAMP	2.4	2.4

RASTER

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[41EN46-2](#)