

Srew Pitch Gauges



Accurately milled gauges for checking internal and external thread forms.

489394

Description	No of blades	Size	Order Code	Price Each
Unified	30	4, 4½, 5, 5½, 6, 7, 8, 9, 10, 11, 11½, 12, 13, 14, 15, 16, 18, 20, 22, 24, 26, 27, 28, 30, 32, 34, 36, 38, 40, 42	137-6812	
American National	30	4, 4½, 5, 5½, 6, 7, 8, 9, 10, 11, 11½, 12, 13, 14, 15, 16, 18, 20, 22, 24, 26, 27, 28, 30, 32, 34, 36, 38, 40, 42	137-6813	
Whit	28	4, 4½, 5, 6, 7, 8, 10, 11, 12, 13, 14, 16, 18, 19, 20, 22, 24, 25, 26, 28, 30, 32, 36, 40, 48, 60 blades and 55° screw cutting gauge	137-6814	
SI Metric	30	0.25, 0.3, 0.35, 0.4, 0.45, 0.5, 0.55, 0.6, 0.65, 0.7, 0.75, 0.8, 0.85, 0.9, 1.0, 1.1, 1.2, 1.25, 1.3, 1.4, 1.5, 1.6, 1.7, 1.75, 1.8, 1.9, 2.0, 2.5, 3.0 blades and 60° screw cutting gauge	137-6815	
Combination set Metric/Whit	50	7.0, 6.5, 6.0, 5.5, 5.0, 4.5, 4.0, 3.5, 3.0, 2.5, 2.0, 1.75, 1.5, 1.25, 1.0, 0.8, 0.75, 0.7, 0.6, 0.5, 0.4 blades plus Whit as No. 800 gauge	137-6816	
ISO/Metric	22	6.0, 5.5, 5.0, 4.5, 4.0, 3.5, 3.0, 2.5, 2.0, 1.75, 1.5, 1.25, 1.0, 0.8, 0.75, 0.7, 0.6, 0.5, 0.45, 0.4, 0.35 blades	137-6817	