

Tyco / Electronics
Raychem Circuit Protection
 308 Constitution Drive
 Menlo Park, CA 94025-1164
 Phone: 800-227-4856
 Fax: 800-227-4866

PolySwitch®
PTC Devices
 Overcurrent Protection Device

PRODUCT: SRP350

DOCUMENT: SCD 21791
 PCN: 715141
 REV LETTER: G
 REV DATE: JULY 25, 2002
 PAGE NO.: 1 OF 1

Specification Status: RELEASED

Electrical Rating

Voltage: 30V MAX

Current: 100A MAX

Leads:

Nickel: 0.125 mm Nominal
 Thickness

Tape:

Polyester

Marking:

— Manufacturer's Mark
 X 350 — Part Identification
 □ □ □ □ — Lot Identification




TABLE I. DIMENSIONS:

	A		B		C		D		E		F		G	
	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX	MIN	MAX
mm:	28.4	31.8	13.0	13.5	0.5	1.1	6.3	8.9	6.3	8.9	6.0	6.6	--	--
in*:	(1.12)	(1.25)	(0.51)	(0.53)	(0.02)	(0.04)	(0.25)	(0.35)	(0.25)	(0.35)	(0.24)	(0.26)	--	--

*Rounded off approximation

TABLE II. PERFORMANCE RATINGS:

I HOLD	CURRENT TRIP LIMITS								TIME TO TRIP		REFERENCE RESISTANCE		ONE-HOUR POST-TRIP RESISTANCE		TRIPPED-STATE POWER DISSIPATION	
AMPS 20°C HOLD	AMPS AT 0°C HOLD TRIP		AMPS AT 20°C HOLD TRIP		AMPS AT 60°C HOLD TRIP		AMPS AT 80°C HOLD TRIP		SECONDS AT 20°C, 20 A TYP MAX		OHMS AT 20°C MIN MAX		OHMS AT 20°C MIN MAX		WATTS AT 20°C, 15V TYP MAX	
3.5	4.3	7.2	3.5	6.3	2.5	4.4	--	--	1.5	3.0	0.017	0.031	0.017	0.050	1.9	2.5

Recognitions:

Reference Documents:

Precedence:

Effectivity:

CAUTION:

UL/TUV approved

PS300

This specification takes precedence over documents referenced herein.

Reference documents shall be the issue in effect on the date of invitation for bid.

Operation beyond the rated voltage or current may result in rupture, electrical arcing or flame.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[TE Connectivity:](#)

[SRP350](#)