

# EMSL12C2H-8.000M TR

[Click part number to visit Part Number Details page](#)

## REGULATORY COMPLIANCE (Data Sheet downloaded on Nov 27, 2017)


[Click badges to download compliance docs](#)

Regulatory Compliance standards are subject to updates by governing bodies. Click the badges to download the latest compliance docs for this part number directly from Ecliptek.



## ITEM DESCRIPTION

MEMS Clock Oscillators HCSL 2.5Vdc 6 Pad 5.0mm x 7.0mm Plastic Surface Mount (SMD) 8.000MHz  $\pm 100$ ppm over 0°C to +70°C

## ELECTRICAL SPECIFICATIONS

|                                                   |                                                                                                                                                                                                                                                                   |
|---------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Nominal Frequency                                 | 8.000MHz                                                                                                                                                                                                                                                          |
| Frequency Tolerance/Stability                     | $\pm 100$ ppm Maximum over 0°C to +70°C (Inclusive of all conditions: Calibration Tolerance at 25°C, Frequency Stability over the Operating Temperature Range, Supply Voltage Change, Output Load Change, First Year Aging at 25°C, Reflow, Shock, and Vibration) |
| Aging at 25°C                                     | $\pm 1$ ppm Maximum First Year                                                                                                                                                                                                                                    |
| Supply Voltage                                    | 2.5Vdc $\pm 5\%$                                                                                                                                                                                                                                                  |
| Input Current                                     | 65mA Maximum (Excluding Load Termination Current)                                                                                                                                                                                                                 |
| Output Voltage Logic High (Voh)                   | 600mVdc Minimum, 750mVdc Typical, 950mVdc Maximum                                                                                                                                                                                                                 |
| Output Voltage Logic Low (Vol)                    | 0mVdc Minimum, 25mVdc Typical, 50mVdc Maximum                                                                                                                                                                                                                     |
| Rise/Fall Time                                    | 300pSec Typical, 350pSec Maximum (Measured over 20% to 80% of waveform)                                                                                                                                                                                           |
| Duty Cycle                                        | 50 $\pm 5\%$ (Measured at 50% of waveform)                                                                                                                                                                                                                        |
| Output Swing (VOpp)                               | 600mVdc Minimum, 750mVdc Typical, 950mVdc Maximum                                                                                                                                                                                                                 |
| Load Drive Capability                             | 50 Ohms to Ground (Output and Complementary Output)                                                                                                                                                                                                               |
| Output Logic Type                                 | HCSL                                                                                                                                                                                                                                                              |
| Logic Control / Additional Output                 | Output Enable (OE) and Complementary Output                                                                                                                                                                                                                       |
| Output Control Input Voltage                      | Vih of 70% of Vdd Minimum or No Connect to Enable Output and Complementary Output, Vil of 30% of Vdd Maximum to Disable Output and Complementary Output (High Impedance)                                                                                          |
| Output Enable Current                             | 60mA Maximum (Without Load)                                                                                                                                                                                                                                       |
| Period Jitter (Deterministic)                     | 0.2pSec Typical                                                                                                                                                                                                                                                   |
| Period Jitter (Random)                            | 2.0pSec Typical                                                                                                                                                                                                                                                   |
| Period Jitter (RMS)                               | 1.5pSec Typical, 3.0pSec Maximum                                                                                                                                                                                                                                  |
| Period Jitter (pk-pk)                             | 20pSec Typical, 25pSec Maximum                                                                                                                                                                                                                                    |
| Period Jitter (Cycle to Cycle)                    | 10pSec Typical                                                                                                                                                                                                                                                    |
| RMS Phase Jitter (Fj = 637kHz to 10MHz; Random)   | 1.7pSec Typical                                                                                                                                                                                                                                                   |
| RMS Phase Jitter (Fj = 1.5MHz to 22MHz; Random)   | 0.8pSec Typical                                                                                                                                                                                                                                                   |
| RMS Phase Jitter (Fj = 1.875MHz to 20MHz; Random) | 0.7pSec Typical                                                                                                                                                                                                                                                   |
| Start Up Time                                     | 10mSec Maximum                                                                                                                                                                                                                                                    |
| Storage Temperature Range                         | -55°C to +125°C                                                                                                                                                                                                                                                   |

## ENVIRONMENTAL & MECHANICAL SPECIFICATIONS

|                              |                                                |
|------------------------------|------------------------------------------------|
| ESD Susceptibility           | MIL-STD-883, Method 3015, Class 2, HBM 2000V   |
| Flammability                 | UL94-V0                                        |
| Mechanical Shock             | MIL-STD-883, Method 2002, Condition G, 30,000G |
| Moisture Resistance          | MIL-STD-883, Method 1004                       |
| Moisture Sensitivity Level   | J-STD-020, MSL 1                               |
| Resistance to Soldering Heat | MIL-STD-202, Method 210, Condition K           |
| Resistance to Solvents       | MIL-STD-202, Method 215                        |




EMSL12C2H-8.000M TR [Click part number to visit Part Number Details page](#)

| ENVIRONMENTAL & MECHANICAL SPECIFICATIONS CONTINUED |                                                                   |
|-----------------------------------------------------|-------------------------------------------------------------------|
| Solderability                                       | MIL-STD-883, Method 2003 (Six I/O Pads on bottom of package only) |
| Temperature Cycling                                 | MIL-STD-883, Method 1010, Condition B                             |
| Thermal Shock                                       | MIL-STD-883, Method 1011, Condition B                             |
| Vibration                                           | MIL-STD-883, Method 2007, Condition A, 20G                        |

EMSL12C2H-8.000M TR

[Click part number to visit  
Part Number Details page](#)

MECHANICAL DIMENSIONS (all dimensions in millimeters)




Note A: Center paddle is connected internally to oscillator ground (Pad 3).

| PIN | CONNECTION           |
|-----|----------------------|
| 1   | Output Enable (OE)   |
| 2   | No Connect           |
| 3   | Case Ground          |
| 4   | Output               |
| 5   | Complementary Output |
| 6   | Supply Voltage       |

| LINE | MARKING                                                             |
|------|---------------------------------------------------------------------|
| 1    | XXXX or XXXXX<br>XXXX or XXXXX=Ecliptek<br>Manufacturing Identifier |

Suggested Solder Pad Layout

All Dimensions in Millimeters




All Tolerances are ±0.1

EMSL12C2H-8.000M TR

[Click part number to visit  
Part Number Details page](#)


OUTPUT WAVEFORM & TIMING DIAGRAM



# EMSL12C2H-8.000M TR

[Click part number to visit Part Number Details page](#)

## Test Circuit for Output Enable and Complementary Output



Note 1: An external  $0.01\mu\text{F}$  ceramic bypass capacitor in parallel with a  $0.1\mu\text{F}$  high frequency ceramic bypass capacitor close (less than 2mm) to the package ground and supply voltage pin is required.

Note 2: A low capacitance ( $<12\text{pF}$ ), 10X attenuation factor, high impedance ( $>10\text{Mohms}$ ), and high bandwidth ( $>500\text{MHz}$ ) passive probe is recommended.

Note 3: Test circuit PCB traces need to be designed for a characteristic line impedance of 50 ohms.

Note 4: A 10 ohm to 33 ohm series resistor is required to limit overshoot.  $R_s$  value is circuit layout dependant.



# EMSL12C2H-8.000M TR

## Tape & Reel Dimensions

Quantity Per Reel: 1,000 units

All Dimensions in Millimeters

Compliant to EIA-481



EMSL12C2H-8.000M TR

[Click part number to visit Part Number Details page](#)

Recommended Solder Reflow Methods




High Temperature Infrared/Convection

|                                     |                                      |
|-------------------------------------|--------------------------------------|
| Ts MAX to TL (Ramp-up Rate)         | 3°C/Second Maximum                   |
| Preheat                             |                                      |
| - Temperature Minimum (Ts MIN)      | 150°C                                |
| - Temperature Typical (Ts TYP)      | 175°C                                |
| - Temperature Maximum (Ts MAX)      | 200°C                                |
| - Time (ts MIN)                     | 60 - 180 Seconds                     |
| Ramp-up Rate (TL to TP)             | 3°C/Second Maximum                   |
| Time Maintained Above:              |                                      |
| - Temperature (TL)                  | 217°C                                |
| - Time (tL)                         | 60 - 150 Seconds                     |
| Peak Temperature (TP)               | 260°C Maximum for 10 Seconds Maximum |
| Target Peak Temperature (TP Target) | 250°C +0/-5°C                        |
| Time within 5°C of actual peak (tp) | 20 - 40 Seconds                      |
| Ramp-down Rate                      | 6°C/Second Maximum                   |
| Time 25°C to Peak Temperature (t)   | 8 Minutes Maximum                    |
| Moisture Sensitivity Level          | Level 1                              |

EMSL12C2H-8.000M TR

 [Click part number to visit Part Number Details page](#)

Recommended Solder Reflow Methods



Low Temperature Infrared/Convection 240°C

|                                     |                                                        |
|-------------------------------------|--------------------------------------------------------|
| TS MAX to TL (Ramp-up Rate)         | 5°C/Second Maximum                                     |
| Preheat                             |                                                        |
| - Temperature Minimum (TS MIN)      | N/A                                                    |
| - Temperature Typical (TS TYP)      | 150°C                                                  |
| - Temperature Maximum (TS MAX)      | N/A                                                    |
| - Time (ts MIN)                     | 60 - 120 Seconds                                       |
| Ramp-up Rate (TL to TP)             | 5°C/Second Maximum                                     |
| Time Maintained Above:              |                                                        |
| - Temperature (TL)                  | 150°C                                                  |
| - Time (tL)                         | 200 Seconds Maximum                                    |
| Peak Temperature (TP)               | 240°C Maximum                                          |
| Target Peak Temperature (TP Target) | 240°C Maximum 2 Times / 230°C Maximum 1 Time           |
| Time within 5°C of actual peak (tP) | 10 Seconds Maximum 2 Times / 80 Seconds Maximum 1 Time |
| Ramp-down Rate                      | 5°C/Second Maximum                                     |
| Time 25°C to Peak Temperature (t)   | N/A                                                    |
| Moisture Sensitivity Level          | Level 1                                                |

Low Temperature Manual Soldering

185°C Maximum for 10 Seconds Maximum, 2 times Maximum.

High Temperature Manual Soldering

260°C Maximum for 5 Seconds Maximum, 2 times Maximum.