



### FEATURES

- Full Load Efficiency up to 93.5% @220VAC
- Metal Case Box Type Package
- Package Dimension:  
110.8x50.8x13.7mm (4.36"x2.0"x0.54")
- Operating Baseplate Temperature Range - 40°C to +100°C
- Input Brown-Out, Output OCP, OTP, OVP, SHORT protection
- 3000VAC Isolation
- RoHs Compliant
- CE Mark
- EMC compatible: CISPR22 ClassB (with EMC Board)
- ISO 9001, ISO 14001 certified manufacturing facility
- UL60950-1 (US&Canada)

The PACSR24021, a wide input voltage range of 85~265VAC, and single isolated output converter, is the latest product offering from a world leader in power systems technology and manufacturing — Delta Electronics, Inc. Such module type ACDC converter can provide 500W, 24V regulated DC output voltage with full load efficiency up to 93.5% @220VAC; The PACSR24021 offers Brown-out, output OCP, OTP, OVP and Short protections, and allows a wide operating baseplate temperature range of -40°C to +100°C. With creative design technology and optimization of component placement, this converter possess outstanding electrical and thermal performance, as well as high reliability under extremely harsh operating conditions.

### Input Characteristics

| Item                                 | Condition                | Min. | Typ.    | Max. | Unit |
|--------------------------------------|--------------------------|------|---------|------|------|
| Rated input voltage range            |                          | 100  | 110/220 | 240  | VAC  |
| Max input voltage range              |                          | 85   |         | 265  | VAC  |
| Input voltage frequency range        |                          | 45   | 50/60   | 65   | Hz   |
| Maximum Input Current                | Vin=85VAC, 100% Load     |      |         | 7    | A    |
| Open load loss                       |                          |      | 2.5     |      | W    |
| Input PF value                       | Vin=110VAC, 100% Load    | 0.95 |         |      |      |
| Allowable bus capacitance range (*1) | Vin=110/220VAC 100% Load | 660  |         | 1000 | uF   |

### Output Characteristics

| Item                            | Conditions                                                        | Min. | Typ. | Max. | Unit |
|---------------------------------|-------------------------------------------------------------------|------|------|------|------|
| Output voltage setpoint         | Vin=220VAC, Io=0-10.5A                                            | 23.6 | 24   | 24.4 | Vdc  |
| Out put current range           |                                                                   | 0    |      | 21   | A    |
| Output OCP point                |                                                                   | 22   | 23.5 | 25   | A    |
| Turn-on rise time               |                                                                   |      | 20   |      | ms   |
| Start up time                   | Vin=110/220VAC                                                    |      | 1500 |      | mS   |
| Hold up time                    | Vin=110/220VAC, Io= 100% Load                                     |      | 20   |      | mS   |
| Output OVP point                |                                                                   | 27.5 | 29   | 30.5 | V    |
| Output trim range               | Trim up                                                           |      |      | 10   | %    |
|                                 | Trim down                                                         |      |      | 5    | %    |
| Output Current Transient        | Positive voltage step, 75% to 25% load dynamic, 0.1A/us slew rate |      | 800  | 1000 | mV   |
|                                 | Negative voltage step, 25% to 75% load dynamic, 0.1A/us slew rate |      | 800  | 1000 | mV   |
| Output Voltage Ripple and Noise | Vin=110/220VAC, Io=10, peak to peak, 20MHz bandwidth              |      | 150  |      | mV   |
|                                 | RMS                                                               |      | 80   |      | mV   |
| Output overshoot                |                                                                   |      |      | 3    | %    |
| Efficiency @ 60% Load           | Vin=110VAC                                                        |      | 91   |      | %    |
| Efficiency @ 60% Load           | Vin=220VAC                                                        |      | 92   |      | %    |
| Efficiency @ 100% Load          | Vin=110VAC                                                        |      | 92   |      | %    |

|                                         |                               |      |      |      |    |
|-----------------------------------------|-------------------------------|------|------|------|----|
| Efficiency @ 100% Load                  | Vin=220VAC                    |      | 93.5 |      | %  |
| Allowable output capacitance range (*2) | Vin=110/220VAC, Io= 100% Load | 1080 |      | 5000 | uF |

### General Characteristics

| Item                     | Conditions        | Min. | Typ. | Max. | Unit   |
|--------------------------|-------------------|------|------|------|--------|
| I/O Isolation Voltage    | Input to output   |      | 3000 |      | VAC    |
|                          | Input to case     |      | 1500 |      | VAC    |
|                          | Output to case    |      | 500  |      | VAC    |
| I/O Isolation Resistance | 500Vdc            | 10   |      |      | MΩ     |
| MTBF                     | Ta=25°C, 100%load |      | TBD  |      | Mhours |
| Weight                   |                   |      | 240  |      | g      |

### Environmental Specifications

| Parameter                   | Conditions       | Min. | Max. | Unit  |
|-----------------------------|------------------|------|------|-------|
| Storage Temperature Range   |                  | -40  | +125 | °C    |
| Operating Temperature Range | Case Temperature | -40  | +100 | °C    |
| Operating altitude          |                  |      | 3000 | meter |

### ELECTRICAL CURVE




Figure 1: Efficiency vs. Output current @ Vin=110,220VAC




Figure 2: Vout vs. Vin @ Full load






Figure 3: Output voltage vs. Output current @ Vin=110/220VAC


## ELECTRICAL CURVES (continuous)




**Figure 4:** Dynamic response to load step 25%~75% with 0.1A/uS slew rate at 110/220Vac  
TOP: Vout, 200mV/div, BOTTOM: Iout, 10A/div, 1ms/div




**Figure 6:** Output ripple & noise at 110/220Vac, 21A Iout  
VOUT: 50mV/div, 5ms/div



**Figure 8:** Inrush current @ Vin=220Vac Iin:10A/div, 5ms/div;




**Figure 5:** Vout start up with Enable on at 220Vac, 21A Iout,  
TOP: Vout, 10V/div, 500ms/div  
BOTTOM: Vin, 500V/div, 500ms/div



**Figure 7:** Output over voltage protection at 110/220Vac, 21A Iout  
VOUT: 5V/div, 500ms/div

## SIMPLIFIED APPLICATION CIRCUIT



*Figure 9: Application connection*

*TYPICAL value ADVISED*

| No | Location | item            | value               | Part No                                                                                                                          |
|----|----------|-----------------|---------------------|----------------------------------------------------------------------------------------------------------------------------------|
| 1  | Cap0     | bus cap         | 220uF/450V          | Capacitor should have good low-temperature characteristics, keep at least 75% capacitance at -40℃ if need -40C application. (*3) |
| 2  | Cap1     | bus cap         | 220uF/450V          |                                                                                                                                  |
| 3  | Cap2     | bus cap         | 220uF/450V          |                                                                                                                                  |
| 4  | Cap3     | Cap for pri-sec | 2200pF/250Vac Y1/X1 |                                                                                                                                  |
| 5  | Cap4     | Output cap      | 1000uF/35V          | ESR≤16m Ω (100kHz), Rated ripple≥2920mArms(105℃) (*4)                                                                            |
| 6  | Cap5     | Output cap      | 270uF/35V           | ESR≤17m Ω (100kHz), Rated ripple≥2200mArms(125℃) (*5)                                                                            |
| 7  | Cap6     | Output cap      | 270uF/35V           |                                                                                                                                  |
| 8  | Cap7     | Output cap      | 270uF/35V           |                                                                                                                                  |
| 9  | Cap8     | Output cap      | 270uF/35V           |                                                                                                                                  |
| 10 | F1       | Input Fuse      | 10A/250Vac          |                                                                                                                                  |
| 11 | RV1      | Input VDR       | 300VAC              | TVR14471K0OOTB9Y/THINKING                                                                                                        |
| 12 | RV2      | Input VDR       | 300VAC              | TVR14471K0OOTB9Y/THINKING                                                                                                        |
| 13 | RV3      | Input VDR       | 300VAC              | TVR14471K0OOTB9Y/THINKING                                                                                                        |
| 14 | RV4      | Input VDR       | 300VAC              | TVR14471K0OOTB9Y/THINKING                                                                                                        |
| 15 | GT1      | Input GAS TUBE  | 2.5KV/10KA          | B88069X8661S102(EF2500X8S)/ EPCOS PTE                                                                                            |
| 16 | C1       | Input Y-cap     | 100pF/250Vac Y2/X1  |                                                                                                                                  |
| 17 | C2       | Input Y-cap     | 4700pF/250Vac Y2/X1 |                                                                                                                                  |
| 18 | C3       | Input X-cap     | 1uF /305VAC X2      |                                                                                                                                  |
| 19 | C4       | Input X-cap     | 0.47uF /275VAC X2   |                                                                                                                                  |
| 20 | C5       | Input X-cap     | 0.47uF /275VAC X2   |                                                                                                                                  |
| 21 | C6       | Input Y-cap     | 100pF/250Vac Y2/X1  |                                                                                                                                  |
| 22 | C7       | Input Y-cap     | 4700pF/250Vac Y2/X1 |                                                                                                                                  |
| 23 | C8       | Cap for pri-PE  | 1500pF/250Vac Y1/X1 |                                                                                                                                  |
| 24 | C9       | output Y-cap    | 4700pF/250Vac Y2/X1 |                                                                                                                                  |
| 25 | C10      | output Y-cap    | 4700pF/250Vac Y2/X1 |                                                                                                                                  |
| 26 | C11      | output Y-cap    | 4700pF/250Vac Y2/X1 |                                                                                                                                  |
| 27 | C12      | output Y-cap    | 4700pF/250Vac Y2/X1 |                                                                                                                                  |
| 28 | C13      | Input Y-cap     | 100pF/250Vac Y2/X1  |                                                                                                                                  |
| 29 | C14      | Input Y-cap     | 100pF/250Vac Y2/X1  |                                                                                                                                  |
| 30 | L1       | Input chock     | 6.5mH φ 1mm         | PH9455.705NL/Pulse Electronics                                                                                                   |
| 31 | L2       | Input chock     | 6.5mH φ 1mm         |                                                                                                                                  |



\*read the Application Note for this module carefully before using the power supply unit

=Note=

\*1 and \*3 . About the bus cap, pls read the Application Note about the hold up time configure.

\*2 and \*5. About the min output cap, pls use the cap which has more performance than the cap in the table above, or refer the cap about the output cap ability in the Application Note.


\*2 and \*4. About the max output cap, pls follow the Application Note about the output cap ability.

## THERMAL CONSIDERATION

Thermal management is an important part of the system design. To ensure proper, reliable operation, sufficient cooling of the power module is needed over the entire temperature range of the module. Conduction cooling is usually the dominant mode of heat transfer.

### Thermal Testing Setup


The following figure shows the testing setup in which the power module is mounted on an Al plate and was cooled by cooling liquid.




**Figure 10:** Thermal test setup

## THERMAL DERATING CURVE

The following figure shows the location to monitor the temperature of the module's baseplate. The baseplate temperature in thermal curve is a reference for customer to make thermal evaluation and make sure the module is operated under allowable temperature. (Thermal curves shown in Figure 12 are based on different input voltage).




**Figure 11:** Baseplate's temperature measured point



**Figure 12:** Thermal derating curves

## Mechanical Drawing

Mechanical Dimensions



Pin Connection

| Pin | Function |
|-----|----------|
| 1   | ACL      |
| 2   | ACN      |
| 3   | BUS+     |
| 4   | BUS-     |
| 5   | PG       |
| 6   | SENSE-   |
| 7   | VOUT-    |
| 8   | VOUT+    |
| 9   | SENSE+   |
| 10  | TRIM     |

All dimensions in mm (inches)  
Tolerance: X.X±0.5 (X.XX±0.02)  
X.XX±0.25 (X.XXX±0.010)

## Physical Outline

|               |                                        |
|---------------|----------------------------------------|
| Case Size     | : 110.8x50.8x13.7mm (4.36"x2.0"x0.54") |
| Case Material | : AL6061+Plastic case                  |
| Weight        | : 240±10g                              |

## Part Numbering System

| P           | AC                  | S                 | R              | 24             | 021            | A                                          |
|-------------|---------------------|-------------------|----------------|----------------|----------------|--------------------------------------------|
| Form Factor | Rated Input Voltage | Number of Outputs | Product Series | Output Voltage | Output Current | Option Code                                |
| P - Module  | AC - 100VAC~240VAC  | S - Single        | R - Regular    | 24V            | 0 - 21A        | A - Through Hole<br>S - Screw hole(M3*0.5) |

## Recommended Part Number

| Model Name  | Rated Input   |      | Output |     | EFF @220VAC 100% LOAD |
|-------------|---------------|------|--------|-----|-----------------------|
| PACSR24021A | 100VAC~240VAC | 5.8A | 24V    | 21A | 93.5%                 |
| PACSR24021S | 100VAC~240VAC | 5.8A | 24V    | 21A | 93.5%                 |

## WARRANTY

Delta offers a three (3) years limited warranty. Complete warranty information is listed on our web site or is available upon request from Delta.

Information furnished by Delta is believed to be accurate and reliable. However, no responsibility is assumed by Delta for its use, nor for any infringements of patents or other rights of third parties, which may result from its use. No license is granted by implication or otherwise under any patent or patent rights of Delta. Delta reserves the right to revise these specifications at any time, without notice.