





SECTION H-H

mat'l. code NOTE 1 & 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADER				
ltr	ecn no	dr	date	tolerances unless otherwise specified					INCH/MM scale 2.5:1	title				
B	V00853	MRC	9/18/90	angles linear	.XX±.01/XX±0.3					STRAIGHT HEADER FOR ROUND WIRE RECEPTACLE				
C	V70775	SAR	6/2/97		.XXX±.005/XXX±0.13									
D	V71034	EPK	9/24/97		.XXX±.0020/.XXX±0.051									
					0°±2'									
E	V01576	MDF	7/5/00	dr	M. CORNMAN	9/18/90		FCI 	dwg no		sheet 1 of 6 size			
F	M05-0167	ERE	7/23/05	enrg	M. LEACH	9/18/90			68664		A3			
G	M07-0116	AGS	2/24/07	chr	M. LEACH	9/18/90			type Product Customer Drawing					
H	N07-0150	MHT	8/01/07	appd	M. LEACH	9/18/90								
sheet index	revision sheet	H	H	H	H	H	H							
		1	2	3	4	5	6							



1. TERMINAL MATERIAL: 3/4 HARD PHOS. BRONZE ALLOY, UNS-C51000.
2. TERMINAL PLATING: 30u"/0.76u Au OR GXT OVER 50u"/1.27u Ni PLATING ON SWAGED TIPS MANUFACTURERS OPTION.
3. MOLDING MATERIAL: GLASS FILLED POLYESTER, FLAME RETARDANT PER UL-94V-0.
COLOR: BLACK.
4. .020/.51 MAX FLASH AROUND ALL WINDOWS.
5. COMPANY LOGO MOLDED IN ON DATUM SURFACE -Z- APPROX. AS SHOWN.
6. .030/.76 MAX FLASH PERMISSIBLE ON THIS END OF PINS.
7. OTHER PLATINGS ARE AVAILABLE ON 68663, 68665, AND 68666.
8. .015/.38 MAX FLASH PERMISSIBLE ON THIS END OF PINS.
9. PLATING OPTIONS:
MAY BE EITHER GOLD OR GXT PLATED AT MANUFACTURER'S OPTION.
10. ADD "LF" SUFFIX AT THE END OF PART NUMBER
FOR LEAD FREE OPTION
11. THIS PRODUCT MEETS EUROPEAN UNION DIRECTIVES AND OTHER
COUNTRY REGULATION AS DESCRIBED IN GS-22-008.
12. THE HOUSING WILL WITHSTAND EXPOSURE TO 260°C PEAK TEMPERATURE
FOR 15 SECONDS IN A WAVE SOLDER APPLICATION WITH A 1.5mm
MINIMUM THICK CIRCUIT BOARD. SEE APPLICATION NOTES/PROCEDURES
IF THEY ARE AVAILABLE.

mat'l. code NOTE 1 & 3				surface ISO 1302 ✓		tolerance ISO 406 ISO 1101		projection 		product family HEADER			
ltr ecn no dr date				tolerances unless otherwise specified				INCH/MM scale 2.5:1		title STRAIGHT HEADER FOR ROUND WIRE RECEPTACLE			
H				angles linear		$XX \pm .01 / X \pm 0.3$ $XXX \pm .005 / XXX \pm 0.13$ $XXXX \pm .0020 / XXXX \pm 0.051$							
				0'±2"						dwg no sheet 2 of 6 size 68664 A3			
				dr M. CORNMAN		9/18/90							
				enrg M. LEACH		9/18/90							
				chr M. LEACH		9/18/90							
				appd M. LEACH		9/18/90				type Product Customer Drawing			
sheet index		revision sheet											



FCIconnect.com

Copyright FCI

PRODUCT NO NOTE 10	NO OF POS	NO OF PINS	A SPACES	DIM B	DIM C $\pm .005$ ± 0.13	DIM D $\pm .005$ ± 0.13	DIM E $\pm .005$ ± 0.13	DIM F	POL. POS.	
									ROW A	ROW B
68664-035	6	6	2	.200/5.08	.332/8.43	.066/1.68	-----	.155/3.94		
↑ -036	8	8	3	.300/7.62	.432/10.97	.066/1.68	-----	↑		
↑ -037	10	10	4	.400/10.16	.532/13.52	.166/4.22	-----			
↑ -038	12	12	5	.500/12.70	.632/16.05	.166/4.22	-----			
↑ -039	14	14	6	.600/15.24	.732/18.59	.266/6.76	-----			
↑ -040	16	16	7	.700/17.78	.832/21.13	.266/6.76	-----			
↑ -041	18	18	8	.800/20.32	.932/23.67	.366/9.30	-----			
↑ -042	20	20	9	.900/22.86	1.032/26.21	.066/1.68	.766/19.46			
↑ -043	22	22	10	1.000/25.40	1.132/28.75		.866/22.00			
↑ -044	24	24	11	1.100/27.94	1.232/31.29		.966/24.54			
↑ -045	26	26	12	1.200/30.48	1.332/33.83		1.066/27.08			
↑ -046	28	28	13	1.300/33.02	1.432/36.37		1.166/29.62			
↑ -047	30	30	14	1.400/35.56	1.532/38.91		1.266/32.16			
↑ -048	32	32	15	1.500/38.10	1.632/41.45		1.366/34.70			
↑ -049	34	34	16	1.600/40.64	1.732/43.99		1.466/37.24			
↑ -050	36	36	17	1.700/43.18	1.832/46.53		1.566/39.78			
↑ -051	38	38	18	1.800/45.72	1.932/49.07		1.666/42.32			
↑ -052	40	40	19	1.900/48.26	2.032/51.61		1.766/44.86			
↑ -053	42	42	20	2.000/50.80	2.132/54.15		1.866/47.40			
↑ -054	44	44	21	2.100/53.34	2.232/56.69		1.966/49.94			
↑ -055	46	46	22	2.200/55.88	2.332/59.23		2.066/52.48			
↑ -056	48	48	23	2.300/58.42	2.432/61.77		2.166/55.02			
↑ -057	50	50	24	2.400/60.96	2.532/64.31		2.266/57.56			
↑ -058	52	52	25	2.500/63.50	2.632/66.85		2.366/60.10			
↑ -059	54	54	26	2.600/66.04	2.732/69.39		2.466/62.64			
↑ -060	56	56	27	2.700/68.58	2.832/71.93		2.566/65.18			
↑ -061	58	58	28	2.800/71.12	2.932/74.47		2.666/67.72			
↑ -062	60	60	29	2.900/73.66	3.032/77.01		2.766/70.26			
↑ -063	62	62	30	3.000/76.20	3.132/79.55		2.866/72.80			
↑ -064	64	64	31	3.100/78.74	3.232/82.09		2.966/75.34			
↑ -065	66	66	32	3.200/81.28	3.332/84.63		3.066/77.88			
↑ -066	68	68	33	3.300/83.82	3.432/87.17		3.166/80.42			
↑ -067	70	70	34	3.400/86.36	3.532/89.71		3.266/82.96			
68664-068	72	72	35	3.500/88.90	3.632/92.25	.066/1.68	3.366/85.50	.155/3.94		

mat'l. code NOTE 1 & 3		surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 		product family HEADER	
ltr	ec	no	dr	date	tolerances unless otherwise specified				title
H					angles	linear	INCH/MM		STRAIGHT HEADER FOR
					0°±2'		scale 2.5:1		ROUND WIRE RECEPTACLE
					dr	M. CORNMANN	9/18/90		dwg no
					enr	M. LEACH	9/18/90		sheet 4 of 6 size
					chr	M. LEACH	9/18/90		68664 A3
					appd	M. LEACH	9/18/90		type Product Customer Drawing
sheet index	revision	sheet							

form: A3



FCIconnect.com

Copyright FCI

PRODUCT NO NOTE 10	NO OF POS	NO OF PINS	A SPACES	DIM B	DIM C ± 0.005 ± 0.13	DIM D ± 0.005 ± 0.13	DIM E ± 0.005 ± 0.13	DIM F	POL. POS.	
									ROW A	ROW B
68664-069	6	6	2	.200/5.08	.332/8.43	.066/1.68	-----	.200/5.08		
↑ -070	8	8	3	.300/7.62	.432/10.97	.066/1.68	-----	↑		
-071	10	10	4	.400/10.16	.532/13.52	.166/4.22	-----			
-072	12	12	5	.500/12.70	.632/16.05	.166/4.22	-----			
-073	14	14	6	.600/15.24	.732/18.59	.266/6.76	-----			
-074	16	16	7	.700/17.78	.832/21.13	.266/6.76	-----			
-075	18	18	8	.800/20.32	.932/23.67	.366/9.30	-----			
-076	20	20	9	.900/22.86	1.032/26.21	.066/1.68	.766/19.46			
-077	22	22	10	1.000/25.40	1.132/28.75	↑	.866/22.00			
-078	24	24	11	1.100/27.94	1.232/31.29		.966/24.54			
-079	26	26	12	1.200/30.48	1.332/33.83		1.066/27.08			
-080	28	28	13	1.300/33.02	1.432/36.37		1.166/29.62			
-081	30	30	14	1.400/35.56	1.532/38.91		1.266/32.16			
-082	32	32	15	1.500/38.10	1.632/41.45		1.366/34.70			
-083	34	34	16	1.600/40.64	1.732/43.99		1.466/37.24			
-084	36	36	17	1.700/43.18	1.832/46.53		1.566/39.78			
-085	38	38	18	1.800/45.72	1.932/49.07		1.666/42.32			
-086	40	40	19	1.900/48.26	2.032/51.61		1.766/44.86			
-087	42	42	20	2.000/50.80	2.132/54.15		1.866/47.40			
-088	44	44	21	2.100/53.34	2.232/56.69		1.966/49.94			
-089	46	46	22	2.200/55.88	2.332/59.23		2.066/52.48			
-090	48	48	23	2.300/58.42	2.432/61.77		2.166/55.02			
-091	50	50	24	2.400/60.96	2.532/64.31		2.266/57.56			
-092	52	52	25	2.500/63.50	2.632/66.85		2.366/60.10			
-093	54	54	26	2.600/66.04	2.732/69.39		2.466/62.64			
-094	56	56	27	2.700/68.58	2.832/71.93		2.566/65.18			
-095	58	58	28	2.800/71.12	2.932/74.47		2.666/67.72			
-096	60	60	29	2.900/73.66	3.032/77.01		2.766/70.26			
-097	62	62	30	3.000/76.20	3.132/79.55		2.866/72.80			
-098	64	64	31	3.100/78.74	3.232/82.09		2.966/75.34			
-099	66	66	32	3.200/81.28	3.332/84.63		3.066/77.88			
-100	68	68	33	3.300/83.82	3.432/87.17		3.166/80.42			
↓ -101	70	70	34	3.400/86.36	3.532/89.71	↓	3.266/82.96	↓		
68664-102	72	72	35	3.500/88.90	3.632/92.25	.066/1.68	3.366/85.50	.200/5.08		

mat'l. code NOTE 1 & 3		surface ISO 1302 ☒		tolerance ISO 406 ISO 1101		projection 		product family HEADER	
ltr	ec	no	dr	date	tolerances unless otherwise specified			title	
H					angles	linear		STRAIGHT HEADER FOR ROUND WIRE RECEPTACLE	
					0°±2'	.XX±.01/XX±0.3 .XXX±.005/XX±0.13 .XXXX±.0020/XXX±0.051	scale 2.5:1	dwg no	
					dr	M. CORNMAN	9/18/90	sheet 5 of 6 size	
					enr	M. LEACH	9/18/90	68664 A3	
					chr	M. LEACH	9/18/90	type Product Customer Drawing	
					appd	M. LEACH	9/18/90		
sheet index	revision sheet								

form: A3

PRODUCT NO NOTE 10	NO. OF POS	NO. OF PINS	A SPACES	DIM B	DIM C ± 0.005 ± 0.13	DIM D ± 0.005 ± 0.13	DIM E ± 0.005 ± 0.13	DIM F	POL. POS.	
									ROW A	ROW B
68664-103	6	6	2	.200/5.08	.332/8.43	.066/1.68	-----	.380/9.65	-----	-----
↑ -104	8	8	3	.300/7.62	.432/10.97	.066/1.68	-----	.380/9.65	↑	↑
-105	12	12	5	.500/12.70	.632/16.05	.166/4.22	-----	.380/9.65	↑	↑
-106	16	16	7	.700/17.78	.832/21.13	.266/6.76	-----	.380/9.65	↑	↑
↓ -107	20	20	9	.900/22.86	1.032/26.21	.066/1.68	.766/19.46	.380/9.65	-----	-----
68664-108	14	13	6	.600/15.24	.732/18.59	.266/6.76	-----	.130/3.30	1	-----
68664-132	32	32	15	1.500/38.10	1.632/41.45	.066/1.68	1.366/34.70	.325/8.26	-----	-----



FCIconnect.com

Copyright FCI

mat'l. code NOTE 1 & 3				surface ISO 1302 ✓	tolerance ISO 406 ISO 1101	projection 	product family HEADER
ltr	ecn	no	dr	date	tolerances unless otherwise specified	INCH/MM scale 2.5:1 	title
H					angles linear .XX±.01/XX±0.3		STRAIGHT HEADER FOR
					0°±2' .XXX±.005/XX±0.13 .XXX±.0020/XXX±0.051		ROUND WIRE RECEPTACLE
			dr	M. CORNMAN	9/18/90		dwg no
			enr	M. LEACH	9/18/90		sheet 6 of 6 size
			chr	M. LEACH	9/18/90		68664 A3
			appd	M. LEACH	9/18/90		type Product Customer Drawing
sheet index	revision sheet						

form: A3