



Transportation

Socket Housing:	IL-AG5-#S- S3C1	Contacts:	IL-AG5-C1-5000 (socket)
Pin housing:	IL-AG5-#P- S3C1	S:	single row
		D:	double row
	IL-AG5-#P- S3L2	L:	right angle
		T:	straight
		Hand tool:	CT150-1-AG5
		Semi auto:	3502-AG5-2
		Automatic:	350-AG5-3B

Socket housing:	MX1900#S51	Contacts:	MX19S10K451 (socket)
Pin housing:	MX1900#P51	Dummy pin:	MX1900XD1
		1:	Black
		2:	Gray
		Hand Tool:	CT150-4C-MX19
		Semi auto:	3502-MX19-2B

Socket housing:	MX23A##SF1	Contacts:	M23S05K351
Pin header:	MX23A##NF1	Dummy pin:	M120-55780
Front cap:	MX23A##XF1	1:	Standard
		2:	Reverse
		Hand tool:	CT160-3B-MX23
		Semi auto:	350-MX23-2

Socket housing:	MX340##SF1	Pin header:	MX340##UF1
		U:	Straight
		N:	Angled
		1:	3-24 pos
		2:	28-40 pos
Contacts	Hand Tool	Semi auto	Automatic
M34S75C4F1	CT150-2-MX34	350-MX34D-2	350-MX34B-3B
M34S75C4F2	CT150-1-MX34	350-MX34D-2	350-MX34B-3B
M34S75C4F3	N/A	350-MX34C-2	350-MX34C-3B
M34S75C4F4	N/A	350-MX34C-2	350-MX34C-3B










Board Mounting Receptacle:	MX39004NQ1
USB Harness:	MX45004S0008397 (150mm)

Socket housing:	MX3600#SQ3	Contacts:	M36S08K4Q3 (socket)
Pin housing:	MX3600#PQ3		M36P08K4Q3 (pin)
Front cap:	MX36004XF3	Semi auto:	350-MX36-2
		Automatic:	350-MX36-3B

Socket housing:	MX37004SP3	Contacts:	Socket M37S07K4P3
Pin housing:	MX37004PP3	Pin M37P75C4P3	
		Semi Auto:	350-MX37S-2
		Automatic:	350-MX37S-3B
			350-MX37P-2
			350-MX37S-3B

Socket housing:	MX44####SF1	Contacts:	M44S05K4F1
Pin header:	MX44####NF1	Hand Tool:	CT150-2-MX44
Retainer:	MX44####XR1	Semi Auto:	3502-MX44-2
Wire seal:	MX44000XP1	Wire O.D.	
		1:	1.4-1.5mm
		2:	1.6-1.7mm

Socket housing:	MX31 ### SG A	31, 34, 35 pos	Modification code
Pin header:	MX31 ### N F D	70, 104, 135 pos	Modification code
		F:	All Sn plated contacts
		Q:	Selective gold plated contacts
Contacts	Wire (AWG)	Semi Auto	Automatic
M31S07K4FA (Sn, signal)	#22-20	350-MX31A-2	350-MX31A-3B
M31S07K4QA (Au, signal)	#22-20	350-MX31A-2	350-MX31A-3B
M31S07K4FB (Sn, signal)	#24	350-MX31A-2	350-MX1A-3B
M31S05K3FA (Sn, power)	#18-16	350-MX31B-2	350-MX31B-3B
M31S05K4FA (Sn, power)	#22-18	350-MX31B-2	350-MX31B-3B
M31S05K4QA (Au, power)	#22-18	350-MX31B-2	350-MX31B-3B

Series	IL-AG5	MX19	MX23A	MX31	MX34	MX36	MX37	MX39/MX45	MX44
Photo									
Pitch	2.5mm	2.5mm	2.5mm	Signal: 2.2mm Power: 3.2mm	2.2mm	2.5mm	2.2mm	2.2mm	3.5mm
Wire Size	AWG #22-18 AV,AVS,AVSS: 0.3 to 0.5mm ² AVS, AVSS: 0.85mm ²	AWG #22-20 CAVS: 0.3 to 0.5mm ² AVSS: 0.5mm ²	AWG #22-16 AVSS, AVS: 0.5 to 1.25mm ²	Signal: AWG #22-20 Power: AWG #22-16 Signal: AVS, AVSS, AVX 0.3 to 0.5mm ² Power: AVS, AVSS AVX 0.3 to 1.25mm ²	AWG #22-20 AVSS: 0.3, 0.5mm ² CHFUS: 0.22 to 0.35mm ² , 0.5 to 0.75mm ² CAN SD: 0.35mm ²	AWG #20 AVSS 0.5, AVSS 0.5F, AVSSX 0.5f, TVSSX 0.5f	AWG #20 AVSS 0.5, AVSS 0.5F, AVSSX 0.5f, TVSSX 0.5f	AWG #28 Twin Ax	AWG #22-20 AVSS 0.3 to 0.5mm ²
Pin Count	1 row: 4,5,6, 7,10 2 rows: 14,16, 18,22,30	2, 4	12, 18, 26, 34, 36,40	Pin: 70,98,104,135 Socket: 31,34,35	3,5,7,12,16,20, 24,28,32,36,40	2, 4	4	4	2, 4, 6
Current Rating	3A	5A	3A	Signal: 2.2A Power: 5.7A	3A	3A	3A	500mA	3A
Operating Temperature	-40 ~ +85 °C	-40 ~ +85 °C	-40 ~ +125 °C	-40 ~ +85 °C	-40 ~ +85 °C	-40 ~ +105 °C	-40 ~ +105 °C	-40 ~ +85 °C	-40 ~ +125 °C
Application	Cable to Cable/ Board to Cable	Cable to Cable	Board to Cable	Board to Cable	Board to Cable	Cable to Cable	Cable to Cable	Cable to Cable/ Board to Cable	Board to Cable
Features	Mechanical lock system enabling complete mating. Secondary lock mechanism to ensure correct terminal retention. Simplified crimp type termination.	Waterproof. Mechanical lock system. Grommet seal. Terminals have low insertion force and stress dispersion. Rear cover protects the grommet from damage.	Waterproof. Low profile. Available in reverse mount type. Retainer detects incomplete insertion of socket contact.	Mechanical lock system with audible click. Socket side contact designed with secondary lock. Simplified crimp type termination.	Lightweight. Mating and unmating force less than 80N. Closed box socket contact increases mechanical strength. Preset retainer allows easy wire harness assembly.	Waterproof. Spring separates connectors if not correctly mated. Shorting contact eliminates static discharge. Retainer detects incomplete insertion of socket contact.	Mechanical complete mating method. Spring separates connector if not correctly mated. Shorting contact eliminates static discharge. Retainer detects incomplete insertion.	USB 2.0 compatible. Sold as a complete harness with USB standard receptacle.	Single contact waterproof. Compact size. Improved vibration resistance by vibration absorption function of rubber. Secondary lock mechanism.