

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20

BY TYCO ELECTRONICS CORPORATION, ALL RIGHTS RESERVED.

LOC

DIST

REVISIONS

P

LTR

DESCRIPTION

DATE

DWN

APVD



D

REVISED PER 0G3B-0119-01



23OCT2001

EZ

DB



282867-3 AS SHOWN



MATERIALS AND FINISH
HOUSING: PA 6-6, UL 94-V0, COLOR GREEN.
CLAMP: BRASS, NICKEL PLATED.
TERMINAL: BRASS, TIN PLATED.
CLAMPING SCREW: M3, BRASS, NICKEL PLATED.

2 SUITABLE FOR 1.6-2.4mm PC BOARD THICKNESS.

3 END-TO-END STACKABLE W/INTERLOCK WITHOUT LOSS OF CENTERLINE SPACING.

4 WIRE SIZE RANGE
12 - 30 AWG


5 RECOGNIZED UNDER THE COMPONENT PROGRAM OF
UNDERWRITERS LABORATORIES INC., FILE N° E60677.

6 WITH IEC 998-1/998-2-1.



NOT CUMULATIVE TOLERANCE.

RECOMMENDED PC BOARD LAYOUT



22.86	3	282867-3
15.24	2	282867-2
DIM. A	N° OF POS.	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT FOR TYCO ELECTRONICS CORPORATION IT IS SUBJECT TO CHANGE AND THE CONTROLLING ENGINEERING ORGANIZATION SHOULD BE CONTACTED FOR THE LATEST REVISION.		DWN 23OCT2001 E. ZANOLINI	BUCHANAN Tyco Electronics Harrisburg, PA 17105-3608	
DIMENSIONS: mm		CHK 23OCT2001 D. BIEVENOUR		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD 23OCT2001 D. BIEVENOUR	NAME TERMINAL BLOCK, PCB MOUNT TOP ENTRY WIRE, STACKING W / INTERLOCK, 7.62mm PITCH	
0 PLC $\pm .3$ 1 PLC $\pm .3$ 2 PLC $\pm .25$ 3 PLC $\pm .3$ 4 PLC $\pm .3$ ANGLES ± 2		PRODUCT SPEC 108-20166	SIZE A3	
MATERIAL $\Delta 1$		APPLICATION SPEC 114-20079	CAGE CODE 00779	
FINISH $\Delta 1$		WEIGHT -	DRAWING NO C-282867	
CUSTOMER DRAWING		SCALE 3:1		SHEET 1 OF 1
				REV D