


SKiiP 37NAB12T4V1



MiniSKiiP® 3

SKiiP 37NAB12T4V1

Features

- Trench 4 IGBTs
- Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised: File no. E63532

Typical Applications*


- Inverter up to 36 kVA
- Typical motor power 22 kW

Remarks

- Max. case temperature limited to $T_C=125^\circ\text{C}$
- Product reliability results valid for $T_j \leq 150^\circ\text{C}$ (recommended $T_{j,op} = -40 \dots +150^\circ\text{C}$)
- MiniSKiiP "Technical Explanations" and "Mounting Instructions" are part of the data sheet. Please refer to both documents for further information.


Absolute Maximum Ratings

Symbol	Conditions	Values	Unit
Inverter - IGBT			
V_{CES}	$T_j = 25^\circ\text{C}$	1200	V
I_C	$\lambda_{paste}=0.8 \text{ W/(mK)}$ $T_j = 175^\circ\text{C}$	$T_s = 25^\circ\text{C}$ 90	A
		$T_s = 70^\circ\text{C}$ 73	A
I_C	$\lambda_{paste}=2.5 \text{ W/(mK)}$ $T_j = 175^\circ\text{C}$	$T_s = 25^\circ\text{C}$ 106	A
		$T_s = 70^\circ\text{C}$ 86	A
I_{Cnom}		75	A
I_{CRM}	$I_{CRM} = 3 \times I_{Cnom}$	225	A
V_{GES}		-20 ... 20	V
t_{psc}	$V_{CC} = 800 \text{ V}$ $V_{GE} \leq 15 \text{ V}$ $V_{CES} \leq 1200 \text{ V}$ $T_j = 150^\circ\text{C}$	10	μs
T_j		-40 ... 175	$^\circ\text{C}$
Chopper - IGBT			
V_{CES}	$T_j = 25^\circ\text{C}$	1200	V
I_C	$\lambda_{paste}=0.8 \text{ W/(mK)}$ $T_j = 175^\circ\text{C}$	$T_s = 25^\circ\text{C}$ 90	A
		$T_s = 70^\circ\text{C}$ 73	A
I_C	$\lambda_{paste}=2.5 \text{ W/(mK)}$ $T_j = 175^\circ\text{C}$	$T_s = 25^\circ\text{C}$ 106	A
		$T_s = 70^\circ\text{C}$ 86	A
I_{Cnom}		75	A
I_{CRM}	$I_{CRM} = 3 \times I_{Cnom}$	225	A
V_{GES}		-20 ... 20	V
t_{psc}	$V_{CC} = 800 \text{ V}$ $V_{GE} \leq 15 \text{ V}$ $V_{CES} \leq 1200 \text{ V}$ $T_j = 150^\circ\text{C}$	10	μs
T_j		-40 ... 175	$^\circ\text{C}$
Inverse - Diode			
V_{RRM}	$T_j = 25^\circ\text{C}$	1200	V
I_F	$\lambda_{paste}=0.8 \text{ W/(mK)}$ $T_j = 175^\circ\text{C}$	$T_s = 25^\circ\text{C}$ 83	A
		$T_s = 70^\circ\text{C}$ 66	A
I_F	$\lambda_{paste}=2.5 \text{ W/(mK)}$ $T_j = 175^\circ\text{C}$	$T_s = 25^\circ\text{C}$ 95	A
		$T_s = 70^\circ\text{C}$ 76	A
I_{Fnom}		75	A
I_{FRM}	$I_{FRM} = 3 \times I_{Fnom}$	225	A
I_{FSM}	$t_p = 10 \text{ ms, sin } 180^\circ, T_j = 150^\circ\text{C}$	430	A
T_j		-40 ... 175	$^\circ\text{C}$
Freewheeling - Diode			
V_{RRM}	$T_j = 25^\circ\text{C}$	1200	V
I_F	$\lambda_{paste}=0.8 \text{ W/(mK)}$ $T_j = 175^\circ\text{C}$	$T_s = 25^\circ\text{C}$ 83	A
		$T_s = 70^\circ\text{C}$ 66	A
I_F	$\lambda_{paste}=2.5 \text{ W/(mK)}$ $T_j = 175^\circ\text{C}$	$T_s = 25^\circ\text{C}$ 95	A
		$T_s = 70^\circ\text{C}$ 76	A
I_{Fnom}		75	A
I_{FRM}	$I_{FRM} = 3 \times I_{Fnom}$	225	A
I_{FSM}	$t_p = 10 \text{ ms, sin } 180^\circ, T_j = 150^\circ\text{C}$	430	A
T_j		-40 ... 175	$^\circ\text{C}$



NAB

SKiiP 37NAB12T4V1



MiniSKiiP® 3

SKiiP 37NAB12T4V1

Features

- Trench 4 IGBTs
- Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised: File no. E63532

Typical Applications*

- Inverter up to 36 kVA
- Typical motor power 22 kW

Remarks


- Max. case temperature limited to $T_C=125^\circ\text{C}$
- Product reliability results valid for $T_J \leq 150^\circ\text{C}$ (recommended $T_{J,op} = -40 \dots +150^\circ\text{C}$)
- MiniSKiiP "Technical Explanations" and "Mounting Instructions" are part of the data sheet. Please refer to both documents for further information.

Absolute Maximum Ratings

Symbol	Conditions	Values	Unit
Rectifier - Diode			
V_{RRM}	$T_J = 25^\circ\text{C}$	1600	V
I_F	$\lambda_{paste}=0.8 \text{ W/(mK)}$ $T_J = 150^\circ\text{C}$	81	A
	$T_s = 25^\circ\text{C}$ $T_s = 70^\circ\text{C}$	60	A
I_F	$\lambda_{paste}=2.5 \text{ W/(mK)}$ $T_J = 150^\circ\text{C}$	92	A
	$T_s = 25^\circ\text{C}$ $T_s = 70^\circ\text{C}$	68	A
I_{Fnom}		25	A
I_{FSM}	10 ms $\sin 180^\circ$	700	A
	$T_J = 25^\circ\text{C}$ $T_J = 150^\circ\text{C}$	490	A
I^2t	10 ms $\sin 180^\circ$	2400	A^2s
	$T_J = 25^\circ\text{C}$ $T_J = 150^\circ\text{C}$	1200	A^2s
T_J		-40 ... 150	$^\circ\text{C}$
Module			
$I_{t(RMS)}$	$T_{terminal} = 80^\circ\text{C}$, 20 A per spring	80	A
T_{stg}		-40 ... 125	$^\circ\text{C}$
V_{isol}	AC sinus 50 Hz, 1 min	2500	V


Characteristics

Symbol	Conditions	min.	typ.	max.	Unit
Inverter - IGBT					
$V_{CE(sat)}$	$I_C = 75 \text{ A}$ $V_{GE} = 15 \text{ V}$ chipelevel	$T_J = 25^\circ\text{C}$	1.85	2.10	V
		$T_J = 150^\circ\text{C}$	2.25	2.45	V
V_{CE0}	chipelevel	$T_J = 25^\circ\text{C}$	0.80	0.90	V
		$T_J = 150^\circ\text{C}$	0.70	0.80	V
r_{CE}	$V_{GE} = 15 \text{ V}$ chipelevel	$T_J = 25^\circ\text{C}$	14	16	$\text{m}\Omega$
		$T_J = 150^\circ\text{C}$	21	22	$\text{m}\Omega$
$V_{GE(th)}$	$V_{GE} = V_{CE} \text{ V}$, $I_C = 3 \text{ mA}$	5	5.8	6.5	V
I_{CES}	$V_{GE} = 0 \text{ V}$, $V_{CE} = 1200 \text{ V}$, $T_J = 25^\circ\text{C}$		0.1	0.3	mA
C_{ies}	$V_{CE} = 25 \text{ V}$ $V_{GE} = 0 \text{ V}$	$f = 1 \text{ MHz}$	4.40		nF
C_{oes}		$f = 1 \text{ MHz}$	0.29		nF
C_{res}		$f = 1 \text{ MHz}$	0.24		nF
Q_G	- 8 V...+ 15 V		425		nC
R_{Gint}	$T_J = 25^\circ\text{C}$		10		Ω
$t_{d(on)}$	$V_{CC} = 600 \text{ V}$ $I_C = 75 \text{ A}$	$T_J = 150^\circ\text{C}$	150		ns
t_r	$R_{G on} = 2 \Omega$	$T_J = 150^\circ\text{C}$	35		ns
E_{on}	$R_{G off} = 2 \Omega$	$T_J = 150^\circ\text{C}$	9.7		mJ
$t_{d(off)}$	$V_{GE} = +15/-15 \text{ V}$	$T_J = 150^\circ\text{C}$	355		ns
t_f		$T_J = 150^\circ\text{C}$	60		ns
E_{off}	$V_{GE} = +15/-15 \text{ V}$	$T_J = 150^\circ\text{C}$	6.8		mJ
$R_{th(j-s)}$	per IGBT, $\lambda_{paste}=0.8 \text{ W/(mK)}$		0.58		K/W
$R_{th(j-s)}$	per IGBT, $\lambda_{paste}=2.5 \text{ W/(mK)}$		0.44		K/W



NAB

SKiiP 37NAB12T4V1



MiniSKiiP® 3

SKiiP 37NAB12T4V1

Features

- Trench 4 IGBTs
- Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised: File no. E63532


Typical Applications*

- Inverter up to 36 kVA
- Typical motor power 22 kW

Remarks


- Max. case temperature limited to $T_C=125^\circ\text{C}$
- Product reliability results valid for $T_J \leq 150^\circ\text{C}$ (recommended $T_{J,op} = -40 \dots +150^\circ\text{C}$)
- MiniSKiiP "Technical Explanations" and "Mounting Instructions" are part of the data sheet. Please refer to both documents for further information.

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
Chopper - IGBT						
V _{CE(sat)}	I _C = 75 A	T _J = 25 °C		1.85	2.10	V
	V _{GE} = 15 V chiplevel	T _J = 150 °C		2.25	2.45	V
V _{CE0}	chiplevel	T _J = 25 °C		0.80	0.90	V
		T _J = 150 °C		0.70	0.80	V
r _{CE}	V _{GE} = 15 V	T _J = 25 °C		14	16	mΩ
	chiplevel	T _J = 150 °C		21	22	mΩ
V _{GE(th)}	V _{GE} = V _{CE} V, I _C = 3 mA		5	5.8	6.5	V
I _{CES}	V _{GE} = 0 V, V _{CE} = 1200 V, T _J = 25 °C			0.1	0.3	mA
Q _G	- 8 V...+ 15 V			425		nC
R _{Gint}	T _J = 25 °C			10.0		Ω
t _{d(on)}	V _{CC} = 600 V	T _J = 150 °C		150		ns
t _r	I _C = 75 A	T _J = 150 °C		35		ns
E _{on}	R _{G on} = 2 Ω	T _J = 150 °C		9.7		mJ
t _{d(off)}	R _{G off} = 2 Ω	T _J = 150 °C		355		ns
t _f		T _J = 150 °C		60		ns
E _{off}	V _{GE} = +15/-15 V	T _J = 150 °C		6.8		mJ
R _{th(j-s)}	per IGBT, λ _{paste} =0.8 W/(mK)			0.58		K/W
R _{th(j-s)}	per IGBT, λ _{paste} =2.5 W/(mK)			0.44		K/W
Inverse - Diode						
V _F = V _{EC}	I _F = 75 A	T _J = 25 °C		2.17	2.49	V
	V _{GE} = 0 V chiplevel	T _J = 150 °C		2.11	2.42	V
V _{F0}	chiplevel	T _J = 25 °C		1.30	1.50	V
		T _J = 150 °C		0.90	1.10	V
r _F	chiplevel	T _J = 25 °C		12	13	mΩ
		T _J = 150 °C		16	18	mΩ
I _{RRM}	I _F = 75 A	T _J = 150 °C		62		A
Q _{rr}	di/dt _{off} = 1940 A/μs	T _J = 150 °C		12.6		μC
E _{rr}	V _{GE} = -15 V V _{CC} = 600 V	T _J = 150 °C		4.9		mJ
R _{th(j-s)}	per Diode, λ _{paste} =0.8 W/(mK)			0.75		K/W
R _{th(j-s)}	per Diode, λ _{paste} =2.5 W/(mK)			0.61		K/W
Freewheeling - Diode						
V _F = V _{EC}	I _F = 75 A	T _J = 25 °C		2.17	2.49	V
	V _{GE} = 0 V chiplevel	T _J = 150 °C		2.11	2.42	V
V _{F0}	chiplevel	T _J = 25 °C		1.30	1.50	V
		T _J = 150 °C		0.90	1.10	V
r _F	chiplevel	T _J = 25 °C		12	13	mΩ
		T _J = 150 °C		16	18	mΩ
I _{RRM}	I _F = 75 A	T _J = 150 °C		62		A
Q _{rr}	di/dt _{off} = 1940 A/μs	T _J = 150 °C		12.6		μC
E _{rr}	V _{GE} = -15 V V _{CC} = 600 V	T _J = 150 °C		4.9		mJ
R _{th(j-s)}	per Diode, λ _{paste} =0.8 W/(mK)			0.75		K/W
R _{th(j-s)}	per Diode, λ _{paste} =2.5 W/(mK)			0.61		K/W



NAB

SKiiP 37NAB12T4V1



MiniSKiiP® 3

SKiiP 37NAB12T4V1

Features

- Trench 4 IGBTs
- Robust and soft freewheeling diodes in CAL technology
- Highly reliable spring contacts for electrical connections
- UL recognised: File no. E63532


Typical Applications*

- Inverter up to 36 kVA
- Typical motor power 22 kW







Remarks

- Max. case temperature limited to $T_C=125^\circ\text{C}$
- Product reliability results valid for $T_J \leq 150^\circ\text{C}$ (recommended $T_{J,op} = -40 \dots +150^\circ\text{C}$)
- MiniSKiiP "Technical Explanations" and "Mounting Instructions" are part of the data sheet. Please refer to both documents for further information.

Characteristics						
Symbol	Conditions		min.	typ.	max.	Unit
Rectifier - Diode						
V _F = V _{EC}	I _F = 25 A	T _j = 25 °C		1.00	1.21	V
	V _{GE} = 0 V chiplevel	T _j = 125 °C		0.90	1.10	V
V _{F0}	chiplevel	T _j = 25 °C		0.88	0.98	V
		T _j = 125 °C		0.73	0.83	V
r _F	chiplevel	T _j = 25 °C		4.8	9.2	mΩ
		T _j = 125 °C		6.8	11	mΩ
R _{th(j-s)}	per Diode, λ _{paste} =0.8 W/(mK)			0.9		K/W
R _{th(j-s)}	per Diode, λ _{paste} =2.5 W/(mK)			0.75		K/W
Module						
M _s	to heat sink		2		2.5	Nm
w				82		g
L _{CE}						nH
Temperature Sensor						
R ₁₀₀	T _r = 100 °C, tolerance = 3 %			1670 ± 3%		Ω
R(T)	R(T)=1000Ω[1+A(T-25°C)+B(T-25°C) ²], A = 7.635*10 ⁻³ °C ⁻¹ , B = 1.731*10 ⁻⁵ °C ⁻²					



NAB






Fig. 7: Typ. switching times vs. I_C




Fig. 8: Typ. switching times vs. gate resistor R_G




Fig. 9: Transient thermal impedance of IGBT and Diode




Fig. 10: CAL diode forward characteristic




Fig. 11: Typ. CAL diode peak reverse recovery current





Fig. 12: Typ. input bridge forward characteristic



7

typical applications, which may still vary depending on the specific application. Therefore, products must be tested for the respective application in advance. Application adjustments may be necessary. The user of SEMIKRON products is responsible for the safety of their applications embedding SEMIKRON products and must take adequate safety measures to prevent the applications from causing a physical injury, fire or other problem if any of SEMIKRON products become faulty. The user is responsible to make sure that the application design is compliant with all applicable laws, regulations, norms and standards. Except as otherwise explicitly approved by SEMIKRON in a written document signed by authorized representatives of SEMIKRON, SEMIKRON products may not be used in any applications where a failure of the product or any consequences of the use thereof can reasonably be expected to result in personal injury. No representation or warranty is given and no liability is assumed with respect to the accuracy, completeness and/or use of any information herein, including without limitation, warranties of non-infringement of intellectual property rights of any third party. SEMIKRON does not assume any liability arising out of the applications or use of any product; neither does it convey any license under its patent rights, copyrights, trade secrets or other intellectual property rights, nor the rights of others. SEMIKRON makes no representation or warranty of non-infringement or alleged non-infringement of intellectual property rights of any third party which may arise from applications. Due to technical requirements our products may contain dangerous substances. For information on the types in question please contact the nearest SEMIKRON sales office. This document supersedes and replaces all information previously supplied and may be superseded by updates. SEMIKRON reserves the right to make changes.