

Distributed by:

JAMECO[®]
ELECTRONICS

www.Jameco.com ♦ 1-800-831-4242



The content and copyrights of the attached
material are the property of its owner.

Jameco Part Number 311344


Date	Rev.	Description

Electrical	
Impedance	50Ω
Frequency range	0-4GHz
VSWR	≤ 1.2 typ
Test voltage	1500 volts rms
Working voltage	400 V rms
Voltage rating	500 volts peak
Power handling	≤ 80 W (2GHz)
Other (MIL-C-39012 Cable Connectors)	Contact resistance: center contact ≤ 1.5 mΩ outer contact ≤ 1 mΩ Insertion loss: ≤ 0.1x√f(GHz)dB Insulation resistance: ≥ 5000 mΩ
Material	
Mating cycles	≥ 500
Center contact captivation	Axial: ≥ 27 N
Environmental	
Temperature range	Del: -45°C~+85°C
Thermal shock	US MIL-STD 202, Meth, 107, Cond, B
Vibration	US MIL-STD 202, Meth, 204, Cond, B
Climatic class	IEC 60068 65/165/21
Shock	US MIL-STD 202, Meth, 213, Cond, B
Corrosion resistance	US MIL-STD 202, Meth, 101, Cond, B
Degree of protection (mated pair)	IEC 60529

NOTE: FINISH (PLATING THICKNESS IN MICRO-INCHES)
 1: BRASS PER QQ-B-626
 2: NICKEL PL 70 MIN THICK OVER COPPER STRIKE
 3: GOLD PL 3 MIN OVER NICKEL PL 70 MIN THICK
 OVER COPPER STRIKE



Mounting Hole



6	Ground Tab	Brass	Nickel
5	Nut	Brass	Nickel
4	Lock Washer	SK5	Nickel
3	Insulator	Delrin	White
2	Contact	PH/Bronze®	Gold
1	Body	Brass	Nickel
NO	Description	Material	Finish

DCC. NO.
A4 DRAWING NO.

MATERIAL		GOLDSUN ELECTRONICS CO., LTD.			
		JAMECO NO.	311344		
		GOLDSUN NO.	31-10-RFX-VP-R		
DRAWN: Kiki Chen		Description	CONNECTOR,BNC BH RECEPT		Rev. 1
VERIFY PEOPLE: Wendy Chen, Fanny Du		UNIT: mm	SCALE:	SHEET 1 OF 1	CAS No: ERN No: