

Universal limit switches

→ Series 83 840 0 Standard

- Adjustable metal head
- 4 positions 90°
- Metal case



Main specifications

	Steel plunger	Reinforced lever with plastic roller	Stepped adjustment roller lever
Housing			
Metal			
Action			
Snap action			
General characteristics			
Function	NO+NC	NO+NC	NO+NC
Sequence	0 2,5 6 mm	0 3 6 mm	0 6 11 mm
Snap action	1-2 3-4 1-2 3-4 0,7	1-2 3-4 1-2 3-4 0,7	1-2 3-4 1-2 3-4 1,5
Mechanical characteristics			
Minimum operating force (N)	10	15	8
Minimum operating force (cmN)	-	-	-
Minimum total travel force (N)	22	25	15
Minimum total travel force (cmN)	-	-	-
Mechanical life (operations)	10 ⁷	10 ⁷	10 ⁷
Temperature limits use (°C)	-10 → +70	-10 → +70	-10 → +70
Weight (g)	310	310	310
Comments			
Accessories for 83 843 0 (see Dimensions - Mounting accessories)			
Galvanized, passivated steel lever			
Thermoplastic roller			
Supplied with nut, washer and locating block loose			

General characteristics

Assigned insulation voltage (Ui) V	600
Thermal current (Ith) A	10
Use category	AC 15 : A600 DC 13 : P300

Product adaptations



- Approvals : UL/CSA



Adjustable roller lever	Adjustable lever with idle-return lever	Rotary head with momentary action Action to right and left	Top-mounted plunger with metal roller	Flexible metal lever
83 842 1	83 842 2	83 843 0	83 845 0	83 846 0
NO+NC	NO+NC	NO+NC	NO+NC	NO+NC
8	8	-	10	1.5
-	-	20	-	-
15	15	-	22	2.5
-	-	33	-	-
10 ⁷	10 ⁷	10 ⁷	10 ⁷	10 ⁷
-10 → +70	-10 → +70	-20 → +70	-10 → +70	-10 → +70
310	310	310	300	310

Principles


Function

Four-terminal double break two-way contact element (form Za). The contacts must be of the same polarity.



Curves


Operating curve for standard version



Dimensions

→ Product

Body




① Axis of head rotation


② No. 13 sealing gland

→ Actuators


83 840 0



83 841 0




83 842 0




Min. angle between 2 successive adjustments 0°10'


83 842 1




83 842 2




83 843 0




83 845 0




83 846 0




79 210 997 (for 83 843 0)




79 210 998 (for 83 843 0)



Lever settings or positions dictated by direction in which block 1 is fitted



① Block 1
Adjustable in 6° steps



① Block 1
Adjustable in 90° steps

Universal limit switches

→ Series 83 840 7 Positive break operation

- Adjustable metal head
- 4 positions 90°
- Plastic or metal cases



Main specifications

		Steel plunger	Reinforced lever with plastic roller
Housing	Action	83 840 7	83 841 7
Metal	Snap action		
General characteristics			
Function		NC	NC
Sequence		0 2,5 4F 6 mm	0 3 4,5F 6 mm
Snap action		1-2 1-2	1-2 1-2
		0,7	0,7
Positive break operation			
Mechanical characteristics			
Minimum operating force (N)		10	15
Minimum operating force (cmN)		-	-
Minimum positive opening force (N)		10	15
Min. positive opening travel (cmN)		-	-
Minimum total travel force (N)		22	25
Minimum total travel force (cmN)		-	-
Mechanical life (operations)		10 ⁷	10 ⁷
Temperature limits use (°C)		-10 → +70	-10 → +70
Weight (g)		310	310

General characteristics

Assigned insulation voltage (Ui) V	600
Thermal current (Ith) A	2.5
Use category	AC 15 : C600 DC 13 : R 300
Short circuit test	Conforms to IEC 947.5.1 paragraph 8.34
Current peak	1000 A at 250 VAC 0.5 < cos φ < 0.7
Short circuit protection (SCPD)	Fuse 10 AgF

Product adaptations



- Approvals : UL/CSA



Stepped adjustment roller lever	Adjustable roller lever	Adjustable lever with idle-return lever	Rotary head with momentary action Action to right and left	Top-mounted plunger with metal roller
83 842 7	83 842 8	83 842 9	83 843 7	83 845 7
NC	NC	NC	NC	NC
8	8	8	-	10
-	-	-	20	-
10	10	10	-	10
-	-	-	20	-
15	15	15	-	22
-	-	-	33	-
10 ⁷	10 ⁷	10 ⁷	10 ⁷	10 ⁷
-10 → +70	-10 → +70	-10 → +70	-20 → +70	-10 → +70
310	310	310	310	300

Principles


Function

Two-terminal double break contact element (form Y : normally closed contact) with positive break operation.



Curves


Operating curve for positive break version



Dimensions

→ Product


Body




- ① Axis of head rotation
- ② No. 13 sealing gland

→ Actuators


83 840 7



83 841 7




83 842 7




- ① Min. angle between 2 successive adjustments 0°10


83 842 8




83 842 9




83 843 7





83 845 7



79 210 997 (for 83 843 7)



79 210 998 (for 83 843 7)



- ① Block 1
Block 1 must not be mounted the other way round
Adjustable in 90° steps