


## Features

- POWERMITE 3 Surface Mount Package
- MOSFET with Schottky Rectifier for reverse voltage blocking
- Single 3 leaded device replaces 2 individual components
- Integral Heat Sink / Locking Tabs
- Supplied in 16mm Tape and Reel – 6000 units/reel
- Superior Low Thermal and Electrical capability

## Mechanical Characteristics


- Footprint Area of 16.51 mm<sup>2</sup>
- Case: Molded Epoxy
- Meets UL94VO at 1/8 inch
- Weight: 72 milligrams
- Lead and Mounting Temperatures: 260°C max for 10 seconds

**SURFACE MOUNT  
P – CHANNEL  
MOSKEY®**



## Description

The MOSKEY® combines a MOSFET with a Schottky Rectifier to provide reverse blocking capability in a single three leaded package. This device is well suited for applications such as battery chargers and switching where the intrinsic source-drain diode is an undesirable feature.



## Absolute Maximum Ratings at 25°C

| RATING                    | SYMBOL    | VALUE        | UNIT  |
|---------------------------|-----------|--------------|-------|
| Cathode-to-Source Voltage | $V_{KSS}$ | $\pm 20$     | Vdc   |
| Gate-to-Source Voltage    | $V_{GS}$  | $\pm 10$     | Vdc   |
| Cathode Current:          |           |              |       |
| Continuous @ TA=25°C      | $I_K$     | 1.0          | Adc   |
| Single Pulsed             | $I_{KM}$  | 6.0          | Apk   |
| Total Power Dissipation   | $PD$ (1)  | 1.9          | Watts |
| Storage Temperature       | $T_{stg}$ | -55 to 150°C | °C    |
| Operating Temperature     | $T_{op}$  | -55 to 150°C | °C    |

## Thermal Characteristics

### Thermal Resistance:

|                         |              |     |         |
|-------------------------|--------------|-----|---------|
| Junction to Tab         | $R_{jtab}$   | 20  | °C/Watt |
| (1) Junction-to-ambient | $R_{ja}$ (1) | 65  | °C/Watt |
| (2) Junction-to-ambient | $R_{ja}$ (2) | 150 | °C/Watt |

(1) Mounted on 2" square by 0.06" thick FR4 board with a 1" x 1" square 2 ounce copper pattern.


(2) Mounted on 0.06 thick FR4 board, using recommended footprint.

# PRELIMINARY

## Electrical Characteristics at 25°C

| ELECTRICAL CHARACTERISTICS (TA = 25°C unless otherwise noted)    |  |  |  |     |     |     |       |
|--|--|--|--|-----|-----|-----|-------|
| Symbol   | Parameter                                  | Conditions                                     |  | Min | Typ | Max | Units |
| <b>OFF CHARACTERISTICS</b>                                       |  |  |  |     |     |     |       |
| BVKSS  | Cathode-Source Breakdown Voltage           | VGS= 0V; IK = 250uA                            |  | 20  |     |     | V     |
| IKSSF  | Zero Gate Voltage Cathode Current: Forward | VKS= -16V, VGS = 0V                            |  |     | 1   |     | uA    |
| IKSSR  | Zero Gate Voltage Cathode Current:Reverse  | VKS= +16V, VGS = 0V                            |  |     | 1   |     | mA    |
| IGSS   | Gate-Body Leakage Current                  | VGS= +/- 8V, VKS = 0V                          |  |     | 100 |     | nA    |
| <b>ON CHARACTERISTICS (pulsed 500us max, duty cycle &lt; 2%)</b> |  |  |  |     |     |     |       |
| VGS(TH)  | Gate Threshold Voltage                     | VKS $\geq$ VGS; IK = 250uA                     |  | 1   | 1.9 | 3   | V     |
| DELTA VGS(TH)/ TJ  | Gate Threshold Voltage Temp Coefficient    | IK = 250uA, Reference to 25°C                  |  |     | 3.5 |     | mV/°C |
| VKS (ON)   | Static Cathode-Source On Voltage           | VGS = 4.5 V; IK = 1A                           |  |     | 750 |     | mV    |
| VKS (ON)   | Static Cathode-Source On Voltage           | VGS = 4.5 ; IK = 0.5A                          |  |     | 550 |     | mV    |
| IK(ON)   | On State Cathode Current                   | VGS = 4.5 V; VKS = 5V                          |  | 3   |     |     | A     |
| Gfs  | Forward Transconductance                   | VDS = 5V; IK = 0.5A                            |  |     | 3   |     | S     |
| <b>DYNAMIC CHARACTERISTICS</b>                                   |  |  |  |     |     |     |       |
| Ciss   | Input Capacitance                          | VKS = 15 V; VGS = 0V, F = 1MHz                 |  | 165 |     |     | pF    |
| Coss   | Output Capacitance                         | VKS = 15 V; VGS = 0V, F = 1MHz                 |  | 60  |     |     | pF    |
| Crss   | Reverse Transfer Capacitance               | VKS = 15 V; VGS = 0V, F = 1MHz                 |  | 25  |     |     | pF    |
| <b>SWITCHING CHARACTERISTICS</b>                                 |  |  |  |     |     |     |       |
| Td(ON)   | Turn On Delay Time                         | VDD = 15V, IK = 1A, VGS = 10V, Rg = 6 $\Omega$ |  | 8   | 20  |     | ns    |
| Tr   | Turn On Rise Time                          | VDD = 15V, IK = 1A, VGS = 10V, Rg = 6 $\Omega$ |  | 9   | 20  |     | ns    |
| Td(OFF)  | Turn Off Delay time                        | VDD = 15V, IK = 1A, VGS = 10V, Rg = 6 $\Omega$ |  | 14  | 30  |     | ns    |
| Tf   | Turn Off Fall time                         | VDD = 15V, IK = 1A, VGS = 10V, Rg = 6 $\Omega$ |  | 2   | 10  |     | ns    |
| Qg   | Total Gate Charge                          | VDS = 15V, IK = 1A, VGS = 10V                  |  | 3.5 | 5   |     | nC    |
| Qgs  | Gate-Source Charge                         | VDS = 15V, IK = 1A, VGS = 10V                  |  | 0.6 |     |     | nC    |
| Qgd  | Gate-Cathode Charge                        | VDS = 15V, IK = 1A, VGS = 10V                  |  | 0.8 |     |     | nC    |

# PRELIMINARY



MECHANICAL SPECIFICATIONS