






**OBSOLETE**

SPECIFICATIONS:

MATERIAL:-

BASE: PA9T/LCP, BLACK/NATURAL COLOR

COVER: SUS, T=0.15mm

CONTACT TERMINAL: C5210-H, T=0.15mm

GUIDE TERMINAL: C5210-H, T=0.15mm

FINISH:-

COVER: FINISH LAYER SELECTED Sn

CONTACT TERMINAL: SELECTED AU Sn-Cu

GUIDE TERMINAL: FINISHED LAYER Sn

ELECTRICAL:-

CONTACT RESISTANCE: 40 mΩ MAX.

INSULATION RESISTANCE: 100 MΩ MIN.

*LEAD CO-PLANARITY: MAX 0.10mm

NOTES: ALL DIMENSIONS AND NOTES
MARKED $\times$ ARE CRITICAL AND
MUST BE CHECKED IN ACCORDANCE
WITH QUALITY DOC. Q1-02A

TOLERANCES
X. = ± 0.30 mm
X.X = ± 0.25 mm
X.XX = ± 0.20 mm

Allan	1	01.08.06	-
NAME	ISS.	DATE	C/NOTE
APPROVED: <i>Pran</i>			
CHECKED: <i>Pran</i>			
DRAWN: Allan			
CUSTOMER REF.:			
ASSEMBLY DRG:			

HARWIN

HARWIN USA
TEL: 603 893 5376
FAX: 603 893 5396
mis@harwin.com

HARWIN Europe (UK)
TEL: 023 9231 4545
FAX: 023 9231 4590
mis@harwin.co.uk

HARWIN Asia
TEL: +65 6 779 4909
FAX: +65 6 779 3868
mis@harwin.com.sg

THIS DRAWING AND ANY
INFORMATION OR DESCRIPTIVE
MATTER SET OUT HEREON ARE
CONFIDENTIAL AND COPYRIGHT
PROPERTY OF THE HARWIN
GROUP AND MUST NOT BE
DISCLOSED, LOANED, COPIED
OR USED FOR MANUFACTURING,
TENDERING OR FOR ANY
OTHER PURPOSE WITHOUT
THEIR WRITTEN PERMISSION.

TOLERANCES
X. = ± 1 mm
X.X = ± 0.25 mm
X.XX = ± 0.10 mm
X.XXX = ± 0.01 mm
ANGLES = $\pm 5^\circ$
UNLESS STATED

MATERIAL:
SEE NOTES
FINISH: SEE NOTES
S/AREA: mm²

TITLE:
LVDS POWER UP 30 PIN
RECEPTACLE (OFFSET TYPE)

DRAWING NUMBER:
M711-2113042R

SHT
1
OF 1