






REVISIONS				DOC. NO. SPC-FD05, Total Pages: 2			
DCP #	REV	DESCRIPTION	DRAWN	DATE	CHECKD	DATE	APPRVD
129	A	RELEASED	DJC	3/10/98	JC	3/13/98	JMM



SPECIFICATIONS:

IMPEDANCE: 50 OHMS
WORKING VOLTAGE: 335 VRMS @ SEA LEVEL
FREQUENCY RANGE: 0-6 GHz
INSERTION LOSS: ≤ .1 dB MAX/1 GHz
VSWR: 1.5 MAX @ 6 GHz
FOR RG-174, 188, 188A, 316/U, ALPHA 9174, 9316,
BELDEN 8216, 83269, 83284, 84316 & TIMES LMR-100 CABLE

ITEM	DESCRIPTION	QTY	MATERIAL	FINISH
7	COVER	1	BRASS	NICKEL
6	FERRULE	1	COPPER	NICKEL
5	HOUSING	1	BRASS	NICKEL
4	DIELECTRIC	1	DELRIIN	NONE
3	DIELECTRIC	1	TEFLON	NONE
2	PIN	1	BRASS	GOLD
1	BODY	1	BeCu	NICKEL



SUGGESTED STRIPPING INSTRUCTIONS
SUGGESTED CRIMP DIES: .130
PIN TO BE SOLDERED

DISCLAIMER
ALL STATEMENTS AND TECHNICAL INFORMATION CONTAINED HEREIN ARE BASED UPON INFORMATION AND/OR TESTS WE BELIEVE TO BE ACCURATE AND RELIABLE. SINCE CONDITIONS OF USE ARE BEYOND OUR CONTROL, THE USER SHALL DETERMINE THE SUITABILITY OF THE PRODUCT FOR THE INTENDED USE AND ASSUME ALL RISK AND LIABILITY WHATSOEVER IN CONNECTION THEREWITH.



SPC TECHNOLOGY

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE FOR REFERENCE PURPOSES ONLY.				DRAWING TITLE: MCX R/A CRIMP PLUG			
DRAWN BY: DANIEL CAREY				DATE: 3/10/98			
CHECKED BY: JOHN COLE				DATE: 3/13/98			
APPROVED BY: JEFF MCYICKER				DATE: 7/7/98			
SCALE: NTS				SHEET: 1 OF 1			