




Hittite
MICROWAVE PRODUCTS
FROM ANALOG DEVICES

Analog Devices Welcomes Hittite Microwave Corporation

NO CONTENT ON THE ATTACHED DOCUMENT HAS CHANGED



THIS PAGE INTENTIONALLY LEFT BLANK



MICROWAVE CORPORATION v00.0511




Typical Applications

The HMC896LP4E is ideal for:

- Test & Measurement Equipment
- Military RADAR & EW/ECM
- SATCOM & Space
- Industrial & Medical Equipment

Functional Diagram



HMC896LP4E

FILTER - TUNABLE, BAND PASS SMT 10 - 18 GHz

Features

- Fast Tuning Response
- Excellent Wideband Rejection
- Tunable low side/high side rejection "notch"
- Single Chip Replacement for Mechanically Tuned Designs
- 24 Lead 4x4 mm SMT Package

General Description

The HMC896LP4E is a MMIC band pass filter which features a user selectable passband frequency. The 3 dB filter bandwidth is approximately 9%. The 20 dB filter bandwidth is approximately 22%. The center frequency can be varied between 10 and 18 GHz by applying an analog tune voltage between 0 and 14V. This tunable filter can be used as a much smaller alternative to physically large switched filter banks and cavity tuned filters. The HMC896LP4E has excellent microphonics due to the monolithic design, and provides a dynamically adjustable solution in advanced communications applications.

Electrical Specifications, $T_A = +25^\circ\text{C}$, $V_{fctl} = V_{nctl}$ Unless Otherwise Stated

Parameter	Min.	Typ.	Max.	Units
F_{center} Tuning Range	10		18	GHz
3 dB Bandwidth		9		%
Low Side Rejection Frequency (Rejection >20 dB)		$0.89 * F_{\text{center}}$		GHz
High Side Rejection Frequency (Rejection >20 dB)		$1.10 * F_{\text{center}}$		GHz
Low Side Sub-Harmonic Rejection (Rejection >40 dB)		$0.75 * F_{\text{center}}$		GHz
High Side Sub-Harmonic Rejection (Rejection >40 dB)		$1.18 * F_{\text{center}}$		GHz
Re-entry Frequency (Rejection <30 dB)		>40		GHz
Insertion Loss		9		dB
Return Loss (2 dB bandwidth)		11		dB
Input IP3 (Pin = 0 to +15 dBm)		26		dBm
Input Power @ 5° Shift In Insertion Phase ($V_{fctl} = 0V$)		8		dBm
Input Power @ 5° Shift In Insertion Phase ($V_{fctl} = 1V$)		12		dBm
Frequency Control Voltage (V_{fctl})	0		14	V
Source/Sink Current (I_{fctl})			±1	mA
Low Side/High Side Rejection Control Voltage (V_{nctl})	0		14	V
Source/Sink current (I_{nctl})			±1	mA
Residual Phase Noise ^[1] (100 kHz Offset)		-158		dBc/Hz
F_{center} Drift Rate		-1.5		MHz/°C
Tuning Speed, Phase Settling to within 10° ^[2]		< 200		ns

[1] Optimum residual phase noise performance requires the use of a low noise driver circuit.

[2] Tuning speed includes 40 ns tuning voltage ramp from driver.


For price, delivery and to place orders: Hittite Microwave Corporation, 2 Elizabeth Drive, Chelmsford, MA 01824

Phone: 978-250-3343 Fax: 978-250-3373 Order On-line at www.hittite.com


Application Support: Phone: 978-250-3343 or apps@hittite.com

FILTER - TUNABLE, BAND PASS SMT 10 - 18 GHz


Broadband Insertion Loss, $V_{fctl} = V_{nctl}$




Broadband Return Loss, $V_{fctl} = V_{nctl}$




Insertion Loss, $V_{fctl} = V_{nctl}$




Return Loss, $V_{fctl} = V_{nctl}$



**Insertion Loss vs. Temperature
 $V_{fctl} = V_{nctl} = 7V$**




**Return Loss vs. Temperature
 $V_{fctl} = V_{nctl} = 7V$**




FILTER - TUNABLE, BAND PASS SMT 10 - 18 GHz


Insertion Loss vs. V_{nctl} , Low Side
 $V_{fctl} = 7V$




Insertion Loss vs. V_{nctl} , High Side
 $V_{fctl} = 7V$




Center Frequency vs. Temperature,
 $V_{fctl} = V_{nctl}$




Insertion Loss vs. Temperature,
 $V_{fctl} = V_{nctl}$



3 dB Bandwidth vs. Temperature,
 $V_{fctl} = V_{nctl}$




Input Return Loss in a 2 dB Bandwidth
vs. Temperature, $V_{fctl} = V_{nctl}$






FILTER - TUNABLE, BAND PASS SMT 10 - 18 GHz


**Low Side Rejection Ratio
vs. Temperature [1]**




**High Side Rejection Ratio
vs. Temperature [1]**




Tuning Sensitivity vs. Temperature




Group Delay vs. Frequency



Group Delay vs. Fcenter vs. Temperature




Input IP3 vs. Temperature




[1] Rejection ratio is defined as the ratio of the frequency at which the relative insertion loss is 20 dB to f_{center}

FILTER - TUNABLE, BAND PASS SMT 10 - 18 GHz


Residual Phase Noise, $V_{fctl} = V_{nctl}$




Phase Sensitivity vs. V_{fctl}



**Insertion Phase vs. Input Power
 $V_{fctl} = V_{nctl}$**



**F_{center} vs. Input Power
 $V_{fctl} = V_{nctl}$**



Absolute Maximum Ratings


Frequency Control Voltage (V_{fctl})	-0.5 to +15V
Notch Control Voltage (V_{nctl})	-0.5 to +15V
RF Power Input	27 dBm
Storage Temperature	-65 to +150 °C
ESD Sensitivity (HBM)	Class 1A

Reliability Information

Junction Temperature to Maintain 1 Million Hour MTTF	150 °C
Nominal Junction Temperature ($T = 85$ °C and $P_{in} = 27$ dBm)	103 °C
Operating Temperature	-40 to +85 °C



**ELECTROSTATIC SENSITIVE DEVICE
OBSERVE HANDLING PRECAUTIONS**

FILTER - TUNABLE, BAND PASS SMT
10 - 18 GHz
Outline Drawing

Package Information

Part Number	Package Body Material	Lead Finish	MSL Rating	Package Marking ^[1]
HMC896LP4E	RoHS-compliant Low Stress Injection Molded Plastic	100% matte Sn	MSL1 ^[2]	H896 XXXX

[1] 4-Digit lot number XXXX

[2] Max peak reflow temperature of 260 °C



MICROWAVE CORPORATION v00.0511




HMC896LP4E

FILTER - TUNABLE, BAND PASS SMT 10 - 18 GHz

Pin Descriptions


Pin Number	Function	Description	Interface Schematic
1, 2, 4 - 7, 12 - 15, 17 - 19, 24	GND	These pins and exposed paddle must be connected to RF/DC ground.	
11, 20 - 23	NC	The pins are not connected internally; however, all data shown herein was measured with these pins connected to RF/DC ground externally	
3	RFIN	This pin is AC coupled and matched to 50 Ohms.	
8	Vnctl	Low side/high side notch control voltage.	
9	Vfctl	Center frequency control voltage.	
10	Vfctl	Center frequency control voltage.	
16	RFOUT	This pin is AC coupled and matched to 50 Ohms.	

Application Circuit



For price, delivery and to place orders: Hittite Microwave Corporation, 2 Elizabeth Drive, Chelmsford, MA 01824
 Phone: 978-250-3343 Fax: 978-250-3373 Order On-line at www.hittite.com
 Application Support: Phone: 978-250-3343 or apps@hittite.com

Evaluation PCB



List of Materials for Evaluation PCB 131085 [1]

Item	Description
J1, J2	Connector, 2.9mm, Female
J5, J6, J7, J8	DC Pin
C1, C2, C3	100 pF Capacitor, 0402 Pkg.
U1	HMC896LP4E Filter - Tunable
PCB [2]	130746 Evaluation PCB

[1] Reference this number when ordering complete evaluation PCB

[2] Circuit Board Material: Arlon 25FR or Rogers 25FR

The circuit board used in the application should use RF circuit design techniques. Signal lines should have 50 Ohms impedance while the package ground leads and exposed paddle should be connected directly to the ground plane similar to that shown. A sufficient number of via holes should be used to connect the top and bottom ground planes. The evaluation circuit board shown is available from Hittite upon request.