


## 5mm Pitch Low Profile Screw Terminal

- 2 & 3 pole interlocking
- Test probe facility
- Moulded in black  
UL94V-0 PA (GF)
- Wire protector  
terminals
- UL approved
- Guided pin alignment

## CTB5202 series



| Type No.   | Poles | Length |
|------------|-------|--------|
| CTB5202/2  | 2     | 10mm   |
| CTB5202/3  | 3     | 15mm   |
| CTB5202/4  | 4     | 20mm   |
| CTB5202/5  | 5     | 25mm   |
| CTB5202/6  | 6     | 30mm   |
| CTB5202/7  | 7     | 35mm   |
| CTB5202/8  | 8     | 40mm   |
| CTB5202/9  | 9     | 45mm   |
| CTB5202/10 | 10    | 50mm   |
| CTB5202/11 | 11    | 55mm   |
| CTB5202/12 | 12    | 60mm   |




|                           |                         |
|---------------------------|-------------------------|
| Rating                    | 300V/15A                |
| Insulation resistance     | 5000M $\Omega$ at 1000V |
| Operating temperature     | -33°C to 120°C          |
| Cable entry               | 1.5mm <sup>2</sup>      |
| Withstand Voltage         | AC2000/1Min             |
| Recommended PCB hole size | ø1.2mm                  |

## 5 mm Pitch Low Profile 90° Terminal Block

- 2-3 pole interlocking
- Test probe facility
- Wire protector terminals
- Moulded in black UL94V-0
- Guided pin alignment
- 1.5mm<sup>2</sup> cable entry
- UL approved

## CTB5252 series



| Type No.   | Poles | Length |
|------------|-------|--------|
| CTB5252/2  | 2     | 10mm   |
| CTB5252/3  | 3     | 15mm   |
| CTB5252/4  | 4     | 20mm   |
| CTB5252/5  | 5     | 25mm   |
| CTB5252/6  | 6     | 30mm   |
| CTB5252/7  | 7     | 35mm   |
| CTB5252/8  | 8     | 40mm   |
| CTB5252/9  | 9     | 45mm   |
| CTB5252/10 | 10    | 50mm   |
| CTB5252/11 | 11    | 55mm   |
| CTB5252/12 | 12    | 60mm   |

|                           |                         |
|---------------------------|-------------------------|
| Rating                    | 300V/15A                |
| Insulation resistance     | 5000M $\Omega$ at 1000V |
| Operating temperature     | -33°C to 120°C          |
| Cable entry               | 1.5mm <sup>2</sup>      |
| Withstand Voltage         | AC2000V/1Min            |
| Recommended PCB hole size | ø1.2mm                  |