

Miniature Fuse, 6.3 x 32 mm, Time-Lag T, UL, 250 VAC



UL 248-14 · 250VAC · Time-Lag T



Description

- UL Standard Fuse
- Glass Tube

Standards

- UL 248-14
- CSA C22.2 no. 248.14

Approvals

- UL File Number: E42088


Weblinks

[pdf-datasheet](#), [html-datasheet](#), [General Product Information](#), [Approvals](#), [CE declaration of conformity](#), [RoHS](#), [CHINA-RoHS](#), [REACH](#), [e-Shop](#), [SCHURTER-Stock-Check](#), [Distributor-Stock-Check](#), [Detailed request for product](#)

Technical Data

Rated Voltage	125 - 250VAC
Rated current	0.063 - 15 A
Breaking Capacity	35 A - 10 kA
Characteristic	Time-Lag T
Mounting	Fuseholder / Clip
Admissible Ambient Air Temp.	-55 °C to 125 °C
Climatic Category	055/085/21 acc. to IEC 60068-1
Material: Tube	Glass
Material: Endcaps	Nickel-Plated Copper Alloy
Unit Weight	2 g
Storage Conditions	0 °C to 60 °C, max. 70% r.h.
Product Marking	Rated current, Rated voltage, Characteristic, Approvals


Dimension



Pre-Arcing Time

Rated Current In	1.1 x In min.	1.35 x In max.	2.0 x In min	2.0 x In max
0.063 A - 2 A	4 h	60 min	5 s	30 s
2.5 A - 20 A	4 h	60 min	5 s	30 s

Time-Current-Curves



All Variants

Rated Current [A]	Rated Voltage [VAC]	Breaking Capacity	Voltage Drop 1.0 In max. [mV]	Power Dissipation 1.1 I _n typ. [mW]	Melting I ² t 10.0 Intyp. [A ² s]	UL	SA	Order Number
0.063	250	1)	7330	700	0.1	●	●	0034.5204
0.1	250	1)	4500	1170	0.24	●	●	0034.5207
0.125	250	1)	4136	1220	0.37	●	●	0034.5208
0.2	250	1)	2808	1350	0.91	●	●	0034.5213
0.25	250	1)	2334	1410	1.42	●	●	0034.5214
0.3	250	1)	1950	1460	2.22	●	●	0034.5215
0.375	250	1)	1800	1580	3.15	●	●	0034.5217
0.5	250	1)	1125	1800	5.41	●	●	0034.5219
0.75	250	1)	931	2030	10.1	●	●	0034.5223
1	250	1)	750	2210	206	●	●	0034.5225
1.25	250	2)	537	2300	32.3	●	●	0034.5227
1.6	250	2)	450	2370	50	●	●	0034.5229
2	250	2)	427	2480	79	●	●	0034.5231
2.5	250	2)	359	2570	123	●	●	0034.5233
3	250	2)	325	2660	192	●	●	0034.5235
4	250	3)	286	2750	300	●	●	0034.5238
5	250	3)	270	2840	469	●	●	0034.5239
6.25	250	3)	180	1400	455	●	●	0034.5241
7	250	3)	156	1470	592	●	●	0034.5243
8	250	3)	140	1530	769	●	●	0034.5244
10	125	4)	91	2700	1300	●	●	0034.5245
12	125	4)	90	3300	2031	●	●	0034.5246
15	125	4)	90	4500	3377	●	●	0034.5247

Most Popular:

Availability for all products can be searched real-time: <http://www.schurter.com/en/Stock-Check/Stock-Check-SCHURTER>

1) 10 kA @ 125 VAC, p.f. = 0.7 - 0.8 / 35 A @ 250 VAC, p.f. = 0.7 - 0.8

2) 10 kA @ 125 VAC, p.f. = 0.7 - 0.8 / 100 A @ 250 VAC, p.f. = 0.7 - 0.8

3) 10 kA @ 125 VAC, p.f. = 0.7 - 0.8 / 200 A @ 250 VAC, p.f. = 0.7 - 0.8

Rated Cur- rent [A]	Rated Vol- tage [VAC]	Breaking Capacity	Voltage Drop 1.0 I _n max. [mV]	Power Dissi- pation 1.1 I _n typ. [mW]	Melting I ² t 10.0 Intyp. [A²s]	 	Order Number
------------------------	--------------------------	----------------------	---	--	---	---	--------------

4) 10 kA @ 125 VAC , p.f. = 0.7 - 0.8

Packaging Unit Small Box Pack (10 pcs.)