



**Advanced Power
Electronics Corp.**


AP2302AGN-HF

Halogen-Free Product

N-CHANNEL ENHANCEMENT MODE

POWER MOSFET

- ▼ Capable of 2.5V gate drive
- ▼ Lower Gate Charge
- ▼ Surface mount package
- ▼ RoHS Compliant & Halogen-Free




BV_{DSS}	20V
$R_{DS(ON)}$	42m Ω
I_D	4.6A

Description

Advanced Power MOSFETs utilized advanced processing techniques to achieve the lowest possible on-resistance, extremely efficient and cost-effectiveness device.

The SOT-23 package is widely used for all commercial-industrial applications.



Absolute Maximum Ratings

Symbol	Parameter	Rating	Units
V_{DS}	Drain-Source Voltage	20	V
V_{GS}	Gate-Source Voltage	± 8	V
$I_D @ T_A = 25^\circ\text{C}$	Continuous Drain Current ³ , V_{GS} @ 4.5V	4.6	A
$I_D @ T_A = 70^\circ\text{C}$	Continuous Drain Current ³ , V_{GS} @ 4.5V	3.7	A
I_{DM}	Pulsed Drain Current ¹	20	A
$P_D @ T_A = 25^\circ\text{C}$	Total Power Dissipation	1.38	W
T_{STG}	Storage Temperature Range	-55 to 150	$^\circ\text{C}$
T_J	Operating Junction Temperature Range	-55 to 150	$^\circ\text{C}$

Thermal Data

Symbol	Parameter	Value	Unit
Rthj-a	Maximum Thermal Resistance, Junction-ambient ³	90	$^\circ\text{C}/\text{W}$



AP2302AGN-HF

Electrical Characteristics@T_j=25°C(unless otherwise specified)

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
BV _{DSS}	Drain-Source Breakdown Voltage	V _{GS} =0V, I _D =250uA	20	-	-	V
R _{DS(ON)}	Static Drain-Source On-Resistance ²	V _{GS} =4.5V, I _D =4A	-	-	42	mΩ
		V _{GS} =2.5V, I _D =3A	-	-	60	mΩ
V _{GS(th)}	Gate Threshold Voltage	V _{DS} =V _{GS} , I _D =250uA	0.3	-	1.2	V
g _{fs}	Forward Transconductance	V _{DS} =5V, I _D =4A	-	14	-	S
I _{DSS}	Drain-Source Leakage Current	V _{DS} =16V, V _{GS} =0V	-	-	10	uA
I _{GSS}	Gate-Source Leakage	V _{GS} =±8V, V _{DS} =0V	-	-	±100	nA
Q _g	Total Gate Charge ²	I _D =4A	-	6.5	10.5	nC
Q _{gs}	Gate-Source Charge	V _{DS} =10V	-	1	-	nC
Q _{gd}	Gate-Drain ("Miller") Charge	V _{GS} =4.5V	-	2.5	-	nC
t _{d(on)}	Turn-on Delay Time ²	V _{DS} =10V	-	9	-	ns
t _r	Rise Time	I _D =1A	-	12	-	ns
t _{d(off)}	Turn-off Delay Time	R _G =3.3Ω	-	16	-	ns
t _f	Fall Time	V _{GS} =5V	-	5	-	ns
C _{iss}	Input Capacitance	V _{GS} =0V	-	300	480	pF
C _{oss}	Output Capacitance	V _{DS} =20V	-	85	-	pF
C _{rss}	Reverse Transfer Capacitance	f=1.0MHz	-	80	-	pF
R _g	Gate Resistance	f=1.0MHz	-	2	-	Ω

Source-Drain Diode

Symbol	Parameter	Test Conditions	Min.	Typ.	Max.	Units
V _{SD}	Forward On Voltage ²	I _S =1.2A, V _{GS} =0V	-	-	1.2	V
t _{rr}	Reverse Recovery Time ²	I _S =4A, V _{GS} =0V,	-	20	-	ns
Q _{rr}	Reverse Recovery Charge	dl/dt=100A/μs	-	10	-	nC

Notes:







- 1.Pulse width limited by Max. junction temperature.
- 2.Pulse test
- 3.Surface mounted on 1 in² copper pad of FR4 board ; 270°C/W when mounted on min. copper pad.

THIS PRODUCT IS SENSITIVE TO ELECTROSTATIC DISCHARGE, PLEASE HANDLE WITH CAUTION.

USE OF THIS PRODUCT AS A CRITICAL COMPONENT IN LIFE SUPPORT OR OTHER SIMILAR SYSTEMS IS NOT AUTHORIZED.

APEC DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS.

APEC RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION OR DESIGN.






Fig 7. Gate Charge Characteristics




Fig 8. Typical Capacitance Characteristics




Fig 9. Maximum Safe Operating Area




Fig 10. Effective Transient Thermal Impedance




Fig 11. Switching Time Waveform




Fig 12. Gate Charge Waveform