









LOC	DIST	REVISIONS					
HM	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
			E1	REVISED PER ECO-11-005033	21MAR11	RK	HMR
			E2	ADD 1/3, REV ECO-11-011931	10JUN2011	LH	SA




QUAD WIRING

ELECTRICAL SCHEMATIC
(USOC)

1. MATERIAL: HOUSING — POLYCARBONATE, 94V-0 RATED. SEE TABLE FOR COLOR.
110 BLOCKS — POLYCARBONATE, 94V-0 RATED.
JACK CONTACTS — PHOSPHOROUS BRONZE, PLATED WITH $1.27\mu\text{m}$ [.000050] MINIMUM THICK GOLD IN LOCALIZED AREA AND $3.81\mu\text{m}$ [.000150] MINIMUM THICK MATTE TIN IN SOLDER AREA OVER $1.27\mu\text{m}$ [.000050] MINIMUM THICK NICKEL UNDERPLATE.
2. 110 BLOCK WILL TERMINATE 22-26 AWG SOLID CONDUCTORS OR 20-26 AWG 7 STRAND CONDUCTORS, 1.27 [.050] MAXIMUM INSULATION DIAMETER.
3. MOUNTING PANEL THICKNESS 1.473 – 1.600 [.058–.063].
4. PACKAGED 25 MODULAR JACK ASSEMBLIES PER CARTON.
5. CAVITY CONFORMS TO FCC RULES AND REGULATIONS PART 68 SUBPART F REQUIREMENTS.
6. THESE TWO SUGGESTED CUTOUT OPENINGS ARE USED IN TANDEM WITH DUAL FRONT AND BACK CUTOUTS.

	ALPINE WHITE	1-406375-3
	ELECTRIC IVORY	1-406375-1
	VIOLET	1-406375-0
	GREEN	406375-9
	YELLOW	406375-8
	RED	406375-7
	BLUE	406375-6
	ORANGE	406375-5
	NEMA GRAY	406375-4
	WHITE	406375-3
	BLACK	406375-2
LIGHT ALMOND	406375-1	
PACKAGED	HOUSING COLOR	PART NUMBER

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN 25 NOV 96 DL DRUMMOND T. WOOTEN 09 JAN 97 G. ROWMAN 09 JAN 97		 TE Connectivity	
DIMENSIONS: mm [INCHES]		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ± — 1 PLC ± 0.25(.01) 3 PLC ± 0.13(.005) 4 PLC ± — ANGLES ± —		NAME 110 MODULAR JACK ASSEMBLY, RJ11	
		PRODUCT SPEC 108-1389 APPLICATION SPEC 408-3389		SIZE A1	
MATERIAL 		FINISH 		CAGE CODE 00779	
		WEIGHT —		DRAWING NO C-406375	
		CUSTOMER DRAWING		RESTRICTED TO SCALE 4:1 SHEET 1 OF 1 REV F	