



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
E	ECN 6899: UPD FORMAT/PKG. CONTACTS FROM 30u" GOLD TO GOLD FLASH	6/14/13	D. DESJARDIN
F	ECN 7529: CHG'D PANTONE TO 424C FROM 422C	7/23/14	D. CASTRO

"P1"
2X IEEE-1394
TYPE 1 (6 PIN)
MALE CONNECTOR



MODEL NUMBER	LENGTH	
	METERS	FEET
CSM94-05M	0.5	1.64
CSM94-1M	1.0	3.28
CSM94-2M	2.0	6.56
CSM94-3M	3.0	9.84
CSM94-5M	5.0	16.40

NOTES:

1. CABLE ASSEMBLY CONSTRUCTED TO MEET THE REQUIREMENTS OF THE IEEE-1394 (FIREWIRE) SPECIFICATION.
2. CONTACT FINISH: GOLD FLASH.
3. TWISTED PAIRS INDIVIDUALLY SHIELDED. SHIELDS TIED TOGETHER AND TIED TO PIN 2.
4. CABLE OVERALL SHIELD CONNECTED TO METAL SHELLS OF BOTH PLUGS. OVERALL SHIELD ISOLATED FROM TWISTED PAIRS' SHIELDS.
5. CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
6. CABLE SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:
CE2011/65/EU(RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0% ALL OTHER DIMENSIONAL TOLERANCES: .X = ±.2 [5.08] .XX = ±.02 [51] .XXX = ±.005 [13] PROJECTION 	APPROVALS	DATE	 45 BEECHWOOD DRIVE NORTH ANDOVER, MA 01845	
	DRAWN BY D. PARHAM	8/15/2001		
	CHECKED BY T. CLARK	8/16/2001	CATEGORY I/O PRODUCTS	
	APPROVED BY Z. W.	9/14/2001	PRODUCT DESCRIPTION CBL, IEEE1394 TYPE 1/1	
CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY		COLOR VARIATIONS MAY OCCUR	SIZE A	FSCM NO. 43321
			DWG. NO. CSM94	REV. F
		SCALE: NONE	CAD FILE: CSM94.SLDDRW	SHEET 1 OF 1