

Multi-layer ceramic chip capacitors

MCH03 (0603 (0201) size, chip capacitor)

●Features

- 1) Ultra miniature (0.6mm×0.3mm×0.3mm), Ultra light weight (0.3mg)
- 2) Suitable for mobile devices
- 3) Lead-free plating terminal
- 4) No polarity

●Quick Reference

The design and specifications are subject to change without prior notice. Please check the most recent technical specifications prior to placing orders or using the product. For more detail information regarding packaging style code, please check product designation.

Thermal compensation


Part No.	Size code	Temperature characteristics	Operating temp. range (°C)	Rated voltage (V)	Capacitance (pF)	Capacitance tolerance	Thickness (mm)
		code					
MCH03	0603	A (AN)	-55 to +125	25	0.5 to 2.7 (E12 Series) *	C(±0.25pF)	0.3 ± 0.03
					3.0 to 3.9 (E12 Series) *		
					4 to 5 (E12 Series) *		
					5.1 to 10 (E12 Series) *		
					11 to 100 (E12 Series)		
						J(±5%)	

* : 0.5pF/0.75pF/2pF/3pF/4pF/5pF/6pF/7pF/8pF/9pF available

●High dielectric constant

Part No.	Size code	Temperature characteristics		Operating temp. range (°C)	Rated voltage (V)	Capacitance (pF)	Capacitance tolerance	Thickness (mm)
		code						
MCH03	0603	CN	±10%(B)	−25 to +85	25	100 to 2,200 (E6 Series)	K (±10%)	0.3 ± 0.03
			±15% (R) (X7R)	−55 to +125	16	4,700 (E3 Series)		
				−55 to +125	25	100 to 2,200 (E6 Series)		
				−55 to +125	16	4,700 (E3 Series)		
		FN	±15%(X5R)	−55 to +85	6.3	10,000 (E6 Series)	Z (+80%, −20%)	
			+30%, −80% (F)	−25 to +85	16	10,000 (E1 Series)		
			+22%, −82% (Y5V)	−30 to +85	16	10,000 (E1 Series)		

●External dimensions (Unit : mm)



Ceramic capacitors

●Product designation

Code	Product thickness	Packing specification	Reel	Basic ordering unit(pcs.)
K	0.3mm	Paper tape(width 8mm, pitch 2mm)	φ180mm (7in.)	15,000

Part No.

Packaging Style



Rated voltage

Code	Voltage
8	6.3V
3	16V
2	25V

Temperature characteristic code
:Refer to quick reference table.

Nominal capacitance	Capacitance tolerance	
	Code	Tolerance
3-digit designation according to IEC	C	±0.25pF(0.5 to 5pF)
	D	±0.5pF(5.1 to 10pF)
	J	±5%(11pF or more)
	K	±10%
	Z	+80%, -20%

●Product No.list

●Thermal compensation capacitors

Capacitance (pF)	Temperature		A・AN(CG) (COG) (CH) Characteristic	
	Rated voltage (V)			25V
	Tolerance	Product thickness(mm)		
0.5	C (±0.25pF)	0.6 ± 0.03	MCH032A (AN) 0R5CK	
0.75			MCH032A (AN) R75CK	
1.0			MCH032A (AN) 010CK	
1.2			MCH032A (AN) 1R2CK	
1.5			MCH032A (AN) 1R5CK	
1.8			MCH032A (AN) 1R8CK	
2.0			MCH032A (AN) 020CK	
2.2			MCH032A (AN) 2R2CK	
2.7			MCH032A (AN) 2R7CK	
3.0			MCH032A (AN) 030CK	
3.3			MCH032A (AN) 3R3CK	
3.9			MCH032A (AN) 3R9CK	
4.0			MCH032A (AN) 040CK	
4.7			MCH032A (AN) 4R7CK	
5.0			MCH032A (AN) 050CK	
5.6	D (±0.5pF)	0.6 ± 0.03	MCH032A (AN) 5R6DK	
6			MCH032A (AN) 060DK	
6.8			MCH032A (AN) 6R8DK	
7			MCH032A (AN) 070DK	
8			MCH032A (AN) 080DK	
8.2			MCH032A (AN) 8R2DK	
9			MCH032A (AN) 090DK	
10			MCH032A (AN) 100DK	

Capacitance (pF)	Temperature		A・AN(CG) (COG) (CH) Characteristic
	Rated voltage (V)		
	Tolerance	Product thickness(mm)	
			25V
			Product No.
12	J (±5%)	0.6 ± 0.03	MCH032A (AN) 120JK
15			MCH032A (AN) 150JK
18			MCH032A (AN) 180JK
22			MCH032A (AN) 220JK
27			MCH032A (AN) 270JK
33			MCH032A (AN) 330JK
39			MCH032A (AN) 390JK
47			MCH032A (AN) 470JK
56			MCH032A (AN) 560JK
68			MCH032A (AN) 680JK
82			MCH032A (AN) 820JK
100			MCH032A (AN) 101JK

Ceramic capacitors

•High dielectric constant capacitors

Capacitance (pF)	Temperature		CN (R) (B) (X7R) Characteristic		CN (X5R) Characteristic
	Rated voltage (V)		25V	16V	6.3V
	Tolerance	Product thickness(mm)	Product No.	Product No.	Product No.
100	K (±10%)	0.6 ± 0.03	MCH032CN101KK		
150			MCH032CN151KK		
220			MCH032CN221KK		
330			MCH032CN331KK		
470			MCH032CN471KK		
680			MCH032CN681KK		
1,000			MCH032CN102KK		
1,500			MCH032CN152KK		
2,200			MCH032CN222KK		
4,700				MCH033CN472KK	
10,000					MCH038CN103KK


Capacitance (pF)	Temperature		FN(F) (Y5V) Characteristic
	Rated voltage (V)		16V
	Tolerance	Product thickness(mm)	Product No.
10,000	Z (+80%, -20%)	0.6 ± 0.03	MCH033FN103ZK

Ceramic capacitors

•Performance and test method

No.	Items	Performance		Test Method (As per JIS C 5101-1, JIS C 5101-10)																	
1	Appearance and dimensions	No marked defects shall be allowed for appearance. Dimensions shall be as specified the clause 4.		As per 4.4 of JIS C 5101-1. As per 4.5 of JIS C 5101-10 Using a Magnifier.																	
2	Withstanding voltage	No dielectrical breakdown or other damage shall be allowed.		As per 4.6 of JIS C 5101-1. As per 4.6.4 of JIS C 5101-10 Voltage shall be applied as per Table1. <table><tr><th colspan="2">Table 1</th></tr><tr><th>Charac- teristic</th><th>Voltage</th></tr><tr><td>A, AN</td><td>300% Rated voltage</td></tr><tr><td>CN</td><td rowspan="2">250% Rated voltage</td></tr><tr><td>FN</td></tr></table> Voltage shall be applied for 1 to 5s with 50mA charging and discharging current.	Table 1		Charac- teristic	Voltage	A, AN	300% Rated voltage	CN	250% Rated voltage	FN								
Table 1																					
Charac- teristic	Voltage																				
A, AN	300% Rated voltage																				
CN	250% Rated voltage																				
FN																					
3	Insulation resistance	Not less than 10000MΩ or 500MΩ · μF, whichever is less. (For products with rated voltage less than 16V, it is not less than 10000MΩ or 100MΩ · μF, whichever is less.)		As per 4.5 of JIS C 5101-1. As per 4.6.3 of JIS C 5101-10 Measurements shall be made after 60+/-5s period of the rated voltage applied.																	
4	Capacitance	Capacitance shall be within specified tolerance range.		As per 4.7 of JIS C 5101-1. As per 4.6.1 of JIS C 5101-10 Measurements shall be made under the conditions specified in Table 2. <table><tr><th colspan="3">Table 2</th></tr><tr><th rowspan="2">Charac- teristic</th><th colspan="2">Frequency · Voltage</th></tr><tr><th>≤ 1000 pF</th><th>> 1000 pF</th></tr><tr><td>A, AN</td><td>1+/-0.1MHz 1+/-0.1Vrms.</td><td>1+/-0.1kHz 1+/-0.1Vrms.</td></tr><tr><td>CN</td><td colspan="2">1+/-0.1kHz</td></tr><tr><td>FN</td><td colspan="2">1+/-0.1Vrms.</td></tr></table>	Table 2			Charac- teristic	Frequency · Voltage		≤ 1000 pF	> 1000 pF	A, AN	1+/-0.1MHz 1+/-0.1Vrms.	1+/-0.1kHz 1+/-0.1Vrms.	CN	1+/-0.1kHz		FN	1+/-0.1Vrms.	
Table 2																					
Charac- teristic	Frequency · Voltage																				
	≤ 1000 pF	> 1000 pF																			
A, AN	1+/-0.1MHz 1+/-0.1Vrms.	1+/-0.1kHz 1+/-0.1Vrms.																			
CN	1+/-0.1kHz																				
FN	1+/-0.1Vrms.																				
5	Dielectric loss tangent	A, AN	Capacitance < 30pF tan δ ≤ 100/(400+20C)% Capacitance ≥ 30pF tan δ ≤ 0.1%	As per 4.8 of JIS C 5101-1. As per 4.6.2 of JIS C 5101-10 Measurements shall be made under the conditions specified in Table 2.																	
	C N	Rated voltage=25V tan δ ≤ 3.0% Rated voltage=16V tan δ ≤ 5.0% Rated voltage=6.3V tan δ ≤ 10.0%																			
	F N	Rated voltage=16V tan δ ≤ 10.0%																			

Ceramic capacitors

No.	Items		Performance		Test Method (As per JIS C 5101-1, JIS C 5101-10)						
6	Temperature characteristic		A, AN	Capacitance $C \leq 2\text{pF}$ $0\pm 250\text{ppm}/^\circ\text{C}$ Capacitance $C=3\text{pF}$ $0\pm 120\text{ppm}/^\circ\text{C}$ Capacitance $C \geq 4\text{pF}$ $0\pm 60\text{ppm}/^\circ\text{C}$ (-55°C to $+125^\circ\text{C}$)	As per 4.24 of JIS C 5101-1. As per 4.7 of JIS C 5101-10 Temperature coefficient shall be calculated at 20°C and 85°C . As per 4.24 of JIS C 5101-1. As per 4.7 of JIS C 5101-10 If required, measurements shall be made at a given temperature.						
			C N	X7R R		$\pm 15\%$ (-55°C to $+125^\circ\text{C}$)					
				B		$\pm 10\%$ (-25°C to $+85^\circ\text{C}$)					
				X5R		$\pm 15\%$ (-55°C to $+85^\circ\text{C}$)					
F N	$+30\%, -80\%$ (-25°C to $+85^\circ\text{C}$) ----- $+22\%, -82\%$ (-30°C to $+85^\circ\text{C}$)										
7	Solderability		More than 3/4 of each end termination shall be covered with new solder.		As per 4.15.2 of JIS C 5101-1. As per 4.11 of JIS C 5101-10 The solder specified in JIS Z 3282 H63A shall be used. Ans the flux containing 25% rosin and ethanol solution shall be used. The specimens shall be immersed into the solder at $235\pm 5^\circ\text{C}$ for $2\pm 0.5\text{s}$ So that both end terminations are completely under solder.						
8	Resistance to solderin heat	Appearance	Without mechanical damage.		As per 4.14 of JIS C 5101-1. As per 4.10 of JIS C 5101-10 The solder specified in JIS Z 3282. H63A shall be used. The specimens shall be immersed into the solder at $260\pm 5^\circ\text{C}$ for $5\pm 0.5\text{s}$ so that both end terminations are completely under the solder. Pre-heating at $150\pm 10^\circ\text{C}$ for 1 to 2min Initial measurements prior to test shall be performed after the thermal Pre-conditioning specified in Remarks (1). Final measurements shall be made after the specimens have been left at room temperature as per Table3. <table><caption>Table3</caption><tr><th>Charac-teristic</th><th>Time</th></tr><tr><td>A, AN</td><td>24 ± 2 h</td></tr><tr><td>CN, FN</td><td>48 ± 4 h</td></tr></table>	Charac-teristic	Time	A, AN	24 ± 2 h	CN, FN	48 ± 4 h
		Charac-teristic	Time								
		A, AN	24 ± 2 h								
		CN, FN	48 ± 4 h								
		Change rate from initial value	A, AN	Within $\pm 2.5\%$ or $\pm 0.25\text{pF}$ whichever is larger.							
			C N	Within $\pm 7.5\%$							
			F N	Within $\pm 20\%$							
Dielectric loss tangent	Within specified initial value.										
Insulation resistance	Within specified initial value.										
Withstanding voltage	No defects shall be allowed.										
9	End termination adherence		Without peeling or sign of peeling shall be allowed on the end terminations.		As per 4.13 of JIS C 5101-1. As per 4.8 of JIS C 5101-10 A 2N weight for $10\pm 1\text{s}$ shall be applied to the soldered specimens as shown by the arrow mark in the below sketch. 						

Ceramic capacitors

No.	Items		Performance		Test Method (As per JIS C 5101-1, JIS C 5101-10)																					
10	Bending strength	Appearance	Without mechanical damage.		As per 4.35 of JIS C 5101-1. As per 4.9 of JIS C 5101-10 Glass epoxy board with soldered specimens shall be bent till 1mm by 1.0mm/s.																					
11	Vibration	Appearance	Without mechanical damage.		As per 4.17 of JIS C 5101-1 The specimens shall be soldered on the specified test jig. Initial measurements shall be made after the thermal pre-conditioning specified in Remarks(1). Final measurements shall be made after the specimens have been left at room temperature as per Table3. [Condition] Directions : 2h each X, Y and Z directions Total : 6h Frequency range : 10 to 55 to 10Hz(1min) Applitude : 1.5mm (shall not exceed acceleration196m/s²) Table3 <table><tr><td>Charac-teristic</td><td>Time</td></tr><tr><td>A, AN</td><td>24+/-2 h</td></tr><tr><td>CN, FN</td><td>48+/-4 h</td></tr></table>	Charac-teristic	Time	A, AN	24+/-2 h	CN, FN	48+/-4 h															
		Charac-teristic	Time																							
		A, AN	24+/-2 h																							
		CN, FN	48+/-4 h																							
		Change rate from initial value	A, AN	Capacitance shall be within specified tolerance range.																						
C N	Within +/-7.5%																									
F N	Within +/-20%																									
Dielectric loss tangent	Within specified initial value.																									
12	Temperature cycling	Appearance	Without mechanical damage.		As per 4.16 of JIS C 5101-1 As per 4.12 of JIS C 5101-10 The specimens shall be soldered on the test jig shown in Remarks. Temperature cycle : 5cycles Initial measurements prior to test shall be performed after the thermal per-conditioning specified in Remarks (1). Final measurements shall be made after the specimens have been left at room temperature as per Table3. Test condition <table><tr><td>Step</td><td>Temp. (°C)</td><td>Time (min)</td></tr><tr><td>1</td><td>Min operating temp.</td><td>30+/-3</td></tr><tr><td>2</td><td>Room temp.</td><td>≤ 3</td></tr><tr><td>3</td><td>Max operating temp.</td><td>30+/-3</td></tr><tr><td>4</td><td>Room temp.</td><td>≤ 3</td></tr></table> Table3 <table><tr><td>Charac-teristic</td><td>Time</td></tr><tr><td>A, AN</td><td>24+/-2 h</td></tr><tr><td>CN, FN</td><td>48+/-4 h</td></tr></table>	Step	Temp. (°C)	Time (min)	1	Min operating temp.	30+/-3	2	Room temp.	≤ 3	3	Max operating temp.	30+/-3	4	Room temp.	≤ 3	Charac-teristic	Time	A, AN	24+/-2 h	CN, FN	48+/-4 h
Step		Temp. (°C)	Time (min)																							
1		Min operating temp.	30+/-3																							
2		Room temp.	≤ 3																							
3		Max operating temp.	30+/-3																							
4		Room temp.	≤ 3																							
Charac-teristic		Time																								
A, AN	24+/-2 h																									
CN, FN	48+/-4 h																									
Change rate from initial value	A, AN	Within +/-2.5% or +/-0.25pF whichever is larger.																								
		C N	Rated voltage 25V,16V	Within +/-7.5%																						
	Rated voltage 6.3V		Within +/-10.0%																							
F N		Within +/-20%																								
Dielectric loss tangent	Within specified initial value.																									
Insulation resistance	Within specified initial value.																									
Withstanding voltage	No defects shall be allowed.																									

Ceramic capacitors

No.	Items		Performance		Test Method (As per JIS C 5101-1, JIS C 5101-10)						
13	Humidity (Steady)	Appearance	Without mechanical damage.		As per 4.22 of JIS C 5101-1 JIS C 5101-10 Test temperature : 60+/-2°C Relative humidity : 90 to 95% Test time : 500 +24/-0 h Initial measurements prior to test shall be made after the voltage pre-conditioning specified in Remarks (2). Final measurements have been left at room temperature as per Table3. Table3 <table><tr><td>Charac-teristic</td><td>Time</td></tr><tr><td>A, AN</td><td>24+/-2 h</td></tr><tr><td>CN, FN</td><td>48+/-4 h</td></tr></table>	Charac-teristic	Time	A, AN	24+/-2 h	CN, FN	48+/-4 h
		Charac-teristic	Time								
		A, AN	24+/-2 h								
		CN, FN	48+/-4 h								
		Change rate from initial value	A, AN			Within +/-5.0% or +/-0.5pF whichever is larger.					
			C N	Rated voltage 25V,16V		Within +/-12.5%					
				Rated voltage 6.3V		Within +/-25.0%					
			F N			Within +/-30.0%					
		Dielectric tangent	A, AN			$\tan \delta \leq 0.3\%$					
			C N			Less than 200% of initial spec.					
F N			Less than 150% of initial spec.								
Insulation resistance	Not less than 1000MΩ or 50MΩ · μF, whichever is less. (For products with rated voltage less than 16V, it is not less than 1000MΩ or 10MΩ · μF, whichever is less.)										
14	Humidity life test	Appearance	Without mechanical damage.		As per 4.22 of JIS C 5101-1 As per 4.14 of JIS C 5101-10 Test temperature : 60+/-2°C Relative humidity : 90 to 95% Voltage : Rated voltage Test time : 500 +24/-0 h Initial measurements prior to test shall be made after the voltage pre-conditioning specified in Remarks (2). Final measurements shall be made after the specimens have been left at room temperature as per Table3. Table3 <table><tr><td>Charac-teristic</td><td>Time</td></tr><tr><td>A, AN</td><td>24+/-2 h</td></tr><tr><td>CN, FN</td><td>48+/-4 h</td></tr></table>	Charac-teristic	Time	A, AN	24+/-2 h	CN, FN	48+/-4 h
		Charac-teristic	Time								
		A, AN	24+/-2 h								
		CN, FN	48+/-4 h								
		Change rate from initial value	A, AN			Within +/-7.5% or +/-0.75pF whichever is larger.					
			C N	Rated voltage 25V,16V		Within +/-12.5%					
				Rated voltage 6.3V		Within +/-25.0%					
			F N			Within +/-30.0%					
		Dielectric loss tangent	A, AN			$\tan \delta \leq 0.5\%$					
			C N			Less than 200% of initial spec.					
F N			Less than 150% of initial spec.								
Insulation resistance	Not less than 500MΩ or 25MΩ · μF, whichever is less. (For products with rated voltage less than 16V, it is not less than 500mΩ or 5MΩ · μF, whichever is less.)										

Ceramic capacitors

No.	Items		Performance		Test Method (As per JIS C 5101-1, JIS C 5101-10)			
15	Heat life test	Appearance	Without mechanical damage.		As per 4.23 of JIS C 5101-1. As per 4.15 of JIS C 5101-10			
		Change rate from initial value	A, AN		Within $\pm 3.0\%$ or $\pm 0.3\text{pF}$ whichever is larger.		Test temperature($^{\circ}\text{C}$)	Voltage
			C N	Rated voltage 25V,16V				
				Rated voltage 6.3V				
			F N		Within $\pm 30.0\%$			
		Dielectric loss tangent	A, AN		$\tan \delta \leq 0.3\%$	1000 +48/-0	200% Rated voltage	1000 +48/-0
			C N		Less than 200% of initial spec.			
			F N		Less than 150% of initial spec.			
		Insulation resistance	Not less than $1000\text{M}\Omega$ or $50\text{M}\Omega \cdot \mu\text{F}$, whichever is less. (For products with rated voltage less than 16V, it is not less than $1000\text{m}\Omega$ or $10\text{M}\Omega \cdot \mu\text{F}$, whichever is less.)				200% Rated voltage	1000 +48/-0

Initial measurements prior to test shall be made after the voltage pre-conditioning specified in Remarks (2).
Final measurements shall be made after the specimens have been left at room temperature

Table3

Charac- teristic	Time
A, AN	24 \pm 2 h
CN, FN	48 \pm 4 h

[Remarks]

Pre-conditioning

If specified in test method of as per 3(Performance and test method), capacitors of CN, FN characteristics shall be pre-conditioned as follows.


(1) Thermal pre-conditioning

Prior to initial measurements, specimens shall be conditioned at a temperature of $150 \pm 10^{\circ}\text{C}$ for a period of 1hr., and shall be allowed to stabilize at room temperature for 48 \pm 4h

(2) Voltage pre-conditioning

Prior to initial measurements, voltage specified as a test condition shall be applied to specimens for a period of 1hr., and the specimens shall be allowed to stabilize at room temperature for 48 \pm 4h

<Test jig>



Ceramic capacitors

●Packaging specifications

Taping dimensions

Diagram illustrating the dimensions for a ceramic capacitor tape. The dimensions are defined as follows:

- C**: Distance between the center of the first and second capacitors.
- D**: Distance between the center of the first and second capacitors (same as C).
- E**: Distance between the center of the first and second capacitors (same as C).
- F**: Distance between the center of the first and second capacitors (same as C).
- G**: Distance between the center of the first and second capacitors (same as C).
- H**: Distance between the center of the first and second capacitors (same as C).
- J**: Diameter of the capacitor.
- d**: Diameter of the capacitor.
- t**: Thickness of the capacitor.
- t₁**: Thickness of the capacitor.

Pulling direction is indicated by an arrow pointing to the right.

Symbol	C	D	E	F	G	H	J	d	t	t ₁
Dimensions	8.0 +/-0.2	3.5 +/-0.05	1.75 +/-0.1	2.0 +/-0.05	2.0 +/-0.05	4.0 +/-0.1	φ1.5 +0.1/-0	0.37 +/-0.02	0.42 +/-0.02	0.5 MAX.

(Unit : mm)

Symbol Style	A	B
MCH03	0.37 +/-0.03	0.67 +/-0.03

(Unit : mm)

Reel dimensions

Diagram illustrating the dimensions for a reel. The dimensions are defined as follows:

- φ13.0±0.2**: Inner diameter of the reel.
- 9.0±1.0**: Width of the reel.
- φ60.0±1.0**: Diameter of the reel.
- φ180±1.5**: Diameter of the reel.

Pulling direction is indicated by an arrow pointing to the right. Label pasting is indicated by an arrow pointing to the label area.

As per EIAJ ET-7200A

(Unit : mm)

(1) The quantity for one reel is as bellows.

Kind of reel	Series	Paper tape	
		Quantity	Symbol
φ180 reel	MCH03	15,000 pcs.	K

- (2) When the tape is pulled out towards the operator with the cover tape facing upward, the feeding holes shall be found on the right portion of the tape.
- (3) Specification of beginning and ending of the tape are as follows.
- Ending(reel's center) : Approx. 300mm (no chips)
- Beginning(reel's round) : Approx. 270mm (no chips)
- : Approx. 30mm (no pasted tape)
- : Approx. 260mm (cover tape only)
- (4) No juncture of tape shall be allowed.
- (5) The share strength of tape shall be more than 5N at the break down strength.
- (6) The peel strength of the cover tape shall be 0.1 to 0.7(N) when the cover tape are peeled 0 to 15° degree from the surface.
- (7) The number of missing components shall not exceed 0.1% of the total number of components (marked number) or one whichever is the larger, and no consecutive missing exceeding two is allowed.
- (8) The reels made from resin shall be used, as per EIAJ ET-7200A.

●Marking

No marking shall be performed on the chip.

Trademark, parts number, quantity, lot No. , and country of origin shall be labeled on each reel, bulk case.

●Numbering system for LOT No.

Example	<u>03</u>	<u>01</u>	<u>A0001</u>	<u>J</u>
	(1)	(2)	(3)	(4)

- (1) The end of the Christian Era <two digits> of production finish.
- (2) Week in completing part of production finish.
- (3) Manufacture continuity number.
- (4) The symbol of manufacturing plant.

The Figure below is label expression

< Label Example > Part Number : MCH032A470JK

The diagram shows a rectangular label with the following content and callouts:

- 1**: Points to the part number **MCH032A470JK** at the top.
- 2**: Points to a small square box on the left side.
- 3**: Points to the quantity **15,000pcs** and the code **0501 00001F**.
- 4**: Points to a QR code in the top right corner.
- 5**: Points to the date code **0123456789** and the lot code **ABCDEFGHI**.
- 6**: Points to the manufacturer name **K. SATO**.
- 7**: Points to the **Pb Free** logo.
- 8**: Points to the **ROHM** logo.


The label also includes a barcode below the quantity and code, and the text **JAPAN** and **Excellence in Electronics** at the bottom.

- ① Part Number
- ② Division cord
- ③ Quantity
- ④ Lot No.
- ⑤ The Country of origin
- ⑥ Inspector
- ⑦ QR code
- ⑧ Trademark

Ceramic capacitors

●Packing method

1) ϕ 180mm Reel



< Packaging unit >

Symbol	K
Quantity of reel in interior box	5
Quantity of reel in box of R-26	20

Dimensions	Packaging	
	R-26	interior box of R-26
A (A')	195	185
B (B')	255	60
C (C')	190	185

(Unit : mm)

< Appearance >

Carton

< Accumulation >

You must do accumulation by ten boxes

< Packaging slip >

1. Customer
2. Parts number
3. Quantity
4. Box quantity
5. Trade mark

●Weight / Piece

(Unit : mg)

Size	Item	Thickness	Characteristic	Weight / Piece
0603 (0201)	MCH03	0.3mm	A, AN	0.3
			CN	0.3
			FN	0.3

(Note) The measured values in the table are for reference only.
Actual weight of these chips may vary slightly lot by lot.

Ceramic capacitors

●Electrical characteristics

■A (C0G) Characteristics




Fig.1 Capacitance-temperature characteristics




Fig.2 Impedance-frequency characteristics

■CN (X7R) Characteristics




Fig.3 Capacitance-temperature characteristics




Fig.4 Impedance-frequency characteristics

■FN (Y5V) Characteristics




Fig.5 Capacitance-temperature characteristics

Notes

- No technical content pages of this document may be reproduced in any form or transmitted by any means without prior permission of ROHM CO.,LTD.
- The contents described herein are subject to change without notice. The specifications for the product described in this document are for reference only. Upon actual use, therefore, please request that specifications to be separately delivered.
- Application circuit diagrams and circuit constants contained herein are shown as examples of standard use and operation. Please pay careful attention to the peripheral conditions when designing circuits and deciding upon circuit constants in the set.
- Any data, including, but not limited to application circuit diagrams information, described herein are intended only as illustrations of such devices and not as the specifications for such devices. ROHM CO.,LTD. disclaims any warranty that any use of such devices shall be free from infringement of any third party's intellectual property rights or other proprietary rights, and further, assumes no liability of whatsoever nature in the event of any such infringement, or arising from or connected with or related to the use of such devices.
- Upon the sale of any such devices, other than for buyer's right to use such devices itself, resell or otherwise dispose of the same, no express or implied right or license to practice or commercially exploit any intellectual property rights or other proprietary rights owned or controlled by
- ROHM CO., LTD. is granted to any such buyer.
- Products listed in this document are no antiradiation design.

The products listed in this document are designed to be used with ordinary electronic equipment or devices (such as audio visual equipment, office-automation equipment, communications devices, electrical appliances and electronic toys).

Should you intend to use these products with equipment or devices which require an extremely high level of reliability and the malfunction of which would directly endanger human life (such as medical instruments, transportation equipment, aerospace machinery, nuclear-reactor controllers, fuel controllers and other safety devices), please be sure to consult with our sales representative in advance.

About Export Control Order in Japan

Products described herein are the objects of controlled goods in Annex 1 (Item 16) of Export Trade Control Order in Japan.

In case of export from Japan, please confirm if it applies to "objective" criteria or an "informed" (by MITI clause) on the basis of "catch all controls for Non-Proliferation of Weapons of Mass Destruction.