

BLF888D; BLF888DS

UHF power LDMOS transistor

Rev. 4 — 18 February 2016

AMPLEON

Product data sheet

1. Product profile

1.1 General description

A 600 W LDMOS RF power transistor for broadcast Doherty transmitter applications. The excellent ruggedness of this device makes it ideal for digital and analog transmitter applications.

Table 1. Application information

RF performance at $V_{DS} = 50$ V in an ultra wide Doherty application.

Test signal	f (MHz)	$P_{L(AV)}$ (W)	G_p (dB)	η_D (%)	IMD_{shldr} (dBc)	PAR (dB)
DVB-T (8k OFDM)	470 to 860	115 to 134 [1]	17	40 to 48 [1]	−38 to −44 [2]	8 [3]

[1] Depending on selected channel.

[2] Depending on exciter used.

[3] PAR (of output signal) at 0.01 % probability on CCDF; PAR of input signal = 9.5 dB at 0.01 % probability on CCDF.

1.2 Features and benefits





- High efficiency
- High power gain
- Excellent ruggedness ($VSWR \geq 40 : 1$ through all phases)
- Excellent thermal stability
- Integrated ESD protection
- One Doherty design covers the full bandwidth from 470 MHz to 860 MHz
- Internal input matching for ease of use
- Compliant to Directive 2002/95/EC, regarding Restriction of Hazardous Substances (RoHS)

1.3 Applications

- Broadcast transmitter applications in the UHF band
- Digital broadcasting

2. Pinning information

Table 2. Pinning

Pin	Description	Simplified outline	Graphic symbol
BLF888D (SOT539A)			
1	drain1 (peak)		
2	drain2 (main)		
3	gate1 (peak)		
4	gate2 (main)		
5	source [1]		
BLF888DS (SOT539B)			
1	drain1 (peak)		
2	drain2 (main)		
3	gate1 (peak)		
4	gate2 (main)		
5	source [1]		

[1] Connected to flange.

3. Ordering information

Table 3. Ordering information

Type number	Package		
	Name	Description	Version
BLF888D	-	flanged balanced ceramic package; 2 mounting holes; 4 leads	SOT539A
BLF888DS	-	earless flanged balanced ceramic package; 4 leads	SOT539B

4. Limiting values

Table 4. Limiting values

In accordance with the Absolute Maximum Rating System (IEC 60134).

Symbol	Parameter	Conditions	Min	Max	Unit
V_{DS}	drain-source voltage		-	104	V
V_{GS}	gate-source voltage		-0.5	+11	V
T_{stg}	storage temperature		-65	+150	°C
T_j	junction temperature	^[1]	-	225	°C

[1] Continuous use at maximum temperature will affect the reliability, for details refer to the on-line MTF calculator.

5. Thermal characteristics

Table 5. Thermal characteristics

Symbol	Parameter	Conditions	Typ	Unit
$R_{th(j-c)}$	thermal resistance from junction to case	$T_{case} = 75\text{ °C}$; $V_{DS} = 50\text{ V}$; $I_{DS} = 2.7\text{ A}$ (main); $I_{DS} = 0\text{ A}$ (peak) [1]	0.27	K/W
		$T_{case} = 90\text{ °C}$; $V_{DS} = 50\text{ V}$; $P_L = 115\text{ W}$; $PAR = 8\text{ dB}$ [2]	0.16	K/W

[1] Measured under DC test conditions, with peak section off.

[2] Measured in an ultra wide Doherty application, using a DVB-T (8k OFDM) signal, PAR (of output signal) at 0.01 % probability on CCDF; PAR of input signal = 9.5 dB at 0.01 % probability on CCDF.

6. Characteristics

Table 6. DC characteristics

$T_j = 25\text{ °C}$; per section unless otherwise specified.

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
$V_{(BR)DSS}$	drain-source breakdown voltage	$V_{GS} = 0\text{ V}$; $I_D = 2.4\text{ mA}$	104	-	-	V
$V_{GS(th)}$	gate-source threshold voltage	$V_{DS} = 10\text{ V}$; $I_D = 240\text{ mA}$	1.4	1.9	2.4	V
I_{DSS}	drain leakage current	$V_{GS} = 0\text{ V}$; $V_{DS} = 50\text{ V}$	-	0.061	2.8	μA
I_{DSX}	drain cut-off current	$V_{GS} = V_{GS(th)} + 3.75\text{ V}$; $V_{DS} = 10\text{ V}$	-	37	-	A
I_{GSS}	gate leakage current	$V_{GS} = 10\text{ V}$; $V_{DS} = 0\text{ V}$	-	-	280	nA
$R_{DS(on)}$	drain-source on-state resistance	$V_{GS} = V_{GS(th)} + 3.75\text{ V}$; $I_D = 8.5\text{ A}$	-	120	-	$\text{m}\Omega$

Table 7. AC characteristics

$T_j = 25\text{ °C}$; per section unless otherwise specified.

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
C_{iss}	input capacitance	$V_{GS} = 0\text{ V}$; $V_{DS} = 50\text{ V}$; $f = 1\text{ MHz}$	-	210	-	pF
C_{oss}	output capacitance	$V_{GS} = 0\text{ V}$; $V_{DS} = 50\text{ V}$; $f = 1\text{ MHz}$	-	70	-	pF
C_{rss}	reverse transfer capacitance	$V_{GS} = 0\text{ V}$; $V_{DS} = 50\text{ V}$; $f = 1\text{ MHz}$	-	1.3	-	pF

Table 8. RF characteristics

$V_{DS} = 50\text{ V}$; $I_{DQ} = 1.3\text{ A}$; $T_{case} = 25\text{ °C}$ unless otherwise specified; in a class-AB production test circuit.

Symbol	Parameter	Conditions	Min	Typ	Max	Unit
Test signal: 2-tone CW						
$P_{L(AV)}$	average output power	$f_1 = 860\text{ MHz}$; $f_2 = 860.1\text{ MHz}$	-	250	-	W
G_p	power gain	$f_1 = 860\text{ MHz}$; $f_2 = 860.1\text{ MHz}$	19	21	-	dB
η_D	drain efficiency	$f_1 = 860\text{ MHz}$; $f_2 = 860.1\text{ MHz}$	43	45	-	%
IMD3	third-order intermodulation distortion	$f_1 = 860\text{ MHz}$; $f_2 = 860.1\text{ MHz}$	-	-32	-29	dBc
Test signal: pulsed CW						
$P_{L(3dB)}$	output power at 3 dB gain compression	$f = 860\text{ MHz}$; $t_p = 100\text{ }\mu\text{s}$; $\delta = 10\text{ %}$	540	580	-	W

7. Test information

7.1 Ruggedness in Doherty operation

The BLF888D and BLF888DS are capable of withstanding a load mismatch corresponding to $VSWR \geq 40 : 1$ through all phases under the following conditions:
 $V_{DS} = 50 \text{ V}$; $f = 810 \text{ MHz}$ at rated load power.

7.2 Test circuit




Table 9. List of components

For test circuit see [Figure 1](#).

Component	Description	Value	Remarks
C1	multilayer ceramic chip capacitor	12 pF [1]	
C2, C3, C4, C5, C6	multilayer ceramic chip capacitor	8.2 pF [1]	
C7	multilayer ceramic chip capacitor	6.8 pF [2]	
C8	multilayer ceramic chip capacitor	4.7 pF [2]	
C9, C12, C13	multilayer ceramic chip capacitor	100 pF [1]	
C10, C11	multilayer ceramic chip capacitor	10 pF [1]	
C14, C15	multilayer ceramic chip capacitor	4.7 μF , 50 V	
C16, C17	multilayer ceramic chip capacitor	3.6 pF [2]	
C18, C19	multilayer ceramic chip capacitor	4.7 μF , 50 V	
C20, C21	electrolytic capacitor	470 μF , 63 V	

Table 9. List of components ...continued

For test circuit see [Figure 1](#).

Component	Description	Value	Remarks
C22, C23	multilayer ceramic chip capacitor	47 pF	[2]
C30	multilayer ceramic chip capacitor	15 pF	[3]
C31	multilayer ceramic chip capacitor	5.6 pF	[3]
C32	multilayer ceramic chip capacitor	2.7 pF	[3]
C33, C34, C35	multilayer ceramic chip capacitor	100 pF	[3]
C36, C37	multilayer ceramic chip capacitor	470 μ F, 50 V	
R1, R2	resistor	10 Ω	
R3, R4	resistor	5.6 Ω	SMD 1206
R5, R6	resistor	100 Ω	
R3, R4	resistor	510 Ω	SMD 1206
T1, T2	semi rigid coax	25 Ω , length = 160 mm	Micro-Coax UT-090C-25


[1] American Technical Ceramics type 180R or capacitor of same quality.

[2] American Technical Ceramics type 100B or capacitor of same quality.

[3] American Technical Ceramics type 100A or capacitor of same quality.

7.3 Graphical data


7.3.1 1-Tone CW pulsed



$I_{DQ} = 2 \times 650$ mA; $t_p = 100$ μ s; $\delta = 10$ %.

- (1) $V_{DS} = 40$ V
- (2) $V_{DS} = 45$ V
- (3) $V_{DS} = 50$ V
- (4) $V_{DS} = 55$ V


Fig 2. Power gain as a function of output power; typical values



$I_{DQ} = 2 \times 650$ mA; $t_p = 100$ μ s; $\delta = 10$ %.

- (1) $V_{DS} = 40$ V
- (2) $V_{DS} = 45$ V
- (3) $V_{DS} = 50$ V
- (4) $V_{DS} = 55$ V

Fig 3. Drain efficiency as a function of output power; typical values



$V_{DS} = 50 \text{ V}$; $t_p = 100 \text{ } \mu\text{s}$; $\delta = 10 \text{ } \%$.


- (1) $I_{DQ} = 2 \times 250 \text{ mA}$
- (2) $I_{DQ} = 2 \times 450 \text{ mA}$
- (3) $I_{DQ} = 2 \times 650 \text{ mA}$
- (4) $I_{DQ} = 2 \times 850 \text{ mA}$

Fig 4. Power gain as a function of output power; typical values

8. Package outline

Flanged balanced ceramic package; 2 mounting holes; 4 leads

SOT539A



DIMENSIONS (millimetre dimensions are derived from the original inch dimensions)

UNIT	A	b	c	D	D ₁	e	E	E ₁	F	H	H ₁	L	p	Q	q	U ₁	U ₂	w ₁	w ₂	w ₃
mm	4.7 4.2	11.81 11.56	0.18 0.10	31.55 30.94	31.52 30.96	13.72	9.50 9.30	9.53 9.27	1.75 1.50	17.12 16.10	25.53 25.27	3.48 2.97	3.30 3.05	2.26 2.01	35.56	41.28 41.02	10.29 10.03	0.25	0.51	0.25
inches	0.185 0.165	0.465 0.455	0.007 0.004	1.242 1.218	1.241 1.219	0.540	0.374 0.366	0.375 0.365	0.069 0.059	0.674 0.634	1.005 0.995	0.137 0.117	0.130 0.120	0.089 0.079	1.400	1.625 1.615	0.405 0.395	0.010	0.020	0.010

Note


1. millimeter dimensions are derived from the original inch dimensions.
2. recommended screw pitch dimension of 1.52 inch (38.6 mm) based on M3 screw.

OUTLINE VERSION	REFERENCES				EUROPEAN PROJECTION	ISSUE DATE
	IEC	JEDEC	EIAJ			
SOT539A						10-02-02 12-05-02

Fig 5. Package outline SOT539A

Earless flanged balanced ceramic package; 4 leads

SOT539B



Dimensions																	
Unit ⁽¹⁾	A	b	c	D	D ₁	E	E ₁	e	F	H	H ₁	L	Q	U ₁	U ₂	w ₂	w ₃
mm	max	4.7	11.81	0.18	31.55	31.52	9.5	9.53	1.75	17.12	25.53	3.48	2.26	32.39	10.29	0.25	0.25
	nom	4.2	11.56	0.10	30.94	30.96	9.3	9.27	1.50	16.10	25.27	2.97	2.01	32.13	10.03		
inches	max	0.185	0.465	0.007	1.242	1.241	0.374	0.375	0.069	0.674	1.005	0.137	0.089	1.275	0.405	0.01	0.01
	nom	0.165	0.455	0.004	1.218	1.219	0.366	0.365	0.059	0.634	0.995	0.117	0.079	1.265	0.395		

Note
1. millimeter dimensions are derived from the original inch dimensions.

sot539b_po

Outline version	References				European projection	Issue date
	IEC	JEDEC	JEITA			
SOT539B						-12-05-02 13-05-24

Fig 6. Package outline SOT539B

9. Handling information

CAUTION



This device is sensitive to ElectroStatic Discharge (ESD). Observe precautions for handling electrostatic sensitive devices.

Such precautions are described in the *ANSI/ESD S20.20*, *IEC/ST 61340-5*, *JESD625-A* or equivalent standards.

10. Abbreviations

Table 10. Abbreviations

Acronym	Description
CCDF	Complementary Cumulative Distribution Function
CW	Continuous Wave
DVB-T	Digital Video Broadcast - Terrestrial
ESD	ElectroStatic Discharge
LDMOS	Laterally Diffused Metal-Oxide Semiconductor
MTF	Median Time to Failure
OFDM	Orthogonal Frequency Division Multiplexing
PAR	Peak-to-Average Ratio
SMD	Surface Mounted Device
UHF	Ultra High Frequency
VSWR	Voltage Standing-Wave Ratio

11. Revision history

Table 11. Revision history

Document ID	Release date	Data sheet status	Change notice	Supersedes
BLF888D_BLF888DS v.4	20160218	Product data sheet	-	BLF888D_BLF888DS#3
Modifications:	Table 8 on page 3: unit of last row has been corrected from “dB” to “W”			
BLF888D_BLF888DS#3	20150901	Product data sheet	-	BLF888D_BLF888DS v.2
BLF888D_BLF888DS v.2	20140627	Product data sheet	-	BLF888D_BLF888DS v.1
BLF888D_BLF888DS v.1	20140305	Objective data sheet	-	-

12. Legal information

12.1 Data sheet status

Document status ^{[1][2]}	Product status ^[3]	Definition
Objective [short] data sheet	Development	This document contains data from the objective specification for product development.
Preliminary [short] data sheet	Qualification	This document contains data from the preliminary specification.
Product [short] data sheet	Production	This document contains the product specification.

[1] Please consult the most recently issued document before initiating or completing a design.

[2] The term 'short data sheet' is explained in section "Definitions".

[3] The product status of device(s) described in this document may have changed since this document was published and may differ in case of multiple devices. The latest product status information is available on the Internet at URL <http://www.ampleon.com>.

12.2 Definitions

Draft — The document is a draft version only. The content is still under internal review and subject to formal approval, which may result in modifications or additions. Ampleon does not give any representations or warranties as to the accuracy or completeness of information included herein and shall have no liability for the consequences of use of such information.

Short data sheet — A short data sheet is an extract from a full data sheet with the same product type number(s) and title. A short data sheet is intended for quick reference only and should not be relied upon to contain detailed and full information. For detailed and full information see the relevant full data sheet, which is available on request via the local Ampleon sales office. In case of any inconsistency or conflict with the short data sheet, the full data sheet shall prevail.

Product specification — The information and data provided in a Product data sheet shall define the specification of the product as agreed between Ampleon and its customer, unless Ampleon and customer have explicitly agreed otherwise in writing. In no event however, shall an agreement be valid in which the Ampleon product is deemed to offer functions and qualities beyond those described in the Product data sheet.

12.3 Disclaimers

Limited warranty and liability — Information in this document is believed to be accurate and reliable. However, Ampleon does not give any representations or warranties, expressed or implied, as to the accuracy or completeness of such information and shall have no liability for the consequences of use of such information. Ampleon takes no responsibility for the content in this document if provided by an information source outside of Ampleon.

In no event shall Ampleon be liable for any indirect, incidental, punitive, special or consequential damages (including - without limitation - lost profits, lost savings, business interruption, costs related to the removal or replacement of any products or rework charges) whether or not such damages are based on tort (including negligence), warranty, breach of contract or any other legal theory.

Notwithstanding any damages that customer might incur for any reason whatsoever, Ampleon's aggregate and cumulative liability towards customer for the products described herein shall be limited in accordance with the *Terms and conditions of commercial sale* of Ampleon.

Right to make changes — Ampleon reserves the right to make changes to information published in this document, including without limitation specifications and product descriptions, at any time and without notice. This document supersedes and replaces all information supplied prior to the publication hereof.

Suitability for use — Ampleon products are not designed, authorized or warranted to be suitable for use in life support, life-critical or safety-critical systems or equipment, nor in applications where failure or malfunction of an

Ampleon product can reasonably be expected to result in personal injury, death or severe property or environmental damage. Ampleon and its suppliers accept no liability for inclusion and/or use of Ampleon products in such equipment or applications and therefore such inclusion and/or use is at the customer's own risk.

Applications — Applications that are described herein for any of these products are for illustrative purposes only. Ampleon makes no representation or warranty that such applications will be suitable for the specified use without further testing or modification.

Customers are responsible for the design and operation of their applications and products using Ampleon products, and Ampleon accepts no liability for any assistance with applications or customer product design. It is customer's sole responsibility to determine whether the Ampleon product is suitable and fit for the customer's applications and products planned, as well as for the planned application and use of customer's third party customer(s). Customers should provide appropriate design and operating safeguards to minimize the risks associated with their applications and products.

Ampleon does not accept any liability related to any default, damage, costs or problem which is based on any weakness or default in the customer's applications or products, or the application or use by customer's third party customer(s). Customer is responsible for doing all necessary testing for the customer's applications and products using Ampleon products in order to avoid a default of the applications and the products or of the application or use by customer's third party customer(s). Ampleon does not accept any liability in this respect.

Limiting values — Stress above one or more limiting values (as defined in the Absolute Maximum Ratings System of IEC 60134) will cause permanent damage to the device. Limiting values are stress ratings only and (proper) operation of the device at these or any other conditions above those given in the Recommended operating conditions section (if present) or the Characteristics sections of this document is not warranted. Constant or repeated exposure to limiting values will permanently and irreversibly affect the quality and reliability of the device.

Terms and conditions of commercial sale — Ampleon products are sold subject to the general terms and conditions of commercial sale, as published at <http://www.ampleon.com/terms>, unless otherwise agreed in a valid written individual agreement. In case an individual agreement is concluded only the terms and conditions of the respective agreement shall apply. Ampleon hereby expressly objects to applying the customer's general terms and conditions with regard to the purchase of Ampleon products by customer.

No offer to sell or license — Nothing in this document may be interpreted or construed as an offer to sell products that is open for acceptance or the grant, conveyance or implication of any license under any copyrights, patents or other industrial or intellectual property rights.

Export control — This document as well as the item(s) described herein may be subject to export control regulations. Export might require a prior authorization from competent authorities.

Non-automotive qualified products — Unless this data sheet expressly states that this specific Ampleon product is automotive qualified, the product is not suitable for automotive use. It is neither qualified nor tested in accordance with automotive testing or application requirements. Ampleon accepts no liability for inclusion and/or use of non-automotive qualified products in automotive equipment or applications.

In the event that customer uses the product for design-in and use in automotive applications to automotive specifications and standards, customer (a) shall use the product without Ampleon's warranty of the product for such automotive applications, use and specifications, and (b) whenever customer uses the product for automotive applications beyond Ampleon's specifications such use shall be solely at customer's own risk, and (c) customer fully indemnifies Ampleon for any liability, damages or failed product claims resulting from customer design and use of the product for automotive applications beyond Ampleon's standard warranty and Ampleon's product specifications.

Translations — A non-English (translated) version of a document is for reference only. The English version shall prevail in case of any discrepancy between the translated and English versions.

12.4 Licenses

ICs with DVB-T or DVB-T2 functionality

Use of this product in any manner that complies with the DVB-T or the DVB-T2 standard may require licenses under applicable patents of the DVB-T respectively the DVB-T2 patent portfolio, which license is available from Sisvel S.p.A., Via Sestriere 100, 10060 None (TO), Italy, and under applicable patents of other parties.

12.5 Trademarks

Notice: All referenced brands, product names, service names and trademarks are the property of their respective owners.

Any reference or use of any 'NXP' trademark in this document or in or on the surface of Ampleon products does not result in any claim, liability or entitlement vis-à-vis the owner of this trademark. Ampleon is no longer part of the NXP group of companies and any reference to or use of the 'NXP' trademarks will be replaced by reference to or use of Ampleon's own trademarks.

13. Contact information

For more information, please visit: <http://www.ampleon.com>

For sales office addresses, please visit: <http://www.ampleon.com/sales>

14. Contents

1	Product profile	1
1.1	General description	1
1.2	Features and benefits	1
1.3	Applications	1
2	Pinning information	2
3	Ordering information	2
4	Limiting values	2
5	Thermal characteristics	3
6	Characteristics	3
7	Test information	4
7.1	Ruggedness in Doherty operation	4
7.2	Test circuit	4
7.3	Graphical data	5
7.3.1	1-Tone CW pulsed	5
8	Package outline	7
9	Handling information	9
10	Abbreviations	9
11	Revision history	9
12	Legal information	10
12.1	Data sheet status	10
12.2	Definitions	10
12.3	Disclaimers	10
12.4	Licenses	11
12.5	Trademarks	11
13	Contact information	11
14	Contents	12

Please be aware that important notices concerning this document and the product(s) described herein, have been included in section 'Legal information'.

© Ampleon Netherlands B.V. 2016.

All rights reserved.

For more information, please visit: <http://www.ampleon.com>

For sales office addresses, please visit: <http://www.ampleon.com/sales>

Date of release: 18 February 2016

Document identifier: BLF888D_BLF888DS