

Detailed information for: S204P-K25

This page contains technical data sheet, documents library and links to offering related to this product. If you require any other information, please contact us using form located at the bottom of the page.

 [Print...](#)
 [Print to Pdf...](#)

 [Data Sheet](#)

 [Documentation](#)



S204P-K25

General Information

Extended Product Type: S204P-K25

Type:

Product ID: 2CDS284001R0517

EAN: 4016779592963

Catalog Description: Miniature Circuit Breaker - S200P - 4P - K - 25 ampere

Long Description: System pro M compact S200P miniature circuit breakers are current limiting. They have two different tripping mechanisms, the delayed thermal tripping mechanism for overload protection and the electromechanic tripping mechanism for short circuit protection. They are available in different characteristics (B,C,D,K,Z), configurations (1P,1P+N,2P,3P,3P+N,4P), breaking capacities (up to 25 kA at 230/400 V AC) and rated currents (up to 63A). All MCBS of the product range S200P comply with IEC/EN 60898-1, IEC/EN 609 47-2, UL1077 and CSA 22.2 No. 235, allowing the use for residential, commercial and industrial applications. Bottom-fitting auxiliary contact can be mounted on S200P to save 50% space.



Categories

Products » Low Voltage Products and Systems » Modular DIN Rail Products » Miniature Circuit Breakers MCBS



+ Accessories

Ordering

Minimum Order Quantity: 1 piece

Customs Tariff Number: 85362010

Popular Downloads

Data Sheet, Technical Information: [9AKK106930A8017](#)

Instructions and Manuals: [2CSC400002D0208](#)

Dimensions

Product Net Width:	70 mm
Product Net Depth / Length:	69 mm
Product Net Height:	88 mm
Product Net Weight:	0.56 kg
Technical	
Standards:	CSA 22.2 No. 235 IEC/EN 60947-2 UL 1077
Number of Poles:	4
Tripping Characteristic:	K
Rated Current (I_n):	25 A
Rated Operational Voltage:	acc. to IEC 60947-2 400 V AC
Power Loss:	14 W at Rated Operating Conditions per Pole 3.5 W
Rated Insulation Voltage (U_i):	acc. to IEC/EN 60664-1 440 V
Operational Voltage:	Maximum (Incl. Tolerance) 440 V AC
Rated Frequency (f):	50 Hz 60 Hz
Rated Short-Circuit Capacity (I_{cn}):	25 kA
Rated Ultimate Short-Circuit Breaking Capacity (I_{cu}):	(400 V AC) 25 kA
Rated Service Short-Circuit Breaking Capacity (I_{cs}):	(400 V AC) 12.5 kA
Energy Limiting Class:	3
Overvoltage Category:	III
Pollution Degree:	3
Rated Impulse Withstand Voltage (U_{imp}):	4 kV (6.2 kV @ sea level) kV (5.0 kV @ 2000 m) kV
Dielectric Test Voltage:	50 / 60 Hz, 1 min: 2 kV
Housing Material:	Insulation Group II, RAL 7035
Actuator Type:	Insulation group II, black, sealable
Contact Position Indication:	Red ON / Green OFF
Degree of Protection:	IP20
Remarks:	IP40 in enclosure with cover
Electrical Endurance:	20000 AC cycle
Mechanical Endurance (N_{endu}):	20000 cycle
Terminal Type:	Screw Terminals
Screw Terminal Type:	Failsafe Bi-directional Cylinder-lift Terminal
Connecting Capacity:	Busbar 10 / 10 mm ² Flexible with Ferrule 0.75 ... 16 mm ² Flexible 0.75 ... 16 mm ² Rigid 0.75 ... 25 mm ² Stranded 0.75 ... 25 mm ²
Tightening Torque:	2.8 N·m
Recommended Screw Driver:	Pozidriv 2

Mounting on DIN Rail:	TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Mounting Position:	Any
Environmental	
Ambient Air Temperature:	Operation -25 ... +55 °C Storage -40 ... +70 °C
Resistance to Shock acc. to IEC 60068-2-27: 25g / 2 shocks / 13 ms	
Resistance to Vibrations acc. to IEC 60068-2-6: 5g, 20 cycles at 5 ... 150 ... 5 Hz with load 0.8 In	
Environmental Conditions:	28 cycles with 55 °C / 90-96 % and 25 °C / 95-100 %
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
Technical UL/CSA	
Maximum Operating Voltage UL/CSA:	480Y/277 V AC
Connecting Capacity UL/CSA:	Busbar 18-8 AWG Conductor 18-4 AWG
Tightening Torque UL/CSA:	25 in·lb
Interrupting Rating acc. to UL1077:	(480Y / 277 V AC) 10 kA
Certificates and Declarations (Document Number)	
Declaration of Conformity - CE:	<u>2CDK403003D0402</u>
Environmental Information:	<u>2CDK400030D0201</u>
Instructions and Manuals:	<u>2CSC400002D0208</u>
RoHS Information:	<u>2CDK400003K0201</u>
Container Information	
Package Level 1 Units:	1 piece
Package Level 1 Width:	92 mm
Package Level 1 Depth / Length:	78 mm
Package Level 1 Height:	80 mm
Package Level 1 Gross Weight:	0.57 kg
Package Level 1 EAN:	4016779612715
Classifications	
Object Classification Code:	F
ETIM 4:	EC000042 - Miniature circuit breaker (MCB)
ETIM 5:	EC000042 - Miniature circuit breaker (MCB)
ETIM 6:	EC000042 - Miniature circuit breaker (MCB)
ETIM 7:	EC000042 - Miniature circuit breaker (MCB)
eClass:	7.0 27141901
UNSPSC:	39121614

Contact information

What would you like to do?

I need more information

ABB Sales

Submit your inquiry

Country / region

United States of America 

Name

Company

E-Mail

Phone

Zip code

Your message

[→ Privacy policy](#)

[Cancel](#)

Send message

Your local ABB Sales Team

Name

Customer Support

 [Close](#)