

DK-SERIES DKZA DK5 24VDC 10-100MS

Weidmüller Interface GmbH & Co. KG
Klingenbergstraße 16
D-32758 Detmold
Germany
Fon: +49 5231 14-0
Fax: +49 5231 14-2083
www.weidmueller.com

Technical data

Dimensions

Length	77 mm	Width	6 mm
Height	62 mm		

Temperature

Ambient temperature (operational)	-25 °C...+50 °C	Storage temperature	-40 °C...+85 °C
-----------------------------------	-----------------	---------------------	-----------------

Input

Rated voltage	300 V	Rated control voltage	24 V DC ±20 %
Rated current DC	Approx. 11 mA	Min. pulse duration	2 ms
Control voltage	24 V DC ± 20 %	Time ranges	0.01 s - 0.1 s

Output

Continuous current	0.1 A	Max. switching current	100 mA
Switch-off delay	10 ... 100 ms (adjustable)	Switching voltage DC, max.	48 V

Contact data

Contact design	NO contact	No. of contacts	1
----------------	------------	-----------------	---

Rated data

Conductor connection system	Screw connection	DIN Rail compatibility	TS 32 TS 35
Humidity	40°C / 93% rel. humidity, no condensation	Solid, max.	4 mm ²

Insulation coordination (EN 50 178)

Clearance and creepage distances for control/load side	≥ 5.5 mm	Dielectric strength for control side - load side	4 kV
Impulse withstand voltage	6 kV	Overvoltage category	IV
Pollution severity	2	Rated voltage	300 V

Other technical data

Version	Timing relay
---------	--------------

Approvals

Approvals institutes	CE
----------------------	----

Classifications

ETIM 2.0	EC001439	ETIM 3.0	EC001439
eClass 5.1	27-14-23-10	eClass 6.0	27-14-23-10

Notes

Note, technical data	For mounting on TS 32/35 rails
----------------------	--------------------------------