





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NO.	MAX. BUNDLE DIA [mm]	LENGTH ±.1 [2]
MSC2W38T15-L6	2" [51]	11.8" [300]
MSC4W38T15-L6	4" [102]	18.0" [457]
MSC6W38T15-L6	6" [152]	24.4" [620]
MSC8W38T15-L6	8" [203]	30.7" [780]
MSC10W38T15-L6	10" [254]	37.0" [940]



NOTES:

1. APPLICATION TOOLS: BT2MS75, BT2HT
2. ALL DIMENSIONS IN BRACKETS [] ARE MILLIMETERS.
3. BASE MATERIAL: 316 STAINLESS STEEL.
4. 100% COATED WITH BLACK NYLON OR POLYESTER.
5. COATING THICKNESS: .003/.005 [.076/.127] PER SIDE.
6. TOLERANCES (UNLESS OTHERWISE SPECIFIED):
 .X ± .03 [.8]
 .XX ± .02 [.5]
 .XXX ± .007 [.18]

							TITLE						
							COATED METAL STRAPPING .375" [9.52] WIDE						
							CUSTOMER DRAWING						
							ITEM REVISION NAME			N41167BS/02			
							DATASET FILE NAME			N41167BS_DC/02A			
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]						MATERIAL: SEE NOTES
							.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °						
02A	4/13	JAMB	MIM	RGR0	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO	SSECN01047	 THIRD ANGLE PROJECTION						DRAWING NUMBER: N41167BS_DC
01A	10/08	JAMB	SKB	---	ORIG CAD FILE SPEC WAS S41167_01. NOTE 1: APPLICATION TOOL BT1HT REPLACED BY BT2HT	-----							
01	10/03	BRH	EJD	JJB	DRAWING RELEASED	11159							
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SIZE		
							BRH	10/03	EJD	1:1	A		