

1		2		3		4		5	
						TECHNICAL CHARACTERISTICS			
						MATERIAL			
						INSULATOR MATERIAL: PET (WHITE)			
						SUPPORT TAPE: PET (BLUE)			
						CONTACT MATERIAL: COPPER			
						CONTACT PLATING: TIN			
						QUALITY CLASS: 20 MATING CYCLES MIN.			
						PITCH: 1.00 MM			
						ENVIRONMENTAL			
						OPERATING TEMPERATURE: -30°C UP TO 85°C			
						HEAT RESISTANCE: 105°C x 95 HRS			
						FLAMMABILITY RATING UL SUB.758			
						MOISTURE RESISTANCE: 40°C, 95% RH x 96 HRS			
						COMPLIANCE: LEAD FREE AND ROHS			
						ELECTRICAL			
						CURRENT RATING: 1.0 A MAX			
						WORKING VOLTAGE: 60V			
						INSULATION RESISTANCE: >1000 MOHM/M (500 VDC)			
						DIELECTRIC STRENGTH: 500 VAC/MN NO BREAKDOWN			
						CONDUCTOR RESISTANCE: <0.33 OHM/M			
						CONTACT RESISTANCE: <20 mOHMS			
						STANDARD			
						UL CERTIFIED: E328849			
						MECHANICAL			
						ELONGATION OF INSULATOR: > 60 %			
						TENSIL STRENGTH OF INSULATION: >3.5KG/MM²			
						FLEXING TEST: 180° >20 TIMES			
						ABRASION: >10000 TIMES			
						PULL/OUT: >20 TIMES			
						PACKAGING			
						BAG			
						DIMENSION & TOLERANCE			
						W= (N+1) x P			
						Pt=(N-1) x P			